

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332830-927

Luminaire Tested: **S124DIW-S1020D1560U927-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332830-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIW-S1020D1560U927-4F0-1E-UDD-A1  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1020 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7937.1 lumens  
Efficiency: N/A  
Efficacy: 103.6 lumens/watt  
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 76.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332830-927

CATALOG NUMBER: S124DIW-S1020D1560U927-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P332830-927

CATALOG NUMBER: S124DIW-S1020D1560U927-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	46				
1	97	93	89	86	89	85	82	79	71	69	67	58	57	55	47	46	45	39				
2	89	81	75	70	81	75	70	65	63	59	56	52	49	47	41	40	38	33				
3	81	72	64	59	74	66	60	55	56	51	47	46	42	40	37	34	33	28				
4	74	64	56	50	68	59	52	47	49	44	40	41	37	34	33	30	28	24				
5	68	57	49	43	62	52	45	40	44	39	35	37	33	30	30	27	25	21				
6	63	51	43	37	57	47	40	35	40	35	30	33	29	26	27	24	22	19				
7	58	46	38	33	53	43	36	31	36	31	27	30	26	23	25	22	19	17				
8	54	42	34	29	49	39	32	27	33	28	24	28	24	21	23	20	17	15				
9	50	38	31	26	46	35	29	24	30	25	21	26	21	19	21	18	16	14				
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	16	14	12				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	10672	10672	10672	10672
5°	12568	10699	9444	10699
10°	15048	10653	8502	10653
15°	17804	10546	7809	10546
20°	19826	10436	7189	10436
25°	20147	10273	6762	10273
30°	17143	10118	6626	10118
35°	13180	9866	6628	9866
40°	10273	9569	6752	9569
45°	8566	9122	6865	9122
50°	7538	8577	7097	8577
55°	6906	7924	7385	7924
60°	6471	7340	7727	7340
65°	6025	6684	8013	6684
70°	5507	6035	8195	6035
75°	4919	5312	8097	5312
80°	4124	4351	7843	4351
85°	3047	3149	7503	3149



TEST NUMBER: P332830-927

CATALOG NUMBER: S124DIW-S1020D1560U927-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	128.8	1.6
10°-20°	397.0	5.0
20°-30°	629.5	7.9
30°-40°	700.6	8.8
40°-50°	637.7	8.0
50°-60°	521.1	6.6
60°-70°	372.0	4.7
70°-80°	204.9	2.6
80°-90°	60.5	0.8
90°-100°	101.9	1.3
100°-110°	301.8	3.8
110°-120°	512.2	6.5
120°-130°	675.4	8.5
130°-140°	758.5	9.6
140°-150°	745.3	9.4
150°-160°	626.9	7.9
160°-170°	417.1	5.3
170°-180°	146.1	1.8
0°-30°	1155.3	14.6
0°-40°	1855.8	23.4
0°-60°	3014.6	38.0
0°-90°	3652.1	46.0
90°-120°	915.8	11.5
90°-150°	3095.0	39.0
90°-180°	4285.0	54.0
0°-180°	7937.1	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1322	1322	1322	1322	1322	
5°	1551	1320	1165	1320	1551	158
15°	2130	1262	934	1262	2130	602
25°	2262	1153	759	1153	2262	997
35°	1337	1001	672	1001	1337	849
45°	750	799	601	799	750	591
55°	491	563	525	563	491	443
65°	315	350	420	350	315	312
75°	158	170	260	170	158	168
85°	33	34	81	34	33	41
90°	36	4	36	4	36	19
95°	94	72	94	72	94	98
105°	291	278	291	278	291	307
115°	516	521	516	521	516	510
125°	752	758	752	758	752	671
135°	980	978	980	978	980	756
145°	1190	1188	1190	1188	1190	744
155°	1360	1362	1360	1362	1360	626
165°	1479	1482	1479	1482	1479	416
175°	1535	1542	1535	1542	1535	146
180°	1544	1544	1544	1544	1544	



TEST NUMBER: P332830-927

CATALOG NUMBER: S124DIW-S1020D1560U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0
2.5°	1407.0	1406.6	1402.2	1401.3	1398.2	1394.3	1393.4	1386.4	1372.4	1365.8	1364.1
5°	1550.9	1561.9	1547.6	1544.9	1543.3	1525.2	1515.8	1504.9	1479.7	1464.9	1453.4
7.5°	1722.7	1723.9	1717.8	1712.7	1698.8	1683.0	1659.4	1634.2	1604.2	1573.0	1549.4
10°	1835.7	1840.1	1833.0	1831.8	1804.0	1786.4	1751.4	1721.8	1687.8	1650.0	1615.6
12.5°	1954.9	1948.7	1945.1	1921.7	1916.5	1884.5	1843.8	1813.4	1761.0	1717.5	1671.6
15°	2130.3	2118.3	2110.6	2078.3	2062.4	2018.1	1974.8	1941.4	1873.0	1807.8	1758.5
17.5°	2233.2	2245.4	2227.6	2214.3	2173.3	2142.1	2097.9	2027.8	1974.3	1893.3	1831.1
20°	2307.8	2308.8	2299.0	2285.3	2253.0	2213.6	2165.4	2088.7	2024.7	1944.1	1858.7
22.5°	2327.9	2328.1	2323.9	2311.1	2286.7	2254.7	2206.1	2142.1	2064.5	1977.0	1891.6
25°	2261.8	2259.5	2264.5	2278.7	2269.4	2259.5	2231.7	2184.0	2111.7	2019.1	1927.1
27.5°	2015.9	2031.1	2058.9	2094.0	2127.7	2153.5	2160.7	2150.9	2106.1	2030.0	1933.6
30°	1839.0	1857.6	1878.4	1913.4	1981.3	2020.2	2063.0	2095.2	2077.2	2016.4	1926.6
32.5°	1644.5	1649.1	1680.0	1719.8	1782.0	1856.8	1924.5	1990.1	2011.9	1980.1	1905.1
35°	1337.4	1345.0	1378.4	1417.8	1494.0	1585.4	1687.3	1778.2	1853.2	1883.3	1845.0
37.5°	1091.3	1113.3	1136.9	1179.3	1246.3	1328.6	1434.5	1552.1	1664.0	1738.8	1751.6
40°	974.8	988.5	1005.4	1037.8	1094.7	1175.8	1266.7	1401.4	1520.3	1627.6	1662.6
42.5°	882.8	890.8	901.2	930.4	973.8	1054.4	1137.4	1255.9	1375.2	1503.6	1562.3
45°	750.3	758.5	776.0	793.0	825.9	881.7	958.9	1056.4	1176.3	1300.1	1408.5
47.5°	654.5	659.8	670.2	688.4	716.3	753.1	815.9	897.4	1008.5	1128.7	1244.2
50°	600.2	604.6	612.8	629.2	650.6	683.4	734.9	811.0	898.1	1019.1	1132.5
52.5°	557.3	559.0	565.1	576.2	593.2	620.8	663.1	726.0	807.0	914.9	1027.8
55°	490.7	492.9	498.4	506.6	521.3	538.8	571.2	618.3	689.0	782.6	880.6
57.5°	435.9	437.4	442.0	445.2	457.4	471.7	496.5	530.1	583.7	663.1	750.6
60°	400.8	399.8	405.3	408.0	416.2	428.3	447.4	479.7	526.2	590.3	670.8
62.5°	366.7	365.2	369.8	373.4	378.1	388.4	404.0	429.4	467.1	525.1	594.6
65°	315.4	313.2	316.0	320.4	324.7	330.3	341.7	364.2	394.3	435.9	489.0
67.5°	264.0	266.3	266.7	268.9	271.4	278.8	286.8	302.6	323.8	357.2	402.2
70°	233.3	233.9	236.1	236.1	237.7	244.2	250.8	260.2	280.9	311.6	348.3
72.5°	202.6	204.9	204.1	205.8	207.0	211.4	216.2	225.1	242.8	265.6	296.6
75°	157.7	159.4	159.4	159.9	161.5	163.2	167.0	173.6	186.2	203.2	224.5
77.5°	115.0	115.3	116.0	118.0	118.0	120.6	123.4	128.7	134.9	146.6	159.5
80°	88.7	89.8	89.3	90.4	90.4	92.5	93.6	100.2	103.0	110.6	121.0
82.5°	65.0	66.1	66.1	67.6	68.4	68.9	70.4	73.0	75.8	82.5	86.8
85°	32.9	34.0	32.9	34.0	35.6	36.1	37.8	38.3	40.6	42.1	46.0
87.5°	16.8	18.0	17.9	18.2	19.0	19.3	19.3	18.6	20.0	20.1	21.5
90°	35.8	35.3	34.8	34.2	33.7	32.6	31.1	29.5	27.9	26.3	24.2
92.5°	53.0	52.7	52.4	52.0	51.7	51.1	50.1	49.2	48.2	47.3	45.8
95°	94.3	94.3	94.3	94.3	94.3	94.0	93.2	92.4	91.6	90.8	89.0
97.5°	147.9	147.9	147.9	147.9	147.9	147.4	146.5	145.5	144.5	143.5	141.4
100°	185.1	185.1	185.1	185.1	185.1	184.9	184.3	183.8	183.3	182.8	180.4
102.5°	227.2	227.0	226.8	226.6	226.3	225.9	225.1	224.3	223.6	222.9	220.7
105°	291.4	290.7	289.9	289.1	288.3	287.5	286.7	285.9	285.1	284.3	283.2
107.5°	354.0	354.1	354.2	354.2	354.3	353.9	353.2	352.4	351.6	350.9	350.8
110°	398.9	398.2	397.4	396.6	395.8	395.6	396.2	396.7	397.2	397.8	398.0



TEST NUMBER: P332830-927

CATALOG NUMBER: S124DIW-S1020D1560U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	444.8	444.7	444.5	444.3	444.2	444.2	444.3	444.3	444.5	444.6	445.0
115°	516.0	516.3	516.6	516.8	517.1	517.4	517.6	517.8	518.2	518.4	519.0
117.5°	583.8	584.4	584.9	585.4	586.0	586.7	587.6	588.5	589.4	590.3	590.7
120°	635.5	634.9	634.4	633.9	633.3	633.7	635.1	636.4	637.7	639.1	639.8
122.5°	678.5	679.5	680.4	681.4	682.3	683.3	684.1	685.0	686.0	686.8	687.2
125°	752.5	753.0	753.6	754.1	754.6	755.2	755.7	756.2	756.8	757.3	757.6
127.5°	821.1	821.5	822.0	822.4	822.8	823.2	823.8	824.3	824.8	825.4	825.9
130°	866.0	867.0	868.2	869.2	870.2	871.0	871.6	872.1	872.7	873.1	873.1
132.5°	913.8	914.2	914.7	915.0	915.4	915.9	916.5	917.0	917.6	918.1	918.3
135°	979.5	980.2	981.0	981.8	982.6	983.3	983.9	984.4	984.9	985.5	985.5
137.5°	1048.5	1048.4	1048.2	1048.1	1047.9	1048.1	1048.8	1049.6	1050.2	1050.9	1050.5
140°	1090.6	1090.8	1091.1	1091.4	1091.6	1091.9	1092.2	1092.4	1092.7	1093.0	1093.0
142.5°	1132.6	1132.7	1132.7	1132.7	1132.8	1132.9	1132.9	1133.0	1133.1	1133.1	1133.3
145°	1189.7	1190.5	1191.3	1192.1	1192.9	1193.4	1193.7	1194.0	1194.2	1194.5	1194.2
147.5°	1247.5	1247.8	1248.1	1248.3	1248.6	1248.8	1249.0	1249.3	1249.4	1249.7	1249.9
150°	1282.9	1283.2	1283.4	1283.7	1284.0	1284.0	1284.0	1284.0	1284.0	1284.0	1284.0
152.5°	1315.3	1316.1	1316.8	1317.4	1318.1	1318.1	1317.5	1316.8	1316.2	1315.6	1315.4
155°	1360.5	1361.6	1362.6	1363.7	1364.8	1364.8	1363.7	1362.6	1361.6	1360.5	1360.8
157.5°	1400.9	1401.8	1402.7	1403.6	1404.5	1404.5	1403.7	1403.0	1402.2	1401.4	1401.4
160°	1423.8	1425.1	1426.5	1427.8	1429.1	1429.4	1428.6	1427.8	1427.0	1426.2	1426.5
162.5°	1447.7	1449.1	1450.4	1451.7	1453.0	1452.9	1451.5	1450.1	1448.7	1447.2	1447.5
165°	1478.8	1479.8	1480.9	1481.9	1483.0	1482.7	1481.1	1479.6	1478.0	1476.4	1476.9
167.5°	1500.9	1502.6	1504.3	1505.9	1507.6	1507.6	1506.0	1504.4	1502.8	1501.3	1501.2
170°	1513.4	1515.3	1517.1	1519.0	1520.8	1521.0	1519.4	1517.8	1516.2	1514.6	1514.3
172.5°	1523.9	1525.7	1527.6	1529.5	1531.4	1531.4	1529.5	1527.8	1526.0	1524.2	1524.1
175°	1534.9	1536.8	1538.7	1540.5	1542.4	1542.4	1540.5	1538.7	1536.8	1534.9	1535.2
177.5°	1540.6	1542.4	1544.0	1545.7	1547.4	1547.5	1546.0	1544.6	1543.1	1541.6	1541.6
180°	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4



TEST NUMBER: P332830-927

CATALOG NUMBER: S124DIW-S1020D1560U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0
2.5°	1364.5	1358.4	1354.0	1350.5	1340.8	1335.1	1330.8	1324.6	1317.6	1310.2	1301.0
5°	1441.9	1423.3	1409.6	1388.9	1369.1	1352.7	1335.7	1320.3	1301.7	1281.5	1266.7
7.5°	1523.3	1495.6	1460.2	1429.3	1394.7	1364.6	1337.7	1310.0	1281.4	1253.5	1228.0
10°	1575.0	1539.4	1500.0	1453.4	1409.6	1370.7	1334.6	1299.6	1265.6	1231.6	1202.6
12.5°	1630.6	1586.3	1528.0	1473.6	1424.5	1372.5	1328.9	1285.9	1245.0	1209.3	1175.4
15°	1705.3	1641.2	1573.9	1501.1	1436.5	1375.7	1316.0	1261.8	1215.8	1168.6	1135.8
17.5°	1751.3	1672.0	1595.0	1518.9	1440.6	1364.0	1299.6	1237.0	1179.4	1132.7	1091.2
20°	1781.5	1702.6	1606.8	1530.7	1437.6	1358.7	1284.2	1214.7	1154.4	1104.6	1061.8
22.5°	1807.8	1716.7	1620.8	1520.6	1427.9	1344.3	1262.7	1192.8	1131.2	1078.7	1037.8
25°	1822.0	1717.4	1613.4	1513.7	1408.5	1309.4	1235.5	1153.3	1087.6	1032.3	988.5
27.5°	1823.5	1711.7	1593.9	1483.2	1374.7	1282.4	1189.1	1115.6	1047.4	989.0	946.9
30°	1818.7	1702.1	1575.6	1455.6	1346.6	1246.4	1165.4	1085.4	1015.9	957.8	914.0
32.5°	1803.4	1681.9	1551.9	1425.0	1312.0	1214.0	1130.4	1054.3	986.5	929.3	883.4
35°	1759.0	1639.1	1500.6	1368.6	1253.0	1153.9	1078.3	1001.1	933.2	878.9	834.6
37.5°	1689.7	1581.3	1440.4	1303.9	1190.3	1090.8	1015.9	946.1	884.9	829.8	784.3
40°	1629.2	1533.9	1392.7	1259.6	1136.9	1042.2	972.1	908.0	847.2	795.2	751.9
42.5°	1559.6	1476.5	1346.2	1205.2	1087.0	991.8	923.4	865.9	808.7	760.6	717.3
45°	1435.4	1380.6	1257.9	1127.6	1004.4	914.6	849.4	799.0	750.8	703.7	667.6
47.5°	1292.5	1265.4	1162.1	1038.3	921.4	832.8	776.3	729.8	687.5	647.6	615.8
50°	1196.6	1183.4	1094.2	974.8	863.1	779.8	722.9	682.9	646.7	611.7	581.6
52.5°	1101.9	1101.5	1021.0	911.7	808.3	728.2	671.6	634.3	602.9	574.5	547.4
55°	957.3	972.6	909.7	812.1	719.6	647.3	596.4	563.0	541.1	517.5	497.3
57.5°	824.4	849.9	797.9	712.0	634.9	568.2	523.9	498.8	475.5	461.2	446.5
60°	737.7	761.8	721.3	649.0	576.2	519.2	477.0	454.6	434.3	424.5	414.0
62.5°	660.6	682.1	652.0	585.0	521.8	467.0	431.4	409.9	396.2	385.4	378.5
65°	550.4	568.5	542.7	494.0	439.7	395.9	366.9	349.9	336.8	332.4	324.7
67.5°	444.9	461.4	447.4	406.0	362.5	329.4	306.7	290.3	282.6	278.8	273.3
70°	382.2	398.7	383.9	347.8	314.3	286.5	265.1	255.7	247.6	245.9	238.2
72.5°	329.2	340.4	325.7	297.4	268.8	245.3	228.7	219.0	214.7	211.8	207.6
75°	247.0	256.8	247.0	225.1	204.8	188.4	174.1	170.3	165.4	163.7	161.0
77.5°	174.8	183.3	175.8	162.1	146.9	134.3	126.6	121.7	120.6	117.7	119.1
80°	133.6	139.1	132.0	122.7	110.6	101.9	96.4	93.6	90.4	89.3	91.4
82.5°	95.9	98.4	94.7	88.5	79.5	73.8	70.1	66.9	66.2	66.5	66.5
85°	49.8	49.3	48.7	43.3	40.6	36.7	34.5	34.0	33.4	34.5	35.6
87.5°	21.1	21.1	20.2	18.0	16.1	14.2	13.2	12.1	13.2	14.2	15.2
90°	22.0	19.9	17.8	15.3	12.4	9.4	6.5	3.6	6.5	9.4	12.4
92.5°	44.4	42.9	41.4	39.0	35.6	32.2	28.9	25.6	28.9	32.2	35.6
95°	87.1	85.2	83.3	81.2	78.8	76.4	74.1	71.7	74.1	76.4	78.8
97.5°	139.2	137.0	134.9	132.8	130.9	129.0	127.1	125.2	127.1	129.0	130.9
100°	178.0	175.6	173.2	171.5	170.4	169.4	168.3	167.2	168.3	169.4	170.4
102.5°	218.6	216.3	214.2	212.9	212.5	212.1	211.6	211.2	211.6	212.1	212.5
105°	282.2	281.1	280.0	279.4	279.1	278.8	278.6	278.3	278.6	278.8	279.1
107.5°	350.6	350.5	350.3	350.1	349.7	349.4	349.1	348.8	349.1	349.4	349.7
110°	398.3	398.5	398.9	398.7	398.2	397.6	397.1	396.6	397.1	397.6	398.2





TEST NUMBER: P332830-927

CATALOG NUMBER: S124DIW-S1020D1560U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	445.5	446.0	446.5	446.7	446.6	446.5	446.4	446.2	446.4	446.5	446.6
115°	519.4	520.0	520.5	520.8	520.8	520.8	520.8	520.8	520.8	520.8	520.8
117.5°	591.0	591.4	591.8	591.9	591.7	591.4	591.2	591.0	591.2	591.4	591.7
120°	640.6	641.4	642.2	642.1	641.0	640.0	638.9	637.9	638.9	640.0	641.0
122.5°	687.5	687.9	688.3	688.2	687.9	687.5	687.0	686.6	687.0	687.5	687.9
125°	757.8	758.1	758.4	758.5	758.5	758.5	758.5	758.5	758.5	758.5	758.5
127.5°	826.2	826.6	827.1	826.9	826.1	825.3	824.5	823.7	824.5	825.3	826.1
130°	873.1	873.1	873.1	872.7	872.0	871.2	870.4	869.6	870.4	871.2	872.0
132.5°	918.5	918.7	918.9	918.8	918.1	917.6	917.0	916.4	917.0	917.6	918.1
135°	985.5	985.5	985.5	984.7	983.1	981.4	979.9	978.3	979.9	981.4	983.1
137.5°	1050.0	1049.6	1049.2	1048.6	1047.9	1047.1	1046.4	1045.7	1046.4	1047.1	1047.9
140°	1093.0	1093.0	1093.0	1092.7	1092.2	1091.6	1091.1	1090.6	1091.1	1091.6	1092.2
142.5°	1133.5	1133.7	1133.9	1133.8	1133.2	1132.7	1132.2	1131.6	1132.2	1132.7	1133.2
145°	1194.0	1193.7	1193.4	1192.8	1191.7	1190.6	1189.5	1188.5	1189.5	1190.6	1191.7
147.5°	1250.1	1250.3	1250.5	1250.0	1248.7	1247.4	1246.2	1244.9	1246.2	1247.4	1248.7
150°	1284.0	1284.0	1284.0	1283.6	1282.5	1281.4	1280.3	1279.3	1280.3	1281.4	1282.5
152.5°	1315.2	1314.9	1314.8	1314.3	1313.7	1313.0	1312.4	1311.8	1312.4	1313.0	1313.7
155°	1361.0	1361.3	1361.6	1361.7	1361.7	1361.7	1361.7	1361.7	1361.7	1361.7	1361.7
157.5°	1401.4	1401.5	1401.6	1401.8	1402.3	1402.8	1403.3	1403.7	1403.3	1402.8	1402.3
160°	1426.7	1427.0	1427.3	1427.5	1427.8	1428.1	1428.3	1428.6	1428.3	1428.1	1427.8
162.5°	1447.8	1448.0	1448.3	1448.7	1449.5	1450.2	1450.9	1451.5	1450.9	1450.2	1449.5
165°	1477.4	1478.0	1478.5	1479.2	1480.0	1480.7	1481.5	1482.3	1481.5	1480.7	1480.0
167.5°	1501.1	1501.1	1501.0	1501.6	1502.7	1503.8	1504.9	1506.0	1504.9	1503.8	1502.7
170°	1514.1	1513.8	1513.5	1514.1	1515.4	1516.7	1518.1	1519.4	1518.1	1516.7	1515.4
172.5°	1524.1	1524.0	1523.9	1524.5	1525.6	1526.7	1527.8	1528.9	1527.8	1526.7	1525.6
175°	1535.4	1535.7	1536.0	1536.8	1538.1	1539.4	1540.7	1542.1	1540.7	1539.4	1538.1
177.5°	1541.6	1541.6	1541.6	1542.1	1543.2	1544.3	1545.3	1546.3	1545.3	1544.3	1543.2
180°	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4



TEST NUMBER: P332830-927

CATALOG NUMBER: S124DIW-S1020D1560U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0
2.5°	1296.6	1292.7	1287.0	1279.1	1272.5	1265.5	1263.8	1261.1	1266.4	1261.9	1260.7
5°	1254.1	1242.6	1227.8	1210.9	1200.9	1186.8	1184.0	1178.5	1173.1	1172.5	1167.0
7.5°	1209.1	1192.2	1172.8	1155.6	1139.6	1123.9	1113.8	1111.6	1103.5	1098.8	1093.3
10°	1180.2	1159.4	1136.9	1120.5	1101.8	1085.4	1074.0	1067.4	1061.8	1055.8	1050.4
12.5°	1146.0	1123.9	1105.3	1087.6	1065.5	1053.0	1034.0	1022.6	1021.6	1021.7	1007.4
15°	1106.2	1084.3	1055.8	1030.6	1018.6	994.5	984.1	971.0	962.7	954.5	948.0
17.5°	1060.8	1033.5	1011.3	982.4	959.3	940.2	926.5	918.6	906.3	894.6	886.2
20°	1032.3	1003.3	979.7	949.0	923.8	900.3	888.8	877.9	868.5	858.7	849.4
22.5°	1003.4	973.0	944.2	914.4	891.0	866.2	855.1	840.2	831.3	825.9	816.5
25°	957.8	925.0	892.1	863.6	839.6	817.6	802.9	791.3	781.5	777.1	771.1
27.5°	908.3	875.7	843.9	811.6	784.3	768.3	756.5	747.8	742.2	736.3	733.6
30°	876.8	842.8	808.9	778.7	753.5	737.7	726.7	720.7	716.3	713.6	710.8
32.5°	844.8	811.3	775.5	748.1	725.5	711.4	703.1	697.0	694.8	693.9	692.8
35°	793.5	759.5	726.7	702.1	680.7	675.3	668.1	664.8	663.8	667.6	669.2
37.5°	743.9	712.4	682.1	658.2	644.3	636.3	633.8	634.0	637.9	641.3	645.2
40°	711.9	681.3	652.8	632.0	618.9	613.9	612.8	615.5	620.0	623.8	628.1
42.5°	680.8	650.6	624.7	605.2	596.0	591.5	592.2	594.9	601.1	605.8	612.4
45°	632.6	607.4	582.2	566.3	558.6	559.7	559.7	564.6	570.6	577.7	584.9
47.5°	587.1	561.7	541.0	527.6	523.6	522.7	525.8	532.2	540.8	549.6	559.6
50°	556.4	532.3	514.2	502.2	497.8	499.5	503.8	509.8	520.2	531.2	541.6
52.5°	525.3	503.4	486.6	475.5	472.4	475.4	479.7	489.3	498.4	510.2	522.8
55°	477.0	458.4	445.2	437.0	435.9	437.6	442.5	452.9	466.0	480.9	492.9
57.5°	428.9	413.4	401.3	395.6	396.2	397.7	405.8	418.2	432.2	448.0	463.5
60°	396.5	382.2	372.4	368.0	368.5	371.9	381.7	393.2	410.7	426.0	442.5
62.5°	365.8	353.3	343.9	340.0	339.2	346.4	355.8	367.8	385.3	402.4	420.2
65°	316.6	306.7	299.0	296.8	298.5	304.0	316.0	331.8	346.7	364.7	383.3
67.5°	268.3	260.2	255.0	256.0	257.9	266.0	276.2	289.8	306.6	325.3	343.7
70°	237.7	230.0	225.6	226.2	229.5	239.3	248.1	261.7	279.9	299.0	314.3
72.5°	206.1	201.1	197.2	199.5	202.7	209.5	220.5	234.2	250.1	267.9	284.1
75°	158.3	158.3	156.1	157.7	162.6	169.2	177.4	191.7	207.6	221.8	235.0
77.5°	117.4	116.2	117.6	119.6	122.5	130.2	139.7	149.8	161.8	176.0	186.9
80°	89.8	90.4	93.1	96.4	97.5	103.5	113.4	122.7	132.0	144.0	154.4
82.5°	67.5	68.0	69.5	73.6	74.7	81.2	87.5	96.8	105.3	113.4	122.0
85°	36.7	36.7	39.5	41.0	43.8	48.2	52.0	57.5	65.2	70.7	78.8
87.5°	17.1	17.6	19.7	21.1	22.8	25.4	26.6	31.8	33.8	36.3	40.5
90°	15.3	17.8	19.9	22.0	24.2	26.3	27.9	29.5	31.1	32.6	33.7
92.5°	39.0	41.4	42.9	44.4	45.8	47.3	48.2	49.2	50.1	51.1	51.7
95°	81.2	83.3	85.2	87.1	89.0	90.8	91.6	92.4	93.2	94.0	94.3
97.5°	132.8	134.9	137.0	139.2	141.4	143.5	144.5	145.5	146.5	147.4	147.9
100°	171.5	173.2	175.6	178.0	180.4	182.8	183.3	183.8	184.3	184.9	185.1
102.5°	212.9	214.2	216.3	218.6	220.7	222.9	223.6	224.3	225.1	225.9	226.3
105°	279.4	280.0	281.1	282.2	283.2	284.3	285.1	285.9	286.7	287.5	288.3
107.5°	350.1	350.3	350.5	350.6	350.8	350.9	351.6	352.4	353.2	353.9	354.3
110°	398.7	398.9	398.5	398.3	398.0	397.8	397.2	396.7	396.2	395.6	395.8



TEST NUMBER: P332830-927

CATALOG NUMBER: S124DIW-S1020D1560U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	446.7	446.5	446.0	445.5	445.0	444.6	444.5	444.3	444.3	444.2	444.2
115°	520.8	520.5	520.0	519.4	519.0	518.4	518.2	517.8	517.6	517.4	517.1
117.5°	591.9	591.8	591.4	591.0	590.7	590.3	589.4	588.5	587.6	586.7	586.0
120°	642.1	642.2	641.4	640.6	639.8	639.1	637.7	636.4	635.1	633.7	633.3
122.5°	688.2	688.3	687.9	687.5	687.2	686.8	686.0	685.0	684.1	683.3	682.3
125°	758.5	758.4	758.1	757.8	757.6	757.3	756.8	756.2	755.7	755.2	754.6
127.5°	826.9	827.1	826.6	826.2	825.9	825.4	824.8	824.3	823.8	823.2	822.8
130°	872.7	873.1	873.1	873.1	873.1	873.1	872.7	872.1	871.6	871.0	870.2
132.5°	918.8	918.9	918.7	918.5	918.3	918.1	917.6	917.0	916.5	915.9	915.4
135°	984.7	985.5	985.5	985.5	985.5	985.5	984.9	984.4	983.9	983.3	982.6
137.5°	1048.6	1049.2	1049.6	1050.0	1050.5	1050.9	1050.2	1049.6	1048.8	1048.1	1047.9
140°	1092.7	1093.0	1093.0	1093.0	1093.0	1093.0	1092.7	1092.4	1092.2	1091.9	1091.6
142.5°	1133.8	1133.9	1133.7	1133.5	1133.3	1133.1	1133.1	1133.0	1132.9	1132.9	1132.8
145°	1192.8	1193.4	1193.7	1194.0	1194.2	1194.5	1194.2	1194.0	1193.7	1193.4	1192.9
147.5°	1250.0	1250.5	1250.3	1250.1	1249.9	1249.7	1249.4	1249.3	1249.0	1248.8	1248.6
150°	1283.6	1284.0	1284.0	1284.0	1284.0	1284.0	1284.0	1284.0	1284.0	1284.0	1284.0
152.5°	1314.3	1314.8	1314.9	1315.2	1315.4	1315.6	1316.2	1316.8	1317.5	1318.1	1318.1
155°	1361.7	1361.6	1361.3	1361.0	1360.8	1360.5	1361.6	1362.6	1363.7	1364.8	1364.8
157.5°	1401.8	1401.6	1401.5	1401.4	1401.4	1401.4	1402.2	1403.0	1403.7	1404.5	1404.5
160°	1427.5	1427.3	1427.0	1426.7	1426.5	1426.2	1427.0	1427.8	1428.6	1429.4	1429.1
162.5°	1448.7	1448.3	1448.0	1447.8	1447.5	1447.2	1448.7	1450.1	1451.5	1452.9	1453.0
165°	1479.2	1478.5	1478.0	1477.4	1476.9	1476.4	1478.0	1479.6	1481.1	1482.7	1483.0
167.5°	1501.6	1501.0	1501.1	1501.1	1501.2	1501.3	1502.8	1504.4	1506.0	1507.6	1507.6
170°	1514.1	1513.5	1513.8	1514.1	1514.3	1514.6	1516.2	1517.8	1519.4	1521.0	1520.8
172.5°	1524.5	1523.9	1524.0	1524.1	1524.1	1524.2	1526.0	1527.8	1529.5	1531.4	1531.4
175°	1536.8	1536.0	1535.7	1535.4	1535.2	1534.9	1536.8	1538.7	1540.5	1542.4	1542.4
177.5°	1542.1	1541.6	1541.6	1541.6	1541.6	1541.6	1543.1	1544.6	1546.0	1547.5	1547.4
180°	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4



TEST NUMBER: P332830-927

CATALOG NUMBER: S124DIW-S1020D1560U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0
2.5°	1259.8	1258.9	1255.8	1255.5	1255.8	1258.9	1259.8	1260.7	1261.9	1266.4	1261.1
5°	1163.7	1161.0	1159.4	1165.4	1159.4	1161.0	1163.7	1167.0	1172.5	1173.1	1178.5
7.5°	1091.3	1089.2	1084.3	1082.8	1084.3	1089.2	1091.3	1093.3	1098.8	1103.5	1111.6
10°	1044.9	1042.7	1038.3	1037.2	1038.3	1042.7	1044.9	1050.4	1055.8	1061.8	1067.4
12.5°	1000.2	995.9	995.0	996.0	995.0	995.9	1000.2	1007.4	1021.7	1021.6	1022.6
15°	940.9	938.7	932.6	934.3	932.6	938.7	940.9	948.0	954.5	962.7	971.0
17.5°	882.3	879.7	872.4	878.8	872.4	879.7	882.3	886.2	894.6	906.3	918.6
20°	845.6	841.1	837.3	836.8	837.3	841.1	845.6	849.4	858.7	868.5	877.9
22.5°	810.5	806.6	806.2	802.6	806.2	806.6	810.5	816.5	825.9	831.3	840.2
25°	766.7	762.9	761.8	759.1	761.8	762.9	766.7	771.1	777.1	781.5	791.3
27.5°	733.1	731.2	729.2	730.1	729.2	731.2	733.1	733.6	736.3	742.2	747.8
30°	712.5	711.9	710.8	710.8	710.8	711.9	712.5	710.8	713.6	716.3	720.7
32.5°	695.4	695.3	695.9	695.9	695.9	695.3	695.4	692.8	693.9	694.8	697.0
35°	671.4	673.0	674.1	672.5	674.1	673.0	671.4	669.2	667.6	663.8	664.8
37.5°	649.7	651.3	652.9	654.7	652.9	651.3	649.7	645.2	641.3	637.9	634.0
40°	633.0	636.9	638.0	640.7	638.0	636.9	633.0	628.1	623.8	620.0	615.5
42.5°	617.3	621.5	624.4	625.0	624.4	621.5	617.3	612.4	605.8	601.1	594.9
45°	593.1	597.5	601.3	601.3	601.3	597.5	593.1	584.9	577.7	570.6	564.6
47.5°	568.0	574.3	578.2	579.2	578.2	574.3	568.0	559.6	549.6	540.8	532.2
50°	551.0	558.6	562.4	565.1	562.4	558.6	551.0	541.6	531.2	520.2	509.8
52.5°	534.2	541.9	547.1	548.5	547.1	541.9	534.2	522.8	510.2	498.4	489.3
55°	505.5	516.4	522.4	524.7	522.4	516.4	505.5	492.9	480.9	466.0	452.9
57.5°	478.3	488.4	495.4	497.0	495.4	488.4	478.3	463.5	448.0	432.2	418.2
60°	457.2	468.3	477.0	478.6	477.0	468.3	457.2	442.5	426.0	410.7	393.2
62.5°	435.8	447.2	455.1	459.4	455.1	447.2	435.8	420.2	402.4	385.3	367.8
65°	398.7	410.2	417.9	419.5	417.9	410.2	398.7	383.3	364.7	346.7	331.8
67.5°	358.1	369.6	374.7	377.9	374.7	369.6	358.1	343.7	325.3	306.6	289.8
70°	329.7	339.0	344.4	347.2	344.4	339.0	329.7	314.3	299.0	279.9	261.7
72.5°	297.2	307.0	313.4	313.9	313.4	307.0	297.2	284.1	267.9	250.1	234.2
75°	247.6	256.3	259.6	259.6	259.6	256.3	247.6	235.0	221.8	207.6	191.7
77.5°	195.9	200.4	204.6	205.5	204.6	200.4	195.9	186.9	176.0	161.8	149.8
80°	162.6	165.4	168.7	168.7	168.7	165.4	162.6	154.4	144.0	132.0	122.7
82.5°	128.5	130.8	134.0	133.6	134.0	130.8	128.5	122.0	113.4	105.3	96.8
85°	77.8	82.7	82.1	81.0	82.1	82.7	77.8	78.8	70.7	65.2	57.5
87.5°	41.9	42.5	43.9	44.8	43.9	42.5	41.9	40.5	36.3	33.8	31.8
90°	34.2	34.8	35.3	35.8	35.3	34.8	34.2	33.7	32.6	31.1	29.5
92.5°	52.0	52.4	52.7	53.0	52.7	52.4	52.0	51.7	51.1	50.1	49.2
95°	94.3	94.3	94.3	94.3	94.3	94.3	94.3	94.3	94.0	93.2	92.4
97.5°	147.9	147.9	147.9	147.9	147.9	147.9	147.9	147.9	147.4	146.5	145.5
100°	185.1	185.1	185.1	185.1	185.1	185.1	185.1	185.1	184.9	184.3	183.8
102.5°	226.6	226.8	227.0	227.2	227.0	226.8	226.6	226.3	225.9	225.1	224.3
105°	289.1	289.9	290.7	291.4	290.7	289.9	289.1	288.3	287.5	286.7	285.9
107.5°	354.2	354.2	354.1	354.0	354.1	354.2	354.2	354.3	353.9	353.2	352.4
110°	396.6	397.4	398.2	398.9	398.2	397.4	396.6	395.8	395.6	396.2	396.7



TEST NUMBER: P332830-927

CATALOG NUMBER: S124DIW-S1020D1560U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	444.3	444.5	444.7	444.8	444.7	444.5	444.3	444.2	444.2	444.3	444.3
115°	516.8	516.6	516.3	516.0	516.3	516.6	516.8	517.1	517.4	517.6	517.8
117.5°	585.4	584.9	584.4	583.8	584.4	584.9	585.4	586.0	586.7	587.6	588.5
120°	633.9	634.4	634.9	635.5	634.9	634.4	633.9	633.3	633.7	635.1	636.4
122.5°	681.4	680.4	679.5	678.5	679.5	680.4	681.4	682.3	683.3	684.1	685.0
125°	754.1	753.6	753.0	752.5	753.0	753.6	754.1	754.6	755.2	755.7	756.2
127.5°	822.4	822.0	821.5	821.1	821.5	822.0	822.4	822.8	823.2	823.8	824.3
130°	869.2	868.2	867.0	866.0	867.0	868.2	869.2	870.2	871.0	871.6	872.1
132.5°	915.0	914.7	914.2	913.8	914.2	914.7	915.0	915.4	915.9	916.5	917.0
135°	981.8	981.0	980.2	979.5	980.2	981.0	981.8	982.6	983.3	983.9	984.4
137.5°	1048.1	1048.2	1048.4	1048.5	1048.4	1048.2	1048.1	1047.9	1048.1	1048.8	1049.6
140°	1091.4	1091.1	1090.8	1090.6	1090.8	1091.1	1091.4	1091.6	1091.9	1092.2	1092.4
142.5°	1132.7	1132.7	1132.7	1132.6	1132.7	1132.7	1132.7	1132.8	1132.9	1132.9	1133.0
145°	1192.1	1191.3	1190.5	1189.7	1190.5	1191.3	1192.1	1192.9	1193.4	1193.7	1194.0
147.5°	1248.3	1248.1	1247.8	1247.5	1247.8	1248.1	1248.3	1248.6	1248.8	1249.0	1249.3
150°	1283.7	1283.4	1283.2	1282.9	1283.2	1283.4	1283.7	1284.0	1284.0	1284.0	1284.0
152.5°	1317.4	1316.8	1316.1	1315.3	1316.1	1316.8	1317.4	1318.1	1318.1	1317.5	1316.8
155°	1363.7	1362.6	1361.6	1360.5	1361.6	1362.6	1363.7	1364.8	1364.8	1363.7	1362.6
157.5°	1403.6	1402.7	1401.8	1400.9	1401.8	1402.7	1403.6	1404.5	1404.5	1403.7	1403.0
160°	1427.8	1426.5	1425.1	1423.8	1425.1	1426.5	1427.8	1429.1	1429.4	1428.6	1427.8
162.5°	1451.7	1450.4	1449.1	1447.7	1449.1	1450.4	1451.7	1453.0	1452.9	1451.5	1450.1
165°	1481.9	1480.9	1479.8	1478.8	1479.8	1480.9	1481.9	1483.0	1482.7	1481.1	1479.6
167.5°	1505.9	1504.3	1502.6	1500.9	1502.6	1504.3	1505.9	1507.6	1507.6	1506.0	1504.4
170°	1519.0	1517.1	1515.3	1513.4	1515.3	1517.1	1519.0	1520.8	1521.0	1519.4	1517.8
172.5°	1529.5	1527.6	1525.7	1523.9	1525.7	1527.6	1529.5	1531.4	1531.4	1529.5	1527.8
175°	1540.5	1538.7	1536.8	1534.9	1536.8	1538.7	1540.5	1542.4	1542.4	1540.5	1538.7
177.5°	1545.7	1544.0	1542.4	1540.6	1542.4	1544.0	1545.7	1547.4	1547.5	1546.0	1544.6
180°	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4



TEST NUMBER: P332830-927

CATALOG NUMBER: S124DIW-S1020D1560U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0
2.5°	1263.8	1265.5	1272.5	1279.1	1287.0	1292.7	1296.6	1301.0	1310.2	1317.6	1324.6
5°	1184.0	1186.8	1200.9	1210.9	1227.8	1242.6	1254.1	1266.7	1281.5	1301.7	1320.3
7.5°	1113.8	1123.9	1139.6	1155.6	1172.8	1192.2	1209.1	1228.0	1253.5	1281.4	1310.0
10°	1074.0	1085.4	1101.8	1120.5	1136.9	1159.4	1180.2	1202.6	1231.6	1265.6	1299.6
12.5°	1034.0	1053.0	1065.5	1087.6	1105.3	1123.9	1146.0	1175.4	1209.3	1245.0	1285.9
15°	984.1	994.5	1018.6	1030.6	1055.8	1084.3	1106.2	1135.8	1168.6	1215.8	1261.8
17.5°	926.5	940.2	959.3	982.4	1011.3	1033.5	1060.8	1091.2	1132.7	1179.4	1237.0
20°	888.8	900.3	923.8	949.0	979.7	1003.3	1032.3	1061.8	1104.6	1154.4	1214.7
22.5°	855.1	866.2	891.0	914.4	944.2	973.0	1003.4	1037.8	1078.7	1131.2	1192.8
25°	802.9	817.6	839.6	863.6	892.1	925.0	957.8	988.5	1032.3	1087.6	1153.3
27.5°	756.5	768.3	784.3	811.6	843.9	875.7	908.3	946.9	989.0	1047.4	1115.6
30°	726.7	737.7	753.5	778.7	808.9	842.8	876.8	914.0	957.8	1015.9	1085.4
32.5°	703.1	711.4	725.5	748.1	775.5	811.3	844.8	883.4	929.3	986.5	1054.3
35°	668.1	675.3	680.7	702.1	726.7	759.5	793.5	834.6	878.9	933.2	1001.1
37.5°	633.8	636.3	644.3	658.2	682.1	712.4	743.9	784.3	829.8	884.9	946.1
40°	612.8	613.9	618.9	632.0	652.8	681.3	711.9	751.9	795.2	847.2	908.0
42.5°	592.2	591.5	596.0	605.2	624.7	650.6	680.8	717.3	760.6	808.7	865.9
45°	559.7	559.7	558.6	566.3	582.2	607.4	632.6	667.6	703.7	750.8	799.0
47.5°	525.8	522.7	523.6	527.6	541.0	561.7	587.1	615.8	647.6	687.5	729.8
50°	503.8	499.5	497.8	502.2	514.2	532.3	556.4	581.6	611.7	646.7	682.9
52.5°	479.7	475.4	472.4	475.5	486.6	503.4	525.3	547.4	574.5	602.9	634.3
55°	442.5	437.6	435.9	437.0	445.2	458.4	477.0	497.3	517.5	541.1	563.0
57.5°	405.8	397.7	396.2	395.6	401.3	413.4	428.9	446.5	461.2	475.5	498.8
60°	381.7	371.9	368.5	368.0	372.4	382.2	396.5	414.0	424.5	434.3	454.6
62.5°	355.8	346.4	339.2	340.0	343.9	353.3	365.8	378.5	385.4	396.2	409.9
65°	316.0	304.0	298.5	296.8	299.0	306.7	316.6	324.7	332.4	336.8	349.9
67.5°	276.2	266.0	257.9	256.0	255.0	260.2	268.3	273.3	278.8	282.6	290.3
70°	248.1	239.3	229.5	226.2	225.6	230.0	237.7	238.2	245.9	247.6	255.7
72.5°	220.5	209.5	202.7	199.5	197.2	201.1	206.1	207.6	211.8	214.7	219.0
75°	177.4	169.2	162.6	157.7	156.1	158.3	158.3	161.0	163.7	165.4	170.3
77.5°	139.7	130.2	122.5	119.6	117.6	116.2	117.4	119.1	117.7	120.6	121.7
80°	113.4	103.5	97.5	96.4	93.1	90.4	89.8	91.4	89.3	90.4	93.6
82.5°	87.5	81.2	74.7	73.6	69.5	68.0	67.5	66.5	66.5	66.2	66.9
85°	52.0	48.2	43.8	41.0	39.5	36.7	36.7	35.6	34.5	33.4	34.0
87.5°	26.6	25.4	22.8	21.1	19.7	17.6	17.1	15.2	14.2	13.2	12.1
90°	27.9	26.3	24.2	22.0	19.9	17.8	15.3	12.4	9.4	6.5	3.6
92.5°	48.2	47.3	45.8	44.4	42.9	41.4	39.0	35.6	32.2	28.9	25.6
95°	91.6	90.8	89.0	87.1	85.2	83.3	81.2	78.8	76.4	74.1	71.7
97.5°	144.5	143.5	141.4	139.2	137.0	134.9	132.8	130.9	129.0	127.1	125.2
100°	183.3	182.8	180.4	178.0	175.6	173.2	171.5	170.4	169.4	168.3	167.2
102.5°	223.6	222.9	220.7	218.6	216.3	214.2	212.9	212.5	212.1	211.6	211.2
105°	285.1	284.3	283.2	282.2	281.1	280.0	279.4	279.1	278.8	278.6	278.3
107.5°	351.6	350.9	350.8	350.6	350.5	350.3	350.1	349.7	349.4	349.1	348.8
110°	397.2	397.8	398.0	398.3	398.5	398.9	398.7	398.2	397.6	397.1	396.6



TEST NUMBER: P332830-927

CATALOG NUMBER: S124DIW-S1020D1560U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	444.5	444.6	445.0	445.5	446.0	446.5	446.7	446.6	446.5	446.4	446.2
115°	518.2	518.4	519.0	519.4	520.0	520.5	520.8	520.8	520.8	520.8	520.8
117.5°	589.4	590.3	590.7	591.0	591.4	591.8	591.9	591.7	591.4	591.2	591.0
120°	637.7	639.1	639.8	640.6	641.4	642.2	642.1	641.0	640.0	638.9	637.9
122.5°	686.0	686.8	687.2	687.5	687.9	688.3	688.2	687.9	687.5	687.0	686.6
125°	756.8	757.3	757.6	757.8	758.1	758.4	758.5	758.5	758.5	758.5	758.5
127.5°	824.8	825.4	825.9	826.2	826.6	827.1	826.9	826.1	825.3	824.5	823.7
130°	872.7	873.1	873.1	873.1	873.1	873.1	872.7	872.0	871.2	870.4	869.6
132.5°	917.6	918.1	918.3	918.5	918.7	918.9	918.8	918.1	917.6	917.0	916.4
135°	984.9	985.5	985.5	985.5	985.5	985.5	984.7	983.1	981.4	979.9	978.3
137.5°	1050.2	1050.9	1050.5	1050.0	1049.6	1049.2	1048.6	1047.9	1047.1	1046.4	1045.7
140°	1092.7	1093.0	1093.0	1093.0	1093.0	1093.0	1092.7	1092.2	1091.6	1091.1	1090.6
142.5°	1133.1	1133.1	1133.3	1133.5	1133.7	1133.9	1133.8	1133.2	1132.7	1132.2	1131.6
145°	1194.2	1194.5	1194.2	1194.0	1193.7	1193.4	1192.8	1191.7	1190.6	1189.5	1188.5
147.5°	1249.4	1249.7	1249.9	1250.1	1250.3	1250.5	1250.0	1248.7	1247.4	1246.2	1244.9
150°	1284.0	1284.0	1284.0	1284.0	1284.0	1284.0	1283.6	1282.5	1281.4	1280.3	1279.3
152.5°	1316.2	1315.6	1315.4	1315.2	1314.9	1314.8	1314.3	1313.7	1313.0	1312.4	1311.8
155°	1361.6	1360.5	1360.8	1361.0	1361.3	1361.6	1361.7	1361.7	1361.7	1361.7	1361.7
157.5°	1402.2	1401.4	1401.4	1401.4	1401.5	1401.6	1401.8	1402.3	1402.8	1403.3	1403.7
160°	1427.0	1426.2	1426.5	1426.7	1427.0	1427.3	1427.5	1427.8	1428.1	1428.3	1428.6
162.5°	1448.7	1447.2	1447.5	1447.8	1448.0	1448.3	1448.7	1449.5	1450.2	1450.9	1451.5
165°	1478.0	1476.4	1476.9	1477.4	1478.0	1478.5	1479.2	1480.0	1480.7	1481.5	1482.3
167.5°	1502.8	1501.3	1501.2	1501.1	1501.1	1501.0	1501.6	1502.7	1503.8	1504.9	1506.0
170°	1516.2	1514.6	1514.3	1514.1	1513.8	1513.5	1514.1	1515.4	1516.7	1518.1	1519.4
172.5°	1526.0	1524.2	1524.1	1524.1	1524.0	1523.9	1524.5	1525.6	1526.7	1527.8	1528.9
175°	1536.8	1534.9	1535.2	1535.4	1535.7	1536.0	1536.8	1538.1	1539.4	1540.7	1542.1
177.5°	1543.1	1541.6	1541.6	1541.6	1541.6	1541.6	1542.1	1543.2	1544.3	1545.3	1546.3
180°	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4



TEST NUMBER: P332830-927

CATALOG NUMBER: S124DIW-S1020D1560U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0
2.5°	1330.8	1335.1	1340.8	1350.5	1354.0	1358.4	1364.5	1364.1	1365.8	1372.4	1386.4
5°	1335.7	1352.7	1369.1	1388.9	1409.6	1423.3	1441.9	1453.4	1464.9	1479.7	1504.9
7.5°	1337.7	1364.6	1394.7	1429.3	1460.2	1495.6	1523.3	1549.4	1573.0	1604.2	1634.2
10°	1334.6	1370.7	1409.6	1453.4	1500.0	1539.4	1575.0	1615.6	1650.0	1687.8	1721.8
12.5°	1328.9	1372.5	1424.5	1473.6	1528.0	1586.3	1630.6	1671.6	1717.5	1761.0	1813.4
15°	1316.0	1375.7	1436.5	1501.1	1573.9	1641.2	1705.3	1758.5	1807.8	1873.0	1941.4
17.5°	1299.6	1364.0	1440.6	1518.9	1595.0	1672.0	1751.3	1831.1	1893.3	1974.3	2027.8
20°	1284.2	1358.7	1437.6	1530.7	1606.8	1702.6	1781.5	1858.7	1944.1	2024.7	2088.7
22.5°	1262.7	1344.3	1427.9	1520.6	1620.8	1716.7	1807.8	1891.6	1977.0	2064.5	2142.1
25°	1235.5	1309.4	1408.5	1513.7	1613.4	1717.4	1822.0	1927.1	2019.1	2111.7	2184.0
27.5°	1189.1	1282.4	1374.7	1483.2	1593.9	1711.7	1823.5	1933.6	2030.0	2106.1	2150.9
30°	1165.4	1246.4	1346.6	1455.6	1575.6	1702.1	1818.7	1926.6	2016.4	2077.2	2095.2
32.5°	1130.4	1214.0	1312.0	1425.0	1551.9	1681.9	1803.4	1905.1	1980.1	2011.9	1990.1
35°	1078.3	1153.9	1253.0	1368.6	1500.6	1639.1	1759.0	1845.0	1883.3	1853.2	1778.2
37.5°	1015.9	1090.8	1190.3	1303.9	1440.4	1581.3	1689.7	1751.6	1738.8	1664.0	1552.1
40°	972.1	1042.2	1136.9	1259.6	1392.7	1533.9	1629.2	1662.6	1627.6	1520.3	1401.4
42.5°	923.4	991.8	1087.0	1205.2	1346.2	1476.5	1559.6	1562.3	1503.6	1375.2	1255.9
45°	849.4	914.6	1004.4	1127.6	1257.9	1380.6	1435.4	1408.5	1300.1	1176.3	1056.4
47.5°	776.3	832.8	921.4	1038.3	1162.1	1265.4	1292.5	1244.2	1128.7	1008.5	897.4
50°	722.9	779.8	863.1	974.8	1094.2	1183.4	1196.6	1132.5	1019.1	898.1	811.0
52.5°	671.6	728.2	808.3	911.7	1021.0	1101.5	1101.9	1027.8	914.9	807.0	726.0
55°	596.4	647.3	719.6	812.1	909.7	972.6	957.3	880.6	782.6	689.0	618.3
57.5°	523.9	568.2	634.9	712.0	797.9	849.9	824.4	750.6	663.1	583.7	530.1
60°	477.0	519.2	576.2	649.0	721.3	761.8	737.7	670.8	590.3	526.2	479.7
62.5°	431.4	467.0	521.8	585.0	652.0	682.1	660.6	594.6	525.1	467.1	429.4
65°	366.9	395.9	439.7	494.0	542.7	568.5	550.4	489.0	435.9	394.3	364.2
67.5°	306.7	329.4	362.5	406.0	447.4	461.4	444.9	402.2	357.2	323.8	302.6
70°	265.1	286.5	314.3	347.8	383.9	398.7	382.2	348.3	311.6	280.9	260.2
72.5°	228.7	245.3	268.8	297.4	325.7	340.4	329.2	296.6	265.6	242.8	225.1
75°	174.1	188.4	204.8	225.1	247.0	256.8	247.0	224.5	203.2	186.2	173.6
77.5°	126.6	134.3	146.9	162.1	175.8	183.3	174.8	159.5	146.6	134.9	128.7
80°	96.4	101.9	110.6	122.7	132.0	139.1	133.6	121.0	110.6	103.0	100.2
82.5°	70.1	73.8	79.5	88.5	94.7	98.4	95.9	86.8	82.5	75.8	73.0
85°	34.5	36.7	40.6	43.3	48.7	49.3	49.8	46.0	42.1	40.6	38.3
87.5°	13.2	14.2	16.1	18.0	20.2	21.1	21.1	21.5	20.1	20.0	18.6
90°	6.5	9.4	12.4	15.3	17.8	19.9	22.0	24.2	26.3	27.9	29.5
92.5°	28.9	32.2	35.6	39.0	41.4	42.9	44.4	45.8	47.3	48.2	49.2
95°	74.1	76.4	78.8	81.2	83.3	85.2	87.1	89.0	90.8	91.6	92.4
97.5°	127.1	129.0	130.9	132.8	134.9	137.0	139.2	141.4	143.5	144.5	145.5
100°	168.3	169.4	170.4	171.5	173.2	175.6	178.0	180.4	182.8	183.3	183.8
102.5°	211.6	212.1	212.5	212.9	214.2	216.3	218.6	220.7	222.9	223.6	224.3
105°	278.6	278.8	279.1	279.4	280.0	281.1	282.2	283.2	284.3	285.1	285.9
107.5°	349.1	349.4	349.7	350.1	350.3	350.5	350.6	350.8	350.9	351.6	352.4
110°	397.1	397.6	398.2	398.7	398.9	398.5	398.3	398.0	397.8	397.2	396.7





TEST NUMBER: P332830-927

CATALOG NUMBER: S124DIW-S1020D1560U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	446.4	446.5	446.6	446.7	446.5	446.0	445.5	445.0	444.6	444.5	444.3
115°	520.8	520.8	520.8	520.8	520.5	520.0	519.4	519.0	518.4	518.2	517.8
117.5°	591.2	591.4	591.7	591.9	591.8	591.4	591.0	590.7	590.3	589.4	588.5
120°	638.9	640.0	641.0	642.1	642.2	641.4	640.6	639.8	639.1	637.7	636.4
122.5°	687.0	687.5	687.9	688.2	688.3	687.9	687.5	687.2	686.8	686.0	685.0
125°	758.5	758.5	758.5	758.5	758.4	758.1	757.8	757.6	757.3	756.8	756.2
127.5°	824.5	825.3	826.1	826.9	827.1	826.6	826.2	825.9	825.4	824.8	824.3
130°	870.4	871.2	872.0	872.7	873.1	873.1	873.1	873.1	873.1	872.7	872.1
132.5°	917.0	917.6	918.1	918.8	918.9	918.7	918.5	918.3	918.1	917.6	917.0
135°	979.9	981.4	983.1	984.7	985.5	985.5	985.5	985.5	985.5	984.9	984.4
137.5°	1046.4	1047.1	1047.9	1048.6	1049.2	1049.6	1050.0	1050.5	1050.9	1050.2	1049.6
140°	1091.1	1091.6	1092.2	1092.7	1093.0	1093.0	1093.0	1093.0	1093.0	1092.7	1092.4
142.5°	1132.2	1132.7	1133.2	1133.8	1133.9	1133.7	1133.5	1133.3	1133.1	1133.1	1133.0
145°	1189.5	1190.6	1191.7	1192.8	1193.4	1193.7	1194.0	1194.2	1194.5	1194.2	1194.0
147.5°	1246.2	1247.4	1248.7	1250.0	1250.5	1250.3	1250.1	1249.9	1249.7	1249.4	1249.3
150°	1280.3	1281.4	1282.5	1283.6	1284.0	1284.0	1284.0	1284.0	1284.0	1284.0	1284.0
152.5°	1312.4	1313.0	1313.7	1314.3	1314.8	1314.9	1315.2	1315.4	1315.6	1316.2	1316.8
155°	1361.7	1361.7	1361.7	1361.7	1361.6	1361.3	1361.0	1360.8	1360.5	1361.6	1362.6
157.5°	1403.3	1402.8	1402.3	1401.8	1401.6	1401.5	1401.4	1401.4	1401.4	1402.2	1403.0
160°	1428.3	1428.1	1427.8	1427.5	1427.3	1427.0	1426.7	1426.5	1426.2	1427.0	1427.8
162.5°	1450.9	1450.2	1449.5	1448.7	1448.3	1448.0	1447.8	1447.5	1447.2	1448.7	1450.1
165°	1481.5	1480.7	1480.0	1479.2	1478.5	1478.0	1477.4	1476.9	1476.4	1478.0	1479.6
167.5°	1504.9	1503.8	1502.7	1501.6	1501.0	1501.1	1501.1	1501.2	1501.3	1502.8	1504.4
170°	1518.1	1516.7	1515.4	1514.1	1513.5	1513.8	1514.1	1514.3	1514.6	1516.2	1517.8
172.5°	1527.8	1526.7	1525.6	1524.5	1523.9	1524.0	1524.1	1524.1	1524.2	1526.0	1527.8
175°	1540.7	1539.4	1538.1	1536.8	1536.0	1535.7	1535.4	1535.2	1534.9	1536.8	1538.7
177.5°	1545.3	1544.3	1543.2	1542.1	1541.6	1541.6	1541.6	1541.6	1541.6	1543.1	1544.6
180°	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4



TEST NUMBER: P332830-927

CATALOG NUMBER: S124DIW-S1020D1560U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0
2.5°	1393.4	1394.3	1398.2	1401.3	1402.2	1406.6	1407.0
5°	1515.8	1525.2	1543.3	1544.9	1547.6	1561.9	1550.9
7.5°	1659.4	1683.0	1698.8	1712.7	1717.8	1723.9	1722.7
10°	1751.4	1786.4	1804.0	1831.8	1833.0	1840.1	1835.7
12.5°	1843.8	1884.5	1916.5	1921.7	1945.1	1948.7	1954.9
15°	1974.8	2018.1	2062.4	2078.3	2110.6	2118.3	2130.3
17.5°	2097.9	2142.1	2173.3	2214.3	2227.6	2245.4	2233.2
20°	2165.4	2213.6	2253.0	2285.3	2299.0	2308.8	2307.8
22.5°	2206.1	2254.7	2286.7	2311.1	2323.9	2328.1	2327.9
25°	2231.7	2259.5	2269.4	2278.7	2264.5	2259.5	2261.8
27.5°	2160.7	2153.5	2127.7	2094.0	2058.9	2031.1	2015.9
30°	2063.0	2020.2	1981.3	1913.4	1878.4	1857.6	1839.0
32.5°	1924.5	1856.8	1782.0	1719.8	1680.0	1649.1	1644.5
35°	1687.3	1585.4	1494.0	1417.8	1378.4	1345.0	1337.4
37.5°	1434.5	1328.6	1246.3	1179.3	1136.9	1113.3	1091.3
40°	1266.7	1175.8	1094.7	1037.8	1005.4	988.5	974.8
42.5°	1137.4	1054.4	973.8	930.4	901.2	890.8	882.8
45°	958.9	881.7	825.9	793.0	776.0	758.5	750.3
47.5°	815.9	753.1	716.3	688.4	670.2	659.8	654.5
50°	734.9	683.4	650.6	629.2	612.8	604.6	600.2
52.5°	663.1	620.8	593.2	576.2	565.1	559.0	557.3
55°	571.2	538.8	521.3	506.6	498.4	492.9	490.7
57.5°	496.5	471.7	457.4	445.2	442.0	437.4	435.9
60°	447.4	428.3	416.2	408.0	405.3	399.8	400.8
62.5°	404.0	388.4	378.1	373.4	369.8	365.2	366.7
65°	341.7	330.3	324.7	320.4	316.0	313.2	315.4
67.5°	286.8	278.8	271.4	268.9	266.7	266.3	264.0
70°	250.8	244.2	237.7	236.1	236.1	233.9	233.3
72.5°	216.2	211.4	207.0	205.8	204.1	204.9	202.6
75°	167.0	163.2	161.5	159.9	159.4	159.4	157.7
77.5°	123.4	120.6	118.0	118.0	116.0	115.3	115.0
80°	93.6	92.5	90.4	90.4	89.3	89.8	88.7
82.5°	70.4	68.9	68.4	67.6	66.1	66.1	65.0
85°	37.8	36.1	35.6	34.0	32.9	34.0	32.9
87.5°	19.3	19.3	19.0	18.2	17.9	18.0	16.8
90°	31.1	32.6	33.7	34.2	34.8	35.3	35.8
92.5°	50.1	51.1	51.7	52.0	52.4	52.7	53.0
95°	93.2	94.0	94.3	94.3	94.3	94.3	94.3
97.5°	146.5	147.4	147.9	147.9	147.9	147.9	147.9
100°	184.3	184.9	185.1	185.1	185.1	185.1	185.1
102.5°	225.1	225.9	226.3	226.6	226.8	227.0	227.2
105°	286.7	287.5	288.3	289.1	289.9	290.7	291.4
107.5°	353.2	353.9	354.3	354.2	354.2	354.1	354.0
110°	396.2	395.6	395.8	396.6	397.4	398.2	398.9



TEST NUMBER: P332830-927

CATALOG NUMBER: S124DIW-S1020D1560U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	444.3	444.2	444.2	444.3	444.5	444.7	444.8
115°	517.6	517.4	517.1	516.8	516.6	516.3	516.0
117.5°	587.6	586.7	586.0	585.4	584.9	584.4	583.8
120°	635.1	633.7	633.3	633.9	634.4	634.9	635.5
122.5°	684.1	683.3	682.3	681.4	680.4	679.5	678.5
125°	755.7	755.2	754.6	754.1	753.6	753.0	752.5
127.5°	823.8	823.2	822.8	822.4	822.0	821.5	821.1
130°	871.6	871.0	870.2	869.2	868.2	867.0	866.0
132.5°	916.5	915.9	915.4	915.0	914.7	914.2	913.8
135°	983.9	983.3	982.6	981.8	981.0	980.2	979.5
137.5°	1048.8	1048.1	1047.9	1048.1	1048.2	1048.4	1048.5
140°	1092.2	1091.9	1091.6	1091.4	1091.1	1090.8	1090.6
142.5°	1132.9	1132.9	1132.8	1132.7	1132.7	1132.7	1132.6
145°	1193.7	1193.4	1192.9	1192.1	1191.3	1190.5	1189.7
147.5°	1249.0	1248.8	1248.6	1248.3	1248.1	1247.8	1247.5
150°	1284.0	1284.0	1284.0	1283.7	1283.4	1283.2	1282.9
152.5°	1317.5	1318.1	1318.1	1317.4	1316.8	1316.1	1315.3
155°	1363.7	1364.8	1364.8	1363.7	1362.6	1361.6	1360.5
157.5°	1403.7	1404.5	1404.5	1403.6	1402.7	1401.8	1400.9
160°	1428.6	1429.4	1429.1	1427.8	1426.5	1425.1	1423.8
162.5°	1451.5	1452.9	1453.0	1451.7	1450.4	1449.1	1447.7
165°	1481.1	1482.7	1483.0	1481.9	1480.9	1479.8	1478.8
167.5°	1506.0	1507.6	1507.6	1505.9	1504.3	1502.6	1500.9
170°	1519.4	1521.0	1520.8	1519.0	1517.1	1515.3	1513.4
172.5°	1529.5	1531.4	1531.4	1529.5	1527.6	1525.7	1523.9
175°	1540.5	1542.4	1542.4	1540.5	1538.7	1536.8	1534.9
177.5°	1546.0	1547.5	1547.4	1545.7	1544.0	1542.4	1540.6
180°	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4

(END OF REPORT)