

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332852

Luminaire Tested: **S124DIW-S1195D1050U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332852
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S1195D1050U835-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1050 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8751.9 lumens
Efficiency: N/A
Efficacy: 129.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 67.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332852

CATALOG NUMBER: S124DIW-S1195D1050U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332852

CATALOG NUMBER: S124DIW-S1195D1050U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	64	64	64	58
1	100	95	91	88	93	89	86	82	77	75	72	66	65	63	56	55	54	49
2	91	83	77	72	84	78	72	68	68	63	60	58	55	52	50	47	45	41
3	83	73	66	60	77	68	62	57	60	55	50	52	48	44	44	41	39	35
4	76	65	57	51	70	61	54	48	53	47	43	46	42	38	39	36	33	30
5	70	58	49	43	65	54	47	41	47	42	37	41	37	33	35	32	29	26
6	64	52	44	38	60	49	41	36	43	37	32	37	33	29	32	28	26	23
7	59	47	39	33	55	44	37	32	39	33	29	34	29	26	29	26	23	20
8	55	43	35	29	51	40	33	28	35	30	25	31	26	23	27	23	20	18
9	51	39	31	26	48	37	30	25	33	27	23	29	24	21	25	21	18	16
10	48	36	28	24	45	34	27	23	30	24	21	27	22	19	23	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16088	16088	16088
5°	16136	15943	16058
10°	16035	15813	15891
15°	15841	15588	15628
20°	15584	15309	15323
25°	15291	14991	14949
30°	14930	14618	14483
35°	14557	14226	14038
40°	14169	13782	13529
45°	13764	13345	13089
50°	13317	12955	12554
55°	12833	12451	12047
60°	12350	11885	11525
65°	11805	11347	10890
70°	11195	10629	10213
75°	10259	9763	9513
80°	9131	8759	8536
85°	7984	7688	7540



TEST NUMBER: P332852

CATALOG NUMBER: S124DIW-S1195D1050U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	187.7	2.1
10°-20°	528.8	6.0
20°-30°	778.3	8.9
30°-40°	904.8	10.3
40°-50°	904.8	10.3
50°-60°	791.5	9.0
60°-70°	587.8	6.7
70°-80°	333.9	3.8
80°-90°	100.3	1.1
90°-100°	86.4	1.0
100°-110°	255.9	2.9
110°-120°	434.4	5.0
120°-130°	572.8	6.5
130°-140°	643.3	7.3
140°-150°	632.1	7.2
150°-160°	531.7	6.1
160°-170°	353.7	4.0
170°-180°	123.9	1.4
0°-30°	1494.7	17.1
0°-40°	2399.5	27.4
0°-60°	4095.8	46.8
0°-90°	5117.8	58.5
90°-120°	776.7	8.9
90°-150°	2624.9	30.0
90°-180°	3634.0	41.5
0°-180°	8751.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1993	1993	1993	1993	1993	
5°	1991	1984	1967	1984	1982	189
15°	1895	1888	1865	1874	1870	534
25°	1717	1705	1683	1684	1678	789
35°	1477	1465	1444	1433	1424	923
45°	1206	1194	1169	1152	1146	929
55°	912	906	885	866	856	816
65°	618	610	594	578	570	612
75°	329	321	313	307	305	350
85°	86	86	83	83	81	95
90°	3	14	22	28	30	8
95°	61	70	77	80	80	68
105°	236	237	241	244	247	250
115°	442	442	440	439	438	435
125°	643	643	642	640	638	573
135°	830	835	836	834	831	642
145°	1008	1012	1013	1012	1009	631
155°	1155	1155	1154	1158	1154	531
165°	1257	1254	1252	1258	1254	354
175°	1308	1303	1302	1308	1302	124
180°	1310	1310	1310	1310	1310	



TEST NUMBER: P332852

CATALOG NUMBER: S124DIW-S1195D1050U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8
2.5°	1997.9	1997.1	1996.2	1995.4	1994.5	1992.5	1989.4	1986.3	1983.2	1980.1	1982.9
5°	1991.2	1989.8	1988.4	1987.0	1985.6	1982.9	1979.0	1975.1	1971.2	1967.3	1971.2
7.5°	1972.7	1971.3	1969.9	1968.4	1967.0	1964.2	1959.8	1955.5	1951.2	1946.8	1950.0
10°	1956.1	1954.7	1953.3	1951.8	1950.4	1947.4	1942.8	1938.2	1933.6	1929.0	1931.8
12.5°	1934.4	1933.0	1931.5	1930.1	1928.7	1925.5	1920.7	1915.8	1910.9	1906.0	1909.1
15°	1895.4	1894.0	1892.6	1891.2	1889.7	1886.4	1881.0	1875.7	1870.4	1865.1	1867.2
17.5°	1848.5	1846.7	1844.9	1843.2	1841.4	1838.0	1832.9	1827.9	1822.9	1817.8	1819.2
20°	1814.0	1812.2	1810.4	1808.7	1806.9	1803.3	1798.0	1792.7	1787.4	1782.0	1783.1
22.5°	1776.9	1774.6	1772.3	1769.9	1767.6	1763.7	1758.4	1753.1	1747.8	1742.4	1744.4
25°	1716.6	1714.1	1711.6	1709.1	1706.6	1702.9	1697.9	1693.0	1688.0	1683.0	1683.4
27.5°	1647.6	1645.0	1642.5	1639.9	1637.4	1633.8	1629.2	1624.6	1620.0	1615.3	1614.5
30°	1601.6	1598.8	1595.9	1593.1	1590.3	1586.5	1581.9	1577.3	1572.7	1568.1	1566.7
32.5°	1553.1	1550.5	1548.0	1545.4	1542.8	1539.1	1534.2	1529.3	1524.4	1519.5	1517.8
35°	1477.1	1474.6	1472.1	1469.6	1467.1	1463.4	1458.4	1453.5	1448.5	1443.5	1441.0
37.5°	1396.9	1394.6	1392.4	1390.1	1387.8	1384.0	1378.7	1373.4	1368.0	1362.7	1360.0
40°	1344.5	1341.7	1338.8	1336.0	1333.2	1329.1	1323.8	1318.4	1313.1	1307.8	1304.2
42.5°	1288.3	1286.6	1284.9	1283.2	1281.5	1277.7	1271.8	1265.9	1260.0	1254.1	1250.0
45°	1205.6	1203.1	1200.6	1198.1	1195.7	1191.6	1185.9	1180.2	1174.5	1168.9	1165.0
47.5°	1119.0	1117.3	1115.6	1113.9	1112.2	1108.8	1103.5	1098.3	1093.0	1087.8	1083.4
50°	1060.3	1058.9	1057.4	1056.0	1054.6	1051.4	1046.4	1041.5	1036.5	1031.5	1026.6
52.5°	1002.8	1001.1	999.4	997.7	996.0	992.5	987.3	982.0	976.8	971.5	967.1
55°	911.8	910.7	909.7	908.6	907.5	904.5	899.5	894.6	889.6	884.6	880.4
57.5°	824.9	823.7	822.5	821.3	820.1	817.0	812.1	807.2	802.3	797.4	793.4
60°	764.9	763.1	761.3	759.6	757.8	754.6	750.0	745.4	740.7	736.1	732.9
62.5°	706.1	704.6	703.1	701.6	700.2	697.0	692.1	687.2	682.3	677.4	674.5
65°	618.0	616.2	614.4	612.6	610.9	608.2	604.7	601.1	597.6	594.0	590.5
67.5°	529.2	527.6	525.9	524.3	522.7	520.1	516.7	513.3	509.9	506.5	503.1
70°	474.3	471.8	469.3	466.8	464.3	461.7	458.8	456.0	453.1	450.3	447.5
72.5°	415.5	413.0	410.5	408.0	405.6	403.2	400.9	398.6	396.4	394.1	391.8
75°	328.9	327.2	325.4	323.6	321.8	320.1	318.3	316.5	314.8	313.0	311.6
77.5°	246.2	245.4	244.7	243.9	243.1	241.9	240.4	238.8	237.3	235.7	235.3
80°	196.4	195.3	194.3	193.2	192.2	191.3	190.6	189.8	189.1	188.4	187.7
82.5°	147.9	147.4	146.9	146.4	145.9	145.6	145.4	145.3	145.1	145.0	144.6
85°	86.2	86.2	86.2	86.2	86.2	85.9	85.2	84.5	83.7	83.0	83.0
87.5°	33.8	34.0	34.2	34.5	34.7	34.8	34.9	35.0	35.0	35.1	35.4
90°	3.0	5.5	8.0	10.5	12.9	15.1	16.9	18.7	20.5	22.3	23.6
92.5°	21.7	24.5	27.4	30.2	33.0	35.1	36.3	37.6	38.9	40.1	40.9
95°	60.8	62.8	64.8	66.9	68.9	70.7	72.3	73.8	75.4	77.0	77.7
97.5°	106.2	107.8	109.4	111.0	112.7	114.4	116.2	118.1	119.9	121.8	122.6
100°	141.8	142.7	143.6	144.5	145.4	146.9	148.9	150.9	153.0	155.0	155.4
102.5°	179.1	179.5	179.8	180.2	180.5	181.6	183.5	185.3	187.2	189.0	189.7
105°	236.0	236.3	236.5	236.7	236.9	237.5	238.4	239.3	240.2	241.1	241.8
107.5°	295.8	296.1	296.3	296.6	296.9	297.1	297.2	297.4	297.5	297.6	298.3
110°	336.3	336.8	337.2	337.7	338.1	338.2	338.0	337.8	337.6	337.3	336.9



TEST NUMBER: P332852

CATALOG NUMBER: S124DIW-S1195D1050U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	378.5	378.6	378.7	378.7	378.8	378.7	378.3	377.9	377.5	377.1	377.0
115°	441.7	441.7	441.7	441.7	441.7	441.5	441.0	440.6	440.1	439.7	439.4
117.5°	501.3	501.4	501.6	501.8	502.0	501.9	501.6	501.3	501.0	500.6	499.9
120°	541.0	541.9	542.8	543.7	544.6	544.7	544.0	543.3	542.7	542.0	540.9
122.5°	582.3	582.7	583.0	583.4	583.7	583.8	583.4	583.1	582.8	582.5	581.7
125°	643.3	643.3	643.3	643.3	643.3	643.2	642.9	642.7	642.5	642.3	641.8
127.5°	698.6	699.3	699.9	700.6	701.3	701.5	701.1	700.7	700.4	700.0	699.6
130°	737.5	738.2	738.8	739.5	740.2	740.5	740.5	740.5	740.5	740.5	740.1
132.5°	777.2	777.7	778.2	778.7	779.2	779.3	779.2	779.0	778.8	778.6	778.2
135°	829.7	831.0	832.4	833.7	835.1	835.8	835.8	835.8	835.8	835.8	835.3
137.5°	886.8	887.4	888.1	888.7	889.3	889.8	890.2	890.6	890.9	891.3	890.7
140°	924.9	925.4	925.8	926.3	926.7	926.9	926.9	926.9	926.9	926.9	926.7
142.5°	959.8	960.2	960.7	961.1	961.6	961.7	961.5	961.3	961.2	961.0	960.9
145°	1008.0	1008.9	1009.8	1010.7	1011.6	1012.1	1012.4	1012.6	1012.8	1013.0	1012.8
147.5°	1055.8	1056.9	1058.0	1059.0	1060.1	1060.6	1060.4	1060.2	1060.0	1059.8	1059.7
150°	1085.0	1085.9	1086.8	1087.7	1088.6	1089.0	1089.0	1089.0	1089.0	1089.0	1089.0
152.5°	1112.5	1113.1	1113.6	1114.1	1114.7	1115.0	1115.2	1115.4	1115.6	1115.8	1116.3
155°	1154.9	1154.9	1154.9	1154.9	1154.9	1154.8	1154.5	1154.3	1154.1	1153.9	1154.8
157.5°	1190.5	1190.1	1189.7	1189.3	1188.9	1188.7	1188.6	1188.6	1188.5	1188.5	1189.2
160°	1211.6	1211.4	1211.1	1210.9	1210.7	1210.5	1210.2	1210.0	1209.8	1209.6	1210.2
162.5°	1231.0	1230.5	1229.9	1229.3	1228.7	1228.3	1228.1	1227.9	1227.6	1227.4	1228.6
165°	1257.2	1256.5	1255.8	1255.2	1254.5	1253.9	1253.5	1253.0	1252.6	1252.1	1253.5
167.5°	1277.2	1276.3	1275.4	1274.4	1273.5	1273.0	1273.1	1273.1	1273.1	1273.2	1274.5
170°	1288.6	1287.5	1286.3	1285.2	1284.1	1283.6	1283.9	1284.1	1284.3	1284.5	1285.9
172.5°	1296.7	1295.7	1294.8	1293.9	1292.9	1292.5	1292.5	1292.6	1292.6	1292.6	1294.2
175°	1307.8	1306.7	1305.6	1304.5	1303.3	1302.7	1302.4	1302.2	1302.0	1301.8	1303.3
177.5°	1311.5	1310.6	1309.7	1308.8	1307.9	1307.4	1307.4	1307.4	1307.4	1307.4	1308.7
180°	1309.9	1309.9	1309.9	1309.9	1309.9	1309.9	1309.9	1309.9	1309.9	1309.9	1309.9



TEST NUMBER: P332852

CATALOG NUMBER: S124DIW-S1195D1050U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8
2.5°	1985.7	1988.6	1991.4	1992.7	1992.4	1992.1	1991.8	1991.5
5°	1975.1	1979.0	1982.9	1984.5	1983.8	1983.1	1982.4	1981.6
7.5°	1953.1	1956.2	1959.3	1960.7	1960.3	1959.8	1959.4	1959.0
10°	1934.6	1937.5	1940.3	1941.4	1940.7	1940.0	1939.2	1938.5
12.5°	1912.2	1915.3	1918.5	1919.5	1918.5	1917.5	1916.5	1915.5
15°	1869.3	1871.5	1873.6	1874.1	1873.1	1872.0	1870.9	1869.9
17.5°	1820.5	1821.9	1823.2	1823.5	1822.8	1822.1	1821.4	1820.7
20°	1784.2	1785.2	1786.3	1786.5	1785.8	1785.1	1784.4	1783.6
22.5°	1746.3	1748.2	1750.1	1750.4	1749.2	1747.9	1746.6	1745.3
25°	1683.8	1684.1	1684.5	1683.9	1682.5	1681.1	1679.7	1678.3
27.5°	1613.6	1612.8	1611.9	1610.6	1608.8	1607.1	1605.3	1603.5
30°	1565.2	1563.8	1562.4	1560.8	1559.0	1557.3	1555.5	1553.7
32.5°	1516.1	1514.4	1512.7	1511.0	1509.2	1507.4	1505.7	1503.9
35°	1438.6	1436.1	1433.6	1431.5	1429.7	1427.9	1426.1	1424.4
37.5°	1357.3	1354.6	1351.9	1349.4	1347.1	1344.7	1342.4	1340.0
40°	1300.7	1297.1	1293.6	1290.9	1289.2	1287.4	1285.6	1283.8
42.5°	1245.9	1241.8	1237.7	1235.0	1233.8	1232.6	1231.4	1230.2
45°	1161.1	1157.2	1153.3	1150.8	1149.7	1148.6	1147.6	1146.5
47.5°	1079.0	1074.6	1070.2	1066.6	1063.9	1061.2	1058.5	1055.8
50°	1021.6	1016.6	1011.7	1008.1	1006.0	1003.9	1001.7	999.6
52.5°	962.7	958.3	953.9	950.4	947.7	945.0	942.3	939.6
55°	876.1	871.9	867.6	864.4	862.3	860.2	858.0	855.9
57.5°	789.4	785.3	781.3	778.2	776.2	774.1	772.0	770.0
60°	729.7	726.6	723.4	720.9	719.1	717.3	715.6	713.8
62.5°	671.5	668.6	665.7	663.4	661.6	659.8	658.1	656.3
65°	586.9	583.4	579.8	577.2	575.4	573.6	571.8	570.1
67.5°	499.7	496.3	492.9	490.9	490.4	489.9	489.4	488.9
70°	444.6	441.8	438.9	437.0	435.9	434.9	433.8	432.7
72.5°	389.6	387.3	385.0	383.3	382.3	381.2	380.1	379.1
75°	310.1	308.7	307.3	306.4	306.1	305.7	305.3	305.0
77.5°	234.8	234.4	234.0	233.3	232.4	231.5	230.5	229.6
80°	187.0	186.3	185.6	185.1	184.7	184.3	184.0	183.6
82.5°	144.1	143.7	143.3	142.9	142.5	142.2	141.8	141.5
85°	83.0	83.0	83.0	82.9	82.5	82.1	81.8	81.4
87.5°	35.7	35.9	36.2	36.4	36.5	36.6	36.6	36.7
90°	25.0	26.3	27.7	28.6	29.0	29.5	29.9	30.4
92.5°	41.7	42.5	43.4	43.9	44.2	44.4	44.7	45.0
95°	78.3	79.0	79.7	80.0	80.0	80.0	80.0	80.0
97.5°	123.4	124.2	125.0	125.4	125.4	125.4	125.4	125.4
100°	155.9	156.3	156.8	157.0	157.0	157.0	157.0	157.0
102.5°	190.3	190.9	191.6	192.0	192.1	192.3	192.5	192.7
105°	242.5	243.1	243.8	244.5	245.2	245.8	246.5	247.2
107.5°	298.9	299.5	300.2	300.4	300.4	300.4	300.3	300.3
110°	336.4	336.0	335.5	335.7	336.3	337.0	337.7	338.4



TEST NUMBER: P332852

CATALOG NUMBER: S124DIW-S1195D1050U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	376.9	376.8	376.7	376.7	376.9	377.0	377.1	377.3
115°	439.2	439.0	438.8	438.5	438.3	438.1	437.9	437.6
117.5°	499.1	498.3	497.6	497.0	496.5	496.1	495.6	495.2
120°	539.7	538.6	537.5	537.1	537.6	538.0	538.5	538.9
122.5°	581.0	580.2	579.4	578.6	577.8	577.0	576.2	575.4
125°	641.4	640.9	640.5	640.0	639.6	639.1	638.7	638.2
127.5°	699.1	698.7	698.2	697.8	697.4	697.1	696.7	696.4
130°	739.6	739.2	738.7	738.1	737.2	736.3	735.4	734.5
132.5°	777.7	777.3	776.8	776.4	776.1	775.7	775.3	775.0
135°	834.9	834.4	834.0	833.4	832.7	832.0	831.4	830.7
137.5°	890.1	889.5	888.9	888.7	888.8	889.0	889.1	889.2
140°	926.5	926.3	926.0	925.8	925.6	925.4	925.1	924.9
142.5°	960.9	960.8	960.8	960.7	960.7	960.7	960.6	960.6
145°	1012.6	1012.4	1012.1	1011.7	1011.0	1010.3	1009.7	1009.0
147.5°	1059.5	1059.3	1059.1	1058.9	1058.7	1058.5	1058.2	1058.0
150°	1089.0	1089.0	1089.0	1088.9	1088.7	1088.5	1088.2	1088.0
152.5°	1116.8	1117.4	1117.9	1117.9	1117.3	1116.7	1116.1	1115.6
155°	1155.7	1156.6	1157.5	1157.5	1156.6	1155.7	1154.8	1153.9
157.5°	1189.9	1190.5	1191.2	1191.2	1190.4	1189.6	1188.9	1188.1
160°	1210.9	1211.6	1212.3	1212.0	1210.9	1209.8	1208.7	1207.5
162.5°	1229.8	1231.0	1232.3	1232.3	1231.2	1230.1	1228.9	1227.8
165°	1254.8	1256.2	1257.5	1257.7	1256.8	1255.9	1255.0	1254.1
167.5°	1275.9	1277.2	1278.6	1278.6	1277.2	1275.8	1274.4	1273.0
170°	1287.2	1288.6	1289.9	1289.8	1288.3	1286.7	1285.1	1283.5
172.5°	1295.7	1297.2	1298.8	1298.7	1297.2	1295.6	1294.0	1292.4
175°	1304.9	1306.5	1308.1	1308.1	1306.5	1304.9	1303.3	1301.8
177.5°	1310.0	1311.2	1312.5	1312.4	1310.9	1309.5	1308.1	1306.6
180°	1309.9	1309.9	1309.9	1309.9	1309.9	1309.9	1309.9	1309.9

(END OF REPORT)