

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332859

Luminaire Tested: **S124DIW-S1195D1560U835-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332859
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S1195D1560U835-4F0-1E-UDD-A
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1560 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 11560.4 lumens
Efficiency: N/A
Efficacy: 139.4 lumens/watt
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 82.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332859

CATALOG NUMBER: S124DIW-S1195D1560U835-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332859

CATALOG NUMBER: S124DIW-S1195D1560U835-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	46				
1	97	93	89	86	89	85	82	79	71	69	67	59	57	55	47	46	45	39				
2	89	81	75	70	81	75	70	65	63	59	56	52	49	47	41	40	38	33				
3	81	72	64	59	74	66	60	55	56	51	47	46	42	40	37	35	33	28				
4	74	64	56	50	68	59	52	47	49	44	40	41	37	34	33	30	28	24				
5	68	57	49	43	62	52	45	40	44	39	35	37	33	30	30	27	25	21				
6	63	51	43	37	57	47	40	35	40	35	30	33	29	26	27	24	22	19				
7	58	46	38	33	53	43	36	31	36	31	27	30	26	23	25	22	19	17				
8	54	42	34	29	49	39	32	27	33	28	24	28	24	21	23	20	17	15				
9	50	38	31	26	46	35	29	24	30	25	21	26	21	19	21	18	16	14				
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	14	12				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15560	15560	15560	15560
5°	18323	15600	13768	15600
10°	21939	15531	12396	15531
15°	25957	15374	11384	15374
20°	28905	15214	10481	15214
25°	29372	14978	9857	14978
30°	24993	14752	9660	14752
35°	19215	14384	9662	14384
40°	14977	13951	9844	13951
45°	12488	13300	10009	13300
50°	10991	12504	10349	12504
55°	10069	11553	10766	11553
60°	9436	10700	11267	10700
65°	8785	9746	11683	9746
70°	8028	8802	11948	8802
75°	7171	7745	11803	7745
80°	6011	6346	11432	6346
85°	4437	4585	10948	4585



TEST NUMBER: P332859

CATALOG NUMBER: S124DIW-S1195D1560U835-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	187.8	1.6
10°-20°	578.8	5.0
20°-30°	917.8	7.9
30°-40°	1021.3	8.8
40°-50°	929.7	8.0
50°-60°	759.7	6.6
60°-70°	542.4	4.7
70°-80°	298.7	2.6
80°-90°	87.4	0.8
90°-100°	69.0	0.6
100°-110°	439.7	3.8
110°-120°	841.1	7.3
120°-130°	1067.8	9.2
130°-140°	1142.4	9.9
140°-150°	1068.3	9.2
150°-160°	861.5	7.5
160°-170°	555.6	4.8
170°-180°	191.5	1.7
0°-30°	1684.3	14.6
0°-40°	2705.6	23.4
0°-60°	4395.1	38.0
0°-90°	5323.5	46.0
90°-120°	1349.8	11.7
90°-150°	4628.2	40.0
90°-180°	6237.0	54.0
0°-180°	11560.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1927	1927	1927	1927	1927	
5°	2261	1925	1699	1925	2261	230
15°	3106	1840	1362	1840	3106	878
25°	3297	1682	1107	1682	3297	1454
35°	1950	1460	980	1460	1950	1238
45°	1094	1165	877	1165	1094	862
55°	715	821	765	821	715	646
65°	460	510	612	510	460	455
75°	230	248	378	248	230	244
85°	48	50	118	50	48	60
90°	45	4	45	4	45	21
95°	44	83	44	83	44	35
105°	430	454	430	454	430	375
115°	854	848	854	848	854	845
125°	1200	1191	1200	1191	1200	1069
135°	1488	1478	1488	1478	1488	1146
145°	1713	1704	1713	1704	1713	1071
155°	1867	1868	1867	1868	1867	861
165°	1962	1971	1962	1971	1962	554
175°	2004	2016	2004	2016	2004	191
180°	2016	2016	2016	2016	2016	



TEST NUMBER: P332859

CATALOG NUMBER: S124DIW-S1195D1560U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4
2.5°	2051.3	2050.6	2044.3	2043.0	2038.5	2032.8	2031.5	2021.3	2000.8	1991.2	1988.7
5°	2261.1	2277.1	2256.3	2252.3	2249.9	2223.6	2210.0	2194.0	2157.3	2135.8	2119.0
7.5°	2511.5	2513.4	2504.3	2497.0	2476.7	2453.7	2419.2	2382.5	2338.7	2293.2	2258.9
10°	2676.3	2682.7	2672.3	2670.7	2630.0	2604.4	2553.3	2510.2	2460.7	2405.6	2355.3
12.5°	2850.0	2841.1	2835.8	2801.6	2794.1	2747.5	2688.1	2643.7	2567.4	2504.0	2437.1
15°	3105.8	3088.3	3077.1	3030.0	3006.8	2942.1	2879.1	2830.4	2730.6	2635.6	2563.7
17.5°	3255.9	3273.5	3247.6	3228.3	3168.4	3123.1	3058.6	2956.4	2878.3	2760.3	2669.6
20°	3364.5	3366.1	3351.7	3331.8	3284.7	3227.2	3156.9	3045.1	2951.7	2834.4	2709.8
22.5°	3393.9	3394.2	3388.1	3369.5	3333.8	3287.2	3216.3	3123.1	3009.9	2882.3	2757.7
25°	3297.4	3294.2	3301.4	3322.2	3308.6	3294.2	3253.5	3184.1	3078.7	2943.7	2809.6
27.5°	2939.1	2961.1	3001.7	3052.8	3102.0	3139.5	3150.1	3135.8	3070.5	2959.6	2819.0
30°	2681.1	2708.2	2738.6	2789.6	2888.7	2945.3	3007.6	3054.7	3028.4	2939.8	2808.8
32.5°	2397.5	2404.2	2449.2	2507.3	2598.0	2707.1	2805.8	2901.4	2933.2	2886.7	2777.5
35°	1949.7	1960.9	2009.6	2067.1	2178.1	2311.4	2459.9	2592.4	2701.8	2745.7	2689.8
37.5°	1591.1	1623.2	1657.5	1719.3	1817.0	1937.1	2091.4	2262.9	2425.9	2535.1	2553.6
40°	1421.2	1441.1	1465.9	1513.0	1596.0	1714.2	1846.7	2043.1	2216.4	2372.9	2424.0
42.5°	1287.0	1298.7	1313.9	1356.5	1419.7	1537.3	1658.3	1831.1	2005.0	2192.1	2277.7
45°	1093.8	1105.8	1131.3	1156.1	1204.0	1285.4	1398.0	1540.1	1715.0	1895.4	2053.5
47.5°	954.3	961.9	977.1	1003.6	1044.3	1098.0	1189.6	1308.3	1470.4	1645.5	1814.0
50°	875.1	881.4	893.4	917.4	948.5	996.4	1071.5	1182.4	1309.4	1485.8	1651.1
52.5°	812.5	815.0	823.8	840.1	864.8	905.1	966.7	1058.5	1176.5	1333.8	1498.5
55°	715.4	718.6	726.6	738.5	760.1	785.6	832.7	901.4	1004.4	1140.9	1283.8
57.5°	635.5	637.8	644.5	649.1	666.8	687.6	723.8	772.9	850.9	966.7	1094.3
60°	584.4	582.8	590.8	594.8	606.8	624.4	652.3	699.4	767.3	860.7	978.1
62.5°	534.6	532.4	539.1	544.4	551.2	566.2	589.1	626.0	681.0	765.5	866.9
65°	459.9	456.7	460.7	467.1	473.5	481.4	498.2	530.9	574.9	635.5	713.0
67.5°	384.8	388.2	388.8	392.0	395.7	406.6	418.0	441.2	472.2	520.7	586.4
70°	340.1	340.9	344.1	344.1	346.5	356.1	365.7	379.2	409.6	454.3	507.8
72.5°	295.4	298.8	297.5	300.0	301.8	308.2	315.2	328.1	354.0	387.2	432.4
75°	229.9	232.3	232.3	233.1	235.5	237.9	243.5	253.1	271.5	296.2	327.3
77.5°	167.7	168.0	169.1	172.0	172.0	175.8	180.0	187.6	196.7	213.7	232.7
80°	129.3	130.9	130.1	131.7	131.7	134.9	136.5	146.1	150.1	161.3	176.4
82.5°	94.9	96.4	96.3	98.5	99.8	100.4	102.7	106.5	110.5	120.4	126.6
85°	47.9	49.5	47.9	49.5	51.9	52.7	55.1	55.9	59.1	61.5	67.1
87.5°	23.1	24.9	24.7	25.3	26.4	26.8	27.0	26.0	28.1	28.4	30.4
90°	45.2	44.6	43.9	43.2	42.6	41.2	39.2	37.2	35.2	33.2	30.5
92.5°	41.6	41.5	41.4	41.2	41.1	40.0	38.0	36.0	34.0	32.0	29.3
95°	43.7	43.4	43.1	42.7	42.4	41.2	39.2	37.2	35.2	33.2	32.8
97.5°	42.2	41.9	41.6	41.2	40.9	40.6	40.4	40.2	40.0	39.8	77.2
100°	42.2	41.9	41.6	41.2	40.9	43.6	49.3	55.0	60.7	66.4	112.6
102.5°	43.4	43.4	43.3	43.2	43.2	73.9	135.3	196.8	258.2	319.7	325.7
105°	429.8	441.9	453.9	466.0	478.0	482.6	479.6	476.5	473.5	470.5	468.8
107.5°	599.0	597.7	596.4	595.2	593.9	592.5	591.1	589.6	588.1	586.6	584.3
110°	672.6	671.6	670.6	669.6	668.6	667.7	667.1	666.4	665.7	665.0	663.0



TEST NUMBER: P332859

CATALOG NUMBER: S124DIW-S1195D1560U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	746.2	744.9	743.6	742.4	741.1	740.5	740.6	740.8	740.9	741.1	740.1
115°	853.6	853.6	853.6	853.6	853.6	853.2	852.5	851.9	851.2	850.5	850.9
117.5°	962.7	962.9	963.0	963.1	963.3	963.4	963.5	963.7	963.8	963.9	963.2
120°	1031.5	1032.2	1032.8	1033.5	1034.2	1034.2	1033.5	1032.8	1032.2	1031.5	1031.8
122.5°	1099.1	1099.7	1100.4	1101.1	1101.7	1101.9	1101.5	1101.1	1100.7	1100.3	1099.8
125°	1200.4	1200.1	1199.7	1199.4	1199.1	1198.4	1197.4	1196.4	1195.4	1194.4	1195.0
127.5°	1289.4	1289.6	1289.9	1290.2	1290.4	1290.7	1290.9	1291.1	1291.3	1291.5	1289.9
130°	1349.7	1349.7	1349.7	1349.7	1349.7	1349.5	1349.2	1348.9	1348.5	1348.2	1347.2
132.5°	1405.2	1405.5	1405.7	1406.0	1406.3	1406.2	1405.9	1405.6	1405.2	1404.9	1403.6
135°	1488.4	1487.8	1487.1	1486.4	1485.8	1485.1	1484.4	1483.7	1483.1	1482.4	1481.1
137.5°	1559.6	1559.8	1560.0	1560.2	1560.4	1560.2	1559.4	1558.7	1557.9	1557.2	1555.7
140°	1609.1	1608.7	1608.4	1608.1	1607.7	1607.1	1606.1	1605.1	1604.1	1603.0	1602.4
142.5°	1650.1	1650.0	1650.0	1649.9	1649.8	1649.4	1648.7	1648.0	1647.2	1646.5	1646.1
145°	1713.1	1712.5	1711.8	1711.1	1710.5	1709.9	1709.6	1709.3	1708.9	1708.6	1708.6
147.5°	1765.3	1765.0	1764.6	1764.3	1764.0	1763.7	1763.4	1763.1	1762.9	1762.6	1762.9
150°	1799.1	1798.8	1798.4	1798.1	1797.8	1797.6	1797.6	1797.6	1797.6	1797.6	1797.9
152.5°	1828.0	1828.2	1828.4	1828.6	1828.8	1828.7	1828.1	1827.6	1827.1	1826.5	1827.1
155°	1867.0	1868.0	1869.0	1870.0	1871.0	1870.8	1869.5	1868.1	1866.8	1865.4	1866.5
157.5°	1899.5	1901.3	1903.0	1904.8	1906.5	1906.5	1904.8	1903.0	1901.3	1899.5	1900.7
160°	1921.2	1923.3	1925.3	1927.3	1929.3	1929.3	1927.3	1925.3	1923.3	1921.2	1921.6
162.5°	1938.1	1940.4	1942.7	1945.0	1947.2	1947.4	1945.4	1943.4	1941.3	1939.3	1939.7
165°	1962.0	1965.0	1968.0	1971.0	1974.0	1974.2	1971.5	1968.8	1966.1	1963.5	1963.5
167.5°	1979.8	1983.1	1986.5	1989.8	1993.2	1993.4	1990.4	1987.5	1984.5	1981.6	1981.8
170°	1990.6	1994.0	1997.3	2000.7	2004.0	2004.4	2001.7	1999.0	1996.3	1993.6	1993.3
172.5°	1996.6	2000.3	2003.9	2007.5	2011.1	2011.6	2008.9	2006.2	2003.5	2000.9	2000.5
175°	2004.2	2008.2	2012.2	2016.2	2020.3	2020.8	2017.8	2014.7	2011.7	2008.7	2008.4
177.5°	2009.0	2012.2	2015.4	2018.7	2021.9	2022.4	2020.3	2018.1	2016.0	2013.8	2013.3
180°	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2



TEST NUMBER: P332859

CATALOG NUMBER: S124DIW-S1195D1560U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4
2.5°	1989.3	1980.4	1974.0	1968.9	1954.8	1946.5	1940.1	1931.2	1921.0	1910.1	1896.7
5°	2102.2	2075.1	2055.1	2024.8	1996.0	1972.1	1947.3	1925.0	1897.8	1868.3	1846.7
7.5°	2220.9	2180.5	2128.7	2083.9	2033.4	1989.5	1950.2	1910.0	1868.1	1827.6	1790.4
10°	2296.2	2244.3	2186.8	2119.0	2055.1	1998.4	1945.7	1894.6	1845.1	1795.6	1753.3
12.5°	2377.4	2312.7	2227.7	2148.4	2076.8	2001.0	1937.4	1874.8	1815.1	1763.1	1713.7
15°	2486.3	2392.8	2294.6	2188.4	2094.2	2005.6	1918.6	1839.5	1772.5	1703.8	1655.9
17.5°	2553.2	2437.6	2325.3	2214.3	2100.3	1988.5	1894.6	1803.5	1719.5	1651.3	1590.9
20°	2597.2	2482.3	2342.5	2231.6	2095.8	1980.9	1872.3	1770.9	1683.1	1610.4	1548.1
22.5°	2635.6	2502.7	2363.0	2216.9	2081.8	1959.8	1841.0	1738.9	1649.2	1572.7	1513.0
25°	2656.3	2503.8	2352.1	2206.8	2053.5	1909.0	1801.2	1681.5	1585.6	1505.0	1441.1
27.5°	2658.6	2495.5	2323.9	2162.4	2004.2	1869.6	1733.5	1626.5	1527.0	1441.8	1380.5
30°	2651.5	2481.5	2297.0	2122.2	1963.3	1817.2	1699.0	1582.5	1481.1	1396.4	1332.5
32.5°	2629.2	2452.1	2262.5	2077.5	1912.8	1769.9	1647.9	1537.1	1438.3	1354.9	1287.8
35°	2564.5	2389.6	2187.6	1995.2	1826.8	1682.3	1572.1	1459.5	1360.5	1281.5	1216.8
37.5°	2463.4	2305.3	2100.0	1900.9	1735.4	1590.3	1481.1	1379.3	1290.1	1209.8	1143.5
40°	2375.3	2236.4	2030.4	1836.3	1657.5	1519.4	1417.2	1323.8	1235.1	1159.3	1096.2
42.5°	2273.7	2152.7	1962.7	1757.1	1584.7	1445.9	1346.3	1262.4	1178.9	1108.8	1045.8
45°	2092.6	2012.8	1834.0	1643.9	1464.3	1333.3	1238.3	1164.9	1094.6	1026.0	973.3
47.5°	1884.4	1844.8	1694.2	1513.8	1343.2	1214.2	1131.8	1064.0	1002.3	944.2	897.7
50°	1744.5	1725.4	1595.2	1421.2	1258.3	1136.9	1053.9	995.6	942.9	891.8	847.9
52.5°	1606.6	1605.9	1488.6	1329.2	1178.5	1061.6	979.2	924.7	879.1	837.5	798.1
55°	1395.6	1418.0	1326.2	1184.0	1049.1	943.7	869.5	820.8	788.8	754.5	725.0
57.5°	1201.9	1239.0	1163.3	1038.1	925.5	828.4	763.8	727.2	693.2	672.4	650.9
60°	1075.5	1110.6	1051.5	946.1	839.9	756.9	695.4	662.7	633.1	618.8	603.6
62.5°	963.0	994.3	950.6	852.9	760.7	680.9	629.0	597.5	577.6	561.9	551.9
65°	802.4	828.8	791.2	720.2	641.1	577.3	534.9	510.2	491.0	484.6	473.5
67.5°	648.6	672.6	652.3	591.9	528.5	480.2	447.1	423.3	412.0	406.4	398.4
70°	557.3	581.2	559.7	507.0	458.3	417.6	386.4	372.9	360.9	358.5	347.3
72.5°	480.0	496.3	474.7	433.5	391.9	357.5	333.4	319.2	313.0	308.7	302.6
75°	360.1	374.5	360.1	328.1	298.6	274.7	253.9	248.3	241.1	238.7	234.7
77.5°	254.9	267.3	256.3	236.3	214.3	195.8	184.6	177.4	175.8	171.7	173.6
80°	194.8	202.8	192.4	178.8	161.3	148.5	140.5	136.5	131.7	130.1	133.3
82.5°	139.9	143.4	138.1	129.0	115.9	107.6	102.2	97.6	96.6	96.9	96.9
85°	72.7	71.9	71.1	63.1	59.1	53.5	50.3	49.5	48.7	50.3	51.9
87.5°	29.8	29.9	28.8	25.6	22.9	20.3	18.9	17.5	18.9	20.3	21.6
90°	27.8	25.1	22.5	19.3	15.6	11.9	8.2	4.5	8.2	11.9	15.6
92.5°	26.6	23.9	21.2	19.8	19.6	19.4	19.2	19.0	19.2	19.4	19.6
95°	32.5	32.2	31.8	37.4	48.8	60.2	71.5	82.9	71.5	60.2	48.8
97.5°	114.6	152.0	189.4	204.6	197.5	190.3	183.2	176.1	183.2	190.3	197.5
100°	158.8	205.1	251.3	271.4	265.4	259.4	253.4	247.3	253.4	259.4	265.4
102.5°	331.8	337.8	343.8	344.6	340.2	335.8	331.4	326.9	331.4	335.8	340.2
105°	467.2	465.5	463.8	462.0	460.0	457.9	455.9	453.9	455.9	457.9	460.0
107.5°	582.1	579.8	577.5	575.9	574.9	573.9	572.9	571.8	572.9	573.9	574.9
110°	661.0	659.0	657.0	655.5	654.5	653.5	652.5	651.5	652.5	653.5	654.5



TEST NUMBER: P332859

CATALOG NUMBER: S124DIW-S1195D1560U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	739.2	738.2	737.3	735.9	734.1	732.3	730.5	728.7	730.5	732.3	734.1
115°	851.2	851.5	851.9	851.5	850.5	849.5	848.5	847.5	848.5	849.5	850.5
117.5°	962.5	961.7	961.0	960.0	958.6	957.3	955.9	954.6	955.9	957.3	958.6
120°	1032.2	1032.5	1032.8	1032.3	1031.0	1029.7	1028.3	1027.0	1028.3	1029.7	1031.0
122.5°	1099.3	1098.9	1098.4	1097.8	1096.9	1096.1	1095.3	1094.5	1095.3	1096.1	1096.9
125°	1195.7	1196.4	1197.0	1196.7	1195.4	1194.0	1192.7	1191.4	1192.7	1194.0	1195.4
127.5°	1288.4	1286.9	1285.3	1284.4	1284.0	1283.7	1283.4	1283.0	1283.4	1283.7	1284.0
130°	1346.2	1345.2	1344.2	1343.5	1343.2	1342.8	1342.5	1342.2	1342.5	1342.8	1343.2
132.5°	1402.3	1401.1	1399.8	1398.9	1398.3	1397.7	1397.0	1396.4	1397.0	1397.7	1398.3
135°	1479.7	1478.4	1477.0	1476.5	1476.9	1477.2	1477.5	1477.9	1477.5	1477.2	1476.9
137.5°	1554.3	1552.8	1551.3	1550.5	1550.4	1550.2	1550.1	1550.0	1550.1	1550.2	1550.4
140°	1601.7	1601.0	1600.4	1599.7	1599.0	1598.4	1597.7	1597.0	1597.7	1598.4	1599.0
142.5°	1645.7	1645.3	1644.9	1644.1	1642.9	1641.7	1640.4	1639.2	1640.4	1641.7	1642.9
145°	1708.6	1708.6	1708.6	1708.1	1707.1	1706.1	1705.1	1704.1	1705.1	1706.1	1707.1
147.5°	1763.3	1763.6	1763.9	1763.2	1761.3	1759.4	1757.5	1755.7	1757.5	1759.4	1761.3
150°	1798.3	1798.6	1798.9	1798.4	1797.1	1795.7	1794.4	1793.1	1794.4	1795.7	1797.1
152.5°	1827.7	1828.3	1829.0	1828.7	1827.6	1826.6	1825.5	1824.4	1825.5	1826.6	1827.6
155°	1867.5	1868.5	1869.5	1869.8	1869.5	1869.1	1868.8	1868.5	1868.8	1869.1	1869.5
157.5°	1901.8	1902.9	1904.1	1904.8	1905.0	1905.2	1905.4	1905.6	1905.4	1905.2	1905.0
160°	1921.9	1922.2	1922.6	1923.3	1924.3	1925.3	1926.3	1927.3	1926.3	1925.3	1924.3
162.5°	1940.0	1940.3	1940.7	1941.5	1942.8	1944.0	1945.3	1946.6	1945.3	1944.0	1942.8
165°	1963.5	1963.5	1963.5	1964.3	1966.0	1967.7	1969.3	1971.0	1969.3	1967.7	1966.0
167.5°	1982.0	1982.2	1982.4	1983.3	1985.1	1986.8	1988.6	1990.3	1988.6	1986.8	1985.1
170°	1993.0	1992.6	1992.3	1993.1	1995.1	1997.1	1999.2	2001.2	1999.2	1997.1	1995.1
172.5°	2000.2	1999.9	1999.5	2000.4	2002.4	2004.4	2006.4	2008.4	2006.4	2004.4	2002.4
175°	2008.0	2007.7	2007.4	2008.2	2010.2	2012.2	2014.2	2016.2	2014.2	2012.2	2010.2
177.5°	2012.8	2012.2	2011.7	2012.4	2014.2	2016.1	2018.0	2019.9	2018.0	2016.1	2014.2
180°	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2



TEST NUMBER: P332859

CATALOG NUMBER: S124DIW-S1195D1560U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4
2.5°	1890.3	1884.6	1876.3	1864.8	1855.2	1845.0	1842.4	1838.6	1846.2	1839.9	1837.9
5°	1828.4	1811.6	1790.0	1765.3	1750.9	1730.2	1726.2	1718.2	1710.2	1709.4	1701.4
7.5°	1762.7	1738.1	1709.9	1684.6	1661.3	1638.7	1623.8	1620.6	1608.8	1601.9	1593.9
10°	1720.6	1690.2	1657.5	1633.6	1606.4	1582.5	1565.7	1556.1	1548.1	1539.3	1531.4
12.5°	1670.8	1638.5	1611.5	1585.6	1553.4	1535.2	1507.6	1491.0	1489.4	1489.5	1468.8
15°	1612.8	1580.9	1539.3	1502.6	1485.0	1449.9	1434.7	1415.6	1403.6	1391.6	1382.1
17.5°	1546.5	1506.8	1474.3	1432.2	1398.7	1370.7	1350.8	1339.3	1321.2	1304.3	1292.0
20°	1505.0	1462.7	1428.4	1383.6	1346.9	1312.6	1295.8	1279.9	1266.3	1251.9	1238.3
22.5°	1462.8	1418.6	1376.6	1333.2	1299.0	1262.8	1246.6	1224.9	1212.0	1204.0	1190.4
25°	1396.4	1348.5	1300.6	1259.1	1224.0	1192.0	1170.5	1153.7	1139.3	1132.9	1124.2
27.5°	1324.2	1276.7	1230.4	1183.2	1143.3	1120.2	1102.9	1090.3	1082.0	1073.5	1069.6
30°	1278.3	1228.8	1179.3	1135.3	1098.6	1075.5	1059.5	1050.7	1044.3	1040.3	1036.3
32.5°	1231.6	1182.8	1130.7	1090.6	1057.7	1037.1	1025.0	1016.2	1013.0	1011.6	1010.2
35°	1156.9	1107.4	1059.5	1023.6	992.4	984.4	974.1	969.3	967.7	973.3	975.7
37.5°	1084.6	1038.6	994.5	959.7	939.3	927.6	924.1	924.2	930.0	934.9	940.7
40°	1037.9	993.2	951.7	921.4	902.2	895.0	893.4	897.4	903.8	909.4	915.8
42.5°	992.6	948.5	910.8	882.4	869.0	862.4	863.4	867.4	876.3	883.2	892.8
45°	922.2	885.4	848.7	825.6	814.4	816.0	816.0	823.2	831.9	842.3	852.7
47.5°	855.9	818.9	788.7	769.2	763.4	762.0	766.5	775.9	788.5	801.3	815.8
50°	811.2	776.1	749.7	732.1	725.8	728.2	734.5	743.3	758.5	774.5	789.6
52.5°	765.8	733.9	709.5	693.2	688.7	693.0	699.4	713.3	726.6	743.8	762.2
55°	695.4	668.3	649.1	637.1	635.5	637.9	645.1	660.3	679.4	701.0	718.6
57.5°	625.3	602.6	585.1	576.8	577.6	579.8	591.6	609.7	630.1	653.1	675.8
60°	578.0	557.3	542.9	536.5	537.3	542.1	556.5	573.3	598.8	621.2	645.1
62.5°	533.3	515.1	501.4	495.7	494.5	505.1	518.8	536.2	561.8	586.7	612.5
65°	461.5	447.1	435.9	432.7	435.1	443.1	460.7	483.8	505.4	531.7	558.9
67.5°	391.2	379.4	371.7	373.2	376.1	387.9	402.6	422.5	447.0	474.3	501.1
70°	346.5	335.3	328.9	329.7	334.5	348.9	361.7	381.6	408.0	435.9	458.3
72.5°	300.5	293.2	287.4	290.8	295.6	305.5	321.4	341.4	364.6	390.6	414.2
75°	230.7	230.7	227.5	229.9	237.1	246.7	258.7	279.4	302.6	323.4	342.5
77.5°	171.2	169.4	171.5	174.4	178.5	189.9	203.6	218.4	235.9	256.6	272.4
80°	130.9	131.7	135.7	140.5	142.1	150.9	165.3	178.8	192.4	210.0	225.2
82.5°	98.4	99.2	101.2	107.3	108.9	118.3	127.6	141.2	153.5	165.3	177.9
85°	53.5	53.5	57.5	59.9	63.9	70.3	75.8	83.8	95.0	103.0	115.0
87.5°	24.3	24.9	28.0	29.8	32.3	36.0	37.7	45.1	48.1	51.7	57.7
90°	19.3	22.5	25.1	27.8	30.5	33.2	35.2	37.2	39.2	41.2	42.6
92.5°	19.8	21.2	23.9	26.6	29.3	32.0	34.0	36.0	38.0	40.0	41.1
95°	37.4	31.8	32.2	32.5	32.8	33.2	35.2	37.2	39.2	41.2	42.4
97.5°	204.6	189.4	152.0	114.6	77.2	39.8	40.0	40.2	40.4	40.6	40.9
100°	271.4	251.3	205.1	158.8	112.6	66.4	60.7	55.0	49.3	43.6	40.9
102.5°	344.6	343.8	337.8	331.8	325.7	319.7	258.2	196.8	135.3	73.9	43.2
105°	462.0	463.8	465.5	467.2	468.8	470.5	473.5	476.5	479.6	482.6	478.0
107.5°	575.9	577.5	579.8	582.1	584.3	586.6	588.1	589.6	591.1	592.5	593.9
110°	655.5	657.0	659.0	661.0	663.0	665.0	665.7	666.4	667.1	667.7	668.6



TEST NUMBER: P332859

CATALOG NUMBER: S124DIW-S1195D1560U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	735.9	737.3	738.2	739.2	740.1	741.1	740.9	740.8	740.6	740.5	741.1
115°	851.5	851.9	851.5	851.2	850.9	850.5	851.2	851.9	852.5	853.2	853.6
117.5°	960.0	961.0	961.7	962.5	963.2	963.9	963.8	963.7	963.5	963.4	963.3
120°	1032.3	1032.8	1032.5	1032.2	1031.8	1031.5	1032.2	1032.8	1033.5	1034.2	1034.2
122.5°	1097.8	1098.4	1098.9	1099.3	1099.8	1100.3	1100.7	1101.1	1101.5	1101.9	1101.7
125°	1196.7	1197.0	1196.4	1195.7	1195.0	1194.4	1195.4	1196.4	1197.4	1198.4	1199.1
127.5°	1284.4	1285.3	1286.9	1288.4	1289.9	1291.5	1291.3	1291.1	1290.9	1290.7	1290.4
130°	1343.5	1344.2	1345.2	1346.2	1347.2	1348.2	1348.5	1348.9	1349.2	1349.5	1349.7
132.5°	1398.9	1399.8	1401.1	1402.3	1403.6	1404.9	1405.2	1405.6	1405.9	1406.2	1406.3
135°	1476.5	1477.0	1478.4	1479.7	1481.1	1482.4	1483.1	1483.7	1484.4	1485.1	1485.8
137.5°	1550.5	1551.3	1552.8	1554.3	1555.7	1557.2	1557.9	1558.7	1559.4	1560.2	1560.4
140°	1599.7	1600.4	1601.0	1601.7	1602.4	1603.0	1604.1	1605.1	1606.1	1607.1	1607.7
142.5°	1644.1	1644.9	1645.3	1645.7	1646.1	1646.5	1647.2	1648.0	1648.7	1649.4	1649.8
145°	1708.1	1708.6	1708.6	1708.6	1708.6	1708.6	1708.9	1709.3	1709.6	1709.9	1710.5
147.5°	1763.2	1763.9	1763.6	1763.3	1762.9	1762.6	1762.9	1763.1	1763.4	1763.7	1764.0
150°	1798.4	1798.9	1798.6	1798.3	1797.9	1797.6	1797.6	1797.6	1797.6	1797.6	1797.8
152.5°	1828.7	1829.0	1828.3	1827.7	1827.1	1826.5	1827.1	1827.6	1828.1	1828.7	1828.8
155°	1869.8	1869.5	1868.5	1867.5	1866.5	1865.4	1866.8	1868.1	1869.5	1870.8	1871.0
157.5°	1904.8	1904.1	1902.9	1901.8	1900.7	1899.5	1901.3	1903.0	1904.8	1906.5	1906.5
160°	1923.3	1922.6	1922.2	1921.9	1921.6	1921.2	1923.3	1925.3	1927.3	1929.3	1929.3
162.5°	1941.5	1940.7	1940.3	1940.0	1939.7	1939.3	1941.3	1943.4	1945.4	1947.4	1947.2
165°	1964.3	1963.5	1963.5	1963.5	1963.5	1963.5	1966.1	1968.8	1971.5	1974.2	1974.0
167.5°	1983.3	1982.4	1982.2	1982.0	1981.8	1981.6	1984.5	1987.5	1990.4	1993.4	1993.2
170°	1993.1	1992.3	1992.6	1993.0	1993.3	1993.6	1996.3	1999.0	2001.7	2004.4	2004.0
172.5°	2000.4	1999.5	1999.9	2000.2	2000.5	2000.9	2003.5	2006.2	2008.9	2011.6	2011.1
175°	2008.2	2007.4	2007.7	2008.0	2008.4	2008.7	2011.7	2014.7	2017.8	2020.8	2020.3
177.5°	2012.4	2011.7	2012.2	2012.8	2013.3	2013.8	2016.0	2018.1	2020.3	2022.4	2021.9
180°	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2



TEST NUMBER: P332859

CATALOG NUMBER: S124DIW-S1195D1560U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4
2.5°	1836.7	1835.4	1830.9	1830.3	1830.9	1835.4	1836.7	1837.9	1839.9	1846.2	1838.6
5°	1696.6	1692.6	1690.2	1699.0	1690.2	1692.6	1696.6	1701.4	1709.4	1710.2	1718.2
7.5°	1591.1	1587.9	1580.9	1578.6	1580.9	1587.9	1591.1	1593.9	1601.9	1608.8	1620.6
10°	1523.4	1520.2	1513.8	1512.2	1513.8	1520.2	1523.4	1531.4	1539.3	1548.1	1556.1
12.5°	1458.2	1451.8	1450.6	1452.2	1450.6	1451.8	1458.2	1468.8	1489.5	1489.4	1491.0
15°	1371.7	1368.5	1359.7	1362.1	1359.7	1368.5	1371.7	1382.1	1391.6	1403.6	1415.6
17.5°	1286.4	1282.6	1271.9	1281.3	1271.9	1282.6	1286.4	1292.0	1304.3	1321.2	1339.3
20°	1232.7	1226.4	1220.8	1220.0	1220.8	1226.4	1232.7	1238.3	1251.9	1266.3	1279.9
22.5°	1181.6	1175.9	1175.4	1170.2	1175.4	1175.9	1181.6	1190.4	1204.0	1212.0	1224.9
25°	1117.8	1112.2	1110.6	1106.6	1110.6	1112.2	1117.8	1124.2	1132.9	1139.3	1153.7
27.5°	1068.8	1066.0	1063.2	1064.4	1063.2	1066.0	1068.8	1069.6	1073.5	1082.0	1090.3
30°	1038.7	1037.9	1036.3	1036.3	1036.3	1037.9	1038.7	1036.3	1040.3	1044.3	1050.7
32.5°	1013.8	1013.7	1014.6	1014.6	1014.6	1013.7	1013.8	1010.2	1011.6	1013.0	1016.2
35°	978.9	981.2	982.8	980.4	982.8	981.2	978.9	975.7	973.3	967.7	969.3
37.5°	947.2	949.6	951.9	954.6	951.9	949.6	947.2	940.7	934.9	930.0	924.2
40°	923.0	928.6	930.1	934.1	930.1	928.6	923.0	915.8	909.4	903.8	897.4
42.5°	900.0	906.2	910.3	911.1	910.3	906.2	900.0	892.8	883.2	876.3	867.4
45°	864.7	871.1	876.7	876.7	876.7	871.1	864.7	852.7	842.3	831.9	823.2
47.5°	828.1	837.4	843.0	844.4	843.0	837.4	828.1	815.8	801.3	788.5	775.9
50°	803.2	814.4	820.0	824.0	820.0	814.4	803.2	789.6	774.5	758.5	743.3
52.5°	778.9	790.1	797.6	799.7	797.6	790.1	778.9	762.2	743.8	726.6	713.3
55°	736.9	752.9	761.7	764.9	761.7	752.9	736.9	718.6	701.0	679.4	660.3
57.5°	697.3	712.0	722.2	724.6	722.2	712.0	697.3	675.8	653.1	630.1	609.7
60°	666.7	682.6	695.4	697.8	695.4	682.6	666.7	645.1	621.2	598.8	573.3
62.5°	635.4	652.0	663.5	669.7	663.5	652.0	635.4	612.5	586.7	561.8	536.2
65°	581.2	598.0	609.2	611.6	609.2	598.0	581.2	558.9	531.7	505.4	483.8
67.5°	522.2	538.9	546.3	550.9	546.3	538.9	522.2	501.1	474.3	447.0	422.5
70°	480.6	494.2	502.2	506.2	502.2	494.2	480.6	458.3	435.9	408.0	381.6
72.5°	433.4	447.6	456.9	457.6	456.9	447.6	433.4	414.2	390.6	364.6	341.4
75°	360.9	373.7	378.4	378.4	378.4	373.7	360.9	342.5	323.4	302.6	279.4
77.5°	285.7	292.2	298.3	299.6	298.3	292.2	285.7	272.4	256.6	235.9	218.4
80°	237.1	241.1	245.9	245.9	245.9	241.1	237.1	225.2	210.0	192.4	178.8
82.5°	187.3	190.7	195.5	194.8	195.5	190.7	187.3	177.9	165.3	153.5	141.2
85°	113.4	120.6	119.8	118.2	119.8	120.6	113.4	115.0	103.0	95.0	83.8
87.5°	59.7	60.5	62.6	64.0	62.6	60.5	59.7	57.7	51.7	48.1	45.1
90°	43.2	43.9	44.6	45.2	44.6	43.9	43.2	42.6	41.2	39.2	37.2
92.5°	41.2	41.4	41.5	41.6	41.5	41.4	41.2	41.1	40.0	38.0	36.0
95°	42.7	43.1	43.4	43.7	43.4	43.1	42.7	42.4	41.2	39.2	37.2
97.5°	41.2	41.6	41.9	42.2	41.9	41.6	41.2	40.9	40.6	40.4	40.2
100°	41.2	41.6	41.9	42.2	41.9	41.6	41.2	40.9	43.6	49.3	55.0
102.5°	43.2	43.3	43.4	43.4	43.4	43.3	43.2	43.2	73.9	135.3	196.8
105°	466.0	453.9	441.9	429.8	441.9	453.9	466.0	478.0	482.6	479.6	476.5
107.5°	595.2	596.4	597.7	599.0	597.7	596.4	595.2	593.9	592.5	591.1	589.6
110°	669.6	670.6	671.6	672.6	671.6	670.6	669.6	668.6	667.7	667.1	666.4



TEST NUMBER: P332859

CATALOG NUMBER: S124DIW-S1195D1560U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	742.4	743.6	744.9	746.2	744.9	743.6	742.4	741.1	740.5	740.6	740.8
115°	853.6	853.6	853.6	853.6	853.6	853.6	853.6	853.6	853.2	852.5	851.9
117.5°	963.1	963.0	962.9	962.7	962.9	963.0	963.1	963.3	963.4	963.5	963.7
120°	1033.5	1032.8	1032.2	1031.5	1032.2	1032.8	1033.5	1034.2	1034.2	1033.5	1032.8
122.5°	1101.1	1100.4	1099.7	1099.1	1099.7	1100.4	1101.1	1101.7	1101.9	1101.5	1101.1
125°	1199.4	1199.7	1200.1	1200.4	1200.1	1199.7	1199.4	1199.1	1198.4	1197.4	1196.4
127.5°	1290.2	1289.9	1289.6	1289.4	1289.6	1289.9	1290.2	1290.4	1290.7	1290.9	1291.1
130°	1349.7	1349.7	1349.7	1349.7	1349.7	1349.7	1349.7	1349.7	1349.5	1349.2	1348.9
132.5°	1406.0	1405.7	1405.5	1405.2	1405.5	1405.7	1406.0	1406.3	1406.2	1405.9	1405.6
135°	1486.4	1487.1	1487.8	1488.4	1487.8	1487.1	1486.4	1485.8	1485.1	1484.4	1483.7
137.5°	1560.2	1560.0	1559.8	1559.6	1559.8	1560.0	1560.2	1560.4	1560.2	1559.4	1558.7
140°	1608.1	1608.4	1608.7	1609.1	1608.7	1608.4	1608.1	1607.7	1607.1	1606.1	1605.1
142.5°	1649.9	1650.0	1650.0	1650.1	1650.0	1650.0	1649.9	1649.8	1649.4	1648.7	1648.0
145°	1711.1	1711.8	1712.5	1713.1	1712.5	1711.8	1711.1	1710.5	1709.9	1709.6	1709.3
147.5°	1764.3	1764.6	1765.0	1765.3	1765.0	1764.6	1764.3	1764.0	1763.7	1763.4	1763.1
150°	1798.1	1798.4	1798.8	1799.1	1798.8	1798.4	1798.1	1797.8	1797.6	1797.6	1797.6
152.5°	1828.6	1828.4	1828.2	1828.0	1828.2	1828.4	1828.6	1828.8	1828.7	1828.1	1827.6
155°	1870.0	1869.0	1868.0	1867.0	1868.0	1869.0	1870.0	1871.0	1870.8	1869.5	1868.1
157.5°	1904.8	1903.0	1901.3	1899.5	1901.3	1903.0	1904.8	1906.5	1906.5	1904.8	1903.0
160°	1927.3	1925.3	1923.3	1921.2	1923.3	1925.3	1927.3	1929.3	1929.3	1927.3	1925.3
162.5°	1945.0	1942.7	1940.4	1938.1	1940.4	1942.7	1945.0	1947.2	1947.4	1945.4	1943.4
165°	1971.0	1968.0	1965.0	1962.0	1965.0	1968.0	1971.0	1974.0	1974.2	1971.5	1968.8
167.5°	1989.8	1986.5	1983.1	1979.8	1983.1	1986.5	1989.8	1993.2	1993.4	1990.4	1987.5
170°	2000.7	1997.3	1994.0	1990.6	1994.0	1997.3	2000.7	2004.0	2004.4	2001.7	1999.0
172.5°	2007.5	2003.9	2000.3	1996.6	2000.3	2003.9	2007.5	2011.1	2011.6	2008.9	2006.2
175°	2016.2	2012.2	2008.2	2004.2	2008.2	2012.2	2016.2	2020.3	2020.8	2017.8	2014.7
177.5°	2018.7	2015.4	2012.2	2009.0	2012.2	2015.4	2018.7	2021.9	2022.4	2020.3	2018.1
180°	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2



TEST NUMBER: P332859

CATALOG NUMBER: S124DIW-S1195D1560U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4
2.5°	1842.4	1845.0	1855.2	1864.8	1876.3	1884.6	1890.3	1896.7	1910.1	1921.0	1931.2
5°	1726.2	1730.2	1750.9	1765.3	1790.0	1811.6	1828.4	1846.7	1868.3	1897.8	1925.0
7.5°	1623.8	1638.7	1661.3	1684.6	1709.9	1738.1	1762.7	1790.4	1827.6	1868.1	1910.0
10°	1565.7	1582.5	1606.4	1633.6	1657.5	1690.2	1720.6	1753.3	1795.6	1845.1	1894.6
12.5°	1507.6	1535.2	1553.4	1585.6	1611.5	1638.5	1670.8	1713.7	1763.1	1815.1	1874.8
15°	1434.7	1449.9	1485.0	1502.6	1539.3	1580.9	1612.8	1655.9	1703.8	1772.5	1839.5
17.5°	1350.8	1370.7	1398.7	1432.2	1474.3	1506.8	1546.5	1590.9	1651.3	1719.5	1803.5
20°	1295.8	1312.6	1346.9	1383.6	1428.4	1462.7	1505.0	1548.1	1610.4	1683.1	1770.9
22.5°	1246.6	1262.8	1299.0	1333.2	1376.6	1418.6	1462.8	1513.0	1572.7	1649.2	1738.9
25°	1170.5	1192.0	1224.0	1259.1	1300.6	1348.5	1396.4	1441.1	1505.0	1585.6	1681.5
27.5°	1102.9	1120.2	1143.3	1183.2	1230.4	1276.7	1324.2	1380.5	1441.8	1527.0	1626.5
30°	1059.5	1075.5	1098.6	1135.3	1179.3	1228.8	1278.3	1332.5	1396.4	1481.1	1582.5
32.5°	1025.0	1037.1	1057.7	1090.6	1130.7	1182.8	1231.6	1287.8	1354.9	1438.3	1537.1
35°	974.1	984.4	992.4	1023.6	1059.5	1107.4	1156.9	1216.8	1281.5	1360.5	1459.5
37.5°	924.1	927.6	939.3	959.7	994.5	1038.6	1084.6	1143.5	1209.8	1290.1	1379.3
40°	893.4	895.0	902.2	921.4	951.7	993.2	1037.9	1096.2	1159.3	1235.1	1323.8
42.5°	863.4	862.4	869.0	882.4	910.8	948.5	992.6	1045.8	1108.8	1178.9	1262.4
45°	816.0	816.0	814.4	825.6	848.7	885.4	922.2	973.3	1026.0	1094.6	1164.9
47.5°	766.5	762.0	763.4	769.2	788.7	818.9	855.9	897.7	944.2	1002.3	1064.0
50°	734.5	728.2	725.8	732.1	749.7	776.1	811.2	847.9	891.8	942.9	995.6
52.5°	699.4	693.0	688.7	693.2	709.5	733.9	765.8	798.1	837.5	879.1	924.7
55°	645.1	637.9	635.5	637.1	649.1	668.3	695.4	725.0	754.5	788.8	820.8
57.5°	591.6	579.8	577.6	576.8	585.1	602.6	625.3	650.9	672.4	693.2	727.2
60°	556.5	542.1	537.3	536.5	542.9	557.3	578.0	603.6	618.8	633.1	662.7
62.5°	518.8	505.1	494.5	495.7	501.4	515.1	533.3	551.9	561.9	577.6	597.5
65°	460.7	443.1	435.1	432.7	435.9	447.1	461.5	473.5	484.6	491.0	510.2
67.5°	402.6	387.9	376.1	373.2	371.7	379.4	391.2	398.4	406.4	412.0	423.3
70°	361.7	348.9	334.5	329.7	328.9	335.3	346.5	347.3	358.5	360.9	372.9
72.5°	321.4	305.5	295.6	290.8	287.4	293.2	300.5	302.6	308.7	313.0	319.2
75°	258.7	246.7	237.1	229.9	227.5	230.7	230.7	234.7	238.7	241.1	248.3
77.5°	203.6	189.9	178.5	174.4	171.5	169.4	171.2	173.6	171.7	175.8	177.4
80°	165.3	150.9	142.1	140.5	135.7	131.7	130.9	133.3	130.1	131.7	136.5
82.5°	127.6	118.3	108.9	107.3	101.2	99.2	98.4	96.9	96.9	96.6	97.6
85°	75.8	70.3	63.9	59.9	57.5	53.5	53.5	51.9	50.3	48.7	49.5
87.5°	37.7	36.0	32.3	29.8	28.0	24.9	24.3	21.6	20.3	18.9	17.5
90°	35.2	33.2	30.5	27.8	25.1	22.5	19.3	15.6	11.9	8.2	4.5
92.5°	34.0	32.0	29.3	26.6	23.9	21.2	19.8	19.6	19.4	19.2	19.0
95°	35.2	33.2	32.8	32.5	32.2	31.8	37.4	48.8	60.2	71.5	82.9
97.5°	40.0	39.8	77.2	114.6	152.0	189.4	204.6	197.5	190.3	183.2	176.1
100°	60.7	66.4	112.6	158.8	205.1	251.3	271.4	265.4	259.4	253.4	247.3
102.5°	258.2	319.7	325.7	331.8	337.8	343.8	344.6	340.2	335.8	331.4	326.9
105°	473.5	470.5	468.8	467.2	465.5	463.8	462.0	460.0	457.9	455.9	453.9
107.5°	588.1	586.6	584.3	582.1	579.8	577.5	575.9	574.9	573.9	572.9	571.8
110°	665.7	665.0	663.0	661.0	659.0	657.0	655.5	654.5	653.5	652.5	651.5



TEST NUMBER: P332859

CATALOG NUMBER: S124DIW-S1195D1560U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	740.9	741.1	740.1	739.2	738.2	737.3	735.9	734.1	732.3	730.5	728.7
115°	851.2	850.5	850.9	851.2	851.5	851.9	851.5	850.5	849.5	848.5	847.5
117.5°	963.8	963.9	963.2	962.5	961.7	961.0	960.0	958.6	957.3	955.9	954.6
120°	1032.2	1031.5	1031.8	1032.2	1032.5	1032.8	1032.3	1031.0	1029.7	1028.3	1027.0
122.5°	1100.7	1100.3	1099.8	1099.3	1098.9	1098.4	1097.8	1096.9	1096.1	1095.3	1094.5
125°	1195.4	1194.4	1195.0	1195.7	1196.4	1197.0	1196.7	1195.4	1194.0	1192.7	1191.4
127.5°	1291.3	1291.5	1289.9	1288.4	1286.9	1285.3	1284.4	1284.0	1283.7	1283.4	1283.0
130°	1348.5	1348.2	1347.2	1346.2	1345.2	1344.2	1343.5	1343.2	1342.8	1342.5	1342.2
132.5°	1405.2	1404.9	1403.6	1402.3	1401.1	1399.8	1398.9	1398.3	1397.7	1397.0	1396.4
135°	1483.1	1482.4	1481.1	1479.7	1478.4	1477.0	1476.5	1476.9	1477.2	1477.5	1477.9
137.5°	1557.9	1557.2	1555.7	1554.3	1552.8	1551.3	1550.5	1550.4	1550.2	1550.1	1550.0
140°	1604.1	1603.0	1602.4	1601.7	1601.0	1600.4	1599.7	1599.0	1598.4	1597.7	1597.0
142.5°	1647.2	1646.5	1646.1	1645.7	1645.3	1644.9	1644.1	1642.9	1641.7	1640.4	1639.2
145°	1708.9	1708.6	1708.6	1708.6	1708.6	1708.6	1708.1	1707.1	1706.1	1705.1	1704.1
147.5°	1762.9	1762.6	1762.9	1763.3	1763.6	1763.9	1763.2	1761.3	1759.4	1757.5	1755.7
150°	1797.6	1797.6	1797.9	1798.3	1798.6	1798.9	1798.4	1797.1	1795.7	1794.4	1793.1
152.5°	1827.1	1826.5	1827.1	1827.7	1828.3	1829.0	1828.7	1827.6	1826.6	1825.5	1824.4
155°	1866.8	1865.4	1866.5	1867.5	1868.5	1869.5	1869.8	1869.5	1869.1	1868.8	1868.5
157.5°	1901.3	1899.5	1900.7	1901.8	1902.9	1904.1	1904.8	1905.0	1905.2	1905.4	1905.6
160°	1923.3	1921.2	1921.6	1921.9	1922.2	1922.6	1923.3	1924.3	1925.3	1926.3	1927.3
162.5°	1941.3	1939.3	1939.7	1940.0	1940.3	1940.7	1941.5	1942.8	1944.0	1945.3	1946.6
165°	1966.1	1963.5	1963.5	1963.5	1963.5	1963.5	1964.3	1966.0	1967.7	1969.3	1971.0
167.5°	1984.5	1981.6	1981.8	1982.0	1982.2	1982.4	1983.3	1985.1	1986.8	1988.6	1990.3
170°	1996.3	1993.6	1993.3	1993.0	1992.6	1992.3	1993.1	1995.1	1997.1	1999.2	2001.2
172.5°	2003.5	2000.9	2000.5	2000.2	1999.9	1999.5	2000.4	2002.4	2004.4	2006.4	2008.4
175°	2011.7	2008.7	2008.4	2008.0	2007.7	2007.4	2008.2	2010.2	2012.2	2014.2	2016.2
177.5°	2016.0	2013.8	2013.3	2012.8	2012.2	2011.7	2012.4	2014.2	2016.1	2018.0	2019.9
180°	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2



TEST NUMBER: P332859

CATALOG NUMBER: S124DIW-S1195D1560U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4
2.5°	1940.1	1946.5	1954.8	1968.9	1974.0	1980.4	1989.3	1988.7	1991.2	2000.8	2021.3
5°	1947.3	1972.1	1996.0	2024.8	2055.1	2075.1	2102.2	2119.0	2135.8	2157.3	2194.0
7.5°	1950.2	1989.5	2033.4	2083.9	2128.7	2180.5	2220.9	2258.9	2293.2	2338.7	2382.5
10°	1945.7	1998.4	2055.1	2119.0	2186.8	2244.3	2296.2	2355.3	2405.6	2460.7	2510.2
12.5°	1937.4	2001.0	2076.8	2148.4	2227.7	2312.7	2377.4	2437.1	2504.0	2567.4	2643.7
15°	1918.6	2005.6	2094.2	2188.4	2294.6	2392.8	2486.3	2563.7	2635.6	2730.6	2830.4
17.5°	1894.6	1988.5	2100.3	2214.3	2325.3	2437.6	2553.2	2669.6	2760.3	2878.3	2956.4
20°	1872.3	1980.9	2095.8	2231.6	2342.5	2482.3	2597.2	2709.8	2834.4	2951.7	3045.1
22.5°	1841.0	1959.8	2081.8	2216.9	2363.0	2502.7	2635.6	2757.7	2882.3	3009.9	3123.1
25°	1801.2	1909.0	2053.5	2206.8	2352.1	2503.8	2656.3	2809.6	2943.7	3078.7	3184.1
27.5°	1733.5	1869.6	2004.2	2162.4	2323.9	2495.5	2658.6	2819.0	2959.6	3070.5	3135.8
30°	1699.0	1817.2	1963.3	2122.2	2297.0	2481.5	2651.5	2808.8	2939.8	3028.4	3054.7
32.5°	1647.9	1769.9	1912.8	2077.5	2262.5	2452.1	2629.2	2777.5	2886.7	2933.2	2901.4
35°	1572.1	1682.3	1826.8	1995.2	2187.6	2389.6	2564.5	2689.8	2745.7	2701.8	2592.4
37.5°	1481.1	1590.3	1735.4	1900.9	2100.0	2305.3	2463.4	2553.6	2535.1	2425.9	2262.9
40°	1417.2	1519.4	1657.5	1836.3	2030.4	2236.4	2375.3	2424.0	2372.9	2216.4	2043.1
42.5°	1346.3	1445.9	1584.7	1757.1	1962.7	2152.7	2273.7	2277.7	2192.1	2005.0	1831.1
45°	1238.3	1333.3	1464.3	1643.9	1834.0	2012.8	2092.6	2053.5	1895.4	1715.0	1540.1
47.5°	1131.8	1214.2	1343.2	1513.8	1694.2	1844.8	1884.4	1814.0	1645.5	1470.4	1308.3
50°	1053.9	1136.9	1258.3	1421.2	1595.2	1725.4	1744.5	1651.1	1485.8	1309.4	1182.4
52.5°	979.2	1061.6	1178.5	1329.2	1488.6	1605.9	1606.6	1498.5	1333.8	1176.5	1058.5
55°	869.5	943.7	1049.1	1184.0	1326.2	1418.0	1395.6	1283.8	1140.9	1004.4	901.4
57.5°	763.8	828.4	925.5	1038.1	1163.3	1239.0	1201.9	1094.3	966.7	850.9	772.9
60°	695.4	756.9	839.9	946.1	1051.5	1110.6	1075.5	978.1	860.7	767.3	699.4
62.5°	629.0	680.9	760.7	852.9	950.6	994.3	963.0	866.9	765.5	681.0	626.0
65°	534.9	577.3	641.1	720.2	791.2	828.8	802.4	713.0	635.5	574.9	530.9
67.5°	447.1	480.2	528.5	591.9	652.3	672.6	648.6	586.4	520.7	472.2	441.2
70°	386.4	417.6	458.3	507.0	559.7	581.2	557.3	507.8	454.3	409.6	379.2
72.5°	333.4	357.5	391.9	433.5	474.7	496.3	480.0	432.4	387.2	354.0	328.1
75°	253.9	274.7	298.6	328.1	360.1	374.5	360.1	327.3	296.2	271.5	253.1
77.5°	184.6	195.8	214.3	236.3	256.3	267.3	254.9	232.7	213.7	196.7	187.6
80°	140.5	148.5	161.3	178.8	192.4	202.8	194.8	176.4	161.3	150.1	146.1
82.5°	102.2	107.6	115.9	129.0	138.1	143.4	139.9	126.6	120.4	110.5	106.5
85°	50.3	53.5	59.1	63.1	71.1	71.9	72.7	67.1	61.5	59.1	55.9
87.5°	18.9	20.3	22.9	25.6	28.8	29.9	29.8	30.4	28.4	28.1	26.0
90°	8.2	11.9	15.6	19.3	22.5	25.1	27.8	30.5	33.2	35.2	37.2
92.5°	19.2	19.4	19.6	19.8	21.2	23.9	26.6	29.3	32.0	34.0	36.0
95°	71.5	60.2	48.8	37.4	31.8	32.2	32.5	32.8	33.2	35.2	37.2
97.5°	183.2	190.3	197.5	204.6	189.4	152.0	114.6	77.2	39.8	40.0	40.2
100°	253.4	259.4	265.4	271.4	251.3	205.1	158.8	112.6	66.4	60.7	55.0
102.5°	331.4	335.8	340.2	344.6	343.8	337.8	331.8	325.7	319.7	258.2	196.8
105°	455.9	457.9	460.0	462.0	463.8	465.5	467.2	468.8	470.5	473.5	476.5
107.5°	572.9	573.9	574.9	575.9	577.5	579.8	582.1	584.3	586.6	588.1	589.6
110°	652.5	653.5	654.5	655.5	657.0	659.0	661.0	663.0	665.0	665.7	666.4



TEST NUMBER: P332859

CATALOG NUMBER: S124DIW-S1195D1560U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	730.5	732.3	734.1	735.9	737.3	738.2	739.2	740.1	741.1	740.9	740.8
115°	848.5	849.5	850.5	851.5	851.9	851.5	851.2	850.9	850.5	851.2	851.9
117.5°	955.9	957.3	958.6	960.0	961.0	961.7	962.5	963.2	963.9	963.8	963.7
120°	1028.3	1029.7	1031.0	1032.3	1032.8	1032.5	1032.2	1031.8	1031.5	1032.2	1032.8
122.5°	1095.3	1096.1	1096.9	1097.8	1098.4	1098.9	1099.3	1099.8	1100.3	1100.7	1101.1
125°	1192.7	1194.0	1195.4	1196.7	1197.0	1196.4	1195.7	1195.0	1194.4	1195.4	1196.4
127.5°	1283.4	1283.7	1284.0	1284.4	1285.3	1286.9	1288.4	1289.9	1291.5	1291.3	1291.1
130°	1342.5	1342.8	1343.2	1343.5	1344.2	1345.2	1346.2	1347.2	1348.2	1348.5	1348.9
132.5°	1397.0	1397.7	1398.3	1398.9	1399.8	1401.1	1402.3	1403.6	1404.9	1405.2	1405.6
135°	1477.5	1477.2	1476.9	1476.5	1477.0	1478.4	1479.7	1481.1	1482.4	1483.1	1483.7
137.5°	1550.1	1550.2	1550.4	1550.5	1551.3	1552.8	1554.3	1555.7	1557.2	1557.9	1558.7
140°	1597.7	1598.4	1599.0	1599.7	1600.4	1601.0	1601.7	1602.4	1603.0	1604.1	1605.1
142.5°	1640.4	1641.7	1642.9	1644.1	1644.9	1645.3	1645.7	1646.1	1646.5	1647.2	1648.0
145°	1705.1	1706.1	1707.1	1708.1	1708.6	1708.6	1708.6	1708.6	1708.6	1708.9	1709.3
147.5°	1757.5	1759.4	1761.3	1763.2	1763.9	1763.6	1763.3	1762.9	1762.6	1762.9	1763.1
150°	1794.4	1795.7	1797.1	1798.4	1798.9	1798.6	1798.3	1797.9	1797.6	1797.6	1797.6
152.5°	1825.5	1826.6	1827.6	1828.7	1829.0	1828.3	1827.7	1827.1	1826.5	1827.1	1827.6
155°	1868.8	1869.1	1869.5	1869.8	1869.5	1868.5	1867.5	1866.5	1865.4	1866.8	1868.1
157.5°	1905.4	1905.2	1905.0	1904.8	1904.1	1902.9	1901.8	1900.7	1899.5	1901.3	1903.0
160°	1926.3	1925.3	1924.3	1923.3	1922.6	1922.2	1921.9	1921.6	1921.2	1923.3	1925.3
162.5°	1945.3	1944.0	1942.8	1941.5	1940.7	1940.3	1940.0	1939.7	1939.3	1941.3	1943.4
165°	1969.3	1967.7	1966.0	1964.3	1963.5	1963.5	1963.5	1963.5	1963.5	1966.1	1968.8
167.5°	1988.6	1986.8	1985.1	1983.3	1982.4	1982.2	1982.0	1981.8	1981.6	1984.5	1987.5
170°	1999.2	1997.1	1995.1	1993.1	1992.3	1992.6	1993.0	1993.3	1993.6	1996.3	1999.0
172.5°	2006.4	2004.4	2002.4	2000.4	1999.5	1999.9	2000.2	2000.5	2000.9	2003.5	2006.2
175°	2014.2	2012.2	2010.2	2008.2	2007.4	2007.7	2008.0	2008.4	2008.7	2011.7	2014.7
177.5°	2018.0	2016.1	2014.2	2012.4	2011.7	2012.2	2012.8	2013.3	2013.8	2016.0	2018.1
180°	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2



TEST NUMBER: P332859

CATALOG NUMBER: S124DIW-S1195D1560U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4
2.5°	2031.5	2032.8	2038.5	2043.0	2044.3	2050.6	2051.3
5°	2210.0	2223.6	2249.9	2252.3	2256.3	2277.1	2261.1
7.5°	2419.2	2453.7	2476.7	2497.0	2504.3	2513.4	2511.5
10°	2553.3	2604.4	2630.0	2670.7	2672.3	2682.7	2676.3
12.5°	2688.1	2747.5	2794.1	2801.6	2835.8	2841.1	2850.0
15°	2879.1	2942.1	3006.8	3030.0	3077.1	3088.3	3105.8
17.5°	3058.6	3123.1	3168.4	3228.3	3247.6	3273.5	3255.9
20°	3156.9	3227.2	3284.7	3331.8	3351.7	3366.1	3364.5
22.5°	3216.3	3287.2	3333.8	3369.5	3388.1	3394.2	3393.9
25°	3253.5	3294.2	3308.6	3322.2	3301.4	3294.2	3297.4
27.5°	3150.1	3139.5	3102.0	3052.8	3001.7	2961.1	2939.1
30°	3007.6	2945.3	2888.7	2789.6	2738.6	2708.2	2681.1
32.5°	2805.8	2707.1	2598.0	2507.3	2449.2	2404.2	2397.5
35°	2459.9	2311.4	2178.1	2067.1	2009.6	1960.9	1949.7
37.5°	2091.4	1937.1	1817.0	1719.3	1657.5	1623.2	1591.1
40°	1846.7	1714.2	1596.0	1513.0	1465.9	1441.1	1421.2
42.5°	1658.3	1537.3	1419.7	1356.5	1313.9	1298.7	1287.0
45°	1398.0	1285.4	1204.0	1156.1	1131.3	1105.8	1093.8
47.5°	1189.6	1098.0	1044.3	1003.6	977.1	961.9	954.3
50°	1071.5	996.4	948.5	917.4	893.4	881.4	875.1
52.5°	966.7	905.1	864.8	840.1	823.8	815.0	812.5
55°	832.7	785.6	760.1	738.5	726.6	718.6	715.4
57.5°	723.8	687.6	666.8	649.1	644.5	637.8	635.5
60°	652.3	624.4	606.8	594.8	590.8	582.8	584.4
62.5°	589.1	566.2	551.2	544.4	539.1	532.4	534.6
65°	498.2	481.4	473.5	467.1	460.7	456.7	459.9
67.5°	418.0	406.6	395.7	392.0	388.8	388.2	384.8
70°	365.7	356.1	346.5	344.1	344.1	340.9	340.1
72.5°	315.2	308.2	301.8	300.0	297.5	298.8	295.4
75°	243.5	237.9	235.5	233.1	232.3	232.3	229.9
77.5°	180.0	175.8	172.0	172.0	169.1	168.0	167.7
80°	136.5	134.9	131.7	131.7	130.1	130.9	129.3
82.5°	102.7	100.4	99.8	98.5	96.3	96.4	94.9
85°	55.1	52.7	51.9	49.5	47.9	49.5	47.9
87.5°	27.0	26.8	26.4	25.3	24.7	24.9	23.1
90°	39.2	41.2	42.6	43.2	43.9	44.6	45.2
92.5°	38.0	40.0	41.1	41.2	41.4	41.5	41.6
95°	39.2	41.2	42.4	42.7	43.1	43.4	43.7
97.5°	40.4	40.6	40.9	41.2	41.6	41.9	42.2
100°	49.3	43.6	40.9	41.2	41.6	41.9	42.2
102.5°	135.3	73.9	43.2	43.2	43.3	43.4	43.4
105°	479.6	482.6	478.0	466.0	453.9	441.9	429.8
107.5°	591.1	592.5	593.9	595.2	596.4	597.7	599.0
110°	667.1	667.7	668.6	669.6	670.6	671.6	672.6



TEST NUMBER: P332859

CATALOG NUMBER: S124DIW-S1195D1560U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	740.6	740.5	741.1	742.4	743.6	744.9	746.2
115°	852.5	853.2	853.6	853.6	853.6	853.6	853.6
117.5°	963.5	963.4	963.3	963.1	963.0	962.9	962.7
120°	1033.5	1034.2	1034.2	1033.5	1032.8	1032.2	1031.5
122.5°	1101.5	1101.9	1101.7	1101.1	1100.4	1099.7	1099.1
125°	1197.4	1198.4	1199.1	1199.4	1199.7	1200.1	1200.4
127.5°	1290.9	1290.7	1290.4	1290.2	1289.9	1289.6	1289.4
130°	1349.2	1349.5	1349.7	1349.7	1349.7	1349.7	1349.7
132.5°	1405.9	1406.2	1406.3	1406.0	1405.7	1405.5	1405.2
135°	1484.4	1485.1	1485.8	1486.4	1487.1	1487.8	1488.4
137.5°	1559.4	1560.2	1560.4	1560.2	1560.0	1559.8	1559.6
140°	1606.1	1607.1	1607.7	1608.1	1608.4	1608.7	1609.1
142.5°	1648.7	1649.4	1649.8	1649.9	1650.0	1650.0	1650.1
145°	1709.6	1709.9	1710.5	1711.1	1711.8	1712.5	1713.1
147.5°	1763.4	1763.7	1764.0	1764.3	1764.6	1765.0	1765.3
150°	1797.6	1797.6	1797.8	1798.1	1798.4	1798.8	1799.1
152.5°	1828.1	1828.7	1828.8	1828.6	1828.4	1828.2	1828.0
155°	1869.5	1870.8	1871.0	1870.0	1869.0	1868.0	1867.0
157.5°	1904.8	1906.5	1906.5	1904.8	1903.0	1901.3	1899.5
160°	1927.3	1929.3	1929.3	1927.3	1925.3	1923.3	1921.2
162.5°	1945.4	1947.4	1947.2	1945.0	1942.7	1940.4	1938.1
165°	1971.5	1974.2	1974.0	1971.0	1968.0	1965.0	1962.0
167.5°	1990.4	1993.4	1993.2	1989.8	1986.5	1983.1	1979.8
170°	2001.7	2004.4	2004.0	2000.7	1997.3	1994.0	1990.6
172.5°	2008.9	2011.6	2011.1	2007.5	2003.9	2000.3	1996.6
175°	2017.8	2020.8	2020.3	2016.2	2012.2	2008.2	2004.2
177.5°	2020.3	2022.4	2021.9	2018.7	2015.4	2012.2	2009.0
180°	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2

(END OF REPORT)