

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332863-927

Luminaire Tested: **S124DIW-S1195D1560U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332863-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S1195D1560U927-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1560 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8996.5 lumens
Efficiency: N/A
Efficacy: 108.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 82.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332863-927

CATALOG NUMBER: S124DIW-S1195D1560U927-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332863-927

CATALOG NUMBER: S124DIW-S1195D1560U927-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	81	81	81	65	65	65	52	52	52	45
1	97	92	88	85	88	85	81	78	71	68	66	58	56	54	46	44	43	38
2	88	81	74	69	80	74	69	64	62	58	55	51	48	45	40	38	37	32
3	80	71	64	58	73	65	59	54	55	50	46	45	41	38	35	33	31	27
4	73	63	55	49	67	58	51	46	48	43	39	40	36	33	32	29	27	23
5	67	56	48	42	61	51	44	39	43	38	34	36	32	28	29	26	23	20
6	62	50	42	36	57	46	39	34	39	33	29	32	28	25	26	23	21	18
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	24	21	18	16
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	16	14
9	49	37	30	25	45	35	28	23	29	24	20	25	21	18	20	17	15	13
10	46	34	27	22	42	32	25	21	27	22	18	23	19	16	19	16	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12745	12745	12745
5°	12783	12630	12721
10°	12703	12527	12588
15°	12549	12349	12380
20°	12345	12128	12138
25°	12113	11875	11843
30°	11828	11580	11473
35°	11532	11269	11121
40°	11225	10918	10718
45°	10904	10572	10369
50°	10550	10262	9946
55°	10166	9864	9543
60°	9783	9415	9131
65°	9352	8990	8627
70°	8868	8419	8091
75°	8125	7735	7536
80°	7234	6936	6760
85°	6326	6095	5974



TEST NUMBER: P332863-927

CATALOG NUMBER: S124DIW-S1195D1560U927-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	148.7	1.7
10°-20°	418.9	4.7
20°-30°	616.5	6.9
30°-40°	716.7	8.0
40°-50°	716.8	8.0
50°-60°	627.0	7.0
60°-70°	465.6	5.2
70°-80°	264.5	2.9
80°-90°	81.0	0.9
90°-100°	54.6	0.6
100°-110°	348.3	3.9
110°-120°	666.3	7.4
120°-130°	845.9	9.4
130°-140°	905.0	10.1
140°-150°	846.3	9.4
150°-160°	682.5	7.6
160°-170°	440.2	4.9
170°-180°	151.7	1.7
0°-30°	1184.1	13.2
0°-40°	1900.8	21.1
0°-60°	3244.6	36.1
0°-90°	4055.7	45.1
90°-120°	1069.3	11.9
90°-150°	3666.4	40.8
90°-180°	4941.0	54.9
0°-180°	8996.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1579	1579	1579	1579	1579	
5°	1577	1572	1558	1571	1570	150
15°	1502	1496	1478	1484	1481	423
25°	1360	1350	1333	1334	1330	625
35°	1170	1161	1144	1135	1128	731
45°	955	946	926	913	908	736
55°	722	718	701	686	678	647
65°	490	483	471	458	452	485
75°	260	254	248	243	242	277
85°	68	68	66	66	64	75
90°	4	17	26	33	36	7
95°	66	27	26	33	35	84
105°	360	367	373	380	340	376
115°	671	675	674	676	676	660
125°	944	948	946	950	951	842
135°	1171	1170	1174	1177	1179	902
145°	1350	1353	1354	1355	1357	843
155°	1480	1481	1478	1482	1479	682
165°	1561	1556	1555	1564	1554	441
175°	1597	1591	1591	1601	1588	152
180°	1597	1597	1597	1597	1597	



TEST NUMBER: P332863-927

CATALOG NUMBER: S124DIW-S1195D1560U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1578.7	1578.7	1578.7	1578.7	1578.7	1578.7	1578.7	1578.7	1578.7	1578.7	1578.7
2.5°	1582.7	1582.1	1581.4	1580.7	1580.0	1578.4	1576.0	1573.5	1571.1	1568.6	1570.8
5°	1577.4	1576.3	1575.2	1574.1	1573.0	1570.8	1567.7	1564.6	1561.5	1558.5	1561.5
7.5°	1562.7	1561.6	1560.5	1559.3	1558.2	1556.0	1552.5	1549.1	1545.7	1542.2	1544.8
10°	1549.6	1548.5	1547.4	1546.2	1545.1	1542.7	1539.1	1535.4	1531.8	1528.1	1530.3
12.5°	1532.4	1531.3	1530.1	1529.0	1527.9	1525.3	1521.5	1517.7	1513.8	1509.9	1512.4
15°	1501.5	1500.4	1499.3	1498.2	1497.0	1494.4	1490.1	1485.9	1481.7	1477.5	1479.2
17.5°	1464.3	1462.9	1461.5	1460.2	1458.7	1456.0	1452.0	1448.0	1444.1	1440.0	1441.1
20°	1437.0	1435.6	1434.2	1432.8	1431.4	1428.5	1424.3	1420.1	1415.9	1411.7	1412.5
22.5°	1407.6	1405.8	1404.0	1402.1	1400.3	1397.2	1393.0	1388.8	1384.6	1380.3	1381.9
25°	1359.9	1357.9	1355.9	1353.9	1351.9	1349.0	1345.0	1341.2	1337.2	1333.2	1333.6
27.5°	1305.2	1303.1	1301.2	1299.1	1297.1	1294.3	1290.6	1287.0	1283.3	1279.6	1279.0
30°	1268.8	1266.5	1264.2	1262.0	1259.8	1256.8	1253.2	1249.5	1245.9	1242.2	1241.1
32.5°	1230.3	1228.3	1226.3	1224.2	1222.2	1219.2	1215.4	1211.5	1207.6	1203.7	1202.4
35°	1170.1	1168.2	1166.2	1164.2	1162.2	1159.3	1155.3	1151.4	1147.5	1143.5	1141.5
37.5°	1106.6	1104.8	1103.0	1101.2	1099.4	1096.4	1092.2	1088.0	1083.7	1079.5	1077.4
40°	1065.1	1062.9	1060.6	1058.4	1056.1	1052.9	1048.7	1044.4	1040.2	1036.0	1033.2
42.5°	1020.6	1019.2	1017.9	1016.5	1015.2	1012.2	1007.5	1002.8	998.1	993.5	990.2
45°	955.1	953.1	951.1	949.1	947.2	944.0	939.4	934.9	930.4	926.0	922.9
47.5°	886.5	885.1	883.8	882.4	881.1	878.4	874.2	870.1	865.9	861.7	858.3
50°	840.0	838.8	837.7	836.5	835.4	832.9	828.9	825.1	821.1	817.1	813.3
52.5°	794.4	793.1	791.7	790.4	789.0	786.2	782.1	777.9	773.8	769.6	766.1
55°	722.3	721.4	720.6	719.8	718.9	716.5	712.6	708.7	704.7	700.8	697.4
57.5°	653.5	652.5	651.6	650.6	649.7	647.2	643.3	639.4	635.6	631.7	628.5
60°	605.9	604.5	603.1	601.7	600.3	597.8	594.1	590.5	586.8	583.1	580.6
62.5°	559.4	558.2	557.0	555.8	554.7	552.2	548.3	544.4	540.5	536.6	534.3
65°	489.6	488.1	486.7	485.3	483.9	481.8	479.0	476.2	473.4	470.6	467.8
67.5°	419.2	418.0	416.6	415.3	414.1	412.0	409.3	406.6	403.9	401.2	398.5
70°	375.7	373.8	371.8	369.8	367.8	365.8	363.5	361.2	358.9	356.7	354.5
72.5°	329.2	327.2	325.2	323.2	321.3	319.4	317.6	315.8	314.0	312.2	310.4
75°	260.5	259.2	257.8	256.4	254.9	253.6	252.2	250.7	249.4	248.0	246.8
77.5°	195.0	194.4	193.8	193.2	192.6	191.6	190.4	189.2	188.0	186.7	186.4
80°	155.6	154.7	153.9	153.0	152.3	151.5	151.0	150.4	149.8	149.2	148.7
82.5°	117.2	116.8	116.4	116.0	115.6	115.3	115.2	115.1	114.9	114.9	114.5
85°	68.3	68.3	68.3	68.3	68.3	68.0	67.5	66.9	66.3	65.8	65.8
87.5°	27.0	27.4	27.7	28.1	28.4	28.8	28.9	29.2	29.3	29.5	29.9
90°	3.6	6.5	9.4	12.4	15.3	17.8	19.9	22.0	24.2	26.3	27.9
92.5°	15.1	15.2	15.4	15.5	15.7	16.8	18.9	21.1	23.2	25.3	26.9
95°	65.7	56.6	47.7	38.7	29.6	25.2	25.5	25.7	26.0	26.3	27.9
97.5°	139.5	145.1	150.8	156.5	162.1	150.0	120.4	90.8	61.2	31.5	31.7
100°	195.9	200.7	205.5	210.2	215.0	199.1	162.5	125.8	89.2	52.6	48.1
102.5°	259.0	262.5	266.0	269.5	273.0	272.4	267.6	262.8	258.0	253.3	204.5
105°	359.6	361.2	362.7	364.4	366.0	367.4	368.8	370.1	371.4	372.7	375.1
107.5°	453.0	453.8	454.6	455.4	456.2	457.5	459.3	461.1	462.9	464.7	465.9
110°	516.1	516.9	517.7	518.5	519.3	520.5	522.0	523.6	525.2	526.8	527.4



TEST NUMBER: P332863-927

CATALOG NUMBER: S124DIW-S1195D1560U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	577.3	578.7	580.1	581.5	583.0	584.1	584.8	585.6	586.3	587.1	586.9
115°	671.4	672.2	673.0	673.8	674.5	674.9	674.5	674.3	674.1	673.8	674.3
117.5°	756.2	757.2	758.4	759.4	760.5	761.3	761.8	762.5	763.0	763.6	763.5
120°	813.6	814.6	815.7	816.7	817.8	818.2	817.9	817.7	817.4	817.1	817.7
122.5°	867.0	867.7	868.3	868.9	869.7	870.1	870.5	870.8	871.2	871.6	872.0
125°	943.8	944.8	945.9	947.0	948.0	948.2	947.8	947.2	946.7	946.2	947.0
127.5°	1016.4	1016.7	1016.9	1017.2	1017.5	1018.2	1019.5	1020.6	1021.8	1023.1	1022.9
130°	1063.3	1063.5	1063.7	1064.1	1064.3	1064.9	1065.6	1066.4	1067.2	1068.0	1068.3
132.5°	1106.2	1106.7	1107.2	1107.7	1108.2	1108.9	1109.9	1110.9	1111.9	1112.9	1113.2
135°	1170.8	1170.4	1170.2	1170.0	1169.7	1170.1	1171.2	1172.2	1173.3	1174.3	1174.9
137.5°	1227.9	1228.0	1228.0	1228.2	1228.3	1228.9	1230.1	1231.3	1232.4	1233.6	1234.1
140°	1265.1	1265.7	1266.2	1266.7	1267.3	1267.8	1268.3	1268.8	1269.4	1269.9	1270.7
142.5°	1298.5	1299.5	1300.5	1301.5	1302.4	1303.1	1303.4	1303.7	1304.0	1304.3	1304.9
145°	1350.0	1350.8	1351.5	1352.3	1353.1	1353.5	1353.5	1353.5	1353.5	1353.5	1353.8
147.5°	1390.8	1392.3	1393.8	1395.3	1396.8	1397.3	1397.1	1396.9	1396.5	1396.3	1396.5
150°	1420.5	1421.5	1422.5	1423.6	1424.7	1425.1	1424.8	1424.6	1424.3	1424.0	1424.0
152.5°	1445.3	1446.1	1447.0	1447.8	1448.7	1448.9	1448.3	1447.9	1447.4	1446.9	1447.4
155°	1480.2	1480.4	1480.7	1481.0	1481.2	1481.0	1480.2	1479.4	1478.6	1477.7	1478.8
157.5°	1509.6	1509.4	1509.3	1509.1	1508.9	1508.4	1507.4	1506.6	1505.7	1504.8	1506.2
160°	1526.8	1526.0	1525.2	1524.4	1523.6	1523.0	1522.7	1522.5	1522.3	1521.9	1523.6
162.5°	1542.1	1541.0	1540.0	1539.1	1538.0	1537.4	1537.1	1536.8	1536.6	1536.3	1537.9
165°	1561.4	1560.0	1558.8	1557.4	1556.1	1555.4	1555.4	1555.4	1555.4	1555.4	1557.5
167.5°	1576.7	1575.3	1573.9	1572.6	1571.1	1570.4	1570.3	1570.1	1569.9	1569.8	1572.1
170°	1585.3	1583.7	1582.1	1580.5	1578.9	1578.3	1578.5	1578.8	1579.1	1579.3	1581.4
172.5°	1591.0	1589.4	1587.9	1586.3	1584.7	1584.0	1584.3	1584.5	1584.8	1585.1	1587.1
175°	1597.2	1595.6	1594.0	1592.4	1590.9	1590.2	1590.5	1590.7	1591.0	1591.3	1593.6
177.5°	1600.1	1598.6	1597.1	1595.6	1594.2	1593.6	1594.0	1594.5	1594.9	1595.3	1597.0
180°	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2



TEST NUMBER: P332863-927

CATALOG NUMBER: S124DIW-S1195D1560U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1578.7	1578.7	1578.7	1578.7	1578.7	1578.7	1578.7	1578.7
2.5°	1573.0	1575.3	1577.6	1578.6	1578.3	1578.1	1577.9	1577.6
5°	1564.6	1567.7	1570.8	1572.1	1571.5	1571.0	1570.4	1569.8
7.5°	1547.2	1549.7	1552.1	1553.2	1552.9	1552.5	1552.2	1551.9
10°	1532.6	1534.9	1537.1	1537.9	1537.4	1536.8	1536.2	1535.6
12.5°	1514.8	1517.3	1519.8	1520.6	1519.8	1519.0	1518.2	1517.4
15°	1480.8	1482.6	1484.2	1484.6	1483.8	1483.0	1482.1	1481.3
17.5°	1442.2	1443.3	1444.3	1444.5	1444.0	1443.4	1442.9	1442.3
20°	1413.4	1414.2	1415.1	1415.2	1414.7	1414.1	1413.6	1412.9
22.5°	1383.4	1384.9	1386.4	1386.6	1385.7	1384.7	1383.6	1382.6
25°	1333.9	1334.1	1334.4	1334.0	1332.8	1331.7	1330.6	1329.5
27.5°	1278.3	1277.6	1276.9	1275.9	1274.5	1273.1	1271.7	1270.3
30°	1239.9	1238.8	1237.7	1236.4	1235.0	1233.7	1232.2	1230.8
32.5°	1201.0	1199.7	1198.3	1197.0	1195.6	1194.1	1192.8	1191.4
35°	1139.6	1137.7	1135.7	1134.0	1132.6	1131.2	1129.7	1128.4
37.5°	1075.2	1073.1	1071.0	1069.0	1067.1	1065.2	1063.4	1061.5
40°	1030.4	1027.5	1024.8	1022.6	1021.3	1019.9	1018.4	1017.0
42.5°	987.0	983.7	980.5	978.3	977.4	976.4	975.5	974.5
45°	919.8	916.7	913.6	911.6	910.8	909.9	909.1	908.2
47.5°	854.8	851.3	847.8	844.9	842.8	840.7	838.5	836.4
50°	809.3	805.3	801.5	798.6	796.9	795.3	793.5	791.9
52.5°	762.6	759.1	755.7	752.9	750.8	748.6	746.5	744.3
55°	694.0	690.7	687.3	684.8	683.1	681.4	679.7	678.0
57.5°	625.3	622.1	618.9	616.5	614.9	613.2	611.6	610.0
60°	578.1	575.6	573.1	571.1	569.7	568.2	566.9	565.5
62.5°	532.0	529.7	527.4	525.5	524.1	522.7	521.3	519.9
65°	464.9	462.2	459.3	457.2	455.8	454.4	453.0	451.6
67.5°	395.9	393.2	390.5	388.9	388.5	388.1	387.7	387.3
70°	352.2	350.0	347.7	346.2	345.3	344.5	343.6	342.8
72.5°	308.6	306.8	305.0	303.6	302.9	302.0	301.1	300.3
75°	245.7	244.5	243.4	242.7	242.5	242.2	241.9	241.6
77.5°	186.0	185.7	185.4	184.8	184.1	183.4	182.6	181.9
80°	148.1	147.6	147.0	146.6	146.3	146.0	145.8	145.4
82.5°	114.2	113.8	113.5	113.2	112.9	112.6	112.3	112.1
85°	65.8	65.8	65.8	65.7	65.4	65.0	64.8	64.5
87.5°	30.2	30.5	30.8	31.1	31.1	31.2	31.4	31.4
90°	29.5	31.1	32.6	33.7	34.2	34.8	35.3	35.8
92.5°	28.5	30.1	31.7	32.6	32.6	32.8	32.9	33.0
95°	29.5	31.1	32.6	33.6	33.8	34.1	34.4	34.6
97.5°	31.8	32.0	32.2	32.4	32.6	33.0	33.2	33.4
100°	43.6	39.1	34.5	32.4	32.6	33.0	33.2	33.4
102.5°	155.9	107.2	58.5	34.2	34.2	34.3	34.4	34.4
105°	377.5	379.9	382.3	378.7	369.2	359.6	350.1	340.5
107.5°	467.1	468.3	469.4	470.5	471.5	472.5	473.5	474.5
110°	527.9	528.5	528.9	529.7	530.4	531.2	532.0	532.8



TEST NUMBER: P332863-927

CATALOG NUMBER: S124DIW-S1195D1560U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	586.8	586.7	586.6	587.1	588.1	589.1	590.1	591.1
115°	674.9	675.3	675.9	676.2	676.2	676.2	676.2	676.2
117.5°	763.4	763.3	763.2	763.1	763.0	762.9	762.8	762.6
120°	818.2	818.7	819.3	819.3	818.7	818.2	817.7	817.1
122.5°	872.3	872.6	872.9	872.7	872.3	871.7	871.2	870.7
125°	947.8	948.6	949.4	949.9	950.1	950.4	950.7	950.9
127.5°	1022.8	1022.6	1022.5	1022.2	1022.1	1021.8	1021.6	1021.4
130°	1068.6	1068.8	1069.1	1069.2	1069.2	1069.2	1069.2	1069.2
132.5°	1113.5	1113.7	1114.0	1114.0	1113.8	1113.6	1113.4	1113.2
135°	1175.4	1175.9	1176.5	1177.0	1177.5	1178.1	1178.6	1179.1
137.5°	1234.8	1235.3	1236.0	1236.1	1236.0	1235.8	1235.6	1235.5
140°	1271.5	1272.3	1273.1	1273.6	1273.9	1274.1	1274.4	1274.7
142.5°	1305.5	1306.1	1306.6	1306.9	1307.0	1307.1	1307.1	1307.2
145°	1354.1	1354.3	1354.6	1355.0	1355.5	1356.1	1356.6	1357.1
147.5°	1396.7	1396.9	1397.2	1397.4	1397.6	1397.9	1398.2	1398.4
150°	1424.0	1424.0	1424.0	1424.2	1424.4	1424.7	1425.0	1425.2
152.5°	1447.8	1448.2	1448.7	1448.7	1448.6	1448.4	1448.3	1448.1
155°	1479.9	1481.0	1482.0	1482.2	1481.4	1480.6	1479.8	1479.0
157.5°	1507.5	1508.9	1510.3	1510.3	1508.9	1507.5	1506.2	1504.8
160°	1525.2	1526.8	1528.4	1528.4	1526.8	1525.2	1523.6	1521.9
162.5°	1539.5	1541.1	1542.7	1542.5	1540.8	1539.0	1537.2	1535.3
165°	1559.6	1561.8	1563.9	1563.8	1561.4	1559.0	1556.6	1554.3
167.5°	1574.5	1576.8	1579.1	1579.0	1576.3	1573.7	1571.0	1568.4
170°	1583.6	1585.7	1587.9	1587.5	1584.9	1582.2	1579.6	1576.9
172.5°	1589.3	1591.4	1593.6	1593.2	1590.3	1587.5	1584.6	1581.7
175°	1596.0	1598.5	1600.8	1600.4	1597.2	1594.0	1590.9	1587.7
177.5°	1598.7	1600.4	1602.1	1601.7	1599.2	1596.6	1594.0	1591.5
180°	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2

(END OF REPORT)