

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332839

Luminaire Tested: **S124DIW-S1195D470U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332839
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S1195D470U835-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 470 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6990.0 lumens
Efficiency: N/A
Efficacy: 133.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 52.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332839

CATALOG NUMBER: S124DIW-S1195D470U835-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332839

CATALOG NUMBER: S124DIW-S1195D470U835-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	113	113	113	113	107	107	107	107	96	96	96	86	86	86	77	77	77	73
1	103	98	94	91	98	94	90	87	84	82	79	76	74	72	68	67	65	62
2	94	86	80	74	89	82	76	71	74	69	66	67	63	60	60	57	55	52
3	86	76	68	62	81	72	65	60	65	60	55	59	55	51	53	50	47	44
4	78	67	59	52	74	64	56	51	58	52	47	53	48	44	48	44	40	37
5	72	60	51	45	68	57	49	44	52	46	41	47	42	38	43	39	35	33
6	66	54	45	39	63	52	44	38	47	41	36	43	38	33	39	35	31	29
7	62	49	40	35	58	47	39	34	43	36	32	39	34	30	36	31	28	25
8	57	44	36	31	54	43	35	30	39	33	28	36	30	27	33	28	25	23
9	53	41	33	28	51	39	32	27	36	30	25	33	28	24	30	26	22	20
10	50	37	30	25	48	36	29	24	33	27	23	31	25	22	28	24	20	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16088	16088	16088
5°	16136	15943	16058
10°	16035	15813	15891
15°	15841	15588	15628
20°	15584	15309	15323
25°	15291	14991	14949
30°	14930	14618	14483
35°	14557	14226	14038
40°	14169	13782	13529
45°	13764	13345	13089
50°	13317	12955	12554
55°	12833	12451	12047
60°	12350	11885	11525
65°	11805	11347	10890
70°	11195	10629	10213
75°	10259	9763	9513
80°	9131	8759	8536
85°	7984	7688	7540



TEST NUMBER: P332839

CATALOG NUMBER: S124DIW-S1195D470U835-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	187.7	2.7
10°-20°	528.8	7.6
20°-30°	778.3	11.1
30°-40°	904.8	12.9
40°-50°	904.8	12.9
50°-60°	791.5	11.3
60°-70°	587.8	8.4
70°-80°	333.9	4.8
80°-90°	98.1	1.4
90°-100°	20.7	0.3
100°-110°	132.1	1.9
110°-120°	252.8	3.6
120°-130°	320.9	4.6
130°-140°	343.3	4.9
140°-150°	321.0	4.6
150°-160°	258.9	3.7
160°-170°	167.0	2.4
170°-180°	57.6	0.8
0°-30°	1494.7	21.4
0°-40°	2399.5	34.3
0°-60°	4095.8	58.6
0°-90°	5115.6	73.2
90°-120°	405.6	5.8
90°-150°	1390.9	19.9
90°-180°	1874.0	26.8
0°-180°	6990.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1993	1993	1993	1993	1993	
5°	1991	1984	1967	1984	1982	189
15°	1895	1888	1865	1874	1870	534
25°	1717	1705	1683	1684	1678	789
35°	1477	1465	1444	1433	1424	923
45°	1206	1194	1169	1152	1146	929
55°	912	906	885	866	856	816
65°	618	610	594	578	570	612
75°	329	321	313	307	305	350
85°	86	86	83	83	81	95
90°	1	6	10	13	14	6
95°	25	10	10	13	13	32
105°	136	139	141	144	129	143
115°	255	256	256	256	256	251
125°	358	360	359	360	361	320
135°	444	444	446	446	447	342
145°	512	513	514	514	515	320
155°	562	562	561	562	561	259
165°	592	590	590	593	590	167
175°	606	603	604	607	602	58
180°	606	606	606	606	606	



TEST NUMBER: P332839

CATALOG NUMBER: S124DIW-S1195D470U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8
2.5°	1997.9	1997.1	1996.2	1995.4	1994.5	1992.5	1989.4	1986.3	1983.2	1980.1	1982.9
5°	1991.2	1989.8	1988.4	1987.0	1985.6	1982.9	1979.0	1975.1	1971.2	1967.3	1971.2
7.5°	1972.7	1971.3	1969.9	1968.4	1967.0	1964.2	1959.8	1955.5	1951.2	1946.8	1950.0
10°	1956.1	1954.7	1953.3	1951.8	1950.4	1947.4	1942.8	1938.2	1933.6	1929.0	1931.8
12.5°	1934.4	1933.0	1931.5	1930.1	1928.7	1925.5	1920.7	1915.8	1910.9	1906.0	1909.1
15°	1895.4	1894.0	1892.6	1891.2	1889.7	1886.4	1881.0	1875.7	1870.4	1865.1	1867.2
17.5°	1848.5	1846.7	1844.9	1843.2	1841.4	1838.0	1832.9	1827.9	1822.9	1817.8	1819.2
20°	1814.0	1812.2	1810.4	1808.7	1806.9	1803.3	1798.0	1792.7	1787.4	1782.0	1783.1
22.5°	1776.9	1774.6	1772.3	1769.9	1767.6	1763.7	1758.4	1753.1	1747.8	1742.4	1744.4
25°	1716.6	1714.1	1711.6	1709.1	1706.6	1702.9	1697.9	1693.0	1688.0	1683.0	1683.4
27.5°	1647.6	1645.0	1642.5	1639.9	1637.4	1633.8	1629.2	1624.6	1620.0	1615.3	1614.5
30°	1601.6	1598.8	1595.9	1593.1	1590.3	1586.5	1581.9	1577.3	1572.7	1568.1	1566.7
32.5°	1553.1	1550.5	1548.0	1545.4	1542.8	1539.1	1534.2	1529.3	1524.4	1519.5	1517.8
35°	1477.1	1474.6	1472.1	1469.6	1467.1	1463.4	1458.4	1453.5	1448.5	1443.5	1441.0
37.5°	1396.9	1394.6	1392.4	1390.1	1387.8	1384.0	1378.7	1373.4	1368.0	1362.7	1360.0
40°	1344.5	1341.7	1338.8	1336.0	1333.2	1329.1	1323.8	1318.4	1313.1	1307.8	1304.2
42.5°	1288.3	1286.6	1284.9	1283.2	1281.5	1277.7	1271.8	1265.9	1260.0	1254.1	1250.0
45°	1205.6	1203.1	1200.6	1198.1	1195.7	1191.6	1185.9	1180.2	1174.5	1168.9	1165.0
47.5°	1119.0	1117.3	1115.6	1113.9	1112.2	1108.8	1103.5	1098.3	1093.0	1087.8	1083.4
50°	1060.3	1058.9	1057.4	1056.0	1054.6	1051.4	1046.4	1041.5	1036.5	1031.5	1026.6
52.5°	1002.8	1001.1	999.4	997.7	996.0	992.5	987.3	982.0	976.8	971.5	967.1
55°	911.8	910.7	909.7	908.6	907.5	904.5	899.5	894.6	889.6	884.6	880.4
57.5°	824.9	823.7	822.5	821.3	820.1	817.0	812.1	807.2	802.3	797.4	793.4
60°	764.9	763.1	761.3	759.6	757.8	754.6	750.0	745.4	740.7	736.1	732.9
62.5°	706.1	704.6	703.1	701.6	700.2	697.0	692.1	687.2	682.3	677.4	674.5
65°	618.0	616.2	614.4	612.6	610.9	608.2	604.7	601.1	597.6	594.0	590.5
67.5°	529.2	527.6	525.9	524.3	522.7	520.1	516.7	513.3	509.9	506.5	503.1
70°	474.3	471.8	469.3	466.8	464.3	461.7	458.8	456.0	453.1	450.3	447.5
72.5°	415.5	413.0	410.5	408.0	405.6	403.2	400.9	398.6	396.4	394.1	391.8
75°	328.9	327.2	325.4	323.6	321.8	320.1	318.3	316.5	314.8	313.0	311.6
77.5°	246.2	245.4	244.7	243.9	243.1	241.9	240.4	238.8	237.3	235.7	235.3
80°	196.4	195.3	194.3	193.2	192.2	191.3	190.6	189.8	189.1	188.4	187.7
82.5°	147.9	147.4	146.9	146.4	145.9	145.6	145.4	145.3	145.1	145.0	144.6
85°	86.2	86.2	86.2	86.2	86.2	85.9	85.2	84.5	83.7	83.0	83.0
87.5°	33.5	33.4	33.4	33.3	33.2	33.1	33.0	32.9	32.8	32.7	32.8
90°	1.4	2.5	3.6	4.7	5.8	6.7	7.6	8.4	9.2	10.0	10.6
92.5°	5.7	5.8	5.8	5.9	6.0	6.4	7.2	8.0	8.8	9.6	10.2
95°	24.9	21.5	18.1	14.7	11.2	9.6	9.7	9.8	9.9	10.0	10.6
97.5°	52.9	55.1	57.2	59.3	61.5	56.9	45.7	34.4	23.2	12.0	12.0
100°	74.3	76.1	78.0	79.8	81.6	75.5	61.6	47.7	33.8	19.9	18.2
102.5°	98.3	99.6	100.9	102.2	103.6	103.3	101.5	99.7	97.9	96.1	77.6
105°	136.4	137.0	137.6	138.2	138.8	139.4	139.9	140.4	140.9	141.4	142.3
107.5°	171.9	172.2	172.5	172.8	173.1	173.6	174.2	174.9	175.6	176.3	176.7
110°	195.8	196.1	196.4	196.7	197.0	197.4	198.0	198.7	199.3	199.9	200.1



TEST NUMBER: P332839

CATALOG NUMBER: S124DIW-S1195D470U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	219.0	219.5	220.1	220.6	221.2	221.6	221.9	222.1	222.4	222.7	222.7
115°	254.7	255.0	255.3	255.6	255.9	256.0	255.9	255.8	255.7	255.6	255.8
117.5°	286.9	287.3	287.7	288.1	288.5	288.8	289.0	289.2	289.5	289.7	289.6
120°	308.6	309.0	309.4	309.8	310.2	310.4	310.3	310.2	310.1	310.0	310.2
122.5°	328.9	329.2	329.4	329.7	329.9	330.1	330.2	330.4	330.5	330.7	330.8
125°	358.0	358.4	358.8	359.2	359.6	359.7	359.5	359.3	359.1	358.9	359.2
127.5°	385.6	385.7	385.8	385.9	386.0	386.3	386.7	387.2	387.7	388.1	388.1
130°	403.3	403.4	403.6	403.7	403.8	404.0	404.3	404.6	404.9	405.2	405.3
132.5°	419.7	419.8	420.0	420.2	420.4	420.7	421.1	421.4	421.8	422.2	422.3
135°	444.1	444.0	443.9	443.8	443.7	443.9	444.3	444.7	445.1	445.5	445.7
137.5°	465.8	465.8	465.9	465.9	466.0	466.2	466.6	467.1	467.5	468.0	468.2
140°	479.9	480.1	480.3	480.5	480.7	480.9	481.1	481.4	481.6	481.8	482.1
142.5°	492.6	493.0	493.4	493.7	494.1	494.3	494.4	494.6	494.7	494.8	495.0
145°	512.1	512.4	512.7	513.0	513.3	513.5	513.5	513.5	513.5	513.5	513.6
147.5°	527.6	528.2	528.7	529.3	529.9	530.1	530.0	529.9	529.8	529.7	529.8
150°	538.9	539.3	539.7	540.1	540.5	540.6	540.5	540.4	540.3	540.2	540.2
152.5°	548.3	548.6	548.9	549.2	549.6	549.6	549.5	549.3	549.1	548.9	549.1
155°	561.5	561.6	561.7	561.8	561.9	561.8	561.5	561.2	560.9	560.6	561.0
157.5°	572.7	572.6	572.5	572.5	572.4	572.2	571.9	571.5	571.2	570.9	571.4
160°	579.2	578.9	578.6	578.3	578.0	577.8	577.7	577.6	577.5	577.4	578.0
162.5°	585.0	584.6	584.2	583.8	583.5	583.2	583.1	583.0	582.9	582.8	583.4
165°	592.3	591.8	591.3	590.8	590.3	590.1	590.1	590.1	590.1	590.1	590.9
167.5°	598.1	597.6	597.1	596.6	596.0	595.7	595.7	595.6	595.6	595.5	596.4
170°	601.4	600.8	600.2	599.6	599.0	598.7	598.8	598.9	599.0	599.1	599.9
172.5°	603.6	603.0	602.4	601.8	601.2	600.9	601.0	601.1	601.2	601.3	602.1
175°	605.9	605.3	604.7	604.1	603.5	603.3	603.4	603.5	603.6	603.7	604.6
177.5°	607.0	606.5	605.9	605.3	604.8	604.6	604.7	604.9	605.0	605.2	605.8
180°	605.9	605.9	605.9	605.9	605.9	605.9	605.9	605.9	605.9	605.9	605.9



TEST NUMBER: P332839

CATALOG NUMBER: S124DIW-S1195D470U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8
2.5°	1985.7	1988.6	1991.4	1992.7	1992.4	1992.1	1991.8	1991.5
5°	1975.1	1979.0	1982.9	1984.5	1983.8	1983.1	1982.4	1981.6
7.5°	1953.1	1956.2	1959.3	1960.7	1960.3	1959.8	1959.4	1959.0
10°	1934.6	1937.5	1940.3	1941.4	1940.7	1940.0	1939.2	1938.5
12.5°	1912.2	1915.3	1918.5	1919.5	1918.5	1917.5	1916.5	1915.5
15°	1869.3	1871.5	1873.6	1874.1	1873.1	1872.0	1870.9	1869.9
17.5°	1820.5	1821.9	1823.2	1823.5	1822.8	1822.1	1821.4	1820.7
20°	1784.2	1785.2	1786.3	1786.5	1785.8	1785.1	1784.4	1783.6
22.5°	1746.3	1748.2	1750.1	1750.4	1749.2	1747.9	1746.6	1745.3
25°	1683.8	1684.1	1684.5	1683.9	1682.5	1681.1	1679.7	1678.3
27.5°	1613.6	1612.8	1611.9	1610.6	1608.8	1607.1	1605.3	1603.5
30°	1565.2	1563.8	1562.4	1560.8	1559.0	1557.3	1555.5	1553.7
32.5°	1516.1	1514.4	1512.7	1511.0	1509.2	1507.4	1505.7	1503.9
35°	1438.6	1436.1	1433.6	1431.5	1429.7	1427.9	1426.1	1424.4
37.5°	1357.3	1354.6	1351.9	1349.4	1347.1	1344.7	1342.4	1340.0
40°	1300.7	1297.1	1293.6	1290.9	1289.2	1287.4	1285.6	1283.8
42.5°	1245.9	1241.8	1237.7	1235.0	1233.8	1232.6	1231.4	1230.2
45°	1161.1	1157.2	1153.3	1150.8	1149.7	1148.6	1147.6	1146.5
47.5°	1079.0	1074.6	1070.2	1066.6	1063.9	1061.2	1058.5	1055.8
50°	1021.6	1016.6	1011.7	1008.1	1006.0	1003.9	1001.7	999.6
52.5°	962.7	958.3	953.9	950.4	947.7	945.0	942.3	939.6
55°	876.1	871.9	867.6	864.4	862.3	860.2	858.0	855.9
57.5°	789.4	785.3	781.3	778.2	776.2	774.1	772.0	770.0
60°	729.7	726.6	723.4	720.9	719.1	717.3	715.6	713.8
62.5°	671.5	668.6	665.7	663.4	661.6	659.8	658.1	656.3
65°	586.9	583.4	579.8	577.2	575.4	573.6	571.8	570.1
67.5°	499.7	496.3	492.9	490.9	490.4	489.9	489.4	488.9
70°	444.6	441.8	438.9	437.0	435.9	434.9	433.8	432.7
72.5°	389.6	387.3	385.0	383.3	382.3	381.2	380.1	379.1
75°	310.1	308.7	307.3	306.4	306.1	305.7	305.3	305.0
77.5°	234.8	234.4	234.0	233.3	232.4	231.5	230.5	229.6
80°	187.0	186.3	185.6	185.1	184.7	184.3	184.0	183.6
82.5°	144.1	143.7	143.3	142.9	142.5	142.2	141.8	141.5
85°	83.0	83.0	83.0	82.9	82.5	82.1	81.8	81.4
87.5°	32.9	33.0	33.1	33.2	33.3	33.3	33.3	33.4
90°	11.2	11.8	12.4	12.8	13.0	13.2	13.4	13.6
92.5°	10.8	11.4	12.0	12.3	12.4	12.4	12.5	12.5
95°	11.2	11.8	12.4	12.7	12.8	12.9	13.0	13.1
97.5°	12.1	12.1	12.2	12.3	12.4	12.5	12.6	12.7
100°	16.5	14.8	13.1	12.3	12.4	12.5	12.6	12.7
102.5°	59.1	40.7	22.2	13.0	13.0	13.0	13.0	13.1
105°	143.2	144.1	145.0	143.7	140.0	136.4	132.8	129.2
107.5°	177.2	177.6	178.1	178.5	178.9	179.2	179.6	180.0
110°	200.3	200.5	200.7	200.9	201.2	201.5	201.8	202.1



TEST NUMBER: P332839

CATALOG NUMBER: S124DIW-S1195D470U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	222.6	222.6	222.5	222.7	223.1	223.5	223.9	224.2
115°	256.0	256.2	256.4	256.5	256.5	256.5	256.5	256.5
117.5°	289.6	289.6	289.5	289.5	289.4	289.4	289.4	289.3
120°	310.4	310.6	310.8	310.8	310.6	310.4	310.2	310.0
122.5°	330.9	331.0	331.1	331.1	330.9	330.7	330.5	330.3
125°	359.5	359.8	360.1	360.3	360.4	360.5	360.6	360.7
127.5°	388.0	387.9	387.9	387.8	387.7	387.6	387.6	387.5
130°	405.4	405.5	405.6	405.6	405.6	405.6	405.6	405.6
132.5°	422.4	422.5	422.6	422.6	422.5	422.5	422.4	422.3
135°	445.9	446.1	446.3	446.5	446.7	446.9	447.1	447.3
137.5°	468.4	468.6	468.9	468.9	468.9	468.8	468.8	468.7
140°	482.4	482.7	483.0	483.2	483.3	483.4	483.5	483.6
142.5°	495.2	495.5	495.7	495.8	495.8	495.9	495.9	495.9
145°	513.7	513.8	513.9	514.0	514.2	514.4	514.6	514.8
147.5°	529.9	529.9	530.0	530.1	530.2	530.3	530.4	530.5
150°	540.2	540.2	540.2	540.3	540.4	540.5	540.6	540.7
152.5°	549.2	549.4	549.6	549.6	549.6	549.5	549.4	549.4
155°	561.4	561.8	562.2	562.3	562.0	561.7	561.4	561.1
157.5°	571.9	572.4	572.9	572.9	572.4	571.9	571.4	570.9
160°	578.6	579.2	579.8	579.8	579.2	578.6	578.0	577.4
162.5°	584.0	584.6	585.2	585.2	584.5	583.8	583.1	582.5
165°	591.7	592.5	593.3	593.2	592.3	591.4	590.5	589.6
167.5°	597.3	598.2	599.1	599.0	598.0	597.0	596.0	595.0
170°	600.7	601.5	602.4	602.3	601.2	600.2	599.2	598.2
172.5°	602.9	603.7	604.5	604.4	603.3	602.2	601.1	600.0
175°	605.5	606.4	607.3	607.1	605.9	604.7	603.5	602.3
177.5°	606.5	607.1	607.8	607.6	606.7	605.7	604.7	603.8
180°	605.9	605.9	605.9	605.9	605.9	605.9	605.9	605.9

(END OF REPORT)