

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332840

Luminaire Tested: **S124DIW-S1195D470U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S1195D470U835-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 470 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6741.2 lumens
Efficiency: N/A
Efficacy: 128.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 52.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332840

CATALOG NUMBER: S124DIW-S1195D470U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332840

CATALOG NUMBER: S124DIW-S1195D470U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	113	113	113	113	108	108	108	108	98	98	98	88	88	88	80	80	80	80	80	80	80	80	80	76														
1	104	99	95	91	98	94	91	88	86	83	80	78	76	74	71	69	67	67	67	67	67	67	67	64														
2	94	86	80	75	89	83	77	72	75	71	67	68	65	62	62	59	57	57	57	57	57	57	57	53														
3	86	76	68	62	82	73	66	60	66	61	56	60	56	52	55	51	48	48	48	48	48	48	48	45														
4	79	67	59	53	75	65	57	51	59	53	48	54	49	45	49	45	42	42	42	42	42	42	42	39														
5	72	60	52	45	69	58	50	44	53	46	41	49	43	39	44	40	36	36	36	36	36	36	36	34														
6	67	54	46	40	63	52	44	39	48	41	36	44	38	34	40	36	32	32	32	32	32	32	32	30														
7	62	49	41	35	59	47	39	34	44	37	32	40	35	30	37	32	29	29	29	29	29	29	29	26														
8	58	45	37	31	55	43	36	30	40	33	29	37	31	27	34	29	26	26	26	26	26	26	26	24														
9	54	41	33	28	51	40	32	27	37	30	26	34	28	25	31	27	23	23	23	23	23	23	23	21														
10	50	38	30	25	48	36	29	25	34	28	23	31	26	22	29	24	21	21	21	21	21	21	21	19														

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16088	16088	16088
5°	16136	15943	16058
10°	16035	15813	15891
15°	15841	15588	15628
20°	15584	15309	15323
25°	15291	14991	14949
30°	14930	14618	14483
35°	14557	14226	14038
40°	14169	13782	13529
45°	13764	13345	13089
50°	13317	12955	12554
55°	12833	12451	12047
60°	12350	11885	11525
65°	11805	11347	10890
70°	11195	10629	10213
75°	10259	9763	9513
80°	9131	8759	8536
85°	7984	7688	7540



TEST NUMBER: P332840

CATALOG NUMBER: S124DIW-S1195D470U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	187.7	2.8
10°-20°	528.8	7.8
20°-30°	778.3	11.5
30°-40°	904.8	13.4
40°-50°	904.8	13.4
50°-60°	791.5	11.7
60°-70°	587.8	8.7
70°-80°	333.9	5.0
80°-90°	98.1	1.5
90°-100°	38.6	0.6
100°-110°	114.5	1.7
110°-120°	194.3	2.9
120°-130°	256.2	3.8
130°-140°	287.7	4.3
140°-150°	282.7	4.2
150°-160°	237.8	3.5
160°-170°	158.2	2.3
170°-180°	55.4	0.8
0°-30°	1494.7	22.2
0°-40°	2399.5	35.6
0°-60°	4095.8	60.8
0°-90°	5115.6	75.9
90°-120°	347.4	5.2
90°-150°	1174.1	17.4
90°-180°	1626.0	24.1
0°-180°	6741.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1993	1993	1993	1993	1993	
5°	1991	1984	1967	1984	1982	189
15°	1895	1888	1865	1874	1870	534
25°	1717	1705	1683	1684	1678	789
35°	1477	1465	1444	1433	1424	923
45°	1206	1194	1169	1152	1146	929
55°	912	906	885	866	856	816
65°	618	610	594	578	570	612
75°	329	321	313	307	305	350
85°	86	86	83	83	81	95
90°	1	6	10	13	14	6
95°	27	31	34	36	36	30
105°	106	106	108	109	111	112
115°	198	198	197	196	196	195
125°	288	288	287	286	286	256
135°	371	374	374	373	372	287
145°	451	453	453	453	451	282
155°	517	517	516	518	516	238
165°	562	561	560	563	561	158
175°	585	583	582	585	582	56
180°	586	586	586	586	586	



TEST NUMBER: P332840

CATALOG NUMBER: S124DIW-S1195D470U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8
2.5°	1997.9	1997.1	1996.2	1995.4	1994.5	1992.5	1989.4	1986.3	1983.2	1980.1	1982.9
5°	1991.2	1989.8	1988.4	1987.0	1985.6	1982.9	1979.0	1975.1	1971.2	1967.3	1971.2
7.5°	1972.7	1971.3	1969.9	1968.4	1967.0	1964.2	1959.8	1955.5	1951.2	1946.8	1950.0
10°	1956.1	1954.7	1953.3	1951.8	1950.4	1947.4	1942.8	1938.2	1933.6	1929.0	1931.8
12.5°	1934.4	1933.0	1931.5	1930.1	1928.7	1925.5	1920.7	1915.8	1910.9	1906.0	1909.1
15°	1895.4	1894.0	1892.6	1891.2	1889.7	1886.4	1881.0	1875.7	1870.4	1865.1	1867.2
17.5°	1848.5	1846.7	1844.9	1843.2	1841.4	1838.0	1832.9	1827.9	1822.9	1817.8	1819.2
20°	1814.0	1812.2	1810.4	1808.7	1806.9	1803.3	1798.0	1792.7	1787.4	1782.0	1783.1
22.5°	1776.9	1774.6	1772.3	1769.9	1767.6	1763.7	1758.4	1753.1	1747.8	1742.4	1744.4
25°	1716.6	1714.1	1711.6	1709.1	1706.6	1702.9	1697.9	1693.0	1688.0	1683.0	1683.4
27.5°	1647.6	1645.0	1642.5	1639.9	1637.4	1633.8	1629.2	1624.6	1620.0	1615.3	1614.5
30°	1601.6	1598.8	1595.9	1593.1	1590.3	1586.5	1581.9	1577.3	1572.7	1568.1	1566.7
32.5°	1553.1	1550.5	1548.0	1545.4	1542.8	1539.1	1534.2	1529.3	1524.4	1519.5	1517.8
35°	1477.1	1474.6	1472.1	1469.6	1467.1	1463.4	1458.4	1453.5	1448.5	1443.5	1441.0
37.5°	1396.9	1394.6	1392.4	1390.1	1387.8	1384.0	1378.7	1373.4	1368.0	1362.7	1360.0
40°	1344.5	1341.7	1338.8	1336.0	1333.2	1329.1	1323.8	1318.4	1313.1	1307.8	1304.2
42.5°	1288.3	1286.6	1284.9	1283.2	1281.5	1277.7	1271.8	1265.9	1260.0	1254.1	1250.0
45°	1205.6	1203.1	1200.6	1198.1	1195.7	1191.6	1185.9	1180.2	1174.5	1168.9	1165.0
47.5°	1119.0	1117.3	1115.6	1113.9	1112.2	1108.8	1103.5	1098.3	1093.0	1087.8	1083.4
50°	1060.3	1058.9	1057.4	1056.0	1054.6	1051.4	1046.4	1041.5	1036.5	1031.5	1026.6
52.5°	1002.8	1001.1	999.4	997.7	996.0	992.5	987.3	982.0	976.8	971.5	967.1
55°	911.8	910.7	909.7	908.6	907.5	904.5	899.5	894.6	889.6	884.6	880.4
57.5°	824.9	823.7	822.5	821.3	820.1	817.0	812.1	807.2	802.3	797.4	793.4
60°	764.9	763.1	761.3	759.6	757.8	754.6	750.0	745.4	740.7	736.1	732.9
62.5°	706.1	704.6	703.1	701.6	700.2	697.0	692.1	687.2	682.3	677.4	674.5
65°	618.0	616.2	614.4	612.6	610.9	608.2	604.7	601.1	597.6	594.0	590.5
67.5°	529.2	527.6	525.9	524.3	522.7	520.1	516.7	513.3	509.9	506.5	503.1
70°	474.3	471.8	469.3	466.8	464.3	461.7	458.8	456.0	453.1	450.3	447.5
72.5°	415.5	413.0	410.5	408.0	405.6	403.2	400.9	398.6	396.4	394.1	391.8
75°	328.9	327.2	325.4	323.6	321.8	320.1	318.3	316.5	314.8	313.0	311.6
77.5°	246.2	245.4	244.7	243.9	243.1	241.9	240.4	238.8	237.3	235.7	235.3
80°	196.4	195.3	194.3	193.2	192.2	191.3	190.6	189.8	189.1	188.4	187.7
82.5°	147.9	147.4	146.9	146.4	145.9	145.6	145.4	145.3	145.1	145.0	144.6
85°	86.2	86.2	86.2	86.2	86.2	85.9	85.2	84.5	83.7	83.0	83.0
87.5°	33.5	33.4	33.4	33.3	33.2	33.1	33.0	32.9	32.8	32.7	32.8
90°	1.4	2.5	3.6	4.7	5.8	6.7	7.6	8.4	9.2	10.0	10.6
92.5°	9.7	11.0	12.2	13.5	14.8	15.7	16.3	16.8	17.4	17.9	18.3
95°	27.2	28.1	29.0	29.9	30.8	31.6	32.3	33.0	33.7	34.4	34.7
97.5°	47.5	48.2	48.9	49.7	50.4	51.2	52.0	52.8	53.6	54.5	54.8
100°	63.4	63.8	64.2	64.6	65.1	65.7	66.6	67.5	68.4	69.3	69.5
102.5°	80.1	80.3	80.4	80.6	80.8	81.3	82.1	82.9	83.7	84.6	84.8
105°	105.6	105.7	105.8	105.9	106.0	106.2	106.6	107.0	107.4	107.8	108.1
107.5°	132.3	132.4	132.6	132.7	132.8	132.9	133.0	133.0	133.1	133.1	133.4
110°	150.4	150.6	150.8	151.0	151.2	151.3	151.2	151.1	151.0	150.9	150.7



TEST NUMBER: P332840

CATALOG NUMBER: S124DIW-S1195D470U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	169.3	169.3	169.4	169.4	169.5	169.4	169.2	169.0	168.8	168.7	168.6
115°	197.6	197.6	197.6	197.6	197.6	197.5	197.3	197.1	196.9	196.7	196.6
117.5°	224.2	224.3	224.4	224.5	224.5	224.5	224.4	224.2	224.1	223.9	223.6
120°	242.0	242.4	242.8	243.2	243.6	243.6	243.3	243.0	242.7	242.4	241.9
122.5°	260.5	260.6	260.8	260.9	261.1	261.1	261.0	260.8	260.7	260.6	260.2
125°	287.7	287.7	287.7	287.7	287.7	287.7	287.6	287.5	287.4	287.3	287.1
127.5°	312.5	312.8	313.1	313.4	313.7	313.8	313.6	313.4	313.3	313.1	312.9
130°	329.9	330.2	330.5	330.8	331.1	331.2	331.2	331.2	331.2	331.2	331.0
132.5°	347.6	347.9	348.1	348.3	348.5	348.6	348.5	348.4	348.4	348.3	348.1
135°	371.1	371.7	372.3	372.9	373.5	373.8	373.8	373.8	373.8	373.8	373.6
137.5°	396.7	397.0	397.2	397.5	397.8	398.0	398.2	398.4	398.5	398.7	398.4
140°	413.7	413.9	414.1	414.3	414.5	414.6	414.6	414.6	414.6	414.6	414.5
142.5°	429.3	429.5	429.7	429.9	430.1	430.2	430.1	430.0	429.9	429.8	429.8
145°	450.9	451.3	451.7	452.1	452.5	452.7	452.8	452.9	453.0	453.1	453.0
147.5°	472.3	472.7	473.2	473.7	474.2	474.4	474.3	474.2	474.2	474.1	474.0
150°	485.3	485.7	486.1	486.5	486.9	487.1	487.1	487.1	487.1	487.1	487.1
152.5°	497.6	497.9	498.1	498.4	498.6	498.8	498.8	498.9	499.0	499.1	499.3
155°	516.6	516.6	516.6	516.6	516.6	516.5	516.4	516.3	516.2	516.1	516.5
157.5°	532.5	532.3	532.2	532.0	531.8	531.7	531.7	531.7	531.6	531.6	531.9
160°	542.0	541.9	541.8	541.7	541.6	541.5	541.4	541.3	541.2	541.1	541.4
162.5°	550.7	550.4	550.1	549.9	549.6	549.4	549.3	549.2	549.1	549.0	549.6
165°	562.3	562.0	561.7	561.4	561.1	560.9	560.7	560.5	560.3	560.1	560.7
167.5°	571.3	570.9	570.5	570.1	569.6	569.4	569.4	569.5	569.5	569.5	570.1
170°	576.4	575.9	575.4	574.9	574.4	574.2	574.3	574.4	574.5	574.6	575.2
172.5°	580.0	579.6	579.2	578.8	578.3	578.1	578.1	578.2	578.2	578.2	578.9
175°	585.0	584.5	584.0	583.5	583.0	582.7	582.6	582.5	582.4	582.3	583.0
177.5°	586.6	586.2	585.8	585.4	585.0	584.8	584.8	584.8	584.8	584.8	585.4
180°	585.9	585.9	585.9	585.9	585.9	585.9	585.9	585.9	585.9	585.9	585.9



TEST NUMBER: P332840

CATALOG NUMBER: S124DIW-S1195D470U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8
2.5°	1985.7	1988.6	1991.4	1992.7	1992.4	1992.1	1991.8	1991.5
5°	1975.1	1979.0	1982.9	1984.5	1983.8	1983.1	1982.4	1981.6
7.5°	1953.1	1956.2	1959.3	1960.7	1960.3	1959.8	1959.4	1959.0
10°	1934.6	1937.5	1940.3	1941.4	1940.7	1940.0	1939.2	1938.5
12.5°	1912.2	1915.3	1918.5	1919.5	1918.5	1917.5	1916.5	1915.5
15°	1869.3	1871.5	1873.6	1874.1	1873.1	1872.0	1870.9	1869.9
17.5°	1820.5	1821.9	1823.2	1823.5	1822.8	1822.1	1821.4	1820.7
20°	1784.2	1785.2	1786.3	1786.5	1785.8	1785.1	1784.4	1783.6
22.5°	1746.3	1748.2	1750.1	1750.4	1749.2	1747.9	1746.6	1745.3
25°	1683.8	1684.1	1684.5	1683.9	1682.5	1681.1	1679.7	1678.3
27.5°	1613.6	1612.8	1611.9	1610.6	1608.8	1607.1	1605.3	1603.5
30°	1565.2	1563.8	1562.4	1560.8	1559.0	1557.3	1555.5	1553.7
32.5°	1516.1	1514.4	1512.7	1511.0	1509.2	1507.4	1505.7	1503.9
35°	1438.6	1436.1	1433.6	1431.5	1429.7	1427.9	1426.1	1424.4
37.5°	1357.3	1354.6	1351.9	1349.4	1347.1	1344.7	1342.4	1340.0
40°	1300.7	1297.1	1293.6	1290.9	1289.2	1287.4	1285.6	1283.8
42.5°	1245.9	1241.8	1237.7	1235.0	1233.8	1232.6	1231.4	1230.2
45°	1161.1	1157.2	1153.3	1150.8	1149.7	1148.6	1147.6	1146.5
47.5°	1079.0	1074.6	1070.2	1066.6	1063.9	1061.2	1058.5	1055.8
50°	1021.6	1016.6	1011.7	1008.1	1006.0	1003.9	1001.7	999.6
52.5°	962.7	958.3	953.9	950.4	947.7	945.0	942.3	939.6
55°	876.1	871.9	867.6	864.4	862.3	860.2	858.0	855.9
57.5°	789.4	785.3	781.3	778.2	776.2	774.1	772.0	770.0
60°	729.7	726.6	723.4	720.9	719.1	717.3	715.6	713.8
62.5°	671.5	668.6	665.7	663.4	661.6	659.8	658.1	656.3
65°	586.9	583.4	579.8	577.2	575.4	573.6	571.8	570.1
67.5°	499.7	496.3	492.9	490.9	490.4	489.9	489.4	488.9
70°	444.6	441.8	438.9	437.0	435.9	434.9	433.8	432.7
72.5°	389.6	387.3	385.0	383.3	382.3	381.2	380.1	379.1
75°	310.1	308.7	307.3	306.4	306.1	305.7	305.3	305.0
77.5°	234.8	234.4	234.0	233.3	232.4	231.5	230.5	229.6
80°	187.0	186.3	185.6	185.1	184.7	184.3	184.0	183.6
82.5°	144.1	143.7	143.3	142.9	142.5	142.2	141.8	141.5
85°	83.0	83.0	83.0	82.9	82.5	82.1	81.8	81.4
87.5°	32.9	33.0	33.1	33.2	33.3	33.3	33.3	33.4
90°	11.2	11.8	12.4	12.8	13.0	13.2	13.4	13.6
92.5°	18.7	19.0	19.4	19.6	19.8	19.9	20.0	20.1
95°	35.0	35.3	35.6	35.8	35.8	35.8	35.8	35.8
97.5°	55.2	55.6	55.9	56.1	56.1	56.1	56.1	56.1
100°	69.7	69.9	70.1	70.2	70.2	70.2	70.2	70.2
102.5°	85.1	85.4	85.7	85.9	85.9	86.0	86.1	86.2
105°	108.5	108.8	109.1	109.4	109.7	110.0	110.3	110.6
107.5°	133.7	134.0	134.3	134.4	134.4	134.4	134.3	134.3
110°	150.5	150.3	150.1	150.1	150.4	150.7	151.0	151.3



TEST NUMBER: P332840

CATALOG NUMBER: S124DIW-S1195D470U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	168.6	168.5	168.5	168.5	168.6	168.6	168.7	168.7
115°	196.5	196.4	196.3	196.2	196.1	196.0	195.9	195.8
117.5°	223.3	222.9	222.6	222.3	222.1	221.9	221.7	221.5
120°	241.4	240.9	240.4	240.3	240.5	240.7	240.9	241.1
122.5°	259.9	259.5	259.2	258.8	258.5	258.1	257.7	257.4
125°	286.9	286.7	286.5	286.3	286.1	285.9	285.7	285.5
127.5°	312.7	312.5	312.3	312.1	312.0	311.8	311.7	311.5
130°	330.8	330.6	330.4	330.1	329.7	329.3	328.9	328.5
132.5°	347.9	347.7	347.5	347.3	347.1	347.0	346.8	346.7
135°	373.4	373.2	373.0	372.8	372.5	372.2	371.9	371.6
137.5°	398.1	397.9	397.6	397.5	397.6	397.6	397.7	397.8
140°	414.4	414.3	414.2	414.1	414.0	413.9	413.8	413.7
142.5°	429.8	429.8	429.8	429.7	429.7	429.7	429.7	429.7
145°	452.9	452.8	452.7	452.5	452.2	451.9	451.6	451.3
147.5°	473.9	473.8	473.8	473.7	473.6	473.5	473.4	473.3
150°	487.1	487.1	487.1	487.1	487.0	486.9	486.8	486.7
152.5°	499.6	499.8	500.1	500.0	499.8	499.5	499.3	499.0
155°	516.9	517.3	517.7	517.7	517.3	516.9	516.5	516.1
157.5°	532.2	532.5	532.8	532.8	532.5	532.1	531.8	531.4
160°	541.7	542.0	542.3	542.2	541.7	541.2	540.6	540.1
162.5°	550.1	550.7	551.2	551.2	550.7	550.2	549.7	549.2
165°	561.3	561.9	562.5	562.6	562.2	561.8	561.4	561.0
167.5°	570.7	571.3	571.9	571.9	571.3	570.7	570.0	569.4
170°	575.8	576.4	577.0	576.9	576.2	575.5	574.8	574.1
172.5°	579.6	580.3	580.9	580.9	580.2	579.5	578.8	578.1
175°	583.7	584.4	585.1	585.1	584.4	583.7	583.0	582.3
177.5°	586.0	586.5	587.1	587.0	586.4	585.8	585.1	584.5
180°	585.9	585.9	585.9	585.9	585.9	585.9	585.9	585.9

(END OF REPORT)