

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332731-927

Luminaire Tested: **S124DIW-S350D1050U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332731-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S350D1050U927-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1050 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4523.4 lumens
Efficiency: N/A
Efficacy: 119.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 38
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332731-927

CATALOG NUMBER: S124DIW-S350D1050U927-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332731-927

CATALOG NUMBER: S124DIW-S350D1050U927-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	70	70	70	52	52	52	35	35	35	27
1	93	88	85	81	82	79	76	73	61	59	57	45	44	43	31	30	29	22
2	84	77	71	66	75	69	64	60	54	50	47	40	38	36	27	26	24	19
3	77	68	61	55	68	61	55	50	47	43	40	35	32	30	24	22	21	16
4	70	60	52	46	62	54	47	42	42	37	34	31	28	26	21	19	18	14
5	64	53	45	40	57	48	41	36	37	33	29	28	25	22	19	17	16	12
6	59	47	40	34	52	43	36	31	34	29	25	25	22	19	17	15	14	10
7	54	43	35	30	48	38	32	27	30	26	22	23	20	17	16	14	12	9
8	50	39	31	26	45	35	28	24	28	23	19	21	18	15	14	12	11	8
9	47	35	28	23	42	32	25	21	25	21	17	19	16	13	13	11	10	7
10	44	32	25	20	39	29	23	19	23	19	15	18	14	12	12	10	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3777	3777	3777
5°	3789	3743	3771
10°	3765	3713	3731
15°	3719	3661	3670
20°	3660	3594	3598
25°	3591	3520	3510
30°	3506	3432	3402
35°	3418	3341	3297
40°	3327	3236	3177
45°	3232	3134	3075
50°	3127	3042	2948
55°	3013	2923	2829
60°	2900	2792	2706
65°	2772	2665	2558
70°	2629	2497	2398
75°	2408	2293	2233
80°	2143	2060	2004
85°	1880	1806	1769



TEST NUMBER: P332731-927

CATALOG NUMBER: S124DIW-S350D1050U927-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.1	1.0
10°-20°	124.2	2.7
20°-30°	182.8	4.0
30°-40°	212.5	4.7
40°-50°	212.5	4.7
50°-60°	185.9	4.1
60°-70°	138.0	3.1
70°-80°	78.4	1.7
80°-90°	25.7	0.6
90°-100°	36.7	0.8
100°-110°	234.0	5.2
110°-120°	447.7	9.9
120°-130°	568.3	12.6
130°-140°	608.0	13.4
140°-150°	568.6	12.6
150°-160°	458.5	10.1
160°-170°	295.7	6.5
170°-180°	101.9	2.3
0°-30°	351.0	7.8
0°-40°	563.5	12.5
0°-60°	961.8	21.3
0°-90°	1204.0	26.6
90°-120°	718.4	15.9
90°-150°	2463.3	54.5
90°-180°	3319.0	73.4
0°-180°	4523.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	468	468	468	468	468	
5°	468	466	462	466	465	44
15°	445	443	438	440	439	125
25°	403	400	395	396	394	185
35°	347	344	339	336	334	217
45°	283	280	274	270	269	218
55°	214	213	208	203	201	192
65°	145	143	140	136	134	144
75°	77	75	74	72	72	82
85°	20	20	20	20	19	22
90°	2	11	18	22	24	3
95°	44	18	18	22	23	57
105°	242	246	250	256	229	253
115°	451	453	453	454	454	444
125°	634	637	636	638	639	566
135°	787	786	789	791	792	606
145°	907	909	909	910	912	567
155°	994	995	993	996	994	458
165°	1049	1045	1045	1051	1044	296
175°	1073	1069	1069	1075	1067	102
180°	1073	1073	1073	1073	1073	



TEST NUMBER: P332731-927

CATALOG NUMBER: S124DIW-S350D1050U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	467.9	467.9	467.9	467.9	467.9	467.9	467.9	467.9	467.9	467.9	467.9
2.5°	469.1	469.0	468.7	468.6	468.3	467.9	467.1	466.4	465.7	464.9	465.6
5°	467.5	467.2	466.9	466.6	466.3	465.6	464.7	463.8	462.9	461.9	462.9
7.5°	463.3	462.9	462.6	462.2	461.9	461.2	460.2	459.2	458.2	457.2	457.9
10°	459.3	459.0	458.7	458.4	458.0	457.3	456.2	455.1	454.1	453.0	453.6
12.5°	454.2	453.9	453.6	453.2	452.9	452.2	451.0	449.9	448.7	447.6	448.3
15°	445.0	444.7	444.4	444.1	443.8	443.0	441.7	440.5	439.2	438.0	438.5
17.5°	434.0	433.6	433.2	432.8	432.4	431.6	430.4	429.2	428.0	426.8	427.1
20°	426.0	425.6	425.2	424.7	424.3	423.5	422.2	421.0	419.7	418.4	418.7
22.5°	417.2	416.7	416.1	415.6	415.0	414.2	412.9	411.7	410.4	409.2	409.6
25°	403.1	402.5	402.0	401.3	400.8	399.9	398.7	397.5	396.4	395.2	395.3
27.5°	386.9	386.3	385.7	385.1	384.5	383.7	382.5	381.5	380.4	379.3	379.1
30°	376.1	375.4	374.8	374.1	373.4	372.6	371.5	370.3	369.3	368.2	367.9
32.5°	364.7	364.1	363.5	362.9	362.3	361.4	360.3	359.1	358.0	356.8	356.4
35°	346.8	346.3	345.7	345.1	344.5	343.6	342.5	341.3	340.2	339.0	338.4
37.5°	328.0	327.5	326.9	326.5	325.9	325.0	323.8	322.5	321.2	320.0	319.3
40°	315.7	315.1	314.4	313.7	313.1	312.1	310.9	309.6	308.3	307.1	306.3
42.5°	302.5	302.1	301.7	301.3	301.0	300.0	298.7	297.2	295.9	294.5	293.5
45°	283.1	282.5	281.9	281.4	280.7	279.8	278.5	277.1	275.8	274.5	273.5
47.5°	262.8	262.4	262.0	261.6	261.2	260.4	259.1	257.9	256.7	255.4	254.4
50°	249.0	248.7	248.3	248.0	247.6	246.9	245.7	244.5	243.4	242.2	241.1
52.5°	235.5	235.0	234.6	234.2	233.9	233.1	231.8	230.6	229.3	228.1	227.1
55°	214.1	213.9	213.6	213.3	213.1	212.4	211.2	210.1	208.9	207.7	206.8
57.5°	193.7	193.5	193.1	192.9	192.6	191.9	190.7	189.6	188.4	187.3	186.3
60°	179.6	179.2	178.8	178.3	177.9	177.2	176.1	175.0	174.0	172.9	172.1
62.5°	165.8	165.5	165.1	164.8	164.4	163.7	162.5	161.4	160.2	159.1	158.4
65°	145.1	144.7	144.3	143.9	143.5	142.8	142.0	141.2	140.3	139.5	138.6
67.5°	124.3	123.9	123.5	123.1	122.7	122.2	121.4	120.6	119.8	118.9	118.1
70°	111.4	110.7	110.2	109.6	109.0	108.4	107.7	107.1	106.4	105.8	105.0
72.5°	97.6	97.0	96.4	95.9	95.2	94.7	94.1	93.6	93.1	92.5	92.0
75°	77.2	76.8	76.4	76.0	75.6	75.2	74.8	74.3	73.9	73.5	73.2
77.5°	57.8	57.7	57.4	57.3	57.1	56.8	56.5	56.1	55.7	55.4	55.2
80°	46.1	45.9	45.6	45.4	45.2	44.9	44.8	44.6	44.4	44.3	44.0
82.5°	34.7	34.6	34.5	34.4	34.2	34.1	34.1	34.1	34.1	34.1	34.0
85°	20.3	20.3	20.3	20.3	20.3	20.2	20.0	19.8	19.6	19.5	19.5
87.5°	8.3	8.6	9.0	9.3	9.6	9.8	10.1	10.3	10.5	10.7	10.9
90°	2.4	4.4	6.3	8.3	10.2	12.0	13.4	14.8	16.2	17.7	18.7
92.5°	10.1	10.2	10.3	10.5	10.5	11.3	12.8	14.2	15.6	17.0	18.1
95°	44.1	38.1	32.0	26.0	19.9	17.0	17.1	17.3	17.5	17.7	18.7
97.5°	93.7	97.5	101.3	105.1	108.8	100.8	80.9	61.0	41.1	21.2	21.3
100°	131.7	134.8	138.1	141.2	144.5	133.8	109.2	84.5	60.0	35.3	32.3
102.5°	174.0	176.3	178.7	181.1	183.4	183.0	179.8	176.6	173.3	170.2	137.4
105°	241.6	242.6	243.8	244.8	245.9	246.8	247.7	248.7	249.5	250.4	252.0
107.5°	304.4	304.9	305.4	305.9	306.5	307.4	308.6	309.8	311.0	312.2	313.0
110°	346.7	347.3	347.8	348.3	348.9	349.7	350.8	351.8	352.9	353.9	354.3



TEST NUMBER: P332731-927

CATALOG NUMBER: S124DIW-S350D1050U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	387.9	388.8	389.8	390.7	391.7	392.4	392.9	393.4	393.9	394.4	394.3
115°	451.1	451.6	452.2	452.7	453.2	453.4	453.2	453.0	452.9	452.7	453.0
117.5°	508.0	508.7	509.5	510.2	510.9	511.4	511.8	512.2	512.6	513.0	512.9
120°	546.6	547.3	548.0	548.7	549.5	549.7	549.5	549.4	549.1	549.0	549.4
122.5°	582.6	583.0	583.4	583.8	584.2	584.6	584.9	585.1	585.3	585.6	585.8
125°	634.1	634.8	635.5	636.2	636.9	637.1	636.8	636.4	636.0	635.6	636.2
127.5°	682.9	683.0	683.3	683.4	683.6	684.0	684.9	685.7	686.5	687.4	687.3
130°	714.3	714.5	714.7	714.9	715.0	715.4	716.0	716.4	717.0	717.6	717.7
132.5°	743.2	743.5	743.9	744.2	744.5	745.0	745.7	746.4	747.0	747.7	747.9
135°	786.6	786.4	786.2	786.0	785.8	786.2	786.9	787.6	788.3	789.0	789.3
137.5°	824.9	825.0	825.1	825.1	825.2	825.6	826.4	827.2	828.0	828.8	829.2
140°	850.0	850.3	850.7	851.0	851.4	851.8	852.2	852.5	852.9	853.2	853.7
142.5°	872.4	873.1	873.7	874.4	875.0	875.4	875.7	875.8	876.1	876.3	876.7
145°	907.0	907.5	908.0	908.6	909.1	909.3	909.3	909.3	909.3	909.3	909.6
147.5°	934.4	935.4	936.4	937.4	938.4	938.8	938.7	938.5	938.3	938.1	938.3
150°	954.3	955.1	955.8	956.5	957.2	957.4	957.3	957.1	956.9	956.7	956.7
152.5°	971.0	971.6	972.2	972.7	973.3	973.4	973.1	972.8	972.5	972.2	972.4
155°	994.4	994.7	994.8	995.0	995.1	995.0	994.4	994.0	993.4	992.8	993.6
157.5°	1014.2	1014.1	1014.0	1013.8	1013.8	1013.4	1012.8	1012.2	1011.6	1011.0	1011.9
160°	1025.7	1025.2	1024.7	1024.1	1023.6	1023.3	1023.1	1022.9	1022.7	1022.5	1023.6
162.5°	1036.0	1035.4	1034.7	1034.0	1033.3	1032.8	1032.7	1032.5	1032.4	1032.1	1033.2
165°	1049.0	1048.1	1047.3	1046.3	1045.4	1045.0	1045.0	1045.0	1045.0	1045.0	1046.5
167.5°	1059.3	1058.4	1057.5	1056.5	1055.6	1055.1	1054.9	1054.9	1054.8	1054.6	1056.2
170°	1065.1	1064.0	1063.0	1061.8	1060.8	1060.3	1060.5	1060.7	1060.9	1061.0	1062.5
172.5°	1068.9	1067.9	1066.8	1065.7	1064.6	1064.2	1064.4	1064.5	1064.8	1064.9	1066.4
175°	1073.1	1072.1	1071.0	1069.9	1068.8	1068.4	1068.6	1068.7	1068.9	1069.1	1070.7
177.5°	1075.0	1074.0	1073.0	1072.1	1071.0	1070.7	1071.0	1071.3	1071.5	1071.8	1072.9
180°	1073.1	1073.1	1073.1	1073.1	1073.1	1073.1	1073.1	1073.1	1073.1	1073.1	1073.1



TEST NUMBER: P332731-927

CATALOG NUMBER: S124DIW-S350D1050U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	467.9	467.9	467.9	467.9	467.9	467.9	467.9	467.9
2.5°	466.3	467.0	467.6	467.9	467.9	467.8	467.7	467.6
5°	463.8	464.7	465.6	466.0	465.8	465.6	465.5	465.3
7.5°	458.6	459.4	460.1	460.4	460.3	460.2	460.1	460.0
10°	454.3	455.0	455.7	455.9	455.7	455.5	455.3	455.2
12.5°	449.0	449.7	450.5	450.8	450.5	450.3	450.0	449.8
15°	438.9	439.4	440.0	440.1	439.8	439.6	439.3	439.1
17.5°	427.5	427.8	428.1	428.2	428.0	427.9	427.7	427.5
20°	419.0	419.2	419.5	419.5	419.3	419.1	419.0	418.8
22.5°	410.0	410.5	411.0	411.1	410.7	410.4	410.1	409.9
25°	395.4	395.5	395.5	395.5	395.1	394.7	394.4	394.1
27.5°	378.9	378.7	378.5	378.2	377.8	377.4	376.9	376.5
30°	367.6	367.3	366.9	366.5	366.1	365.7	365.3	364.9
32.5°	356.0	355.6	355.2	354.8	354.4	353.9	353.6	353.2
35°	337.8	337.2	336.6	336.1	335.7	335.3	334.9	334.5
37.5°	318.7	318.1	317.4	316.9	316.3	315.8	315.2	314.7
40°	305.5	304.6	303.8	303.2	302.7	302.3	301.9	301.5
42.5°	292.6	291.6	290.7	290.0	289.7	289.5	289.1	288.9
45°	272.7	271.7	270.8	270.2	270.0	269.7	269.5	269.3
47.5°	253.3	252.3	251.3	250.5	249.9	249.2	248.6	248.0
50°	239.9	238.8	237.6	236.7	236.2	235.8	235.2	234.7
52.5°	226.1	225.1	224.0	223.2	222.5	221.9	221.3	220.6
55°	205.7	204.7	203.7	203.0	202.5	202.0	201.5	201.0
57.5°	185.4	184.4	183.5	182.8	182.3	181.8	181.3	180.8
60°	171.3	170.6	169.8	169.3	168.9	168.4	168.0	167.6
62.5°	157.7	157.0	156.3	155.7	155.3	155.0	154.6	154.1
65°	137.8	137.0	136.2	135.5	135.1	134.7	134.3	133.9
67.5°	117.3	116.5	115.7	115.3	115.2	115.0	114.9	114.8
70°	104.4	103.8	103.1	102.6	102.3	102.1	101.9	101.6
72.5°	91.5	90.9	90.4	90.0	89.8	89.5	89.3	89.0
75°	72.8	72.5	72.2	71.9	71.9	71.8	71.7	71.6
77.5°	55.1	55.1	55.0	54.8	54.6	54.3	54.1	53.9
80°	43.9	43.7	43.6	43.5	43.3	43.3	43.2	43.1
82.5°	33.8	33.7	33.7	33.6	33.5	33.4	33.3	33.2
85°	19.5	19.5	19.5	19.5	19.4	19.3	19.2	19.1
87.5°	11.2	11.4	11.6	11.7	11.8	11.9	12.0	12.0
90°	19.8	20.8	21.9	22.7	23.0	23.4	23.7	24.1
92.5°	19.2	20.2	21.3	21.9	21.9	22.0	22.1	22.2
95°	19.8	20.8	21.9	22.6	22.7	22.9	23.1	23.3
97.5°	21.4	21.5	21.6	21.8	21.9	22.1	22.3	22.5
100°	29.2	26.2	23.2	21.8	21.9	22.1	22.3	22.5
102.5°	104.7	72.0	39.3	23.0	23.0	23.1	23.1	23.1
105°	253.7	255.2	256.8	254.4	248.0	241.6	235.2	228.8
107.5°	313.8	314.6	315.4	316.1	316.8	317.4	318.1	318.8
110°	354.7	355.1	355.4	355.8	356.4	356.9	357.4	358.0



TEST NUMBER: P332731-927

CATALOG NUMBER: S124DIW-S350D1050U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	394.3	394.2	394.1	394.4	395.1	395.8	396.5	397.1
115°	453.4	453.8	454.1	454.3	454.3	454.3	454.3	454.3
117.5°	512.9	512.9	512.8	512.7	512.6	512.5	512.5	512.4
120°	549.7	550.1	550.4	550.4	550.1	549.7	549.4	549.0
122.5°	586.1	586.2	586.5	586.4	586.1	585.7	585.3	584.9
125°	636.8	637.3	637.8	638.2	638.3	638.5	638.7	638.9
127.5°	687.1	687.1	686.9	686.8	686.7	686.5	686.3	686.3
130°	717.9	718.1	718.3	718.4	718.4	718.4	718.4	718.4
132.5°	748.1	748.3	748.5	748.5	748.3	748.1	748.1	747.9
135°	789.7	790.0	790.4	790.8	791.2	791.5	791.9	792.2
137.5°	829.6	830.0	830.4	830.5	830.4	830.3	830.2	830.0
140°	854.3	854.8	855.3	855.7	855.9	856.0	856.2	856.4
142.5°	877.1	877.5	877.9	878.1	878.1	878.1	878.2	878.2
145°	909.7	909.9	910.1	910.4	910.7	911.1	911.4	911.8
147.5°	938.4	938.5	938.7	938.8	939.1	939.2	939.4	939.5
150°	956.7	956.7	956.7	956.8	957.0	957.2	957.4	957.5
152.5°	972.7	973.0	973.3	973.4	973.3	973.1	973.0	973.0
155°	994.3	995.0	995.7	995.8	995.2	994.7	994.2	993.6
157.5°	1012.8	1013.8	1014.7	1014.7	1013.8	1012.8	1011.9	1011.0
160°	1024.7	1025.7	1026.8	1026.8	1025.7	1024.7	1023.6	1022.5
162.5°	1034.3	1035.4	1036.4	1036.4	1035.1	1034.0	1032.8	1031.5
165°	1047.9	1049.3	1050.8	1050.6	1049.0	1047.4	1045.8	1044.2
167.5°	1057.8	1059.4	1060.9	1060.8	1059.1	1057.2	1055.5	1053.7
170°	1063.9	1065.3	1066.8	1066.6	1064.8	1063.0	1061.2	1059.5
172.5°	1067.8	1069.2	1070.6	1070.4	1068.4	1066.5	1064.6	1062.6
175°	1072.3	1073.9	1075.5	1075.2	1073.1	1071.0	1068.8	1066.7
177.5°	1074.1	1075.2	1076.4	1076.1	1074.4	1072.7	1071.0	1069.3
180°	1073.1	1073.1	1073.1	1073.1	1073.1	1073.1	1073.1	1073.1

(END OF REPORT)