

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332845

Luminaire Tested: **S124DIW-S1195D770U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332845  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIW-S1195D770U835-4F0-1E-UDD-F  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 770 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8186.7 lumens  
Efficiency: N/A  
Efficacy: 136.9 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 59.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332845

CATALOG NUMBER: S124DIW-S1195D770U835-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332845

CATALOG NUMBER: S124DIW-S1195D770U835-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	68	68	68	63
1	101	96	92	89	94	90	87	84	79	77	74	69	67	65	60	58	57	53
2	92	84	78	72	86	79	73	69	69	65	61	61	57	55	53	50	48	44
3	84	74	66	60	78	69	63	57	61	56	52	54	50	46	47	43	41	37
4	76	65	57	51	71	62	54	49	54	49	44	48	43	40	42	38	35	32
5	70	58	50	44	66	55	48	42	49	43	38	43	38	34	38	34	31	28
6	65	52	44	38	61	50	42	37	44	38	33	39	34	30	34	30	27	24
7	60	47	39	34	56	45	37	32	40	34	29	35	30	27	31	27	24	22
8	56	43	35	30	52	41	34	29	36	30	26	32	27	24	29	25	22	19
9	52	39	32	27	49	37	30	26	34	28	24	30	25	22	26	22	20	17
10	49	36	29	24	46	34	28	23	31	25	21	28	23	20	25	21	18	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	16088	16088	16088
5°	16136	15943	16058
10°	16035	15813	15891
15°	15841	15588	15628
20°	15584	15309	15323
25°	15291	14991	14949
30°	14930	14618	14483
35°	14557	14226	14038
40°	14169	13782	13529
45°	13764	13345	13089
50°	13317	12955	12554
55°	12833	12451	12047
60°	12350	11885	11525
65°	11805	11347	10890
70°	11195	10629	10213
75°	10259	9763	9513
80°	9131	8759	8536
85°	7984	7688	7540



TEST NUMBER: P332845

CATALOG NUMBER: S124DIW-S1195D770U835-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	187.7	2.3
10°-20°	528.8	6.5
20°-30°	778.3	9.5
30°-40°	904.8	11.1
40°-50°	904.8	11.1
50°-60°	791.5	9.7
60°-70°	587.8	7.2
70°-80°	333.9	4.1
80°-90°	99.2	1.2
90°-100°	33.9	0.4
100°-110°	216.4	2.6
110°-120°	414.0	5.1
120°-130°	525.6	6.4
130°-140°	562.3	6.9
140°-150°	525.8	6.4
150°-160°	424.0	5.2
160°-170°	273.5	3.3
170°-180°	94.3	1.2
0°-30°	1494.7	18.3
0°-40°	2399.5	29.3
0°-60°	4095.8	50.0
0°-90°	5116.7	62.5
90°-120°	664.4	8.1
90°-150°	2278.1	27.8
90°-180°	3070.0	37.5
0°-180°	8186.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1993	1993	1993	1993	1993	
5°	1991	1984	1967	1984	1982	189
15°	1895	1888	1865	1874	1870	534
25°	1717	1705	1683	1684	1678	789
35°	1477	1465	1444	1433	1424	923
45°	1206	1194	1169	1152	1146	929
55°	912	906	885	866	856	816
65°	618	610	594	578	570	612
75°	329	321	313	307	305	350
85°	86	86	83	83	81	95
90°	2	10	16	21	22	7
95°	41	17	16	21	22	52
105°	223	228	232	236	212	234
115°	417	419	419	420	420	410
125°	586	589	588	590	591	523
135°	727	727	730	731	733	560
145°	839	841	841	842	843	524
155°	920	920	918	921	919	424
165°	970	967	966	972	966	274
175°	992	988	989	995	986	94
180°	992	992	992	992	992	



TEST NUMBER: P332845

CATALOG NUMBER: S124DIW-S1195D770U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8
2.5°	1997.9	1997.1	1996.2	1995.4	1994.5	1992.5	1989.4	1986.3	1983.2	1980.1	1982.9
5°	1991.2	1989.8	1988.4	1987.0	1985.6	1982.9	1979.0	1975.1	1971.2	1967.3	1971.2
7.5°	1972.7	1971.3	1969.9	1968.4	1967.0	1964.2	1959.8	1955.5	1951.2	1946.8	1950.0
10°	1956.1	1954.7	1953.3	1951.8	1950.4	1947.4	1942.8	1938.2	1933.6	1929.0	1931.8
12.5°	1934.4	1933.0	1931.5	1930.1	1928.7	1925.5	1920.7	1915.8	1910.9	1906.0	1909.1
15°	1895.4	1894.0	1892.6	1891.2	1889.7	1886.4	1881.0	1875.7	1870.4	1865.1	1867.2
17.5°	1848.5	1846.7	1844.9	1843.2	1841.4	1838.0	1832.9	1827.9	1822.9	1817.8	1819.2
20°	1814.0	1812.2	1810.4	1808.7	1806.9	1803.3	1798.0	1792.7	1787.4	1782.0	1783.1
22.5°	1776.9	1774.6	1772.3	1769.9	1767.6	1763.7	1758.4	1753.1	1747.8	1742.4	1744.4
25°	1716.6	1714.1	1711.6	1709.1	1706.6	1702.9	1697.9	1693.0	1688.0	1683.0	1683.4
27.5°	1647.6	1645.0	1642.5	1639.9	1637.4	1633.8	1629.2	1624.6	1620.0	1615.3	1614.5
30°	1601.6	1598.8	1595.9	1593.1	1590.3	1586.5	1581.9	1577.3	1572.7	1568.1	1566.7
32.5°	1553.1	1550.5	1548.0	1545.4	1542.8	1539.1	1534.2	1529.3	1524.4	1519.5	1517.8
35°	1477.1	1474.6	1472.1	1469.6	1467.1	1463.4	1458.4	1453.5	1448.5	1443.5	1441.0
37.5°	1396.9	1394.6	1392.4	1390.1	1387.8	1384.0	1378.7	1373.4	1368.0	1362.7	1360.0
40°	1344.5	1341.7	1338.8	1336.0	1333.2	1329.1	1323.8	1318.4	1313.1	1307.8	1304.2
42.5°	1288.3	1286.6	1284.9	1283.2	1281.5	1277.7	1271.8	1265.9	1260.0	1254.1	1250.0
45°	1205.6	1203.1	1200.6	1198.1	1195.7	1191.6	1185.9	1180.2	1174.5	1168.9	1165.0
47.5°	1119.0	1117.3	1115.6	1113.9	1112.2	1108.8	1103.5	1098.3	1093.0	1087.8	1083.4
50°	1060.3	1058.9	1057.4	1056.0	1054.6	1051.4	1046.4	1041.5	1036.5	1031.5	1026.6
52.5°	1002.8	1001.1	999.4	997.7	996.0	992.5	987.3	982.0	976.8	971.5	967.1
55°	911.8	910.7	909.7	908.6	907.5	904.5	899.5	894.6	889.6	884.6	880.4
57.5°	824.9	823.7	822.5	821.3	820.1	817.0	812.1	807.2	802.3	797.4	793.4
60°	764.9	763.1	761.3	759.6	757.8	754.6	750.0	745.4	740.7	736.1	732.9
62.5°	706.1	704.6	703.1	701.6	700.2	697.0	692.1	687.2	682.3	677.4	674.5
65°	618.0	616.2	614.4	612.6	610.9	608.2	604.7	601.1	597.6	594.0	590.5
67.5°	529.2	527.6	525.9	524.3	522.7	520.1	516.7	513.3	509.9	506.5	503.1
70°	474.3	471.8	469.3	466.8	464.3	461.7	458.8	456.0	453.1	450.3	447.5
72.5°	415.5	413.0	410.5	408.0	405.6	403.2	400.9	398.6	396.4	394.1	391.8
75°	328.9	327.2	325.4	323.6	321.8	320.1	318.3	316.5	314.8	313.0	311.6
77.5°	246.2	245.4	244.7	243.9	243.1	241.9	240.4	238.8	237.3	235.7	235.3
80°	196.4	195.3	194.3	193.2	192.2	191.3	190.6	189.8	189.1	188.4	187.7
82.5°	147.9	147.4	146.9	146.4	145.9	145.6	145.4	145.3	145.1	145.0	144.6
85°	86.2	86.2	86.2	86.2	86.2	85.9	85.2	84.5	83.7	83.0	83.0
87.5°	33.7	33.7	33.8	33.9	34.0	34.0	34.0	34.0	33.9	33.9	34.1
90°	2.2	4.0	5.9	7.7	9.5	11.1	12.4	13.7	15.0	16.3	17.3
92.5°	9.4	9.5	9.6	9.6	9.7	10.5	11.8	13.1	14.4	15.7	16.7
95°	40.8	35.2	29.6	24.0	18.4	15.7	15.8	16.0	16.2	16.3	17.3
97.5°	86.7	90.2	93.7	97.2	100.7	93.2	74.8	56.4	38.0	19.6	19.7
100°	121.7	124.7	127.7	130.6	133.6	123.7	101.0	78.2	55.4	32.7	29.9
102.5°	160.9	163.1	165.3	167.5	169.6	169.2	166.3	163.3	160.3	157.4	127.1
105°	223.4	224.4	225.4	226.4	227.4	228.3	229.1	229.9	230.8	231.6	233.1
107.5°	281.5	282.0	282.5	283.0	283.5	284.3	285.4	286.5	287.6	288.7	289.5
110°	320.7	321.2	321.7	322.2	322.6	323.4	324.4	325.4	326.4	327.3	327.7



TEST NUMBER: P332845

CATALOG NUMBER: S124DIW-S1195D770U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	358.7	359.6	360.5	361.3	362.2	362.9	363.4	363.8	364.3	364.8	364.7
115°	417.2	417.7	418.2	418.6	419.1	419.3	419.1	419.0	418.8	418.6	419.0
117.5°	469.9	470.5	471.2	471.8	472.5	473.0	473.4	473.7	474.1	474.5	474.4
120°	505.5	506.2	506.8	507.5	508.1	508.4	508.2	508.1	507.9	507.7	508.1
122.5°	538.8	539.1	539.5	539.9	540.3	540.6	540.9	541.1	541.3	541.6	541.8
125°	586.4	587.1	587.7	588.4	589.0	589.2	588.9	588.6	588.2	587.9	588.4
127.5°	631.5	631.7	631.9	632.0	632.2	632.7	633.4	634.2	634.9	635.7	635.6
130°	660.6	660.8	661.0	661.1	661.3	661.6	662.1	662.6	663.1	663.6	663.8
132.5°	687.4	687.7	688.0	688.2	688.5	689.0	689.6	690.3	690.9	691.5	691.7
135°	727.4	727.3	727.1	726.9	726.8	727.0	727.7	728.3	729.0	729.7	730.0
137.5°	762.9	763.0	763.1	763.1	763.2	763.6	764.3	765.0	765.8	766.5	766.8
140°	786.1	786.4	786.7	787.1	787.4	787.7	788.1	788.4	788.7	789.1	789.5
142.5°	806.9	807.5	808.1	808.6	809.2	809.6	809.8	810.0	810.2	810.4	810.8
145°	838.8	839.3	839.8	840.3	840.8	841.0	841.0	841.0	841.0	841.0	841.2
147.5°	864.2	865.1	866.0	866.9	867.9	868.2	868.1	867.9	867.7	867.6	867.7
150°	882.6	883.2	883.9	884.6	885.2	885.5	885.3	885.1	885.0	884.8	884.8
152.5°	898.0	898.5	899.1	899.6	900.1	900.2	899.9	899.7	899.4	899.1	899.3
155°	919.7	919.9	920.0	920.2	920.4	920.2	919.7	919.2	918.7	918.2	918.9
157.5°	938.0	937.9	937.8	937.7	937.6	937.2	936.7	936.1	935.5	935.0	935.8
160°	948.6	948.1	947.7	947.2	946.7	946.3	946.2	946.0	945.8	945.7	946.7
162.5°	958.1	957.5	956.9	956.3	955.6	955.2	955.1	954.9	954.7	954.6	955.6
165°	970.2	969.3	968.5	967.7	966.9	966.5	966.5	966.5	966.5	966.5	967.8
167.5°	979.7	978.8	978.0	977.1	976.2	975.8	975.7	975.6	975.5	975.4	976.8
170°	985.0	984.0	983.0	982.0	981.1	980.6	980.8	981.0	981.1	981.3	982.6
172.5°	988.6	987.6	986.6	985.6	984.6	984.2	984.4	984.5	984.7	984.9	986.2
175°	992.4	991.4	990.5	989.5	988.5	988.1	988.2	988.4	988.6	988.7	990.2
177.5°	994.2	993.3	992.4	991.4	990.5	990.2	990.5	990.7	991.0	991.2	992.3
180°	992.4	992.4	992.4	992.4	992.4	992.4	992.4	992.4	992.4	992.4	992.4



TEST NUMBER: P332845

CATALOG NUMBER: S124DIW-S1195D770U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8
2.5°	1985.7	1988.6	1991.4	1992.7	1992.4	1992.1	1991.8	1991.5
5°	1975.1	1979.0	1982.9	1984.5	1983.8	1983.1	1982.4	1981.6
7.5°	1953.1	1956.2	1959.3	1960.7	1960.3	1959.8	1959.4	1959.0
10°	1934.6	1937.5	1940.3	1941.4	1940.7	1940.0	1939.2	1938.5
12.5°	1912.2	1915.3	1918.5	1919.5	1918.5	1917.5	1916.5	1915.5
15°	1869.3	1871.5	1873.6	1874.1	1873.1	1872.0	1870.9	1869.9
17.5°	1820.5	1821.9	1823.2	1823.5	1822.8	1822.1	1821.4	1820.7
20°	1784.2	1785.2	1786.3	1786.5	1785.8	1785.1	1784.4	1783.6
22.5°	1746.3	1748.2	1750.1	1750.4	1749.2	1747.9	1746.6	1745.3
25°	1683.8	1684.1	1684.5	1683.9	1682.5	1681.1	1679.7	1678.3
27.5°	1613.6	1612.8	1611.9	1610.6	1608.8	1607.1	1605.3	1603.5
30°	1565.2	1563.8	1562.4	1560.8	1559.0	1557.3	1555.5	1553.7
32.5°	1516.1	1514.4	1512.7	1511.0	1509.2	1507.4	1505.7	1503.9
35°	1438.6	1436.1	1433.6	1431.5	1429.7	1427.9	1426.1	1424.4
37.5°	1357.3	1354.6	1351.9	1349.4	1347.1	1344.7	1342.4	1340.0
40°	1300.7	1297.1	1293.6	1290.9	1289.2	1287.4	1285.6	1283.8
42.5°	1245.9	1241.8	1237.7	1235.0	1233.8	1232.6	1231.4	1230.2
45°	1161.1	1157.2	1153.3	1150.8	1149.7	1148.6	1147.6	1146.5
47.5°	1079.0	1074.6	1070.2	1066.6	1063.9	1061.2	1058.5	1055.8
50°	1021.6	1016.6	1011.7	1008.1	1006.0	1003.9	1001.7	999.6
52.5°	962.7	958.3	953.9	950.4	947.7	945.0	942.3	939.6
55°	876.1	871.9	867.6	864.4	862.3	860.2	858.0	855.9
57.5°	789.4	785.3	781.3	778.2	776.2	774.1	772.0	770.0
60°	729.7	726.6	723.4	720.9	719.1	717.3	715.6	713.8
62.5°	671.5	668.6	665.7	663.4	661.6	659.8	658.1	656.3
65°	586.9	583.4	579.8	577.2	575.4	573.6	571.8	570.1
67.5°	499.7	496.3	492.9	490.9	490.4	489.9	489.4	488.9
70°	444.6	441.8	438.9	437.0	435.9	434.9	433.8	432.7
72.5°	389.6	387.3	385.0	383.3	382.3	381.2	380.1	379.1
75°	310.1	308.7	307.3	306.4	306.1	305.7	305.3	305.0
77.5°	234.8	234.4	234.0	233.3	232.4	231.5	230.5	229.6
80°	187.0	186.3	185.6	185.1	184.7	184.3	184.0	183.6
82.5°	144.1	143.7	143.3	142.9	142.5	142.2	141.8	141.5
85°	83.0	83.0	83.0	82.9	82.5	82.1	81.8	81.4
87.5°	34.3	34.5	34.7	34.8	34.9	35.0	35.0	35.1
90°	18.3	19.3	20.3	20.9	21.3	21.6	21.9	22.3
92.5°	17.7	18.7	19.7	20.2	20.3	20.4	20.4	20.5
95°	18.3	19.3	20.3	20.9	21.0	21.2	21.4	21.5
97.5°	19.8	19.9	20.0	20.1	20.3	20.5	20.6	20.8
100°	27.1	24.2	21.4	20.1	20.3	20.5	20.6	20.8
102.5°	96.9	66.6	36.4	21.2	21.3	21.3	21.3	21.4
105°	234.6	236.0	237.5	235.3	229.4	223.4	217.5	211.6
107.5°	290.2	290.9	291.7	292.3	293.0	293.6	294.2	294.8
110°	328.0	328.3	328.7	329.1	329.6	330.1	330.6	331.1





TEST NUMBER: P332845

CATALOG NUMBER: S124DIW-S1195D770U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	364.6	364.6	364.5	364.8	365.4	366.0	366.7	367.3
115°	419.3	419.6	420.0	420.1	420.1	420.1	420.1	420.1
117.5°	474.3	474.3	474.2	474.1	474.1	474.0	473.9	473.9
120°	508.4	508.7	509.0	509.0	508.7	508.4	508.1	507.7
122.5°	542.0	542.2	542.4	542.3	542.0	541.6	541.3	541.0
125°	588.9	589.4	589.9	590.2	590.4	590.5	590.7	590.9
127.5°	635.5	635.4	635.3	635.2	635.1	634.9	634.8	634.7
130°	663.9	664.1	664.3	664.3	664.3	664.3	664.3	664.3
132.5°	691.8	692.0	692.2	692.2	692.1	691.9	691.8	691.7
135°	730.3	730.7	731.0	731.3	731.6	732.0	732.3	732.6
137.5°	767.2	767.6	767.9	768.1	768.0	767.9	767.8	767.7
140°	790.0	790.5	791.0	791.4	791.5	791.7	791.9	792.0
142.5°	811.2	811.5	811.9	812.1	812.1	812.1	812.2	812.2
145°	841.3	841.5	841.7	841.9	842.2	842.6	842.9	843.2
147.5°	867.8	868.0	868.1	868.3	868.4	868.6	868.8	868.9
150°	884.8	884.8	884.8	884.9	885.1	885.2	885.4	885.5
152.5°	899.6	899.8	900.1	900.2	900.1	900.0	899.9	899.8
155°	919.5	920.2	920.8	920.9	920.4	919.9	919.4	919.0
157.5°	936.7	937.6	938.4	938.4	937.6	936.7	935.8	935.0
160°	947.7	948.6	949.6	949.6	948.6	947.7	946.7	945.7
162.5°	956.6	957.5	958.5	958.5	957.4	956.2	955.1	954.0
165°	969.1	970.4	971.7	971.7	970.2	968.7	967.2	965.7
167.5°	978.3	979.7	981.2	981.1	979.4	977.8	976.1	974.5
170°	983.9	985.3	986.6	986.4	984.8	983.1	981.5	979.8
172.5°	987.5	988.8	990.1	989.9	988.1	986.4	984.6	982.8
175°	991.7	993.2	994.7	994.4	992.4	990.5	988.5	986.5
177.5°	993.4	994.4	995.5	995.2	993.6	992.0	990.5	988.9
180°	992.4	992.4	992.4	992.4	992.4	992.4	992.4	992.4

(END OF REPORT)