

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332726-927

Luminaire Tested: **S124DIW-S350D770U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332726-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S350D770U927-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 770 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3312.3 lumens
Efficiency: N/A
Efficacy: 109.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 30.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332726-927

CATALOG NUMBER: S124DIW-S350D770U927-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332726-927

CATALOG NUMBER: S124DIW-S350D770U927-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44	36
1	95	90	87	83	86	82	79	76	66	64	62	52	50	49	38	37	37	30
2	86	79	73	68	78	72	67	62	58	54	51	45	43	41	34	32	31	26
3	79	69	62	56	71	63	57	52	51	47	43	40	37	34	30	28	26	22
4	72	61	54	48	65	56	49	44	45	40	37	36	32	29	27	24	23	19
5	66	54	47	41	59	50	43	38	41	35	31	32	28	25	24	22	20	16
6	61	49	41	35	55	45	38	33	36	31	27	29	25	22	22	19	17	14
7	56	44	36	31	51	40	33	28	33	28	24	26	22	20	20	17	15	13
8	52	40	32	27	47	36	30	25	30	25	21	24	20	17	18	16	14	11
9	48	36	29	24	44	33	27	22	27	22	19	22	18	16	17	14	12	10
10	45	33	26	21	41	30	24	20	25	20	17	20	17	14	16	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3777	3777	3777
5°	3789	3743	3771
10°	3765	3713	3731
15°	3719	3661	3670
20°	3660	3594	3598
25°	3591	3520	3510
30°	3506	3432	3402
35°	3418	3341	3297
40°	3327	3236	3177
45°	3232	3134	3075
50°	3127	3042	2948
55°	3013	2923	2829
60°	2900	2792	2706
65°	2772	2665	2558
70°	2629	2497	2398
75°	2408	2293	2233
80°	2143	2060	2004
85°	1880	1806	1769



TEST NUMBER: P332726-927

CATALOG NUMBER: S124DIW-S350D770U927-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.1	1.3
10°-20°	124.2	3.7
20°-30°	182.8	5.5
30°-40°	212.5	6.4
40°-50°	212.5	6.4
50°-60°	185.9	5.6
60°-70°	138.0	4.2
70°-80°	78.4	2.4
80°-90°	24.9	0.8
90°-100°	50.1	1.5
100°-110°	148.5	4.5
110°-120°	252.1	7.6
120°-130°	332.4	10.0
130°-140°	373.3	11.3
140°-150°	366.9	11.1
150°-160°	308.6	9.3
160°-170°	205.3	6.2
170°-180°	71.9	2.2
0°-30°	351.0	10.6
0°-40°	563.5	17.0
0°-60°	961.8	29.0
0°-90°	1203.1	36.3
90°-120°	450.8	13.6
90°-150°	1523.4	46.0
90°-180°	2109.0	63.7
0°-180°	3312.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	468	468	468	468	468	
5°	468	466	462	466	465	44
15°	445	443	438	440	439	125
25°	403	400	395	396	394	185
35°	347	344	339	336	334	217
45°	283	280	274	270	269	218
55°	214	213	208	203	201	192
65°	145	143	140	136	134	144
75°	77	75	74	72	72	82
85°	20	20	20	20	19	22
90°	2	8	13	16	18	3
95°	35	40	45	46	46	39
105°	137	138	140	142	144	145
115°	256	256	255	255	254	253
125°	373	373	373	372	370	333
135°	482	485	485	484	482	372
145°	585	587	588	587	586	366
155°	670	670	670	672	670	308
165°	730	728	727	730	728	206
175°	759	756	756	759	756	72
180°	760	760	760	760	760	



TEST NUMBER: P332726-927

CATALOG NUMBER: S124DIW-S350D770U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	467.9	467.9	467.9	467.9	467.9	467.9	467.9	467.9	467.9	467.9	467.9
2.5°	469.1	469.0	468.7	468.6	468.3	467.9	467.1	466.4	465.7	464.9	465.6
5°	467.5	467.2	466.9	466.6	466.3	465.6	464.7	463.8	462.9	461.9	462.9
7.5°	463.3	462.9	462.6	462.2	461.9	461.2	460.2	459.2	458.2	457.2	457.9
10°	459.3	459.0	458.7	458.4	458.0	457.3	456.2	455.1	454.1	453.0	453.6
12.5°	454.2	453.9	453.6	453.2	452.9	452.2	451.0	449.9	448.7	447.6	448.3
15°	445.0	444.7	444.4	444.1	443.8	443.0	441.7	440.5	439.2	438.0	438.5
17.5°	434.0	433.6	433.2	432.8	432.4	431.6	430.4	429.2	428.0	426.8	427.1
20°	426.0	425.6	425.2	424.7	424.3	423.5	422.2	421.0	419.7	418.4	418.7
22.5°	417.2	416.7	416.1	415.6	415.0	414.2	412.9	411.7	410.4	409.2	409.6
25°	403.1	402.5	402.0	401.3	400.8	399.9	398.7	397.5	396.4	395.2	395.3
27.5°	386.9	386.3	385.7	385.1	384.5	383.7	382.5	381.5	380.4	379.3	379.1
30°	376.1	375.4	374.8	374.1	373.4	372.6	371.5	370.3	369.3	368.2	367.9
32.5°	364.7	364.1	363.5	362.9	362.3	361.4	360.3	359.1	358.0	356.8	356.4
35°	346.8	346.3	345.7	345.1	344.5	343.6	342.5	341.3	340.2	339.0	338.4
37.5°	328.0	327.5	326.9	326.5	325.9	325.0	323.8	322.5	321.2	320.0	319.3
40°	315.7	315.1	314.4	313.7	313.1	312.1	310.9	309.6	308.3	307.1	306.3
42.5°	302.5	302.1	301.7	301.3	301.0	300.0	298.7	297.2	295.9	294.5	293.5
45°	283.1	282.5	281.9	281.4	280.7	279.8	278.5	277.1	275.8	274.5	273.5
47.5°	262.8	262.4	262.0	261.6	261.2	260.4	259.1	257.9	256.7	255.4	254.4
50°	249.0	248.7	248.3	248.0	247.6	246.9	245.7	244.5	243.4	242.2	241.1
52.5°	235.5	235.0	234.6	234.2	233.9	233.1	231.8	230.6	229.3	228.1	227.1
55°	214.1	213.9	213.6	213.3	213.1	212.4	211.2	210.1	208.9	207.7	206.8
57.5°	193.7	193.5	193.1	192.9	192.6	191.9	190.7	189.6	188.4	187.3	186.3
60°	179.6	179.2	178.8	178.3	177.9	177.2	176.1	175.0	174.0	172.9	172.1
62.5°	165.8	165.5	165.1	164.8	164.4	163.7	162.5	161.4	160.2	159.1	158.4
65°	145.1	144.7	144.3	143.9	143.5	142.8	142.0	141.2	140.3	139.5	138.6
67.5°	124.3	123.9	123.5	123.1	122.7	122.2	121.4	120.6	119.8	118.9	118.1
70°	111.4	110.7	110.2	109.6	109.0	108.4	107.7	107.1	106.4	105.8	105.0
72.5°	97.6	97.0	96.4	95.9	95.2	94.7	94.1	93.6	93.1	92.5	92.0
75°	77.2	76.8	76.4	76.0	75.6	75.2	74.8	74.3	73.9	73.5	73.2
77.5°	57.8	57.7	57.4	57.3	57.1	56.8	56.5	56.1	55.7	55.4	55.2
80°	46.1	45.9	45.6	45.4	45.2	44.9	44.8	44.6	44.4	44.3	44.0
82.5°	34.7	34.6	34.5	34.4	34.2	34.1	34.1	34.1	34.1	34.1	34.0
85°	20.3	20.3	20.3	20.3	20.3	20.2	20.0	19.8	19.6	19.5	19.5
87.5°	8.2	8.4	8.6	8.8	9.0	9.2	9.3	9.5	9.7	9.8	10.0
90°	1.7	3.2	4.7	6.1	7.5	8.8	9.8	10.9	11.9	12.9	13.7
92.5°	12.6	14.3	15.8	17.5	19.2	20.4	21.1	21.8	22.6	23.3	23.8
95°	35.3	36.4	37.6	38.8	40.0	41.0	41.9	42.9	43.8	44.7	45.1
97.5°	61.6	62.6	63.5	64.4	65.4	66.4	67.5	68.5	69.6	70.7	71.1
100°	82.3	82.9	83.3	83.9	84.4	85.2	86.4	87.6	88.8	90.0	90.2
102.5°	103.9	104.2	104.3	104.6	104.8	105.4	106.5	107.6	108.6	109.7	110.1
105°	137.0	137.1	137.3	137.4	137.5	137.8	138.4	138.9	139.4	139.9	140.3
107.5°	171.7	171.8	172.0	172.1	172.3	172.5	172.5	172.6	172.7	172.8	173.1
110°	195.2	195.4	195.7	196.0	196.2	196.3	196.1	196.1	195.9	195.7	195.5



TEST NUMBER: P332726-927

CATALOG NUMBER: S124DIW-S350D770U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	219.7	219.7	219.8	219.8	219.8	219.8	219.5	219.3	219.0	218.8	218.8
115°	256.4	256.4	256.4	256.4	256.4	256.2	256.0	255.7	255.4	255.2	255.0
117.5°	290.9	291.0	291.1	291.2	291.4	291.3	291.1	291.0	290.7	290.6	290.1
120°	313.9	314.5	315.0	315.5	316.1	316.1	315.8	315.4	315.0	314.6	313.9
122.5°	337.9	338.2	338.3	338.6	338.8	338.8	338.7	338.4	338.3	338.1	337.6
125°	373.4	373.4	373.4	373.4	373.4	373.3	373.1	373.0	372.9	372.7	372.5
127.5°	405.4	405.8	406.2	406.6	407.0	407.1	406.9	406.7	406.5	406.3	406.0
130°	428.0	428.4	428.8	429.2	429.6	429.8	429.8	429.8	429.8	429.8	429.5
132.5°	451.1	451.4	451.6	451.9	452.3	452.3	452.2	452.1	452.0	451.9	451.6
135°	481.6	482.3	483.1	483.9	484.7	485.1	485.1	485.1	485.1	485.1	484.8
137.5°	514.7	515.1	515.4	515.8	516.2	516.4	516.7	516.8	517.1	517.3	516.9
140°	536.8	537.0	537.3	537.6	537.8	538.0	538.0	538.0	538.0	538.0	537.8
142.5°	557.0	557.3	557.5	557.8	558.1	558.2	558.0	557.9	557.9	557.7	557.7
145°	585.0	585.5	586.1	586.6	587.1	587.4	587.6	587.7	587.8	588.0	587.8
147.5°	612.8	613.4	614.0	614.7	615.3	615.5	615.4	615.3	615.2	615.1	615.0
150°	629.7	630.2	630.7	631.3	631.8	632.1	632.1	632.1	632.1	632.1	632.1
152.5°	645.7	646.0	646.3	646.7	647.0	647.1	647.2	647.4	647.5	647.5	647.8
155°	670.3	670.3	670.3	670.3	670.3	670.2	670.0	669.9	669.8	669.7	670.2
157.5°	690.9	690.7	690.5	690.2	690.0	689.9	689.8	689.8	689.8	689.8	690.1
160°	703.2	703.1	702.9	702.8	702.7	702.5	702.4	702.3	702.1	702.0	702.4
162.5°	714.5	714.2	713.8	713.4	713.1	712.9	712.7	712.6	712.5	712.3	713.0
165°	729.7	729.3	728.9	728.5	728.1	727.8	727.5	727.2	727.0	726.7	727.5
167.5°	741.2	740.8	740.2	739.7	739.1	738.8	738.9	738.9	738.9	738.9	739.7
170°	747.9	747.2	746.6	745.9	745.3	745.0	745.1	745.3	745.4	745.5	746.3
172.5°	752.6	752.0	751.5	750.9	750.4	750.1	750.1	750.2	750.2	750.2	751.1
175°	759.1	758.4	757.7	757.1	756.5	756.1	755.9	755.7	755.7	755.5	756.5
177.5°	761.1	760.7	760.1	759.6	759.1	758.8	758.8	758.8	758.8	758.8	759.5
180°	760.2	760.2	760.2	760.2	760.2	760.2	760.2	760.2	760.2	760.2	760.2



TEST NUMBER: P332726-927

CATALOG NUMBER: S124DIW-S350D770U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	467.9	467.9	467.9	467.9	467.9	467.9	467.9	467.9
2.5°	466.3	467.0	467.6	467.9	467.9	467.8	467.7	467.6
5°	463.8	464.7	465.6	466.0	465.8	465.6	465.5	465.3
7.5°	458.6	459.4	460.1	460.4	460.3	460.2	460.1	460.0
10°	454.3	455.0	455.7	455.9	455.7	455.5	455.3	455.2
12.5°	449.0	449.7	450.5	450.8	450.5	450.3	450.0	449.8
15°	438.9	439.4	440.0	440.1	439.8	439.6	439.3	439.1
17.5°	427.5	427.8	428.1	428.2	428.0	427.9	427.7	427.5
20°	419.0	419.2	419.5	419.5	419.3	419.1	419.0	418.8
22.5°	410.0	410.5	411.0	411.1	410.7	410.4	410.1	409.9
25°	395.4	395.5	395.5	395.5	395.1	394.7	394.4	394.1
27.5°	378.9	378.7	378.5	378.2	377.8	377.4	376.9	376.5
30°	367.6	367.3	366.9	366.5	366.1	365.7	365.3	364.9
32.5°	356.0	355.6	355.2	354.8	354.4	353.9	353.6	353.2
35°	337.8	337.2	336.6	336.1	335.7	335.3	334.9	334.5
37.5°	318.7	318.1	317.4	316.9	316.3	315.8	315.2	314.7
40°	305.5	304.6	303.8	303.2	302.7	302.3	301.9	301.5
42.5°	292.6	291.6	290.7	290.0	289.7	289.5	289.1	288.9
45°	272.7	271.7	270.8	270.2	270.0	269.7	269.5	269.3
47.5°	253.3	252.3	251.3	250.5	249.9	249.2	248.6	248.0
50°	239.9	238.8	237.6	236.7	236.2	235.8	235.2	234.7
52.5°	226.1	225.1	224.0	223.2	222.5	221.9	221.3	220.6
55°	205.7	204.7	203.7	203.0	202.5	202.0	201.5	201.0
57.5°	185.4	184.4	183.5	182.8	182.3	181.8	181.3	180.8
60°	171.3	170.6	169.8	169.3	168.9	168.4	168.0	167.6
62.5°	157.7	157.0	156.3	155.7	155.3	155.0	154.6	154.1
65°	137.8	137.0	136.2	135.5	135.1	134.7	134.3	133.9
67.5°	117.3	116.5	115.7	115.3	115.2	115.0	114.9	114.8
70°	104.4	103.8	103.1	102.6	102.3	102.1	101.9	101.6
72.5°	91.5	90.9	90.4	90.0	89.8	89.5	89.3	89.0
75°	72.8	72.5	72.2	71.9	71.9	71.8	71.7	71.6
77.5°	55.1	55.1	55.0	54.8	54.6	54.3	54.1	53.9
80°	43.9	43.7	43.6	43.5	43.3	43.3	43.2	43.1
82.5°	33.8	33.7	33.7	33.6	33.5	33.4	33.3	33.2
85°	19.5	19.5	19.5	19.5	19.4	19.3	19.2	19.1
87.5°	10.1	10.2	10.4	10.5	10.5	10.6	10.7	10.7
90°	14.5	15.3	16.1	16.6	16.9	17.1	17.3	17.7
92.5°	24.2	24.7	25.2	25.5	25.7	25.8	26.0	26.1
95°	45.5	45.9	46.3	46.4	46.4	46.4	46.4	46.4
97.5°	71.6	72.1	72.6	72.8	72.8	72.8	72.8	72.8
100°	90.5	90.7	91.0	91.1	91.1	91.1	91.1	91.1
102.5°	110.4	110.8	111.1	111.4	111.5	111.6	111.7	111.9
105°	140.7	141.1	141.5	141.9	142.3	142.7	143.1	143.5
107.5°	173.5	173.8	174.2	174.4	174.4	174.4	174.3	174.3
110°	195.3	195.0	194.7	194.8	195.2	195.6	196.0	196.4



TEST NUMBER: P332726-927

CATALOG NUMBER: S124DIW-S350D770U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	218.7	218.6	218.6	218.6	218.7	218.8	218.9	219.0
115°	254.9	254.8	254.6	254.5	254.4	254.3	254.1	254.0
117.5°	289.7	289.2	288.8	288.4	288.2	287.9	287.6	287.4
120°	313.2	312.6	312.0	311.7	312.0	312.3	312.5	312.8
122.5°	337.2	336.8	336.3	335.8	335.3	334.9	334.5	334.0
125°	372.2	372.0	371.7	371.5	371.2	370.9	370.7	370.4
127.5°	405.8	405.5	405.2	405.0	404.8	404.6	404.3	404.2
130°	429.3	429.0	428.7	428.3	427.9	427.3	426.7	426.3
132.5°	451.4	451.1	450.8	450.6	450.4	450.2	450.0	449.8
135°	484.5	484.3	484.0	483.7	483.3	482.9	482.5	482.1
137.5°	516.6	516.3	515.9	515.8	515.9	515.9	516.0	516.1
140°	537.7	537.6	537.4	537.3	537.2	537.0	536.9	536.8
142.5°	557.7	557.6	557.6	557.6	557.5	557.5	557.5	557.5
145°	587.7	587.6	587.4	587.2	586.8	586.4	586.0	585.6
147.5°	614.9	614.8	614.7	614.6	614.4	614.3	614.2	614.0
150°	632.1	632.1	632.1	632.0	631.8	631.7	631.6	631.4
152.5°	648.2	648.5	648.8	648.8	648.5	648.2	647.8	647.5
155°	670.7	671.2	671.8	671.8	671.2	670.7	670.2	669.7
157.5°	690.5	690.9	691.3	691.3	690.9	690.5	690.0	689.5
160°	702.8	703.2	703.6	703.5	702.8	702.1	701.5	700.8
162.5°	713.8	714.5	715.2	715.2	714.5	713.9	713.3	712.6
165°	728.3	729.0	729.8	730.0	729.4	728.9	728.4	727.9
167.5°	740.5	741.2	742.0	742.0	741.2	740.5	739.7	738.8
170°	747.1	747.9	748.7	748.6	747.7	746.8	745.8	745.0
172.5°	752.0	752.9	753.8	753.8	752.8	751.9	751.0	750.1
175°	757.3	758.3	759.1	759.1	758.3	757.3	756.5	755.5
177.5°	760.3	761.0	761.8	761.7	760.8	760.0	759.1	758.4
180°	760.2	760.2	760.2	760.2	760.2	760.2	760.2	760.2

(END OF REPORT)