

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332762

Luminaire Tested: **S124DIW-S575D1050U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332762
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S575D1050U835-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1050 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6130.1 lumens
Efficiency: N/A
Efficacy: 135.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 45.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332762

CATALOG NUMBER: S124DIW-S575D1050U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332762

CATALOG NUMBER: S124DIW-S575D1050U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	48	48	48	41
1	96	91	88	84	87	83	80	77	68	66	64	55	53	52	42	41	40	34
2	87	80	74	69	79	73	68	63	60	56	53	48	45	43	37	35	34	29
3	79	70	63	57	72	64	58	53	53	48	44	42	39	36	33	31	29	24
4	73	62	54	48	66	57	50	45	47	42	38	38	34	31	29	27	25	21
5	67	55	47	41	60	51	44	38	42	37	33	34	30	27	26	24	22	18
6	61	49	41	36	56	45	38	33	38	32	28	31	27	24	24	21	19	16
7	57	45	37	31	51	41	34	29	34	29	25	28	24	21	22	19	17	14
8	52	40	33	27	48	37	30	26	31	26	22	25	21	19	20	17	15	13
9	49	37	29	24	44	34	27	23	28	23	20	23	19	17	18	16	14	11
10	46	34	27	22	42	31	25	20	26	21	18	22	18	15	17	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7840	7840	7840
5°	7864	7769	7826
10°	7814	7706	7744
15°	7720	7596	7616
20°	7594	7460	7467
25°	7451	7306	7285
30°	7276	7124	7058
35°	7094	6933	6841
40°	6905	6716	6593
45°	6707	6503	6379
50°	6489	6314	6118
55°	6253	6068	5871
60°	6018	5792	5616
65°	5752	5530	5307
70°	5455	5179	4978
75°	5000	4757	4635
80°	4449	4268	4161
85°	3890	3751	3677



TEST NUMBER: P332762

CATALOG NUMBER: S124DIW-S575D1050U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.5	1.5
10°-20°	257.7	4.2
20°-30°	379.3	6.2
30°-40°	440.9	7.2
40°-50°	440.9	7.2
50°-60°	385.7	6.3
60°-70°	286.4	4.7
70°-80°	162.7	2.7
80°-90°	50.9	0.8
90°-100°	86.4	1.4
100°-110°	255.9	4.2
110°-120°	434.4	7.1
120°-130°	572.8	9.3
130°-140°	643.3	10.5
140°-150°	632.1	10.3
150°-160°	531.7	8.7
160°-170°	353.7	5.8
170°-180°	123.9	2.0
0°-30°	728.4	11.9
0°-40°	1169.3	19.1
0°-60°	1996.0	32.6
0°-90°	2496.0	40.7
90°-120°	776.7	12.7
90°-150°	2624.9	42.8
90°-180°	3634.0	59.3
0°-180°	6130.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	971	971	971	971	971	
5°	970	967	959	967	966	92
15°	924	920	909	913	911	260
25°	836	831	820	821	818	385
35°	720	714	704	698	694	450
45°	588	582	570	561	559	453
55°	444	442	431	422	417	398
65°	301	297	290	282	278	298
75°	160	156	152	150	149	170
85°	42	42	40	40	40	46
90°	3	14	22	28	30	6
95°	61	70	77	80	80	68
105°	236	237	241	244	247	250
115°	442	442	440	439	438	435
125°	643	643	642	640	638	573
135°	830	835	836	834	831	642
145°	1008	1012	1013	1012	1009	631
155°	1155	1155	1154	1158	1154	531
165°	1257	1254	1252	1258	1254	354
175°	1308	1303	1302	1308	1302	124
180°	1310	1310	1310	1310	1310	



TEST NUMBER: P332762

CATALOG NUMBER: S124DIW-S575D1050U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	971.1	971.1	971.1	971.1	971.1	971.1	971.1	971.1	971.1	971.1	971.1
2.5°	973.6	973.2	972.8	972.4	972.0	971.0	969.5	968.0	966.4	964.9	966.3
5°	970.4	969.7	969.0	968.3	967.6	966.3	964.4	962.5	960.6	958.7	960.6
7.5°	961.3	960.6	960.0	959.3	958.6	957.2	955.1	953.0	950.8	948.7	950.3
10°	953.2	952.6	951.9	951.2	950.5	949.0	946.8	944.5	942.3	940.0	941.4
12.5°	942.7	942.0	941.3	940.6	939.9	938.4	936.0	933.6	931.2	928.8	930.3
15°	923.7	923.0	922.3	921.6	920.9	919.3	916.7	914.1	911.5	908.9	909.9
17.5°	900.8	899.9	899.1	898.2	897.3	895.7	893.2	890.8	888.3	885.9	886.5
20°	884.0	883.1	882.3	881.4	880.5	878.8	876.2	873.6	871.0	868.4	868.9
22.5°	865.9	864.8	863.7	862.5	861.4	859.5	856.9	854.3	851.7	849.1	850.1
25°	836.5	835.3	834.1	832.9	831.7	829.9	827.4	825.0	822.6	820.2	820.4
27.5°	802.9	801.7	800.4	799.2	797.9	796.2	793.9	791.7	789.4	787.2	786.8
30°	780.5	779.1	777.7	776.3	775.0	773.1	770.9	768.6	766.4	764.2	763.5
32.5°	756.8	755.6	754.3	753.1	751.9	750.0	747.7	745.3	742.9	740.5	739.7
35°	719.8	718.6	717.4	716.2	715.0	713.1	710.7	708.3	705.9	703.5	702.2
37.5°	680.7	679.6	678.5	677.4	676.3	674.5	671.9	669.3	666.7	664.1	662.8
40°	655.2	653.8	652.4	651.1	649.7	647.7	645.1	642.5	639.9	637.3	635.6
42.5°	627.8	627.0	626.2	625.3	624.5	622.6	619.8	616.9	614.0	611.2	609.2
45°	587.5	586.3	585.1	583.9	582.7	580.7	577.9	575.1	572.4	569.6	567.7
47.5°	545.3	544.5	543.7	542.8	542.0	540.3	537.8	535.2	532.6	530.1	527.9
50°	516.7	516.0	515.3	514.6	513.9	512.4	510.0	507.5	505.1	502.7	500.3
52.5°	488.7	487.9	487.0	486.2	485.4	483.7	481.1	478.6	476.0	473.4	471.3
55°	444.3	443.8	443.3	442.8	442.3	440.8	438.4	435.9	433.5	431.1	429.0
57.5°	402.0	401.4	400.8	400.2	399.6	398.2	395.8	393.4	391.0	388.6	386.6
60°	372.7	371.9	371.0	370.1	369.3	367.7	365.5	363.2	361.0	358.7	357.2
62.5°	344.1	343.4	342.6	341.9	341.2	339.6	337.3	334.9	332.5	330.1	328.7
65°	301.1	300.3	299.4	298.6	297.7	296.4	294.7	292.9	291.2	289.5	287.7
67.5°	257.9	257.1	256.3	255.5	254.7	253.5	251.8	250.2	248.5	246.8	245.2
70°	231.1	229.9	228.7	227.5	226.3	225.0	223.6	222.2	220.8	219.4	218.1
72.5°	202.5	201.3	200.1	198.8	197.6	196.5	195.4	194.3	193.2	192.0	190.9
75°	160.3	159.4	158.6	157.7	156.8	156.0	155.1	154.2	153.4	152.5	151.8
77.5°	120.0	119.6	119.2	118.9	118.5	117.9	117.1	116.4	115.6	114.9	114.6
80°	95.7	95.2	94.7	94.2	93.6	93.2	92.9	92.5	92.2	91.8	91.5
82.5°	72.1	71.8	71.6	71.3	71.1	70.9	70.9	70.8	70.7	70.7	70.4
85°	42.0	42.0	42.0	42.0	42.0	41.8	41.5	41.2	40.8	40.5	40.5
87.5°	16.8	17.2	17.5	17.9	18.2	18.5	18.7	19.0	19.2	19.4	19.7
90°	3.0	5.5	8.0	10.5	12.9	15.1	16.9	18.7	20.5	22.3	23.6
92.5°	21.7	24.5	27.4	30.2	33.0	35.1	36.3	37.6	38.9	40.1	40.9
95°	60.8	62.8	64.8	66.9	68.9	70.7	72.3	73.8	75.4	77.0	77.7
97.5°	106.2	107.8	109.4	111.0	112.7	114.4	116.2	118.1	119.9	121.8	122.6
100°	141.8	142.7	143.6	144.5	145.4	146.9	148.9	150.9	153.0	155.0	155.4
102.5°	179.1	179.5	179.8	180.2	180.5	181.6	183.5	185.3	187.2	189.0	189.7
105°	236.0	236.3	236.5	236.7	236.9	237.5	238.4	239.3	240.2	241.1	241.8
107.5°	295.8	296.1	296.3	296.6	296.9	297.1	297.2	297.4	297.5	297.6	298.3
110°	336.3	336.8	337.2	337.7	338.1	338.2	338.0	337.8	337.6	337.3	336.9



TEST NUMBER: P332762

CATALOG NUMBER: S124DIW-S575D1050U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	378.5	378.6	378.7	378.7	378.8	378.7	378.3	377.9	377.5	377.1	377.0
115°	441.7	441.7	441.7	441.7	441.7	441.5	441.0	440.6	440.1	439.7	439.4
117.5°	501.3	501.4	501.6	501.8	502.0	501.9	501.6	501.3	501.0	500.6	499.9
120°	541.0	541.9	542.8	543.7	544.6	544.7	544.0	543.3	542.7	542.0	540.9
122.5°	582.3	582.7	583.0	583.4	583.7	583.8	583.4	583.1	582.8	582.5	581.7
125°	643.3	643.3	643.3	643.3	643.3	643.2	642.9	642.7	642.5	642.3	641.8
127.5°	698.6	699.3	699.9	700.6	701.3	701.5	701.1	700.7	700.4	700.0	699.6
130°	737.5	738.2	738.8	739.5	740.2	740.5	740.5	740.5	740.5	740.5	740.1
132.5°	777.2	777.7	778.2	778.7	779.2	779.3	779.2	779.0	778.8	778.6	778.2
135°	829.7	831.0	832.4	833.7	835.1	835.8	835.8	835.8	835.8	835.8	835.3
137.5°	886.8	887.4	888.1	888.7	889.3	889.8	890.2	890.6	890.9	891.3	890.7
140°	924.9	925.4	925.8	926.3	926.7	926.9	926.9	926.9	926.9	926.9	926.7
142.5°	959.8	960.2	960.7	961.1	961.6	961.7	961.5	961.3	961.2	961.0	960.9
145°	1008.0	1008.9	1009.8	1010.7	1011.6	1012.1	1012.4	1012.6	1012.8	1013.0	1012.8
147.5°	1055.8	1056.9	1058.0	1059.0	1060.1	1060.6	1060.4	1060.2	1060.0	1059.8	1059.7
150°	1085.0	1085.9	1086.8	1087.7	1088.6	1089.0	1089.0	1089.0	1089.0	1089.0	1089.0
152.5°	1112.5	1113.1	1113.6	1114.1	1114.7	1115.0	1115.2	1115.4	1115.6	1115.8	1116.3
155°	1154.9	1154.9	1154.9	1154.9	1154.9	1154.8	1154.5	1154.3	1154.1	1153.9	1154.8
157.5°	1190.5	1190.1	1189.7	1189.3	1188.9	1188.7	1188.6	1188.6	1188.5	1188.5	1189.2
160°	1211.6	1211.4	1211.1	1210.9	1210.7	1210.5	1210.2	1210.0	1209.8	1209.6	1210.2
162.5°	1231.0	1230.5	1229.9	1229.3	1228.7	1228.3	1228.1	1227.9	1227.6	1227.4	1228.6
165°	1257.2	1256.5	1255.8	1255.2	1254.5	1253.9	1253.5	1253.0	1252.6	1252.1	1253.5
167.5°	1277.2	1276.3	1275.4	1274.4	1273.5	1273.0	1273.1	1273.1	1273.1	1273.2	1274.5
170°	1288.6	1287.5	1286.3	1285.2	1284.1	1283.6	1283.9	1284.1	1284.3	1284.5	1285.9
172.5°	1296.7	1295.7	1294.8	1293.9	1292.9	1292.5	1292.5	1292.6	1292.6	1292.6	1294.2
175°	1307.8	1306.7	1305.6	1304.5	1303.3	1302.7	1302.4	1302.2	1302.0	1301.8	1303.3
177.5°	1311.5	1310.6	1309.7	1308.8	1307.9	1307.4	1307.4	1307.4	1307.4	1307.4	1308.7
180°	1309.9	1309.9	1309.9	1309.9	1309.9	1309.9	1309.9	1309.9	1309.9	1309.9	1309.9



TEST NUMBER: P332762

CATALOG NUMBER: S124DIW-S575D1050U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	971.1	971.1	971.1	971.1	971.1	971.1	971.1	971.1
2.5°	967.7	969.1	970.5	971.1	970.9	970.8	970.7	970.5
5°	962.5	964.4	966.3	967.1	966.7	966.4	966.0	965.7
7.5°	951.8	953.3	954.8	955.5	955.3	955.1	954.9	954.6
10°	942.8	944.2	945.6	946.1	945.7	945.4	945.0	944.7
12.5°	931.9	933.4	934.9	935.4	934.9	934.4	934.0	933.5
15°	911.0	912.0	913.0	913.3	912.8	912.3	911.7	911.2
17.5°	887.2	887.8	888.5	888.6	888.3	887.9	887.6	887.3
20°	869.5	870.0	870.5	870.6	870.2	869.9	869.6	869.2
22.5°	851.0	851.9	852.9	853.0	852.4	851.8	851.2	850.5
25°	820.5	820.7	820.9	820.6	819.9	819.2	818.5	817.8
27.5°	786.4	785.9	785.5	784.9	784.0	783.2	782.3	781.4
30°	762.8	762.1	761.4	760.6	759.7	758.9	758.0	757.1
32.5°	738.8	738.0	737.2	736.3	735.5	734.6	733.7	732.9
35°	701.0	699.8	698.6	697.6	696.7	695.8	695.0	694.1
37.5°	661.5	660.1	658.8	657.6	656.5	655.3	654.2	653.0
40°	633.9	632.1	630.4	629.1	628.2	627.4	626.5	625.6
42.5°	607.2	605.1	603.1	601.8	601.3	600.7	600.1	599.5
45°	565.8	563.9	562.0	560.8	560.3	559.8	559.2	558.7
47.5°	525.8	523.6	521.5	519.8	518.5	517.1	515.8	514.5
50°	497.8	495.4	493.0	491.3	490.2	489.2	488.2	487.1
52.5°	469.1	467.0	464.9	463.1	461.8	460.5	459.2	457.9
55°	427.0	424.9	422.8	421.2	420.2	419.2	418.1	417.1
57.5°	384.7	382.7	380.7	379.2	378.2	377.2	376.2	375.2
60°	355.6	354.1	352.5	351.3	350.4	349.6	348.7	347.8
62.5°	327.3	325.8	324.4	323.3	322.4	321.6	320.7	319.8
65°	286.0	284.3	282.6	281.3	280.4	279.5	278.7	277.8
67.5°	243.5	241.9	240.2	239.2	239.0	238.8	238.5	238.3
70°	216.7	215.3	213.9	213.0	212.4	211.9	211.4	210.9
72.5°	189.8	188.7	187.6	186.8	186.3	185.8	185.3	184.7
75°	151.1	150.4	149.8	149.3	149.1	149.0	148.8	148.6
77.5°	114.4	114.2	114.0	113.7	113.2	112.8	112.3	111.9
80°	91.1	90.8	90.4	90.2	90.0	89.8	89.7	89.5
82.5°	70.2	70.0	69.8	69.6	69.5	69.3	69.1	68.9
85°	40.5	40.5	40.5	40.4	40.2	40.0	39.9	39.7
87.5°	19.9	20.2	20.5	20.7	20.7	20.8	20.9	21.0
90°	25.0	26.3	27.7	28.6	29.0	29.5	29.9	30.4
92.5°	41.7	42.5	43.4	43.9	44.2	44.4	44.7	45.0
95°	78.3	79.0	79.7	80.0	80.0	80.0	80.0	80.0
97.5°	123.4	124.2	125.0	125.4	125.4	125.4	125.4	125.4
100°	155.9	156.3	156.8	157.0	157.0	157.0	157.0	157.0
102.5°	190.3	190.9	191.6	192.0	192.1	192.3	192.5	192.7
105°	242.5	243.1	243.8	244.5	245.2	245.8	246.5	247.2
107.5°	298.9	299.5	300.2	300.4	300.4	300.4	300.3	300.3
110°	336.4	336.0	335.5	335.7	336.3	337.0	337.7	338.4



TEST NUMBER: P332762

CATALOG NUMBER: S124DIW-S575D1050U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	376.9	376.8	376.7	376.7	376.9	377.0	377.1	377.3
115°	439.2	439.0	438.8	438.5	438.3	438.1	437.9	437.6
117.5°	499.1	498.3	497.6	497.0	496.5	496.1	495.6	495.2
120°	539.7	538.6	537.5	537.1	537.6	538.0	538.5	538.9
122.5°	581.0	580.2	579.4	578.6	577.8	577.0	576.2	575.4
125°	641.4	640.9	640.5	640.0	639.6	639.1	638.7	638.2
127.5°	699.1	698.7	698.2	697.8	697.4	697.1	696.7	696.4
130°	739.6	739.2	738.7	738.1	737.2	736.3	735.4	734.5
132.5°	777.7	777.3	776.8	776.4	776.1	775.7	775.3	775.0
135°	834.9	834.4	834.0	833.4	832.7	832.0	831.4	830.7
137.5°	890.1	889.5	888.9	888.7	888.8	889.0	889.1	889.2
140°	926.5	926.3	926.0	925.8	925.6	925.4	925.1	924.9
142.5°	960.9	960.8	960.8	960.7	960.7	960.7	960.6	960.6
145°	1012.6	1012.4	1012.1	1011.7	1011.0	1010.3	1009.7	1009.0
147.5°	1059.5	1059.3	1059.1	1058.9	1058.7	1058.5	1058.2	1058.0
150°	1089.0	1089.0	1089.0	1088.9	1088.7	1088.5	1088.2	1088.0
152.5°	1116.8	1117.4	1117.9	1117.9	1117.3	1116.7	1116.1	1115.6
155°	1155.7	1156.6	1157.5	1157.5	1156.6	1155.7	1154.8	1153.9
157.5°	1189.9	1190.5	1191.2	1191.2	1190.4	1189.6	1188.9	1188.1
160°	1210.9	1211.6	1212.3	1212.0	1210.9	1209.8	1208.7	1207.5
162.5°	1229.8	1231.0	1232.3	1232.3	1231.2	1230.1	1228.9	1227.8
165°	1254.8	1256.2	1257.5	1257.7	1256.8	1255.9	1255.0	1254.1
167.5°	1275.9	1277.2	1278.6	1278.6	1277.2	1275.8	1274.4	1273.0
170°	1287.2	1288.6	1289.9	1289.8	1288.3	1286.7	1285.1	1283.5
172.5°	1295.7	1297.2	1298.8	1298.7	1297.2	1295.6	1294.0	1292.4
175°	1304.9	1306.5	1308.1	1308.1	1306.5	1304.9	1303.3	1301.8
177.5°	1310.0	1311.2	1312.5	1312.4	1310.9	1309.5	1308.1	1306.6
180°	1309.9	1309.9	1309.9	1309.9	1309.9	1309.9	1309.9	1309.9

(END OF REPORT)