

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332769

Luminaire Tested: **S124DIW-S575D1560U835-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332769  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIW-S575D1560U835-4F0-1E-UDD-A  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 575 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1560 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8834.1 lumens  
Efficiency: N/A  
Efficacy: 145.8 lumens/watt  
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 60.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332769

CATALOG NUMBER: S124DIW-S575D1560U835-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P332769

CATALOG NUMBER: S124DIW-S575D1560U835-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	37	37	37	29				
1	93	89	85	82	83	80	77	74	63	61	59	47	46	45	33	32	32	25				
2	85	78	72	67	76	70	65	61	55	52	49	42	40	38	29	28	27	21				
3	78	69	62	56	69	62	56	51	49	45	41	37	34	32	26	24	23	18				
4	71	61	53	47	63	55	48	43	43	39	35	33	30	27	23	21	20	16				
5	65	54	46	40	58	49	42	37	39	34	30	30	26	24	21	19	17	14				
6	60	48	41	35	53	44	37	32	35	30	26	27	23	21	19	17	15	12				
7	55	43	36	31	49	39	33	28	32	27	23	24	21	18	17	15	14	11				
8	51	39	32	27	46	36	29	25	29	24	20	22	19	16	16	14	12	10				
9	48	36	29	24	43	33	26	22	26	22	18	20	17	15	15	13	11	9				
10	44	33	26	21	40	30	24	20	24	19	16	19	15	13	14	11	10	8				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	7582	7582	7582	7582
5°	8930	7602	6710	7602
10°	10691	7569	6041	7569
15°	12649	7492	5548	7492
20°	14086	7414	5107	7414
25°	14313	7299	4804	7299
30°	12179	7189	4708	7189
35°	9363	7009	4709	7009
40°	7299	6798	4797	6798
45°	6085	6481	4877	6481
50°	5355	6094	5043	6094
55°	4906	5630	5246	5630
60°	4598	5214	5491	5214
65°	4281	4749	5692	4749
70°	3911	4289	5823	4289
75°	3497	3774	5752	3774
80°	2929	3092	5570	3092
85°	2158	2232	5335	2232



TEST NUMBER: P332769

CATALOG NUMBER: S124DIW-S575D1560U835-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	91.5	1.0
10°-20°	282.0	3.2
20°-30°	447.2	5.1
30°-40°	497.7	5.6
40°-50°	453.1	5.1
50°-60°	370.2	4.2
60°-70°	264.3	3.0
70°-80°	145.5	1.6
80°-90°	45.6	0.5
90°-100°	69.0	0.8
100°-110°	439.7	5.0
110°-120°	841.1	9.5
120°-130°	1067.8	12.1
130°-140°	1142.4	12.9
140°-150°	1068.3	12.1
150°-160°	861.5	9.8
160°-170°	555.6	6.3
170°-180°	191.5	2.2
0°-30°	820.8	9.3
0°-40°	1318.5	14.9
0°-60°	2141.8	24.2
0°-90°	2597.2	29.4
90°-120°	1349.8	15.3
90°-150°	4628.2	52.4
90°-180°	6237.0	70.6
0°-180°	8834.1	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	939	939	939	939	939	
5°	1102	938	828	938	1102	112
15°	1514	896	664	896	1514	428
25°	1607	819	539	819	1607	708
35°	950	711	478	711	950	603
45°	533	568	427	568	533	420
55°	349	400	373	400	349	315
65°	224	249	298	249	224	222
75°	112	121	184	121	112	119
85°	23	24	58	24	23	30
90°	45	4	45	4	45	20
95°	44	83	44	83	44	35
105°	430	454	430	454	430	375
115°	854	848	854	848	854	845
125°	1200	1191	1200	1191	1200	1069
135°	1488	1478	1488	1478	1488	1146
145°	1713	1704	1713	1704	1713	1071
155°	1867	1868	1867	1868	1867	861
165°	1962	1971	1962	1971	1962	554
175°	2004	2016	2004	2016	2004	191
180°	2016	2016	2016	2016	2016	



TEST NUMBER: P332769

CATALOG NUMBER: S124DIW-S575D1560U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	939.2	939.2	939.2	939.2	939.2	939.2	939.2	939.2	939.2	939.2	939.2
2.5°	999.6	999.3	996.2	995.6	993.4	990.6	990.0	985.0	975.0	970.4	969.1
5°	1101.9	1109.7	1099.5	1097.6	1096.4	1083.6	1077.0	1069.2	1051.3	1040.8	1032.6
7.5°	1223.9	1224.8	1220.4	1216.8	1206.9	1195.7	1178.9	1161.0	1139.7	1117.5	1100.8
10°	1304.2	1307.3	1302.3	1301.5	1281.6	1269.2	1244.3	1223.3	1199.1	1172.3	1147.8
12.5°	1388.9	1384.5	1381.9	1365.3	1361.6	1338.9	1310.0	1288.3	1251.1	1220.2	1187.6
15°	1513.5	1505.0	1499.5	1476.6	1465.3	1433.8	1403.0	1379.3	1330.7	1284.4	1249.3
17.5°	1586.7	1595.2	1582.6	1573.2	1544.0	1521.9	1490.5	1440.7	1402.6	1345.1	1300.9
20°	1639.6	1640.4	1633.4	1623.6	1600.7	1572.7	1538.4	1484.0	1438.4	1381.2	1320.5
22.5°	1653.9	1654.1	1651.1	1642.0	1624.6	1601.9	1567.4	1521.9	1466.8	1404.6	1343.9
25°	1606.9	1605.4	1608.9	1619.0	1612.4	1605.4	1585.5	1551.7	1500.3	1434.5	1369.2
27.5°	1432.3	1443.0	1462.8	1487.7	1511.7	1529.9	1535.1	1528.2	1496.3	1442.2	1373.8
30°	1306.5	1319.8	1334.5	1359.5	1407.7	1435.3	1465.7	1488.6	1475.8	1432.6	1368.8
32.5°	1168.3	1171.6	1193.5	1221.9	1266.1	1319.2	1367.3	1413.9	1429.4	1406.8	1353.5
35°	950.1	955.6	979.3	1007.3	1061.4	1126.4	1198.8	1263.3	1316.7	1338.1	1310.8
37.5°	775.4	791.0	807.7	837.8	885.5	944.0	1019.2	1102.7	1182.2	1235.4	1244.4
40°	692.6	702.3	714.4	737.3	777.8	835.4	899.9	995.7	1080.1	1156.4	1181.3
42.5°	627.2	632.9	640.3	661.0	691.9	749.1	808.1	892.3	977.1	1068.3	1110.0
45°	533.0	538.9	551.3	563.4	586.7	626.4	681.3	750.5	835.7	923.7	1000.7
47.5°	465.0	468.8	476.2	489.1	508.9	535.1	579.7	637.5	716.5	801.9	884.0
50°	426.4	429.5	435.4	447.1	462.2	485.6	522.1	576.2	638.1	724.1	804.6
52.5°	395.9	397.2	401.5	409.4	421.5	441.1	471.1	515.8	573.4	650.0	730.2
55°	348.6	350.2	354.1	359.9	370.4	382.9	405.8	439.3	489.5	556.0	625.6
57.5°	309.7	310.8	314.1	316.3	325.0	335.1	352.7	376.6	414.7	471.1	533.3
60°	284.8	284.0	287.9	289.9	295.7	304.3	317.9	340.8	373.9	419.4	476.6
62.5°	260.5	259.4	262.7	265.3	268.6	275.9	287.1	305.0	331.9	373.1	422.5
65°	224.1	222.6	224.5	227.6	230.7	234.6	242.8	258.7	280.1	309.7	347.4
67.5°	187.5	189.2	189.5	191.0	192.8	198.1	203.7	215.0	230.1	253.8	285.7
70°	165.7	166.1	167.7	167.7	168.9	173.5	178.2	184.8	199.6	221.4	247.5
72.5°	144.0	145.6	145.0	146.2	147.1	150.2	153.6	159.9	172.5	188.7	210.7
75°	112.1	113.2	113.2	113.6	114.8	115.9	118.7	123.3	132.3	144.3	159.5
77.5°	81.7	81.9	82.4	83.8	83.8	85.7	87.7	91.4	95.9	104.1	113.4
80°	63.0	63.8	63.4	64.2	64.2	65.8	66.5	71.2	73.1	78.6	86.0
82.5°	46.2	47.0	46.9	48.0	48.6	48.9	50.0	51.9	53.8	58.7	61.7
85°	23.3	24.1	23.3	24.1	25.3	25.7	26.8	27.2	28.8	30.0	32.7
87.5°	15.9	16.7	16.6	16.7	17.2	17.3	17.2	16.5	17.3	17.2	17.9
90°	45.2	44.6	43.9	43.2	42.6	41.2	39.2	37.2	35.2	33.2	30.5
92.5°	41.6	41.5	41.4	41.2	41.1	40.0	38.0	36.0	34.0	32.0	29.3
95°	43.7	43.4	43.1	42.7	42.4	41.2	39.2	37.2	35.2	33.2	32.8
97.5°	42.2	41.9	41.6	41.2	40.9	40.6	40.4	40.2	40.0	39.8	77.2
100°	42.2	41.9	41.6	41.2	40.9	43.6	49.3	55.0	60.7	66.4	112.6
102.5°	43.4	43.4	43.3	43.2	43.2	73.9	135.3	196.8	258.2	319.7	325.7
105°	429.8	441.9	453.9	466.0	478.0	482.6	479.6	476.5	473.5	470.5	468.8
107.5°	599.0	597.7	596.4	595.2	593.9	592.5	591.1	589.6	588.1	586.6	584.3
110°	672.6	671.6	670.6	669.6	668.6	667.7	667.1	666.4	665.7	665.0	663.0



TEST NUMBER: P332769

CATALOG NUMBER: S124DIW-S575D1560U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	746.2	744.9	743.6	742.4	741.1	740.5	740.6	740.8	740.9	741.1	740.1
115°	853.6	853.6	853.6	853.6	853.6	853.2	852.5	851.9	851.2	850.5	850.9
117.5°	962.7	962.9	963.0	963.1	963.3	963.4	963.5	963.7	963.8	963.9	963.2
120°	1031.5	1032.2	1032.8	1033.5	1034.2	1034.2	1033.5	1032.8	1032.2	1031.5	1031.8
122.5°	1099.1	1099.7	1100.4	1101.1	1101.7	1101.9	1101.5	1101.1	1100.7	1100.3	1099.8
125°	1200.4	1200.1	1199.7	1199.4	1199.1	1198.4	1197.4	1196.4	1195.4	1194.4	1195.0
127.5°	1289.4	1289.6	1289.9	1290.2	1290.4	1290.7	1290.9	1291.1	1291.3	1291.5	1289.9
130°	1349.7	1349.7	1349.7	1349.7	1349.7	1349.5	1349.2	1348.9	1348.5	1348.2	1347.2
132.5°	1405.2	1405.5	1405.7	1406.0	1406.3	1406.2	1405.9	1405.6	1405.2	1404.9	1403.6
135°	1488.4	1487.8	1487.1	1486.4	1485.8	1485.1	1484.4	1483.7	1483.1	1482.4	1481.1
137.5°	1559.6	1559.8	1560.0	1560.2	1560.4	1560.2	1559.4	1558.7	1557.9	1557.2	1555.7
140°	1609.1	1608.7	1608.4	1608.1	1607.7	1607.1	1606.1	1605.1	1604.1	1603.0	1602.4
142.5°	1650.1	1650.0	1650.0	1649.9	1649.8	1649.4	1648.7	1648.0	1647.2	1646.5	1646.1
145°	1713.1	1712.5	1711.8	1711.1	1710.5	1709.9	1709.6	1709.3	1708.9	1708.6	1708.6
147.5°	1765.3	1765.0	1764.6	1764.3	1764.0	1763.7	1763.4	1763.1	1762.9	1762.6	1762.9
150°	1799.1	1798.8	1798.4	1798.1	1797.8	1797.6	1797.6	1797.6	1797.6	1797.6	1797.9
152.5°	1828.0	1828.2	1828.4	1828.6	1828.8	1828.7	1828.1	1827.6	1827.1	1826.5	1827.1
155°	1867.0	1868.0	1869.0	1870.0	1871.0	1870.8	1869.5	1868.1	1866.8	1865.4	1866.5
157.5°	1899.5	1901.3	1903.0	1904.8	1906.5	1906.5	1904.8	1903.0	1901.3	1899.5	1900.7
160°	1921.2	1923.3	1925.3	1927.3	1929.3	1929.3	1927.3	1925.3	1923.3	1921.2	1921.6
162.5°	1938.1	1940.4	1942.7	1945.0	1947.2	1947.4	1945.4	1943.4	1941.3	1939.3	1939.7
165°	1962.0	1965.0	1968.0	1971.0	1974.0	1974.2	1971.5	1968.8	1966.1	1963.5	1963.5
167.5°	1979.8	1983.1	1986.5	1989.8	1993.2	1993.4	1990.4	1987.5	1984.5	1981.6	1981.8
170°	1990.6	1994.0	1997.3	2000.7	2004.0	2004.4	2001.7	1999.0	1996.3	1993.6	1993.3
172.5°	1996.6	2000.3	2003.9	2007.5	2011.1	2011.6	2008.9	2006.2	2003.5	2000.9	2000.5
175°	2004.2	2008.2	2012.2	2016.2	2020.3	2020.8	2017.8	2014.7	2011.7	2008.7	2008.4
177.5°	2009.0	2012.2	2015.4	2018.7	2021.9	2022.4	2020.3	2018.1	2016.0	2013.8	2013.3
180°	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2



TEST NUMBER: P332769

CATALOG NUMBER: S124DIW-S575D1560U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	939.2	939.2	939.2	939.2	939.2	939.2	939.2	939.2	939.2	939.2	939.2
2.5°	969.4	965.1	962.0	959.5	952.6	948.6	945.5	941.1	936.1	930.8	924.3
5°	1024.5	1011.2	1001.5	986.7	972.7	961.0	949.0	938.1	924.8	910.5	899.9
7.5°	1082.3	1062.6	1037.4	1015.5	990.9	969.5	950.4	930.8	910.4	890.6	872.5
10°	1119.0	1093.7	1065.7	1032.6	1001.5	973.9	948.2	923.3	899.2	875.0	854.4
12.5°	1158.5	1127.0	1085.6	1046.9	1012.1	975.1	944.1	913.6	884.5	859.2	835.1
15°	1211.6	1166.1	1118.2	1066.5	1020.6	977.4	935.0	896.4	863.8	830.3	807.0
17.5°	1244.2	1187.9	1133.2	1079.1	1023.5	969.0	923.3	878.9	837.9	804.7	775.3
20°	1265.7	1209.7	1141.6	1087.5	1021.3	965.3	912.4	863.0	820.2	784.8	754.4
22.5°	1284.4	1219.6	1151.5	1080.3	1014.5	955.0	897.1	847.4	803.7	766.4	737.3
25°	1294.5	1220.2	1146.2	1075.4	1000.7	930.3	877.8	819.4	772.7	733.4	702.3
27.5°	1295.6	1216.1	1132.5	1053.8	976.7	911.1	844.8	792.6	744.2	702.6	672.7
30°	1292.1	1209.3	1119.4	1034.2	956.8	885.5	828.0	771.2	721.7	680.5	649.4
32.5°	1281.2	1194.9	1102.6	1012.4	932.2	862.5	803.1	749.1	700.9	660.3	627.6
35°	1249.7	1164.5	1066.1	972.3	890.2	819.8	766.1	711.2	663.0	624.5	593.0
37.5°	1200.5	1123.4	1023.4	926.3	845.7	775.0	721.7	672.2	628.7	589.5	557.2
40°	1157.5	1089.8	989.4	894.9	807.7	740.4	690.6	645.1	601.9	564.9	534.2
42.5°	1108.0	1049.0	956.4	856.3	772.2	704.6	656.1	615.2	574.5	540.4	509.6
45°	1019.8	980.9	893.7	801.1	713.6	649.8	603.5	567.7	533.4	500.0	474.3
47.5°	918.3	899.0	825.6	737.7	654.6	591.7	551.6	518.5	488.5	460.1	437.5
50°	850.1	840.8	777.4	692.6	613.2	554.1	513.6	485.2	459.5	434.6	413.2
52.5°	782.9	782.6	725.4	647.7	574.3	517.3	477.2	450.6	428.4	408.1	388.9
55°	680.1	691.0	646.3	577.0	511.3	459.9	423.7	400.0	384.4	367.7	353.3
57.5°	585.7	603.8	566.9	505.9	451.0	403.7	372.2	354.4	337.8	327.7	317.2
60°	524.1	541.2	512.4	461.1	409.3	368.8	338.9	322.9	308.5	301.5	294.1
62.5°	469.3	484.6	463.2	415.6	370.7	331.8	306.5	291.2	281.5	273.8	268.9
65°	391.0	403.9	385.6	351.0	312.4	281.3	260.7	248.6	239.3	236.2	230.7
67.5°	316.1	327.8	317.9	288.5	257.6	234.0	217.9	206.3	200.8	198.0	194.2
70°	271.6	283.3	272.7	247.1	223.3	203.5	188.3	181.7	175.9	174.7	169.3
72.5°	233.9	241.9	231.3	211.3	191.0	174.2	162.5	155.6	152.5	150.4	147.5
75°	175.5	182.5	175.5	159.9	145.5	133.8	123.7	121.0	117.5	116.3	114.4
77.5°	124.2	130.3	124.9	115.2	104.4	95.4	90.0	86.5	85.7	83.7	84.6
80°	94.9	98.8	93.8	87.2	78.6	72.4	68.5	66.5	64.2	63.4	65.0
82.5°	68.2	69.9	67.3	62.9	56.5	52.4	49.8	47.5	47.1	47.2	47.2
85°	35.4	35.0	34.6	30.7	28.8	26.1	24.5	24.1	23.7	24.5	25.3
87.5°	17.4	17.2	16.3	14.4	12.8	11.1	10.0	9.0	10.0	11.1	12.1
90°	27.8	25.1	22.5	19.3	15.6	11.9	8.2	4.5	8.2	11.9	15.6
92.5°	26.6	23.9	21.2	19.8	19.6	19.4	19.2	19.0	19.2	19.4	19.6
95°	32.5	32.2	31.8	37.4	48.8	60.2	71.5	82.9	71.5	60.2	48.8
97.5°	114.6	152.0	189.4	204.6	197.5	190.3	183.2	176.1	183.2	190.3	197.5
100°	158.8	205.1	251.3	271.4	265.4	259.4	253.4	247.3	253.4	259.4	265.4
102.5°	331.8	337.8	343.8	344.6	340.2	335.8	331.4	326.9	331.4	335.8	340.2
105°	467.2	465.5	463.8	462.0	460.0	457.9	455.9	453.9	455.9	457.9	460.0
107.5°	582.1	579.8	577.5	575.9	574.9	573.9	572.9	571.8	572.9	573.9	574.9
110°	661.0	659.0	657.0	655.5	654.5	653.5	652.5	651.5	652.5	653.5	654.5





TEST NUMBER: P332769

CATALOG NUMBER: S124DIW-S575D1560U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	739.2	738.2	737.3	735.9	734.1	732.3	730.5	728.7	730.5	732.3	734.1
115°	851.2	851.5	851.9	851.5	850.5	849.5	848.5	847.5	848.5	849.5	850.5
117.5°	962.5	961.7	961.0	960.0	958.6	957.3	955.9	954.6	955.9	957.3	958.6
120°	1032.2	1032.5	1032.8	1032.3	1031.0	1029.7	1028.3	1027.0	1028.3	1029.7	1031.0
122.5°	1099.3	1098.9	1098.4	1097.8	1096.9	1096.1	1095.3	1094.5	1095.3	1096.1	1096.9
125°	1195.7	1196.4	1197.0	1196.7	1195.4	1194.0	1192.7	1191.4	1192.7	1194.0	1195.4
127.5°	1288.4	1286.9	1285.3	1284.4	1284.0	1283.7	1283.4	1283.0	1283.4	1283.7	1284.0
130°	1346.2	1345.2	1344.2	1343.5	1343.2	1342.8	1342.5	1342.2	1342.5	1342.8	1343.2
132.5°	1402.3	1401.1	1399.8	1398.9	1398.3	1397.7	1397.0	1396.4	1397.0	1397.7	1398.3
135°	1479.7	1478.4	1477.0	1476.5	1476.9	1477.2	1477.5	1477.9	1477.5	1477.2	1476.9
137.5°	1554.3	1552.8	1551.3	1550.5	1550.4	1550.2	1550.1	1550.0	1550.1	1550.2	1550.4
140°	1601.7	1601.0	1600.4	1599.7	1599.0	1598.4	1597.7	1597.0	1597.7	1598.4	1599.0
142.5°	1645.7	1645.3	1644.9	1644.1	1642.9	1641.7	1640.4	1639.2	1640.4	1641.7	1642.9
145°	1708.6	1708.6	1708.6	1708.1	1707.1	1706.1	1705.1	1704.1	1705.1	1706.1	1707.1
147.5°	1763.3	1763.6	1763.9	1763.2	1761.3	1759.4	1757.5	1755.7	1757.5	1759.4	1761.3
150°	1798.3	1798.6	1798.9	1798.4	1797.1	1795.7	1794.4	1793.1	1794.4	1795.7	1797.1
152.5°	1827.7	1828.3	1829.0	1828.7	1827.6	1826.6	1825.5	1824.4	1825.5	1826.6	1827.6
155°	1867.5	1868.5	1869.5	1869.8	1869.5	1869.1	1868.8	1868.5	1868.8	1869.1	1869.5
157.5°	1901.8	1902.9	1904.1	1904.8	1905.0	1905.2	1905.4	1905.6	1905.4	1905.2	1905.0
160°	1921.9	1922.2	1922.6	1923.3	1924.3	1925.3	1926.3	1927.3	1926.3	1925.3	1924.3
162.5°	1940.0	1940.3	1940.7	1941.5	1942.8	1944.0	1945.3	1946.6	1945.3	1944.0	1942.8
165°	1963.5	1963.5	1963.5	1964.3	1966.0	1967.7	1969.3	1971.0	1969.3	1967.7	1966.0
167.5°	1982.0	1982.2	1982.4	1983.3	1985.1	1986.8	1988.6	1990.3	1988.6	1986.8	1985.1
170°	1993.0	1992.6	1992.3	1993.1	1995.1	1997.1	1999.2	2001.2	1999.2	1997.1	1995.1
172.5°	2000.2	1999.9	1999.5	2000.4	2002.4	2004.4	2006.4	2008.4	2006.4	2004.4	2002.4
175°	2008.0	2007.7	2007.4	2008.2	2010.2	2012.2	2014.2	2016.2	2014.2	2012.2	2010.2
177.5°	2012.8	2012.2	2011.7	2012.4	2014.2	2016.1	2018.0	2019.9	2018.0	2016.1	2014.2
180°	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2



TEST NUMBER: P332769

CATALOG NUMBER: S124DIW-S575D1560U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	939.2	939.2	939.2	939.2	939.2	939.2	939.2	939.2	939.2	939.2	939.2
2.5°	921.2	918.4	914.3	908.7	904.1	899.1	897.8	896.0	899.7	896.6	895.7
5°	891.0	882.8	872.3	860.3	853.3	843.1	841.2	837.3	833.4	833.0	829.1
7.5°	859.0	847.0	833.3	821.0	809.6	798.6	791.3	789.8	784.0	780.7	776.8
10°	838.5	823.7	807.7	796.1	782.8	771.2	763.0	758.3	754.4	750.1	746.3
12.5°	814.2	798.5	785.3	772.7	757.0	748.1	734.7	726.6	725.8	725.9	715.8
15°	785.9	770.4	750.1	732.3	723.7	706.6	699.2	689.8	684.0	678.2	673.5
17.5°	753.7	734.3	718.5	697.9	681.6	668.0	658.2	652.6	643.9	635.6	629.6
20°	733.4	712.8	696.1	674.3	656.4	639.7	631.5	623.7	617.1	610.1	603.5
22.5°	712.9	691.3	670.9	649.7	633.0	615.4	607.5	596.9	590.6	586.7	580.1
25°	680.5	657.2	633.8	613.6	596.5	580.9	570.4	562.2	555.2	552.1	547.8
27.5°	645.3	622.1	599.6	576.6	557.2	545.9	537.5	531.3	527.3	523.2	521.2
30°	622.9	598.8	574.7	553.3	535.4	524.1	516.3	512.0	508.9	507.0	505.0
32.5°	600.2	576.4	551.0	531.5	515.5	505.4	499.5	495.2	493.7	493.0	492.3
35°	563.8	539.7	516.3	498.8	483.6	479.7	474.7	472.3	471.6	474.3	475.5
37.5°	528.5	506.1	484.6	467.7	457.7	452.0	450.3	450.4	453.2	455.6	458.4
40°	505.8	484.0	463.8	449.0	439.7	436.2	435.4	437.3	440.4	443.2	446.3
42.5°	483.7	462.2	443.9	430.0	423.5	420.3	420.8	422.7	427.1	430.4	435.1
45°	449.4	431.5	413.6	402.3	396.9	397.6	397.6	401.1	405.4	410.5	415.5
47.5°	417.1	399.0	384.3	374.8	372.0	371.3	373.5	378.1	384.3	390.5	397.6
50°	395.3	378.2	365.3	356.8	353.7	354.8	358.0	362.2	369.6	377.4	384.8
52.5°	373.2	357.6	345.7	337.8	335.6	337.7	340.8	347.6	354.1	362.5	371.4
55°	338.9	325.7	316.3	310.5	309.7	310.9	314.4	321.8	331.1	341.6	350.2
57.5°	304.7	293.7	285.1	281.1	281.5	282.6	288.3	297.1	307.1	318.3	329.3
60°	281.7	271.6	264.6	261.5	261.9	264.2	271.2	279.4	291.8	302.7	314.4
62.5°	259.9	251.0	244.3	241.5	241.0	246.1	252.8	261.3	273.8	285.9	298.5
65°	224.9	217.9	212.4	210.9	212.0	215.9	224.5	235.8	246.3	259.1	272.4
67.5°	190.6	184.9	181.2	181.9	183.3	189.0	196.2	205.9	217.8	231.1	244.2
70°	168.9	163.4	160.3	160.7	163.0	170.0	176.3	186.0	198.8	212.4	223.3
72.5°	146.5	142.9	140.1	141.7	144.0	148.9	156.6	166.4	177.7	190.3	201.9
75°	112.4	112.4	110.9	112.1	115.6	120.2	126.1	136.2	147.5	157.6	166.9
77.5°	83.4	82.6	83.6	85.0	87.0	92.5	99.2	106.5	114.9	125.1	132.8
80°	63.8	64.2	66.1	68.5	69.3	73.5	80.5	87.2	93.8	102.3	109.7
82.5°	47.9	48.3	49.3	52.3	53.1	57.7	62.2	68.8	74.8	80.5	86.7
85°	26.1	26.1	28.0	29.2	31.1	34.2	37.0	40.9	46.3	50.2	56.0
87.5°	13.8	14.5	16.2	17.4	18.9	21.0	22.0	25.8	27.5	29.4	32.5
90°	19.3	22.5	25.1	27.8	30.5	33.2	35.2	37.2	39.2	41.2	42.6
92.5°	19.8	21.2	23.9	26.6	29.3	32.0	34.0	36.0	38.0	40.0	41.1
95°	37.4	31.8	32.2	32.5	32.8	33.2	35.2	37.2	39.2	41.2	42.4
97.5°	204.6	189.4	152.0	114.6	77.2	39.8	40.0	40.2	40.4	40.6	40.9
100°	271.4	251.3	205.1	158.8	112.6	66.4	60.7	55.0	49.3	43.6	40.9
102.5°	344.6	343.8	337.8	331.8	325.7	319.7	258.2	196.8	135.3	73.9	43.2
105°	462.0	463.8	465.5	467.2	468.8	470.5	473.5	476.5	479.6	482.6	478.0
107.5°	575.9	577.5	579.8	582.1	584.3	586.6	588.1	589.6	591.1	592.5	593.9
110°	655.5	657.0	659.0	661.0	663.0	665.0	665.7	666.4	667.1	667.7	668.6



TEST NUMBER: P332769

CATALOG NUMBER: S124DIW-S575D1560U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	735.9	737.3	738.2	739.2	740.1	741.1	740.9	740.8	740.6	740.5	741.1
115°	851.5	851.9	851.5	851.2	850.9	850.5	851.2	851.9	852.5	853.2	853.6
117.5°	960.0	961.0	961.7	962.5	963.2	963.9	963.8	963.7	963.5	963.4	963.3
120°	1032.3	1032.8	1032.5	1032.2	1031.8	1031.5	1032.2	1032.8	1033.5	1034.2	1034.2
122.5°	1097.8	1098.4	1098.9	1099.3	1099.8	1100.3	1100.7	1101.1	1101.5	1101.9	1101.7
125°	1196.7	1197.0	1196.4	1195.7	1195.0	1194.4	1195.4	1196.4	1197.4	1198.4	1199.1
127.5°	1284.4	1285.3	1286.9	1288.4	1289.9	1291.5	1291.3	1291.1	1290.9	1290.7	1290.4
130°	1343.5	1344.2	1345.2	1346.2	1347.2	1348.2	1348.5	1348.9	1349.2	1349.5	1349.7
132.5°	1398.9	1399.8	1401.1	1402.3	1403.6	1404.9	1405.2	1405.6	1405.9	1406.2	1406.3
135°	1476.5	1477.0	1478.4	1479.7	1481.1	1482.4	1483.1	1483.7	1484.4	1485.1	1485.8
137.5°	1550.5	1551.3	1552.8	1554.3	1555.7	1557.2	1557.9	1558.7	1559.4	1560.2	1560.4
140°	1599.7	1600.4	1601.0	1601.7	1602.4	1603.0	1604.1	1605.1	1606.1	1607.1	1607.7
142.5°	1644.1	1644.9	1645.3	1645.7	1646.1	1646.5	1647.2	1648.0	1648.7	1649.4	1649.8
145°	1708.1	1708.6	1708.6	1708.6	1708.6	1708.6	1708.9	1709.3	1709.6	1709.9	1710.5
147.5°	1763.2	1763.9	1763.6	1763.3	1762.9	1762.6	1762.9	1763.1	1763.4	1763.7	1764.0
150°	1798.4	1798.9	1798.6	1798.3	1797.9	1797.6	1797.6	1797.6	1797.6	1797.6	1797.8
152.5°	1828.7	1829.0	1828.3	1827.7	1827.1	1826.5	1827.1	1827.6	1828.1	1828.7	1828.8
155°	1869.8	1869.5	1868.5	1867.5	1866.5	1865.4	1866.8	1868.1	1869.5	1870.8	1871.0
157.5°	1904.8	1904.1	1902.9	1901.8	1900.7	1899.5	1901.3	1903.0	1904.8	1906.5	1906.5
160°	1923.3	1922.6	1922.2	1921.9	1921.6	1921.2	1923.3	1925.3	1927.3	1929.3	1929.3
162.5°	1941.5	1940.7	1940.3	1940.0	1939.7	1939.3	1941.3	1943.4	1945.4	1947.4	1947.2
165°	1964.3	1963.5	1963.5	1963.5	1963.5	1963.5	1966.1	1968.8	1971.5	1974.2	1974.0
167.5°	1983.3	1982.4	1982.2	1982.0	1981.8	1981.6	1984.5	1987.5	1990.4	1993.4	1993.2
170°	1993.1	1992.3	1992.6	1993.0	1993.3	1993.6	1996.3	1999.0	2001.7	2004.4	2004.0
172.5°	2000.4	1999.5	1999.9	2000.2	2000.5	2000.9	2003.5	2006.2	2008.9	2011.6	2011.1
175°	2008.2	2007.4	2007.7	2008.0	2008.4	2008.7	2011.7	2014.7	2017.8	2020.8	2020.3
177.5°	2012.4	2011.7	2012.2	2012.8	2013.3	2013.8	2016.0	2018.1	2020.3	2022.4	2021.9
180°	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2



TEST NUMBER: P332769

CATALOG NUMBER: S124DIW-S575D1560U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	939.2	939.2	939.2	939.2	939.2	939.2	939.2	939.2	939.2	939.2	939.2
2.5°	895.0	894.4	892.2	891.9	892.2	894.4	895.0	895.7	896.6	899.7	896.0
5°	826.8	824.9	823.7	828.0	823.7	824.9	826.8	829.1	833.0	833.4	837.3
7.5°	775.4	773.8	770.4	769.3	770.4	773.8	775.4	776.8	780.7	784.0	789.8
10°	742.4	740.8	737.7	736.9	737.7	740.8	742.4	746.3	750.1	754.4	758.3
12.5°	710.6	707.5	706.9	707.7	706.9	707.5	710.6	715.8	725.9	725.8	726.6
15°	668.4	666.9	662.6	663.8	662.6	666.9	668.4	673.5	678.2	684.0	689.8
17.5°	626.9	625.0	619.8	624.4	619.8	625.0	626.9	629.6	635.6	643.9	652.6
20°	600.7	597.6	594.9	594.5	594.9	597.6	600.7	603.5	610.1	617.1	623.7
22.5°	575.8	573.0	572.8	570.2	572.8	573.0	575.8	580.1	586.7	590.6	596.9
25°	544.7	542.0	541.2	539.3	541.2	542.0	544.7	547.8	552.1	555.2	562.2
27.5°	520.8	519.5	518.1	518.7	518.1	519.5	520.8	521.2	523.2	527.3	531.3
30°	506.2	505.8	505.0	505.0	505.0	505.8	506.2	505.0	507.0	508.9	512.0
32.5°	494.1	494.0	494.4	494.4	494.4	494.0	494.1	492.3	493.0	493.7	495.2
35°	477.0	478.2	479.0	477.8	479.0	478.2	477.0	475.5	474.3	471.6	472.3
37.5°	461.6	462.8	463.9	465.2	463.9	462.8	461.6	458.4	455.6	453.2	450.4
40°	449.8	452.5	453.3	455.2	453.3	452.5	449.8	446.3	443.2	440.4	437.3
42.5°	438.6	441.6	443.6	444.0	443.6	441.6	438.6	435.1	430.4	427.1	422.7
45°	421.4	424.5	427.2	427.2	427.2	424.5	421.4	415.5	410.5	405.4	401.1
47.5°	403.6	408.1	410.8	411.5	410.8	408.1	403.6	397.6	390.5	384.3	378.1
50°	391.4	396.9	399.6	401.5	399.6	396.9	391.4	384.8	377.4	369.6	362.2
52.5°	379.6	385.0	388.7	389.7	388.7	385.0	379.6	371.4	362.5	354.1	347.6
55°	359.1	366.9	371.2	372.7	371.2	366.9	359.1	350.2	341.6	331.1	321.8
57.5°	339.8	347.0	352.0	353.1	352.0	347.0	339.8	329.3	318.3	307.1	297.1
60°	324.9	332.7	338.9	340.1	338.9	332.7	324.9	314.4	302.7	291.8	279.4
62.5°	309.6	317.7	323.3	326.4	323.3	317.7	309.6	298.5	285.9	273.8	261.3
65°	283.3	291.4	296.9	298.0	296.9	291.4	283.3	272.4	259.1	246.3	235.8
67.5°	254.5	262.6	266.2	268.5	266.2	262.6	254.5	244.2	231.1	217.8	205.9
70°	234.2	240.8	244.7	246.7	244.7	240.8	234.2	223.3	212.4	198.8	186.0
72.5°	211.2	218.1	222.6	223.0	222.6	218.1	211.2	201.9	190.3	177.7	166.4
75°	175.9	182.1	184.4	184.4	184.4	182.1	175.9	166.9	157.6	147.5	136.2
77.5°	139.2	142.4	145.4	146.0	145.4	142.4	139.2	132.8	125.1	114.9	106.5
80°	115.6	117.5	119.8	119.8	119.8	117.5	115.6	109.7	102.3	93.8	87.2
82.5°	91.3	92.9	95.2	94.9	95.2	92.9	91.3	86.7	80.5	74.8	68.8
85°	55.2	58.8	58.4	57.6	58.4	58.8	55.2	56.0	50.2	46.3	40.9
87.5°	33.5	34.0	35.1	35.8	35.1	34.0	33.5	32.5	29.4	27.5	25.8
90°	43.2	43.9	44.6	45.2	44.6	43.9	43.2	42.6	41.2	39.2	37.2
92.5°	41.2	41.4	41.5	41.6	41.5	41.4	41.2	41.1	40.0	38.0	36.0
95°	42.7	43.1	43.4	43.7	43.4	43.1	42.7	42.4	41.2	39.2	37.2
97.5°	41.2	41.6	41.9	42.2	41.9	41.6	41.2	40.9	40.6	40.4	40.2
100°	41.2	41.6	41.9	42.2	41.9	41.6	41.2	40.9	43.6	49.3	55.0
102.5°	43.2	43.3	43.4	43.4	43.4	43.3	43.2	43.2	73.9	135.3	196.8
105°	466.0	453.9	441.9	429.8	441.9	453.9	466.0	478.0	482.6	479.6	476.5
107.5°	595.2	596.4	597.7	599.0	597.7	596.4	595.2	593.9	592.5	591.1	589.6
110°	669.6	670.6	671.6	672.6	671.6	670.6	669.6	668.6	667.7	667.1	666.4



TEST NUMBER: P332769

CATALOG NUMBER: S124DIW-S575D1560U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	742.4	743.6	744.9	746.2	744.9	743.6	742.4	741.1	740.5	740.6	740.8
115°	853.6	853.6	853.6	853.6	853.6	853.6	853.6	853.6	853.2	852.5	851.9
117.5°	963.1	963.0	962.9	962.7	962.9	963.0	963.1	963.3	963.4	963.5	963.7
120°	1033.5	1032.8	1032.2	1031.5	1032.2	1032.8	1033.5	1034.2	1034.2	1033.5	1032.8
122.5°	1101.1	1100.4	1099.7	1099.1	1099.7	1100.4	1101.1	1101.7	1101.9	1101.5	1101.1
125°	1199.4	1199.7	1200.1	1200.4	1200.1	1199.7	1199.4	1199.1	1198.4	1197.4	1196.4
127.5°	1290.2	1289.9	1289.6	1289.4	1289.6	1289.9	1290.2	1290.4	1290.7	1290.9	1291.1
130°	1349.7	1349.7	1349.7	1349.7	1349.7	1349.7	1349.7	1349.7	1349.5	1349.2	1348.9
132.5°	1406.0	1405.7	1405.5	1405.2	1405.5	1405.7	1406.0	1406.3	1406.2	1405.9	1405.6
135°	1486.4	1487.1	1487.8	1488.4	1487.8	1487.1	1486.4	1485.8	1485.1	1484.4	1483.7
137.5°	1560.2	1560.0	1559.8	1559.6	1559.8	1560.0	1560.2	1560.4	1560.2	1559.4	1558.7
140°	1608.1	1608.4	1608.7	1609.1	1608.7	1608.4	1608.1	1607.7	1607.1	1606.1	1605.1
142.5°	1649.9	1650.0	1650.0	1650.1	1650.0	1650.0	1649.9	1649.8	1649.4	1648.7	1648.0
145°	1711.1	1711.8	1712.5	1713.1	1712.5	1711.8	1711.1	1710.5	1709.9	1709.6	1709.3
147.5°	1764.3	1764.6	1765.0	1765.3	1765.0	1764.6	1764.3	1764.0	1763.7	1763.4	1763.1
150°	1798.1	1798.4	1798.8	1799.1	1798.8	1798.4	1798.1	1797.8	1797.6	1797.6	1797.6
152.5°	1828.6	1828.4	1828.2	1828.0	1828.2	1828.4	1828.6	1828.8	1828.7	1828.1	1827.6
155°	1870.0	1869.0	1868.0	1867.0	1868.0	1869.0	1870.0	1871.0	1870.8	1869.5	1868.1
157.5°	1904.8	1903.0	1901.3	1899.5	1901.3	1903.0	1904.8	1906.5	1906.5	1904.8	1903.0
160°	1927.3	1925.3	1923.3	1921.2	1923.3	1925.3	1927.3	1929.3	1929.3	1927.3	1925.3
162.5°	1945.0	1942.7	1940.4	1938.1	1940.4	1942.7	1945.0	1947.2	1947.4	1945.4	1943.4
165°	1971.0	1968.0	1965.0	1962.0	1965.0	1968.0	1971.0	1974.0	1974.2	1971.5	1968.8
167.5°	1989.8	1986.5	1983.1	1979.8	1983.1	1986.5	1989.8	1993.2	1993.4	1990.4	1987.5
170°	2000.7	1997.3	1994.0	1990.6	1994.0	1997.3	2000.7	2004.0	2004.4	2001.7	1999.0
172.5°	2007.5	2003.9	2000.3	1996.6	2000.3	2003.9	2007.5	2011.1	2011.6	2008.9	2006.2
175°	2016.2	2012.2	2008.2	2004.2	2008.2	2012.2	2016.2	2020.3	2020.8	2017.8	2014.7
177.5°	2018.7	2015.4	2012.2	2009.0	2012.2	2015.4	2018.7	2021.9	2022.4	2020.3	2018.1
180°	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2



TEST NUMBER: P332769

CATALOG NUMBER: S124DIW-S575D1560U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	939.2	939.2	939.2	939.2	939.2	939.2	939.2	939.2	939.2	939.2	939.2
2.5°	897.8	899.1	904.1	908.7	914.3	918.4	921.2	924.3	930.8	936.1	941.1
5°	841.2	843.1	853.3	860.3	872.3	882.8	891.0	899.9	910.5	924.8	938.1
7.5°	791.3	798.6	809.6	821.0	833.3	847.0	859.0	872.5	890.6	910.4	930.8
10°	763.0	771.2	782.8	796.1	807.7	823.7	838.5	854.4	875.0	899.2	923.3
12.5°	734.7	748.1	757.0	772.7	785.3	798.5	814.2	835.1	859.2	884.5	913.6
15°	699.2	706.6	723.7	732.3	750.1	770.4	785.9	807.0	830.3	863.8	896.4
17.5°	658.2	668.0	681.6	697.9	718.5	734.3	753.7	775.3	804.7	837.9	878.9
20°	631.5	639.7	656.4	674.3	696.1	712.8	733.4	754.4	784.8	820.2	863.0
22.5°	607.5	615.4	633.0	649.7	670.9	691.3	712.9	737.3	766.4	803.7	847.4
25°	570.4	580.9	596.5	613.6	633.8	657.2	680.5	702.3	733.4	772.7	819.4
27.5°	537.5	545.9	557.2	576.6	599.6	622.1	645.3	672.7	702.6	744.2	792.6
30°	516.3	524.1	535.4	553.3	574.7	598.8	622.9	649.4	680.5	721.7	771.2
32.5°	499.5	505.4	515.5	531.5	551.0	576.4	600.2	627.6	660.3	700.9	749.1
35°	474.7	479.7	483.6	498.8	516.3	539.7	563.8	593.0	624.5	663.0	711.2
37.5°	450.3	452.0	457.7	467.7	484.6	506.1	528.5	557.2	589.5	628.7	672.2
40°	435.4	436.2	439.7	449.0	463.8	484.0	505.8	534.2	564.9	601.9	645.1
42.5°	420.8	420.3	423.5	430.0	443.9	462.2	483.7	509.6	540.4	574.5	615.2
45°	397.6	397.6	396.9	402.3	413.6	431.5	449.4	474.3	500.0	533.4	567.7
47.5°	373.5	371.3	372.0	374.8	384.3	399.0	417.1	437.5	460.1	488.5	518.5
50°	358.0	354.8	353.7	356.8	365.3	378.2	395.3	413.2	434.6	459.5	485.2
52.5°	340.8	337.7	335.6	337.8	345.7	357.6	373.2	388.9	408.1	428.4	450.6
55°	314.4	310.9	309.7	310.5	316.3	325.7	338.9	353.3	367.7	384.4	400.0
57.5°	288.3	282.6	281.5	281.1	285.1	293.7	304.7	317.2	327.7	337.8	354.4
60°	271.2	264.2	261.9	261.5	264.6	271.6	281.7	294.1	301.5	308.5	322.9
62.5°	252.8	246.1	241.0	241.5	244.3	251.0	259.9	268.9	273.8	281.5	291.2
65°	224.5	215.9	212.0	210.9	212.4	217.9	224.9	230.7	236.2	239.3	248.6
67.5°	196.2	189.0	183.3	181.9	181.2	184.9	190.6	194.2	198.0	200.8	206.3
70°	176.3	170.0	163.0	160.7	160.3	163.4	168.9	169.3	174.7	175.9	181.7
72.5°	156.6	148.9	144.0	141.7	140.1	142.9	146.5	147.5	150.4	152.5	155.6
75°	126.1	120.2	115.6	112.1	110.9	112.4	112.4	114.4	116.3	117.5	121.0
77.5°	99.2	92.5	87.0	85.0	83.6	82.6	83.4	84.6	83.7	85.7	86.5
80°	80.5	73.5	69.3	68.5	66.1	64.2	63.8	65.0	63.4	64.2	66.5
82.5°	62.2	57.7	53.1	52.3	49.3	48.3	47.9	47.2	47.2	47.1	47.5
85°	37.0	34.2	31.1	29.2	28.0	26.1	26.1	25.3	24.5	23.7	24.1
87.5°	22.0	21.0	18.9	17.4	16.2	14.5	13.8	12.1	11.1	10.0	9.0
90°	35.2	33.2	30.5	27.8	25.1	22.5	19.3	15.6	11.9	8.2	4.5
92.5°	34.0	32.0	29.3	26.6	23.9	21.2	19.8	19.6	19.4	19.2	19.0
95°	35.2	33.2	32.8	32.5	32.2	31.8	37.4	48.8	60.2	71.5	82.9
97.5°	40.0	39.8	77.2	114.6	152.0	189.4	204.6	197.5	190.3	183.2	176.1
100°	60.7	66.4	112.6	158.8	205.1	251.3	271.4	265.4	259.4	253.4	247.3
102.5°	258.2	319.7	325.7	331.8	337.8	343.8	344.6	340.2	335.8	331.4	326.9
105°	473.5	470.5	468.8	467.2	465.5	463.8	462.0	460.0	457.9	455.9	453.9
107.5°	588.1	586.6	584.3	582.1	579.8	577.5	575.9	574.9	573.9	572.9	571.8
110°	665.7	665.0	663.0	661.0	659.0	657.0	655.5	654.5	653.5	652.5	651.5



TEST NUMBER: P332769

CATALOG NUMBER: S124DIW-S575D1560U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	740.9	741.1	740.1	739.2	738.2	737.3	735.9	734.1	732.3	730.5	728.7
115°	851.2	850.5	850.9	851.2	851.5	851.9	851.5	850.5	849.5	848.5	847.5
117.5°	963.8	963.9	963.2	962.5	961.7	961.0	960.0	958.6	957.3	955.9	954.6
120°	1032.2	1031.5	1031.8	1032.2	1032.5	1032.8	1032.3	1031.0	1029.7	1028.3	1027.0
122.5°	1100.7	1100.3	1099.8	1099.3	1098.9	1098.4	1097.8	1096.9	1096.1	1095.3	1094.5
125°	1195.4	1194.4	1195.0	1195.7	1196.4	1197.0	1196.7	1195.4	1194.0	1192.7	1191.4
127.5°	1291.3	1291.5	1289.9	1288.4	1286.9	1285.3	1284.4	1284.0	1283.7	1283.4	1283.0
130°	1348.5	1348.2	1347.2	1346.2	1345.2	1344.2	1343.5	1343.2	1342.8	1342.5	1342.2
132.5°	1405.2	1404.9	1403.6	1402.3	1401.1	1399.8	1398.9	1398.3	1397.7	1397.0	1396.4
135°	1483.1	1482.4	1481.1	1479.7	1478.4	1477.0	1476.5	1476.9	1477.2	1477.5	1477.9
137.5°	1557.9	1557.2	1555.7	1554.3	1552.8	1551.3	1550.5	1550.4	1550.2	1550.1	1550.0
140°	1604.1	1603.0	1602.4	1601.7	1601.0	1600.4	1599.7	1599.0	1598.4	1597.7	1597.0
142.5°	1647.2	1646.5	1646.1	1645.7	1645.3	1644.9	1644.1	1642.9	1641.7	1640.4	1639.2
145°	1708.9	1708.6	1708.6	1708.6	1708.6	1708.6	1708.1	1707.1	1706.1	1705.1	1704.1
147.5°	1762.9	1762.6	1762.9	1763.3	1763.6	1763.9	1763.2	1761.3	1759.4	1757.5	1755.7
150°	1797.6	1797.6	1797.9	1798.3	1798.6	1798.9	1798.4	1797.1	1795.7	1794.4	1793.1
152.5°	1827.1	1826.5	1827.1	1827.7	1828.3	1829.0	1828.7	1827.6	1826.6	1825.5	1824.4
155°	1866.8	1865.4	1866.5	1867.5	1868.5	1869.5	1869.8	1869.5	1869.1	1868.8	1868.5
157.5°	1901.3	1899.5	1900.7	1901.8	1902.9	1904.1	1904.8	1905.0	1905.2	1905.4	1905.6
160°	1923.3	1921.2	1921.6	1921.9	1922.2	1922.6	1923.3	1924.3	1925.3	1926.3	1927.3
162.5°	1941.3	1939.3	1939.7	1940.0	1940.3	1940.7	1941.5	1942.8	1944.0	1945.3	1946.6
165°	1966.1	1963.5	1963.5	1963.5	1963.5	1963.5	1964.3	1966.0	1967.7	1969.3	1971.0
167.5°	1984.5	1981.6	1981.8	1982.0	1982.2	1982.4	1983.3	1985.1	1986.8	1988.6	1990.3
170°	1996.3	1993.6	1993.3	1993.0	1992.6	1992.3	1993.1	1995.1	1997.1	1999.2	2001.2
172.5°	2003.5	2000.9	2000.5	2000.2	1999.9	1999.5	2000.4	2002.4	2004.4	2006.4	2008.4
175°	2011.7	2008.7	2008.4	2008.0	2007.7	2007.4	2008.2	2010.2	2012.2	2014.2	2016.2
177.5°	2016.0	2013.8	2013.3	2012.8	2012.2	2011.7	2012.4	2014.2	2016.1	2018.0	2019.9
180°	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2



TEST NUMBER: P332769

CATALOG NUMBER: S124DIW-S575D1560U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	939.2	939.2	939.2	939.2	939.2	939.2	939.2	939.2	939.2	939.2	939.2
2.5°	945.5	948.6	952.6	959.5	962.0	965.1	969.4	969.1	970.4	975.0	985.0
5°	949.0	961.0	972.7	986.7	1001.5	1011.2	1024.5	1032.6	1040.8	1051.3	1069.2
7.5°	950.4	969.5	990.9	1015.5	1037.4	1062.6	1082.3	1100.8	1117.5	1139.7	1161.0
10°	948.2	973.9	1001.5	1032.6	1065.7	1093.7	1119.0	1147.8	1172.3	1199.1	1223.3
12.5°	944.1	975.1	1012.1	1046.9	1085.6	1127.0	1158.5	1187.6	1220.2	1251.1	1288.3
15°	935.0	977.4	1020.6	1066.5	1118.2	1166.1	1211.6	1249.3	1284.4	1330.7	1379.3
17.5°	923.3	969.0	1023.5	1079.1	1133.2	1187.9	1244.2	1300.9	1345.1	1402.6	1440.7
20°	912.4	965.3	1021.3	1087.5	1141.6	1209.7	1265.7	1320.5	1381.2	1438.4	1484.0
22.5°	897.1	955.0	1014.5	1080.3	1151.5	1219.6	1284.4	1343.9	1404.6	1466.8	1521.9
25°	877.8	930.3	1000.7	1075.4	1146.2	1220.2	1294.5	1369.2	1434.5	1500.3	1551.7
27.5°	844.8	911.1	976.7	1053.8	1132.5	1216.1	1295.6	1373.8	1442.2	1496.3	1528.2
30°	828.0	885.5	956.8	1034.2	1119.4	1209.3	1292.1	1368.8	1432.6	1475.8	1488.6
32.5°	803.1	862.5	932.2	1012.4	1102.6	1194.9	1281.2	1353.5	1406.8	1429.4	1413.9
35°	766.1	819.8	890.2	972.3	1066.1	1164.5	1249.7	1310.8	1338.1	1316.7	1263.3
37.5°	721.7	775.0	845.7	926.3	1023.4	1123.4	1200.5	1244.4	1235.4	1182.2	1102.7
40°	690.6	740.4	807.7	894.9	989.4	1089.8	1157.5	1181.3	1156.4	1080.1	995.7
42.5°	656.1	704.6	772.2	856.3	956.4	1049.0	1108.0	1110.0	1068.3	977.1	892.3
45°	603.5	649.8	713.6	801.1	893.7	980.9	1019.8	1000.7	923.7	835.7	750.5
47.5°	551.6	591.7	654.6	737.7	825.6	899.0	918.3	884.0	801.9	716.5	637.5
50°	513.6	554.1	613.2	692.6	777.4	840.8	850.1	804.6	724.1	638.1	576.2
52.5°	477.2	517.3	574.3	647.7	725.4	782.6	782.9	730.2	650.0	573.4	515.8
55°	423.7	459.9	511.3	577.0	646.3	691.0	680.1	625.6	556.0	489.5	439.3
57.5°	372.2	403.7	451.0	505.9	566.9	603.8	585.7	533.3	471.1	414.7	376.6
60°	338.9	368.8	409.3	461.1	512.4	541.2	524.1	476.6	419.4	373.9	340.8
62.5°	306.5	331.8	370.7	415.6	463.2	484.6	469.3	422.5	373.1	331.9	305.0
65°	260.7	281.3	312.4	351.0	385.6	403.9	391.0	347.4	309.7	280.1	258.7
67.5°	217.9	234.0	257.6	288.5	317.9	327.8	316.1	285.7	253.8	230.1	215.0
70°	188.3	203.5	223.3	247.1	272.7	283.3	271.6	247.5	221.4	199.6	184.8
72.5°	162.5	174.2	191.0	211.3	231.3	241.9	233.9	210.7	188.7	172.5	159.9
75°	123.7	133.8	145.5	159.9	175.5	182.5	175.5	159.5	144.3	132.3	123.3
77.5°	90.0	95.4	104.4	115.2	124.9	130.3	124.2	113.4	104.1	95.9	91.4
80°	68.5	72.4	78.6	87.2	93.8	98.8	94.9	86.0	78.6	73.1	71.2
82.5°	49.8	52.4	56.5	62.9	67.3	69.9	68.2	61.7	58.7	53.8	51.9
85°	24.5	26.1	28.8	30.7	34.6	35.0	35.4	32.7	30.0	28.8	27.2
87.5°	10.0	11.1	12.8	14.4	16.3	17.2	17.4	17.9	17.2	17.3	16.5
90°	8.2	11.9	15.6	19.3	22.5	25.1	27.8	30.5	33.2	35.2	37.2
92.5°	19.2	19.4	19.6	19.8	21.2	23.9	26.6	29.3	32.0	34.0	36.0
95°	71.5	60.2	48.8	37.4	31.8	32.2	32.5	32.8	33.2	35.2	37.2
97.5°	183.2	190.3	197.5	204.6	189.4	152.0	114.6	77.2	39.8	40.0	40.2
100°	253.4	259.4	265.4	271.4	251.3	205.1	158.8	112.6	66.4	60.7	55.0
102.5°	331.4	335.8	340.2	344.6	343.8	337.8	331.8	325.7	319.7	258.2	196.8
105°	455.9	457.9	460.0	462.0	463.8	465.5	467.2	468.8	470.5	473.5	476.5
107.5°	572.9	573.9	574.9	575.9	577.5	579.8	582.1	584.3	586.6	588.1	589.6
110°	652.5	653.5	654.5	655.5	657.0	659.0	661.0	663.0	665.0	665.7	666.4





TEST NUMBER: P332769

CATALOG NUMBER: S124DIW-S575D1560U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	730.5	732.3	734.1	735.9	737.3	738.2	739.2	740.1	741.1	740.9	740.8
115°	848.5	849.5	850.5	851.5	851.9	851.5	851.2	850.9	850.5	851.2	851.9
117.5°	955.9	957.3	958.6	960.0	961.0	961.7	962.5	963.2	963.9	963.8	963.7
120°	1028.3	1029.7	1031.0	1032.3	1032.8	1032.5	1032.2	1031.8	1031.5	1032.2	1032.8
122.5°	1095.3	1096.1	1096.9	1097.8	1098.4	1098.9	1099.3	1099.8	1100.3	1100.7	1101.1
125°	1192.7	1194.0	1195.4	1196.7	1197.0	1196.4	1195.7	1195.0	1194.4	1195.4	1196.4
127.5°	1283.4	1283.7	1284.0	1284.4	1285.3	1286.9	1288.4	1289.9	1291.5	1291.3	1291.1
130°	1342.5	1342.8	1343.2	1343.5	1344.2	1345.2	1346.2	1347.2	1348.2	1348.5	1348.9
132.5°	1397.0	1397.7	1398.3	1398.9	1399.8	1401.1	1402.3	1403.6	1404.9	1405.2	1405.6
135°	1477.5	1477.2	1476.9	1476.5	1477.0	1478.4	1479.7	1481.1	1482.4	1483.1	1483.7
137.5°	1550.1	1550.2	1550.4	1550.5	1551.3	1552.8	1554.3	1555.7	1557.2	1557.9	1558.7
140°	1597.7	1598.4	1599.0	1599.7	1600.4	1601.0	1601.7	1602.4	1603.0	1604.1	1605.1
142.5°	1640.4	1641.7	1642.9	1644.1	1644.9	1645.3	1645.7	1646.1	1646.5	1647.2	1648.0
145°	1705.1	1706.1	1707.1	1708.1	1708.6	1708.6	1708.6	1708.6	1708.6	1708.9	1709.3
147.5°	1757.5	1759.4	1761.3	1763.2	1763.9	1763.6	1763.3	1762.9	1762.6	1762.9	1763.1
150°	1794.4	1795.7	1797.1	1798.4	1798.9	1798.6	1798.3	1797.9	1797.6	1797.6	1797.6
152.5°	1825.5	1826.6	1827.6	1828.7	1829.0	1828.3	1827.7	1827.1	1826.5	1827.1	1827.6
155°	1868.8	1869.1	1869.5	1869.8	1869.5	1868.5	1867.5	1866.5	1865.4	1866.8	1868.1
157.5°	1905.4	1905.2	1905.0	1904.8	1904.1	1902.9	1901.8	1900.7	1899.5	1901.3	1903.0
160°	1926.3	1925.3	1924.3	1923.3	1922.6	1922.2	1921.9	1921.6	1921.2	1923.3	1925.3
162.5°	1945.3	1944.0	1942.8	1941.5	1940.7	1940.3	1940.0	1939.7	1939.3	1941.3	1943.4
165°	1969.3	1967.7	1966.0	1964.3	1963.5	1963.5	1963.5	1963.5	1963.5	1966.1	1968.8
167.5°	1988.6	1986.8	1985.1	1983.3	1982.4	1982.2	1982.0	1981.8	1981.6	1984.5	1987.5
170°	1999.2	1997.1	1995.1	1993.1	1992.3	1992.6	1993.0	1993.3	1993.6	1996.3	1999.0
172.5°	2006.4	2004.4	2002.4	2000.4	1999.5	1999.9	2000.2	2000.5	2000.9	2003.5	2006.2
175°	2014.2	2012.2	2010.2	2008.2	2007.4	2007.7	2008.0	2008.4	2008.7	2011.7	2014.7
177.5°	2018.0	2016.1	2014.2	2012.4	2011.7	2012.2	2012.8	2013.3	2013.8	2016.0	2018.1
180°	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2



TEST NUMBER: P332769

CATALOG NUMBER: S124DIW-S575D1560U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	939.2	939.2	939.2	939.2	939.2	939.2	939.2
2.5°	990.0	990.6	993.4	995.6	996.2	999.3	999.6
5°	1077.0	1083.6	1096.4	1097.6	1099.5	1109.7	1101.9
7.5°	1178.9	1195.7	1206.9	1216.8	1220.4	1224.8	1223.9
10°	1244.3	1269.2	1281.6	1301.5	1302.3	1307.3	1304.2
12.5°	1310.0	1338.9	1361.6	1365.3	1381.9	1384.5	1388.9
15°	1403.0	1433.8	1465.3	1476.6	1499.5	1505.0	1513.5
17.5°	1490.5	1521.9	1544.0	1573.2	1582.6	1595.2	1586.7
20°	1538.4	1572.7	1600.7	1623.6	1633.4	1640.4	1639.6
22.5°	1567.4	1601.9	1624.6	1642.0	1651.1	1654.1	1653.9
25°	1585.5	1605.4	1612.4	1619.0	1608.9	1605.4	1606.9
27.5°	1535.1	1529.9	1511.7	1487.7	1462.8	1443.0	1432.3
30°	1465.7	1435.3	1407.7	1359.5	1334.5	1319.8	1306.5
32.5°	1367.3	1319.2	1266.1	1221.9	1193.5	1171.6	1168.3
35°	1198.8	1126.4	1061.4	1007.3	979.3	955.6	950.1
37.5°	1019.2	944.0	885.5	837.8	807.7	791.0	775.4
40°	899.9	835.4	777.8	737.3	714.4	702.3	692.6
42.5°	808.1	749.1	691.9	661.0	640.3	632.9	627.2
45°	681.3	626.4	586.7	563.4	551.3	538.9	533.0
47.5°	579.7	535.1	508.9	489.1	476.2	468.8	465.0
50°	522.1	485.6	462.2	447.1	435.4	429.5	426.4
52.5°	471.1	441.1	421.5	409.4	401.5	397.2	395.9
55°	405.8	382.9	370.4	359.9	354.1	350.2	348.6
57.5°	352.7	335.1	325.0	316.3	314.1	310.8	309.7
60°	317.9	304.3	295.7	289.9	287.9	284.0	284.8
62.5°	287.1	275.9	268.6	265.3	262.7	259.4	260.5
65°	242.8	234.6	230.7	227.6	224.5	222.6	224.1
67.5°	203.7	198.1	192.8	191.0	189.5	189.2	187.5
70°	178.2	173.5	168.9	167.7	167.7	166.1	165.7
72.5°	153.6	150.2	147.1	146.2	145.0	145.6	144.0
75°	118.7	115.9	114.8	113.6	113.2	113.2	112.1
77.5°	87.7	85.7	83.8	83.8	82.4	81.9	81.7
80°	66.5	65.8	64.2	64.2	63.4	63.8	63.0
82.5°	50.0	48.9	48.6	48.0	46.9	47.0	46.2
85°	26.8	25.7	25.3	24.1	23.3	24.1	23.3
87.5°	17.2	17.3	17.2	16.7	16.6	16.7	15.9
90°	39.2	41.2	42.6	43.2	43.9	44.6	45.2
92.5°	38.0	40.0	41.1	41.2	41.4	41.5	41.6
95°	39.2	41.2	42.4	42.7	43.1	43.4	43.7
97.5°	40.4	40.6	40.9	41.2	41.6	41.9	42.2
100°	49.3	43.6	40.9	41.2	41.6	41.9	42.2
102.5°	135.3	73.9	43.2	43.2	43.3	43.4	43.4
105°	479.6	482.6	478.0	466.0	453.9	441.9	429.8
107.5°	591.1	592.5	593.9	595.2	596.4	597.7	599.0
110°	667.1	667.7	668.6	669.6	670.6	671.6	672.6



TEST NUMBER: P332769

CATALOG NUMBER: S124DIW-S575D1560U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	740.6	740.5	741.1	742.4	743.6	744.9	746.2
115°	852.5	853.2	853.6	853.6	853.6	853.6	853.6
117.5°	963.5	963.4	963.3	963.1	963.0	962.9	962.7
120°	1033.5	1034.2	1034.2	1033.5	1032.8	1032.2	1031.5
122.5°	1101.5	1101.9	1101.7	1101.1	1100.4	1099.7	1099.1
125°	1197.4	1198.4	1199.1	1199.4	1199.7	1200.1	1200.4
127.5°	1290.9	1290.7	1290.4	1290.2	1289.9	1289.6	1289.4
130°	1349.2	1349.5	1349.7	1349.7	1349.7	1349.7	1349.7
132.5°	1405.9	1406.2	1406.3	1406.0	1405.7	1405.5	1405.2
135°	1484.4	1485.1	1485.8	1486.4	1487.1	1487.8	1488.4
137.5°	1559.4	1560.2	1560.4	1560.2	1560.0	1559.8	1559.6
140°	1606.1	1607.1	1607.7	1608.1	1608.4	1608.7	1609.1
142.5°	1648.7	1649.4	1649.8	1649.9	1650.0	1650.0	1650.1
145°	1709.6	1709.9	1710.5	1711.1	1711.8	1712.5	1713.1
147.5°	1763.4	1763.7	1764.0	1764.3	1764.6	1765.0	1765.3
150°	1797.6	1797.6	1797.8	1798.1	1798.4	1798.8	1799.1
152.5°	1828.1	1828.7	1828.8	1828.6	1828.4	1828.2	1828.0
155°	1869.5	1870.8	1871.0	1870.0	1869.0	1868.0	1867.0
157.5°	1904.8	1906.5	1906.5	1904.8	1903.0	1901.3	1899.5
160°	1927.3	1929.3	1929.3	1927.3	1925.3	1923.3	1921.2
162.5°	1945.4	1947.4	1947.2	1945.0	1942.7	1940.4	1938.1
165°	1971.5	1974.2	1974.0	1971.0	1968.0	1965.0	1962.0
167.5°	1990.4	1993.4	1993.2	1989.8	1986.5	1983.1	1979.8
170°	2001.7	2004.4	2004.0	2000.7	1997.3	1994.0	1990.6
172.5°	2008.9	2011.6	2011.1	2007.5	2003.9	2000.3	1996.6
175°	2017.8	2020.8	2020.3	2016.2	2012.2	2008.2	2004.2
177.5°	2020.3	2022.4	2021.9	2018.7	2015.4	2012.2	2009.0
180°	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2

(END OF REPORT)