

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: NEO-RAY

Report Number: P332749

Luminaire Tested: **S124DIW-S575D470U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332749  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIW-S575D470U835-4F0-1E-UDD-F  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 470 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4368.2 lumens  
Efficiency: N/A  
Efficacy: 144.6 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 30.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332749

CATALOG NUMBER: S124DIW-S575D470U835-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332749

CATALOG NUMBER: S124DIW-S575D470U835-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	63	63	63	57
1	99	95	91	87	92	89	85	82	76	74	72	65	64	62	55	54	53	48
2	90	83	77	71	84	77	72	67	67	63	59	57	54	52	49	46	44	40
3	83	73	65	59	76	68	62	56	59	54	50	51	47	44	43	40	38	34
4	76	65	56	50	70	60	53	48	53	47	43	45	41	38	39	35	33	29
5	69	58	49	43	64	54	47	41	47	41	37	41	36	33	35	31	28	25
6	64	52	43	38	59	48	41	36	42	37	32	37	32	29	32	28	25	22
7	59	47	39	33	55	44	37	31	39	33	28	33	29	25	29	25	22	20
8	55	42	35	29	51	40	33	28	35	29	25	31	26	23	26	23	20	18
9	51	39	31	26	48	37	30	25	32	27	23	28	24	20	24	21	18	16
10	48	36	28	23	45	34	27	22	30	24	20	26	22	18	23	19	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	7840	7840	7840
5°	7864	7769	7826
10°	7814	7706	7744
15°	7720	7596	7616
20°	7594	7460	7467
25°	7451	7306	7285
30°	7276	7124	7058
35°	7094	6933	6841
40°	6905	6716	6593
45°	6707	6503	6379
50°	6489	6314	6118
55°	6253	6068	5871
60°	6018	5792	5616
65°	5752	5530	5307
70°	5455	5179	4978
75°	5000	4757	4635
80°	4449	4268	4161
85°	3890	3751	3677



TEST NUMBER: P332749

CATALOG NUMBER: S124DIW-S575D470U835-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	91.5	2.1
10°-20°	257.7	5.9
20°-30°	379.3	8.7
30°-40°	440.9	10.1
40°-50°	440.9	10.1
50°-60°	385.7	8.8
60°-70°	286.4	6.6
70°-80°	162.7	3.7
80°-90°	48.7	1.1
90°-100°	20.7	0.5
100°-110°	132.1	3.0
110°-120°	252.8	5.8
120°-130°	320.9	7.3
130°-140°	343.3	7.9
140°-150°	321.0	7.3
150°-160°	258.9	5.9
160°-170°	167.0	3.8
170°-180°	57.6	1.3
0°-30°	728.4	16.7
0°-40°	1169.3	26.8
0°-60°	1996.0	45.7
0°-90°	2493.8	57.1
90°-120°	405.6	9.3
90°-150°	1390.9	31.8
90°-180°	1874.0	42.9
0°-180°	4368.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	971	971	971	971	971	
5°	970	967	959	967	966	92
15°	924	920	909	913	911	260
25°	836	831	820	821	818	385
35°	720	714	704	698	694	450
45°	588	582	570	561	559	453
55°	444	442	431	422	417	398
65°	301	297	290	282	278	298
75°	160	156	152	150	149	170
85°	42	42	40	40	40	46
90°	1	6	10	13	14	3
95°	25	10	10	13	13	32
105°	136	139	141	144	129	143
115°	255	256	256	256	256	251
125°	358	360	359	360	361	320
135°	444	444	446	446	447	342
145°	512	513	514	514	515	320
155°	562	562	561	562	561	259
165°	592	590	590	593	590	167
175°	606	603	604	607	602	58
180°	606	606	606	606	606	



TEST NUMBER: P332749

CATALOG NUMBER: S124DIW-S575D470U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	971.1	971.1	971.1	971.1	971.1	971.1	971.1	971.1	971.1	971.1	971.1
2.5°	973.6	973.2	972.8	972.4	972.0	971.0	969.5	968.0	966.4	964.9	966.3
5°	970.4	969.7	969.0	968.3	967.6	966.3	964.4	962.5	960.6	958.7	960.6
7.5°	961.3	960.6	960.0	959.3	958.6	957.2	955.1	953.0	950.8	948.7	950.3
10°	953.2	952.6	951.9	951.2	950.5	949.0	946.8	944.5	942.3	940.0	941.4
12.5°	942.7	942.0	941.3	940.6	939.9	938.4	936.0	933.6	931.2	928.8	930.3
15°	923.7	923.0	922.3	921.6	920.9	919.3	916.7	914.1	911.5	908.9	909.9
17.5°	900.8	899.9	899.1	898.2	897.3	895.7	893.2	890.8	888.3	885.9	886.5
20°	884.0	883.1	882.3	881.4	880.5	878.8	876.2	873.6	871.0	868.4	868.9
22.5°	865.9	864.8	863.7	862.5	861.4	859.5	856.9	854.3	851.7	849.1	850.1
25°	836.5	835.3	834.1	832.9	831.7	829.9	827.4	825.0	822.6	820.2	820.4
27.5°	802.9	801.7	800.4	799.2	797.9	796.2	793.9	791.7	789.4	787.2	786.8
30°	780.5	779.1	777.7	776.3	775.0	773.1	770.9	768.6	766.4	764.2	763.5
32.5°	756.8	755.6	754.3	753.1	751.9	750.0	747.7	745.3	742.9	740.5	739.7
35°	719.8	718.6	717.4	716.2	715.0	713.1	710.7	708.3	705.9	703.5	702.2
37.5°	680.7	679.6	678.5	677.4	676.3	674.5	671.9	669.3	666.7	664.1	662.8
40°	655.2	653.8	652.4	651.1	649.7	647.7	645.1	642.5	639.9	637.3	635.6
42.5°	627.8	627.0	626.2	625.3	624.5	622.6	619.8	616.9	614.0	611.2	609.2
45°	587.5	586.3	585.1	583.9	582.7	580.7	577.9	575.1	572.4	569.6	567.7
47.5°	545.3	544.5	543.7	542.8	542.0	540.3	537.8	535.2	532.6	530.1	527.9
50°	516.7	516.0	515.3	514.6	513.9	512.4	510.0	507.5	505.1	502.7	500.3
52.5°	488.7	487.9	487.0	486.2	485.4	483.7	481.1	478.6	476.0	473.4	471.3
55°	444.3	443.8	443.3	442.8	442.3	440.8	438.4	435.9	433.5	431.1	429.0
57.5°	402.0	401.4	400.8	400.2	399.6	398.2	395.8	393.4	391.0	388.6	386.6
60°	372.7	371.9	371.0	370.1	369.3	367.7	365.5	363.2	361.0	358.7	357.2
62.5°	344.1	343.4	342.6	341.9	341.2	339.6	337.3	334.9	332.5	330.1	328.7
65°	301.1	300.3	299.4	298.6	297.7	296.4	294.7	292.9	291.2	289.5	287.7
67.5°	257.9	257.1	256.3	255.5	254.7	253.5	251.8	250.2	248.5	246.8	245.2
70°	231.1	229.9	228.7	227.5	226.3	225.0	223.6	222.2	220.8	219.4	218.1
72.5°	202.5	201.3	200.1	198.8	197.6	196.5	195.4	194.3	193.2	192.0	190.9
75°	160.3	159.4	158.6	157.7	156.8	156.0	155.1	154.2	153.4	152.5	151.8
77.5°	120.0	119.6	119.2	118.9	118.5	117.9	117.1	116.4	115.6	114.9	114.6
80°	95.7	95.2	94.7	94.2	93.6	93.2	92.9	92.5	92.2	91.8	91.5
82.5°	72.1	71.8	71.6	71.3	71.1	70.9	70.9	70.8	70.7	70.7	70.4
85°	42.0	42.0	42.0	42.0	42.0	41.8	41.5	41.2	40.8	40.5	40.5
87.5°	16.5	16.5	16.6	16.7	16.8	16.8	16.9	16.9	16.9	16.9	17.1
90°	1.4	2.5	3.6	4.7	5.8	6.7	7.6	8.4	9.2	10.0	10.6
92.5°	5.7	5.8	5.8	5.9	6.0	6.4	7.2	8.0	8.8	9.6	10.2
95°	24.9	21.5	18.1	14.7	11.2	9.6	9.7	9.8	9.9	10.0	10.6
97.5°	52.9	55.1	57.2	59.3	61.5	56.9	45.7	34.4	23.2	12.0	12.0
100°	74.3	76.1	78.0	79.8	81.6	75.5	61.6	47.7	33.8	19.9	18.2
102.5°	98.3	99.6	100.9	102.2	103.6	103.3	101.5	99.7	97.9	96.1	77.6
105°	136.4	137.0	137.6	138.2	138.8	139.4	139.9	140.4	140.9	141.4	142.3
107.5°	171.9	172.2	172.5	172.8	173.1	173.6	174.2	174.9	175.6	176.3	176.7
110°	195.8	196.1	196.4	196.7	197.0	197.4	198.0	198.7	199.3	199.9	200.1



TEST NUMBER: P332749

CATALOG NUMBER: S124DIW-S575D470U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	219.0	219.5	220.1	220.6	221.2	221.6	221.9	222.1	222.4	222.7	222.7
115°	254.7	255.0	255.3	255.6	255.9	256.0	255.9	255.8	255.7	255.6	255.8
117.5°	286.9	287.3	287.7	288.1	288.5	288.8	289.0	289.2	289.5	289.7	289.6
120°	308.6	309.0	309.4	309.8	310.2	310.4	310.3	310.2	310.1	310.0	310.2
122.5°	328.9	329.2	329.4	329.7	329.9	330.1	330.2	330.4	330.5	330.7	330.8
125°	358.0	358.4	358.8	359.2	359.6	359.7	359.5	359.3	359.1	358.9	359.2
127.5°	385.6	385.7	385.8	385.9	386.0	386.3	386.7	387.2	387.7	388.1	388.1
130°	403.3	403.4	403.6	403.7	403.8	404.0	404.3	404.6	404.9	405.2	405.3
132.5°	419.7	419.8	420.0	420.2	420.4	420.7	421.1	421.4	421.8	422.2	422.3
135°	444.1	444.0	443.9	443.8	443.7	443.9	444.3	444.7	445.1	445.5	445.7
137.5°	465.8	465.8	465.9	465.9	466.0	466.2	466.6	467.1	467.5	468.0	468.2
140°	479.9	480.1	480.3	480.5	480.7	480.9	481.1	481.4	481.6	481.8	482.1
142.5°	492.6	493.0	493.4	493.7	494.1	494.3	494.4	494.6	494.7	494.8	495.0
145°	512.1	512.4	512.7	513.0	513.3	513.5	513.5	513.5	513.5	513.5	513.6
147.5°	527.6	528.2	528.7	529.3	529.9	530.1	530.0	529.9	529.8	529.7	529.8
150°	538.9	539.3	539.7	540.1	540.5	540.6	540.5	540.4	540.3	540.2	540.2
152.5°	548.3	548.6	548.9	549.2	549.6	549.6	549.5	549.3	549.1	548.9	549.1
155°	561.5	561.6	561.7	561.8	561.9	561.8	561.5	561.2	560.9	560.6	561.0
157.5°	572.7	572.6	572.5	572.5	572.4	572.2	571.9	571.5	571.2	570.9	571.4
160°	579.2	578.9	578.6	578.3	578.0	577.8	577.7	577.6	577.5	577.4	578.0
162.5°	585.0	584.6	584.2	583.8	583.5	583.2	583.1	583.0	582.9	582.8	583.4
165°	592.3	591.8	591.3	590.8	590.3	590.1	590.1	590.1	590.1	590.1	590.9
167.5°	598.1	597.6	597.1	596.6	596.0	595.7	595.7	595.6	595.6	595.5	596.4
170°	601.4	600.8	600.2	599.6	599.0	598.7	598.8	598.9	599.0	599.1	599.9
172.5°	603.6	603.0	602.4	601.8	601.2	600.9	601.0	601.1	601.2	601.3	602.1
175°	605.9	605.3	604.7	604.1	603.5	603.3	603.4	603.5	603.6	603.7	604.6
177.5°	607.0	606.5	605.9	605.3	604.8	604.6	604.7	604.9	605.0	605.2	605.8
180°	605.9	605.9	605.9	605.9	605.9	605.9	605.9	605.9	605.9	605.9	605.9



TEST NUMBER: P332749

CATALOG NUMBER: S124DIW-S575D470U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	971.1	971.1	971.1	971.1	971.1	971.1	971.1	971.1
2.5°	967.7	969.1	970.5	971.1	970.9	970.8	970.7	970.5
5°	962.5	964.4	966.3	967.1	966.7	966.4	966.0	965.7
7.5°	951.8	953.3	954.8	955.5	955.3	955.1	954.9	954.6
10°	942.8	944.2	945.6	946.1	945.7	945.4	945.0	944.7
12.5°	931.9	933.4	934.9	935.4	934.9	934.4	934.0	933.5
15°	911.0	912.0	913.0	913.3	912.8	912.3	911.7	911.2
17.5°	887.2	887.8	888.5	888.6	888.3	887.9	887.6	887.3
20°	869.5	870.0	870.5	870.6	870.2	869.9	869.6	869.2
22.5°	851.0	851.9	852.9	853.0	852.4	851.8	851.2	850.5
25°	820.5	820.7	820.9	820.6	819.9	819.2	818.5	817.8
27.5°	786.4	785.9	785.5	784.9	784.0	783.2	782.3	781.4
30°	762.8	762.1	761.4	760.6	759.7	758.9	758.0	757.1
32.5°	738.8	738.0	737.2	736.3	735.5	734.6	733.7	732.9
35°	701.0	699.8	698.6	697.6	696.7	695.8	695.0	694.1
37.5°	661.5	660.1	658.8	657.6	656.5	655.3	654.2	653.0
40°	633.9	632.1	630.4	629.1	628.2	627.4	626.5	625.6
42.5°	607.2	605.1	603.1	601.8	601.3	600.7	600.1	599.5
45°	565.8	563.9	562.0	560.8	560.3	559.8	559.2	558.7
47.5°	525.8	523.6	521.5	519.8	518.5	517.1	515.8	514.5
50°	497.8	495.4	493.0	491.3	490.2	489.2	488.2	487.1
52.5°	469.1	467.0	464.9	463.1	461.8	460.5	459.2	457.9
55°	427.0	424.9	422.8	421.2	420.2	419.2	418.1	417.1
57.5°	384.7	382.7	380.7	379.2	378.2	377.2	376.2	375.2
60°	355.6	354.1	352.5	351.3	350.4	349.6	348.7	347.8
62.5°	327.3	325.8	324.4	323.3	322.4	321.6	320.7	319.8
65°	286.0	284.3	282.6	281.3	280.4	279.5	278.7	277.8
67.5°	243.5	241.9	240.2	239.2	239.0	238.8	238.5	238.3
70°	216.7	215.3	213.9	213.0	212.4	211.9	211.4	210.9
72.5°	189.8	188.7	187.6	186.8	186.3	185.8	185.3	184.7
75°	151.1	150.4	149.8	149.3	149.1	149.0	148.8	148.6
77.5°	114.4	114.2	114.0	113.7	113.2	112.8	112.3	111.9
80°	91.1	90.8	90.4	90.2	90.0	89.8	89.7	89.5
82.5°	70.2	70.0	69.8	69.6	69.5	69.3	69.1	68.9
85°	40.5	40.5	40.5	40.4	40.2	40.0	39.9	39.7
87.5°	17.2	17.3	17.4	17.5	17.5	17.6	17.6	17.7
90°	11.2	11.8	12.4	12.8	13.0	13.2	13.4	13.6
92.5°	10.8	11.4	12.0	12.3	12.4	12.4	12.5	12.5
95°	11.2	11.8	12.4	12.7	12.8	12.9	13.0	13.1
97.5°	12.1	12.1	12.2	12.3	12.4	12.5	12.6	12.7
100°	16.5	14.8	13.1	12.3	12.4	12.5	12.6	12.7
102.5°	59.1	40.7	22.2	13.0	13.0	13.0	13.0	13.1
105°	143.2	144.1	145.0	143.7	140.0	136.4	132.8	129.2
107.5°	177.2	177.6	178.1	178.5	178.9	179.2	179.6	180.0
110°	200.3	200.5	200.7	200.9	201.2	201.5	201.8	202.1





TEST NUMBER: P332749

CATALOG NUMBER: S124DIW-S575D470U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	222.6	222.6	222.5	222.7	223.1	223.5	223.9	224.2
115°	256.0	256.2	256.4	256.5	256.5	256.5	256.5	256.5
117.5°	289.6	289.6	289.5	289.5	289.4	289.4	289.4	289.3
120°	310.4	310.6	310.8	310.8	310.6	310.4	310.2	310.0
122.5°	330.9	331.0	331.1	331.1	330.9	330.7	330.5	330.3
125°	359.5	359.8	360.1	360.3	360.4	360.5	360.6	360.7
127.5°	388.0	387.9	387.9	387.8	387.7	387.6	387.6	387.5
130°	405.4	405.5	405.6	405.6	405.6	405.6	405.6	405.6
132.5°	422.4	422.5	422.6	422.6	422.5	422.5	422.4	422.3
135°	445.9	446.1	446.3	446.5	446.7	446.9	447.1	447.3
137.5°	468.4	468.6	468.9	468.9	468.9	468.8	468.8	468.7
140°	482.4	482.7	483.0	483.2	483.3	483.4	483.5	483.6
142.5°	495.2	495.5	495.7	495.8	495.8	495.9	495.9	495.9
145°	513.7	513.8	513.9	514.0	514.2	514.4	514.6	514.8
147.5°	529.9	529.9	530.0	530.1	530.2	530.3	530.4	530.5
150°	540.2	540.2	540.2	540.3	540.4	540.5	540.6	540.7
152.5°	549.2	549.4	549.6	549.6	549.6	549.5	549.4	549.4
155°	561.4	561.8	562.2	562.3	562.0	561.7	561.4	561.1
157.5°	571.9	572.4	572.9	572.9	572.4	571.9	571.4	570.9
160°	578.6	579.2	579.8	579.8	579.2	578.6	578.0	577.4
162.5°	584.0	584.6	585.2	585.2	584.5	583.8	583.1	582.5
165°	591.7	592.5	593.3	593.2	592.3	591.4	590.5	589.6
167.5°	597.3	598.2	599.1	599.0	598.0	597.0	596.0	595.0
170°	600.7	601.5	602.4	602.3	601.2	600.2	599.2	598.2
172.5°	602.9	603.7	604.5	604.4	603.3	602.2	601.1	600.0
175°	605.5	606.4	607.3	607.1	605.9	604.7	603.5	602.3
177.5°	606.5	607.1	607.8	607.6	606.7	605.7	604.7	603.8
180°	605.9	605.9	605.9	605.9	605.9	605.9	605.9	605.9

(END OF REPORT)