

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332804

Luminaire Tested: **S124DIW-S795D1560U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332804
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S795D1560U835-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8821.4 lumens
Efficiency: N/A
Efficacy: 129.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 68.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332804

CATALOG NUMBER: S124DIW-S795D1560U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332804

CATALOG NUMBER: S124DIW-S795D1560U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	95	95	95	95	77	77	77	61	61	61	46	46	46	39
1	95	91	87	84	86	83	79	77	67	65	63	53	52	50	40	39	38	32
2	87	79	73	68	78	72	67	63	59	55	52	47	44	42	35	34	32	27
3	79	70	63	57	71	64	57	52	52	48	44	41	38	36	31	29	28	23
4	72	62	54	48	65	56	50	44	46	41	37	37	33	30	28	26	24	20
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	25	23	21	17
6	61	49	41	35	55	45	38	33	37	32	28	30	26	23	23	20	18	15
7	56	44	36	31	51	41	34	29	34	28	25	27	23	20	21	18	16	13
8	52	40	33	27	47	37	30	25	31	25	22	25	21	18	19	16	14	12
9	49	37	29	24	44	34	27	23	28	23	19	23	19	16	18	15	13	11
10	45	33	26	22	41	31	24	20	26	21	17	21	17	15	16	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10717	10717	10717
5°	10749	10619	10697
10°	10681	10533	10585
15°	10552	10384	10410
20°	10381	10198	10207
25°	10185	9986	9958
30°	9945	9737	9648
35°	9697	9477	9351
40°	9438	9180	9013
45°	9169	8889	8719
50°	8871	8629	8363
55°	8549	8294	8024
60°	8226	7918	7677
65°	7862	7559	7253
70°	7456	7081	6805
75°	6834	6503	6338
80°	6081	5835	5686
85°	5317	5122	5020



TEST NUMBER: P332804

CATALOG NUMBER: S124DIW-S795D1560U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	125.0	1.4
10°-20°	352.2	4.0
20°-30°	518.4	5.9
30°-40°	602.7	6.8
40°-50°	602.7	6.8
50°-60°	527.2	6.0
60°-70°	391.5	4.4
70°-80°	222.4	2.5
80°-90°	70.0	0.8
90°-100°	128.6	1.5
100°-110°	380.9	4.3
110°-120°	646.6	7.3
120°-130°	852.5	9.7
130°-140°	957.5	10.9
140°-150°	940.9	10.7
150°-160°	791.3	9.0
160°-170°	526.5	6.0
170°-180°	184.4	2.1
0°-30°	995.7	11.3
0°-40°	1598.4	18.1
0°-60°	2728.3	30.9
0°-90°	3412.3	38.7
90°-120°	1156.1	13.1
90°-150°	3906.9	44.3
90°-180°	5409.0	61.3
0°-180°	8821.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1328	1328	1328	1328	1328	
5°	1326	1322	1310	1321	1320	126
15°	1263	1258	1242	1248	1246	356
25°	1143	1136	1121	1122	1118	526
35°	984	976	962	954	949	615
45°	803	795	779	767	764	619
55°	607	604	589	577	570	544
65°	412	406	396	385	380	407
75°	219	214	208	204	203	233
85°	57	57	55	55	54	63
90°	4	21	33	42	45	9
95°	90	104	115	119	119	101
105°	351	353	359	363	368	373
115°	657	657	654	653	651	648
125°	958	957	956	953	950	853
135°	1235	1244	1244	1241	1236	955
145°	1500	1506	1508	1506	1502	939
155°	1719	1719	1717	1723	1717	791
165°	1871	1867	1864	1872	1867	527
175°	1947	1939	1938	1947	1938	185
180°	1950	1950	1950	1950	1950	



TEST NUMBER: P332804

CATALOG NUMBER: S124DIW-S795D1560U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1327.5	1327.5	1327.5	1327.5	1327.5	1327.5	1327.5	1327.5	1327.5	1327.5	1327.5
2.5°	1330.9	1330.3	1329.7	1329.2	1328.6	1327.3	1325.2	1323.1	1321.0	1319.0	1320.8
5°	1326.4	1325.5	1324.5	1323.6	1322.6	1320.8	1318.2	1315.6	1313.0	1310.4	1313.0
7.5°	1314.1	1313.1	1312.2	1311.2	1310.3	1308.4	1305.5	1302.6	1299.7	1296.8	1298.9
10°	1303.0	1302.1	1301.1	1300.2	1299.2	1297.2	1294.1	1291.1	1288.0	1284.9	1286.8
12.5°	1288.5	1287.6	1286.6	1285.7	1284.8	1282.6	1279.4	1276.1	1272.9	1269.6	1271.7
15°	1262.6	1261.6	1260.7	1259.7	1258.8	1256.6	1253.0	1249.5	1245.9	1242.4	1243.8
17.5°	1231.3	1230.1	1228.9	1227.8	1226.6	1224.3	1221.0	1217.6	1214.2	1210.9	1211.8
20°	1208.3	1207.1	1206.0	1204.8	1203.6	1201.2	1197.7	1194.1	1190.6	1187.1	1187.8
22.5°	1183.7	1182.1	1180.5	1179.0	1177.4	1174.9	1171.3	1167.8	1164.2	1160.7	1162.0
25°	1143.4	1141.8	1140.1	1138.5	1136.8	1134.3	1131.0	1127.7	1124.4	1121.1	1121.3
27.5°	1097.5	1095.8	1094.1	1092.4	1090.7	1088.3	1085.2	1082.2	1079.1	1076.0	1075.4
30°	1066.9	1065.0	1063.1	1061.2	1059.3	1056.8	1053.7	1050.7	1047.6	1044.5	1043.6
32.5°	1034.5	1032.8	1031.1	1029.4	1027.7	1025.2	1022.0	1018.7	1015.5	1012.2	1011.1
35°	983.9	982.2	980.6	978.9	977.3	974.8	971.5	968.2	964.9	961.6	959.9
37.5°	930.5	929.0	927.5	926.0	924.4	921.9	918.4	914.8	911.3	907.7	905.9
40°	895.6	893.7	891.8	889.9	888.0	885.3	881.8	878.2	874.7	871.1	868.8
42.5°	858.2	857.0	855.9	854.8	853.6	851.1	847.2	843.3	839.3	835.4	832.7
45°	803.1	801.4	799.8	798.1	796.5	793.7	790.0	786.2	782.4	778.6	776.0
47.5°	745.4	744.3	743.2	742.0	740.9	738.6	735.1	731.6	728.1	724.6	721.6
50°	706.3	705.3	704.4	703.4	702.5	700.4	697.1	693.8	690.4	687.1	683.8
52.5°	668.0	666.9	665.7	664.6	663.4	661.1	657.6	654.1	650.6	647.1	644.2
55°	607.4	606.6	605.9	605.2	604.5	602.5	599.2	595.9	592.6	589.3	586.4
57.5°	549.5	548.7	547.9	547.1	546.3	544.2	541.0	537.7	534.5	531.2	528.5
60°	509.5	508.3	507.1	506.0	504.8	502.6	499.6	496.5	493.4	490.4	488.2
62.5°	470.4	469.4	468.4	467.4	466.4	464.3	461.0	457.7	454.5	451.2	449.3
65°	411.6	410.5	409.3	408.1	406.9	405.1	402.8	400.4	398.0	395.7	393.3
67.5°	352.5	351.4	350.3	349.2	348.2	346.5	344.2	341.9	339.7	337.4	335.1
70°	315.9	314.3	312.6	310.9	309.3	307.5	305.6	303.7	301.8	300.0	298.1
72.5°	276.8	275.1	273.5	271.8	270.1	268.6	267.1	265.5	264.0	262.5	261.0
75°	219.1	217.9	216.8	215.6	214.4	213.2	212.0	210.8	209.7	208.5	207.5
77.5°	164.0	163.5	163.0	162.5	161.9	161.2	160.1	159.1	158.0	157.0	156.7
80°	130.8	130.1	129.4	128.7	128.0	127.4	126.9	126.5	126.0	125.5	125.0
82.5°	98.5	98.2	97.8	97.5	97.2	97.0	96.9	96.8	96.7	96.6	96.3
85°	57.4	57.4	57.4	57.4	57.4	57.2	56.7	56.3	55.8	55.3	55.3
87.5°	23.0	23.6	24.1	24.7	25.2	25.7	26.0	26.4	26.7	27.1	27.5
90°	4.5	8.2	11.9	15.6	19.3	22.5	25.1	27.8	30.5	33.2	35.2
92.5°	32.3	36.5	40.7	44.9	49.2	52.2	54.1	56.0	57.8	59.7	60.9
95°	90.5	93.5	96.5	99.5	102.5	105.2	107.6	109.9	112.3	114.6	115.6
97.5°	158.0	160.4	162.8	165.3	167.7	170.3	173.0	175.7	178.5	181.2	182.4
100°	211.1	212.4	213.8	215.1	216.5	218.6	221.7	224.7	227.7	230.7	231.4
102.5°	266.6	267.1	267.7	268.2	268.7	270.4	273.1	275.9	278.6	281.4	282.3
105°	351.3	351.7	352.0	352.3	352.7	353.5	354.8	356.2	357.5	358.9	359.9
107.5°	440.3	440.7	441.1	441.5	441.9	442.2	442.4	442.6	442.8	443.0	443.9
110°	500.6	501.3	501.9	502.6	503.3	503.5	503.1	502.8	502.4	502.1	501.4



TEST NUMBER: P332804

CATALOG NUMBER: S124DIW-S795D1560U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	563.3	563.5	563.6	563.7	563.9	563.6	563.0	562.4	561.8	561.2	561.1
115°	657.4	657.4	657.4	657.4	657.4	657.1	656.4	655.7	655.1	654.4	654.1
117.5°	746.1	746.3	746.6	746.9	747.2	747.1	746.6	746.1	745.6	745.2	744.0
120°	805.2	806.5	807.9	809.2	810.5	810.7	809.7	808.7	807.7	806.7	805.0
122.5°	866.7	867.2	867.8	868.3	868.8	868.9	868.4	867.9	867.5	867.0	865.9
125°	957.5	957.5	957.5	957.5	957.5	957.3	957.0	956.6	956.3	956.0	955.3
127.5°	1039.8	1040.8	1041.8	1042.8	1043.8	1044.1	1043.5	1043.0	1042.5	1041.9	1041.2
130°	1097.7	1098.7	1099.7	1100.7	1101.7	1102.2	1102.2	1102.2	1102.2	1102.2	1101.6
132.5°	1156.8	1157.6	1158.3	1159.0	1159.8	1160.0	1159.7	1159.5	1159.2	1158.9	1158.3
135°	1234.9	1236.9	1238.9	1241.0	1243.0	1244.0	1244.0	1244.0	1244.0	1244.0	1243.3
137.5°	1320.0	1320.9	1321.8	1322.8	1323.7	1324.5	1325.0	1325.5	1326.1	1326.6	1325.7
140°	1376.7	1377.3	1378.0	1378.7	1379.3	1379.7	1379.7	1379.7	1379.7	1379.7	1379.3
142.5°	1428.5	1429.2	1429.9	1430.5	1431.2	1431.4	1431.1	1430.9	1430.6	1430.3	1430.3
145°	1500.3	1501.6	1503.0	1504.3	1505.7	1506.5	1506.8	1507.2	1507.5	1507.8	1507.5
147.5°	1571.5	1573.1	1574.7	1576.3	1577.9	1578.6	1578.3	1578.0	1577.8	1577.5	1577.2
150°	1614.9	1616.2	1617.6	1618.9	1620.3	1620.9	1620.9	1620.9	1620.9	1620.9	1620.9
152.5°	1655.9	1656.7	1657.5	1658.3	1659.1	1659.7	1659.9	1660.2	1660.5	1660.7	1661.5
155°	1718.9	1718.9	1718.9	1718.9	1718.9	1718.8	1718.4	1718.1	1717.8	1717.4	1718.8
157.5°	1772.0	1771.4	1770.8	1770.2	1769.6	1769.3	1769.2	1769.1	1769.1	1769.0	1770.0
160°	1803.4	1803.0	1802.7	1802.4	1802.0	1801.7	1801.4	1801.0	1800.7	1800.4	1801.4
162.5°	1832.3	1831.5	1830.6	1829.7	1828.8	1828.2	1827.9	1827.6	1827.2	1826.9	1828.7
165°	1871.2	1870.2	1869.2	1868.2	1867.2	1866.4	1865.7	1865.0	1864.4	1863.7	1865.7
167.5°	1901.1	1899.7	1898.3	1896.9	1895.5	1894.8	1894.9	1894.9	1895.0	1895.1	1897.1
170°	1918.0	1916.3	1914.6	1912.9	1911.3	1910.6	1910.9	1911.3	1911.6	1911.9	1913.9
172.5°	1930.0	1928.6	1927.2	1925.8	1924.4	1923.7	1923.8	1923.9	1923.9	1924.0	1926.3
175°	1946.6	1944.9	1943.3	1941.6	1939.9	1938.9	1938.6	1938.2	1937.9	1937.6	1939.9
177.5°	1952.0	1950.7	1949.4	1948.0	1946.7	1946.0	1946.0	1946.0	1946.0	1946.0	1947.9
180°	1949.6	1949.6	1949.6	1949.6	1949.6	1949.6	1949.6	1949.6	1949.6	1949.6	1949.6



TEST NUMBER: P332804

CATALOG NUMBER: S124DIW-S795D1560U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1327.5	1327.5	1327.5	1327.5	1327.5	1327.5	1327.5	1327.5
2.5°	1322.7	1324.6	1326.5	1327.4	1327.2	1327.0	1326.8	1326.6
5°	1315.6	1318.2	1320.8	1321.9	1321.4	1321.0	1320.5	1320.0
7.5°	1301.0	1303.1	1305.1	1306.0	1305.8	1305.5	1305.2	1304.9
10°	1288.7	1290.6	1292.5	1293.2	1292.7	1292.2	1291.8	1291.3
12.5°	1273.8	1275.8	1277.9	1278.6	1278.0	1277.3	1276.6	1276.0
15°	1245.2	1246.6	1248.0	1248.4	1247.7	1247.0	1246.3	1245.6
17.5°	1212.7	1213.6	1214.5	1214.7	1214.2	1213.7	1213.3	1212.8
20°	1188.5	1189.2	1189.9	1190.0	1189.5	1189.1	1188.6	1188.1
22.5°	1163.2	1164.5	1165.8	1166.0	1165.1	1164.3	1163.4	1162.6
25°	1121.6	1121.8	1122.1	1121.7	1120.8	1119.8	1118.9	1117.9
27.5°	1074.9	1074.3	1073.7	1072.9	1071.7	1070.5	1069.3	1068.1
30°	1042.6	1041.7	1040.7	1039.7	1038.5	1037.3	1036.1	1035.0
32.5°	1009.9	1008.8	1007.7	1006.5	1005.3	1004.1	1002.9	1001.8
35°	958.3	956.6	954.9	953.5	952.3	951.2	950.0	948.8
37.5°	904.1	902.3	900.6	898.9	897.3	895.8	894.2	892.6
40°	866.4	864.1	861.7	859.9	858.7	857.6	856.4	855.2
42.5°	829.9	827.2	824.4	822.7	821.9	821.1	820.3	819.5
45°	773.4	770.8	768.2	766.6	765.8	765.1	764.4	763.7
47.5°	718.7	715.8	712.8	710.5	708.7	706.9	705.1	703.3
50°	680.5	677.2	673.9	671.5	670.1	668.7	667.3	665.9
52.5°	641.3	638.3	635.4	633.1	631.3	629.5	627.7	625.9
55°	583.6	580.8	577.9	575.8	574.4	573.0	571.5	570.1
57.5°	525.8	523.1	520.4	518.4	517.0	515.6	514.3	512.9
60°	486.1	484.0	481.8	480.2	479.0	477.8	476.6	475.5
62.5°	447.3	445.4	443.5	441.9	440.7	439.5	438.4	437.2
65°	391.0	388.6	386.2	384.5	383.3	382.1	380.9	379.7
67.5°	332.9	330.6	328.3	327.0	326.7	326.4	326.0	325.7
70°	296.2	294.3	292.4	291.1	290.4	289.7	289.0	288.3
72.5°	259.5	258.0	256.5	255.4	254.6	253.9	253.2	252.5
75°	206.6	205.6	204.7	204.1	203.9	203.6	203.4	203.2
77.5°	156.4	156.1	155.9	155.4	154.8	154.2	153.6	153.0
80°	124.6	124.1	123.6	123.3	123.0	122.8	122.6	122.3
82.5°	96.0	95.7	95.4	95.2	95.0	94.7	94.5	94.2
85°	55.3	55.3	55.3	55.2	55.0	54.7	54.5	54.2
87.5°	27.9	28.3	28.7	28.9	29.1	29.2	29.3	29.5
90°	37.2	39.2	41.2	42.6	43.2	43.9	44.6	45.2
92.5°	62.1	63.3	64.5	65.3	65.7	66.1	66.5	66.9
95°	116.6	117.6	118.6	119.1	119.1	119.1	119.1	119.1
97.5°	183.7	184.9	186.1	186.7	186.7	186.7	186.7	186.7
100°	232.0	232.7	233.4	233.7	233.7	233.7	233.7	233.7
102.5°	283.2	284.2	285.1	285.7	286.0	286.3	286.5	286.8
105°	360.9	361.9	362.9	363.9	364.9	365.9	366.9	367.9
107.5°	444.9	445.8	446.8	447.2	447.1	447.1	447.0	446.9
110°	500.8	500.1	499.4	499.6	500.6	501.6	502.6	503.6



TEST NUMBER: P332804

CATALOG NUMBER: S124DIW-S795D1560U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	560.9	560.8	560.7	560.7	560.9	561.1	561.3	561.5
115°	653.7	653.4	653.1	652.7	652.4	652.1	651.7	651.4
117.5°	742.9	741.8	740.6	739.7	739.0	738.4	737.7	737.0
120°	803.3	801.7	800.0	799.5	800.2	800.8	801.5	802.2
122.5°	864.7	863.6	862.5	861.3	860.1	858.9	857.7	856.5
125°	954.6	954.0	953.3	952.6	951.9	951.3	950.6	949.9
127.5°	1040.6	1039.9	1039.2	1038.6	1038.1	1037.6	1037.0	1036.5
130°	1100.9	1100.2	1099.5	1098.5	1097.2	1095.9	1094.5	1093.2
132.5°	1157.6	1156.9	1156.2	1155.6	1155.1	1154.6	1154.0	1153.5
135°	1242.6	1242.0	1241.3	1240.4	1239.4	1238.4	1237.4	1236.4
137.5°	1324.9	1324.0	1323.1	1322.8	1323.0	1323.2	1323.4	1323.6
140°	1379.0	1378.7	1378.3	1378.0	1377.7	1377.3	1377.0	1376.7
142.5°	1430.2	1430.1	1430.1	1430.0	1429.9	1429.9	1429.8	1429.7
145°	1507.2	1506.8	1506.5	1505.8	1504.8	1503.8	1502.8	1501.8
147.5°	1577.0	1576.7	1576.4	1576.1	1575.8	1575.5	1575.1	1574.8
150°	1620.9	1620.9	1620.9	1620.8	1620.4	1620.1	1619.8	1619.4
152.5°	1662.3	1663.1	1663.9	1663.9	1663.0	1662.2	1661.3	1660.4
155°	1720.1	1721.4	1722.8	1722.8	1721.4	1720.1	1718.8	1717.4
157.5°	1771.0	1772.0	1773.0	1772.9	1771.8	1770.7	1769.5	1768.4
160°	1802.4	1803.4	1804.4	1804.0	1802.4	1800.7	1799.0	1797.3
162.5°	1830.5	1832.3	1834.1	1834.2	1832.5	1830.9	1829.2	1827.5
165°	1867.7	1869.7	1871.7	1872.1	1870.7	1869.4	1868.0	1866.7
167.5°	1899.1	1901.1	1903.1	1903.1	1901.0	1898.9	1896.8	1894.7
170°	1916.0	1918.0	1920.0	1919.8	1917.5	1915.1	1912.8	1910.4
172.5°	1928.6	1930.8	1933.1	1933.1	1930.7	1928.4	1926.0	1923.7
175°	1942.3	1944.6	1947.0	1947.0	1944.6	1942.3	1939.9	1937.6
177.5°	1949.8	1951.6	1953.5	1953.4	1951.2	1949.1	1947.0	1944.8
180°	1949.6	1949.6	1949.6	1949.6	1949.6	1949.6	1949.6	1949.6

(END OF REPORT)