

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: NEO-RAY

Report Number: P332785

Luminaire Tested: **S124DIW-S795D770U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332785  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIW-S795D770U835-4F0-1E-UDD-F  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 770 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6479.2 lumens  
Efficiency: N/A  
Efficacy: 144.0 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 45  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332785  
CATALOG NUMBER: S124DIW-S795D770U835-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332785

CATALOG NUMBER: S124DIW-S795D770U835-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	53
1	98	94	90	86	91	87	84	81	74	72	70	63	61	59	52	50	49	44
2	90	82	76	71	83	76	71	66	65	61	58	55	52	49	45	43	42	37
3	82	72	65	59	75	67	61	55	57	52	48	49	45	42	40	38	35	31
4	75	64	56	50	69	59	52	47	51	46	41	43	39	36	36	33	30	27
5	69	57	49	43	63	53	46	40	46	40	36	39	34	31	32	29	27	23
6	63	51	43	37	58	48	40	35	41	35	31	35	31	27	29	26	23	21
7	58	46	38	32	54	43	36	31	37	32	27	32	27	24	27	23	21	18
8	54	42	34	29	50	39	32	27	34	28	24	29	25	21	25	21	19	16
9	51	38	31	26	47	36	29	24	31	26	22	27	22	19	23	19	17	15
10	47	35	28	23	44	33	26	22	29	23	20	25	21	17	21	18	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	10717	10717	10717
5°	10749	10619	10697
10°	10681	10533	10585
15°	10552	10384	10410
20°	10381	10198	10207
25°	10185	9986	9958
30°	9945	9737	9648
35°	9697	9477	9351
40°	9438	9180	9013
45°	9169	8889	8719
50°	8871	8629	8363
55°	8549	8294	8024
60°	8226	7918	7677
65°	7862	7559	7253
70°	7456	7081	6805
75°	6834	6503	6338
80°	6081	5835	5686
85°	5317	5122	5020



TEST NUMBER: P332785

CATALOG NUMBER: S124DIW-S795D770U835-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	125.0	1.9
10°-20°	352.2	5.4
20°-30°	518.4	8.0
30°-40°	602.7	9.3
40°-50°	602.7	9.3
50°-60°	527.2	8.1
60°-70°	391.5	6.0
70°-80°	222.4	3.4
80°-90°	67.1	1.0
90°-100°	33.9	0.5
100°-110°	216.4	3.3
110°-120°	414.0	6.4
120°-130°	525.6	8.1
130°-140°	562.3	8.7
140°-150°	525.8	8.1
150°-160°	424.0	6.5
160°-170°	273.5	4.2
170°-180°	94.3	1.5
0°-30°	995.7	15.4
0°-40°	1598.4	24.7
0°-60°	2728.3	42.1
0°-90°	3409.3	52.6
90°-120°	664.4	10.3
90°-150°	2278.1	35.2
90°-180°	3070.0	47.4
0°-180°	6479.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1328	1328	1328	1328	1328	
5°	1326	1322	1310	1321	1320	126
15°	1263	1258	1242	1248	1246	356
25°	1143	1136	1121	1122	1118	526
35°	984	976	962	954	949	615
45°	803	795	779	767	764	619
55°	607	604	589	577	570	544
65°	412	406	396	385	380	407
75°	219	214	208	204	203	233
85°	57	57	55	55	54	63
90°	2	10	16	21	22	5
95°	41	17	16	21	22	52
105°	223	228	232	236	212	234
115°	417	419	419	420	420	410
125°	586	589	588	590	591	523
135°	727	727	730	731	733	560
145°	839	841	841	842	843	524
155°	920	920	918	921	919	424
165°	970	967	966	972	966	274
175°	992	988	989	995	986	94
180°	992	992	992	992	992	



TEST NUMBER: P332785

CATALOG NUMBER: S124DIW-S795D770U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1327.5	1327.5	1327.5	1327.5	1327.5	1327.5	1327.5	1327.5	1327.5	1327.5	1327.5
2.5°	1330.9	1330.3	1329.7	1329.2	1328.6	1327.3	1325.2	1323.1	1321.0	1319.0	1320.8
5°	1326.4	1325.5	1324.5	1323.6	1322.6	1320.8	1318.2	1315.6	1313.0	1310.4	1313.0
7.5°	1314.1	1313.1	1312.2	1311.2	1310.3	1308.4	1305.5	1302.6	1299.7	1296.8	1298.9
10°	1303.0	1302.1	1301.1	1300.2	1299.2	1297.2	1294.1	1291.1	1288.0	1284.9	1286.8
12.5°	1288.5	1287.6	1286.6	1285.7	1284.8	1282.6	1279.4	1276.1	1272.9	1269.6	1271.7
15°	1262.6	1261.6	1260.7	1259.7	1258.8	1256.6	1253.0	1249.5	1245.9	1242.4	1243.8
17.5°	1231.3	1230.1	1228.9	1227.8	1226.6	1224.3	1221.0	1217.6	1214.2	1210.9	1211.8
20°	1208.3	1207.1	1206.0	1204.8	1203.6	1201.2	1197.7	1194.1	1190.6	1187.1	1187.8
22.5°	1183.7	1182.1	1180.5	1179.0	1177.4	1174.9	1171.3	1167.8	1164.2	1160.7	1162.0
25°	1143.4	1141.8	1140.1	1138.5	1136.8	1134.3	1131.0	1127.7	1124.4	1121.1	1121.3
27.5°	1097.5	1095.8	1094.1	1092.4	1090.7	1088.3	1085.2	1082.2	1079.1	1076.0	1075.4
30°	1066.9	1065.0	1063.1	1061.2	1059.3	1056.8	1053.7	1050.7	1047.6	1044.5	1043.6
32.5°	1034.5	1032.8	1031.1	1029.4	1027.7	1025.2	1022.0	1018.7	1015.5	1012.2	1011.1
35°	983.9	982.2	980.6	978.9	977.3	974.8	971.5	968.2	964.9	961.6	959.9
37.5°	930.5	929.0	927.5	926.0	924.4	921.9	918.4	914.8	911.3	907.7	905.9
40°	895.6	893.7	891.8	889.9	888.0	885.3	881.8	878.2	874.7	871.1	868.8
42.5°	858.2	857.0	855.9	854.8	853.6	851.1	847.2	843.3	839.3	835.4	832.7
45°	803.1	801.4	799.8	798.1	796.5	793.7	790.0	786.2	782.4	778.6	776.0
47.5°	745.4	744.3	743.2	742.0	740.9	738.6	735.1	731.6	728.1	724.6	721.6
50°	706.3	705.3	704.4	703.4	702.5	700.4	697.1	693.8	690.4	687.1	683.8
52.5°	668.0	666.9	665.7	664.6	663.4	661.1	657.6	654.1	650.6	647.1	644.2
55°	607.4	606.6	605.9	605.2	604.5	602.5	599.2	595.9	592.6	589.3	586.4
57.5°	549.5	548.7	547.9	547.1	546.3	544.2	541.0	537.7	534.5	531.2	528.5
60°	509.5	508.3	507.1	506.0	504.8	502.6	499.6	496.5	493.4	490.4	488.2
62.5°	470.4	469.4	468.4	467.4	466.4	464.3	461.0	457.7	454.5	451.2	449.3
65°	411.6	410.5	409.3	408.1	406.9	405.1	402.8	400.4	398.0	395.7	393.3
67.5°	352.5	351.4	350.3	349.2	348.2	346.5	344.2	341.9	339.7	337.4	335.1
70°	315.9	314.3	312.6	310.9	309.3	307.5	305.6	303.7	301.8	300.0	298.1
72.5°	276.8	275.1	273.5	271.8	270.1	268.6	267.1	265.5	264.0	262.5	261.0
75°	219.1	217.9	216.8	215.6	214.4	213.2	212.0	210.8	209.7	208.5	207.5
77.5°	164.0	163.5	163.0	162.5	161.9	161.2	160.1	159.1	158.0	157.0	156.7
80°	130.8	130.1	129.4	128.7	128.0	127.4	126.9	126.5	126.0	125.5	125.0
82.5°	98.5	98.2	97.8	97.5	97.2	97.0	96.9	96.8	96.7	96.6	96.3
85°	57.4	57.4	57.4	57.4	57.4	57.2	56.7	56.3	55.8	55.3	55.3
87.5°	22.6	22.7	22.9	23.1	23.3	23.4	23.5	23.5	23.6	23.7	23.9
90°	2.2	4.0	5.9	7.7	9.5	11.1	12.4	13.7	15.0	16.3	17.3
92.5°	9.4	9.5	9.6	9.6	9.7	10.5	11.8	13.1	14.4	15.7	16.7
95°	40.8	35.2	29.6	24.0	18.4	15.7	15.8	16.0	16.2	16.3	17.3
97.5°	86.7	90.2	93.7	97.2	100.7	93.2	74.8	56.4	38.0	19.6	19.7
100°	121.7	124.7	127.7	130.6	133.6	123.7	101.0	78.2	55.4	32.7	29.9
102.5°	160.9	163.1	165.3	167.5	169.6	169.2	166.3	163.3	160.3	157.4	127.1
105°	223.4	224.4	225.4	226.4	227.4	228.3	229.1	229.9	230.8	231.6	233.1
107.5°	281.5	282.0	282.5	283.0	283.5	284.3	285.4	286.5	287.6	288.7	289.5
110°	320.7	321.2	321.7	322.2	322.6	323.4	324.4	325.4	326.4	327.3	327.7



TEST NUMBER: P332785

CATALOG NUMBER: S124DIW-S795D770U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	358.7	359.6	360.5	361.3	362.2	362.9	363.4	363.8	364.3	364.8	364.7
115°	417.2	417.7	418.2	418.6	419.1	419.3	419.1	419.0	418.8	418.6	419.0
117.5°	469.9	470.5	471.2	471.8	472.5	473.0	473.4	473.7	474.1	474.5	474.4
120°	505.5	506.2	506.8	507.5	508.1	508.4	508.2	508.1	507.9	507.7	508.1
122.5°	538.8	539.1	539.5	539.9	540.3	540.6	540.9	541.1	541.3	541.6	541.8
125°	586.4	587.1	587.7	588.4	589.0	589.2	588.9	588.6	588.2	587.9	588.4
127.5°	631.5	631.7	631.9	632.0	632.2	632.7	633.4	634.2	634.9	635.7	635.6
130°	660.6	660.8	661.0	661.1	661.3	661.6	662.1	662.6	663.1	663.6	663.8
132.5°	687.4	687.7	688.0	688.2	688.5	689.0	689.6	690.3	690.9	691.5	691.7
135°	727.4	727.3	727.1	726.9	726.8	727.0	727.7	728.3	729.0	729.7	730.0
137.5°	762.9	763.0	763.1	763.1	763.2	763.6	764.3	765.0	765.8	766.5	766.8
140°	786.1	786.4	786.7	787.1	787.4	787.7	788.1	788.4	788.7	789.1	789.5
142.5°	806.9	807.5	808.1	808.6	809.2	809.6	809.8	810.0	810.2	810.4	810.8
145°	838.8	839.3	839.8	840.3	840.8	841.0	841.0	841.0	841.0	841.0	841.2
147.5°	864.2	865.1	866.0	866.9	867.9	868.2	868.1	867.9	867.7	867.6	867.7
150°	882.6	883.2	883.9	884.6	885.2	885.5	885.3	885.1	885.0	884.8	884.8
152.5°	898.0	898.5	899.1	899.6	900.1	900.2	899.9	899.7	899.4	899.1	899.3
155°	919.7	919.9	920.0	920.2	920.4	920.2	919.7	919.2	918.7	918.2	918.9
157.5°	938.0	937.9	937.8	937.7	937.6	937.2	936.7	936.1	935.5	935.0	935.8
160°	948.6	948.1	947.7	947.2	946.7	946.3	946.2	946.0	945.8	945.7	946.7
162.5°	958.1	957.5	956.9	956.3	955.6	955.2	955.1	954.9	954.7	954.6	955.6
165°	970.2	969.3	968.5	967.7	966.9	966.5	966.5	966.5	966.5	966.5	967.8
167.5°	979.7	978.8	978.0	977.1	976.2	975.8	975.7	975.6	975.5	975.4	976.8
170°	985.0	984.0	983.0	982.0	981.1	980.6	980.8	981.0	981.1	981.3	982.6
172.5°	988.6	987.6	986.6	985.6	984.6	984.2	984.4	984.5	984.7	984.9	986.2
175°	992.4	991.4	990.5	989.5	988.5	988.1	988.2	988.4	988.6	988.7	990.2
177.5°	994.2	993.3	992.4	991.4	990.5	990.2	990.5	990.7	991.0	991.2	992.3
180°	992.4	992.4	992.4	992.4	992.4	992.4	992.4	992.4	992.4	992.4	992.4



TEST NUMBER: P332785

CATALOG NUMBER: S124DIW-S795D770U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1327.5	1327.5	1327.5	1327.5	1327.5	1327.5	1327.5	1327.5
2.5°	1322.7	1324.6	1326.5	1327.4	1327.2	1327.0	1326.8	1326.6
5°	1315.6	1318.2	1320.8	1321.9	1321.4	1321.0	1320.5	1320.0
7.5°	1301.0	1303.1	1305.1	1306.0	1305.8	1305.5	1305.2	1304.9
10°	1288.7	1290.6	1292.5	1293.2	1292.7	1292.2	1291.8	1291.3
12.5°	1273.8	1275.8	1277.9	1278.6	1278.0	1277.3	1276.6	1276.0
15°	1245.2	1246.6	1248.0	1248.4	1247.7	1247.0	1246.3	1245.6
17.5°	1212.7	1213.6	1214.5	1214.7	1214.2	1213.7	1213.3	1212.8
20°	1188.5	1189.2	1189.9	1190.0	1189.5	1189.1	1188.6	1188.1
22.5°	1163.2	1164.5	1165.8	1166.0	1165.1	1164.3	1163.4	1162.6
25°	1121.6	1121.8	1122.1	1121.7	1120.8	1119.8	1118.9	1117.9
27.5°	1074.9	1074.3	1073.7	1072.9	1071.7	1070.5	1069.3	1068.1
30°	1042.6	1041.7	1040.7	1039.7	1038.5	1037.3	1036.1	1035.0
32.5°	1009.9	1008.8	1007.7	1006.5	1005.3	1004.1	1002.9	1001.8
35°	958.3	956.6	954.9	953.5	952.3	951.2	950.0	948.8
37.5°	904.1	902.3	900.6	898.9	897.3	895.8	894.2	892.6
40°	866.4	864.1	861.7	859.9	858.7	857.6	856.4	855.2
42.5°	829.9	827.2	824.4	822.7	821.9	821.1	820.3	819.5
45°	773.4	770.8	768.2	766.6	765.8	765.1	764.4	763.7
47.5°	718.7	715.8	712.8	710.5	708.7	706.9	705.1	703.3
50°	680.5	677.2	673.9	671.5	670.1	668.7	667.3	665.9
52.5°	641.3	638.3	635.4	633.1	631.3	629.5	627.7	625.9
55°	583.6	580.8	577.9	575.8	574.4	573.0	571.5	570.1
57.5°	525.8	523.1	520.4	518.4	517.0	515.6	514.3	512.9
60°	486.1	484.0	481.8	480.2	479.0	477.8	476.6	475.5
62.5°	447.3	445.4	443.5	441.9	440.7	439.5	438.4	437.2
65°	391.0	388.6	386.2	384.5	383.3	382.1	380.9	379.7
67.5°	332.9	330.6	328.3	327.0	326.7	326.4	326.0	325.7
70°	296.2	294.3	292.4	291.1	290.4	289.7	289.0	288.3
72.5°	259.5	258.0	256.5	255.4	254.6	253.9	253.2	252.5
75°	206.6	205.6	204.7	204.1	203.9	203.6	203.4	203.2
77.5°	156.4	156.1	155.9	155.4	154.8	154.2	153.6	153.0
80°	124.6	124.1	123.6	123.3	123.0	122.8	122.6	122.3
82.5°	96.0	95.7	95.4	95.2	95.0	94.7	94.5	94.2
85°	55.3	55.3	55.3	55.2	55.0	54.7	54.5	54.2
87.5°	24.1	24.3	24.5	24.6	24.7	24.7	24.8	24.9
90°	18.3	19.3	20.3	20.9	21.3	21.6	21.9	22.3
92.5°	17.7	18.7	19.7	20.2	20.3	20.4	20.4	20.5
95°	18.3	19.3	20.3	20.9	21.0	21.2	21.4	21.5
97.5°	19.8	19.9	20.0	20.1	20.3	20.5	20.6	20.8
100°	27.1	24.2	21.4	20.1	20.3	20.5	20.6	20.8
102.5°	96.9	66.6	36.4	21.2	21.3	21.3	21.3	21.4
105°	234.6	236.0	237.5	235.3	229.4	223.4	217.5	211.6
107.5°	290.2	290.9	291.7	292.3	293.0	293.6	294.2	294.8
110°	328.0	328.3	328.7	329.1	329.6	330.1	330.6	331.1





TEST NUMBER: P332785

CATALOG NUMBER: S124DIW-S795D770U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	364.6	364.6	364.5	364.8	365.4	366.0	366.7	367.3
115°	419.3	419.6	420.0	420.1	420.1	420.1	420.1	420.1
117.5°	474.3	474.3	474.2	474.1	474.1	474.0	473.9	473.9
120°	508.4	508.7	509.0	509.0	508.7	508.4	508.1	507.7
122.5°	542.0	542.2	542.4	542.3	542.0	541.6	541.3	541.0
125°	588.9	589.4	589.9	590.2	590.4	590.5	590.7	590.9
127.5°	635.5	635.4	635.3	635.2	635.1	634.9	634.8	634.7
130°	663.9	664.1	664.3	664.3	664.3	664.3	664.3	664.3
132.5°	691.8	692.0	692.2	692.2	692.1	691.9	691.8	691.7
135°	730.3	730.7	731.0	731.3	731.6	732.0	732.3	732.6
137.5°	767.2	767.6	767.9	768.1	768.0	767.9	767.8	767.7
140°	790.0	790.5	791.0	791.4	791.5	791.7	791.9	792.0
142.5°	811.2	811.5	811.9	812.1	812.1	812.1	812.2	812.2
145°	841.3	841.5	841.7	841.9	842.2	842.6	842.9	843.2
147.5°	867.8	868.0	868.1	868.3	868.4	868.6	868.8	868.9
150°	884.8	884.8	884.8	884.9	885.1	885.2	885.4	885.5
152.5°	899.6	899.8	900.1	900.2	900.1	900.0	899.9	899.8
155°	919.5	920.2	920.8	920.9	920.4	919.9	919.4	919.0
157.5°	936.7	937.6	938.4	938.4	937.6	936.7	935.8	935.0
160°	947.7	948.6	949.6	949.6	948.6	947.7	946.7	945.7
162.5°	956.6	957.5	958.5	958.5	957.4	956.2	955.1	954.0
165°	969.1	970.4	971.7	971.7	970.2	968.7	967.2	965.7
167.5°	978.3	979.7	981.2	981.1	979.4	977.8	976.1	974.5
170°	983.9	985.3	986.6	986.4	984.8	983.1	981.5	979.8
172.5°	987.5	988.8	990.1	989.9	988.1	986.4	984.6	982.8
175°	991.7	993.2	994.7	994.4	992.4	990.5	988.5	986.5
177.5°	993.4	994.4	995.5	995.2	993.6	992.0	990.5	988.9
180°	992.4	992.4	992.4	992.4	992.4	992.4	992.4	992.4

(END OF REPORT)