

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332782-927

Luminaire Tested: **S124DIW-S795D770U927-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332782-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIW-S795D770U927-4F0-1E-UDD-A1  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 795 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 770 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4917.5 lumens  
Efficiency: N/A  
Efficacy: 109.3 lumens/watt  
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 45  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332782-927

CATALOG NUMBER: S124DIW-S795D770U927-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P332782-927

CATALOG NUMBER: S124DIW-S795D770U927-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	63	63	63	57
1	100	95	91	88	93	89	86	83	77	74	72	66	64	63	56	55	53	49
2	91	84	77	72	84	78	73	68	68	64	60	58	55	53	49	47	45	41
3	83	74	66	61	77	69	63	57	60	55	51	52	48	45	44	41	39	35
4	76	65	58	52	71	61	54	49	53	48	44	46	42	39	39	36	34	30
5	70	58	50	44	65	55	48	42	48	42	38	42	37	34	36	32	30	27
6	65	53	44	39	60	49	42	37	43	38	33	38	33	30	32	29	26	23
7	60	48	40	34	56	45	38	32	39	34	29	34	30	26	30	26	23	21
8	56	43	35	30	52	41	34	29	36	30	26	32	27	24	27	24	21	19
9	52	40	32	27	48	37	30	26	33	27	23	29	24	21	25	22	19	17
10	48	36	29	24	45	34	28	23	30	25	21	27	22	19	23	20	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	8211	8211	8211	8211
5°	9669	8232	7266	8232
10°	11576	8196	6542	8196
15°	13697	8113	6007	8113
20°	15253	8028	5530	8028
25°	15499	7904	5201	7904
30°	13189	7784	5097	7784
35°	10139	7591	5099	7591
40°	7904	7361	5195	7361
45°	6590	7018	5281	7018
50°	5800	6599	5461	6599
55°	5313	6096	5681	6096
60°	4979	5646	5945	5646
65°	4634	5142	6164	5142
70°	4237	4645	6305	4645
75°	3787	4086	6229	4086
80°	3175	3347	6034	3347
85°	2343	2418	5771	2418



TEST NUMBER: P332782-927

CATALOG NUMBER: S124DIW-S795D770U927-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	99.1	2.0
10°-20°	305.4	6.2
20°-30°	484.3	9.8
30°-40°	539.0	11.0
40°-50°	490.6	10.0
50°-60°	400.9	8.2
60°-70°	286.2	5.8
70°-80°	157.6	3.2
80°-90°	45.3	0.9
90°-100°	50.1	1.0
100°-110°	148.5	3.0
110°-120°	252.1	5.1
120°-130°	332.4	6.8
130°-140°	373.3	7.6
140°-150°	366.9	7.5
150°-160°	308.6	6.3
160°-170°	205.3	4.2
170°-180°	71.9	1.5
0°-30°	888.8	18.1
0°-40°	1427.7	29.0
0°-60°	2319.2	47.2
0°-90°	2808.3	57.1
90°-120°	450.8	9.2
90°-150°	1523.4	31.0
90°-180°	2109.0	42.9
0°-180°	4917.5	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1017	1017	1017	1017	1017	
5°	1193	1016	897	1016	1193	121
15°	1639	971	719	971	1639	463
25°	1740	887	584	887	1740	767
35°	1029	770	517	770	1029	653
45°	577	615	463	615	577	455
55°	378	433	404	433	378	341
65°	243	269	323	269	243	240
75°	121	131	200	131	121	129
85°	25	26	62	26	25	31
90°	18	2	18	2	18	10
95°	46	35	46	35	46	48
105°	144	137	144	137	144	151
115°	254	256	254	256	254	251
125°	370	373	370	373	370	330
135°	482	482	482	482	482	372
145°	586	585	586	585	586	366
155°	670	670	670	670	670	308
165°	728	730	728	730	728	205
175°	756	759	756	759	756	72
180°	760	760	760	760	760	



TEST NUMBER: P332782-927

CATALOG NUMBER: S124DIW-S795D770U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1017.1	1017.1	1017.1	1017.1	1017.1	1017.1	1017.1	1017.1	1017.1	1017.1	1017.1
2.5°	1082.4	1082.1	1078.7	1078.1	1075.7	1072.7	1072.0	1066.6	1055.8	1050.8	1049.4
5°	1193.2	1201.6	1190.6	1188.5	1187.2	1173.4	1166.2	1157.8	1138.4	1127.0	1118.2
7.5°	1325.3	1326.3	1321.5	1317.6	1306.9	1294.7	1276.6	1257.2	1234.1	1210.1	1192.0
10°	1412.2	1415.6	1410.2	1409.3	1387.8	1374.4	1347.3	1324.6	1298.5	1269.4	1242.9
12.5°	1504.0	1499.2	1496.4	1478.4	1474.4	1449.9	1418.5	1395.0	1354.8	1321.4	1286.0
15°	1638.9	1629.7	1623.7	1598.9	1586.7	1552.5	1519.2	1493.6	1440.9	1390.8	1352.8
17.5°	1718.1	1727.4	1713.7	1703.5	1671.9	1648.0	1614.0	1560.0	1518.9	1456.6	1408.7
20°	1775.4	1776.2	1768.7	1758.2	1733.3	1703.0	1665.9	1606.9	1557.6	1495.6	1430.0
22.5°	1790.9	1791.1	1787.9	1778.1	1759.2	1734.6	1697.3	1648.0	1588.2	1520.9	1455.2
25°	1740.0	1738.4	1742.2	1753.1	1745.9	1738.4	1716.8	1680.2	1624.6	1553.4	1482.6
27.5°	1550.9	1562.6	1584.0	1610.9	1636.9	1656.7	1662.2	1654.7	1620.3	1561.7	1487.6
30°	1414.8	1429.1	1445.1	1472.0	1524.3	1554.3	1587.1	1611.9	1598.1	1551.3	1482.2
32.5°	1265.1	1268.7	1292.4	1323.1	1371.0	1428.5	1480.6	1531.1	1547.8	1523.3	1465.7
35°	1028.8	1034.7	1060.4	1090.8	1149.4	1219.7	1298.1	1368.0	1425.7	1448.9	1419.4
37.5°	839.6	856.5	874.6	907.3	958.9	1022.2	1103.6	1194.1	1280.1	1337.8	1347.5
40°	750.0	760.5	773.6	798.4	842.2	904.6	974.5	1078.2	1169.6	1252.1	1279.1
42.5°	679.1	685.3	693.3	715.8	749.2	811.2	875.0	966.2	1058.0	1156.7	1201.9
45°	577.2	583.5	597.0	610.1	635.3	678.3	737.7	812.7	905.0	1000.2	1083.6
47.5°	503.6	507.6	515.6	529.6	551.0	579.4	627.7	690.4	775.9	868.3	957.2
50°	461.8	465.1	471.4	484.1	500.5	525.8	565.4	624.0	690.9	784.1	871.2
52.5°	428.7	430.1	434.7	443.3	456.4	477.6	510.1	558.6	620.8	703.9	790.8
55°	377.5	379.2	383.4	389.8	401.1	414.5	439.4	475.6	530.0	602.1	677.5
57.5°	335.3	336.5	340.1	342.5	351.9	362.8	382.0	407.8	449.0	510.1	577.4
60°	308.4	307.5	311.8	313.9	320.2	329.5	344.2	369.1	404.9	454.2	516.1
62.5°	282.1	280.9	284.5	287.2	290.9	298.8	310.9	330.3	359.4	403.9	457.5
65°	242.6	241.0	243.1	246.4	249.9	254.1	262.9	280.2	303.3	335.3	376.2
67.5°	203.0	204.9	205.2	206.8	208.8	214.5	220.6	232.8	249.1	274.8	309.4
70°	179.5	179.9	181.6	181.6	182.8	187.9	193.0	200.1	216.1	239.7	267.9
72.5°	155.9	157.6	157.0	158.4	159.2	162.6	166.4	173.2	186.8	204.3	228.1
75°	121.4	122.6	122.6	123.0	124.3	125.6	128.5	133.6	143.2	156.3	172.8
77.5°	88.5	88.6	89.2	90.8	90.8	92.8	95.0	99.0	103.8	112.7	122.8
80°	68.3	69.1	68.7	69.6	69.6	71.2	72.0	77.1	79.2	85.1	93.1
82.5°	50.1	50.9	50.8	52.0	52.7	53.0	54.2	56.2	58.3	63.5	66.8
85°	25.3	26.1	25.3	26.1	27.4	27.8	29.1	29.5	31.2	32.5	35.4
87.5°	10.9	11.9	11.9	12.1	12.8	13.0	13.2	12.7	13.9	14.0	15.2
90°	17.7	17.3	17.1	16.9	16.6	16.1	15.3	14.5	13.7	12.9	11.9
92.5°	26.1	26.0	25.8	25.7	25.5	25.2	24.7	24.2	23.8	23.3	22.6
95°	46.4	46.4	46.4	46.4	46.4	46.3	45.9	45.5	45.1	44.7	43.8
97.5°	72.8	72.8	72.8	72.8	72.8	72.6	72.1	71.6	71.1	70.7	69.6
100°	91.1	91.1	91.1	91.1	91.1	91.0	90.7	90.5	90.2	90.0	88.8
102.5°	111.9	111.7	111.6	111.5	111.4	111.1	110.8	110.4	110.1	109.7	108.6
105°	143.5	143.1	142.7	142.3	141.9	141.5	141.1	140.7	140.3	139.9	139.4
107.5°	174.3	174.3	174.4	174.4	174.4	174.2	173.8	173.5	173.1	172.8	172.7
110°	196.4	196.0	195.6	195.2	194.8	194.7	195.0	195.3	195.5	195.7	195.9



TEST NUMBER: P332782-927

CATALOG NUMBER: S124DIW-S795D770U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	219.0	218.9	218.8	218.7	218.6	218.6	218.6	218.7	218.8	218.8	219.0
115°	254.0	254.1	254.3	254.4	254.5	254.6	254.8	254.9	255.0	255.2	255.4
117.5°	287.4	287.6	287.9	288.2	288.4	288.8	289.2	289.7	290.1	290.6	290.7
120°	312.8	312.5	312.3	312.0	311.7	312.0	312.6	313.2	313.9	314.6	315.0
122.5°	334.0	334.5	334.9	335.3	335.8	336.3	336.8	337.2	337.6	338.1	338.3
125°	370.4	370.7	370.9	371.2	371.5	371.7	372.0	372.2	372.5	372.7	372.9
127.5°	404.2	404.3	404.6	404.8	405.0	405.2	405.5	405.8	406.0	406.3	406.5
130°	426.3	426.7	427.3	427.9	428.3	428.7	429.0	429.3	429.5	429.8	429.8
132.5°	449.8	450.0	450.2	450.4	450.6	450.8	451.1	451.4	451.6	451.9	452.0
135°	482.1	482.5	482.9	483.3	483.7	484.0	484.3	484.5	484.8	485.1	485.1
137.5°	516.1	516.0	515.9	515.9	515.8	515.9	516.3	516.6	516.9	517.3	517.1
140°	536.8	536.9	537.0	537.2	537.3	537.4	537.6	537.7	537.8	538.0	538.0
142.5°	557.5	557.5	557.5	557.5	557.6	557.6	557.6	557.7	557.7	557.7	557.9
145°	585.6	586.0	586.4	586.8	587.2	587.4	587.6	587.7	587.8	588.0	587.8
147.5°	614.0	614.2	614.3	614.4	614.6	614.7	614.8	614.9	615.0	615.1	615.2
150°	631.4	631.6	631.7	631.8	632.0	632.1	632.1	632.1	632.1	632.1	632.1
152.5°	647.5	647.8	648.2	648.5	648.8	648.8	648.5	648.2	647.8	647.5	647.5
155°	669.7	670.2	670.7	671.2	671.8	671.8	671.2	670.7	670.2	669.7	669.8
157.5°	689.5	690.0	690.5	690.9	691.3	691.3	690.9	690.5	690.1	689.8	689.8
160°	700.8	701.5	702.1	702.8	703.5	703.6	703.2	702.8	702.4	702.0	702.1
162.5°	712.6	713.3	713.9	714.5	715.2	715.2	714.5	713.8	713.0	712.3	712.5
165°	727.9	728.4	728.9	729.4	730.0	729.8	729.0	728.3	727.5	726.7	727.0
167.5°	738.8	739.7	740.5	741.2	742.0	742.0	741.2	740.5	739.7	738.9	738.9
170°	745.0	745.8	746.8	747.7	748.6	748.7	747.9	747.1	746.3	745.5	745.4
172.5°	750.1	751.0	751.9	752.8	753.8	753.8	752.9	752.0	751.1	750.2	750.2
175°	755.5	756.5	757.3	758.3	759.1	759.1	758.3	757.3	756.5	755.5	755.7
177.5°	758.4	759.1	760.0	760.8	761.7	761.8	761.0	760.3	759.5	758.8	758.8
180°	760.2	760.2	760.2	760.2	760.2	760.2	760.2	760.2	760.2	760.2	760.2



TEST NUMBER: P332782-927

CATALOG NUMBER: S124DIW-S795D770U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1017.1	1017.1	1017.1	1017.1	1017.1	1017.1	1017.1	1017.1	1017.1	1017.1	1017.1
2.5°	1049.7	1045.0	1041.6	1038.9	1031.6	1027.1	1023.8	1019.1	1013.7	1008.0	1000.8
5°	1109.3	1095.0	1084.5	1068.4	1053.3	1040.6	1027.6	1015.8	1001.5	985.9	974.5
7.5°	1172.0	1150.6	1123.3	1099.6	1073.0	1049.8	1029.1	1007.9	985.8	964.4	944.8
10°	1211.7	1184.3	1154.0	1118.2	1084.5	1054.6	1026.7	999.8	973.7	947.5	925.2
12.5°	1254.5	1220.4	1175.5	1133.7	1095.9	1055.9	1022.4	989.4	957.8	930.3	904.3
15°	1311.9	1262.7	1210.9	1154.8	1105.1	1058.4	1012.4	970.7	935.3	899.0	873.8
17.5°	1347.3	1286.3	1227.0	1168.5	1108.3	1049.3	999.8	951.6	907.4	871.3	839.5
20°	1370.6	1309.9	1236.1	1177.6	1106.0	1045.3	988.0	934.5	888.1	849.8	816.9
22.5°	1390.8	1320.6	1246.9	1169.8	1098.5	1034.2	971.5	917.6	870.3	829.9	798.4
25°	1401.7	1321.2	1241.2	1164.5	1083.6	1007.3	950.5	887.3	836.7	794.2	760.5
27.5°	1402.9	1316.8	1226.3	1141.1	1057.6	986.6	914.7	858.3	805.8	760.8	728.4
30°	1399.2	1309.5	1212.1	1119.8	1036.0	958.9	896.6	835.0	781.6	736.9	703.1
32.5°	1387.3	1294.0	1193.9	1096.2	1009.4	934.0	869.6	811.1	759.0	714.9	679.6
35°	1353.3	1261.0	1154.4	1052.9	963.9	887.7	829.6	770.2	718.0	676.2	642.1
37.5°	1299.9	1216.5	1108.1	1003.1	915.8	839.2	781.6	727.9	680.7	638.3	603.4
40°	1253.4	1180.1	1071.4	969.0	874.6	801.8	747.8	698.5	651.8	611.7	578.5
42.5°	1199.8	1135.9	1035.7	927.2	836.2	763.0	710.4	666.1	622.1	585.1	551.8
45°	1104.2	1062.2	967.7	867.5	772.7	703.6	653.5	614.7	577.7	541.4	513.6
47.5°	994.3	973.5	894.1	798.8	708.8	640.7	597.2	561.4	528.9	498.3	473.7
50°	920.6	910.5	841.8	750.0	664.0	599.9	556.1	525.4	497.6	470.6	447.4
52.5°	847.8	847.4	785.5	701.4	621.9	560.2	516.7	488.0	463.9	442.0	421.1
55°	736.5	748.2	699.8	624.8	553.6	498.0	458.8	433.1	416.3	398.2	382.5
57.5°	634.2	653.8	613.9	547.8	488.4	437.1	403.1	383.7	365.8	354.8	343.5
60°	567.5	586.1	554.8	499.2	443.2	399.4	366.9	349.7	334.1	326.5	318.5
62.5°	508.2	524.7	501.6	450.0	401.4	359.3	331.9	315.3	304.8	296.5	291.2
65°	423.4	437.3	417.6	380.0	338.3	304.6	282.3	269.2	259.1	255.7	249.9
67.5°	342.3	354.9	344.2	312.4	278.9	253.3	235.9	223.4	217.4	214.4	210.2
70°	294.1	306.7	295.3	267.5	241.9	220.4	203.9	196.8	190.4	189.2	183.2
72.5°	253.3	261.9	250.5	228.8	206.8	188.7	175.9	168.4	165.2	162.9	159.7
75°	190.0	197.6	190.0	173.2	157.6	145.0	134.0	131.0	127.2	126.0	123.9
77.5°	134.5	141.1	135.2	124.7	113.0	103.3	97.4	93.6	92.8	90.5	91.6
80°	102.8	107.0	101.6	94.3	85.1	78.3	74.1	72.0	69.6	68.7	70.3
82.5°	73.8	75.7	72.9	68.0	61.2	56.8	53.9	51.5	51.0	51.2	51.2
85°	38.3	37.9	37.5	33.3	31.2	28.2	26.5	26.1	25.7	26.5	27.4
87.5°	15.0	15.1	14.6	13.0	11.6	10.4	9.7	9.1	9.7	10.4	11.0
90°	10.9	9.8	8.8	7.5	6.1	4.7	3.2	1.7	3.2	4.7	6.1
92.5°	21.8	21.1	20.4	19.2	17.5	15.8	14.3	12.6	14.3	15.8	17.5
95°	42.9	41.9	41.0	40.0	38.8	37.6	36.4	35.3	36.4	37.6	38.8
97.5°	68.5	67.5	66.4	65.4	64.4	63.5	62.6	61.6	62.6	63.5	64.4
100°	87.6	86.4	85.2	84.4	83.9	83.3	82.9	82.3	82.9	83.3	83.9
102.5°	107.6	106.5	105.4	104.8	104.6	104.3	104.2	103.9	104.2	104.3	104.6
105°	138.9	138.4	137.8	137.5	137.4	137.3	137.1	137.0	137.1	137.3	137.4
107.5°	172.6	172.5	172.5	172.3	172.1	172.0	171.8	171.7	171.8	172.0	172.1
110°	196.1	196.1	196.3	196.2	196.0	195.7	195.4	195.2	195.4	195.7	196.0





TEST NUMBER: P332782-927

CATALOG NUMBER: S124DIW-S795D770U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	219.3	219.5	219.8	219.8	219.8	219.8	219.7	219.7	219.7	219.8	219.8
115°	255.7	256.0	256.2	256.4	256.4	256.4	256.4	256.4	256.4	256.4	256.4
117.5°	291.0	291.1	291.3	291.4	291.2	291.1	291.0	290.9	291.0	291.1	291.2
120°	315.4	315.8	316.1	316.1	315.5	315.0	314.5	313.9	314.5	315.0	315.5
122.5°	338.4	338.7	338.8	338.8	338.6	338.3	338.2	337.9	338.2	338.3	338.6
125°	373.0	373.1	373.3	373.4	373.4	373.4	373.4	373.4	373.4	373.4	373.4
127.5°	406.7	406.9	407.1	407.0	406.6	406.2	405.8	405.4	405.8	406.2	406.6
130°	429.8	429.8	429.8	429.6	429.2	428.8	428.4	428.0	428.4	428.8	429.2
132.5°	452.1	452.2	452.3	452.3	451.9	451.6	451.4	451.1	451.4	451.6	451.9
135°	485.1	485.1	485.1	484.7	483.9	483.1	482.3	481.6	482.3	483.1	483.9
137.5°	516.8	516.7	516.4	516.2	515.8	515.4	515.1	514.7	515.1	515.4	515.8
140°	538.0	538.0	538.0	537.8	537.6	537.3	537.0	536.8	537.0	537.3	537.6
142.5°	557.9	558.0	558.2	558.1	557.8	557.5	557.3	557.0	557.3	557.5	557.8
145°	587.7	587.6	587.4	587.1	586.6	586.1	585.5	585.0	585.5	586.1	586.6
147.5°	615.3	615.4	615.5	615.3	614.7	614.0	613.4	612.8	613.4	614.0	614.7
150°	632.1	632.1	632.1	631.8	631.3	630.7	630.2	629.7	630.2	630.7	631.3
152.5°	647.4	647.2	647.1	647.0	646.7	646.3	646.0	645.7	646.0	646.3	646.7
155°	669.9	670.0	670.2	670.3	670.3	670.3	670.3	670.3	670.3	670.3	670.3
157.5°	689.8	689.8	689.9	690.0	690.2	690.5	690.7	690.9	690.7	690.5	690.2
160°	702.3	702.4	702.5	702.7	702.8	702.9	703.1	703.2	703.1	702.9	702.8
162.5°	712.6	712.7	712.9	713.1	713.4	713.8	714.2	714.5	714.2	713.8	713.4
165°	727.2	727.5	727.8	728.1	728.5	728.9	729.3	729.7	729.3	728.9	728.5
167.5°	738.9	738.9	738.8	739.1	739.7	740.2	740.8	741.2	740.8	740.2	739.7
170°	745.3	745.1	745.0	745.3	745.9	746.6	747.2	747.9	747.2	746.6	745.9
172.5°	750.2	750.1	750.1	750.4	750.9	751.5	752.0	752.6	752.0	751.5	750.9
175°	755.7	755.9	756.1	756.5	757.1	757.7	758.4	759.1	758.4	757.7	757.1
177.5°	758.8	758.8	758.8	759.1	759.6	760.1	760.7	761.1	760.7	760.1	759.6
180°	760.2	760.2	760.2	760.2	760.2	760.2	760.2	760.2	760.2	760.2	760.2



TEST NUMBER: P332782-927

CATALOG NUMBER: S124DIW-S795D770U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1017.1	1017.1	1017.1	1017.1	1017.1	1017.1	1017.1	1017.1	1017.1	1017.1	1017.1
2.5°	997.5	994.5	990.1	984.0	979.0	973.6	972.2	970.2	974.2	970.9	969.9
5°	964.8	955.9	944.6	931.5	923.9	913.0	910.9	906.7	902.5	902.1	897.8
7.5°	930.2	917.2	902.3	889.0	876.6	864.7	856.9	855.2	849.0	845.3	841.1
10°	907.9	891.9	874.6	862.0	847.7	835.0	826.2	821.2	816.9	812.3	808.1
12.5°	881.6	864.6	850.4	836.7	819.7	810.1	795.5	786.8	785.9	786.0	775.1
15°	851.0	834.2	812.3	792.9	783.6	765.1	757.1	746.9	740.7	734.4	729.3
17.5°	816.1	795.1	778.0	755.7	738.1	723.3	712.8	706.7	697.2	688.2	681.8
20°	794.2	771.8	753.8	730.2	710.7	692.6	683.8	675.3	668.2	660.6	653.5
22.5°	771.9	748.6	726.4	703.5	685.5	666.4	657.8	646.3	639.5	635.3	628.2
25°	736.9	711.6	686.3	664.4	645.9	629.0	617.7	608.8	601.2	597.9	593.2
27.5°	698.8	673.7	649.3	624.4	603.3	591.1	582.0	575.4	570.9	566.5	564.4
30°	674.5	648.4	622.3	599.1	579.7	567.5	559.0	554.4	551.0	549.0	546.8
32.5°	649.9	624.2	596.7	575.5	558.2	547.3	540.9	536.2	534.6	533.8	533.1
35°	610.5	584.4	559.0	540.1	523.7	519.5	514.0	511.5	510.6	513.6	514.8
37.5°	572.3	548.0	524.8	506.4	495.7	489.5	487.6	487.7	490.8	493.4	496.4
40°	547.7	524.1	502.2	486.2	476.1	472.3	471.4	473.6	476.9	479.9	483.2
42.5°	523.8	500.5	480.6	465.6	458.6	455.1	455.6	457.7	462.4	466.0	471.1
45°	486.6	467.2	447.8	435.6	429.8	430.6	430.6	434.4	439.0	444.5	450.0
47.5°	451.6	432.1	416.1	405.9	402.8	402.1	404.5	409.4	416.1	422.9	430.5
50°	428.0	409.5	395.6	386.3	382.9	384.2	387.6	392.2	400.2	408.7	416.7
52.5°	404.1	387.3	374.4	365.8	363.5	365.7	369.1	376.4	383.4	392.5	402.2
55°	366.9	352.6	342.5	336.2	335.3	336.6	340.4	348.4	358.5	369.9	379.2
57.5°	329.9	318.0	308.7	304.4	304.8	305.9	312.2	321.7	332.5	344.6	356.6
60°	305.1	294.1	286.5	283.1	283.5	286.1	293.7	302.5	316.0	327.8	340.4
62.5°	281.5	271.8	264.6	261.6	260.9	266.5	273.8	283.0	296.4	309.6	323.2
65°	243.5	235.9	230.0	228.4	229.7	233.9	243.1	255.3	266.7	280.6	294.9
67.5°	206.4	200.2	196.1	196.9	198.4	204.7	212.5	222.9	235.8	250.3	264.4
70°	182.8	177.0	173.6	174.0	176.5	184.1	190.8	201.4	215.3	230.0	241.9
72.5°	158.6	154.7	151.7	153.4	156.0	161.2	169.6	180.1	192.3	206.1	218.6
75°	121.8	121.8	120.1	121.4	125.2	130.2	136.5	147.4	159.7	170.6	180.8
77.5°	90.3	89.4	90.5	92.1	94.2	100.2	107.4	115.3	124.5	135.4	143.8
80°	69.1	69.6	71.6	74.1	75.0	79.6	87.2	94.3	101.6	110.8	118.8
82.5°	51.9	52.4	53.4	56.6	57.4	62.4	67.3	74.5	81.0	87.2	93.9
85°	28.2	28.2	30.3	31.6	33.7	37.1	40.0	44.2	50.1	54.3	60.7
87.5°	12.3	12.5	14.1	15.0	16.2	18.1	18.9	22.8	24.3	26.1	29.3
90°	7.5	8.8	9.8	10.9	11.9	12.9	13.7	14.5	15.3	16.1	16.6
92.5°	19.2	20.4	21.1	21.8	22.6	23.3	23.8	24.2	24.7	25.2	25.5
95°	40.0	41.0	41.9	42.9	43.8	44.7	45.1	45.5	45.9	46.3	46.4
97.5°	65.4	66.4	67.5	68.5	69.6	70.7	71.1	71.6	72.1	72.6	72.8
100°	84.4	85.2	86.4	87.6	88.8	90.0	90.2	90.5	90.7	91.0	91.1
102.5°	104.8	105.4	106.5	107.6	108.6	109.7	110.1	110.4	110.8	111.1	111.4
105°	137.5	137.8	138.4	138.9	139.4	139.9	140.3	140.7	141.1	141.5	141.9
107.5°	172.3	172.5	172.5	172.6	172.7	172.8	173.1	173.5	173.8	174.2	174.4
110°	196.2	196.3	196.1	196.1	195.9	195.7	195.5	195.3	195.0	194.7	194.8



TEST NUMBER: P332782-927

CATALOG NUMBER: S124DIW-S795D770U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	219.8	219.8	219.5	219.3	219.0	218.8	218.8	218.7	218.6	218.6	218.6
115°	256.4	256.2	256.0	255.7	255.4	255.2	255.0	254.9	254.8	254.6	254.5
117.5°	291.4	291.3	291.1	291.0	290.7	290.6	290.1	289.7	289.2	288.8	288.4
120°	316.1	316.1	315.8	315.4	315.0	314.6	313.9	313.2	312.6	312.0	311.7
122.5°	338.8	338.8	338.7	338.4	338.3	338.1	337.6	337.2	336.8	336.3	335.8
125°	373.4	373.3	373.1	373.0	372.9	372.7	372.5	372.2	372.0	371.7	371.5
127.5°	407.0	407.1	406.9	406.7	406.5	406.3	406.0	405.8	405.5	405.2	405.0
130°	429.6	429.8	429.8	429.8	429.8	429.8	429.5	429.3	429.0	428.7	428.3
132.5°	452.3	452.3	452.2	452.1	452.0	451.9	451.6	451.4	451.1	450.8	450.6
135°	484.7	485.1	485.1	485.1	485.1	485.1	484.8	484.5	484.3	484.0	483.7
137.5°	516.2	516.4	516.7	516.8	517.1	517.3	516.9	516.6	516.3	515.9	515.8
140°	537.8	538.0	538.0	538.0	538.0	538.0	537.8	537.7	537.6	537.4	537.3
142.5°	558.1	558.2	558.0	557.9	557.9	557.7	557.7	557.7	557.6	557.6	557.6
145°	587.1	587.4	587.6	587.7	587.8	588.0	587.8	587.7	587.6	587.4	587.2
147.5°	615.3	615.5	615.4	615.3	615.2	615.1	615.0	614.9	614.8	614.7	614.6
150°	631.8	632.1	632.1	632.1	632.1	632.1	632.1	632.1	632.1	632.1	632.0
152.5°	647.0	647.1	647.2	647.4	647.5	647.5	647.8	648.2	648.5	648.8	648.8
155°	670.3	670.2	670.0	669.9	669.8	669.7	670.2	670.7	671.2	671.8	671.8
157.5°	690.0	689.9	689.8	689.8	689.8	689.8	690.1	690.5	690.9	691.3	691.3
160°	702.7	702.5	702.4	702.3	702.1	702.0	702.4	702.8	703.2	703.6	703.5
162.5°	713.1	712.9	712.7	712.6	712.5	712.3	713.0	713.8	714.5	715.2	715.2
165°	728.1	727.8	727.5	727.2	727.0	726.7	727.5	728.3	729.0	729.8	730.0
167.5°	739.1	738.8	738.9	738.9	738.9	738.9	739.7	740.5	741.2	742.0	742.0
170°	745.3	745.0	745.1	745.3	745.4	745.5	746.3	747.1	747.9	748.7	748.6
172.5°	750.4	750.1	750.1	750.2	750.2	750.2	751.1	752.0	752.9	753.8	753.8
175°	756.5	756.1	755.9	755.7	755.7	755.5	756.5	757.3	758.3	759.1	759.1
177.5°	759.1	758.8	758.8	758.8	758.8	758.8	759.5	760.3	761.0	761.8	761.7
180°	760.2	760.2	760.2	760.2	760.2	760.2	760.2	760.2	760.2	760.2	760.2



TEST NUMBER: P332782-927

CATALOG NUMBER: S124DIW-S795D770U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1017.1	1017.1	1017.1	1017.1	1017.1	1017.1	1017.1	1017.1	1017.1	1017.1	1017.1
2.5°	969.2	968.5	966.1	965.8	966.1	968.5	969.2	969.9	970.9	974.2	970.2
5°	895.3	893.2	891.9	896.6	891.9	893.2	895.3	897.8	902.1	902.5	906.7
7.5°	839.6	837.9	834.2	833.1	834.2	837.9	839.6	841.1	845.3	849.0	855.2
10°	803.8	802.2	798.8	798.0	798.8	802.2	803.8	808.1	812.3	816.9	821.2
12.5°	769.4	766.1	765.4	766.3	765.4	766.1	769.4	775.1	786.0	785.9	786.8
15°	723.8	722.2	717.5	718.7	717.5	722.2	723.8	729.3	734.4	740.7	746.9
17.5°	678.8	676.8	671.1	676.1	671.1	676.8	678.8	681.8	688.2	697.2	706.7
20°	650.5	647.1	644.2	643.7	644.2	647.1	650.5	653.5	660.6	668.2	675.3
22.5°	623.5	620.5	620.3	617.5	620.3	620.5	623.5	628.2	635.3	639.5	646.3
25°	589.9	586.9	586.1	583.9	586.1	586.9	589.9	593.2	597.9	601.2	608.8
27.5°	564.0	562.5	561.0	561.7	561.0	562.5	564.0	564.4	566.5	570.9	575.4
30°	548.1	547.7	546.8	546.8	546.8	547.7	548.1	546.8	549.0	551.0	554.4
32.5°	535.0	534.9	535.4	535.4	535.4	534.9	535.0	533.1	533.8	534.6	536.2
35°	516.5	517.8	518.6	517.4	518.6	517.8	516.5	514.8	513.6	510.6	511.5
37.5°	499.9	501.1	502.3	503.7	502.3	501.1	499.9	496.4	493.4	490.8	487.7
40°	487.0	490.0	490.8	493.0	490.8	490.0	487.0	483.2	479.9	476.9	473.6
42.5°	474.9	478.2	480.4	480.8	480.4	478.2	474.9	471.1	466.0	462.4	457.7
45°	456.3	459.6	462.6	462.6	462.6	459.6	456.3	450.0	444.5	439.0	434.4
47.5°	437.0	441.9	444.8	445.6	444.8	441.9	437.0	430.5	422.9	416.1	409.4
50°	423.8	429.8	432.7	434.8	432.7	429.8	423.8	416.7	408.7	400.2	392.2
52.5°	411.1	416.9	420.9	422.0	420.9	416.9	411.1	402.2	392.5	383.4	376.4
55°	388.9	397.3	402.0	403.6	402.0	397.3	388.9	379.2	369.9	358.5	348.4
57.5°	368.0	375.7	381.1	382.4	381.1	375.7	368.0	356.6	344.6	332.5	321.7
60°	351.8	360.2	366.9	368.2	366.9	360.2	351.8	340.4	327.8	316.0	302.5
62.5°	335.3	344.0	350.1	353.4	350.1	344.0	335.3	323.2	309.6	296.4	283.0
65°	306.7	315.5	321.5	322.7	321.5	315.5	306.7	294.9	280.6	266.7	255.3
67.5°	275.5	284.4	288.3	290.7	288.3	284.4	275.5	264.4	250.3	235.8	222.9
70°	253.7	260.8	265.0	267.1	265.0	260.8	253.7	241.9	230.0	215.3	201.4
72.5°	228.7	236.1	241.1	241.5	241.1	236.1	228.7	218.6	206.1	192.3	180.1
75°	190.4	197.2	199.7	199.7	199.7	197.2	190.4	180.8	170.6	159.7	147.4
77.5°	150.8	154.2	157.4	158.0	157.4	154.2	150.8	143.8	135.4	124.5	115.3
80°	125.2	127.2	129.8	129.8	129.8	127.2	125.2	118.8	110.8	101.6	94.3
82.5°	98.9	100.6	103.1	102.8	103.1	100.6	98.9	93.9	87.2	81.0	74.5
85°	59.8	63.6	63.2	62.3	63.2	63.6	59.8	60.7	54.3	50.1	44.2
87.5°	30.3	30.7	31.8	32.5	31.8	30.7	30.3	29.3	26.1	24.3	22.8
90°	16.9	17.1	17.3	17.7	17.3	17.1	16.9	16.6	16.1	15.3	14.5
92.5°	25.7	25.8	26.0	26.1	26.0	25.8	25.7	25.5	25.2	24.7	24.2
95°	46.4	46.4	46.4	46.4	46.4	46.4	46.4	46.4	46.3	45.9	45.5
97.5°	72.8	72.8	72.8	72.8	72.8	72.8	72.8	72.8	72.6	72.1	71.6
100°	91.1	91.1	91.1	91.1	91.1	91.1	91.1	91.1	91.0	90.7	90.5
102.5°	111.5	111.6	111.7	111.9	111.7	111.6	111.5	111.4	111.1	110.8	110.4
105°	142.3	142.7	143.1	143.5	143.1	142.7	142.3	141.9	141.5	141.1	140.7
107.5°	174.4	174.4	174.3	174.3	174.3	174.4	174.4	174.4	174.2	173.8	173.5
110°	195.2	195.6	196.0	196.4	196.0	195.6	195.2	194.8	194.7	195.0	195.3



TEST NUMBER: P332782-927

CATALOG NUMBER: S124DIW-S795D770U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	218.7	218.8	218.9	219.0	218.9	218.8	218.7	218.6	218.6	218.6	218.7
115°	254.4	254.3	254.1	254.0	254.1	254.3	254.4	254.5	254.6	254.8	254.9
117.5°	288.2	287.9	287.6	287.4	287.6	287.9	288.2	288.4	288.8	289.2	289.7
120°	312.0	312.3	312.5	312.8	312.5	312.3	312.0	311.7	312.0	312.6	313.2
122.5°	335.3	334.9	334.5	334.0	334.5	334.9	335.3	335.8	336.3	336.8	337.2
125°	371.2	370.9	370.7	370.4	370.7	370.9	371.2	371.5	371.7	372.0	372.2
127.5°	404.8	404.6	404.3	404.2	404.3	404.6	404.8	405.0	405.2	405.5	405.8
130°	427.9	427.3	426.7	426.3	426.7	427.3	427.9	428.3	428.7	429.0	429.3
132.5°	450.4	450.2	450.0	449.8	450.0	450.2	450.4	450.6	450.8	451.1	451.4
135°	483.3	482.9	482.5	482.1	482.5	482.9	483.3	483.7	484.0	484.3	484.5
137.5°	515.9	515.9	516.0	516.1	516.0	515.9	515.9	515.8	515.9	516.3	516.6
140°	537.2	537.0	536.9	536.8	536.9	537.0	537.2	537.3	537.4	537.6	537.7
142.5°	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.6	557.6	557.6	557.7
145°	586.8	586.4	586.0	585.6	586.0	586.4	586.8	587.2	587.4	587.6	587.7
147.5°	614.4	614.3	614.2	614.0	614.2	614.3	614.4	614.6	614.7	614.8	614.9
150°	631.8	631.7	631.6	631.4	631.6	631.7	631.8	632.0	632.1	632.1	632.1
152.5°	648.5	648.2	647.8	647.5	647.8	648.2	648.5	648.8	648.8	648.5	648.2
155°	671.2	670.7	670.2	669.7	670.2	670.7	671.2	671.8	671.8	671.2	670.7
157.5°	690.9	690.5	690.0	689.5	690.0	690.5	690.9	691.3	691.3	690.9	690.5
160°	702.8	702.1	701.5	700.8	701.5	702.1	702.8	703.5	703.6	703.2	702.8
162.5°	714.5	713.9	713.3	712.6	713.3	713.9	714.5	715.2	715.2	714.5	713.8
165°	729.4	728.9	728.4	727.9	728.4	728.9	729.4	730.0	729.8	729.0	728.3
167.5°	741.2	740.5	739.7	738.8	739.7	740.5	741.2	742.0	742.0	741.2	740.5
170°	747.7	746.8	745.8	745.0	745.8	746.8	747.7	748.6	748.7	747.9	747.1
172.5°	752.8	751.9	751.0	750.1	751.0	751.9	752.8	753.8	753.8	752.9	752.0
175°	758.3	757.3	756.5	755.5	756.5	757.3	758.3	759.1	759.1	758.3	757.3
177.5°	760.8	760.0	759.1	758.4	759.1	760.0	760.8	761.7	761.8	761.0	760.3
180°	760.2	760.2	760.2	760.2	760.2	760.2	760.2	760.2	760.2	760.2	760.2



TEST NUMBER: P332782-927

CATALOG NUMBER: S124DIW-S795D770U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1017.1	1017.1	1017.1	1017.1	1017.1	1017.1	1017.1	1017.1	1017.1	1017.1	1017.1
2.5°	972.2	973.6	979.0	984.0	990.1	994.5	997.5	1000.8	1008.0	1013.7	1019.1
5°	910.9	913.0	923.9	931.5	944.6	955.9	964.8	974.5	985.9	1001.5	1015.8
7.5°	856.9	864.7	876.6	889.0	902.3	917.2	930.2	944.8	964.4	985.8	1007.9
10°	826.2	835.0	847.7	862.0	874.6	891.9	907.9	925.2	947.5	973.7	999.8
12.5°	795.5	810.1	819.7	836.7	850.4	864.6	881.6	904.3	930.3	957.8	989.4
15°	757.1	765.1	783.6	792.9	812.3	834.2	851.0	873.8	899.0	935.3	970.7
17.5°	712.8	723.3	738.1	755.7	778.0	795.1	816.1	839.5	871.3	907.4	951.6
20°	683.8	692.6	710.7	730.2	753.8	771.8	794.2	816.9	849.8	888.1	934.5
22.5°	657.8	666.4	685.5	703.5	726.4	748.6	771.9	798.4	829.9	870.3	917.6
25°	617.7	629.0	645.9	664.4	686.3	711.6	736.9	760.5	794.2	836.7	887.3
27.5°	582.0	591.1	603.3	624.4	649.3	673.7	698.8	728.4	760.8	805.8	858.3
30°	559.0	567.5	579.7	599.1	622.3	648.4	674.5	703.1	736.9	781.6	835.0
32.5°	540.9	547.3	558.2	575.5	596.7	624.2	649.9	679.6	714.9	759.0	811.1
35°	514.0	519.5	523.7	540.1	559.0	584.4	610.5	642.1	676.2	718.0	770.2
37.5°	487.6	489.5	495.7	506.4	524.8	548.0	572.3	603.4	638.3	680.7	727.9
40°	471.4	472.3	476.1	486.2	502.2	524.1	547.7	578.5	611.7	651.8	698.5
42.5°	455.6	455.1	458.6	465.6	480.6	500.5	523.8	551.8	585.1	622.1	666.1
45°	430.6	430.6	429.8	435.6	447.8	467.2	486.6	513.6	541.4	577.7	614.7
47.5°	404.5	402.1	402.8	405.9	416.1	432.1	451.6	473.7	498.3	528.9	561.4
50°	387.6	384.2	382.9	386.3	395.6	409.5	428.0	447.4	470.6	497.6	525.4
52.5°	369.1	365.7	363.5	365.8	374.4	387.3	404.1	421.1	442.0	463.9	488.0
55°	340.4	336.6	335.3	336.2	342.5	352.6	366.9	382.5	398.2	416.3	433.1
57.5°	312.2	305.9	304.8	304.4	308.7	318.0	329.9	343.5	354.8	365.8	383.7
60°	293.7	286.1	283.5	283.1	286.5	294.1	305.1	318.5	326.5	334.1	349.7
62.5°	273.8	266.5	260.9	261.6	264.6	271.8	281.5	291.2	296.5	304.8	315.3
65°	243.1	233.9	229.7	228.4	230.0	235.9	243.5	249.9	255.7	259.1	269.2
67.5°	212.5	204.7	198.4	196.9	196.1	200.2	206.4	210.2	214.4	217.4	223.4
70°	190.8	184.1	176.5	174.0	173.6	177.0	182.8	183.2	189.2	190.4	196.8
72.5°	169.6	161.2	156.0	153.4	151.7	154.7	158.6	159.7	162.9	165.2	168.4
75°	136.5	130.2	125.2	121.4	120.1	121.8	121.8	123.9	126.0	127.2	131.0
77.5°	107.4	100.2	94.2	92.1	90.5	89.4	90.3	91.6	90.5	92.8	93.6
80°	87.2	79.6	75.0	74.1	71.6	69.6	69.1	70.3	68.7	69.6	72.0
82.5°	67.3	62.4	57.4	56.6	53.4	52.4	51.9	51.2	51.2	51.0	51.5
85°	40.0	37.1	33.7	31.6	30.3	28.2	28.2	27.4	26.5	25.7	26.1
87.5°	18.9	18.1	16.2	15.0	14.1	12.5	12.3	11.0	10.4	9.7	9.1
90°	13.7	12.9	11.9	10.9	9.8	8.8	7.5	6.1	4.7	3.2	1.7
92.5°	23.8	23.3	22.6	21.8	21.1	20.4	19.2	17.5	15.8	14.3	12.6
95°	45.1	44.7	43.8	42.9	41.9	41.0	40.0	38.8	37.6	36.4	35.3
97.5°	71.1	70.7	69.6	68.5	67.5	66.4	65.4	64.4	63.5	62.6	61.6
100°	90.2	90.0	88.8	87.6	86.4	85.2	84.4	83.9	83.3	82.9	82.3
102.5°	110.1	109.7	108.6	107.6	106.5	105.4	104.8	104.6	104.3	104.2	103.9
105°	140.3	139.9	139.4	138.9	138.4	137.8	137.5	137.4	137.3	137.1	137.0
107.5°	173.1	172.8	172.7	172.6	172.5	172.5	172.3	172.1	172.0	171.8	171.7
110°	195.5	195.7	195.9	196.1	196.1	196.3	196.2	196.0	195.7	195.4	195.2



TEST NUMBER: P332782-927

CATALOG NUMBER: S124DIW-S795D770U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	218.8	218.8	219.0	219.3	219.5	219.8	219.8	219.8	219.8	219.7	219.7
115°	255.0	255.2	255.4	255.7	256.0	256.2	256.4	256.4	256.4	256.4	256.4
117.5°	290.1	290.6	290.7	291.0	291.1	291.3	291.4	291.2	291.1	291.0	290.9
120°	313.9	314.6	315.0	315.4	315.8	316.1	316.1	315.5	315.0	314.5	313.9
122.5°	337.6	338.1	338.3	338.4	338.7	338.8	338.8	338.6	338.3	338.2	337.9
125°	372.5	372.7	372.9	373.0	373.1	373.3	373.4	373.4	373.4	373.4	373.4
127.5°	406.0	406.3	406.5	406.7	406.9	407.1	407.0	406.6	406.2	405.8	405.4
130°	429.5	429.8	429.8	429.8	429.8	429.8	429.6	429.2	428.8	428.4	428.0
132.5°	451.6	451.9	452.0	452.1	452.2	452.3	452.3	451.9	451.6	451.4	451.1
135°	484.8	485.1	485.1	485.1	485.1	485.1	484.7	483.9	483.1	482.3	481.6
137.5°	516.9	517.3	517.1	516.8	516.7	516.4	516.2	515.8	515.4	515.1	514.7
140°	537.8	538.0	538.0	538.0	538.0	538.0	537.8	537.6	537.3	537.0	536.8
142.5°	557.7	557.7	557.9	557.9	558.0	558.2	558.1	557.8	557.5	557.3	557.0
145°	587.8	588.0	587.8	587.7	587.6	587.4	587.1	586.6	586.1	585.5	585.0
147.5°	615.0	615.1	615.2	615.3	615.4	615.5	615.3	614.7	614.0	613.4	612.8
150°	632.1	632.1	632.1	632.1	632.1	632.1	631.8	631.3	630.7	630.2	629.7
152.5°	647.8	647.5	647.5	647.4	647.2	647.1	647.0	646.7	646.3	646.0	645.7
155°	670.2	669.7	669.8	669.9	670.0	670.2	670.3	670.3	670.3	670.3	670.3
157.5°	690.1	689.8	689.8	689.8	689.8	689.9	690.0	690.2	690.5	690.7	690.9
160°	702.4	702.0	702.1	702.3	702.4	702.5	702.7	702.8	702.9	703.1	703.2
162.5°	713.0	712.3	712.5	712.6	712.7	712.9	713.1	713.4	713.8	714.2	714.5
165°	727.5	726.7	727.0	727.2	727.5	727.8	728.1	728.5	728.9	729.3	729.7
167.5°	739.7	738.9	738.9	738.9	738.9	738.8	739.1	739.7	740.2	740.8	741.2
170°	746.3	745.5	745.4	745.3	745.1	745.0	745.3	745.9	746.6	747.2	747.9
172.5°	751.1	750.2	750.2	750.2	750.1	750.1	750.4	750.9	751.5	752.0	752.6
175°	756.5	755.5	755.7	755.7	755.9	756.1	756.5	757.1	757.7	758.4	759.1
177.5°	759.5	758.8	758.8	758.8	758.8	758.8	759.1	759.6	760.1	760.7	761.1
180°	760.2	760.2	760.2	760.2	760.2	760.2	760.2	760.2	760.2	760.2	760.2



TEST NUMBER: P332782-927

CATALOG NUMBER: S124DIW-S795D770U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1017.1	1017.1	1017.1	1017.1	1017.1	1017.1	1017.1	1017.1	1017.1	1017.1	1017.1
2.5°	1023.8	1027.1	1031.6	1038.9	1041.6	1045.0	1049.7	1049.4	1050.8	1055.8	1066.6
5°	1027.6	1040.6	1053.3	1068.4	1084.5	1095.0	1109.3	1118.2	1127.0	1138.4	1157.8
7.5°	1029.1	1049.8	1073.0	1099.6	1123.3	1150.6	1172.0	1192.0	1210.1	1234.1	1257.2
10°	1026.7	1054.6	1084.5	1118.2	1154.0	1184.3	1211.7	1242.9	1269.4	1298.5	1324.6
12.5°	1022.4	1055.9	1095.9	1133.7	1175.5	1220.4	1254.5	1286.0	1321.4	1354.8	1395.0
15°	1012.4	1058.4	1105.1	1154.8	1210.9	1262.7	1311.9	1352.8	1390.8	1440.9	1493.6
17.5°	999.8	1049.3	1108.3	1168.5	1227.0	1286.3	1347.3	1408.7	1456.6	1518.9	1560.0
20°	988.0	1045.3	1106.0	1177.6	1236.1	1309.9	1370.6	1430.0	1495.6	1557.6	1606.9
22.5°	971.5	1034.2	1098.5	1169.8	1246.9	1320.6	1390.8	1455.2	1520.9	1588.2	1648.0
25°	950.5	1007.3	1083.6	1164.5	1241.2	1321.2	1401.7	1482.6	1553.4	1624.6	1680.2
27.5°	914.7	986.6	1057.6	1141.1	1226.3	1316.8	1402.9	1487.6	1561.7	1620.3	1654.7
30°	896.6	958.9	1036.0	1119.8	1212.1	1309.5	1399.2	1482.2	1551.3	1598.1	1611.9
32.5°	869.6	934.0	1009.4	1096.2	1193.9	1294.0	1387.3	1465.7	1523.3	1547.8	1531.1
35°	829.6	887.7	963.9	1052.9	1154.4	1261.0	1353.3	1419.4	1448.9	1425.7	1368.0
37.5°	781.6	839.2	915.8	1003.1	1108.1	1216.5	1299.9	1347.5	1337.8	1280.1	1194.1
40°	747.8	801.8	874.6	969.0	1071.4	1180.1	1253.4	1279.1	1252.1	1169.6	1078.2
42.5°	710.4	763.0	836.2	927.2	1035.7	1135.9	1199.8	1201.9	1156.7	1058.0	966.2
45°	653.5	703.6	772.7	867.5	967.7	1062.2	1104.2	1083.6	1000.2	905.0	812.7
47.5°	597.2	640.7	708.8	798.8	894.1	973.5	994.3	957.2	868.3	775.9	690.4
50°	556.1	599.9	664.0	750.0	841.8	910.5	920.6	871.2	784.1	690.9	624.0
52.5°	516.7	560.2	621.9	701.4	785.5	847.4	847.8	790.8	703.9	620.8	558.6
55°	458.8	498.0	553.6	624.8	699.8	748.2	736.5	677.5	602.1	530.0	475.6
57.5°	403.1	437.1	488.4	547.8	613.9	653.8	634.2	577.4	510.1	449.0	407.8
60°	366.9	399.4	443.2	499.2	554.8	586.1	567.5	516.1	454.2	404.9	369.1
62.5°	331.9	359.3	401.4	450.0	501.6	524.7	508.2	457.5	403.9	359.4	330.3
65°	282.3	304.6	338.3	380.0	417.6	437.3	423.4	376.2	335.3	303.3	280.2
67.5°	235.9	253.3	278.9	312.4	344.2	354.9	342.3	309.4	274.8	249.1	232.8
70°	203.9	220.4	241.9	267.5	295.3	306.7	294.1	267.9	239.7	216.1	200.1
72.5°	175.9	188.7	206.8	228.8	250.5	261.9	253.3	228.1	204.3	186.8	173.2
75°	134.0	145.0	157.6	173.2	190.0	197.6	190.0	172.8	156.3	143.2	133.6
77.5°	97.4	103.3	113.0	124.7	135.2	141.1	134.5	122.8	112.7	103.8	99.0
80°	74.1	78.3	85.1	94.3	101.6	107.0	102.8	93.1	85.1	79.2	77.1
82.5°	53.9	56.8	61.2	68.0	72.9	75.7	73.8	66.8	63.5	58.3	56.2
85°	26.5	28.2	31.2	33.3	37.5	37.9	38.3	35.4	32.5	31.2	29.5
87.5°	9.7	10.4	11.6	13.0	14.6	15.1	15.0	15.2	14.0	13.9	12.7
90°	3.2	4.7	6.1	7.5	8.8	9.8	10.9	11.9	12.9	13.7	14.5
92.5°	14.3	15.8	17.5	19.2	20.4	21.1	21.8	22.6	23.3	23.8	24.2
95°	36.4	37.6	38.8	40.0	41.0	41.9	42.9	43.8	44.7	45.1	45.5
97.5°	62.6	63.5	64.4	65.4	66.4	67.5	68.5	69.6	70.7	71.1	71.6
100°	82.9	83.3	83.9	84.4	85.2	86.4	87.6	88.8	90.0	90.2	90.5
102.5°	104.2	104.3	104.6	104.8	105.4	106.5	107.6	108.6	109.7	110.1	110.4
105°	137.1	137.3	137.4	137.5	137.8	138.4	138.9	139.4	139.9	140.3	140.7
107.5°	171.8	172.0	172.1	172.3	172.5	172.5	172.6	172.7	172.8	173.1	173.5
110°	195.4	195.7	196.0	196.2	196.3	196.1	196.1	195.9	195.7	195.5	195.3





TEST NUMBER: P332782-927

CATALOG NUMBER: S124DIW-S795D770U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	219.7	219.8	219.8	219.8	219.8	219.5	219.3	219.0	218.8	218.8	218.7
115°	256.4	256.4	256.4	256.4	256.2	256.0	255.7	255.4	255.2	255.0	254.9
117.5°	291.0	291.1	291.2	291.4	291.3	291.1	291.0	290.7	290.6	290.1	289.7
120°	314.5	315.0	315.5	316.1	316.1	315.8	315.4	315.0	314.6	313.9	313.2
122.5°	338.2	338.3	338.6	338.8	338.8	338.7	338.4	338.3	338.1	337.6	337.2
125°	373.4	373.4	373.4	373.4	373.3	373.1	373.0	372.9	372.7	372.5	372.2
127.5°	405.8	406.2	406.6	407.0	407.1	406.9	406.7	406.5	406.3	406.0	405.8
130°	428.4	428.8	429.2	429.6	429.8	429.8	429.8	429.8	429.8	429.5	429.3
132.5°	451.4	451.6	451.9	452.3	452.3	452.2	452.1	452.0	451.9	451.6	451.4
135°	482.3	483.1	483.9	484.7	485.1	485.1	485.1	485.1	485.1	484.8	484.5
137.5°	515.1	515.4	515.8	516.2	516.4	516.7	516.8	517.1	517.3	516.9	516.6
140°	537.0	537.3	537.6	537.8	538.0	538.0	538.0	538.0	538.0	537.8	537.7
142.5°	557.3	557.5	557.8	558.1	558.2	558.0	557.9	557.9	557.7	557.7	557.7
145°	585.5	586.1	586.6	587.1	587.4	587.6	587.7	587.8	588.0	587.8	587.7
147.5°	613.4	614.0	614.7	615.3	615.5	615.4	615.3	615.2	615.1	615.0	614.9
150°	630.2	630.7	631.3	631.8	632.1	632.1	632.1	632.1	632.1	632.1	632.1
152.5°	646.0	646.3	646.7	647.0	647.1	647.2	647.4	647.5	647.5	647.8	648.2
155°	670.3	670.3	670.3	670.3	670.2	670.0	669.9	669.8	669.7	670.2	670.7
157.5°	690.7	690.5	690.2	690.0	689.9	689.8	689.8	689.8	689.8	690.1	690.5
160°	703.1	702.9	702.8	702.7	702.5	702.4	702.3	702.1	702.0	702.4	702.8
162.5°	714.2	713.8	713.4	713.1	712.9	712.7	712.6	712.5	712.3	713.0	713.8
165°	729.3	728.9	728.5	728.1	727.8	727.5	727.2	727.0	726.7	727.5	728.3
167.5°	740.8	740.2	739.7	739.1	738.8	738.9	738.9	738.9	738.9	739.7	740.5
170°	747.2	746.6	745.9	745.3	745.0	745.1	745.3	745.4	745.5	746.3	747.1
172.5°	752.0	751.5	750.9	750.4	750.1	750.1	750.2	750.2	750.2	751.1	752.0
175°	758.4	757.7	757.1	756.5	756.1	755.9	755.7	755.7	755.5	756.5	757.3
177.5°	760.7	760.1	759.6	759.1	758.8	758.8	758.8	758.8	758.8	759.5	760.3
180°	760.2	760.2	760.2	760.2	760.2	760.2	760.2	760.2	760.2	760.2	760.2



TEST NUMBER: P332782-927

CATALOG NUMBER: S124DIW-S795D770U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1017.1	1017.1	1017.1	1017.1	1017.1	1017.1	1017.1
2.5°	1072.0	1072.7	1075.7	1078.1	1078.7	1082.1	1082.4
5°	1166.2	1173.4	1187.2	1188.5	1190.6	1201.6	1193.2
7.5°	1276.6	1294.7	1306.9	1317.6	1321.5	1326.3	1325.3
10°	1347.3	1374.4	1387.8	1409.3	1410.2	1415.6	1412.2
12.5°	1418.5	1449.9	1474.4	1478.4	1496.4	1499.2	1504.0
15°	1519.2	1552.5	1586.7	1598.9	1623.7	1629.7	1638.9
17.5°	1614.0	1648.0	1671.9	1703.5	1713.7	1727.4	1718.1
20°	1665.9	1703.0	1733.3	1758.2	1768.7	1776.2	1775.4
22.5°	1697.3	1734.6	1759.2	1778.1	1787.9	1791.1	1790.9
25°	1716.8	1738.4	1745.9	1753.1	1742.2	1738.4	1740.0
27.5°	1662.2	1656.7	1636.9	1610.9	1584.0	1562.6	1550.9
30°	1587.1	1554.3	1524.3	1472.0	1445.1	1429.1	1414.8
32.5°	1480.6	1428.5	1371.0	1323.1	1292.4	1268.7	1265.1
35°	1298.1	1219.7	1149.4	1090.8	1060.4	1034.7	1028.8
37.5°	1103.6	1022.2	958.9	907.3	874.6	856.5	839.6
40°	974.5	904.6	842.2	798.4	773.6	760.5	750.0
42.5°	875.0	811.2	749.2	715.8	693.3	685.3	679.1
45°	737.7	678.3	635.3	610.1	597.0	583.5	577.2
47.5°	627.7	579.4	551.0	529.6	515.6	507.6	503.6
50°	565.4	525.8	500.5	484.1	471.4	465.1	461.8
52.5°	510.1	477.6	456.4	443.3	434.7	430.1	428.7
55°	439.4	414.5	401.1	389.8	383.4	379.2	377.5
57.5°	382.0	362.8	351.9	342.5	340.1	336.5	335.3
60°	344.2	329.5	320.2	313.9	311.8	307.5	308.4
62.5°	310.9	298.8	290.9	287.2	284.5	280.9	282.1
65°	262.9	254.1	249.9	246.4	243.1	241.0	242.6
67.5°	220.6	214.5	208.8	206.8	205.2	204.9	203.0
70°	193.0	187.9	182.8	181.6	181.6	179.9	179.5
72.5°	166.4	162.6	159.2	158.4	157.0	157.6	155.9
75°	128.5	125.6	124.3	123.0	122.6	122.6	121.4
77.5°	95.0	92.8	90.8	90.8	89.2	88.6	88.5
80°	72.0	71.2	69.6	69.6	68.7	69.1	68.3
82.5°	54.2	53.0	52.7	52.0	50.8	50.9	50.1
85°	29.1	27.8	27.4	26.1	25.3	26.1	25.3
87.5°	13.2	13.0	12.8	12.1	11.9	11.9	10.9
90°	15.3	16.1	16.6	16.9	17.1	17.3	17.7
92.5°	24.7	25.2	25.5	25.7	25.8	26.0	26.1
95°	45.9	46.3	46.4	46.4	46.4	46.4	46.4
97.5°	72.1	72.6	72.8	72.8	72.8	72.8	72.8
100°	90.7	91.0	91.1	91.1	91.1	91.1	91.1
102.5°	110.8	111.1	111.4	111.5	111.6	111.7	111.9
105°	141.1	141.5	141.9	142.3	142.7	143.1	143.5
107.5°	173.8	174.2	174.4	174.4	174.4	174.3	174.3
110°	195.0	194.7	194.8	195.2	195.6	196.0	196.4



TEST NUMBER: P332782-927

CATALOG NUMBER: S124DIW-S795D770U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	218.6	218.6	218.6	218.7	218.8	218.9	219.0
115°	254.8	254.6	254.5	254.4	254.3	254.1	254.0
117.5°	289.2	288.8	288.4	288.2	287.9	287.6	287.4
120°	312.6	312.0	311.7	312.0	312.3	312.5	312.8
122.5°	336.8	336.3	335.8	335.3	334.9	334.5	334.0
125°	372.0	371.7	371.5	371.2	370.9	370.7	370.4
127.5°	405.5	405.2	405.0	404.8	404.6	404.3	404.2
130°	429.0	428.7	428.3	427.9	427.3	426.7	426.3
132.5°	451.1	450.8	450.6	450.4	450.2	450.0	449.8
135°	484.3	484.0	483.7	483.3	482.9	482.5	482.1
137.5°	516.3	515.9	515.8	515.9	515.9	516.0	516.1
140°	537.6	537.4	537.3	537.2	537.0	536.9	536.8
142.5°	557.6	557.6	557.6	557.5	557.5	557.5	557.5
145°	587.6	587.4	587.2	586.8	586.4	586.0	585.6
147.5°	614.8	614.7	614.6	614.4	614.3	614.2	614.0
150°	632.1	632.1	632.0	631.8	631.7	631.6	631.4
152.5°	648.5	648.8	648.8	648.5	648.2	647.8	647.5
155°	671.2	671.8	671.8	671.2	670.7	670.2	669.7
157.5°	690.9	691.3	691.3	690.9	690.5	690.0	689.5
160°	703.2	703.6	703.5	702.8	702.1	701.5	700.8
162.5°	714.5	715.2	715.2	714.5	713.9	713.3	712.6
165°	729.0	729.8	730.0	729.4	728.9	728.4	727.9
167.5°	741.2	742.0	742.0	741.2	740.5	739.7	738.8
170°	747.9	748.7	748.6	747.7	746.8	745.8	745.0
172.5°	752.9	753.8	753.8	752.8	751.9	751.0	750.1
175°	758.3	759.1	759.1	758.3	757.3	756.5	755.5
177.5°	761.0	761.8	761.7	760.8	760.0	759.1	758.4
180°	760.2	760.2	760.2	760.2	760.2	760.2	760.2

(END OF REPORT)