

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333086

Luminaire Tested: **S124RDIW-S1020D1050U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333086
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S1020D1050U835-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1050 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7809.9 lumens
Efficiency: N/A
Efficacy: 127.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 61.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333086

CATALOG NUMBER: S124RDIW-S1020D1050U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333086

CATALOG NUMBER: S124RDIW-S1020D1050U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	53
1	99	95	91	87	91	88	85	82	75	73	71	64	62	60	53	52	51	46
2	90	83	77	72	83	77	72	67	66	62	59	56	53	51	47	45	43	39
3	82	73	66	60	76	68	62	57	59	54	50	50	46	43	42	39	37	33
4	76	65	57	51	70	61	54	48	52	47	43	45	41	37	37	35	32	29
5	69	58	50	44	64	54	47	42	47	41	37	40	36	33	34	31	28	25
6	64	52	44	38	59	49	42	36	42	37	32	36	32	29	31	27	25	22
7	59	47	39	34	55	44	37	32	38	33	29	33	29	25	28	25	22	20
8	55	43	35	30	51	40	33	28	35	30	26	30	26	23	26	23	20	18
9	51	39	32	27	48	37	30	25	32	27	23	28	24	21	24	21	18	16
10	48	36	29	24	45	34	27	23	30	24	21	26	22	19	22	19	16	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14577	14577	14577
5°	14610	14431	14521
10°	14519	14258	14258
15°	14352	13959	13855
20°	14123	13564	13315
25°	13831	13104	12772
30°	13546	12618	12089
35°	13231	12113	11404
40°	12852	11540	10666
45°	12501	10970	9913
50°	12103	10315	9117
55°	11676	9633	8251
60°	11207	8885	7367
65°	10776	7950	6497
70°	10150	6918	5516
75°	9357	5736	4485
80°	8164	4370	4114
85°	6919	3974	3714



TEST NUMBER: P333086

CATALOG NUMBER: S124RDIW-S1020D1050U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	169.6	2.2
10°-20°	473.0	6.1
20°-30°	683.0	8.7
30°-40°	774.2	9.9
40°-50°	747.6	9.6
50°-60°	621.7	8.0
60°-70°	429.3	5.5
70°-80°	217.6	2.8
80°-90°	59.7	0.8
90°-100°	86.4	1.1
100°-110°	255.9	3.3
110°-120°	434.4	5.6
120°-130°	572.8	7.3
130°-140°	643.3	8.2
140°-150°	632.1	8.1
150°-160°	531.7	6.8
160°-170°	353.7	4.5
170°-180°	123.9	1.6
0°-30°	1325.6	17.0
0°-40°	2099.9	26.9
0°-60°	3469.2	44.4
0°-90°	4175.8	53.5
90°-120°	776.7	9.9
90°-150°	2624.9	33.6
90°-180°	3634.0	46.5
0°-180°	7809.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1806	1806	1806	1806	1806	
5°	1803	1797	1781	1794	1792	171
15°	1717	1704	1670	1667	1658	484
25°	1553	1526	1471	1448	1434	715
35°	1342	1297	1229	1183	1157	839
45°	1095	1042	961	896	868	844
55°	830	772	684	615	586	742
65°	564	503	416	359	340	557
75°	300	248	184	153	144	317
85°	75	48	43	40	40	84
90°	3	14	22	28	30	7
95°	61	70	77	80	80	68
105°	236	237	241	244	247	250
115°	442	442	440	439	438	435
125°	643	643	642	640	638	573
135°	830	835	836	834	831	642
145°	1008	1012	1013	1012	1009	631
155°	1155	1155	1154	1158	1154	531
165°	1257	1254	1252	1258	1254	354
175°	1308	1303	1302	1308	1302	124
180°	1310	1310	1310	1310	1310	



TEST NUMBER: P333086

CATALOG NUMBER: S124RDIW-S1020D1050U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7
2.5°	1810.1	1809.1	1808.1	1807.2	1806.2	1804.3	1801.6	1798.9	1796.2	1793.5	1796.2
5°	1802.9	1801.7	1800.5	1799.2	1798.0	1795.5	1791.9	1788.2	1784.5	1780.8	1783.9
7.5°	1786.6	1785.3	1784.0	1782.7	1781.4	1778.4	1773.6	1768.8	1764.0	1759.2	1761.2
10°	1771.1	1769.6	1768.0	1766.5	1765.0	1761.4	1755.9	1750.4	1744.8	1739.3	1740.5
12.5°	1751.2	1749.4	1747.6	1745.9	1744.1	1739.9	1733.4	1726.9	1720.4	1713.9	1714.6
15°	1717.2	1714.4	1711.7	1708.9	1706.1	1700.9	1693.2	1685.5	1677.9	1670.2	1669.6
17.5°	1676.0	1672.0	1668.0	1664.0	1660.0	1653.4	1644.2	1635.0	1625.8	1616.5	1614.8
20°	1643.9	1639.9	1635.9	1631.9	1627.9	1620.7	1610.3	1599.8	1589.4	1578.9	1576.5
22.5°	1608.5	1604.0	1599.5	1595.1	1590.6	1582.7	1571.6	1560.4	1549.2	1538.0	1534.3
25°	1552.7	1547.1	1541.6	1536.1	1530.5	1521.5	1508.9	1496.3	1483.7	1471.1	1465.9
27.5°	1494.0	1487.1	1480.2	1473.2	1466.3	1456.1	1442.6	1429.2	1415.7	1402.2	1395.8
30°	1453.1	1445.4	1437.8	1430.1	1422.4	1411.3	1396.9	1382.4	1368.0	1353.6	1345.9
32.5°	1410.0	1401.3	1392.6	1384.0	1375.3	1363.5	1348.6	1333.7	1318.7	1303.8	1294.9
35°	1342.5	1332.7	1322.8	1313.0	1303.2	1290.6	1275.2	1259.9	1244.5	1229.1	1218.7
37.5°	1270.3	1260.2	1250.1	1239.9	1229.8	1216.2	1199.2	1182.2	1165.1	1148.1	1136.4
40°	1219.5	1209.3	1199.2	1189.0	1178.9	1165.1	1147.6	1130.0	1112.5	1095.0	1082.1
42.5°	1170.8	1160.2	1149.5	1138.9	1128.3	1113.8	1095.6	1077.3	1059.1	1040.8	1027.7
45°	1095.0	1083.7	1072.3	1060.9	1049.5	1034.6	1016.2	997.8	979.3	960.9	945.9
47.5°	1016.8	1005.0	993.3	981.6	969.8	954.4	935.2	916.0	896.8	877.7	862.1
50°	963.7	951.7	939.7	927.7	915.7	899.9	880.3	860.6	840.9	821.3	805.9
52.5°	909.5	897.7	886.0	874.3	862.5	846.6	826.4	806.3	786.1	766.0	750.4
55°	829.6	817.3	805.0	792.7	780.4	764.3	744.3	724.3	704.4	684.4	668.4
57.5°	750.5	737.7	724.9	712.1	699.4	683.1	663.5	643.8	624.1	604.5	588.3
60°	694.1	681.8	669.5	657.2	644.9	628.9	609.3	589.6	569.9	550.3	534.3
62.5°	643.2	630.4	617.6	604.8	592.1	575.6	555.4	535.3	515.1	495.0	480.2
65°	564.1	550.9	537.7	524.5	511.3	494.8	475.2	455.5	435.8	416.2	403.0
67.5°	482.0	469.3	456.7	444.0	431.3	415.9	397.6	379.4	361.1	342.9	331.5
70°	430.0	417.1	404.2	391.3	378.4	363.2	345.7	328.1	310.6	293.1	283.0
72.5°	374.7	363.0	351.3	339.7	328.0	313.9	297.4	280.8	264.3	247.8	239.1
75°	300.0	288.7	277.3	265.9	254.6	241.6	227.2	212.8	198.3	183.9	176.8
77.5°	224.3	214.6	205.0	195.3	185.7	175.0	163.3	151.7	140.0	128.3	124.2
80°	175.6	166.7	157.8	148.9	140.0	130.9	121.7	112.5	103.2	94.0	93.1
82.5°	133.6	125.4	117.2	109.0	100.9	94.1	88.9	83.6	78.3	73.0	72.3
85°	74.7	68.5	62.4	56.2	50.1	46.5	45.6	44.7	43.8	42.9	42.2
87.5°	26.0	24.6	23.1	21.6	20.2	19.5	19.6	19.7	19.8	19.9	20.0
90°	3.0	5.5	8.0	10.5	12.9	15.1	16.9	18.7	20.5	22.3	23.6
92.5°	21.7	24.5	27.4	30.2	33.0	35.1	36.3	37.6	38.9	40.1	40.9
95°	60.8	62.8	64.8	66.9	68.9	70.7	72.3	73.8	75.4	77.0	77.7
97.5°	106.2	107.8	109.4	111.0	112.7	114.4	116.2	118.1	119.9	121.8	122.6
100°	141.8	142.7	143.6	144.5	145.4	146.9	148.9	150.9	153.0	155.0	155.4
102.5°	179.1	179.5	179.8	180.2	180.5	181.6	183.5	185.3	187.2	189.0	189.7
105°	236.0	236.3	236.5	236.7	236.9	237.5	238.4	239.3	240.2	241.1	241.8
107.5°	295.8	296.1	296.3	296.6	296.9	297.1	297.2	297.4	297.5	297.6	298.3
110°	336.3	336.8	337.2	337.7	338.1	338.2	338.0	337.8	337.6	337.3	336.9



TEST NUMBER: P333086

CATALOG NUMBER: S124RDIW-S1020D1050U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	378.5	378.6	378.7	378.7	378.8	378.7	378.3	377.9	377.5	377.1	377.0
115°	441.7	441.7	441.7	441.7	441.7	441.5	441.0	440.6	440.1	439.7	439.4
117.5°	501.3	501.4	501.6	501.8	502.0	501.9	501.6	501.3	501.0	500.6	499.9
120°	541.0	541.9	542.8	543.7	544.6	544.7	544.0	543.3	542.7	542.0	540.9
122.5°	582.3	582.7	583.0	583.4	583.7	583.8	583.4	583.1	582.8	582.5	581.7
125°	643.3	643.3	643.3	643.3	643.3	643.2	642.9	642.7	642.5	642.3	641.8
127.5°	698.6	699.3	699.9	700.6	701.3	701.5	701.1	700.7	700.4	700.0	699.6
130°	737.5	738.2	738.8	739.5	740.2	740.5	740.5	740.5	740.5	740.5	740.1
132.5°	777.2	777.7	778.2	778.7	779.2	779.3	779.2	779.0	778.8	778.6	778.2
135°	829.7	831.0	832.4	833.7	835.1	835.8	835.8	835.8	835.8	835.8	835.3
137.5°	886.8	887.4	888.1	888.7	889.3	889.8	890.2	890.6	890.9	891.3	890.7
140°	924.9	925.4	925.8	926.3	926.7	926.9	926.9	926.9	926.9	926.9	926.7
142.5°	959.8	960.2	960.7	961.1	961.6	961.7	961.5	961.3	961.2	961.0	960.9
145°	1008.0	1008.9	1009.8	1010.7	1011.6	1012.1	1012.4	1012.6	1012.8	1013.0	1012.8
147.5°	1055.8	1056.9	1058.0	1059.0	1060.1	1060.6	1060.4	1060.2	1060.0	1059.8	1059.7
150°	1085.0	1085.9	1086.8	1087.7	1088.6	1089.0	1089.0	1089.0	1089.0	1089.0	1089.0
152.5°	1112.5	1113.1	1113.6	1114.1	1114.7	1115.0	1115.2	1115.4	1115.6	1115.8	1116.3
155°	1154.9	1154.9	1154.9	1154.9	1154.9	1154.8	1154.5	1154.3	1154.1	1153.9	1154.8
157.5°	1190.5	1190.1	1189.7	1189.3	1188.9	1188.7	1188.6	1188.6	1188.5	1188.5	1189.2
160°	1211.6	1211.4	1211.1	1210.9	1210.7	1210.5	1210.2	1210.0	1209.8	1209.6	1210.2
162.5°	1231.0	1230.5	1229.9	1229.3	1228.7	1228.3	1228.1	1227.9	1227.6	1227.4	1228.6
165°	1257.2	1256.5	1255.8	1255.2	1254.5	1253.9	1253.5	1253.0	1252.6	1252.1	1253.5
167.5°	1277.2	1276.3	1275.4	1274.4	1273.5	1273.0	1273.1	1273.1	1273.1	1273.2	1274.5
170°	1288.6	1287.5	1286.3	1285.2	1284.1	1283.6	1283.9	1284.1	1284.3	1284.5	1285.9
172.5°	1296.7	1295.7	1294.8	1293.9	1292.9	1292.5	1292.5	1292.6	1292.6	1292.6	1294.2
175°	1307.8	1306.7	1305.6	1304.5	1303.3	1302.7	1302.4	1302.2	1302.0	1301.8	1303.3
177.5°	1311.5	1310.6	1309.7	1308.8	1307.9	1307.4	1307.4	1307.4	1307.4	1307.4	1308.7
180°	1309.9	1309.9	1309.9	1309.9	1309.9	1309.9	1309.9	1309.9	1309.9	1309.9	1309.9



TEST NUMBER: P333086

CATALOG NUMBER: S124RDIW-S1020D1050U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7
2.5°	1798.9	1801.6	1804.3	1805.6	1805.3	1805.1	1804.8	1804.6
5°	1786.9	1790.0	1793.1	1794.3	1793.7	1793.1	1792.5	1791.9
7.5°	1763.2	1765.1	1767.1	1767.6	1766.6	1765.6	1764.6	1763.6
10°	1741.8	1743.0	1744.2	1744.2	1743.0	1741.8	1740.5	1739.3
12.5°	1715.3	1716.1	1716.8	1716.3	1714.6	1712.9	1711.2	1709.5
15°	1669.0	1668.3	1667.7	1666.3	1664.2	1662.0	1659.9	1657.7
17.5°	1613.1	1611.4	1609.7	1607.2	1603.9	1600.7	1597.4	1594.1
20°	1574.0	1571.6	1569.1	1565.9	1561.9	1557.9	1553.9	1549.9
22.5°	1530.6	1526.9	1523.3	1519.8	1516.5	1513.3	1510.0	1506.8
25°	1460.6	1455.4	1450.2	1446.0	1443.0	1439.9	1436.8	1433.8
27.5°	1389.3	1382.9	1376.4	1371.0	1366.6	1362.1	1357.7	1353.3
30°	1338.2	1330.5	1322.8	1316.5	1311.6	1306.7	1301.8	1296.9
32.5°	1286.0	1277.1	1268.2	1261.4	1256.7	1252.0	1247.4	1242.7
35°	1208.2	1197.8	1187.3	1179.4	1173.8	1168.3	1162.8	1157.2
37.5°	1124.8	1113.1	1101.4	1092.8	1087.3	1081.7	1076.2	1070.7
40°	1069.2	1056.3	1043.4	1034.2	1028.7	1023.1	1017.6	1012.1
42.5°	1014.5	1001.4	988.2	978.8	973.0	967.2	961.4	955.7
45°	930.8	915.7	900.7	890.4	884.9	879.3	873.8	868.3
47.5°	846.5	830.9	815.2	804.4	798.3	792.2	786.1	780.1
50°	790.5	775.2	759.8	749.2	743.4	737.5	731.7	725.9
52.5°	734.7	719.1	703.5	692.7	686.6	680.5	674.4	668.4
55°	652.4	636.5	620.5	609.6	603.7	597.9	592.1	586.2
57.5°	572.0	555.8	539.6	529.3	524.8	520.4	516.0	511.6
60°	518.3	502.3	486.4	475.9	471.0	466.1	461.2	456.3
62.5°	465.5	450.7	436.0	426.6	422.7	418.8	414.8	410.9
65°	389.7	376.5	363.3	354.9	351.2	347.5	343.8	340.1
67.5°	320.1	308.8	297.4	289.7	285.6	281.6	277.5	273.5
70°	272.8	262.7	252.6	245.9	242.9	239.8	236.7	233.7
72.5°	230.4	221.8	213.1	207.4	204.5	201.7	198.9	196.1
75°	169.8	162.7	155.6	151.2	149.3	147.5	145.6	143.8
77.5°	120.1	116.0	111.8	109.5	108.9	108.4	107.8	107.3
80°	92.2	91.3	90.3	89.7	89.4	89.1	88.8	88.5
82.5°	71.6	71.0	70.3	69.8	69.5	69.2	68.9	68.6
85°	41.6	41.0	40.4	40.1	40.1	40.1	40.1	40.1
87.5°	20.0	20.0	20.0	20.2	20.6	20.9	21.2	21.6
90°	25.0	26.3	27.7	28.6	29.0	29.5	29.9	30.4
92.5°	41.7	42.5	43.4	43.9	44.2	44.4	44.7	45.0
95°	78.3	79.0	79.7	80.0	80.0	80.0	80.0	80.0
97.5°	123.4	124.2	125.0	125.4	125.4	125.4	125.4	125.4
100°	155.9	156.3	156.8	157.0	157.0	157.0	157.0	157.0
102.5°	190.3	190.9	191.6	192.0	192.1	192.3	192.5	192.7
105°	242.5	243.1	243.8	244.5	245.2	245.8	246.5	247.2
107.5°	298.9	299.5	300.2	300.4	300.4	300.4	300.3	300.3
110°	336.4	336.0	335.5	335.7	336.3	337.0	337.7	338.4



TEST NUMBER: P333086

CATALOG NUMBER: S124RDIW-S1020D1050U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	376.9	376.8	376.7	376.7	376.9	377.0	377.1	377.3
115°	439.2	439.0	438.8	438.5	438.3	438.1	437.9	437.6
117.5°	499.1	498.3	497.6	497.0	496.5	496.1	495.6	495.2
120°	539.7	538.6	537.5	537.1	537.6	538.0	538.5	538.9
122.5°	581.0	580.2	579.4	578.6	577.8	577.0	576.2	575.4
125°	641.4	640.9	640.5	640.0	639.6	639.1	638.7	638.2
127.5°	699.1	698.7	698.2	697.8	697.4	697.1	696.7	696.4
130°	739.6	739.2	738.7	738.1	737.2	736.3	735.4	734.5
132.5°	777.7	777.3	776.8	776.4	776.1	775.7	775.3	775.0
135°	834.9	834.4	834.0	833.4	832.7	832.0	831.4	830.7
137.5°	890.1	889.5	888.9	888.7	888.8	889.0	889.1	889.2
140°	926.5	926.3	926.0	925.8	925.6	925.4	925.1	924.9
142.5°	960.9	960.8	960.8	960.7	960.7	960.7	960.6	960.6
145°	1012.6	1012.4	1012.1	1011.7	1011.0	1010.3	1009.7	1009.0
147.5°	1059.5	1059.3	1059.1	1058.9	1058.7	1058.5	1058.2	1058.0
150°	1089.0	1089.0	1089.0	1088.9	1088.7	1088.5	1088.2	1088.0
152.5°	1116.8	1117.4	1117.9	1117.9	1117.3	1116.7	1116.1	1115.6
155°	1155.7	1156.6	1157.5	1157.5	1156.6	1155.7	1154.8	1153.9
157.5°	1189.9	1190.5	1191.2	1191.2	1190.4	1189.6	1188.9	1188.1
160°	1210.9	1211.6	1212.3	1212.0	1210.9	1209.8	1208.7	1207.5
162.5°	1229.8	1231.0	1232.3	1232.3	1231.2	1230.1	1228.9	1227.8
165°	1254.8	1256.2	1257.5	1257.7	1256.8	1255.9	1255.0	1254.1
167.5°	1275.9	1277.2	1278.6	1278.6	1277.2	1275.8	1274.4	1273.0
170°	1287.2	1288.6	1289.9	1289.8	1288.3	1286.7	1285.1	1283.5
172.5°	1295.7	1297.2	1298.8	1298.7	1297.2	1295.6	1294.0	1292.4
175°	1304.9	1306.5	1308.1	1308.1	1306.5	1304.9	1303.3	1301.8
177.5°	1310.0	1311.2	1312.5	1312.4	1310.9	1309.5	1308.1	1306.6
180°	1309.9	1309.9	1309.9	1309.9	1309.9	1309.9	1309.9	1309.9

(END OF REPORT)