

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332785-927

Luminaire Tested: **S124DIW-S795D770U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332785-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S795D770U927-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 770 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5132.7 lumens
Efficiency: N/A
Efficacy: 114.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 45
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332785-927

CATALOG NUMBER: S124DIW-S795D770U927-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332785-927

CATALOG NUMBER: S124DIW-S795D770U927-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	53				
1	98	94	90	86	91	87	84	81	74	72	70	63	61	59	52	50	49	44				
2	90	82	76	71	83	76	71	66	65	61	58	55	52	49	45	43	42	37				
3	82	72	65	59	75	67	61	55	57	52	48	49	45	42	40	38	35	31				
4	75	64	56	50	69	59	52	47	51	46	41	43	39	36	36	33	30	27				
5	69	57	49	43	63	53	46	40	46	40	36	39	34	31	32	29	27	23				
6	63	51	43	37	58	48	40	35	41	35	31	35	31	27	29	26	23	21				
7	58	46	38	32	54	43	36	31	37	32	27	32	27	24	27	23	21	18				
8	54	42	34	29	50	39	32	27	34	28	24	29	25	21	25	21	19	16				
9	51	38	31	26	47	36	29	24	31	26	22	27	22	19	23	19	17	15				
10	47	35	28	23	44	33	26	22	29	23	20	25	21	17	21	18	15	13				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8490	8490	8490
5°	8515	8413	8474
10°	8461	8344	8385
15°	8359	8226	8247
20°	8223	8079	8086
25°	8068	7911	7888
30°	7879	7713	7643
35°	7681	7508	7407
40°	7477	7273	7140
45°	7263	7042	6907
50°	7027	6836	6625
55°	6773	6570	6356
60°	6516	6273	6082
65°	6229	5989	5746
70°	5908	5611	5391
75°	5415	5153	5022
80°	4816	4621	4505
85°	4215	4057	3974



TEST NUMBER: P332785-927

CATALOG NUMBER: S124DIW-S795D770U927-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	99.0	1.9
10°-20°	279.0	5.4
20°-30°	410.7	8.0
30°-40°	477.4	9.3
40°-50°	477.5	9.3
50°-60°	417.6	8.1
60°-70°	310.2	6.0
70°-80°	176.2	3.4
80°-90°	53.1	1.0
90°-100°	26.9	0.5
100°-110°	171.5	3.3
110°-120°	328.0	6.4
120°-130°	416.3	8.1
130°-140°	445.5	8.7
140°-150°	416.6	8.1
150°-160°	335.9	6.5
160°-170°	216.7	4.2
170°-180°	74.7	1.5
0°-30°	788.7	15.4
0°-40°	1266.2	24.7
0°-60°	2161.3	42.1
0°-90°	2700.8	52.6
90°-120°	526.3	10.3
90°-150°	1804.7	35.2
90°-180°	2432.0	47.4
0°-180°	5132.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1052	1052	1052	1052	1052	
5°	1051	1047	1038	1047	1046	100
15°	1000	996	984	989	987	282
25°	906	900	888	889	886	417
35°	779	773	762	756	752	487
45°	636	630	617	608	605	490
55°	481	478	467	457	452	431
65°	326	322	314	305	301	323
75°	174	169	165	162	161	184
85°	46	45	44	44	43	50
90°	2	8	13	16	18	4
95°	32	14	13	16	17	42
105°	177	180	184	187	168	185
115°	330	332	332	333	333	325
125°	464	467	466	467	468	415
135°	576	576	578	579	580	444
145°	664	666	666	667	668	415
155°	729	729	727	729	728	336
165°	769	766	766	770	765	217
175°	786	783	783	788	782	75
180°	786	786	786	786	786	



TEST NUMBER: P332785-927

CATALOG NUMBER: S124DIW-S795D770U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1051.6	1051.6	1051.6	1051.6	1051.6	1051.6	1051.6	1051.6	1051.6	1051.6	1051.6
2.5°	1054.3	1053.8	1053.4	1053.0	1052.5	1051.5	1049.8	1048.1	1046.5	1044.9	1046.3
5°	1050.8	1050.0	1049.2	1048.5	1047.7	1046.3	1044.3	1042.2	1040.1	1038.1	1040.1
7.5°	1041.0	1040.2	1039.5	1038.7	1038.0	1036.5	1034.2	1031.9	1029.6	1027.3	1029.0
10°	1032.2	1031.5	1030.7	1030.0	1029.2	1027.6	1025.2	1022.8	1020.3	1017.9	1019.4
12.5°	1020.7	1020.0	1019.2	1018.5	1017.8	1016.1	1013.5	1010.9	1008.4	1005.8	1007.4
15°	1000.2	999.4	998.7	997.9	997.2	995.5	992.6	989.8	987.0	984.2	985.3
17.5°	975.4	974.5	973.5	972.6	971.7	969.9	967.3	964.6	961.9	959.3	960.0
20°	957.2	956.2	955.4	954.4	953.5	951.6	948.8	945.9	943.2	940.4	941.0
22.5°	937.7	936.4	935.2	934.0	932.7	930.7	927.9	925.1	922.3	919.5	920.5
25°	905.8	904.5	903.2	901.9	900.6	898.6	896.0	893.3	890.7	888.1	888.3
27.5°	869.4	868.1	866.7	865.4	864.0	862.1	859.7	857.3	854.8	852.4	851.9
30°	845.2	843.7	842.2	840.7	839.2	837.2	834.7	832.3	829.9	827.4	826.7
32.5°	819.5	818.2	816.8	815.5	814.1	812.1	809.6	807.0	804.5	801.8	801.0
35°	779.4	778.1	776.8	775.5	774.2	772.2	769.6	767.0	764.4	761.8	760.4
37.5°	737.1	735.9	734.7	733.6	732.3	730.3	727.5	724.7	721.9	719.1	717.6
40°	709.5	708.0	706.5	705.0	703.5	701.3	698.5	695.7	692.9	690.1	688.2
42.5°	679.9	678.9	678.0	677.2	676.2	674.2	671.1	668.0	664.9	661.8	659.7
45°	636.2	634.9	633.6	632.2	631.0	628.8	625.8	622.8	619.8	616.8	614.7
47.5°	590.5	589.6	588.7	587.8	586.9	585.1	582.3	579.6	576.8	574.0	571.6
50°	559.5	558.7	558.0	557.2	556.5	554.8	552.2	549.6	546.9	544.3	541.7
52.5°	529.2	528.3	527.4	526.5	525.5	523.7	520.9	518.2	515.4	512.6	510.3
55°	481.2	480.5	480.0	479.4	478.9	477.3	474.7	472.1	469.4	466.8	464.5
57.5°	435.3	434.7	434.0	433.4	432.8	431.1	428.6	426.0	423.4	420.8	418.7
60°	403.6	402.7	401.7	400.8	399.9	398.2	395.8	393.3	390.9	388.5	386.7
62.5°	372.6	371.9	371.1	370.3	369.5	367.8	365.2	362.6	360.0	357.4	355.9
65°	326.1	325.2	324.2	323.3	322.3	320.9	319.1	317.2	315.3	313.5	311.6
67.5°	279.2	278.4	277.5	276.6	275.8	274.5	272.7	270.8	269.1	267.3	265.5
70°	250.3	249.0	247.6	246.3	245.0	243.6	242.1	240.6	239.1	237.7	236.1
72.5°	219.3	217.9	216.7	215.3	214.0	212.8	211.6	210.3	209.1	207.9	206.8
75°	173.6	172.6	171.7	170.8	169.8	168.9	167.9	167.0	166.1	165.2	164.4
77.5°	129.9	129.5	129.1	128.7	128.3	127.7	126.8	126.0	125.2	124.4	124.1
80°	103.6	103.1	102.5	102.0	101.4	100.9	100.5	100.2	99.8	99.4	99.0
82.5°	78.0	77.8	77.5	77.2	77.0	76.8	76.8	76.7	76.6	76.5	76.3
85°	45.5	45.5	45.5	45.5	45.5	45.3	44.9	44.6	44.2	43.8	43.8
87.5°	17.9	18.0	18.1	18.3	18.5	18.5	18.6	18.6	18.7	18.8	18.9
90°	1.7	3.2	4.7	6.1	7.5	8.8	9.8	10.9	11.9	12.9	13.7
92.5°	7.4	7.5	7.6	7.6	7.7	8.3	9.3	10.4	11.4	12.4	13.2
95°	32.3	27.9	23.4	19.0	14.6	12.4	12.5	12.7	12.8	12.9	13.7
97.5°	68.7	71.5	74.2	77.0	79.8	73.8	59.3	44.7	30.1	15.5	15.6
100°	96.4	98.8	101.2	103.5	105.8	98.0	80.0	61.9	43.9	25.9	23.7
102.5°	127.5	129.2	130.9	132.7	134.4	134.0	131.7	129.4	127.0	124.7	100.7
105°	177.0	177.8	178.6	179.4	180.1	180.9	181.5	182.1	182.8	183.5	184.7
107.5°	223.0	223.4	223.8	224.2	224.6	225.2	226.1	227.0	227.8	228.7	229.3
110°	254.1	254.4	254.8	255.2	255.6	256.2	257.0	257.8	258.6	259.3	259.6



TEST NUMBER: P332785-927

CATALOG NUMBER: S124DIW-S795D770U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	284.2	284.9	285.6	286.2	286.9	287.5	287.9	288.2	288.6	289.0	288.9
115°	330.5	330.9	331.3	331.6	332.0	332.2	332.0	331.9	331.8	331.6	331.9
117.5°	372.2	372.7	373.3	373.8	374.3	374.7	375.0	375.3	375.6	375.9	375.8
120°	400.4	401.0	401.5	402.0	402.5	402.7	402.6	402.5	402.3	402.2	402.5
122.5°	426.8	427.1	427.4	427.7	428.0	428.3	428.5	428.6	428.8	429.0	429.2
125°	464.5	465.1	465.6	466.1	466.6	466.8	466.5	466.3	466.0	465.7	466.1
127.5°	500.3	500.4	500.6	500.7	500.8	501.2	501.8	502.4	503.0	503.6	503.5
130°	523.3	523.5	523.6	523.7	523.9	524.1	524.5	524.9	525.3	525.7	525.9
132.5°	544.5	544.8	545.0	545.2	545.4	545.8	546.3	546.8	547.3	547.8	548.0
135°	576.2	576.2	576.0	575.8	575.8	575.9	576.5	576.9	577.5	578.1	578.3
137.5°	604.4	604.4	604.5	604.5	604.6	604.9	605.5	606.0	606.7	607.2	607.4
140°	622.7	623.0	623.2	623.5	623.8	624.0	624.3	624.6	624.8	625.1	625.4
142.5°	639.2	639.7	640.2	640.6	641.0	641.4	641.5	641.7	641.8	642.0	642.3
145°	664.5	664.9	665.3	665.7	666.1	666.2	666.2	666.2	666.2	666.2	666.4
147.5°	684.6	685.3	686.0	686.7	687.5	687.8	687.7	687.5	687.4	687.3	687.4
150°	699.2	699.7	700.2	700.8	701.2	701.5	701.3	701.2	701.1	700.9	700.9
152.5°	711.4	711.8	712.3	712.6	713.0	713.1	712.9	712.7	712.5	712.3	712.4
155°	728.6	728.7	728.8	729.0	729.1	729.0	728.6	728.2	727.8	727.4	727.9
157.5°	743.1	743.0	742.9	742.8	742.8	742.4	742.0	741.6	741.1	740.7	741.3
160°	751.5	751.1	750.8	750.4	750.0	749.6	749.6	749.4	749.2	749.2	750.0
162.5°	759.0	758.5	758.0	757.6	757.0	756.7	756.6	756.5	756.3	756.2	757.0
165°	768.6	767.9	767.2	766.6	766.0	765.6	765.6	765.6	765.6	765.6	766.7
167.5°	776.1	775.4	774.8	774.0	773.3	773.0	772.9	772.9	772.8	772.7	773.8
170°	780.3	779.5	778.7	777.9	777.2	776.8	777.0	777.1	777.2	777.4	778.4
172.5°	783.2	782.4	781.6	780.8	780.0	779.7	779.8	779.9	780.1	780.2	781.3
175°	786.2	785.4	784.7	783.9	783.1	782.8	782.8	783.0	783.2	783.2	784.4
177.5°	787.6	786.9	786.2	785.4	784.7	784.4	784.7	784.8	785.1	785.2	786.1
180°	786.2	786.2	786.2	786.2	786.2	786.2	786.2	786.2	786.2	786.2	786.2



TEST NUMBER: P332785-927

CATALOG NUMBER: S124DIW-S795D770U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1051.6	1051.6	1051.6	1051.6	1051.6	1051.6	1051.6	1051.6
2.5°	1047.8	1049.3	1050.8	1051.5	1051.4	1051.2	1051.1	1050.9
5°	1042.2	1044.3	1046.3	1047.2	1046.8	1046.5	1046.1	1045.7
7.5°	1030.6	1032.3	1033.9	1034.6	1034.4	1034.2	1034.0	1033.7
10°	1020.9	1022.4	1023.9	1024.5	1024.1	1023.7	1023.3	1022.9
12.5°	1009.1	1010.7	1012.3	1012.9	1012.4	1011.9	1011.3	1010.8
15°	986.4	987.5	988.6	989.0	988.4	987.9	987.3	986.7
17.5°	960.7	961.4	962.1	962.3	961.9	961.5	961.2	960.8
20°	941.5	942.1	942.6	942.7	942.3	942.0	941.6	941.2
22.5°	921.5	922.5	923.5	923.7	923.0	922.3	921.6	921.0
25°	888.5	888.7	888.9	888.6	887.9	887.1	886.4	885.6
27.5°	851.5	851.0	850.6	849.9	849.0	848.0	847.1	846.1
30°	825.9	825.2	824.4	823.6	822.7	821.7	820.8	819.9
32.5°	800.0	799.2	798.3	797.3	796.4	795.4	794.5	793.6
35°	759.1	757.8	756.5	755.3	754.4	753.5	752.6	751.6
37.5°	716.2	714.8	713.4	712.1	710.8	709.6	708.4	707.1
40°	686.3	684.5	682.6	681.2	680.2	679.4	678.4	677.5
42.5°	657.4	655.3	653.1	651.7	651.1	650.5	649.8	649.2
45°	612.7	610.6	608.6	607.3	606.7	606.1	605.5	605.0
47.5°	569.3	567.0	564.7	562.8	561.4	560.0	558.6	557.1
50°	539.1	536.5	533.9	532.0	530.8	529.7	528.6	527.5
52.5°	508.0	505.6	503.4	501.5	500.1	498.7	497.3	495.8
55°	462.3	460.1	457.8	456.1	455.0	453.9	452.7	451.6
57.5°	416.5	414.4	412.3	410.7	409.6	408.4	407.4	406.3
60°	385.1	383.4	381.7	380.4	379.5	378.5	377.6	376.7
62.5°	354.3	352.8	351.3	350.1	349.1	348.2	347.3	346.3
65°	309.7	307.8	305.9	304.6	303.6	302.7	301.7	300.8
67.5°	263.7	261.9	260.1	259.0	258.8	258.6	258.3	258.0
70°	234.6	233.1	231.6	230.6	230.0	229.5	228.9	228.4
72.5°	205.6	204.4	203.2	202.3	201.7	201.1	200.6	200.0
75°	163.7	162.9	162.2	161.7	161.5	161.3	161.1	161.0
77.5°	123.9	123.7	123.5	123.1	122.6	122.2	121.7	121.2
80°	98.7	98.3	97.9	97.7	97.4	97.3	97.1	96.9
82.5°	76.0	75.8	75.6	75.4	75.3	75.0	74.9	74.6
85°	43.8	43.8	43.8	43.7	43.6	43.3	43.2	42.9
87.5°	19.1	19.3	19.4	19.5	19.6	19.6	19.6	19.7
90°	14.5	15.3	16.1	16.6	16.9	17.1	17.3	17.7
92.5°	14.0	14.8	15.6	16.0	16.1	16.2	16.2	16.2
95°	14.5	15.3	16.1	16.6	16.6	16.8	17.0	17.0
97.5°	15.7	15.8	15.8	15.9	16.1	16.2	16.3	16.5
100°	21.5	19.2	17.0	15.9	16.1	16.2	16.3	16.5
102.5°	76.8	52.8	28.8	16.8	16.9	16.9	16.9	17.0
105°	185.8	187.0	188.1	186.4	181.7	177.0	172.3	167.6
107.5°	229.9	230.4	231.1	231.6	232.1	232.6	233.1	233.5
110°	259.8	260.1	260.4	260.7	261.1	261.5	261.9	262.3



TEST NUMBER: P332785-927

CATALOG NUMBER: S124DIW-S795D770U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	288.8	288.8	288.8	289.0	289.5	289.9	290.5	291.0
115°	332.2	332.4	332.7	332.8	332.8	332.8	332.8	332.8
117.5°	375.7	375.7	375.7	375.6	375.6	375.5	375.4	375.4
120°	402.7	403.0	403.2	403.2	403.0	402.7	402.5	402.2
122.5°	429.4	429.5	429.7	429.6	429.4	429.0	428.8	428.6
125°	466.5	466.9	467.3	467.5	467.7	467.8	467.9	468.1
127.5°	503.4	503.4	503.3	503.2	503.1	503.0	502.9	502.8
130°	525.9	526.1	526.2	526.2	526.2	526.2	526.2	526.2
132.5°	548.0	548.2	548.3	548.3	548.3	548.1	548.0	548.0
135°	578.5	578.8	579.1	579.3	579.6	579.9	580.1	580.4
137.5°	607.8	608.1	608.3	608.5	608.4	608.3	608.2	608.2
140°	625.8	626.2	626.6	626.9	627.0	627.2	627.3	627.4
142.5°	642.6	642.9	643.2	643.3	643.3	643.3	643.4	643.4
145°	666.5	666.6	666.8	666.9	667.2	667.5	667.7	668.0
147.5°	687.5	687.6	687.7	687.9	687.9	688.1	688.2	688.3
150°	700.9	700.9	700.9	701.0	701.2	701.2	701.4	701.5
152.5°	712.6	712.8	713.0	713.1	713.0	713.0	712.9	712.8
155°	728.4	729.0	729.4	729.5	729.1	728.7	728.3	728.0
157.5°	742.0	742.8	743.4	743.4	742.8	742.0	741.3	740.7
160°	750.8	751.5	752.3	752.3	751.5	750.8	750.0	749.2
162.5°	757.8	758.5	759.3	759.3	758.4	757.5	756.6	755.7
165°	767.7	768.7	769.8	769.8	768.6	767.4	766.2	765.0
167.5°	775.0	776.1	777.3	777.2	775.9	774.6	773.2	772.0
170°	779.4	780.5	781.6	781.4	780.1	778.8	777.5	776.2
172.5°	782.3	783.3	784.3	784.2	782.8	781.4	780.0	778.6
175°	785.6	786.8	788.0	787.7	786.2	784.7	783.1	781.5
177.5°	787.0	787.7	788.6	788.4	787.1	785.8	784.7	783.4
180°	786.2	786.2	786.2	786.2	786.2	786.2	786.2	786.2

(END OF REPORT)