

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333089

Luminaire Tested: **S124RDIW-S1020D1340U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333089  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIW-S1020D1340U835-4F0-1E-UDD-F  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1340 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 9541.2 lumens  
Efficiency: N/A  
Efficacy: 136.7 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 69.8  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333089

CATALOG NUMBER: S124RDIW-S1020D1340U835-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P333089

CATALOG NUMBER: S124RDIW-S1020D1340U835-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	50	50	50	44
1	97	92	89	85	88	85	82	79	70	68	66	57	56	54	45	44	43	37
2	88	81	75	70	80	74	69	65	62	58	55	50	48	46	40	38	37	32
3	81	71	64	59	73	66	59	54	55	50	46	45	41	39	35	33	31	27
4	74	63	56	50	67	58	51	46	49	44	40	40	36	33	32	29	27	23
5	68	56	48	43	62	52	45	40	44	38	34	36	32	29	29	26	24	20
6	62	51	43	37	57	47	40	35	39	34	30	33	29	25	26	23	21	18
7	58	46	38	32	53	42	35	30	36	30	26	30	26	23	24	21	19	16
8	54	41	34	29	49	38	32	27	33	27	24	27	23	20	22	19	17	14
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	20	17	15	13
10	47	35	28	23	43	32	26	22	28	22	19	23	19	16	19	16	14	12

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	14577	14577	14577
5°	14610	14431	14521
10°	14519	14258	14258
15°	14352	13959	13855
20°	14123	13564	13315
25°	13831	13104	12772
30°	13546	12618	12089
35°	13231	12113	11404
40°	12852	11540	10666
45°	12501	10970	9913
50°	12103	10315	9117
55°	11676	9633	8251
60°	11207	8885	7367
65°	10776	7950	6497
70°	10150	6918	5516
75°	9357	5736	4485
80°	8164	4370	4114
85°	6919	3974	3714



TEST NUMBER: P333089

CATALOG NUMBER: S124RDIW-S1020D1340U835-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	169.6	1.8
10°-20°	473.0	5.0
20°-30°	683.0	7.2
30°-40°	774.2	8.1
40°-50°	747.6	7.8
50°-60°	621.7	6.5
60°-70°	429.3	4.5
70°-80°	217.6	2.3
80°-90°	60.8	0.6
90°-100°	59.3	0.6
100°-110°	378.2	4.0
110°-120°	723.4	7.6
120°-130°	918.4	9.6
130°-140°	982.6	10.3
140°-150°	918.8	9.6
150°-160°	741.0	7.8
160°-170°	477.9	5.0
170°-180°	164.7	1.7
0°-30°	1325.6	13.9
0°-40°	2099.9	22.0
0°-60°	3469.2	36.4
0°-90°	4176.9	43.8
90°-120°	1160.9	12.2
90°-150°	3980.7	41.7
90°-180°	5364.0	56.2
0°-180°	9541.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1806	1806	1806	1806	1806	
5°	1803	1797	1781	1794	1792	171
15°	1717	1704	1670	1667	1658	484
25°	1553	1526	1471	1448	1434	715
35°	1342	1297	1229	1183	1157	839
45°	1095	1042	961	896	868	844
55°	830	772	684	615	586	742
65°	564	503	416	359	340	557
75°	300	248	184	153	144	317
85°	75	48	43	40	40	84
90°	4	18	28	36	39	7
95°	71	30	28	36	38	92
105°	390	398	405	413	370	408
115°	729	733	732	734	734	717
125°	1025	1029	1027	1031	1032	914
135°	1271	1270	1275	1278	1280	979
145°	1466	1469	1470	1471	1474	916
155°	1607	1608	1604	1609	1606	741
165°	1695	1689	1689	1698	1688	479
175°	1734	1727	1728	1738	1724	165
180°	1734	1734	1734	1734	1734	



TEST NUMBER: P333089

CATALOG NUMBER: S124RDIW-S1020D1340U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7
2.5°	1810.1	1809.1	1808.1	1807.2	1806.2	1804.3	1801.6	1798.9	1796.2	1793.5	1796.2
5°	1802.9	1801.7	1800.5	1799.2	1798.0	1795.5	1791.9	1788.2	1784.5	1780.8	1783.9
7.5°	1786.6	1785.3	1784.0	1782.7	1781.4	1778.4	1773.6	1768.8	1764.0	1759.2	1761.2
10°	1771.1	1769.6	1768.0	1766.5	1765.0	1761.4	1755.9	1750.4	1744.8	1739.3	1740.5
12.5°	1751.2	1749.4	1747.6	1745.9	1744.1	1739.9	1733.4	1726.9	1720.4	1713.9	1714.6
15°	1717.2	1714.4	1711.7	1708.9	1706.1	1700.9	1693.2	1685.5	1677.9	1670.2	1669.6
17.5°	1676.0	1672.0	1668.0	1664.0	1660.0	1653.4	1644.2	1635.0	1625.8	1616.5	1614.8
20°	1643.9	1639.9	1635.9	1631.9	1627.9	1620.7	1610.3	1599.8	1589.4	1578.9	1576.5
22.5°	1608.5	1604.0	1599.5	1595.1	1590.6	1582.7	1571.6	1560.4	1549.2	1538.0	1534.3
25°	1552.7	1547.1	1541.6	1536.1	1530.5	1521.5	1508.9	1496.3	1483.7	1471.1	1465.9
27.5°	1494.0	1487.1	1480.2	1473.2	1466.3	1456.1	1442.6	1429.2	1415.7	1402.2	1395.8
30°	1453.1	1445.4	1437.8	1430.1	1422.4	1411.3	1396.9	1382.4	1368.0	1353.6	1345.9
32.5°	1410.0	1401.3	1392.6	1384.0	1375.3	1363.5	1348.6	1333.7	1318.7	1303.8	1294.9
35°	1342.5	1332.7	1322.8	1313.0	1303.2	1290.6	1275.2	1259.9	1244.5	1229.1	1218.7
37.5°	1270.3	1260.2	1250.1	1239.9	1229.8	1216.2	1199.2	1182.2	1165.1	1148.1	1136.4
40°	1219.5	1209.3	1199.2	1189.0	1178.9	1165.1	1147.6	1130.0	1112.5	1095.0	1082.1
42.5°	1170.8	1160.2	1149.5	1138.9	1128.3	1113.8	1095.6	1077.3	1059.1	1040.8	1027.7
45°	1095.0	1083.7	1072.3	1060.9	1049.5	1034.6	1016.2	997.8	979.3	960.9	945.9
47.5°	1016.8	1005.0	993.3	981.6	969.8	954.4	935.2	916.0	896.8	877.7	862.1
50°	963.7	951.7	939.7	927.7	915.7	899.9	880.3	860.6	840.9	821.3	805.9
52.5°	909.5	897.7	886.0	874.3	862.5	846.6	826.4	806.3	786.1	766.0	750.4
55°	829.6	817.3	805.0	792.7	780.4	764.3	744.3	724.3	704.4	684.4	668.4
57.5°	750.5	737.7	724.9	712.1	699.4	683.1	663.5	643.8	624.1	604.5	588.3
60°	694.1	681.8	669.5	657.2	644.9	628.9	609.3	589.6	569.9	550.3	534.3
62.5°	643.2	630.4	617.6	604.8	592.1	575.6	555.4	535.3	515.1	495.0	480.2
65°	564.1	550.9	537.7	524.5	511.3	494.8	475.2	455.5	435.8	416.2	403.0
67.5°	482.0	469.3	456.7	444.0	431.3	415.9	397.6	379.4	361.1	342.9	331.5
70°	430.0	417.1	404.2	391.3	378.4	363.2	345.7	328.1	310.6	293.1	283.0
72.5°	374.7	363.0	351.3	339.7	328.0	313.9	297.4	280.8	264.3	247.8	239.1
75°	300.0	288.7	277.3	265.9	254.6	241.6	227.2	212.8	198.3	183.9	176.8
77.5°	224.3	214.6	205.0	195.3	185.7	175.0	163.3	151.7	140.0	128.3	124.2
80°	175.6	166.7	157.8	148.9	140.0	130.9	121.7	112.5	103.2	94.0	93.1
82.5°	133.6	125.4	117.2	109.0	100.9	94.1	88.9	83.6	78.3	73.0	72.3
85°	74.7	68.5	62.4	56.2	50.1	46.5	45.6	44.7	43.8	42.9	42.2
87.5°	26.2	24.9	23.6	22.2	20.9	20.3	20.5	20.8	21.0	21.2	21.3
90°	3.9	7.1	10.2	13.4	16.6	19.3	21.6	23.9	26.2	28.5	30.3
92.5°	16.3	16.5	16.7	16.9	17.0	18.3	20.6	22.9	25.2	27.5	29.2
95°	71.3	61.5	51.7	41.9	32.1	27.4	27.7	28.0	28.2	28.5	30.3
97.5°	151.5	157.6	163.7	169.8	175.9	162.9	130.7	98.6	66.4	34.2	34.4
100°	212.7	217.9	223.1	228.3	233.5	216.2	176.4	136.6	96.8	57.1	52.2
102.5°	281.2	285.0	288.8	292.6	296.4	295.7	290.5	285.4	280.2	275.0	222.1
105°	390.4	392.1	393.9	395.6	397.3	398.9	400.4	401.8	403.2	404.7	407.3
107.5°	491.8	492.7	493.6	494.4	495.3	496.7	498.7	500.6	502.6	504.6	505.8
110°	560.3	561.2	562.1	562.9	563.8	565.1	566.8	568.5	570.3	572.0	572.6



TEST NUMBER: P333089

CATALOG NUMBER: S124RDIW-S1020D1340U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	626.7	628.3	629.9	631.4	633.0	634.1	635.0	635.8	636.6	637.4	637.3
115°	728.9	729.8	730.7	731.5	732.4	732.7	732.4	732.1	731.8	731.5	732.1
117.5°	821.0	822.2	823.3	824.5	825.6	826.5	827.2	827.8	828.4	829.1	829.0
120°	883.3	884.4	885.6	886.8	887.9	888.3	888.1	887.8	887.5	887.2	887.8
122.5°	941.4	942.1	942.8	943.5	944.2	944.7	945.1	945.5	945.9	946.3	946.7
125°	1024.7	1025.8	1027.0	1028.1	1029.3	1029.6	1029.0	1028.4	1027.8	1027.3	1028.1
127.5°	1103.5	1103.8	1104.1	1104.4	1104.7	1105.5	1106.8	1108.1	1109.5	1110.8	1110.6
130°	1154.4	1154.7	1155.0	1155.2	1155.5	1156.1	1157.0	1157.8	1158.7	1159.6	1159.9
132.5°	1201.1	1201.6	1202.1	1202.6	1203.1	1204.0	1205.1	1206.1	1207.2	1208.3	1208.6
135°	1271.1	1270.8	1270.5	1270.3	1270.0	1270.4	1271.5	1272.7	1273.9	1275.0	1275.6
137.5°	1333.1	1333.2	1333.3	1333.5	1333.6	1334.3	1335.5	1336.8	1338.1	1339.3	1340.0
140°	1373.6	1374.2	1374.7	1375.3	1375.9	1376.5	1377.0	1377.6	1378.2	1378.8	1379.6
142.5°	1409.9	1410.9	1412.0	1413.0	1414.1	1414.7	1415.1	1415.4	1415.8	1416.1	1416.8
145°	1465.7	1466.5	1467.4	1468.3	1469.1	1469.6	1469.6	1469.6	1469.6	1469.6	1469.9
147.5°	1510.0	1511.6	1513.3	1514.9	1516.5	1517.2	1516.9	1516.6	1516.3	1516.0	1516.2
150°	1542.2	1543.4	1544.5	1545.7	1546.8	1547.2	1547.0	1546.7	1546.4	1546.1	1546.1
152.5°	1569.2	1570.1	1571.0	1571.9	1572.9	1573.1	1572.6	1572.0	1571.5	1571.0	1571.5
155°	1607.1	1607.3	1607.6	1607.9	1608.2	1607.9	1607.1	1606.2	1605.3	1604.5	1605.6
157.5°	1639.0	1638.8	1638.6	1638.4	1638.3	1637.7	1636.7	1635.7	1634.8	1633.8	1635.3
160°	1657.6	1656.8	1655.9	1655.0	1654.2	1653.6	1653.3	1653.0	1652.7	1652.5	1654.2
162.5°	1674.2	1673.1	1672.1	1671.0	1669.9	1669.2	1668.9	1668.6	1668.3	1668.0	1669.7
165°	1695.3	1693.8	1692.4	1690.9	1689.5	1688.8	1688.8	1688.8	1688.8	1688.8	1691.1
167.5°	1711.9	1710.4	1708.9	1707.4	1705.9	1705.0	1704.9	1704.7	1704.5	1704.3	1706.9
170°	1721.2	1719.5	1717.7	1716.0	1714.3	1713.6	1713.8	1714.1	1714.4	1714.7	1717.0
172.5°	1727.4	1725.7	1724.0	1722.2	1720.5	1719.8	1720.1	1720.4	1720.6	1720.9	1723.2
175°	1734.2	1732.4	1730.7	1729.0	1727.2	1726.5	1726.8	1727.1	1727.4	1727.7	1730.3
177.5°	1737.3	1735.7	1734.0	1732.4	1730.8	1730.2	1730.7	1731.2	1731.6	1732.1	1733.9
180°	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2



TEST NUMBER: P333089

CATALOG NUMBER: S124RDIW-S1020D1340U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7
2.5°	1798.9	1801.6	1804.3	1805.6	1805.3	1805.1	1804.8	1804.6
5°	1786.9	1790.0	1793.1	1794.3	1793.7	1793.1	1792.5	1791.9
7.5°	1763.2	1765.1	1767.1	1767.6	1766.6	1765.6	1764.6	1763.6
10°	1741.8	1743.0	1744.2	1744.2	1743.0	1741.8	1740.5	1739.3
12.5°	1715.3	1716.1	1716.8	1716.3	1714.6	1712.9	1711.2	1709.5
15°	1669.0	1668.3	1667.7	1666.3	1664.2	1662.0	1659.9	1657.7
17.5°	1613.1	1611.4	1609.7	1607.2	1603.9	1600.7	1597.4	1594.1
20°	1574.0	1571.6	1569.1	1565.9	1561.9	1557.9	1553.9	1549.9
22.5°	1530.6	1526.9	1523.3	1519.8	1516.5	1513.3	1510.0	1506.8
25°	1460.6	1455.4	1450.2	1446.0	1443.0	1439.9	1436.8	1433.8
27.5°	1389.3	1382.9	1376.4	1371.0	1366.6	1362.1	1357.7	1353.3
30°	1338.2	1330.5	1322.8	1316.5	1311.6	1306.7	1301.8	1296.9
32.5°	1286.0	1277.1	1268.2	1261.4	1256.7	1252.0	1247.4	1242.7
35°	1208.2	1197.8	1187.3	1179.4	1173.8	1168.3	1162.8	1157.2
37.5°	1124.8	1113.1	1101.4	1092.8	1087.3	1081.7	1076.2	1070.7
40°	1069.2	1056.3	1043.4	1034.2	1028.7	1023.1	1017.6	1012.1
42.5°	1014.5	1001.4	988.2	978.8	973.0	967.2	961.4	955.7
45°	930.8	915.7	900.7	890.4	884.9	879.3	873.8	868.3
47.5°	846.5	830.9	815.2	804.4	798.3	792.2	786.1	780.1
50°	790.5	775.2	759.8	749.2	743.4	737.5	731.7	725.9
52.5°	734.7	719.1	703.5	692.7	686.6	680.5	674.4	668.4
55°	652.4	636.5	620.5	609.6	603.7	597.9	592.1	586.2
57.5°	572.0	555.8	539.6	529.3	524.8	520.4	516.0	511.6
60°	518.3	502.3	486.4	475.9	471.0	466.1	461.2	456.3
62.5°	465.5	450.7	436.0	426.6	422.7	418.8	414.8	410.9
65°	389.7	376.5	363.3	354.9	351.2	347.5	343.8	340.1
67.5°	320.1	308.8	297.4	289.7	285.6	281.6	277.5	273.5
70°	272.8	262.7	252.6	245.9	242.9	239.8	236.7	233.7
72.5°	230.4	221.8	213.1	207.4	204.5	201.7	198.9	196.1
75°	169.8	162.7	155.6	151.2	149.3	147.5	145.6	143.8
77.5°	120.1	116.0	111.8	109.5	108.9	108.4	107.8	107.3
80°	92.2	91.3	90.3	89.7	89.4	89.1	88.8	88.5
82.5°	71.6	71.0	70.3	69.8	69.5	69.2	68.9	68.6
85°	41.6	41.0	40.4	40.1	40.1	40.1	40.1	40.1
87.5°	21.4	21.5	21.6	21.8	22.2	22.5	22.9	23.3
90°	32.0	33.7	35.5	36.6	37.2	37.8	38.3	38.9
92.5°	31.0	32.7	34.4	35.3	35.5	35.6	35.7	35.8
95°	32.0	33.7	35.5	36.5	36.7	37.0	37.3	37.6
97.5°	34.6	34.8	34.9	35.2	35.5	35.7	36.0	36.3
100°	47.3	42.4	37.5	35.2	35.5	35.7	36.0	36.3
102.5°	169.3	116.4	63.5	37.1	37.2	37.2	37.3	37.4
105°	409.9	412.5	415.1	411.2	400.8	390.4	380.0	369.7
107.5°	507.1	508.4	509.6	510.8	511.9	513.0	514.1	515.2
110°	573.2	573.7	574.3	575.0	575.9	576.8	577.6	578.5





TEST NUMBER: P333089

CATALOG NUMBER: S124RDIW-S1020D1340U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	637.1	637.0	636.9	637.4	638.5	639.6	640.7	641.8
115°	732.7	733.3	733.8	734.1	734.1	734.1	734.1	734.1
117.5°	828.8	828.7	828.6	828.5	828.4	828.3	828.2	828.0
120°	888.3	888.9	889.5	889.5	888.9	888.3	887.8	887.2
122.5°	947.0	947.4	947.7	947.6	947.0	946.4	945.9	945.3
125°	1029.0	1029.9	1030.7	1031.3	1031.6	1031.9	1032.2	1032.5
127.5°	1110.5	1110.3	1110.1	1109.9	1109.7	1109.4	1109.2	1109.0
130°	1160.1	1160.4	1160.7	1160.9	1160.9	1160.9	1160.9	1160.9
132.5°	1208.9	1209.2	1209.5	1209.5	1209.3	1209.1	1208.8	1208.6
135°	1276.2	1276.7	1277.3	1277.9	1278.5	1279.0	1279.6	1280.2
137.5°	1340.6	1341.2	1341.9	1342.1	1341.9	1341.8	1341.6	1341.4
140°	1380.5	1381.4	1382.2	1382.8	1383.1	1383.4	1383.7	1384.0
142.5°	1417.4	1418.0	1418.7	1419.0	1419.1	1419.1	1419.2	1419.2
145°	1470.1	1470.4	1470.7	1471.2	1471.7	1472.3	1472.9	1473.5
147.5°	1516.5	1516.7	1516.9	1517.2	1517.5	1517.8	1518.0	1518.3
150°	1546.1	1546.1	1546.1	1546.2	1546.5	1546.8	1547.1	1547.4
152.5°	1571.9	1572.4	1572.8	1573.0	1572.8	1572.6	1572.5	1572.3
155°	1606.8	1607.9	1609.1	1609.2	1608.4	1607.5	1606.6	1605.8
157.5°	1636.8	1638.3	1639.8	1639.8	1638.3	1636.8	1635.3	1633.8
160°	1655.9	1657.6	1659.4	1659.4	1657.6	1655.9	1654.2	1652.5
162.5°	1671.5	1673.2	1674.9	1674.8	1672.9	1670.9	1668.9	1667.0
165°	1693.4	1695.7	1698.0	1697.8	1695.3	1692.7	1690.1	1687.5
167.5°	1709.4	1711.9	1714.5	1714.3	1711.4	1708.5	1705.7	1702.8
170°	1719.3	1721.6	1723.9	1723.6	1720.8	1717.9	1715.0	1712.1
172.5°	1725.5	1727.9	1730.2	1729.8	1726.6	1723.5	1720.4	1717.3
175°	1732.9	1735.5	1738.1	1737.6	1734.2	1730.7	1727.2	1723.8
177.5°	1735.8	1737.6	1739.5	1739.0	1736.2	1733.5	1730.7	1727.9
180°	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2

(END OF REPORT)