

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333090

Luminaire Tested: **S124RDIW-S1020D1340U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333090
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S1020D1340U835-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8829.2 lumens
Efficiency: N/A
Efficacy: 126.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 69.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333090

CATALOG NUMBER: S124RDIW-S1020D1340U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333090

CATALOG NUMBER: S124RDIW-S1020D1340U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54	47								
1	97	93	89	86	89	86	83	80	72	70	68	59	58	56	48	47	46	40								
2	89	82	76	71	82	75	70	66	63	60	56	52	50	47	42	41	39	34								
3	81	72	65	59	74	67	60	55	56	52	48	47	43	40	38	35	33	29								
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	34	31	29	25								
5	68	57	49	43	63	53	46	40	45	39	35	37	33	30	31	28	25	22								
6	63	51	43	37	58	47	40	35	40	35	31	34	30	27	28	25	22	19								
7	58	46	38	33	54	43	36	31	37	31	27	31	27	24	25	22	20	17								
8	54	42	34	29	50	39	32	28	34	28	24	28	24	21	23	20	18	16								
9	50	38	31	26	46	36	29	25	31	25	22	26	22	19	22	19	16	14								
10	47	35	28	23	43	33	26	22	28	23	20	24	20	17	20	17	15	13								

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14577	14577	14577
5°	14610	14431	14521
10°	14519	14258	14258
15°	14352	13959	13855
20°	14123	13564	13315
25°	13831	13104	12772
30°	13546	12618	12089
35°	13231	12113	11404
40°	12852	11540	10666
45°	12501	10970	9913
50°	12103	10315	9117
55°	11676	9633	8251
60°	11207	8885	7367
65°	10776	7950	6497
70°	10150	6918	5516
75°	9357	5736	4485
80°	8164	4370	4114
85°	6919	3974	3714



TEST NUMBER: P333090

CATALOG NUMBER: S124RDIW-S1020D1340U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	169.6	1.9
10°-20°	473.0	5.4
20°-30°	683.0	7.7
30°-40°	774.2	8.8
40°-50°	747.6	8.5
50°-60°	621.7	7.0
60°-70°	429.3	4.9
70°-80°	217.6	2.5
80°-90°	60.8	0.7
90°-100°	110.6	1.3
100°-110°	327.6	3.7
110°-120°	556.1	6.3
120°-130°	733.3	8.3
130°-140°	823.5	9.3
140°-150°	809.2	9.2
150°-160°	680.6	7.7
160°-170°	452.8	5.1
170°-180°	158.6	1.8
0°-30°	1325.6	15.0
0°-40°	2099.9	23.8
0°-60°	3469.2	39.3
0°-90°	4176.9	47.3
90°-120°	994.3	11.3
90°-150°	3360.3	38.1
90°-180°	4652.0	52.7
0°-180°	8829.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1806	1806	1806	1806	1806	
5°	1803	1797	1781	1794	1792	171
15°	1717	1704	1670	1667	1658	484
25°	1553	1526	1471	1448	1434	715
35°	1342	1297	1229	1183	1157	839
45°	1095	1042	961	896	868	844
55°	830	772	684	615	586	742
65°	564	503	416	359	340	557
75°	300	248	184	153	144	317
85°	75	48	43	40	40	84
90°	4	18	28	36	39	8
95°	78	89	99	102	102	87
105°	302	304	309	313	316	321
115°	565	565	563	562	560	557
125°	824	823	822	820	817	734
135°	1062	1070	1070	1067	1063	821
145°	1290	1295	1297	1295	1292	807
155°	1478	1478	1477	1482	1477	680
165°	1609	1606	1603	1610	1606	453
175°	1674	1668	1666	1675	1666	159
180°	1677	1677	1677	1677	1677	



TEST NUMBER: P333090

CATALOG NUMBER: S124RDIW-S1020D1340U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7
2.5°	1810.1	1809.1	1808.1	1807.2	1806.2	1804.3	1801.6	1798.9	1796.2	1793.5	1796.2
5°	1802.9	1801.7	1800.5	1799.2	1798.0	1795.5	1791.9	1788.2	1784.5	1780.8	1783.9
7.5°	1786.6	1785.3	1784.0	1782.7	1781.4	1778.4	1773.6	1768.8	1764.0	1759.2	1761.2
10°	1771.1	1769.6	1768.0	1766.5	1765.0	1761.4	1755.9	1750.4	1744.8	1739.3	1740.5
12.5°	1751.2	1749.4	1747.6	1745.9	1744.1	1739.9	1733.4	1726.9	1720.4	1713.9	1714.6
15°	1717.2	1714.4	1711.7	1708.9	1706.1	1700.9	1693.2	1685.5	1677.9	1670.2	1669.6
17.5°	1676.0	1672.0	1668.0	1664.0	1660.0	1653.4	1644.2	1635.0	1625.8	1616.5	1614.8
20°	1643.9	1639.9	1635.9	1631.9	1627.9	1620.7	1610.3	1599.8	1589.4	1578.9	1576.5
22.5°	1608.5	1604.0	1599.5	1595.1	1590.6	1582.7	1571.6	1560.4	1549.2	1538.0	1534.3
25°	1552.7	1547.1	1541.6	1536.1	1530.5	1521.5	1508.9	1496.3	1483.7	1471.1	1465.9
27.5°	1494.0	1487.1	1480.2	1473.2	1466.3	1456.1	1442.6	1429.2	1415.7	1402.2	1395.8
30°	1453.1	1445.4	1437.8	1430.1	1422.4	1411.3	1396.9	1382.4	1368.0	1353.6	1345.9
32.5°	1410.0	1401.3	1392.6	1384.0	1375.3	1363.5	1348.6	1333.7	1318.7	1303.8	1294.9
35°	1342.5	1332.7	1322.8	1313.0	1303.2	1290.6	1275.2	1259.9	1244.5	1229.1	1218.7
37.5°	1270.3	1260.2	1250.1	1239.9	1229.8	1216.2	1199.2	1182.2	1165.1	1148.1	1136.4
40°	1219.5	1209.3	1199.2	1189.0	1178.9	1165.1	1147.6	1130.0	1112.5	1095.0	1082.1
42.5°	1170.8	1160.2	1149.5	1138.9	1128.3	1113.8	1095.6	1077.3	1059.1	1040.8	1027.7
45°	1095.0	1083.7	1072.3	1060.9	1049.5	1034.6	1016.2	997.8	979.3	960.9	945.9
47.5°	1016.8	1005.0	993.3	981.6	969.8	954.4	935.2	916.0	896.8	877.7	862.1
50°	963.7	951.7	939.7	927.7	915.7	899.9	880.3	860.6	840.9	821.3	805.9
52.5°	909.5	897.7	886.0	874.3	862.5	846.6	826.4	806.3	786.1	766.0	750.4
55°	829.6	817.3	805.0	792.7	780.4	764.3	744.3	724.3	704.4	684.4	668.4
57.5°	750.5	737.7	724.9	712.1	699.4	683.1	663.5	643.8	624.1	604.5	588.3
60°	694.1	681.8	669.5	657.2	644.9	628.9	609.3	589.6	569.9	550.3	534.3
62.5°	643.2	630.4	617.6	604.8	592.1	575.6	555.4	535.3	515.1	495.0	480.2
65°	564.1	550.9	537.7	524.5	511.3	494.8	475.2	455.5	435.8	416.2	403.0
67.5°	482.0	469.3	456.7	444.0	431.3	415.9	397.6	379.4	361.1	342.9	331.5
70°	430.0	417.1	404.2	391.3	378.4	363.2	345.7	328.1	310.6	293.1	283.0
72.5°	374.7	363.0	351.3	339.7	328.0	313.9	297.4	280.8	264.3	247.8	239.1
75°	300.0	288.7	277.3	265.9	254.6	241.6	227.2	212.8	198.3	183.9	176.8
77.5°	224.3	214.6	205.0	195.3	185.7	175.0	163.3	151.7	140.0	128.3	124.2
80°	175.6	166.7	157.8	148.9	140.0	130.9	121.7	112.5	103.2	94.0	93.1
82.5°	133.6	125.4	117.2	109.0	100.9	94.1	88.9	83.6	78.3	73.0	72.3
85°	74.7	68.5	62.4	56.2	50.1	46.5	45.6	44.7	43.8	42.9	42.2
87.5°	26.2	24.9	23.6	22.2	20.9	20.3	20.5	20.8	21.0	21.2	21.3
90°	3.9	7.1	10.2	13.4	16.6	19.3	21.6	23.9	26.2	28.5	30.3
92.5°	27.8	31.4	35.0	38.6	42.3	44.9	46.5	48.1	49.7	51.4	52.4
95°	77.8	80.4	83.0	85.6	88.2	90.5	92.5	94.5	96.5	98.6	99.4
97.5°	135.9	138.0	140.1	142.1	144.2	146.4	148.8	151.2	153.5	155.9	156.9
100°	181.6	182.7	183.9	185.0	186.2	188.0	190.6	193.2	195.8	198.4	199.0
102.5°	229.3	229.8	230.2	230.7	231.1	232.5	234.9	237.3	239.6	242.0	242.8
105°	302.2	302.5	302.8	303.0	303.3	304.0	305.2	306.4	307.5	308.7	309.5
107.5°	378.7	379.0	379.4	379.7	380.1	380.3	380.5	380.7	380.9	381.0	381.8
110°	430.6	431.1	431.7	432.3	432.9	433.0	432.7	432.4	432.2	431.9	431.3



TEST NUMBER: P333090

CATALOG NUMBER: S124RDIW-S1020D1340U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	484.5	484.6	484.7	484.9	485.0	484.8	484.3	483.7	483.2	482.7	482.6
115°	565.4	565.4	565.4	565.4	565.4	565.2	564.6	564.0	563.4	562.8	562.6
117.5°	641.7	641.9	642.2	642.4	642.6	642.5	642.1	641.7	641.3	640.9	639.9
120°	692.5	693.7	694.8	696.0	697.1	697.3	696.4	695.6	694.7	693.8	692.4
122.5°	745.4	745.9	746.4	746.8	747.3	747.3	746.9	746.5	746.1	745.7	744.7
125°	823.5	823.5	823.5	823.5	823.5	823.4	823.1	822.8	822.5	822.2	821.6
127.5°	894.3	895.2	896.1	896.9	897.8	898.0	897.5	897.1	896.6	896.1	895.6
130°	944.1	945.0	945.9	946.7	947.6	948.0	948.0	948.0	948.0	948.0	947.4
132.5°	995.0	995.6	996.2	996.9	997.5	997.7	997.5	997.2	997.0	996.8	996.2
135°	1062.1	1063.9	1065.6	1067.3	1069.1	1069.9	1069.9	1069.9	1069.9	1069.9	1069.4
137.5°	1135.3	1136.1	1136.9	1137.7	1138.5	1139.2	1139.6	1140.1	1140.5	1141.0	1140.2
140°	1184.1	1184.6	1185.2	1185.8	1186.4	1186.6	1186.6	1186.6	1186.6	1186.6	1186.4
142.5°	1228.7	1229.2	1229.8	1230.4	1231.0	1231.1	1230.9	1230.7	1230.5	1230.2	1230.2
145°	1290.4	1291.6	1292.7	1293.9	1295.0	1295.7	1296.0	1296.3	1296.6	1296.9	1296.6
147.5°	1351.6	1353.0	1354.4	1355.8	1357.1	1357.7	1357.5	1357.3	1357.0	1356.8	1356.6
150°	1389.0	1390.1	1391.3	1392.4	1393.6	1394.1	1394.1	1394.1	1394.1	1394.1	1394.1
152.5°	1424.2	1424.9	1425.6	1426.3	1427.0	1427.5	1427.7	1427.9	1428.2	1428.4	1429.1
155°	1478.4	1478.4	1478.4	1478.4	1478.4	1478.3	1478.0	1477.7	1477.4	1477.2	1478.3
157.5°	1524.1	1523.6	1523.1	1522.5	1522.0	1521.7	1521.7	1521.6	1521.6	1521.5	1522.4
160°	1551.1	1550.8	1550.5	1550.2	1549.9	1549.6	1549.3	1549.1	1548.8	1548.5	1549.3
162.5°	1576.0	1575.2	1574.5	1573.7	1573.0	1572.5	1572.2	1571.9	1571.6	1571.3	1572.9
165°	1609.4	1608.6	1607.7	1606.8	1606.0	1605.3	1604.7	1604.1	1603.5	1602.9	1604.7
167.5°	1635.1	1633.9	1632.7	1631.5	1630.3	1629.7	1629.8	1629.8	1629.9	1629.9	1631.7
170°	1649.6	1648.2	1646.8	1645.3	1643.9	1643.3	1643.6	1643.9	1644.2	1644.4	1646.2
172.5°	1660.0	1658.8	1657.6	1656.4	1655.2	1654.6	1654.7	1654.7	1654.8	1654.8	1656.8
175°	1674.3	1672.8	1671.4	1670.0	1668.5	1667.6	1667.4	1667.1	1666.8	1666.5	1668.5
177.5°	1678.9	1677.8	1676.6	1675.5	1674.3	1673.8	1673.8	1673.8	1673.8	1673.8	1675.4
180°	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9



TEST NUMBER: P333090

CATALOG NUMBER: S124RDIW-S1020D1340U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7
2.5°	1798.9	1801.6	1804.3	1805.6	1805.3	1805.1	1804.8	1804.6
5°	1786.9	1790.0	1793.1	1794.3	1793.7	1793.1	1792.5	1791.9
7.5°	1763.2	1765.1	1767.1	1767.6	1766.6	1765.6	1764.6	1763.6
10°	1741.8	1743.0	1744.2	1744.2	1743.0	1741.8	1740.5	1739.3
12.5°	1715.3	1716.1	1716.8	1716.3	1714.6	1712.9	1711.2	1709.5
15°	1669.0	1668.3	1667.7	1666.3	1664.2	1662.0	1659.9	1657.7
17.5°	1613.1	1611.4	1609.7	1607.2	1603.9	1600.7	1597.4	1594.1
20°	1574.0	1571.6	1569.1	1565.9	1561.9	1557.9	1553.9	1549.9
22.5°	1530.6	1526.9	1523.3	1519.8	1516.5	1513.3	1510.0	1506.8
25°	1460.6	1455.4	1450.2	1446.0	1443.0	1439.9	1436.8	1433.8
27.5°	1389.3	1382.9	1376.4	1371.0	1366.6	1362.1	1357.7	1353.3
30°	1338.2	1330.5	1322.8	1316.5	1311.6	1306.7	1301.8	1296.9
32.5°	1286.0	1277.1	1268.2	1261.4	1256.7	1252.0	1247.4	1242.7
35°	1208.2	1197.8	1187.3	1179.4	1173.8	1168.3	1162.8	1157.2
37.5°	1124.8	1113.1	1101.4	1092.8	1087.3	1081.7	1076.2	1070.7
40°	1069.2	1056.3	1043.4	1034.2	1028.7	1023.1	1017.6	1012.1
42.5°	1014.5	1001.4	988.2	978.8	973.0	967.2	961.4	955.7
45°	930.8	915.7	900.7	890.4	884.9	879.3	873.8	868.3
47.5°	846.5	830.9	815.2	804.4	798.3	792.2	786.1	780.1
50°	790.5	775.2	759.8	749.2	743.4	737.5	731.7	725.9
52.5°	734.7	719.1	703.5	692.7	686.6	680.5	674.4	668.4
55°	652.4	636.5	620.5	609.6	603.7	597.9	592.1	586.2
57.5°	572.0	555.8	539.6	529.3	524.8	520.4	516.0	511.6
60°	518.3	502.3	486.4	475.9	471.0	466.1	461.2	456.3
62.5°	465.5	450.7	436.0	426.6	422.7	418.8	414.8	410.9
65°	389.7	376.5	363.3	354.9	351.2	347.5	343.8	340.1
67.5°	320.1	308.8	297.4	289.7	285.6	281.6	277.5	273.5
70°	272.8	262.7	252.6	245.9	242.9	239.8	236.7	233.7
72.5°	230.4	221.8	213.1	207.4	204.5	201.7	198.9	196.1
75°	169.8	162.7	155.6	151.2	149.3	147.5	145.6	143.8
77.5°	120.1	116.0	111.8	109.5	108.9	108.4	107.8	107.3
80°	92.2	91.3	90.3	89.7	89.4	89.1	88.8	88.5
82.5°	71.6	71.0	70.3	69.8	69.5	69.2	68.9	68.6
85°	41.6	41.0	40.4	40.1	40.1	40.1	40.1	40.1
87.5°	21.4	21.5	21.6	21.8	22.2	22.5	22.9	23.3
90°	32.0	33.7	35.4	36.6	37.2	37.8	38.3	38.9
92.5°	53.4	54.5	55.5	56.2	56.5	56.9	57.2	57.6
95°	100.3	101.2	102.0	102.5	102.5	102.5	102.5	102.5
97.5°	158.0	159.0	160.0	160.6	160.6	160.6	160.6	160.6
100°	199.6	200.2	200.7	201.0	201.0	201.0	201.0	201.0
102.5°	243.6	244.4	245.2	245.7	246.0	246.2	246.4	246.7
105°	310.4	311.3	312.1	313.0	313.8	314.7	315.6	316.4
107.5°	382.6	383.4	384.3	384.6	384.6	384.5	384.5	384.4
110°	430.7	430.1	429.6	429.7	430.6	431.4	432.3	433.2



TEST NUMBER: P333090

CATALOG NUMBER: S124RDIW-S1020D1340U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	482.5	482.4	482.2	482.3	482.4	482.6	482.8	483.0
115°	562.3	562.0	561.7	561.4	561.1	560.8	560.5	560.3
117.5°	639.0	638.0	637.0	636.2	635.6	635.1	634.5	633.9
120°	691.0	689.5	688.1	687.6	688.2	688.8	689.4	689.9
122.5°	743.7	742.8	741.8	740.8	739.7	738.7	737.7	736.6
125°	821.1	820.5	819.9	819.3	818.8	818.2	817.6	817.0
127.5°	895.0	894.4	893.8	893.3	892.9	892.4	891.9	891.5
130°	946.9	946.3	945.7	944.9	943.7	942.5	941.4	940.2
132.5°	995.6	995.1	994.5	994.0	993.5	993.0	992.6	992.1
135°	1068.8	1068.2	1067.6	1066.9	1066.0	1065.2	1064.3	1063.4
137.5°	1139.5	1138.8	1138.0	1137.7	1137.9	1138.1	1138.2	1138.4
140°	1186.1	1185.8	1185.5	1185.2	1184.9	1184.6	1184.3	1184.1
142.5°	1230.1	1230.1	1230.0	1229.9	1229.9	1229.8	1229.8	1229.7
145°	1296.3	1296.0	1295.7	1295.2	1294.3	1293.4	1292.6	1291.7
147.5°	1356.3	1356.1	1355.9	1355.6	1355.3	1355.0	1354.8	1354.5
150°	1394.1	1394.1	1394.1	1394.0	1393.7	1393.4	1393.1	1392.9
152.5°	1429.8	1430.5	1431.2	1431.1	1430.4	1429.6	1428.9	1428.1
155°	1479.5	1480.6	1481.8	1481.8	1480.6	1479.5	1478.3	1477.2
157.5°	1523.2	1524.1	1525.0	1524.9	1523.9	1522.9	1522.0	1521.0
160°	1550.2	1551.1	1551.9	1551.6	1550.2	1548.8	1547.3	1545.9
162.5°	1574.4	1576.0	1577.5	1577.6	1576.1	1574.7	1573.3	1571.8
165°	1606.4	1608.1	1609.9	1610.2	1609.0	1607.8	1606.7	1605.5
167.5°	1633.4	1635.1	1636.8	1636.8	1635.0	1633.2	1631.5	1629.7
170°	1647.9	1649.6	1651.4	1651.2	1649.2	1647.2	1645.2	1643.2
172.5°	1658.7	1660.7	1662.7	1662.6	1660.6	1658.6	1656.6	1654.6
175°	1670.5	1672.5	1674.6	1674.6	1672.5	1670.5	1668.5	1666.5
177.5°	1677.0	1678.6	1680.2	1680.1	1678.3	1676.4	1674.6	1672.7
180°	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9

(END OF REPORT)