

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333089-927

Luminaire Tested: **S124RDIW-S1020D1340U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333089-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S1020D1340U927-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1340 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7558.4 lumens
Efficiency: N/A
Efficacy: 108.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 69.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333089-927

CATALOG NUMBER: S124RDIW-S1020D1340U927-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333089-927

CATALOG NUMBER: S124RDIW-S1020D1340U927-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	50	50	50	44
1	97	92	89	85	88	85	82	79	70	68	66	57	56	54	45	44	43	37
2	88	81	75	70	80	74	69	65	62	58	55	50	48	46	40	38	37	32
3	81	71	64	59	73	66	59	54	55	50	46	45	41	39	35	33	31	27
4	74	63	56	50	67	58	51	46	49	44	40	40	36	33	32	29	27	23
5	68	56	48	43	62	52	45	40	44	38	34	36	32	29	29	26	24	20
6	62	51	43	37	57	47	40	35	39	34	30	33	29	25	26	23	21	18
7	58	46	38	32	53	42	35	30	36	30	26	30	26	23	24	21	19	16
8	54	41	34	29	49	38	32	27	33	27	24	27	23	20	22	19	17	14
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	20	17	15	13
10	47	35	28	23	43	32	26	22	28	22	19	23	19	16	19	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11548	11548	11548
5°	11574	11432	11503
10°	11501	11294	11294
15°	11369	11058	10975
20°	11188	10746	10548
25°	10956	10381	10117
30°	10730	9996	9577
35°	10481	9596	9034
40°	10181	9141	8450
45°	9903	8691	7854
50°	9588	8171	7222
55°	9250	7631	6536
60°	8879	7038	5837
65°	8537	6298	5146
70°	8039	5481	4369
75°	7414	4545	3553
80°	6467	3464	3259
85°	5483	3149	2946



TEST NUMBER: P333089-927

CATALOG NUMBER: S124RDIW-S1020D1340U927-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	134.4	1.8
10°-20°	374.7	5.0
20°-30°	541.1	7.2
30°-40°	613.3	8.1
40°-50°	592.3	7.8
50°-60°	492.5	6.5
60°-70°	340.1	4.5
70°-80°	172.4	2.3
80°-90°	48.2	0.6
90°-100°	47.0	0.6
100°-110°	299.6	4.0
110°-120°	573.1	7.6
120°-130°	727.5	9.6
130°-140°	778.4	10.3
140°-150°	727.9	9.6
150°-160°	587.0	7.8
160°-170°	378.6	5.0
170°-180°	130.5	1.7
0°-30°	1050.1	13.9
0°-40°	1663.5	22.0
0°-60°	2748.2	36.4
0°-90°	3308.9	43.8
90°-120°	919.7	12.2
90°-150°	3153.4	41.7
90°-180°	4250.0	56.2
0°-180°	7558.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1430	1430	1430	1430	1430	
5°	1428	1423	1411	1421	1420	135
15°	1360	1349	1323	1321	1313	383
25°	1230	1209	1165	1147	1136	566
35°	1064	1027	974	937	917	664
45°	867	826	761	709	688	669
55°	657	612	542	487	464	588
65°	447	398	330	284	269	441
75°	238	197	146	122	114	251
85°	59	38	34	32	32	67
90°	3	14	23	29	31	5
95°	56	24	23	28	30	73
105°	309	315	321	327	293	324
115°	577	580	580	581	582	568
125°	812	816	814	817	818	724
135°	1007	1006	1010	1012	1014	776
145°	1161	1164	1164	1165	1167	725
155°	1273	1274	1271	1275	1272	587
165°	1343	1338	1338	1345	1337	379
175°	1374	1368	1369	1377	1366	131
180°	1374	1374	1374	1374	1374	



TEST NUMBER: P333089-927

CATALOG NUMBER: S124RDIW-S1020D1340U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1430.4	1430.4	1430.4	1430.4	1430.4	1430.4	1430.4	1430.4	1430.4	1430.4	1430.4
2.5°	1433.9	1433.1	1432.3	1431.6	1430.8	1429.3	1427.2	1425.1	1422.9	1420.8	1422.9
5°	1428.2	1427.3	1426.3	1425.3	1424.3	1422.4	1419.5	1416.6	1413.6	1410.7	1413.2
7.5°	1415.3	1414.3	1413.3	1412.2	1411.2	1408.8	1405.0	1401.2	1397.4	1393.6	1395.2
10°	1403.0	1401.8	1400.6	1399.4	1398.2	1395.3	1391.0	1386.6	1382.2	1377.8	1378.8
12.5°	1387.3	1385.8	1384.4	1383.1	1381.6	1378.3	1373.2	1368.0	1362.9	1357.7	1358.3
15°	1360.3	1358.1	1356.0	1353.8	1351.5	1347.4	1341.3	1335.2	1329.2	1323.1	1322.6
17.5°	1327.7	1324.5	1321.4	1318.2	1315.0	1309.8	1302.5	1295.2	1287.9	1280.6	1279.2
20°	1302.3	1299.1	1295.9	1292.8	1289.6	1283.9	1275.7	1267.3	1259.1	1250.8	1248.9
22.5°	1274.2	1270.7	1267.1	1263.6	1260.0	1253.8	1245.0	1236.1	1227.2	1218.4	1215.4
25°	1230.0	1225.6	1221.2	1216.9	1212.4	1205.3	1195.3	1185.3	1175.4	1165.4	1161.3
27.5°	1183.5	1178.1	1172.6	1167.0	1161.6	1153.5	1142.8	1132.2	1121.5	1110.8	1105.7
30°	1151.1	1145.0	1139.0	1132.9	1126.8	1118.0	1106.6	1095.1	1083.7	1072.3	1066.2
32.5°	1117.0	1110.1	1103.2	1096.4	1089.5	1080.1	1068.3	1056.5	1044.7	1032.8	1025.8
35°	1063.5	1055.7	1047.9	1040.1	1032.4	1022.4	1010.2	998.1	985.9	973.7	965.4
37.5°	1006.3	998.3	990.3	982.2	974.2	963.5	950.0	936.5	923.0	909.5	900.2
40°	966.1	958.0	950.0	941.9	933.9	923.0	909.1	895.2	881.3	867.4	857.2
42.5°	927.5	919.1	910.6	902.2	893.8	882.3	867.9	853.4	839.0	824.5	814.1
45°	867.4	858.5	849.5	840.4	831.4	819.6	805.0	790.4	775.8	761.2	749.3
47.5°	805.5	796.1	786.9	777.6	768.3	756.1	740.8	725.6	710.4	695.3	682.9
50°	763.4	753.9	744.4	734.9	725.4	712.9	697.4	681.8	666.1	650.6	638.4
52.5°	720.5	711.1	701.9	692.6	683.3	670.7	654.7	638.7	622.7	606.8	594.5
55°	657.2	647.5	637.7	628.0	618.2	605.5	589.6	573.8	558.0	542.2	529.5
57.5°	594.5	584.4	574.3	564.1	554.1	541.1	525.6	510.0	494.4	478.9	466.0
60°	549.9	540.1	530.4	520.6	510.9	498.2	482.7	467.1	451.5	435.9	423.3
62.5°	509.5	499.4	489.3	479.1	469.1	456.0	440.0	424.1	408.1	392.1	380.4
65°	446.9	436.4	426.0	415.5	405.0	392.0	376.4	360.8	345.2	329.7	319.2
67.5°	381.8	371.8	361.8	351.7	341.7	329.5	315.0	300.6	286.1	271.6	262.6
70°	340.6	330.4	320.2	310.0	299.8	287.7	273.9	259.9	246.1	232.2	224.2
72.5°	296.8	287.6	278.3	269.1	259.8	248.7	235.6	222.4	209.4	196.3	189.4
75°	237.7	228.7	219.7	210.6	201.7	191.4	180.0	168.6	157.1	145.7	140.1
77.5°	177.7	170.0	162.4	154.7	147.1	138.6	129.4	120.2	110.9	101.6	98.4
80°	139.1	132.1	125.0	118.0	110.9	103.7	96.4	89.1	81.8	74.5	73.8
82.5°	105.8	99.3	92.8	86.3	79.9	74.5	70.4	66.2	62.0	57.8	57.3
85°	59.2	54.3	49.4	44.5	39.7	36.8	36.1	35.4	34.7	34.0	33.4
87.5°	20.8	19.7	18.7	17.6	16.6	16.1	16.2	16.5	16.6	16.8	16.9
90°	3.1	5.6	8.1	10.6	13.2	15.3	17.1	18.9	20.8	22.6	24.0
92.5°	12.9	13.1	13.2	13.4	13.5	14.5	16.3	18.1	20.0	21.8	23.1
95°	56.5	48.7	41.0	33.2	25.4	21.7	21.9	22.2	22.3	22.6	24.0
97.5°	120.0	124.8	129.7	134.5	139.3	129.0	103.5	78.1	52.6	27.1	27.3
100°	168.5	172.6	176.7	180.9	185.0	171.3	139.7	108.2	76.7	45.2	41.4
102.5°	222.8	225.8	228.8	231.8	234.8	234.2	230.1	226.1	222.0	217.9	175.9
105°	309.3	310.6	312.0	313.4	314.7	316.0	317.2	318.3	319.4	320.6	322.7
107.5°	389.6	390.3	391.0	391.7	392.4	393.5	395.1	396.6	398.2	399.7	400.7
110°	443.9	444.6	445.3	445.9	446.6	447.7	449.0	450.4	451.8	453.1	453.6



TEST NUMBER: P333089-927

CATALOG NUMBER: S124RDIW-S1020D1340U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	496.5	497.7	499.0	500.2	501.5	502.3	503.0	503.7	504.3	504.9	504.9
115°	577.4	578.1	578.8	579.5	580.2	580.4	580.2	580.0	579.7	579.5	580.0
117.5°	650.4	651.3	652.2	653.2	654.0	654.7	655.3	655.8	656.2	656.8	656.7
120°	699.7	700.6	701.6	702.5	703.4	703.7	703.5	703.3	703.1	702.8	703.3
122.5°	745.8	746.3	746.9	747.4	748.0	748.4	748.7	749.0	749.3	749.6	750.0
125°	811.7	812.6	813.6	814.4	815.4	815.6	815.2	814.7	814.2	813.8	814.4
127.5°	874.2	874.4	874.6	874.9	875.1	875.8	876.8	877.8	878.9	880.0	879.8
130°	914.5	914.7	915.0	915.1	915.4	915.8	916.6	917.2	917.9	918.6	918.9
132.5°	951.5	951.9	952.3	952.7	953.1	953.8	954.7	955.5	956.3	957.2	957.4
135°	1006.9	1006.7	1006.5	1006.3	1006.1	1006.4	1007.3	1008.2	1009.2	1010.0	1010.5
137.5°	1056.1	1056.1	1056.2	1056.4	1056.5	1057.0	1058.0	1059.0	1060.0	1061.0	1061.5
140°	1088.1	1088.6	1089.0	1089.5	1090.0	1090.4	1090.8	1091.3	1091.8	1092.3	1092.9
142.5°	1116.9	1117.7	1118.6	1119.4	1120.2	1120.7	1121.0	1121.3	1121.6	1121.8	1122.4
145°	1161.1	1161.7	1162.4	1163.2	1163.8	1164.2	1164.2	1164.2	1164.2	1164.2	1164.4
147.5°	1196.2	1197.5	1198.8	1200.1	1201.3	1201.9	1201.7	1201.4	1201.2	1200.9	1201.1
150°	1221.7	1222.7	1223.5	1224.5	1225.3	1225.7	1225.5	1225.3	1225.0	1224.8	1224.8
152.5°	1243.1	1243.8	1244.5	1245.2	1246.0	1246.2	1245.8	1245.3	1244.9	1244.5	1244.9
155°	1273.1	1273.3	1273.5	1273.7	1274.0	1273.7	1273.1	1272.4	1271.7	1271.1	1271.9
157.5°	1298.4	1298.2	1298.1	1297.9	1297.8	1297.4	1296.6	1295.8	1295.1	1294.3	1295.5
160°	1313.1	1312.5	1311.8	1311.1	1310.4	1310.0	1309.7	1309.5	1309.2	1309.1	1310.4
162.5°	1326.3	1325.4	1324.6	1323.7	1322.9	1322.3	1322.1	1321.8	1321.6	1321.4	1322.7
165°	1343.0	1341.8	1340.7	1339.5	1338.4	1337.8	1337.8	1337.8	1337.8	1337.8	1339.7
167.5°	1356.1	1354.9	1353.8	1352.6	1351.4	1350.7	1350.6	1350.4	1350.3	1350.1	1352.2
170°	1363.5	1362.2	1360.7	1359.4	1358.0	1357.5	1357.6	1357.9	1358.1	1358.4	1360.2
172.5°	1368.4	1367.1	1365.7	1364.3	1362.9	1362.4	1362.6	1362.9	1363.0	1363.3	1365.1
175°	1373.8	1372.4	1371.0	1369.7	1368.3	1367.7	1367.9	1368.2	1368.4	1368.7	1370.7
177.5°	1376.3	1375.0	1373.6	1372.4	1371.1	1370.6	1371.0	1371.4	1371.7	1372.1	1373.6
180°	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8



TEST NUMBER: P333089-927

CATALOG NUMBER: S124RDIW-S1020D1340U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1430.4	1430.4	1430.4	1430.4	1430.4	1430.4	1430.4	1430.4
2.5°	1425.1	1427.2	1429.3	1430.4	1430.1	1430.0	1429.7	1429.6
5°	1415.6	1418.0	1420.5	1421.4	1420.9	1420.5	1420.0	1419.5
7.5°	1396.8	1398.3	1399.9	1400.3	1399.5	1398.7	1397.9	1397.1
10°	1379.8	1380.8	1381.7	1381.7	1380.8	1379.8	1378.8	1377.8
12.5°	1358.8	1359.5	1360.0	1359.6	1358.3	1356.9	1355.6	1354.2
15°	1322.2	1321.6	1321.1	1320.0	1318.3	1316.6	1314.9	1313.2
17.5°	1277.9	1276.5	1275.2	1273.2	1270.6	1268.0	1265.4	1262.8
20°	1246.9	1245.0	1243.0	1240.5	1237.3	1234.1	1231.0	1227.8
22.5°	1212.5	1209.6	1206.7	1204.0	1201.3	1198.8	1196.2	1193.7
25°	1157.1	1152.9	1148.8	1145.5	1143.1	1140.7	1138.2	1135.8
27.5°	1100.6	1095.5	1090.4	1086.1	1082.6	1079.0	1075.5	1072.1
30°	1060.1	1054.0	1047.9	1042.9	1039.0	1035.1	1031.3	1027.4
32.5°	1018.7	1011.7	1004.6	999.3	995.5	991.8	988.2	984.4
35°	957.1	948.9	940.6	934.3	929.9	925.5	921.1	916.7
37.5°	891.0	881.8	872.5	865.7	861.3	856.9	852.5	848.2
40°	847.0	836.8	826.6	819.3	814.9	810.5	806.1	801.8
42.5°	803.7	793.3	782.8	775.4	770.8	766.2	761.6	757.1
45°	737.4	725.4	713.5	705.4	701.0	696.6	692.2	687.9
47.5°	670.6	658.2	645.8	637.2	632.4	627.6	622.7	618.0
50°	626.2	614.1	601.9	593.5	588.9	584.2	579.6	575.0
52.5°	582.0	569.7	557.3	548.7	543.9	539.1	534.2	529.5
55°	516.8	504.2	491.5	482.9	478.2	473.6	469.1	464.4
57.5°	453.1	440.3	427.5	419.3	415.7	412.3	408.8	405.3
60°	410.6	397.9	385.3	377.0	373.1	369.2	365.4	361.5
62.5°	368.8	357.0	345.4	337.9	334.9	331.8	328.6	325.5
65°	308.7	298.3	287.8	281.1	278.2	275.3	272.4	269.4
67.5°	253.6	244.6	235.6	229.5	226.2	223.1	219.8	216.7
70°	216.1	208.1	200.1	194.8	192.4	190.0	187.5	185.1
72.5°	182.5	175.7	168.8	164.3	162.0	159.8	157.6	155.3
75°	134.5	128.9	123.3	119.8	118.3	116.8	115.3	113.9
77.5°	95.1	91.9	88.6	86.7	86.3	85.9	85.4	85.0
80°	73.0	72.3	71.5	71.1	70.8	70.6	70.3	70.1
82.5°	56.7	56.2	55.7	55.3	55.1	54.8	54.6	54.3
85°	33.0	32.5	32.0	31.8	31.8	31.8	31.8	31.8
87.5°	17.0	17.0	17.1	17.3	17.6	17.8	18.1	18.5
90°	25.3	26.7	28.1	29.0	29.5	29.9	30.3	30.8
92.5°	24.6	25.9	27.3	28.0	28.1	28.2	28.3	28.4
95°	25.3	26.7	28.1	28.9	29.1	29.3	29.5	29.8
97.5°	27.4	27.6	27.6	27.9	28.1	28.3	28.5	28.8
100°	37.5	33.6	29.7	27.9	28.1	28.3	28.5	28.8
102.5°	134.1	92.2	50.3	29.4	29.5	29.5	29.5	29.6
105°	324.7	326.8	328.8	325.7	317.5	309.3	301.0	292.9
107.5°	401.7	402.7	403.7	404.6	405.5	406.4	407.3	408.1
110°	454.1	454.5	455.0	455.5	456.2	456.9	457.6	458.3



TEST NUMBER: P333089-927

CATALOG NUMBER: S124RDIW-S1020D1340U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	504.7	504.6	504.5	504.9	505.8	506.7	507.6	508.4
115°	580.4	580.9	581.3	581.5	581.5	581.5	581.5	581.5
117.5°	656.6	656.5	656.4	656.3	656.2	656.2	656.1	655.9
120°	703.7	704.2	704.6	704.6	704.2	703.7	703.3	702.8
122.5°	750.2	750.5	750.8	750.7	750.2	749.7	749.3	748.8
125°	815.2	815.9	816.5	817.0	817.2	817.5	817.7	817.9
127.5°	879.7	879.6	879.4	879.2	879.1	878.8	878.7	878.5
130°	919.0	919.2	919.5	919.6	919.6	919.6	919.6	919.6
132.5°	957.7	957.9	958.1	958.1	958.0	957.8	957.6	957.4
135°	1011.0	1011.4	1011.9	1012.3	1012.8	1013.2	1013.7	1014.2
137.5°	1062.0	1062.5	1063.0	1063.2	1063.0	1063.0	1062.8	1062.6
140°	1093.6	1094.3	1095.0	1095.4	1095.7	1095.9	1096.1	1096.4
142.5°	1122.8	1123.3	1123.9	1124.1	1124.2	1124.2	1124.3	1124.3
145°	1164.6	1164.8	1165.1	1165.5	1165.9	1166.3	1166.8	1167.3
147.5°	1201.3	1201.5	1201.7	1201.9	1202.1	1202.4	1202.5	1202.8
150°	1224.8	1224.8	1224.8	1224.9	1225.1	1225.3	1225.6	1225.8
152.5°	1245.2	1245.6	1245.9	1246.1	1245.9	1245.8	1245.7	1245.5
155°	1272.9	1273.7	1274.7	1274.8	1274.1	1273.4	1272.7	1272.1
157.5°	1296.6	1297.8	1299.0	1299.0	1297.8	1296.6	1295.5	1294.3
160°	1311.8	1313.1	1314.5	1314.5	1313.1	1311.8	1310.4	1309.1
162.5°	1324.1	1325.5	1326.8	1326.7	1325.2	1323.7	1322.1	1320.6
165°	1341.5	1343.3	1345.1	1345.0	1343.0	1340.9	1338.9	1336.8
167.5°	1354.2	1356.1	1358.2	1358.0	1355.7	1353.4	1351.2	1348.9
170°	1362.0	1363.8	1365.6	1365.4	1363.2	1360.9	1358.6	1356.3
172.5°	1366.9	1368.8	1370.6	1370.3	1367.8	1365.3	1362.9	1360.4
175°	1372.8	1374.8	1376.9	1376.5	1373.8	1371.0	1368.3	1365.6
177.5°	1375.1	1376.5	1378.0	1377.6	1375.4	1373.2	1371.0	1368.8
180°	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8

(END OF REPORT)