

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333113

Luminaire Tested: **S124RDIW-S1195D1560U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333113
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S1195D1560U835-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1560 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 11060.9 lumens
Efficiency: N/A
Efficacy: 133.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 82.9
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333113

CATALOG NUMBER: S124RDIW-S1195D1560U835-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333113

CATALOG NUMBER: S124RDIW-S1195D1560U835-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	44				
1	97	92	89	85	88	85	81	79	70	68	66	57	55	54	45	44	43	37				
2	88	81	75	70	80	74	69	65	62	58	55	50	48	45	40	38	36	32				
3	80	71	64	58	73	66	59	54	55	50	46	45	41	39	35	33	31	27				
4	74	63	55	50	67	58	51	46	49	44	40	40	36	33	32	29	27	23				
5	68	56	48	43	62	52	45	40	44	38	34	36	32	29	29	26	24	20				
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	26	23	21	18				
7	58	46	38	32	53	42	35	30	36	30	26	30	26	23	24	21	19	16				
8	54	41	34	29	49	38	32	27	33	27	24	27	23	20	22	19	17	14				
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	20	17	15	13				
10	47	35	28	23	43	32	26	22	27	22	19	23	19	16	19	16	14	12				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16835	16835	16835
5°	16874	16667	16771
10°	16768	16467	16467
15°	16575	16121	16002
20°	16311	15667	15378
25°	15973	15134	14750
30°	15645	14573	13962
35°	15281	13991	13172
40°	14842	13328	12318
45°	14439	12670	11449
50°	13978	11912	10528
55°	13485	11125	9529
60°	12943	10261	8507
65°	12445	9181	7503
70°	11722	7990	6371
75°	10808	6625	5181
80°	9428	5049	4751
85°	7984	4585	4289



TEST NUMBER: P333113

CATALOG NUMBER: S124RDIW-S1195D1560U835-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	195.9	1.8
10°-20°	546.3	4.9
20°-30°	788.8	7.1
30°-40°	894.2	8.1
40°-50°	863.5	7.8
50°-60°	718.0	6.5
60°-70°	495.8	4.5
70°-80°	251.3	2.3
80°-90°	70.3	0.6
90°-100°	69.0	0.6
100°-110°	439.7	4.0
110°-120°	841.1	7.6
120°-130°	1067.8	9.7
130°-140°	1142.4	10.3
140°-150°	1068.3	9.7
150°-160°	861.5	7.8
160°-170°	555.6	5.0
170°-180°	191.5	1.7
0°-30°	1531.0	13.8
0°-40°	2425.2	21.9
0°-60°	4006.7	36.2
0°-90°	4824.1	43.6
90°-120°	1349.8	12.2
90°-150°	4628.2	41.8
90°-180°	6237.0	56.4
0°-180°	11060.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2085	2085	2085	2085	2085	
5°	2082	2075	2057	2072	2070	197
15°	1983	1967	1929	1925	1915	559
25°	1793	1762	1699	1672	1656	826
35°	1550	1498	1420	1367	1336	968
45°	1265	1204	1110	1034	1003	975
55°	958	892	790	710	677	857
65°	652	581	481	415	393	643
75°	346	287	212	177	166	366
85°	86	56	50	46	46	97
90°	4	21	33	42	45	8
95°	83	35	33	42	44	107
105°	454	463	470	480	430	475
115°	848	852	850	853	854	834
125°	1191	1197	1194	1199	1200	1063
135°	1478	1477	1482	1485	1488	1138
145°	1704	1708	1709	1710	1713	1064
155°	1868	1870	1865	1871	1867	861
165°	1971	1964	1964	1974	1962	557
175°	2016	2008	2009	2021	2004	192
180°	2016	2016	2016	2016	2016	



TEST NUMBER: P333113

CATALOG NUMBER: S124RDIW-S1195D1560U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2085.4	2085.4	2085.4	2085.4	2085.4	2085.4	2085.4	2085.4	2085.4	2085.4	2085.4
2.5°	2090.5	2089.4	2088.3	2087.1	2086.0	2083.9	2080.8	2077.6	2074.5	2071.4	2074.5
5°	2082.2	2080.8	2079.4	2078.0	2076.6	2073.7	2069.5	2065.2	2061.0	2056.7	2060.2
7.5°	2063.4	2061.9	2060.4	2058.9	2057.4	2053.9	2048.4	2042.9	2037.3	2031.8	2034.1
10°	2045.5	2043.7	2042.0	2040.2	2038.4	2034.3	2028.0	2021.6	2015.2	2008.8	2010.2
12.5°	2022.5	2020.5	2018.4	2016.3	2014.3	2009.5	2002.0	1994.5	1986.9	1979.4	1980.3
15°	1983.2	1980.0	1976.9	1973.7	1970.5	1964.4	1955.6	1946.7	1937.8	1928.9	1928.2
17.5°	1935.7	1931.0	1926.4	1921.8	1917.2	1909.6	1898.9	1888.3	1877.6	1867.0	1865.0
20°	1898.6	1894.0	1889.4	1884.8	1880.2	1871.8	1859.8	1847.7	1835.6	1823.6	1820.7
22.5°	1857.7	1852.6	1847.4	1842.2	1837.0	1828.0	1815.0	1802.1	1789.2	1776.3	1772.0
25°	1793.2	1786.8	1780.4	1774.1	1767.7	1757.2	1742.7	1728.1	1713.6	1699.0	1693.0
27.5°	1725.5	1717.5	1709.5	1701.5	1693.4	1681.7	1666.1	1650.6	1635.0	1619.5	1612.0
30°	1678.3	1669.4	1660.5	1651.6	1642.8	1630.0	1613.3	1596.6	1580.0	1563.3	1554.4
32.5°	1628.4	1618.4	1608.4	1598.4	1588.4	1574.8	1557.5	1540.3	1523.0	1505.8	1495.5
35°	1550.5	1539.1	1527.8	1516.4	1505.1	1490.5	1472.8	1455.1	1437.3	1419.6	1407.5
37.5°	1467.2	1455.4	1443.7	1432.0	1420.3	1404.6	1385.0	1365.3	1345.7	1326.0	1312.5
40°	1408.4	1396.7	1385.0	1373.3	1361.5	1345.6	1325.4	1305.1	1284.9	1264.7	1249.8
42.5°	1352.2	1339.9	1327.6	1315.3	1303.1	1286.4	1265.3	1244.2	1223.2	1202.1	1186.9
45°	1264.7	1251.5	1238.4	1225.3	1212.2	1194.9	1173.7	1152.4	1131.1	1109.8	1092.4
47.5°	1174.3	1160.7	1147.2	1133.6	1120.1	1102.2	1080.1	1057.9	1035.8	1013.7	995.6
50°	1113.0	1099.1	1085.3	1071.5	1057.6	1039.3	1016.6	993.9	971.2	948.5	930.8
52.5°	1050.4	1036.8	1023.3	1009.7	996.2	977.7	954.5	931.2	907.9	884.6	866.6
55°	958.1	943.9	929.7	915.5	901.3	882.7	859.6	836.6	813.5	790.4	772.0
57.5°	866.7	852.0	837.2	822.5	807.7	789.0	766.3	743.5	720.8	698.1	679.4
60°	801.6	787.4	773.2	759.0	744.8	726.4	703.7	681.0	658.2	635.5	617.1
62.5°	742.8	728.1	713.3	698.6	683.8	664.8	641.5	618.2	594.9	571.7	554.6
65°	651.5	636.2	621.0	605.7	590.5	571.5	548.8	526.1	503.4	480.6	465.4
67.5°	556.6	542.0	527.4	512.8	498.2	480.3	459.2	438.2	417.1	396.0	382.9
70°	496.6	481.7	466.8	451.9	437.0	419.4	399.2	379.0	358.8	338.5	326.8
72.5°	432.7	419.3	405.8	392.3	378.8	362.5	343.4	324.3	305.2	286.1	276.1
75°	346.5	333.4	320.2	307.1	294.0	279.1	262.4	245.7	229.1	212.4	204.2
77.5°	259.0	247.9	236.7	225.6	214.4	202.1	188.6	175.2	161.7	148.2	143.4
80°	202.8	192.5	182.2	171.9	161.6	151.2	140.5	129.9	119.2	108.6	107.5
82.5°	154.3	144.8	135.4	125.9	116.5	108.7	102.6	96.5	90.4	84.3	83.5
85°	86.2	79.1	72.0	64.9	57.8	53.8	52.7	51.6	50.6	49.5	48.8
87.5°	30.3	28.8	27.2	25.7	24.2	23.5	23.8	24.0	24.3	24.5	24.6
90°	4.5	8.2	11.9	15.6	19.3	22.5	25.1	27.8	30.5	33.2	35.2
92.5°	19.0	19.2	19.4	19.6	19.8	21.2	23.9	26.6	29.3	32.0	34.0
95°	82.9	71.5	60.2	48.8	37.4	31.8	32.2	32.5	32.8	33.2	35.2
97.5°	176.1	183.2	190.3	197.5	204.6	189.4	152.0	114.6	77.2	39.8	40.0
100°	247.3	253.4	259.4	265.4	271.4	251.3	205.1	158.8	112.6	66.4	60.7
102.5°	326.9	331.4	335.8	340.2	344.6	343.8	337.8	331.8	325.7	319.7	258.2
105°	453.9	455.9	457.9	460.0	462.0	463.8	465.5	467.2	468.8	470.5	473.5
107.5°	571.8	572.9	573.9	574.9	575.9	577.5	579.8	582.1	584.3	586.6	588.1
110°	651.5	652.5	653.5	654.5	655.5	657.0	659.0	661.0	663.0	665.0	665.7



TEST NUMBER: P333113

CATALOG NUMBER: S124RDIW-S1195D1560U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	728.7	730.5	732.3	734.1	735.9	737.3	738.2	739.2	740.1	741.1	740.9
115°	847.5	848.5	849.5	850.5	851.5	851.9	851.5	851.2	850.9	850.5	851.2
117.5°	954.6	955.9	957.3	958.6	960.0	961.0	961.7	962.5	963.2	963.9	963.8
120°	1027.0	1028.3	1029.7	1031.0	1032.3	1032.8	1032.5	1032.2	1031.8	1031.5	1032.2
122.5°	1094.5	1095.3	1096.1	1096.9	1097.8	1098.4	1098.9	1099.3	1099.8	1100.3	1100.7
125°	1191.4	1192.7	1194.0	1195.4	1196.7	1197.0	1196.4	1195.7	1195.0	1194.4	1195.4
127.5°	1283.0	1283.4	1283.7	1284.0	1284.4	1285.3	1286.9	1288.4	1289.9	1291.5	1291.3
130°	1342.2	1342.5	1342.8	1343.2	1343.5	1344.2	1345.2	1346.2	1347.2	1348.2	1348.5
132.5°	1396.4	1397.0	1397.7	1398.3	1398.9	1399.8	1401.1	1402.3	1403.6	1404.9	1405.2
135°	1477.9	1477.5	1477.2	1476.9	1476.5	1477.0	1478.4	1479.7	1481.1	1482.4	1483.1
137.5°	1550.0	1550.1	1550.2	1550.4	1550.5	1551.3	1552.8	1554.3	1555.7	1557.2	1557.9
140°	1597.0	1597.7	1598.4	1599.0	1599.7	1600.4	1601.0	1601.7	1602.4	1603.0	1604.1
142.5°	1639.2	1640.4	1641.7	1642.9	1644.1	1644.9	1645.3	1645.7	1646.1	1646.5	1647.2
145°	1704.1	1705.1	1706.1	1707.1	1708.1	1708.6	1708.6	1708.6	1708.6	1708.6	1708.9
147.5°	1755.7	1757.5	1759.4	1761.3	1763.2	1763.9	1763.6	1763.3	1762.9	1762.6	1762.9
150°	1793.1	1794.4	1795.7	1797.1	1798.4	1798.9	1798.6	1798.3	1797.9	1797.6	1797.6
152.5°	1824.4	1825.5	1826.6	1827.6	1828.7	1829.0	1828.3	1827.7	1827.1	1826.5	1827.1
155°	1868.5	1868.8	1869.1	1869.5	1869.8	1869.5	1868.5	1867.5	1866.5	1865.4	1866.8
157.5°	1905.6	1905.4	1905.2	1905.0	1904.8	1904.1	1902.9	1901.8	1900.7	1899.5	1901.3
160°	1927.3	1926.3	1925.3	1924.3	1923.3	1922.6	1922.2	1921.9	1921.6	1921.2	1923.3
162.5°	1946.6	1945.3	1944.0	1942.8	1941.5	1940.7	1940.3	1940.0	1939.7	1939.3	1941.3
165°	1971.0	1969.3	1967.7	1966.0	1964.3	1963.5	1963.5	1963.5	1963.5	1963.5	1966.1
167.5°	1990.3	1988.6	1986.8	1985.1	1983.3	1982.4	1982.2	1982.0	1981.8	1981.6	1984.5
170°	2001.2	1999.2	1997.1	1995.1	1993.1	1992.3	1992.6	1993.0	1993.3	1993.6	1996.3
172.5°	2008.4	2006.4	2004.4	2002.4	2000.4	1999.5	1999.9	2000.2	2000.5	2000.9	2003.5
175°	2016.2	2014.2	2012.2	2010.2	2008.2	2007.4	2007.7	2008.0	2008.4	2008.7	2011.7
177.5°	2019.9	2018.0	2016.1	2014.2	2012.4	2011.7	2012.2	2012.8	2013.3	2013.8	2016.0
180°	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2



TEST NUMBER: P333113

CATALOG NUMBER: S124RDIW-S1195D1560U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	2085.4	2085.4	2085.4	2085.4	2085.4	2085.4	2085.4	2085.4
2.5°	2077.6	2080.8	2083.9	2085.3	2085.0	2084.7	2084.4	2084.2
5°	2063.8	2067.3	2070.9	2072.3	2071.6	2070.9	2070.2	2069.5
7.5°	2036.3	2038.6	2040.9	2041.4	2040.3	2039.2	2038.0	2036.9
10°	2011.6	2013.0	2014.5	2014.5	2013.0	2011.6	2010.2	2008.8
12.5°	1981.1	1982.0	1982.8	1982.2	1980.3	1978.3	1976.3	1974.3
15°	1927.5	1926.8	1926.1	1924.5	1922.0	1919.5	1917.1	1914.6
17.5°	1863.0	1861.0	1859.0	1856.2	1852.4	1848.6	1844.9	1841.1
20°	1817.9	1815.0	1812.2	1808.5	1803.9	1799.3	1794.6	1790.0
22.5°	1767.8	1763.5	1759.3	1755.3	1751.5	1747.7	1744.0	1740.2
25°	1686.9	1680.9	1674.9	1670.1	1666.5	1663.0	1659.4	1655.9
27.5°	1604.6	1597.1	1589.7	1583.4	1578.3	1573.2	1568.1	1563.0
30°	1545.5	1536.7	1527.8	1520.5	1514.8	1509.2	1503.5	1497.8
32.5°	1485.2	1474.9	1464.6	1456.8	1451.4	1446.0	1440.6	1435.2
35°	1395.4	1383.4	1371.3	1362.1	1355.7	1349.3	1342.9	1336.5
37.5°	1299.0	1285.5	1272.1	1262.1	1255.7	1249.3	1243.0	1236.6
40°	1234.9	1220.0	1205.1	1194.4	1188.0	1181.6	1175.3	1168.9
42.5°	1171.7	1156.5	1141.3	1130.4	1123.7	1117.1	1110.4	1103.7
45°	1075.0	1057.6	1040.2	1028.3	1022.0	1015.6	1009.2	1002.8
47.5°	977.6	959.6	941.6	929.0	922.0	915.0	907.9	900.9
50°	913.0	895.3	877.5	865.3	858.6	851.8	845.1	838.3
52.5°	848.6	830.6	812.5	800.0	793.0	786.0	778.9	771.9
55°	753.5	735.1	716.6	704.0	697.3	690.5	683.8	677.0
57.5°	660.7	641.9	623.2	611.3	606.2	601.0	595.9	590.8
60°	598.6	580.2	561.7	549.7	544.0	538.3	532.6	526.9
62.5°	537.6	520.6	503.5	492.7	488.2	483.7	479.1	474.6
65°	450.1	434.9	419.6	409.8	405.6	401.3	397.1	392.8
67.5°	369.8	356.6	343.5	334.6	329.9	325.2	320.5	315.8
70°	315.1	303.4	291.7	284.1	280.5	277.0	273.4	269.9
72.5°	266.1	256.1	246.1	239.5	236.2	233.0	229.7	226.4
75°	196.1	187.9	179.7	174.6	172.5	170.3	168.2	166.1
77.5°	138.7	133.9	129.2	126.5	125.8	125.2	124.6	123.9
80°	106.5	105.4	104.3	103.6	103.3	102.9	102.6	102.2
82.5°	82.8	82.0	81.2	80.6	80.3	79.9	79.6	79.2
85°	48.1	47.4	46.7	46.3	46.3	46.3	46.3	46.3
87.5°	24.8	24.9	25.0	25.3	25.7	26.1	26.5	26.9
90°	37.2	39.2	41.2	42.6	43.2	43.9	44.6	45.2
92.5°	36.0	38.0	40.0	41.1	41.2	41.4	41.5	41.6
95°	37.2	39.2	41.2	42.4	42.7	43.1	43.4	43.7
97.5°	40.2	40.4	40.6	40.9	41.2	41.6	41.9	42.2
100°	55.0	49.3	43.6	40.9	41.2	41.6	41.9	42.2
102.5°	196.8	135.3	73.9	43.2	43.2	43.3	43.4	43.4
105°	476.5	479.6	482.6	478.0	466.0	453.9	441.9	429.8
107.5°	589.6	591.1	592.5	593.9	595.2	596.4	597.7	599.0
110°	666.4	667.1	667.7	668.6	669.6	670.6	671.6	672.6



TEST NUMBER: P333113

CATALOG NUMBER: S124RDIW-S1195D1560U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	740.8	740.6	740.5	741.1	742.4	743.6	744.9	746.2
115°	851.9	852.5	853.2	853.6	853.6	853.6	853.6	853.6
117.5°	963.7	963.5	963.4	963.3	963.1	963.0	962.9	962.7
120°	1032.8	1033.5	1034.2	1034.2	1033.5	1032.8	1032.2	1031.5
122.5°	1101.1	1101.5	1101.9	1101.7	1101.1	1100.4	1099.7	1099.1
125°	1196.4	1197.4	1198.4	1199.1	1199.4	1199.7	1200.1	1200.4
127.5°	1291.1	1290.9	1290.7	1290.4	1290.2	1289.9	1289.6	1289.4
130°	1348.9	1349.2	1349.5	1349.7	1349.7	1349.7	1349.7	1349.7
132.5°	1405.6	1405.9	1406.2	1406.3	1406.0	1405.7	1405.5	1405.2
135°	1483.7	1484.4	1485.1	1485.8	1486.4	1487.1	1487.8	1488.4
137.5°	1558.7	1559.4	1560.2	1560.4	1560.2	1560.0	1559.8	1559.6
140°	1605.1	1606.1	1607.1	1607.7	1608.1	1608.4	1608.7	1609.1
142.5°	1648.0	1648.7	1649.4	1649.8	1649.9	1650.0	1650.0	1650.1
145°	1709.3	1709.6	1709.9	1710.5	1711.1	1711.8	1712.5	1713.1
147.5°	1763.1	1763.4	1763.7	1764.0	1764.3	1764.6	1765.0	1765.3
150°	1797.6	1797.6	1797.6	1797.8	1798.1	1798.4	1798.8	1799.1
152.5°	1827.6	1828.1	1828.7	1828.8	1828.6	1828.4	1828.2	1828.0
155°	1868.1	1869.5	1870.8	1871.0	1870.0	1869.0	1868.0	1867.0
157.5°	1903.0	1904.8	1906.5	1906.5	1904.8	1903.0	1901.3	1899.5
160°	1925.3	1927.3	1929.3	1929.3	1927.3	1925.3	1923.3	1921.2
162.5°	1943.4	1945.4	1947.4	1947.2	1945.0	1942.7	1940.4	1938.1
165°	1968.8	1971.5	1974.2	1974.0	1971.0	1968.0	1965.0	1962.0
167.5°	1987.5	1990.4	1993.4	1993.2	1989.8	1986.5	1983.1	1979.8
170°	1999.0	2001.7	2004.4	2004.0	2000.7	1997.3	1994.0	1990.6
172.5°	2006.2	2008.9	2011.6	2011.1	2007.5	2003.9	2000.3	1996.6
175°	2014.7	2017.8	2020.8	2020.3	2016.2	2012.2	2008.2	2004.2
177.5°	2018.1	2020.3	2022.4	2021.9	2018.7	2015.4	2012.2	2009.0
180°	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2

(END OF REPORT)