

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: NEO-RAY

Report Number: P333095

Luminaire Tested: **S124RDIW-S1195D470U835-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333095
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S1195D470U835-4F0-1E-UDD-A
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 470 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6885.2 lumens
Efficiency: N/A
Efficacy: 131.4 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 52.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333095

CATALOG NUMBER: S124RDIW-S1195D470U835-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P333095

CATALOG NUMBER: S124RDIW-S1195D470U835-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	113	113	113	113	107	107	107	107	96	96	96	86	86	86	77	77	77	73
1	104	99	96	92	98	94	91	88	85	83	80	77	75	73	69	68	66	63
2	95	88	82	76	90	83	78	73	76	71	68	68	65	62	62	59	57	54
3	87	78	70	65	82	74	67	62	67	62	58	61	57	53	55	52	49	46
4	80	69	61	55	76	66	59	53	60	54	50	55	50	46	50	46	43	40
5	74	62	54	48	70	59	52	46	54	48	43	50	45	41	45	41	38	35
6	68	56	48	42	65	54	46	41	49	43	38	45	40	36	41	37	34	31
7	63	51	43	37	60	49	41	36	45	39	34	41	36	32	38	33	30	28
8	59	46	39	33	56	45	37	32	41	35	31	38	33	29	35	30	27	25
9	55	43	35	30	52	41	34	29	38	32	28	35	30	26	32	28	25	23
10	51	39	32	27	49	38	31	26	35	29	25	32	27	24	30	26	22	21

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15998	15998	15998	15998
5°	18556	16046	14182	16046
10°	21952	15976	12658	15976
15°	25357	15828	10877	15828
20°	28233	15625	9836	15625
25°	29144	15425	9132	15425
30°	25513	15183	8708	15183
35°	19860	14824	8451	14824
40°	14893	14413	8313	14413
45°	11758	13755	8241	13755
50°	9927	12995	8002	12995
55°	8653	12159	7574	12159
60°	7786	11292	6704	11292
65°	6863	10355	5765	10355
70°	6182	9385	5202	9385
75°	5181	8319	4432	8319
80°	4379	7090	4156	7090
85°	3696	5548	3696	5548



TEST NUMBER: P333095

CATALOG NUMBER: S124RDIW-S1195D470U835-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	192.0	2.8
10°-20°	579.2	8.4
20°-30°	905.9	13.2
30°-40°	1007.1	14.6
40°-50°	893.5	13.0
50°-60°	696.2	10.1
60°-70°	455.8	6.6
70°-80°	224.2	3.3
80°-90°	57.1	0.8
90°-100°	20.7	0.3
100°-110°	132.1	1.9
110°-120°	252.8	3.7
120°-130°	320.9	4.7
130°-140°	343.3	5.0
140°-150°	321.0	4.7
150°-160°	258.9	3.8
160°-170°	167.0	2.4
170°-180°	57.6	0.8
0°-30°	1677.1	24.4
0°-40°	2684.1	39.0
0°-60°	4273.8	62.1
0°-90°	5010.9	72.8
90°-120°	405.6	5.9
90°-150°	1390.9	20.2
90°-180°	1874.0	27.2
0°-180°	6885.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1982	1982	1982	1982	1982	
5°	2290	1980	1750	1980	2290	232
15°	3034	1894	1301	1894	3034	863
25°	3272	1732	1025	1732	3272	1452
35°	2015	1504	858	1504	2015	1263
45°	1030	1205	722	1205	1030	816
55°	615	864	538	864	615	559
65°	359	542	302	542	359	361
75°	166	267	142	267	166	183
85°	40	60	40	60	40	45
90°	14	1	14	1	14	8
95°	13	25	13	25	13	10
105°	129	136	129	136	129	113
115°	256	255	256	255	256	254
125°	361	358	361	358	361	321
135°	447	444	447	444	447	344
145°	515	512	515	512	515	322
155°	561	562	561	562	561	259
165°	590	592	590	592	590	167
175°	602	606	602	606	602	57
180°	606	606	606	606	606	



TEST NUMBER: P333095

CATALOG NUMBER: S124RDIW-S1195D470U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7
2.5°	2090.2	2096.0	2090.2	2089.6	2083.2	2081.3	2078.7	2070.4	2055.1	2046.2	2048.1
5°	2289.8	2309.8	2298.6	2297.0	2279.5	2261.9	2250.7	2225.2	2198.0	2179.7	2164.5
7.5°	2520.7	2532.2	2525.2	2514.0	2485.6	2469.5	2443.6	2409.9	2361.2	2324.0	2290.0
10°	2677.9	2687.4	2684.3	2663.5	2642.7	2600.4	2576.5	2529.4	2467.9	2419.2	2373.7
12.5°	2832.4	2842.7	2814.6	2815.5	2776.2	2742.9	2704.9	2645.6	2574.6	2511.8	2454.8
15°	3034.0	3021.2	3021.2	3005.2	2961.3	2915.0	2875.9	2813.6	2724.2	2649.1	2570.1
17.5°	3191.7	3196.2	3189.6	3152.0	3117.5	3069.6	2997.9	2925.2	2842.2	2741.4	2660.6
20°	3286.3	3286.3	3279.1	3253.5	3208.8	3157.7	3080.3	3001.2	2895.8	2794.4	2703.4
22.5°	3324.6	3327.1	3318.7	3297.6	3257.4	3207.5	3141.6	3061.3	2952.7	2838.5	2725.8
25°	3271.9	3287.1	3288.6	3283.1	3271.1	3240.7	3184.1	3101.8	3004.4	2880.7	2759.3
27.5°	3003.9	3023.1	3039.9	3067.5	3104.2	3123.4	3125.9	3084.1	2999.1	2880.0	2757.9
30°	2736.9	2752.9	2804.8	2872.7	2925.4	2973.3	3014.8	3026.0	2978.1	2871.1	2742.5
32.5°	2440.6	2462.3	2514.2	2587.2	2675.0	2756.1	2849.4	2896.9	2895.7	2831.5	2712.5
35°	2015.2	2031.2	2079.1	2155.7	2261.1	2381.7	2529.4	2644.3	2722.6	2717.0	2644.3
37.5°	1625.2	1643.3	1691.7	1755.2	1857.4	2006.7	2149.6	2308.0	2452.7	2534.0	2509.7
40°	1413.2	1414.0	1461.1	1526.6	1622.4	1752.5	1908.2	2083.8	2245.1	2376.9	2402.4
42.5°	1245.8	1246.0	1277.1	1347.7	1416.7	1539.2	1687.8	1862.2	2051.0	2203.1	2270.8
45°	1029.9	1037.1	1062.7	1105.0	1159.3	1263.1	1382.0	1544.1	1755.7	1936.1	2048.7
47.5°	872.2	882.7	899.0	933.5	976.8	1045.9	1144.3	1289.9	1462.0	1660.5	1820.7
50°	790.4	792.0	812.8	831.9	869.5	924.6	1010.8	1132.1	1290.2	1481.0	1659.1
52.5°	720.2	719.8	732.3	756.6	787.1	830.0	899.6	1010.1	1150.3	1321.4	1505.2
55°	614.8	618.8	628.3	647.5	670.7	701.0	756.1	839.1	949.3	1095.4	1262.3
57.5°	534.6	536.7	544.2	552.3	573.6	595.6	637.0	694.6	787.6	907.2	1062.7
60°	482.2	483.0	485.4	497.4	514.2	534.9	562.9	611.6	689.8	799.2	922.2
62.5°	431.1	432.6	436.3	445.0	458.0	472.3	501.6	540.7	605.5	698.9	809.7
65°	359.3	360.1	365.7	368.9	379.2	392.0	413.6	439.9	484.6	562.9	646.7
67.5°	300.2	300.2	300.5	304.8	312.0	320.5	333.4	354.5	388.2	436.3	510.2
70°	261.9	261.9	263.5	265.9	269.9	277.0	284.2	300.2	325.0	364.1	420.8
72.5°	226.1	226.7	228.3	228.8	230.9	236.8	242.1	252.3	270.7	300.2	346.0
75°	166.1	168.5	172.5	175.7	179.6	178.8	184.4	190.8	196.4	214.0	240.3
77.5°	123.6	122.3	122.8	125.5	126.0	126.8	130.8	135.7	139.9	148.2	157.6
80°	94.2	94.2	96.6	97.4	96.6	97.4	101.4	103.8	105.4	108.6	117.4
82.5°	71.2	72.5	71.7	72.5	73.0	73.8	77.1	77.6	79.2	80.5	84.2
85°	39.9	40.7	41.5	39.9	39.9	39.9	41.5	42.3	43.9	43.1	44.7
87.5°	16.8	16.1	16.7	16.7	17.2	16.5	17.0	18.2	16.8	17.3	17.2
90°	13.6	13.4	13.2	13.0	12.8	12.4	11.8	11.2	10.6	10.0	9.2
92.5°	12.5	12.5	12.4	12.4	12.3	12.0	11.4	10.8	10.2	9.6	8.8
95°	13.1	13.0	12.9	12.8	12.7	12.4	11.8	11.2	10.6	10.0	9.9
97.5°	12.7	12.6	12.5	12.4	12.3	12.2	12.1	12.1	12.0	12.0	23.2
100°	12.7	12.6	12.5	12.4	12.3	13.1	14.8	16.5	18.2	19.9	33.8
102.5°	13.1	13.0	13.0	13.0	13.0	22.2	40.7	59.1	77.6	96.1	97.9
105°	129.2	132.8	136.4	140.0	143.7	145.0	144.1	143.2	142.3	141.4	140.9
107.5°	180.0	179.6	179.2	178.9	178.5	178.1	177.6	177.2	176.7	176.3	175.6
110°	202.1	201.8	201.5	201.2	200.9	200.7	200.5	200.3	200.1	199.9	199.3



TEST NUMBER: P333095

CATALOG NUMBER: S124RDIW-S1195D470U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	224.2	223.9	223.5	223.1	222.7	222.5	222.6	222.6	222.7	222.7	222.4
115°	256.5	256.5	256.5	256.5	256.5	256.4	256.2	256.0	255.8	255.6	255.7
117.5°	289.3	289.4	289.4	289.4	289.5	289.5	289.6	289.6	289.6	289.7	289.5
120°	310.0	310.2	310.4	310.6	310.8	310.8	310.6	310.4	310.2	310.0	310.1
122.5°	330.3	330.5	330.7	330.9	331.1	331.1	331.0	330.9	330.8	330.7	330.5
125°	360.7	360.6	360.5	360.4	360.3	360.1	359.8	359.5	359.2	358.9	359.1
127.5°	387.5	387.6	387.6	387.7	387.8	387.9	387.9	388.0	388.1	388.1	387.7
130°	405.6	405.6	405.6	405.6	405.6	405.6	405.5	405.4	405.3	405.2	404.9
132.5°	422.3	422.4	422.5	422.5	422.6	422.6	422.5	422.4	422.3	422.2	421.8
135°	447.3	447.1	446.9	446.7	446.5	446.3	446.1	445.9	445.7	445.5	445.1
137.5°	468.7	468.8	468.8	468.9	468.9	468.9	468.6	468.4	468.2	468.0	467.5
140°	483.6	483.5	483.4	483.3	483.2	483.0	482.7	482.4	482.1	481.8	481.6
142.5°	495.9	495.9	495.9	495.8	495.8	495.7	495.5	495.2	495.0	494.8	494.7
145°	514.8	514.6	514.4	514.2	514.0	513.9	513.8	513.7	513.6	513.5	513.5
147.5°	530.5	530.4	530.3	530.2	530.1	530.0	529.9	529.9	529.8	529.7	529.8
150°	540.7	540.6	540.5	540.4	540.3	540.2	540.2	540.2	540.2	540.2	540.3
152.5°	549.4	549.4	549.5	549.6	549.6	549.6	549.4	549.2	549.1	548.9	549.1
155°	561.1	561.4	561.7	562.0	562.3	562.2	561.8	561.4	561.0	560.6	560.9
157.5°	570.9	571.4	571.9	572.4	572.9	572.9	572.4	571.9	571.4	570.9	571.2
160°	577.4	578.0	578.6	579.2	579.8	579.8	579.2	578.6	578.0	577.4	577.5
162.5°	582.5	583.1	583.8	584.5	585.2	585.2	584.6	584.0	583.4	582.8	582.9
165°	589.6	590.5	591.4	592.3	593.2	593.3	592.5	591.7	590.9	590.1	590.1
167.5°	595.0	596.0	597.0	598.0	599.0	599.1	598.2	597.3	596.4	595.5	595.6
170°	598.2	599.2	600.2	601.2	602.3	602.4	601.5	600.7	599.9	599.1	599.0
172.5°	600.0	601.1	602.2	603.3	604.4	604.5	603.7	602.9	602.1	601.3	601.2
175°	602.3	603.5	604.7	605.9	607.1	607.3	606.4	605.5	604.6	603.7	603.6
177.5°	603.8	604.7	605.7	606.7	607.6	607.8	607.1	606.5	605.8	605.2	605.0
180°	605.9	605.9	605.9	605.9	605.9	605.9	605.9	605.9	605.9	605.9	605.9



TEST NUMBER: P333095

CATALOG NUMBER: S124RDIW-S1195D470U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7
2.5°	2041.7	2032.8	2028.3	2018.1	2005.9	1999.5	1993.8	1985.5	1974.6	1963.1	1954.8
5°	2145.3	2126.2	2102.2	2073.5	2047.9	2023.2	2001.6	1980.1	1955.3	1929.8	1904.2
7.5°	2251.7	2214.0	2173.3	2126.2	2080.3	2038.7	2000.3	1963.6	1922.1	1884.9	1851.0
10°	2325.8	2274.7	2218.0	2158.1	2098.2	2046.3	1995.2	1948.9	1897.8	1852.3	1814.0
12.5°	2385.8	2325.8	2257.6	2183.0	2111.0	2048.2	1989.5	1929.1	1871.0	1821.7	1770.6
15°	2485.4	2403.2	2311.4	2222.0	2128.6	2043.1	1964.1	1893.8	1827.6	1758.1	1709.4
17.5°	2554.0	2456.4	2344.8	2237.3	2127.0	2026.2	1935.0	1851.4	1774.9	1704.0	1646.0
20°	2594.8	2487.0	2363.3	2241.1	2117.4	2009.6	1911.4	1818.8	1739.7	1663.1	1603.2
22.5°	2617.8	2498.5	2363.3	2235.4	2107.2	1990.4	1882.6	1786.2	1700.1	1623.5	1557.2
25°	2625.2	2497.4	2359.3	2212.4	2071.9	1948.1	1836.3	1731.7	1635.9	1559.3	1489.0
27.5°	2615.0	2464.5	2323.1	2172.3	2027.3	1896.9	1779.5	1669.6	1573.7	1491.4	1419.4
30°	2599.6	2438.3	2286.6	2130.2	1983.2	1857.9	1734.1	1628.8	1529.0	1443.5	1370.9
32.5°	2566.4	2406.4	2243.2	2082.9	1934.1	1804.9	1687.5	1581.5	1483.6	1396.3	1319.1
35°	2500.6	2338.5	2161.3	1996.8	1850.7	1716.6	1606.4	1504.2	1410.8	1317.4	1235.9
37.5°	2413.9	2248.3	2072.0	1891.9	1745.6	1619.0	1517.9	1422.0	1330.8	1245.5	1155.3
40°	2332.2	2181.3	1999.2	1820.4	1670.3	1548.1	1454.7	1367.7	1275.9	1191.2	1101.0
42.5°	2233.2	2104.6	1920.7	1741.2	1593.0	1475.3	1388.3	1303.2	1219.7	1137.6	1043.5
45°	2067.9	1970.5	1798.0	1625.6	1476.3	1359.7	1279.9	1204.8	1131.3	1053.1	964.5
47.5°	1878.5	1812.5	1663.7	1487.1	1349.0	1244.1	1167.0	1105.6	1043.5	965.3	887.5
50°	1746.9	1704.6	1560.9	1399.6	1267.9	1171.3	1092.2	1034.7	982.8	907.8	838.3
52.5°	1606.4	1583.9	1462.5	1308.3	1181.0	1086.3	1018.8	967.0	914.5	852.2	787.2
55°	1392.4	1404.4	1301.4	1168.1	1048.3	968.5	907.0	863.9	819.2	766.5	716.2
57.5°	1173.7	1217.4	1148.3	1031.2	919.0	845.2	798.9	762.6	725.1	681.4	638.4
60°	1042.7	1079.4	1040.3	937.3	839.1	770.5	727.4	699.4	661.9	622.0	589.2
62.5°	915.0	954.3	931.1	847.9	756.7	697.7	659.6	633.6	605.7	570.9	536.9
65°	754.5	780.0	768.9	711.4	646.7	596.4	561.3	542.1	516.6	491.0	460.7
67.5°	577.9	627.2	620.7	590.2	534.3	495.0	472.0	455.1	431.8	412.8	392.2
70°	475.1	520.6	519.8	495.0	464.7	427.9	412.0	397.6	376.8	358.5	341.7
72.5°	388.8	430.5	436.7	417.7	397.0	369.2	353.9	344.0	323.8	311.2	297.6
75°	272.3	302.6	310.6	310.6	301.0	286.6	273.1	266.7	252.3	241.1	233.1
77.5°	178.5	197.7	210.1	213.0	214.5	209.7	198.5	194.0	183.0	179.0	171.3
80°	126.1	138.9	153.3	158.1	162.1	160.5	155.7	152.5	142.1	138.1	134.9
82.5°	87.2	94.2	106.0	116.6	115.4	119.6	115.4	112.9	105.1	103.6	100.4
85°	45.5	46.3	47.9	55.1	59.1	60.7	61.5	59.9	57.5	57.5	51.9
87.5°	17.0	16.2	17.3	17.1	17.5	19.9	21.6	22.0	20.3	18.6	16.9
90°	8.4	7.6	6.7	5.8	4.7	3.6	2.5	1.4	2.5	3.6	4.7
92.5°	8.0	7.2	6.4	6.0	5.9	5.8	5.8	5.7	5.8	5.8	5.9
95°	9.8	9.7	9.6	11.2	14.7	18.1	21.5	24.9	21.5	18.1	14.7
97.5°	34.4	45.7	56.9	61.5	59.3	57.2	55.1	52.9	55.1	57.2	59.3
100°	47.7	61.6	75.5	81.6	79.8	78.0	76.1	74.3	76.1	78.0	79.8
102.5°	99.7	101.5	103.3	103.6	102.2	100.9	99.6	98.3	99.6	100.9	102.2
105°	140.4	139.9	139.4	138.8	138.2	137.6	137.0	136.4	137.0	137.6	138.2
107.5°	174.9	174.2	173.6	173.1	172.8	172.5	172.2	171.9	172.2	172.5	172.8
110°	198.7	198.0	197.4	197.0	196.7	196.4	196.1	195.8	196.1	196.4	196.7



TEST NUMBER: P333095

CATALOG NUMBER: S124RDIW-S1195D470U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	222.1	221.9	221.6	221.2	220.6	220.1	219.5	219.0	219.5	220.1	220.6
115°	255.8	255.9	256.0	255.9	255.6	255.3	255.0	254.7	255.0	255.3	255.6
117.5°	289.2	289.0	288.8	288.5	288.1	287.7	287.3	286.9	287.3	287.7	288.1
120°	310.2	310.3	310.4	310.2	309.8	309.4	309.0	308.6	309.0	309.4	309.8
122.5°	330.4	330.2	330.1	329.9	329.7	329.4	329.2	328.9	329.2	329.4	329.7
125°	359.3	359.5	359.7	359.6	359.2	358.8	358.4	358.0	358.4	358.8	359.2
127.5°	387.2	386.7	386.3	386.0	385.9	385.8	385.7	385.6	385.7	385.8	385.9
130°	404.6	404.3	404.0	403.8	403.7	403.6	403.4	403.3	403.4	403.6	403.7
132.5°	421.4	421.1	420.7	420.4	420.2	420.0	419.8	419.7	419.8	420.0	420.2
135°	444.7	444.3	443.9	443.7	443.8	443.9	444.0	444.1	444.0	443.9	443.8
137.5°	467.1	466.6	466.2	466.0	465.9	465.9	465.8	465.8	465.8	465.9	465.9
140°	481.4	481.1	480.9	480.7	480.5	480.3	480.1	479.9	480.1	480.3	480.5
142.5°	494.6	494.4	494.3	494.1	493.7	493.4	493.0	492.6	493.0	493.4	493.7
145°	513.5	513.5	513.5	513.3	513.0	512.7	512.4	512.1	512.4	512.7	513.0
147.5°	529.9	530.0	530.1	529.9	529.3	528.7	528.2	527.6	528.2	528.7	529.3
150°	540.4	540.5	540.6	540.5	540.1	539.7	539.3	538.9	539.3	539.7	540.1
152.5°	549.3	549.5	549.6	549.6	549.2	548.9	548.6	548.3	548.6	548.9	549.2
155°	561.2	561.5	561.8	561.9	561.8	561.7	561.6	561.5	561.6	561.7	561.8
157.5°	571.5	571.9	572.2	572.4	572.5	572.5	572.6	572.7	572.6	572.5	572.5
160°	577.6	577.7	577.8	578.0	578.3	578.6	578.9	579.2	578.9	578.6	578.3
162.5°	583.0	583.1	583.2	583.5	583.8	584.2	584.6	585.0	584.6	584.2	583.8
165°	590.1	590.1	590.1	590.3	590.8	591.3	591.8	592.3	591.8	591.3	590.8
167.5°	595.6	595.7	595.7	596.0	596.6	597.1	597.6	598.1	597.6	597.1	596.6
170°	598.9	598.8	598.7	599.0	599.6	600.2	600.8	601.4	600.8	600.2	599.6
172.5°	601.1	601.0	600.9	601.2	601.8	602.4	603.0	603.6	603.0	602.4	601.8
175°	603.5	603.4	603.3	603.5	604.1	604.7	605.3	605.9	605.3	604.7	604.1
177.5°	604.9	604.7	604.6	604.8	605.3	605.9	606.5	607.0	606.5	605.9	605.3
180°	605.9	605.9	605.9	605.9	605.9	605.9	605.9	605.9	605.9	605.9	605.9



TEST NUMBER: P333095

CATALOG NUMBER: S124RDIW-S1195D470U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7
2.5°	1945.9	1939.5	1931.2	1921.6	1910.1	1899.9	1895.4	1899.3	1901.2	1896.1	1895.4
5°	1886.6	1866.7	1850.7	1826.8	1807.6	1791.6	1780.5	1775.7	1777.3	1764.5	1761.3
7.5°	1820.1	1796.4	1770.2	1741.8	1715.3	1691.8	1679.5	1672.8	1659.3	1653.5	1643.8
10°	1777.3	1745.3	1719.8	1686.2	1655.9	1628.0	1614.4	1603.2	1589.6	1583.2	1569.7
12.5°	1733.2	1696.1	1668.0	1633.2	1602.2	1568.6	1555.6	1534.9	1513.6	1500.2	1482.8
15°	1671.1	1626.4	1592.0	1550.5	1513.8	1475.5	1441.1	1402.8	1388.4	1358.1	1340.5
17.5°	1598.4	1553.1	1510.6	1454.9	1398.2	1350.6	1314.0	1277.3	1255.3	1235.9	1227.0
20°	1550.5	1509.0	1449.9	1385.2	1322.2	1269.5	1239.9	1216.0	1192.0	1178.5	1168.9
22.5°	1505.2	1452.1	1383.5	1313.7	1250.6	1209.4	1184.4	1159.8	1140.3	1127.4	1114.6
25°	1429.2	1359.7	1287.0	1207.2	1164.1	1128.2	1101.0	1081.0	1069.1	1052.3	1045.9
27.5°	1351.1	1266.9	1186.8	1133.1	1088.2	1055.3	1031.7	1016.7	1001.5	990.8	982.5
30°	1291.0	1205.6	1133.7	1082.6	1037.1	1010.0	990.8	973.3	961.3	952.5	946.1
32.5°	1231.6	1146.2	1085.8	1030.9	995.0	968.5	948.0	934.9	925.5	914.2	910.3
35°	1145.7	1069.9	1017.2	967.7	930.9	907.0	891.0	877.5	869.5	866.3	863.9
37.5°	1063.2	1001.0	944.4	903.8	871.1	852.2	833.4	826.7	821.2	815.5	818.1
40°	1010.8	952.5	902.2	859.1	832.7	812.0	800.8	792.8	788.0	788.0	788.0
42.5°	965.4	908.4	859.4	820.8	794.4	776.9	764.4	757.7	756.1	755.5	759.3
45°	895.0	842.3	792.8	760.9	738.5	721.0	713.8	708.2	708.2	711.4	712.2
47.5°	825.2	775.9	736.1	700.4	679.9	668.9	662.7	659.8	660.1	663.3	667.0
50°	782.4	733.7	694.6	662.7	643.5	633.1	627.5	626.0	627.5	627.5	633.1
52.5°	735.8	692.2	653.7	626.9	605.2	595.5	592.4	590.2	591.1	593.7	596.1
55°	667.5	628.3	591.6	566.1	550.1	543.7	536.5	537.3	535.7	537.3	537.3
57.5°	599.0	563.8	529.7	509.4	495.3	486.1	478.2	480.5	478.1	477.8	476.5
60°	554.9	516.6	489.4	471.1	455.1	447.1	439.9	441.5	439.1	437.5	434.3
62.5°	507.0	475.1	449.2	431.5	418.7	409.4	402.2	400.6	395.1	389.6	382.6
65°	437.5	411.2	388.0	371.3	359.3	352.1	346.5	341.7	329.7	317.0	310.6
67.5°	370.0	351.0	329.4	315.2	305.5	296.1	285.4	277.2	266.0	259.0	255.0
70°	326.5	308.2	289.8	276.2	265.9	257.1	245.1	239.5	231.5	228.3	224.4
72.5°	285.0	267.9	250.9	238.6	227.5	220.7	211.3	205.7	202.2	200.9	196.9
75°	222.0	208.4	195.6	184.4	175.7	170.9	166.9	162.9	161.3	154.1	150.1
77.5°	161.9	153.0	145.0	137.0	130.8	127.6	119.9	115.3	112.6	109.2	108.4
80°	126.1	119.8	111.8	107.0	98.2	95.0	91.8	91.0	90.2	89.4	88.6
82.5°	94.9	88.5	80.5	77.6	75.2	73.3	71.4	70.6	69.8	70.3	70.1
85°	47.9	44.7	44.7	43.9	43.1	42.3	41.5	41.5	40.7	41.5	40.7
87.5°	17.1	16.7	16.8	15.7	16.5	16.7	16.2	16.3	17.0	15.9	16.0
90°	5.8	6.7	7.6	8.4	9.2	10.0	10.6	11.2	11.8	12.4	12.8
92.5°	6.0	6.4	7.2	8.0	8.8	9.6	10.2	10.8	11.4	12.0	12.3
95°	11.2	9.6	9.7	9.8	9.9	10.0	10.6	11.2	11.8	12.4	12.7
97.5°	61.5	56.9	45.7	34.4	23.2	12.0	12.0	12.1	12.1	12.2	12.3
100°	81.6	75.5	61.6	47.7	33.8	19.9	18.2	16.5	14.8	13.1	12.3
102.5°	103.6	103.3	101.5	99.7	97.9	96.1	77.6	59.1	40.7	22.2	13.0
105°	138.8	139.4	139.9	140.4	140.9	141.4	142.3	143.2	144.1	145.0	143.7
107.5°	173.1	173.6	174.2	174.9	175.6	176.3	176.7	177.2	177.6	178.1	178.5
110°	197.0	197.4	198.0	198.7	199.3	199.9	200.1	200.3	200.5	200.7	200.9



TEST NUMBER: P333095

CATALOG NUMBER: S124RDIW-S1195D470U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	221.2	221.6	221.9	222.1	222.4	222.7	222.7	222.6	222.6	222.5	222.7
115°	255.9	256.0	255.9	255.8	255.7	255.6	255.8	256.0	256.2	256.4	256.5
117.5°	288.5	288.8	289.0	289.2	289.5	289.7	289.6	289.6	289.6	289.5	289.5
120°	310.2	310.4	310.3	310.2	310.1	310.0	310.2	310.4	310.6	310.8	310.8
122.5°	329.9	330.1	330.2	330.4	330.5	330.7	330.8	330.9	331.0	331.1	331.1
125°	359.6	359.7	359.5	359.3	359.1	358.9	359.2	359.5	359.8	360.1	360.3
127.5°	386.0	386.3	386.7	387.2	387.7	388.1	388.1	388.0	387.9	387.9	387.8
130°	403.8	404.0	404.3	404.6	404.9	405.2	405.3	405.4	405.5	405.6	405.6
132.5°	420.4	420.7	421.1	421.4	421.8	422.2	422.3	422.4	422.5	422.6	422.6
135°	443.7	443.9	444.3	444.7	445.1	445.5	445.7	445.9	446.1	446.3	446.5
137.5°	466.0	466.2	466.6	467.1	467.5	468.0	468.2	468.4	468.6	468.9	468.9
140°	480.7	480.9	481.1	481.4	481.6	481.8	482.1	482.4	482.7	483.0	483.2
142.5°	494.1	494.3	494.4	494.6	494.7	494.8	495.0	495.2	495.5	495.7	495.8
145°	513.3	513.5	513.5	513.5	513.5	513.5	513.6	513.7	513.8	513.9	514.0
147.5°	529.9	530.1	530.0	529.9	529.8	529.7	529.8	529.9	529.9	530.0	530.1
150°	540.5	540.6	540.5	540.4	540.3	540.2	540.2	540.2	540.2	540.2	540.3
152.5°	549.6	549.6	549.5	549.3	549.1	548.9	549.1	549.2	549.4	549.6	549.6
155°	561.9	561.8	561.5	561.2	560.9	560.6	561.0	561.4	561.8	562.2	562.3
157.5°	572.4	572.2	571.9	571.5	571.2	570.9	571.4	571.9	572.4	572.9	572.9
160°	578.0	577.8	577.7	577.6	577.5	577.4	578.0	578.6	579.2	579.8	579.8
162.5°	583.5	583.2	583.1	583.0	582.9	582.8	583.4	584.0	584.6	585.2	585.2
165°	590.3	590.1	590.1	590.1	590.1	590.1	590.9	591.7	592.5	593.3	593.2
167.5°	596.0	595.7	595.7	595.6	595.6	595.5	596.4	597.3	598.2	599.1	599.0
170°	599.0	598.7	598.8	598.9	599.0	599.1	599.9	600.7	601.5	602.4	602.3
172.5°	601.2	600.9	601.0	601.1	601.2	601.3	602.1	602.9	603.7	604.5	604.4
175°	603.5	603.3	603.4	603.5	603.6	603.7	604.6	605.5	606.4	607.3	607.1
177.5°	604.8	604.6	604.7	604.9	605.0	605.2	605.8	606.5	607.1	607.8	607.6
180°	605.9	605.9	605.9	605.9	605.9	605.9	605.9	605.9	605.9	605.9	605.9



TEST NUMBER: P333095

CATALOG NUMBER: S124RDIW-S1195D470U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7
2.5°	1891.6	1892.9	1888.4	1887.1	1888.4	1892.9	1891.6	1895.4	1896.1	1901.2	1899.3
5°	1754.9	1753.3	1749.3	1750.1	1749.3	1753.3	1754.9	1761.3	1764.5	1777.3	1775.7
7.5°	1638.0	1631.8	1633.5	1627.2	1633.5	1631.8	1638.0	1643.8	1653.5	1659.3	1672.8
10°	1566.5	1557.7	1550.5	1544.1	1550.5	1557.7	1566.5	1569.7	1583.2	1589.6	1603.2
12.5°	1468.8	1461.2	1451.5	1453.4	1451.5	1461.2	1468.8	1482.8	1500.2	1513.6	1534.9
15°	1330.1	1318.2	1299.0	1301.4	1299.0	1318.2	1330.1	1340.5	1358.1	1388.4	1402.8
17.5°	1212.8	1212.9	1204.2	1206.2	1204.2	1212.9	1212.8	1227.0	1235.9	1255.3	1277.3
20°	1152.1	1146.5	1147.3	1144.9	1147.3	1146.5	1152.1	1168.9	1178.5	1192.0	1216.0
22.5°	1109.9	1103.1	1097.5	1092.5	1097.5	1103.1	1109.9	1114.6	1127.4	1140.3	1159.8
25°	1038.7	1033.9	1026.8	1025.2	1026.8	1033.9	1038.7	1045.9	1052.3	1069.1	1081.0
27.5°	976.1	975.2	972.3	968.6	972.3	975.2	976.1	982.5	990.8	1001.5	1016.7
30°	939.7	938.1	936.5	934.1	936.5	938.1	939.7	946.1	952.5	961.3	973.3
32.5°	907.2	906.2	904.6	904.8	904.6	906.2	907.2	910.3	914.2	925.5	934.9
35°	860.7	859.9	858.3	857.5	858.3	859.9	860.7	863.9	866.3	869.5	877.5
37.5°	817.3	819.3	818.4	818.2	818.4	819.3	817.3	818.1	815.5	821.2	826.7
40°	787.2	788.0	789.6	788.8	789.6	788.0	787.2	788.0	788.0	788.0	792.8
42.5°	762.3	762.5	764.7	762.0	764.7	762.5	762.3	759.3	755.5	756.1	757.7
45°	717.8	722.6	721.8	721.8	721.8	722.6	717.8	712.2	711.4	708.2	708.2
47.5°	669.1	673.2	674.3	674.2	674.3	673.2	669.1	667.0	663.3	660.1	659.8
50°	637.1	635.5	637.9	637.1	637.9	635.5	637.1	633.1	627.5	627.5	626.0
52.5°	598.2	598.5	598.3	597.5	598.3	598.5	598.2	596.1	593.7	591.1	590.2
55°	538.1	538.9	537.3	538.1	537.3	538.9	538.1	537.3	537.3	535.7	537.3
57.5°	473.0	469.1	470.7	468.8	470.7	469.1	473.0	476.5	477.8	478.1	480.5
60°	426.4	420.0	418.4	415.2	418.4	420.0	426.4	434.3	437.5	439.1	441.5
62.5°	374.0	369.5	364.1	366.6	364.1	369.5	374.0	382.6	389.6	395.1	400.6
65°	304.2	301.0	298.6	301.8	298.6	301.0	304.2	310.6	317.0	329.7	341.7
67.5°	251.8	250.1	250.1	248.5	250.1	250.1	251.8	255.0	259.0	266.0	277.2
70°	224.4	222.0	222.0	220.4	222.0	222.0	224.4	224.4	228.3	231.5	239.5
72.5°	196.2	193.9	194.5	193.5	194.5	193.9	196.2	196.9	200.9	202.2	205.7
75°	145.3	141.3	141.3	142.1	141.3	141.3	145.3	150.1	154.1	161.3	162.9
77.5°	108.4	107.6	108.7	107.3	108.7	107.6	108.4	108.4	109.2	112.6	115.3
80°	88.6	87.8	87.0	89.4	87.0	87.8	88.6	88.6	89.4	90.2	91.0
82.5°	68.8	68.7	68.5	71.5	68.5	68.7	68.8	70.1	70.3	69.8	70.6
85°	41.5	39.9	41.5	39.9	41.5	39.9	41.5	40.7	41.5	40.7	41.5
87.5°	17.3	16.7	16.1	16.8	16.1	16.7	17.3	16.0	15.9	17.0	16.3
90°	13.0	13.2	13.4	13.6	13.4	13.2	13.0	12.8	12.4	11.8	11.2
92.5°	12.4	12.4	12.5	12.5	12.5	12.4	12.4	12.3	12.0	11.4	10.8
95°	12.8	12.9	13.0	13.1	13.0	12.9	12.8	12.7	12.4	11.8	11.2
97.5°	12.4	12.5	12.6	12.7	12.6	12.5	12.4	12.3	12.2	12.1	12.1
100°	12.4	12.5	12.6	12.7	12.6	12.5	12.4	12.3	13.1	14.8	16.5
102.5°	13.0	13.0	13.0	13.1	13.0	13.0	13.0	13.0	22.2	40.7	59.1
105°	140.0	136.4	132.8	129.2	132.8	136.4	140.0	143.7	145.0	144.1	143.2
107.5°	178.9	179.2	179.6	180.0	179.6	179.2	178.9	178.5	178.1	177.6	177.2
110°	201.2	201.5	201.8	202.1	201.8	201.5	201.2	200.9	200.7	200.5	200.3



TEST NUMBER: P333095

CATALOG NUMBER: S124RDIW-S1195D470U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	223.1	223.5	223.9	224.2	223.9	223.5	223.1	222.7	222.5	222.6	222.6
115°	256.5	256.5	256.5	256.5	256.5	256.5	256.5	256.5	256.4	256.2	256.0
117.5°	289.4	289.4	289.4	289.3	289.4	289.4	289.4	289.5	289.5	289.6	289.6
120°	310.6	310.4	310.2	310.0	310.2	310.4	310.6	310.8	310.8	310.6	310.4
122.5°	330.9	330.7	330.5	330.3	330.5	330.7	330.9	331.1	331.1	331.0	330.9
125°	360.4	360.5	360.6	360.7	360.6	360.5	360.4	360.3	360.1	359.8	359.5
127.5°	387.7	387.6	387.6	387.5	387.6	387.6	387.7	387.8	387.9	387.9	388.0
130°	405.6	405.6	405.6	405.6	405.6	405.6	405.6	405.6	405.6	405.5	405.4
132.5°	422.5	422.5	422.4	422.3	422.4	422.5	422.5	422.6	422.6	422.5	422.4
135°	446.7	446.9	447.1	447.3	447.1	446.9	446.7	446.5	446.3	446.1	445.9
137.5°	468.9	468.8	468.8	468.7	468.8	468.8	468.9	468.9	468.9	468.6	468.4
140°	483.3	483.4	483.5	483.6	483.5	483.4	483.3	483.2	483.0	482.7	482.4
142.5°	495.8	495.9	495.9	495.9	495.9	495.9	495.8	495.8	495.7	495.5	495.2
145°	514.2	514.4	514.6	514.8	514.6	514.4	514.2	514.0	513.9	513.8	513.7
147.5°	530.2	530.3	530.4	530.5	530.4	530.3	530.2	530.1	530.0	529.9	529.9
150°	540.4	540.5	540.6	540.7	540.6	540.5	540.4	540.3	540.2	540.2	540.2
152.5°	549.6	549.5	549.4	549.4	549.4	549.5	549.6	549.6	549.6	549.4	549.2
155°	562.0	561.7	561.4	561.1	561.4	561.7	562.0	562.3	562.2	561.8	561.4
157.5°	572.4	571.9	571.4	570.9	571.4	571.9	572.4	572.9	572.9	572.4	571.9
160°	579.2	578.6	578.0	577.4	578.0	578.6	579.2	579.8	579.8	579.2	578.6
162.5°	584.5	583.8	583.1	582.5	583.1	583.8	584.5	585.2	585.2	584.6	584.0
165°	592.3	591.4	590.5	589.6	590.5	591.4	592.3	593.2	593.3	592.5	591.7
167.5°	598.0	597.0	596.0	595.0	596.0	597.0	598.0	599.0	599.1	598.2	597.3
170°	601.2	600.2	599.2	598.2	599.2	600.2	601.2	602.3	602.4	601.5	600.7
172.5°	603.3	602.2	601.1	600.0	601.1	602.2	603.3	604.4	604.5	603.7	602.9
175°	605.9	604.7	603.5	602.3	603.5	604.7	605.9	607.1	607.3	606.4	605.5
177.5°	606.7	605.7	604.7	603.8	604.7	605.7	606.7	607.6	607.8	607.1	606.5
180°	605.9	605.9	605.9	605.9	605.9	605.9	605.9	605.9	605.9	605.9	605.9



TEST NUMBER: P333095

CATALOG NUMBER: S124RDIW-S1195D470U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7
2.5°	1895.4	1899.9	1910.1	1921.6	1931.2	1939.5	1945.9	1954.8	1963.1	1974.6	1985.5
5°	1780.5	1791.6	1807.6	1826.8	1850.7	1866.7	1886.6	1904.2	1929.8	1955.3	1980.1
7.5°	1679.5	1691.8	1715.3	1741.8	1770.2	1796.4	1820.1	1851.0	1884.9	1922.1	1963.6
10°	1614.4	1628.0	1655.9	1686.2	1719.8	1745.3	1777.3	1814.0	1852.3	1897.8	1948.9
12.5°	1555.6	1568.6	1602.2	1633.2	1668.0	1696.1	1733.2	1770.6	1821.7	1871.0	1929.1
15°	1441.1	1475.5	1513.8	1550.5	1592.0	1626.4	1671.1	1709.4	1758.1	1827.6	1893.8
17.5°	1314.0	1350.6	1398.2	1454.9	1510.6	1553.1	1598.4	1646.0	1704.0	1774.9	1851.4
20°	1239.9	1269.5	1322.2	1385.2	1449.9	1509.0	1550.5	1603.2	1663.1	1739.7	1818.8
22.5°	1184.4	1209.4	1250.6	1313.7	1383.5	1452.1	1505.2	1557.2	1623.5	1700.1	1786.2
25°	1101.0	1128.2	1164.1	1207.2	1287.0	1359.7	1429.2	1489.0	1559.3	1635.9	1731.7
27.5°	1031.7	1055.3	1088.2	1133.1	1186.8	1266.9	1351.1	1419.4	1491.4	1573.7	1669.6
30°	990.8	1010.0	1037.1	1082.6	1133.7	1205.6	1291.0	1370.9	1443.5	1529.0	1628.8
32.5°	948.0	968.5	995.0	1030.9	1085.8	1146.2	1231.6	1319.1	1396.3	1483.6	1581.5
35°	891.0	907.0	930.9	967.7	1017.2	1069.9	1145.7	1235.9	1317.4	1410.8	1504.2
37.5°	833.4	852.2	871.1	903.8	944.4	1001.0	1063.2	1155.3	1245.5	1330.8	1422.0
40°	800.8	812.0	832.7	859.1	902.2	952.5	1010.8	1101.0	1191.2	1275.9	1367.7
42.5°	764.4	776.9	794.4	820.8	859.4	908.4	965.4	1043.5	1137.6	1219.7	1303.2
45°	713.8	721.0	738.5	760.9	792.8	842.3	895.0	964.5	1053.1	1131.3	1204.8
47.5°	662.7	668.9	679.9	700.4	736.1	775.9	825.2	887.5	965.3	1043.5	1105.6
50°	627.5	633.1	643.5	662.7	694.6	733.7	782.4	838.3	907.8	982.8	1034.7
52.5°	592.4	595.5	605.2	626.9	653.7	692.2	735.8	787.2	852.2	914.5	967.0
55°	536.5	543.7	550.1	566.1	591.6	628.3	667.5	716.2	766.5	819.2	863.9
57.5°	478.2	486.1	495.3	509.4	529.7	563.8	599.0	638.4	681.4	725.1	762.6
60°	439.9	447.1	455.1	471.1	489.4	516.6	554.9	589.2	622.0	661.9	699.4
62.5°	402.2	409.4	418.7	431.5	449.2	475.1	507.0	536.9	570.9	605.7	633.6
65°	346.5	352.1	359.3	371.3	388.0	411.2	437.5	460.7	491.0	516.6	542.1
67.5°	285.4	296.1	305.5	315.2	329.4	351.0	370.0	392.2	412.8	431.8	455.1
70°	245.1	257.1	265.9	276.2	289.8	308.2	326.5	341.7	358.5	376.8	397.6
72.5°	211.3	220.7	227.5	238.6	250.9	267.9	285.0	297.6	311.2	323.8	344.0
75°	166.9	170.9	175.7	184.4	195.6	208.4	222.0	233.1	241.1	252.3	266.7
77.5°	119.9	127.6	130.8	137.0	145.0	153.0	161.9	171.3	179.0	183.0	194.0
80°	91.8	95.0	98.2	107.0	111.8	119.8	126.1	134.9	138.1	142.1	152.5
82.5°	71.4	73.3	75.2	77.6	80.5	88.5	94.9	100.4	103.6	105.1	112.9
85°	41.5	42.3	43.1	43.9	44.7	44.7	47.9	51.9	57.5	57.5	59.9
87.5°	16.2	16.7	16.5	15.7	16.8	16.7	17.1	16.9	18.6	20.3	22.0
90°	10.6	10.0	9.2	8.4	7.6	6.7	5.8	4.7	3.6	2.5	1.4
92.5°	10.2	9.6	8.8	8.0	7.2	6.4	6.0	5.9	5.8	5.8	5.7
95°	10.6	10.0	9.9	9.8	9.7	9.6	11.2	14.7	18.1	21.5	24.9
97.5°	12.0	12.0	23.2	34.4	45.7	56.9	61.5	59.3	57.2	55.1	52.9
100°	18.2	19.9	33.8	47.7	61.6	75.5	81.6	79.8	78.0	76.1	74.3
102.5°	77.6	96.1	97.9	99.7	101.5	103.3	103.6	102.2	100.9	99.6	98.3
105°	142.3	141.4	140.9	140.4	139.9	139.4	138.8	138.2	137.6	137.0	136.4
107.5°	176.7	176.3	175.6	174.9	174.2	173.6	173.1	172.8	172.5	172.2	171.9
110°	200.1	199.9	199.3	198.7	198.0	197.4	197.0	196.7	196.4	196.1	195.8



TEST NUMBER: P333095

CATALOG NUMBER: S124RDIW-S1195D470U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	222.7	222.7	222.4	222.1	221.9	221.6	221.2	220.6	220.1	219.5	219.0
115°	255.8	255.6	255.7	255.8	255.9	256.0	255.9	255.6	255.3	255.0	254.7
117.5°	289.6	289.7	289.5	289.2	289.0	288.8	288.5	288.1	287.7	287.3	286.9
120°	310.2	310.0	310.1	310.2	310.3	310.4	310.2	309.8	309.4	309.0	308.6
122.5°	330.8	330.7	330.5	330.4	330.2	330.1	329.9	329.7	329.4	329.2	328.9
125°	359.2	358.9	359.1	359.3	359.5	359.7	359.6	359.2	358.8	358.4	358.0
127.5°	388.1	388.1	387.7	387.2	386.7	386.3	386.0	385.9	385.8	385.7	385.6
130°	405.3	405.2	404.9	404.6	404.3	404.0	403.8	403.7	403.6	403.4	403.3
132.5°	422.3	422.2	421.8	421.4	421.1	420.7	420.4	420.2	420.0	419.8	419.7
135°	445.7	445.5	445.1	444.7	444.3	443.9	443.7	443.8	443.9	444.0	444.1
137.5°	468.2	468.0	467.5	467.1	466.6	466.2	466.0	465.9	465.9	465.8	465.8
140°	482.1	481.8	481.6	481.4	481.1	480.9	480.7	480.5	480.3	480.1	479.9
142.5°	495.0	494.8	494.7	494.6	494.4	494.3	494.1	493.7	493.4	493.0	492.6
145°	513.6	513.5	513.5	513.5	513.5	513.5	513.3	513.0	512.7	512.4	512.1
147.5°	529.8	529.7	529.8	529.9	530.0	530.1	529.9	529.3	528.7	528.2	527.6
150°	540.2	540.2	540.3	540.4	540.5	540.6	540.5	540.1	539.7	539.3	538.9
152.5°	549.1	548.9	549.1	549.3	549.5	549.6	549.6	549.2	548.9	548.6	548.3
155°	561.0	560.6	560.9	561.2	561.5	561.8	561.9	561.8	561.7	561.6	561.5
157.5°	571.4	570.9	571.2	571.5	571.9	572.2	572.4	572.5	572.5	572.6	572.7
160°	578.0	577.4	577.5	577.6	577.7	577.8	578.0	578.3	578.6	578.9	579.2
162.5°	583.4	582.8	582.9	583.0	583.1	583.2	583.5	583.8	584.2	584.6	585.0
165°	590.9	590.1	590.1	590.1	590.1	590.1	590.3	590.8	591.3	591.8	592.3
167.5°	596.4	595.5	595.6	595.6	595.7	595.7	596.0	596.6	597.1	597.6	598.1
170°	599.9	599.1	599.0	598.9	598.8	598.7	599.0	599.6	600.2	600.8	601.4
172.5°	602.1	601.3	601.2	601.1	601.0	600.9	601.2	601.8	602.4	603.0	603.6
175°	604.6	603.7	603.6	603.5	603.4	603.3	603.5	604.1	604.7	605.3	605.9
177.5°	605.8	605.2	605.0	604.9	604.7	604.6	604.8	605.3	605.9	606.5	607.0
180°	605.9	605.9	605.9	605.9	605.9	605.9	605.9	605.9	605.9	605.9	605.9



TEST NUMBER: P333095

CATALOG NUMBER: S124RDIW-S1195D470U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7
2.5°	1993.8	1999.5	2005.9	2018.1	2028.3	2032.8	2041.7	2048.1	2046.2	2055.1	2070.4
5°	2001.6	2023.2	2047.9	2073.5	2102.2	2126.2	2145.3	2164.5	2179.7	2198.0	2225.2
7.5°	2000.3	2038.7	2080.3	2126.2	2173.3	2214.0	2251.7	2290.0	2324.0	2361.2	2409.9
10°	1995.2	2046.3	2098.2	2158.1	2218.0	2274.7	2325.8	2373.7	2419.2	2467.9	2529.4
12.5°	1989.5	2048.2	2111.0	2183.0	2257.6	2325.8	2385.8	2454.8	2511.8	2574.6	2645.6
15°	1964.1	2043.1	2128.6	2222.0	2311.4	2403.2	2485.4	2570.1	2649.1	2724.2	2813.6
17.5°	1935.0	2026.2	2127.0	2237.3	2344.8	2456.4	2554.0	2660.6	2741.4	2842.2	2925.2
20°	1911.4	2009.6	2117.4	2241.1	2363.3	2487.0	2594.8	2703.4	2794.4	2895.8	3001.2
22.5°	1882.6	1990.4	2107.2	2235.4	2363.3	2498.5	2617.8	2725.8	2838.5	2952.7	3061.3
25°	1836.3	1948.1	2071.9	2212.4	2359.3	2497.4	2625.2	2759.3	2880.7	3004.4	3101.8
27.5°	1779.5	1896.9	2027.3	2172.3	2323.1	2464.5	2615.0	2757.9	2880.0	2999.1	3084.1
30°	1734.1	1857.9	1983.2	2130.2	2286.6	2438.3	2599.6	2742.5	2871.1	2978.1	3026.0
32.5°	1687.5	1804.9	1934.1	2082.9	2243.2	2406.4	2566.4	2712.5	2831.5	2895.7	2896.9
35°	1606.4	1716.6	1850.7	1996.8	2161.3	2338.5	2500.6	2644.3	2717.0	2722.6	2644.3
37.5°	1517.9	1619.0	1745.6	1891.9	2072.0	2248.3	2413.9	2509.7	2534.0	2452.7	2308.0
40°	1454.7	1548.1	1670.3	1820.4	1999.2	2181.3	2332.2	2402.4	2376.9	2245.1	2083.8
42.5°	1388.3	1475.3	1593.0	1741.2	1920.7	2104.6	2233.2	2270.8	2203.1	2051.0	1862.2
45°	1279.9	1359.7	1476.3	1625.6	1798.0	1970.5	2067.9	2048.7	1936.1	1755.7	1544.1
47.5°	1167.0	1244.1	1349.0	1487.1	1663.7	1812.5	1878.5	1820.7	1660.5	1462.0	1289.9
50°	1092.2	1171.3	1267.9	1399.6	1560.9	1704.6	1746.9	1659.1	1481.0	1290.2	1132.1
52.5°	1018.8	1086.3	1181.0	1308.3	1462.5	1583.9	1606.4	1505.2	1321.4	1150.3	1010.1
55°	907.0	968.5	1048.3	1168.1	1301.4	1404.4	1392.4	1262.3	1095.4	949.3	839.1
57.5°	798.9	845.2	919.0	1031.2	1148.3	1217.4	1173.7	1062.7	907.2	787.6	694.6
60°	727.4	770.5	839.1	937.3	1040.3	1079.4	1042.7	922.2	799.2	689.8	611.6
62.5°	659.6	697.7	756.7	847.9	931.1	954.3	915.0	809.7	698.9	605.5	540.7
65°	561.3	596.4	646.7	711.4	768.9	780.0	754.5	646.7	562.9	484.6	439.9
67.5°	472.0	495.0	534.3	590.2	620.7	627.2	577.9	510.2	436.3	388.2	354.5
70°	412.0	427.9	464.7	495.0	519.8	520.6	475.1	420.8	364.1	325.0	300.2
72.5°	353.9	369.2	397.0	417.7	436.7	430.5	388.8	346.0	300.2	270.7	252.3
75°	273.1	286.6	301.0	310.6	310.6	302.6	272.3	240.3	214.0	196.4	190.8
77.5°	198.5	209.7	214.5	213.0	210.1	197.7	178.5	157.6	148.2	139.9	135.7
80°	155.7	160.5	162.1	158.1	153.3	138.9	126.1	117.4	108.6	105.4	103.8
82.5°	115.4	119.6	115.4	116.6	106.0	94.2	87.2	84.2	80.5	79.2	77.6
85°	61.5	60.7	59.1	55.1	47.9	46.3	45.5	44.7	43.1	43.9	42.3
87.5°	21.6	19.9	17.5	17.1	17.3	16.2	17.0	17.2	17.3	16.8	18.2
90°	2.5	3.6	4.7	5.8	6.7	7.6	8.4	9.2	10.0	10.6	11.2
92.5°	5.8	5.8	5.9	6.0	6.4	7.2	8.0	8.8	9.6	10.2	10.8
95°	21.5	18.1	14.7	11.2	9.6	9.7	9.8	9.9	10.0	10.6	11.2
97.5°	55.1	57.2	59.3	61.5	56.9	45.7	34.4	23.2	12.0	12.0	12.1
100°	76.1	78.0	79.8	81.6	75.5	61.6	47.7	33.8	19.9	18.2	16.5
102.5°	99.6	100.9	102.2	103.6	103.3	101.5	99.7	97.9	96.1	77.6	59.1
105°	137.0	137.6	138.2	138.8	139.4	139.9	140.4	140.9	141.4	142.3	143.2
107.5°	172.2	172.5	172.8	173.1	173.6	174.2	174.9	175.6	176.3	176.7	177.2
110°	196.1	196.4	196.7	197.0	197.4	198.0	198.7	199.3	199.9	200.1	200.3



TEST NUMBER: P333095

CATALOG NUMBER: S124RDIW-S1195D470U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	219.5	220.1	220.6	221.2	221.6	221.9	222.1	222.4	222.7	222.7	222.6
115°	255.0	255.3	255.6	255.9	256.0	255.9	255.8	255.7	255.6	255.8	256.0
117.5°	287.3	287.7	288.1	288.5	288.8	289.0	289.2	289.5	289.7	289.6	289.6
120°	309.0	309.4	309.8	310.2	310.4	310.3	310.2	310.1	310.0	310.2	310.4
122.5°	329.2	329.4	329.7	329.9	330.1	330.2	330.4	330.5	330.7	330.8	330.9
125°	358.4	358.8	359.2	359.6	359.7	359.5	359.3	359.1	358.9	359.2	359.5
127.5°	385.7	385.8	385.9	386.0	386.3	386.7	387.2	387.7	388.1	388.1	388.0
130°	403.4	403.6	403.7	403.8	404.0	404.3	404.6	404.9	405.2	405.3	405.4
132.5°	419.8	420.0	420.2	420.4	420.7	421.1	421.4	421.8	422.2	422.3	422.4
135°	444.0	443.9	443.8	443.7	443.9	444.3	444.7	445.1	445.5	445.7	445.9
137.5°	465.8	465.9	465.9	466.0	466.2	466.6	467.1	467.5	468.0	468.2	468.4
140°	480.1	480.3	480.5	480.7	480.9	481.1	481.4	481.6	481.8	482.1	482.4
142.5°	493.0	493.4	493.7	494.1	494.3	494.4	494.6	494.7	494.8	495.0	495.2
145°	512.4	512.7	513.0	513.3	513.5	513.5	513.5	513.5	513.5	513.6	513.7
147.5°	528.2	528.7	529.3	529.9	530.1	530.0	529.9	529.8	529.7	529.8	529.9
150°	539.3	539.7	540.1	540.5	540.6	540.5	540.4	540.3	540.2	540.2	540.2
152.5°	548.6	548.9	549.2	549.6	549.6	549.5	549.3	549.1	548.9	549.1	549.2
155°	561.6	561.7	561.8	561.9	561.8	561.5	561.2	560.9	560.6	561.0	561.4
157.5°	572.6	572.5	572.5	572.4	572.2	571.9	571.5	571.2	570.9	571.4	571.9
160°	578.9	578.6	578.3	578.0	577.8	577.7	577.6	577.5	577.4	578.0	578.6
162.5°	584.6	584.2	583.8	583.5	583.2	583.1	583.0	582.9	582.8	583.4	584.0
165°	591.8	591.3	590.8	590.3	590.1	590.1	590.1	590.1	590.1	590.9	591.7
167.5°	597.6	597.1	596.6	596.0	595.7	595.7	595.6	595.6	595.5	596.4	597.3
170°	600.8	600.2	599.6	599.0	598.7	598.8	598.9	599.0	599.1	599.9	600.7
172.5°	603.0	602.4	601.8	601.2	600.9	601.0	601.1	601.2	601.3	602.1	602.9
175°	605.3	604.7	604.1	603.5	603.3	603.4	603.5	603.6	603.7	604.6	605.5
177.5°	606.5	605.9	605.3	604.8	604.6	604.7	604.9	605.0	605.2	605.8	606.5
180°	605.9	605.9	605.9	605.9	605.9	605.9	605.9	605.9	605.9	605.9	605.9



TEST NUMBER: P333095

CATALOG NUMBER: S124RDIW-S1195D470U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7
2.5°	2078.7	2081.3	2083.2	2089.6	2090.2	2096.0	2090.2
5°	2250.7	2261.9	2279.5	2297.0	2298.6	2309.8	2289.8
7.5°	2443.6	2469.5	2485.6	2514.0	2525.2	2532.2	2520.7
10°	2576.5	2600.4	2642.7	2663.5	2684.3	2687.4	2677.9
12.5°	2704.9	2742.9	2776.2	2815.5	2814.6	2842.7	2832.4
15°	2875.9	2915.0	2961.3	3005.2	3021.2	3021.2	3034.0
17.5°	2997.9	3069.6	3117.5	3152.0	3189.6	3196.2	3191.7
20°	3080.3	3157.7	3208.8	3253.5	3279.1	3286.3	3286.3
22.5°	3141.6	3207.5	3257.4	3297.6	3318.7	3327.1	3324.6
25°	3184.1	3240.7	3271.1	3283.1	3288.6	3287.1	3271.9
27.5°	3125.9	3123.4	3104.2	3067.5	3039.9	3023.1	3003.9
30°	3014.8	2973.3	2925.4	2872.7	2804.8	2752.9	2736.9
32.5°	2849.4	2756.1	2675.0	2587.2	2514.2	2462.3	2440.6
35°	2529.4	2381.7	2261.1	2155.7	2079.1	2031.2	2015.2
37.5°	2149.6	2006.7	1857.4	1755.2	1691.7	1643.3	1625.2
40°	1908.2	1752.5	1622.4	1526.6	1461.1	1414.0	1413.2
42.5°	1687.8	1539.2	1416.7	1347.7	1277.1	1246.0	1245.8
45°	1382.0	1263.1	1159.3	1105.0	1062.7	1037.1	1029.9
47.5°	1144.3	1045.9	976.8	933.5	899.0	882.7	872.2
50°	1010.8	924.6	869.5	831.9	812.8	792.0	790.4
52.5°	899.6	830.0	787.1	756.6	732.3	719.8	720.2
55°	756.1	701.0	670.7	647.5	628.3	618.8	614.8
57.5°	637.0	595.6	573.6	552.3	544.2	536.7	534.6
60°	562.9	534.9	514.2	497.4	485.4	483.0	482.2
62.5°	501.6	472.3	458.0	445.0	436.3	432.6	431.1
65°	413.6	392.0	379.2	368.9	365.7	360.1	359.3
67.5°	333.4	320.5	312.0	304.8	300.5	300.2	300.2
70°	284.2	277.0	269.9	265.9	263.5	261.9	261.9
72.5°	242.1	236.8	230.9	228.8	228.3	226.7	226.1
75°	184.4	178.8	179.6	175.7	172.5	168.5	166.1
77.5°	130.8	126.8	126.0	125.5	122.8	122.3	123.6
80°	101.4	97.4	96.6	97.4	96.6	94.2	94.2
82.5°	77.1	73.8	73.0	72.5	71.7	72.5	71.2
85°	41.5	39.9	39.9	39.9	41.5	40.7	39.9
87.5°	17.0	16.5	17.2	16.7	16.7	16.1	16.8
90°	11.8	12.4	12.8	13.0	13.2	13.4	13.6
92.5°	11.4	12.0	12.3	12.4	12.4	12.5	12.5
95°	11.8	12.4	12.7	12.8	12.9	13.0	13.1
97.5°	12.1	12.2	12.3	12.4	12.5	12.6	12.7
100°	14.8	13.1	12.3	12.4	12.5	12.6	12.7
102.5°	40.7	22.2	13.0	13.0	13.0	13.0	13.1
105°	144.1	145.0	143.7	140.0	136.4	132.8	129.2
107.5°	177.6	178.1	178.5	178.9	179.2	179.6	180.0
110°	200.5	200.7	200.9	201.2	201.5	201.8	202.1



TEST NUMBER: P333095

CATALOG NUMBER: S124RDIW-S1195D470U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	222.6	222.5	222.7	223.1	223.5	223.9	224.2
115°	256.2	256.4	256.5	256.5	256.5	256.5	256.5
117.5°	289.6	289.5	289.5	289.4	289.4	289.4	289.3
120°	310.6	310.8	310.8	310.6	310.4	310.2	310.0
122.5°	331.0	331.1	331.1	330.9	330.7	330.5	330.3
125°	359.8	360.1	360.3	360.4	360.5	360.6	360.7
127.5°	387.9	387.9	387.8	387.7	387.6	387.6	387.5
130°	405.5	405.6	405.6	405.6	405.6	405.6	405.6
132.5°	422.5	422.6	422.6	422.5	422.5	422.4	422.3
135°	446.1	446.3	446.5	446.7	446.9	447.1	447.3
137.5°	468.6	468.9	468.9	468.9	468.8	468.8	468.7
140°	482.7	483.0	483.2	483.3	483.4	483.5	483.6
142.5°	495.5	495.7	495.8	495.8	495.9	495.9	495.9
145°	513.8	513.9	514.0	514.2	514.4	514.6	514.8
147.5°	529.9	530.0	530.1	530.2	530.3	530.4	530.5
150°	540.2	540.2	540.3	540.4	540.5	540.6	540.7
152.5°	549.4	549.6	549.6	549.6	549.5	549.4	549.4
155°	561.8	562.2	562.3	562.0	561.7	561.4	561.1
157.5°	572.4	572.9	572.9	572.4	571.9	571.4	570.9
160°	579.2	579.8	579.8	579.2	578.6	578.0	577.4
162.5°	584.6	585.2	585.2	584.5	583.8	583.1	582.5
165°	592.5	593.3	593.2	592.3	591.4	590.5	589.6
167.5°	598.2	599.1	599.0	598.0	597.0	596.0	595.0
170°	601.5	602.4	602.3	601.2	600.2	599.2	598.2
172.5°	603.7	604.5	604.4	603.3	602.2	601.1	600.0
175°	606.4	607.3	607.1	605.9	604.7	603.5	602.3
177.5°	607.1	607.8	607.6	606.7	605.7	604.7	603.8
180°	605.9	605.9	605.9	605.9	605.9	605.9	605.9

(END OF REPORT)