

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333023

Luminaire Tested: **S124RDIW-S350D1050U835-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333023
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S350D1050U835-4F0-1E-UDD-A
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1050 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5679.0 lumens
Efficiency: N/A
Efficacy: 149.4 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 38
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333023

CATALOG NUMBER: S124RDIW-S350D1050U835-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P333023

CATALOG NUMBER: S124RDIW-S350D1050U835-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	101	101	101	101	91	91	91	91	70	70	70	51	51	51	34	34	34	26				
1	93	89	85	82	83	79	76	73	62	60	58	45	44	43	31	30	29	23				
2	85	78	72	67	75	69	65	61	54	51	48	40	38	36	27	26	25	19				
3	77	68	61	56	69	61	55	51	48	44	41	36	33	31	24	23	22	17				
4	71	60	53	47	63	54	48	43	43	38	35	32	29	27	22	20	19	14				
5	65	54	46	40	58	48	42	37	38	33	30	29	26	23	20	18	16	13				
6	60	48	41	35	53	43	37	32	34	30	26	26	23	20	18	16	14	11				
7	55	43	36	31	49	39	33	28	31	26	23	23	20	18	16	14	13	10				
8	51	39	32	27	45	35	29	25	28	24	20	21	18	16	15	13	12	9				
9	47	36	29	24	42	32	26	22	26	21	18	20	16	14	14	12	10	8				
10	44	33	26	21	39	30	24	19	24	19	16	18	15	13	13	11	9	7				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4742	4742	4742	4742
5°	5501	4756	4204	4756
10°	6507	4736	3752	4736
15°	7516	4692	3224	4692
20°	8369	4631	2916	4631
25°	8639	4572	2707	4572
30°	7563	4501	2581	4501
35°	5887	4394	2505	4394
40°	4415	4272	2464	4272
45°	3486	4077	2442	4077
50°	2943	3852	2372	3852
55°	2564	3605	2245	3605
60°	2307	3347	1988	3347
65°	2034	3070	1710	3070
70°	1832	2783	1541	2783
75°	1535	2464	1313	2464
80°	1297	2101	1232	2101
85°	1093	1649	1093	1649



TEST NUMBER: P333023

CATALOG NUMBER: S124RDIW-S350D1050U835-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.9	1.0
10°-20°	171.7	3.0
20°-30°	268.5	4.7
30°-40°	298.5	5.3
40°-50°	264.9	4.7
50°-60°	206.4	3.6
60°-70°	135.1	2.4
70°-80°	66.4	1.2
80°-90°	20.3	0.4
90°-100°	46.3	0.8
100°-110°	295.4	5.2
110°-120°	565.1	10.0
120°-130°	717.4	12.6
130°-140°	767.5	13.5
140°-150°	717.7	12.6
150°-160°	578.8	10.2
160°-170°	373.3	6.6
170°-180°	128.7	2.3
0°-30°	497.1	8.8
0°-40°	795.6	14.0
0°-60°	1266.9	22.3
0°-90°	1488.7	26.2
90°-120°	906.8	16.0
90°-150°	3109.5	54.8
90°-180°	4190.0	73.8
0°-180°	5679.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	587	587	587	587	587	
5°	679	587	519	587	679	69
15°	899	561	386	561	899	256
25°	970	513	304	513	970	430
35°	597	446	254	446	597	374
45°	305	357	214	357	305	242
55°	182	256	160	256	182	166
65°	106	161	90	161	106	107
75°	49	79	42	79	49	54
85°	12	18	12	18	12	14
90°	30	3	30	3	30	14
95°	29	56	29	56	29	23
105°	289	305	289	305	289	252
115°	574	569	574	569	574	568
125°	806	800	806	800	806	718
135°	1000	993	1000	993	1000	770
145°	1151	1145	1151	1145	1151	719
155°	1254	1255	1254	1255	1254	578
165°	1318	1324	1318	1324	1318	372
175°	1346	1355	1346	1355	1346	128
180°	1355	1355	1355	1355	1355	



TEST NUMBER: P333023

CATALOG NUMBER: S124RDIW-S350D1050U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4
2.5°	619.6	621.3	619.6	619.4	617.5	616.9	616.2	613.7	609.2	606.5	607.1
5°	678.8	684.7	681.4	680.9	675.7	670.5	667.2	659.6	651.5	646.1	641.6
7.5°	747.2	750.6	748.5	745.2	736.8	732.0	724.3	714.4	699.9	688.9	678.8
10°	793.8	796.6	795.7	789.5	783.4	770.8	763.7	749.8	731.5	717.1	703.6
12.5°	839.6	842.6	834.3	834.6	822.9	813.0	801.8	784.2	763.2	744.6	727.7
15°	899.3	895.5	895.5	890.8	877.8	864.1	852.5	834.0	807.5	785.3	761.8
17.5°	946.1	947.4	945.5	934.3	924.1	909.9	888.6	867.1	842.5	812.6	788.7
20°	974.1	974.1	972.0	964.4	951.2	936.0	913.1	889.6	858.4	828.3	801.4
22.5°	985.5	986.2	983.7	977.5	965.6	950.8	931.2	907.4	875.2	841.4	808.0
25°	969.9	974.4	974.8	973.2	969.6	960.6	943.8	919.5	890.6	853.9	817.9
27.5°	890.4	896.1	901.1	909.3	920.2	925.8	926.6	914.2	889.0	853.7	817.5
30°	811.3	816.0	831.4	851.5	867.1	881.3	893.7	897.0	882.8	851.1	813.0
32.5°	723.4	729.9	745.3	766.9	792.9	817.0	844.6	858.7	858.3	839.3	804.1
35°	597.3	602.1	616.3	639.0	670.2	706.0	749.8	783.8	807.0	805.4	783.8
37.5°	481.8	487.1	501.4	520.3	550.6	594.8	637.2	684.2	727.0	751.1	743.9
40°	418.9	419.1	433.1	452.5	480.9	519.5	565.6	617.7	665.5	704.6	712.1
42.5°	369.3	369.3	378.6	399.5	419.9	456.2	500.3	552.0	608.0	653.1	673.1
45°	305.3	307.4	315.0	327.5	343.6	374.4	409.7	457.7	520.4	573.9	607.3
47.5°	258.5	261.7	266.5	276.7	289.5	310.0	339.2	382.4	433.4	492.2	539.7
50°	234.3	234.8	240.9	246.6	257.7	274.1	299.6	335.6	382.5	439.0	491.8
52.5°	213.5	213.4	217.1	224.3	233.3	246.0	266.7	299.4	341.0	391.7	446.2
55°	182.2	183.4	186.3	191.9	198.8	207.8	224.1	248.7	281.4	324.7	374.2
57.5°	158.5	159.1	161.3	163.7	170.0	176.6	188.8	205.9	233.4	268.9	315.0
60°	142.9	143.2	143.9	147.4	152.4	158.6	166.9	181.3	204.5	236.9	273.4
62.5°	127.8	128.2	129.3	131.9	135.8	140.0	148.7	160.3	179.5	207.2	240.0
65°	106.5	106.7	108.4	109.3	112.4	116.2	122.6	130.4	143.7	166.9	191.7
67.5°	89.0	89.0	89.1	90.4	92.5	95.0	98.8	105.1	115.1	129.3	151.2
70°	77.6	77.6	78.1	78.8	80.0	82.1	84.3	89.0	96.3	107.9	124.7
72.5°	67.0	67.2	67.7	67.8	68.4	70.2	71.8	74.8	80.2	89.0	102.6
75°	49.2	49.9	51.1	52.1	53.3	53.0	54.7	56.6	58.2	63.4	71.2
77.5°	36.6	36.3	36.4	37.2	37.3	37.6	38.8	40.2	41.5	43.9	46.7
80°	27.9	27.9	28.6	28.9	28.6	28.9	30.1	30.8	31.2	32.2	34.8
82.5°	21.1	21.5	21.3	21.5	21.6	21.9	22.9	23.0	23.5	23.9	24.9
85°	11.8	12.1	12.3	11.8	11.8	11.8	12.3	12.5	13.0	12.8	13.3
87.5°	10.2	10.0	10.1	10.0	10.1	9.7	9.6	9.7	9.1	9.0	8.6
90°	30.4	29.9	29.5	29.0	28.6	27.7	26.3	25.0	23.6	22.3	20.5
92.5°	28.0	27.9	27.8	27.7	27.6	26.9	25.5	24.2	22.8	21.5	19.7
95°	29.4	29.2	28.9	28.7	28.5	27.7	26.3	25.0	23.6	22.3	22.1
97.5°	28.4	28.1	27.9	27.7	27.5	27.3	27.2	27.0	26.9	26.7	51.9
100°	28.4	28.1	27.9	27.7	27.5	29.3	33.1	36.9	40.8	44.6	75.7
102.5°	29.2	29.1	29.1	29.0	29.0	49.6	90.9	132.2	173.5	214.8	218.8
105°	288.8	296.9	305.0	313.1	321.2	324.2	322.2	320.2	318.1	316.1	315.0
107.5°	402.4	401.6	400.7	399.9	399.0	398.1	397.1	396.1	395.1	394.1	392.6
110°	451.9	451.2	450.5	449.9	449.2	448.6	448.2	447.7	447.3	446.8	445.5



TEST NUMBER: P333023

CATALOG NUMBER: S124RDIW-S350D1050U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	501.3	500.5	499.6	498.8	497.9	497.5	497.6	497.7	497.8	497.9	497.2
115°	573.5	573.5	573.5	573.5	573.5	573.2	572.8	572.3	571.9	571.4	571.7
117.5°	646.8	646.9	647.0	647.1	647.2	647.3	647.4	647.4	647.5	647.6	647.1
120°	693.0	693.5	693.9	694.4	694.8	694.8	694.4	693.9	693.5	693.0	693.2
122.5°	738.4	738.9	739.3	739.8	740.2	740.3	740.0	739.8	739.5	739.2	738.9
125°	806.5	806.3	806.0	805.8	805.6	805.1	804.5	803.8	803.1	802.4	802.9
127.5°	866.3	866.4	866.6	866.8	867.0	867.1	867.3	867.4	867.6	867.7	866.6
130°	906.8	906.8	906.8	906.8	906.8	906.7	906.5	906.2	906.0	905.8	905.1
132.5°	944.1	944.3	944.4	944.6	944.8	944.8	944.6	944.3	944.1	943.9	943.0
135°	1000.0	999.6	999.1	998.7	998.2	997.8	997.3	996.9	996.4	996.0	995.1
137.5°	1047.8	1048.0	1048.1	1048.2	1048.4	1048.2	1047.7	1047.2	1046.7	1046.2	1045.2
140°	1081.1	1080.8	1080.6	1080.4	1080.2	1079.7	1079.0	1078.4	1077.7	1077.0	1076.6
142.5°	1108.6	1108.6	1108.5	1108.5	1108.4	1108.2	1107.7	1107.2	1106.7	1106.2	1105.9
145°	1151.0	1150.5	1150.1	1149.6	1149.2	1148.8	1148.6	1148.4	1148.2	1147.9	1147.9
147.5°	1186.0	1185.8	1185.6	1185.4	1185.1	1184.9	1184.7	1184.6	1184.4	1184.2	1184.4
150°	1208.7	1208.5	1208.3	1208.0	1207.8	1207.7	1207.7	1207.7	1207.7	1207.7	1207.9
152.5°	1228.2	1228.3	1228.4	1228.6	1228.7	1228.6	1228.2	1227.9	1227.5	1227.2	1227.6
155°	1254.3	1255.0	1255.7	1256.3	1257.0	1256.9	1256.0	1255.1	1254.2	1253.3	1254.0
157.5°	1276.2	1277.4	1278.5	1279.7	1280.9	1280.9	1279.7	1278.5	1277.4	1276.2	1277.0
160°	1290.8	1292.1	1293.5	1294.8	1296.2	1296.2	1294.8	1293.5	1292.1	1290.8	1291.0
162.5°	1302.1	1303.7	1305.2	1306.7	1308.3	1308.3	1307.0	1305.6	1304.3	1302.9	1303.2
165°	1318.1	1320.2	1322.2	1324.2	1326.2	1326.4	1324.6	1322.8	1321.0	1319.2	1319.2
167.5°	1330.1	1332.4	1334.6	1336.9	1339.1	1339.2	1337.3	1335.3	1333.3	1331.3	1331.5
170°	1337.4	1339.6	1341.9	1344.1	1346.4	1346.6	1344.8	1343.0	1341.2	1339.4	1339.2
172.5°	1341.4	1343.9	1346.3	1348.7	1351.2	1351.5	1349.7	1347.9	1346.1	1344.3	1344.1
175°	1346.5	1349.2	1351.9	1354.6	1357.3	1357.7	1355.6	1353.6	1351.6	1349.6	1349.3
177.5°	1349.8	1351.9	1354.1	1356.2	1358.4	1358.8	1357.3	1355.9	1354.4	1353.0	1352.6
180°	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6



TEST NUMBER: P333023

CATALOG NUMBER: S124RDIW-S350D1050U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4
2.5°	605.2	602.6	601.2	598.2	594.6	592.7	591.0	588.5	585.3	581.9	579.5
5°	635.9	630.2	623.1	614.6	607.1	599.7	593.3	586.9	579.6	572.0	564.5
7.5°	667.4	656.3	644.2	630.2	616.7	604.3	592.9	582.1	569.8	558.7	548.7
10°	689.4	674.3	657.5	639.7	622.0	606.6	591.4	577.7	562.6	549.1	537.7
12.5°	707.2	689.4	669.2	647.1	625.7	607.1	589.7	571.8	554.6	540.0	524.8
15°	736.7	712.4	685.2	658.6	631.0	605.6	582.2	561.4	541.7	521.1	506.7
17.5°	757.1	728.1	695.0	663.2	630.5	600.6	573.6	548.8	526.1	505.1	487.9
20°	769.2	737.2	700.5	664.3	627.6	595.7	566.6	539.1	515.7	493.0	475.2
22.5°	776.0	740.6	700.5	662.6	624.6	590.0	558.1	529.5	504.0	481.2	461.6
25°	778.2	740.3	699.4	655.8	614.2	577.5	544.3	513.3	484.9	462.2	441.4
27.5°	775.1	730.5	688.6	643.9	600.9	562.3	527.5	494.9	466.5	442.1	420.7
30°	770.6	722.8	677.8	631.4	587.9	550.7	514.0	482.8	453.2	427.9	406.4
32.5°	760.7	713.3	664.9	617.4	573.3	535.0	500.2	468.8	439.8	413.9	391.0
35°	741.2	693.2	640.7	591.9	548.6	508.8	476.2	445.9	418.2	390.5	366.4
37.5°	715.5	666.5	614.2	560.8	517.4	479.9	450.0	421.5	394.5	369.2	342.5
40°	691.3	646.6	592.6	539.6	495.1	458.9	431.2	405.4	378.2	353.1	326.4
42.5°	662.0	623.9	569.3	516.1	472.2	437.3	411.5	386.3	361.5	337.2	309.3
45°	613.0	584.1	533.0	481.9	437.6	403.0	379.4	357.1	335.4	312.2	285.9
47.5°	556.8	537.3	493.2	440.8	399.9	368.8	345.9	327.7	309.3	286.1	263.1
50°	517.8	505.3	462.7	414.9	375.8	347.2	323.8	306.7	291.3	269.1	248.5
52.5°	476.2	469.5	433.5	387.8	350.1	322.0	302.0	286.7	271.1	252.6	233.4
55°	412.7	416.3	385.8	346.2	310.7	287.1	268.9	256.1	242.8	227.2	212.3
57.5°	347.9	360.9	340.4	305.7	272.4	250.5	236.8	226.1	214.9	202.0	189.2
60°	309.1	320.0	308.4	277.8	248.7	228.4	215.6	207.3	196.2	184.4	174.7
62.5°	271.2	282.9	276.0	251.3	224.3	206.8	195.5	187.8	179.5	169.2	159.1
65°	223.7	231.2	227.9	210.9	191.7	176.8	166.4	160.7	153.1	145.6	136.6
67.5°	171.3	185.9	184.0	174.9	158.4	146.7	139.9	134.9	128.0	122.4	116.3
70°	140.8	154.3	154.1	146.7	137.7	126.9	122.1	117.9	111.7	106.3	101.3
72.5°	115.3	127.6	129.5	123.8	117.7	109.4	104.9	102.0	96.0	92.3	88.2
75°	80.7	89.7	92.1	92.1	89.2	85.0	80.9	79.0	74.8	71.5	69.1
77.5°	52.9	58.6	62.3	63.1	63.6	62.1	58.8	57.5	54.2	53.1	50.8
80°	37.4	41.2	45.4	46.9	48.0	47.6	46.2	45.2	42.1	40.9	40.0
82.5°	25.8	27.9	31.4	34.6	34.2	35.5	34.2	33.5	31.1	30.7	29.8
85°	13.5	13.7	14.2	16.3	17.5	18.0	18.2	17.8	17.0	17.0	15.4
87.5°	8.3	7.7	7.8	7.3	7.0	7.3	7.4	7.0	7.0	6.9	6.8
90°	18.7	16.9	15.1	12.9	10.5	8.0	5.5	3.0	5.5	8.0	10.5
92.5°	17.9	16.1	14.3	13.3	13.2	13.0	12.9	12.8	12.9	13.0	13.2
95°	21.8	21.6	21.4	25.1	32.8	40.4	48.1	55.7	48.1	40.4	32.8
97.5°	77.0	102.1	127.3	137.4	132.7	127.9	123.1	118.3	123.1	127.9	132.7
100°	106.7	137.8	168.9	182.4	178.3	174.3	170.2	166.2	170.2	174.3	178.3
102.5°	222.9	227.0	231.0	231.5	228.6	225.6	222.6	219.7	222.6	225.6	228.6
105°	313.9	312.7	311.6	310.4	309.0	307.7	306.3	305.0	306.3	307.7	309.0
107.5°	391.1	389.5	388.0	386.9	386.2	385.5	384.9	384.2	384.9	385.5	386.2
110°	444.1	442.8	441.4	440.4	439.7	439.0	438.4	437.7	438.4	439.0	439.7



TEST NUMBER: P333023

CATALOG NUMBER: S124RDIW-S350D1050U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	496.6	496.0	495.4	494.4	493.2	492.0	490.8	489.6	490.8	492.0	493.2
115°	571.9	572.1	572.3	572.1	571.4	570.8	570.1	569.4	570.1	570.8	571.4
117.5°	646.6	646.1	645.6	644.9	644.0	643.1	642.2	641.3	642.2	643.1	644.0
120°	693.5	693.7	693.9	693.6	692.7	691.8	690.9	690.0	690.9	691.8	692.7
122.5°	738.6	738.3	738.0	737.5	737.0	736.4	735.9	735.4	735.9	736.4	737.0
125°	803.3	803.8	804.2	804.0	803.1	802.2	801.3	800.4	801.3	802.2	803.1
127.5°	865.6	864.6	863.5	862.9	862.7	862.5	862.2	862.0	862.2	862.5	862.7
130°	904.4	903.8	903.1	902.6	902.4	902.2	902.0	901.7	902.0	902.2	902.4
132.5°	942.2	941.3	940.5	939.8	939.4	939.0	938.6	938.2	938.6	939.0	939.4
135°	994.2	993.3	992.4	992.0	992.2	992.5	992.7	992.9	992.7	992.5	992.2
137.5°	1044.2	1043.2	1042.2	1041.7	1041.6	1041.5	1041.4	1041.3	1041.4	1041.5	1041.6
140°	1076.1	1075.7	1075.2	1074.8	1074.3	1073.9	1073.4	1073.0	1073.4	1073.9	1074.3
142.5°	1105.6	1105.4	1105.1	1104.6	1103.8	1102.9	1102.1	1101.3	1102.1	1102.9	1103.8
145°	1147.9	1147.9	1147.9	1147.6	1146.9	1146.2	1145.6	1144.9	1145.6	1146.2	1146.9
147.5°	1184.7	1184.9	1185.1	1184.6	1183.3	1182.1	1180.8	1179.5	1180.8	1182.1	1183.3
150°	1208.2	1208.4	1208.6	1208.3	1207.4	1206.5	1205.6	1204.7	1205.6	1206.5	1207.4
152.5°	1228.0	1228.4	1228.8	1228.6	1227.9	1227.2	1226.5	1225.7	1226.5	1227.2	1227.9
155°	1254.7	1255.3	1256.0	1256.2	1256.0	1255.8	1255.6	1255.3	1255.6	1255.8	1256.0
157.5°	1277.7	1278.5	1279.3	1279.7	1279.8	1280.0	1280.1	1280.3	1280.1	1280.0	1279.8
160°	1291.2	1291.5	1291.7	1292.1	1292.8	1293.5	1294.2	1294.8	1294.2	1293.5	1292.8
162.5°	1303.4	1303.6	1303.8	1304.4	1305.2	1306.1	1307.0	1307.8	1307.0	1306.1	1305.2
165°	1319.2	1319.2	1319.2	1319.7	1320.8	1322.0	1323.1	1324.2	1323.1	1322.0	1320.8
167.5°	1331.6	1331.7	1331.9	1332.5	1333.7	1334.9	1336.0	1337.2	1336.0	1334.9	1333.7
170°	1339.0	1338.7	1338.5	1339.1	1340.4	1341.8	1343.1	1344.5	1343.1	1341.8	1340.4
172.5°	1343.8	1343.6	1343.4	1343.9	1345.3	1346.6	1348.0	1349.3	1348.0	1346.6	1345.3
175°	1349.1	1348.9	1348.7	1349.2	1350.6	1351.9	1353.3	1354.6	1353.3	1351.9	1350.6
177.5°	1352.3	1351.9	1351.6	1352.0	1353.3	1354.5	1355.8	1357.0	1355.8	1354.5	1353.3
180°	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6



TEST NUMBER: P333023

CATALOG NUMBER: S124RDIW-S350D1050U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4
2.5°	576.8	574.9	572.5	569.6	566.2	563.2	561.8	563.0	563.6	562.0	561.8
5°	559.2	553.3	548.6	541.5	535.8	531.1	527.8	526.3	526.8	523.0	522.1
7.5°	539.5	532.5	524.7	516.3	508.5	501.5	497.9	495.9	491.8	490.1	487.2
10°	526.8	517.4	509.8	499.8	490.8	482.6	478.5	475.2	471.2	469.3	465.3
12.5°	513.8	502.8	494.4	484.1	474.9	465.0	461.1	455.0	448.7	444.7	439.5
15°	495.3	482.1	471.9	459.6	448.7	437.4	427.2	415.8	411.6	402.6	397.4
17.5°	473.8	460.4	447.8	431.3	414.5	400.3	389.5	378.6	372.1	366.4	363.7
20°	459.6	447.3	429.8	410.6	391.9	376.3	367.5	360.4	353.3	349.3	346.5
22.5°	446.2	430.4	410.1	389.4	370.7	358.5	351.1	343.8	338.0	334.2	330.4
25°	423.6	403.0	381.5	357.8	345.1	334.4	326.4	320.4	316.9	311.9	310.0
27.5°	400.5	375.5	351.8	335.9	322.6	312.8	305.8	301.4	296.9	293.7	291.2
30°	382.7	357.4	336.1	320.9	307.4	299.4	293.7	288.5	284.9	282.3	280.5
32.5°	365.1	339.8	321.9	305.6	294.9	287.1	281.0	277.1	274.3	271.0	269.8
35°	339.6	317.1	301.5	286.8	276.0	268.9	264.1	260.1	257.7	256.8	256.1
37.5°	315.1	296.7	279.9	267.9	258.2	252.6	247.0	245.0	243.4	241.7	242.5
40°	299.6	282.3	267.4	254.7	246.8	240.7	237.4	235.0	233.6	233.6	233.6
42.5°	286.2	269.3	254.7	243.3	235.5	230.3	226.6	224.6	224.1	223.9	225.1
45°	265.3	249.7	235.0	225.5	218.9	213.7	211.6	209.9	209.9	210.9	211.1
47.5°	244.6	230.0	218.2	207.6	201.5	198.3	196.4	195.6	195.7	196.6	197.7
50°	231.9	217.5	205.9	196.4	190.8	187.7	186.0	185.5	186.0	186.0	187.7
52.5°	218.1	205.2	193.8	185.8	179.4	176.5	175.6	174.9	175.2	176.0	176.7
55°	197.9	186.3	175.4	167.8	163.1	161.2	159.0	159.3	158.8	159.3	159.3
57.5°	177.5	167.1	157.0	151.0	146.8	144.1	141.8	142.4	141.7	141.6	141.2
60°	164.5	153.1	145.1	139.6	134.9	132.5	130.4	130.9	130.2	129.7	128.7
62.5°	150.3	140.8	133.1	127.9	124.1	121.4	119.2	118.8	117.1	115.5	113.4
65°	129.7	121.9	115.0	110.1	106.5	104.4	102.7	101.3	97.7	94.0	92.1
67.5°	109.7	104.0	97.6	93.4	90.5	87.8	84.6	82.2	78.9	76.8	75.6
70°	96.8	91.4	85.9	81.9	78.8	76.2	72.7	71.0	68.6	67.7	66.5
72.5°	84.5	79.4	74.4	70.7	67.5	65.4	62.6	61.0	59.9	59.5	58.4
75°	65.8	61.8	58.0	54.7	52.1	50.6	49.5	48.3	47.8	45.7	44.5
77.5°	48.0	45.3	43.0	40.6	38.8	37.8	35.5	34.2	33.4	32.4	32.1
80°	37.4	35.5	33.1	31.7	29.1	28.2	27.2	27.0	26.7	26.5	26.3
82.5°	28.1	26.2	23.9	23.0	22.3	21.7	21.2	20.9	20.7	20.8	20.8
85°	14.2	13.3	13.3	13.0	12.8	12.5	12.3	12.3	12.1	12.3	12.1
87.5°	7.3	7.6	7.9	7.9	8.5	8.8	8.9	9.2	9.6	9.5	9.7
90°	12.9	15.1	16.9	18.7	20.5	22.3	23.6	25.0	26.3	27.7	28.6
92.5°	13.3	14.3	16.1	17.9	19.7	21.5	22.8	24.2	25.5	26.9	27.6
95°	25.1	21.4	21.6	21.8	22.1	22.3	23.6	25.0	26.3	27.7	28.5
97.5°	137.4	127.3	102.1	77.0	51.9	26.7	26.9	27.0	27.2	27.3	27.5
100°	182.4	168.9	137.8	106.7	75.7	44.6	40.8	36.9	33.1	29.3	27.5
102.5°	231.5	231.0	227.0	222.9	218.8	214.8	173.5	132.2	90.9	49.6	29.0
105°	310.4	311.6	312.7	313.9	315.0	316.1	318.1	320.2	322.2	324.2	321.2
107.5°	386.9	388.0	389.5	391.1	392.6	394.1	395.1	396.1	397.1	398.1	399.0
110°	440.4	441.4	442.8	444.1	445.5	446.8	447.3	447.7	448.2	448.6	449.2



TEST NUMBER: P333023

CATALOG NUMBER: S124RDIW-S350D1050U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	494.4	495.4	496.0	496.6	497.2	497.9	497.8	497.7	497.6	497.5	497.9
115°	572.1	572.3	572.1	571.9	571.7	571.4	571.9	572.3	572.8	573.2	573.5
117.5°	644.9	645.6	646.1	646.6	647.1	647.6	647.5	647.4	647.4	647.3	647.2
120°	693.6	693.9	693.7	693.5	693.2	693.0	693.5	693.9	694.4	694.8	694.8
122.5°	737.5	738.0	738.3	738.6	738.9	739.2	739.5	739.8	740.0	740.3	740.2
125°	804.0	804.2	803.8	803.3	802.9	802.4	803.1	803.8	804.5	805.1	805.6
127.5°	862.9	863.5	864.6	865.6	866.6	867.7	867.6	867.4	867.3	867.1	867.0
130°	902.6	903.1	903.8	904.4	905.1	905.8	906.0	906.2	906.5	906.7	906.8
132.5°	939.8	940.5	941.3	942.2	943.0	943.9	944.1	944.3	944.6	944.8	944.8
135°	992.0	992.4	993.3	994.2	995.1	996.0	996.4	996.9	997.3	997.8	998.2
137.5°	1041.7	1042.2	1043.2	1044.2	1045.2	1046.2	1046.7	1047.2	1047.7	1048.2	1048.4
140°	1074.8	1075.2	1075.7	1076.1	1076.6	1077.0	1077.7	1078.4	1079.0	1079.7	1080.2
142.5°	1104.6	1105.1	1105.4	1105.6	1105.9	1106.2	1106.7	1107.2	1107.7	1108.2	1108.4
145°	1147.6	1147.9	1147.9	1147.9	1147.9	1147.9	1148.2	1148.4	1148.6	1148.8	1149.2
147.5°	1184.6	1185.1	1184.9	1184.7	1184.4	1184.2	1184.4	1184.6	1184.7	1184.9	1185.1
150°	1208.3	1208.6	1208.4	1208.2	1207.9	1207.7	1207.7	1207.7	1207.7	1207.7	1207.8
152.5°	1228.6	1228.8	1228.4	1228.0	1227.6	1227.2	1227.5	1227.9	1228.2	1228.6	1228.7
155°	1256.2	1256.0	1255.3	1254.7	1254.0	1253.3	1254.2	1255.1	1256.0	1256.9	1257.0
157.5°	1279.7	1279.3	1278.5	1277.7	1277.0	1276.2	1277.4	1278.5	1279.7	1280.9	1280.9
160°	1292.1	1291.7	1291.5	1291.2	1291.0	1290.8	1292.1	1293.5	1294.8	1296.2	1296.2
162.5°	1304.4	1303.8	1303.6	1303.4	1303.2	1302.9	1304.3	1305.6	1307.0	1308.3	1308.3
165°	1319.7	1319.2	1319.2	1319.2	1319.2	1319.2	1321.0	1322.8	1324.6	1326.4	1326.2
167.5°	1332.5	1331.9	1331.7	1331.6	1331.5	1331.3	1333.3	1335.3	1337.3	1339.2	1339.1
170°	1339.1	1338.5	1338.7	1339.0	1339.2	1339.4	1341.2	1343.0	1344.8	1346.6	1346.4
172.5°	1343.9	1343.4	1343.6	1343.8	1344.1	1344.3	1346.1	1347.9	1349.7	1351.5	1351.2
175°	1349.2	1348.7	1348.9	1349.1	1349.3	1349.6	1351.6	1353.6	1355.6	1357.7	1357.3
177.5°	1352.0	1351.6	1351.9	1352.3	1352.6	1353.0	1354.4	1355.9	1357.3	1358.8	1358.4
180°	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6



TEST NUMBER: P333023

CATALOG NUMBER: S124RDIW-S350D1050U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4
2.5°	560.7	561.1	559.8	559.4	559.8	561.1	560.7	561.8	562.0	563.6	563.0
5°	520.2	519.7	518.5	518.8	518.5	519.7	520.2	522.1	523.0	526.8	526.3
7.5°	485.5	483.7	484.2	482.3	484.2	483.7	485.5	487.2	490.1	491.8	495.9
10°	464.3	461.7	459.6	457.7	459.6	461.7	464.3	465.3	469.3	471.2	475.2
12.5°	435.4	433.1	430.3	430.8	430.3	433.1	435.4	439.5	444.7	448.7	455.0
15°	394.3	390.7	385.1	385.8	385.1	390.7	394.3	397.4	402.6	411.6	415.8
17.5°	359.5	359.5	356.9	357.6	356.9	359.5	359.5	363.7	366.4	372.1	378.6
20°	341.5	339.9	340.1	339.4	340.1	339.9	341.5	346.5	349.3	353.3	360.4
22.5°	329.0	327.0	325.3	323.9	325.3	327.0	329.0	330.4	334.2	338.0	343.8
25°	307.9	306.5	304.4	303.9	304.4	306.5	307.9	310.0	311.9	316.9	320.4
27.5°	289.3	289.1	288.2	287.1	288.2	289.1	289.3	291.2	293.7	296.9	301.4
30°	278.6	278.1	277.6	276.9	277.6	278.1	278.6	280.5	282.3	284.9	288.5
32.5°	268.9	268.6	268.1	268.2	268.1	268.6	268.9	269.8	271.0	274.3	277.1
35°	255.1	254.9	254.4	254.2	254.4	254.9	255.1	256.1	256.8	257.7	260.1
37.5°	242.3	242.9	242.6	242.5	242.6	242.9	242.3	242.5	241.7	243.4	245.0
40°	233.4	233.6	234.1	233.8	234.1	233.6	233.4	233.6	233.6	233.6	235.0
42.5°	226.0	226.0	226.7	225.9	226.7	226.0	226.0	225.1	223.9	224.1	224.6
45°	212.8	214.2	213.9	213.9	213.9	214.2	212.8	211.1	210.9	209.9	209.9
47.5°	198.3	199.6	199.9	199.8	199.9	199.6	198.3	197.7	196.6	195.7	195.6
50°	188.9	188.4	189.1	188.9	189.1	188.4	188.9	187.7	186.0	186.0	185.5
52.5°	177.3	177.4	177.4	177.1	177.4	177.4	177.3	176.7	176.0	175.2	174.9
55°	159.5	159.8	159.3	159.5	159.3	159.8	159.5	159.3	159.3	158.8	159.3
57.5°	140.2	139.1	139.5	139.0	139.5	139.1	140.2	141.2	141.6	141.7	142.4
60°	126.4	124.5	124.0	123.1	124.0	124.5	126.4	128.7	129.7	130.2	130.9
62.5°	110.9	109.5	107.9	108.7	107.9	109.5	110.9	113.4	115.5	117.1	118.8
65°	90.2	89.2	88.5	89.5	88.5	89.2	90.2	92.1	94.0	97.7	101.3
67.5°	74.6	74.1	74.1	73.7	74.1	74.1	74.6	75.6	76.8	78.9	82.2
70°	66.5	65.8	65.8	65.3	65.8	65.8	66.5	66.5	67.7	68.6	71.0
72.5°	58.2	57.5	57.7	57.4	57.7	57.5	58.2	58.4	59.5	59.9	61.0
75°	43.1	41.9	41.9	42.1	41.9	41.9	43.1	44.5	45.7	47.8	48.3
77.5°	32.1	31.9	32.2	31.8	32.2	31.9	32.1	32.1	32.4	33.4	34.2
80°	26.3	26.0	25.8	26.5	25.8	26.0	26.3	26.3	26.5	26.7	27.0
82.5°	20.4	20.4	20.3	21.2	20.3	20.4	20.4	20.8	20.8	20.7	20.9
85°	12.3	11.8	12.3	11.8	12.3	11.8	12.3	12.1	12.3	12.1	12.3
87.5°	10.2	10.1	10.0	10.2	10.0	10.1	10.2	9.7	9.5	9.6	9.2
90°	29.0	29.5	29.9	30.4	29.9	29.5	29.0	28.6	27.7	26.3	25.0
92.5°	27.7	27.8	27.9	28.0	27.9	27.8	27.7	27.6	26.9	25.5	24.2
95°	28.7	28.9	29.2	29.4	29.2	28.9	28.7	28.5	27.7	26.3	25.0
97.5°	27.7	27.9	28.1	28.4	28.1	27.9	27.7	27.5	27.3	27.2	27.0
100°	27.7	27.9	28.1	28.4	28.1	27.9	27.7	27.5	29.3	33.1	36.9
102.5°	29.0	29.1	29.1	29.2	29.1	29.1	29.0	29.0	49.6	90.9	132.2
105°	313.1	305.0	296.9	288.8	296.9	305.0	313.1	321.2	324.2	322.2	320.2
107.5°	399.9	400.7	401.6	402.4	401.6	400.7	399.9	399.0	398.1	397.1	396.1
110°	449.9	450.5	451.2	451.9	451.2	450.5	449.9	449.2	448.6	448.2	447.7



TEST NUMBER: P333023

CATALOG NUMBER: S124RDIW-S350D1050U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	498.8	499.6	500.5	501.3	500.5	499.6	498.8	497.9	497.5	497.6	497.7
115°	573.5	573.5	573.5	573.5	573.5	573.5	573.5	573.5	573.2	572.8	572.3
117.5°	647.1	647.0	646.9	646.8	646.9	647.0	647.1	647.2	647.3	647.4	647.4
120°	694.4	693.9	693.5	693.0	693.5	693.9	694.4	694.8	694.8	694.4	693.9
122.5°	739.8	739.3	738.9	738.4	738.9	739.3	739.8	740.2	740.3	740.0	739.8
125°	805.8	806.0	806.3	806.5	806.3	806.0	805.8	805.6	805.1	804.5	803.8
127.5°	866.8	866.6	866.4	866.3	866.4	866.6	866.8	867.0	867.1	867.3	867.4
130°	906.8	906.8	906.8	906.8	906.8	906.8	906.8	906.8	906.7	906.5	906.2
132.5°	944.6	944.4	944.3	944.1	944.3	944.4	944.6	944.8	944.8	944.6	944.3
135°	998.7	999.1	999.6	1000.0	999.6	999.1	998.7	998.2	997.8	997.3	996.9
137.5°	1048.2	1048.1	1048.0	1047.8	1048.0	1048.1	1048.2	1048.4	1048.2	1047.7	1047.2
140°	1080.4	1080.6	1080.8	1081.1	1080.8	1080.6	1080.4	1080.2	1079.7	1079.0	1078.4
142.5°	1108.5	1108.5	1108.6	1108.6	1108.6	1108.5	1108.5	1108.4	1108.2	1107.7	1107.2
145°	1149.6	1150.1	1150.5	1151.0	1150.5	1150.1	1149.6	1149.2	1148.8	1148.6	1148.4
147.5°	1185.4	1185.6	1185.8	1186.0	1185.8	1185.6	1185.4	1185.1	1184.9	1184.7	1184.6
150°	1208.0	1208.3	1208.5	1208.7	1208.5	1208.3	1208.0	1207.8	1207.7	1207.7	1207.7
152.5°	1228.6	1228.4	1228.3	1228.2	1228.3	1228.4	1228.6	1228.7	1228.6	1228.2	1227.9
155°	1256.3	1255.7	1255.0	1254.3	1255.0	1255.7	1256.3	1257.0	1256.9	1256.0	1255.1
157.5°	1279.7	1278.5	1277.4	1276.2	1277.4	1278.5	1279.7	1280.9	1280.9	1279.7	1278.5
160°	1294.8	1293.5	1292.1	1290.8	1292.1	1293.5	1294.8	1296.2	1296.2	1294.8	1293.5
162.5°	1306.7	1305.2	1303.7	1302.1	1303.7	1305.2	1306.7	1308.3	1308.3	1307.0	1305.6
165°	1324.2	1322.2	1320.2	1318.1	1320.2	1322.2	1324.2	1326.2	1326.4	1324.6	1322.8
167.5°	1336.9	1334.6	1332.4	1330.1	1332.4	1334.6	1336.9	1339.1	1339.2	1337.3	1335.3
170°	1344.1	1341.9	1339.6	1337.4	1339.6	1341.9	1344.1	1346.4	1346.6	1344.8	1343.0
172.5°	1348.7	1346.3	1343.9	1341.4	1343.9	1346.3	1348.7	1351.2	1351.5	1349.7	1347.9
175°	1354.6	1351.9	1349.2	1346.5	1349.2	1351.9	1354.6	1357.3	1357.7	1355.6	1353.6
177.5°	1356.2	1354.1	1351.9	1349.8	1351.9	1354.1	1356.2	1358.4	1358.8	1357.3	1355.9
180°	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6



TEST NUMBER: P333023

CATALOG NUMBER: S124RDIW-S350D1050U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4
2.5°	561.8	563.2	566.2	569.6	572.5	574.9	576.8	579.5	581.9	585.3	588.5
5°	527.8	531.1	535.8	541.5	548.6	553.3	559.2	564.5	572.0	579.6	586.9
7.5°	497.9	501.5	508.5	516.3	524.7	532.5	539.5	548.7	558.7	569.8	582.1
10°	478.5	482.6	490.8	499.8	509.8	517.4	526.8	537.7	549.1	562.6	577.7
12.5°	461.1	465.0	474.9	484.1	494.4	502.8	513.8	524.8	540.0	554.6	571.8
15°	427.2	437.4	448.7	459.6	471.9	482.1	495.3	506.7	521.1	541.7	561.4
17.5°	389.5	400.3	414.5	431.3	447.8	460.4	473.8	487.9	505.1	526.1	548.8
20°	367.5	376.3	391.9	410.6	429.8	447.3	459.6	475.2	493.0	515.7	539.1
22.5°	351.1	358.5	370.7	389.4	410.1	430.4	446.2	461.6	481.2	504.0	529.5
25°	326.4	334.4	345.1	357.8	381.5	403.0	423.6	441.4	462.2	484.9	513.3
27.5°	305.8	312.8	322.6	335.9	351.8	375.5	400.5	420.7	442.1	466.5	494.9
30°	293.7	299.4	307.4	320.9	336.1	357.4	382.7	406.4	427.9	453.2	482.8
32.5°	281.0	287.1	294.9	305.6	321.9	339.8	365.1	391.0	413.9	439.8	468.8
35°	264.1	268.9	276.0	286.8	301.5	317.1	339.6	366.4	390.5	418.2	445.9
37.5°	247.0	252.6	258.2	267.9	279.9	296.7	315.1	342.5	369.2	394.5	421.5
40°	237.4	240.7	246.8	254.7	267.4	282.3	299.6	326.4	353.1	378.2	405.4
42.5°	226.6	230.3	235.5	243.3	254.7	269.3	286.2	309.3	337.2	361.5	386.3
45°	211.6	213.7	218.9	225.5	235.0	249.7	265.3	285.9	312.2	335.4	357.1
47.5°	196.4	198.3	201.5	207.6	218.2	230.0	244.6	263.1	286.1	309.3	327.7
50°	186.0	187.7	190.8	196.4	205.9	217.5	231.9	248.5	269.1	291.3	306.7
52.5°	175.6	176.5	179.4	185.8	193.8	205.2	218.1	233.4	252.6	271.1	286.7
55°	159.0	161.2	163.1	167.8	175.4	186.3	197.9	212.3	227.2	242.8	256.1
57.5°	141.8	144.1	146.8	151.0	157.0	167.1	177.5	189.2	202.0	214.9	226.1
60°	130.4	132.5	134.9	139.6	145.1	153.1	164.5	174.7	184.4	196.2	207.3
62.5°	119.2	121.4	124.1	127.9	133.1	140.8	150.3	159.1	169.2	179.5	187.8
65°	102.7	104.4	106.5	110.1	115.0	121.9	129.7	136.6	145.6	153.1	160.7
67.5°	84.6	87.8	90.5	93.4	97.6	104.0	109.7	116.3	122.4	128.0	134.9
70°	72.7	76.2	78.8	81.9	85.9	91.4	96.8	101.3	106.3	111.7	117.9
72.5°	62.6	65.4	67.5	70.7	74.4	79.4	84.5	88.2	92.3	96.0	102.0
75°	49.5	50.6	52.1	54.7	58.0	61.8	65.8	69.1	71.5	74.8	79.0
77.5°	35.5	37.8	38.8	40.6	43.0	45.3	48.0	50.8	53.1	54.2	57.5
80°	27.2	28.2	29.1	31.7	33.1	35.5	37.4	40.0	40.9	42.1	45.2
82.5°	21.2	21.7	22.3	23.0	23.9	26.2	28.1	29.8	30.7	31.1	33.5
85°	12.3	12.5	12.8	13.0	13.3	13.3	14.2	15.4	17.0	17.0	17.8
87.5°	8.9	8.8	8.5	7.9	7.9	7.6	7.3	6.8	6.9	7.0	7.0
90°	23.6	22.3	20.5	18.7	16.9	15.1	12.9	10.5	8.0	5.5	3.0
92.5°	22.8	21.5	19.7	17.9	16.1	14.3	13.3	13.2	13.0	12.9	12.8
95°	23.6	22.3	22.1	21.8	21.6	21.4	25.1	32.8	40.4	48.1	55.7
97.5°	26.9	26.7	51.9	77.0	102.1	127.3	137.4	132.7	127.9	123.1	118.3
100°	40.8	44.6	75.7	106.7	137.8	168.9	182.4	178.3	174.3	170.2	166.2
102.5°	173.5	214.8	218.8	222.9	227.0	231.0	231.5	228.6	225.6	222.6	219.7
105°	318.1	316.1	315.0	313.9	312.7	311.6	310.4	309.0	307.7	306.3	305.0
107.5°	395.1	394.1	392.6	391.1	389.5	388.0	386.9	386.2	385.5	384.9	384.2
110°	447.3	446.8	445.5	444.1	442.8	441.4	440.4	439.7	439.0	438.4	437.7



TEST NUMBER: P333023

CATALOG NUMBER: S124RDIW-S350D1050U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	497.8	497.9	497.2	496.6	496.0	495.4	494.4	493.2	492.0	490.8	489.6
115°	571.9	571.4	571.7	571.9	572.1	572.3	572.1	571.4	570.8	570.1	569.4
117.5°	647.5	647.6	647.1	646.6	646.1	645.6	644.9	644.0	643.1	642.2	641.3
120°	693.5	693.0	693.2	693.5	693.7	693.9	693.6	692.7	691.8	690.9	690.0
122.5°	739.5	739.2	738.9	738.6	738.3	738.0	737.5	737.0	736.4	735.9	735.4
125°	803.1	802.4	802.9	803.3	803.8	804.2	804.0	803.1	802.2	801.3	800.4
127.5°	867.6	867.7	866.6	865.6	864.6	863.5	862.9	862.7	862.5	862.2	862.0
130°	906.0	905.8	905.1	904.4	903.8	903.1	902.6	902.4	902.2	902.0	901.7
132.5°	944.1	943.9	943.0	942.2	941.3	940.5	939.8	939.4	939.0	938.6	938.2
135°	996.4	996.0	995.1	994.2	993.3	992.4	992.0	992.2	992.5	992.7	992.9
137.5°	1046.7	1046.2	1045.2	1044.2	1043.2	1042.2	1041.7	1041.6	1041.5	1041.4	1041.3
140°	1077.7	1077.0	1076.6	1076.1	1075.7	1075.2	1074.8	1074.3	1073.9	1073.4	1073.0
142.5°	1106.7	1106.2	1105.9	1105.6	1105.4	1105.1	1104.6	1103.8	1102.9	1102.1	1101.3
145°	1148.2	1147.9	1147.9	1147.9	1147.9	1147.9	1147.6	1146.9	1146.2	1145.6	1144.9
147.5°	1184.4	1184.2	1184.4	1184.7	1184.9	1185.1	1184.6	1183.3	1182.1	1180.8	1179.5
150°	1207.7	1207.7	1207.9	1208.2	1208.4	1208.6	1208.3	1207.4	1206.5	1205.6	1204.7
152.5°	1227.5	1227.2	1227.6	1228.0	1228.4	1228.8	1228.6	1227.9	1227.2	1226.5	1225.7
155°	1254.2	1253.3	1254.0	1254.7	1255.3	1256.0	1256.2	1256.0	1255.8	1255.6	1255.3
157.5°	1277.4	1276.2	1277.0	1277.7	1278.5	1279.3	1279.7	1279.8	1280.0	1280.1	1280.3
160°	1292.1	1290.8	1291.0	1291.2	1291.5	1291.7	1292.1	1292.8	1293.5	1294.2	1294.8
162.5°	1304.3	1302.9	1303.2	1303.4	1303.6	1303.8	1304.4	1305.2	1306.1	1307.0	1307.8
165°	1321.0	1319.2	1319.2	1319.2	1319.2	1319.2	1319.7	1320.8	1322.0	1323.1	1324.2
167.5°	1333.3	1331.3	1331.5	1331.6	1331.7	1331.9	1332.5	1333.7	1334.9	1336.0	1337.2
170°	1341.2	1339.4	1339.2	1339.0	1338.7	1338.5	1339.1	1340.4	1341.8	1343.1	1344.5
172.5°	1346.1	1344.3	1344.1	1343.8	1343.6	1343.4	1343.9	1345.3	1346.6	1348.0	1349.3
175°	1351.6	1349.6	1349.3	1349.1	1348.9	1348.7	1349.2	1350.6	1351.9	1353.3	1354.6
177.5°	1354.4	1353.0	1352.6	1352.3	1351.9	1351.6	1352.0	1353.3	1354.5	1355.8	1357.0
180°	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6



TEST NUMBER: P333023

CATALOG NUMBER: S124RDIW-S350D1050U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4
2.5°	591.0	592.7	594.6	598.2	601.2	602.6	605.2	607.1	606.5	609.2	613.7
5°	593.3	599.7	607.1	614.6	623.1	630.2	635.9	641.6	646.1	651.5	659.6
7.5°	592.9	604.3	616.7	630.2	644.2	656.3	667.4	678.8	688.9	699.9	714.4
10°	591.4	606.6	622.0	639.7	657.5	674.3	689.4	703.6	717.1	731.5	749.8
12.5°	589.7	607.1	625.7	647.1	669.2	689.4	707.2	727.7	744.6	763.2	784.2
15°	582.2	605.6	631.0	658.6	685.2	712.4	736.7	761.8	785.3	807.5	834.0
17.5°	573.6	600.6	630.5	663.2	695.0	728.1	757.1	788.7	812.6	842.5	867.1
20°	566.6	595.7	627.6	664.3	700.5	737.2	769.2	801.4	828.3	858.4	889.6
22.5°	558.1	590.0	624.6	662.6	700.5	740.6	776.0	808.0	841.4	875.2	907.4
25°	544.3	577.5	614.2	655.8	699.4	740.3	778.2	817.9	853.9	890.6	919.5
27.5°	527.5	562.3	600.9	643.9	688.6	730.5	775.1	817.5	853.7	889.0	914.2
30°	514.0	550.7	587.9	631.4	677.8	722.8	770.6	813.0	851.1	882.8	897.0
32.5°	500.2	535.0	573.3	617.4	664.9	713.3	760.7	804.1	839.3	858.3	858.7
35°	476.2	508.8	548.6	591.9	640.7	693.2	741.2	783.8	805.4	807.0	783.8
37.5°	450.0	479.9	517.4	560.8	614.2	666.5	715.5	743.9	751.1	727.0	684.2
40°	431.2	458.9	495.1	539.6	592.6	646.6	691.3	712.1	704.6	665.5	617.7
42.5°	411.5	437.3	472.2	516.1	569.3	623.9	662.0	673.1	653.1	608.0	552.0
45°	379.4	403.0	437.6	481.9	533.0	584.1	613.0	607.3	573.9	520.4	457.7
47.5°	345.9	368.8	399.9	440.8	493.2	537.3	556.8	539.7	492.2	433.4	382.4
50°	323.8	347.2	375.8	414.9	462.7	505.3	517.8	491.8	439.0	382.5	335.6
52.5°	302.0	322.0	350.1	387.8	433.5	469.5	476.2	446.2	391.7	341.0	299.4
55°	268.9	287.1	310.7	346.2	385.8	416.3	412.7	374.2	324.7	281.4	248.7
57.5°	236.8	250.5	272.4	305.7	340.4	360.9	347.9	315.0	268.9	233.4	205.9
60°	215.6	228.4	248.7	277.8	308.4	320.0	309.1	273.4	236.9	204.5	181.3
62.5°	195.5	206.8	224.3	251.3	276.0	282.9	271.2	240.0	207.2	179.5	160.3
65°	166.4	176.8	191.7	210.9	227.9	231.2	223.7	191.7	166.9	143.7	130.4
67.5°	139.9	146.7	158.4	174.9	184.0	185.9	171.3	151.2	129.3	115.1	105.1
70°	122.1	126.9	137.7	146.7	154.1	154.3	140.8	124.7	107.9	96.3	89.0
72.5°	104.9	109.4	117.7	123.8	129.5	127.6	115.3	102.6	89.0	80.2	74.8
75°	80.9	85.0	89.2	92.1	92.1	89.7	80.7	71.2	63.4	58.2	56.6
77.5°	58.8	62.1	63.6	63.1	62.3	58.6	52.9	46.7	43.9	41.5	40.2
80°	46.2	47.6	48.0	46.9	45.4	41.2	37.4	34.8	32.2	31.2	30.8
82.5°	34.2	35.5	34.2	34.6	31.4	27.9	25.8	24.9	23.9	23.5	23.0
85°	18.2	18.0	17.5	16.3	14.2	13.7	13.5	13.3	12.8	13.0	12.5
87.5°	7.4	7.3	7.0	7.3	7.8	7.7	8.3	8.6	9.0	9.1	9.7
90°	5.5	8.0	10.5	12.9	15.1	16.9	18.7	20.5	22.3	23.6	25.0
92.5°	12.9	13.0	13.2	13.3	14.3	16.1	17.9	19.7	21.5	22.8	24.2
95°	48.1	40.4	32.8	25.1	21.4	21.6	21.8	22.1	22.3	23.6	25.0
97.5°	123.1	127.9	132.7	137.4	127.3	102.1	77.0	51.9	26.7	26.9	27.0
100°	170.2	174.3	178.3	182.4	168.9	137.8	106.7	75.7	44.6	40.8	36.9
102.5°	222.6	225.6	228.6	231.5	231.0	227.0	222.9	218.8	214.8	173.5	132.2
105°	306.3	307.7	309.0	310.4	311.6	312.7	313.9	315.0	316.1	318.1	320.2
107.5°	384.9	385.5	386.2	386.9	388.0	389.5	391.1	392.6	394.1	395.1	396.1
110°	438.4	439.0	439.7	440.4	441.4	442.8	444.1	445.5	446.8	447.3	447.7



TEST NUMBER: P333023

CATALOG NUMBER: S124RDIW-S350D1050U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	490.8	492.0	493.2	494.4	495.4	496.0	496.6	497.2	497.9	497.8	497.7
115°	570.1	570.8	571.4	572.1	572.3	572.1	571.9	571.7	571.4	571.9	572.3
117.5°	642.2	643.1	644.0	644.9	645.6	646.1	646.6	647.1	647.6	647.5	647.4
120°	690.9	691.8	692.7	693.6	693.9	693.7	693.5	693.2	693.0	693.5	693.9
122.5°	735.9	736.4	737.0	737.5	738.0	738.3	738.6	738.9	739.2	739.5	739.8
125°	801.3	802.2	803.1	804.0	804.2	803.8	803.3	802.9	802.4	803.1	803.8
127.5°	862.2	862.5	862.7	862.9	863.5	864.6	865.6	866.6	867.7	867.6	867.4
130°	902.0	902.2	902.4	902.6	903.1	903.8	904.4	905.1	905.8	906.0	906.2
132.5°	938.6	939.0	939.4	939.8	940.5	941.3	942.2	943.0	943.9	944.1	944.3
135°	992.7	992.5	992.2	992.0	992.4	993.3	994.2	995.1	996.0	996.4	996.9
137.5°	1041.4	1041.5	1041.6	1041.7	1042.2	1043.2	1044.2	1045.2	1046.2	1046.7	1047.2
140°	1073.4	1073.9	1074.3	1074.8	1075.2	1075.7	1076.1	1076.6	1077.0	1077.7	1078.4
142.5°	1102.1	1102.9	1103.8	1104.6	1105.1	1105.4	1105.6	1105.9	1106.2	1106.7	1107.2
145°	1145.6	1146.2	1146.9	1147.6	1147.9	1147.9	1147.9	1147.9	1147.9	1148.2	1148.4
147.5°	1180.8	1182.1	1183.3	1184.6	1185.1	1184.9	1184.7	1184.4	1184.2	1184.4	1184.6
150°	1205.6	1206.5	1207.4	1208.3	1208.6	1208.4	1208.2	1207.9	1207.7	1207.7	1207.7
152.5°	1226.5	1227.2	1227.9	1228.6	1228.8	1228.4	1228.0	1227.6	1227.2	1227.5	1227.9
155°	1255.6	1255.8	1256.0	1256.2	1256.0	1255.3	1254.7	1254.0	1253.3	1254.2	1255.1
157.5°	1280.1	1280.0	1279.8	1279.7	1279.3	1278.5	1277.7	1277.0	1276.2	1277.4	1278.5
160°	1294.2	1293.5	1292.8	1292.1	1291.7	1291.5	1291.2	1291.0	1290.8	1292.1	1293.5
162.5°	1307.0	1306.1	1305.2	1304.4	1303.8	1303.6	1303.4	1303.2	1302.9	1304.3	1305.6
165°	1323.1	1322.0	1320.8	1319.7	1319.2	1319.2	1319.2	1319.2	1319.2	1321.0	1322.8
167.5°	1336.0	1334.9	1333.7	1332.5	1331.9	1331.7	1331.6	1331.5	1331.3	1333.3	1335.3
170°	1343.1	1341.8	1340.4	1339.1	1338.5	1338.7	1339.0	1339.2	1339.4	1341.2	1343.0
172.5°	1348.0	1346.6	1345.3	1343.9	1343.4	1343.6	1343.8	1344.1	1344.3	1346.1	1347.9
175°	1353.3	1351.9	1350.6	1349.2	1348.7	1348.9	1349.1	1349.3	1349.6	1351.6	1353.6
177.5°	1355.8	1354.5	1353.3	1352.0	1351.6	1351.9	1352.3	1352.6	1353.0	1354.4	1355.9
180°	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6



TEST NUMBER: P333023

CATALOG NUMBER: S124RDIW-S350D1050U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	587.4	587.4	587.4	587.4	587.4	587.4	587.4
2.5°	616.2	616.9	617.5	619.4	619.6	621.3	619.6
5°	667.2	670.5	675.7	680.9	681.4	684.7	678.8
7.5°	724.3	732.0	736.8	745.2	748.5	750.6	747.2
10°	763.7	770.8	783.4	789.5	795.7	796.6	793.8
12.5°	801.8	813.0	822.9	834.6	834.3	842.6	839.6
15°	852.5	864.1	877.8	890.8	895.5	895.5	899.3
17.5°	888.6	909.9	924.1	934.3	945.5	947.4	946.1
20°	913.1	936.0	951.2	964.4	972.0	974.1	974.1
22.5°	931.2	950.8	965.6	977.5	983.7	986.2	985.5
25°	943.8	960.6	969.6	973.2	974.8	974.4	969.9
27.5°	926.6	925.8	920.2	909.3	901.1	896.1	890.4
30°	893.7	881.3	867.1	851.5	831.4	816.0	811.3
32.5°	844.6	817.0	792.9	766.9	745.3	729.9	723.4
35°	749.8	706.0	670.2	639.0	616.3	602.1	597.3
37.5°	637.2	594.8	550.6	520.3	501.4	487.1	481.8
40°	565.6	519.5	480.9	452.5	433.1	419.1	418.9
42.5°	500.3	456.2	419.9	399.5	378.6	369.3	369.3
45°	409.7	374.4	343.6	327.5	315.0	307.4	305.3
47.5°	339.2	310.0	289.5	276.7	266.5	261.7	258.5
50°	299.6	274.1	257.7	246.6	240.9	234.8	234.3
52.5°	266.7	246.0	233.3	224.3	217.1	213.4	213.5
55°	224.1	207.8	198.8	191.9	186.3	183.4	182.2
57.5°	188.8	176.6	170.0	163.7	161.3	159.1	158.5
60°	166.9	158.6	152.4	147.4	143.9	143.2	142.9
62.5°	148.7	140.0	135.8	131.9	129.3	128.2	127.8
65°	122.6	116.2	112.4	109.3	108.4	106.7	106.5
67.5°	98.8	95.0	92.5	90.4	89.1	89.0	89.0
70°	84.3	82.1	80.0	78.8	78.1	77.6	77.6
72.5°	71.8	70.2	68.4	67.8	67.7	67.2	67.0
75°	54.7	53.0	53.3	52.1	51.1	49.9	49.2
77.5°	38.8	37.6	37.3	37.2	36.4	36.3	36.6
80°	30.1	28.9	28.6	28.9	28.6	27.9	27.9
82.5°	22.9	21.9	21.6	21.5	21.3	21.5	21.1
85°	12.3	11.8	11.8	11.8	12.3	12.1	11.8
87.5°	9.6	9.7	10.1	10.0	10.1	10.0	10.2
90°	26.3	27.7	28.6	29.0	29.5	29.9	30.4
92.5°	25.5	26.9	27.6	27.7	27.8	27.9	28.0
95°	26.3	27.7	28.5	28.7	28.9	29.2	29.4
97.5°	27.2	27.3	27.5	27.7	27.9	28.1	28.4
100°	33.1	29.3	27.5	27.7	27.9	28.1	28.4
102.5°	90.9	49.6	29.0	29.0	29.1	29.1	29.2
105°	322.2	324.2	321.2	313.1	305.0	296.9	288.8
107.5°	397.1	398.1	399.0	399.9	400.7	401.6	402.4
110°	448.2	448.6	449.2	449.9	450.5	451.2	451.9



TEST NUMBER: P333023

CATALOG NUMBER: S124RDIW-S350D1050U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	497.6	497.5	497.9	498.8	499.6	500.5	501.3
115°	572.8	573.2	573.5	573.5	573.5	573.5	573.5
117.5°	647.4	647.3	647.2	647.1	647.0	646.9	646.8
120°	694.4	694.8	694.8	694.4	693.9	693.5	693.0
122.5°	740.0	740.3	740.2	739.8	739.3	738.9	738.4
125°	804.5	805.1	805.6	805.8	806.0	806.3	806.5
127.5°	867.3	867.1	867.0	866.8	866.6	866.4	866.3
130°	906.5	906.7	906.8	906.8	906.8	906.8	906.8
132.5°	944.6	944.8	944.8	944.6	944.4	944.3	944.1
135°	997.3	997.8	998.2	998.7	999.1	999.6	1000.0
137.5°	1047.7	1048.2	1048.4	1048.2	1048.1	1048.0	1047.8
140°	1079.0	1079.7	1080.2	1080.4	1080.6	1080.8	1081.1
142.5°	1107.7	1108.2	1108.4	1108.5	1108.5	1108.6	1108.6
145°	1148.6	1148.8	1149.2	1149.6	1150.1	1150.5	1151.0
147.5°	1184.7	1184.9	1185.1	1185.4	1185.6	1185.8	1186.0
150°	1207.7	1207.7	1207.8	1208.0	1208.3	1208.5	1208.7
152.5°	1228.2	1228.6	1228.7	1228.6	1228.4	1228.3	1228.2
155°	1256.0	1256.9	1257.0	1256.3	1255.7	1255.0	1254.3
157.5°	1279.7	1280.9	1280.9	1279.7	1278.5	1277.4	1276.2
160°	1294.8	1296.2	1296.2	1294.8	1293.5	1292.1	1290.8
162.5°	1307.0	1308.3	1308.3	1306.7	1305.2	1303.7	1302.1
165°	1324.6	1326.4	1326.2	1324.2	1322.2	1320.2	1318.1
167.5°	1337.3	1339.2	1339.1	1336.9	1334.6	1332.4	1330.1
170°	1344.8	1346.6	1346.4	1344.1	1341.9	1339.6	1337.4
172.5°	1349.7	1351.5	1351.2	1348.7	1346.3	1343.9	1341.4
175°	1355.6	1357.7	1357.3	1354.6	1351.9	1349.2	1346.5
177.5°	1357.3	1358.8	1358.4	1356.2	1354.1	1351.9	1349.8
180°	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6

(END OF REPORT)