

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333097-927

Luminaire Tested: **S124RDIW-S1195D470U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333097-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIW-S1195D470U927-4F0-1E-UDD-F  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 470 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5303.1 lumens  
Efficiency: N/A  
Efficacy: 101.2 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 52.4  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333097-927

CATALOG NUMBER: S124RDIW-S1195D470U927-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P333097-927

CATALOG NUMBER: S124RDIW-S1195D470U927-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	107	107	107	107	96	96	96	86	86	86	76	76	76	72
1	103	99	95	91	98	94	90	87	85	82	80	76	74	72	68	67	65	61
2	94	87	81	75	89	83	77	72	75	70	66	67	64	61	60	58	56	52
3	86	77	69	63	81	73	66	61	66	61	56	60	56	52	54	51	48	45
4	79	68	60	54	75	65	58	52	59	53	48	54	49	45	48	45	41	38
5	73	61	53	47	69	58	51	45	53	47	42	48	43	39	44	40	36	34
6	67	55	47	41	64	53	45	40	48	42	37	44	39	35	40	36	32	30
7	62	50	42	36	59	48	40	35	44	37	33	40	35	31	36	32	29	26
8	58	46	38	32	55	44	36	31	40	34	29	37	31	28	34	29	26	24
9	54	42	34	29	51	40	33	28	37	31	27	34	29	25	31	27	23	22
10	51	38	31	26	48	37	30	25	34	28	24	31	26	23	29	25	21	20

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	13337	13337	13337
5°	13367	13203	13285
10°	13283	13045	13045
15°	13131	12771	12676
20°	12921	12411	12182
25°	12653	11989	11685
30°	12393	11544	11060
35°	12105	11083	10435
40°	11758	10559	9759
45°	11439	10038	9070
50°	11074	9437	8341
55°	10683	8812	7548
60°	10253	8128	6739
65°	9859	7272	5945
70°	9286	6331	5046
75°	8562	5250	4105
80°	7471	3998	3766
85°	6326	3631	3399



TEST NUMBER: P333097-927

CATALOG NUMBER: S124RDIW-S1195D470U927-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	155.2	2.9
10°-20°	432.8	8.2
20°-30°	624.9	11.8
30°-40°	708.3	13.4
40°-50°	684.0	12.9
50°-60°	568.8	10.7
60°-70°	392.8	7.4
70°-80°	199.1	3.8
80°-90°	52.5	1.0
90°-100°	16.4	0.3
100°-110°	104.7	2.0
110°-120°	200.2	3.8
120°-130°	254.2	4.8
130°-140°	272.0	5.1
140°-150°	254.3	4.8
150°-160°	205.1	3.9
160°-170°	132.3	2.5
170°-180°	45.6	0.9
0°-30°	1212.9	22.9
0°-40°	1921.2	36.2
0°-60°	3174.0	59.9
0°-90°	3818.3	72.0
90°-120°	321.3	6.1
90°-150°	1101.8	20.8
90°-180°	1485.0	28.0
0°-180°	5303.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1652	1652	1652	1652	1652	
5°	1650	1644	1629	1641	1639	156
15°	1571	1559	1528	1525	1517	442
25°	1420	1396	1346	1325	1312	654
35°	1228	1186	1125	1083	1059	767
45°	1002	953	879	819	794	772
55°	759	707	626	563	536	679
65°	516	460	381	328	311	509
75°	274	227	168	140	132	290
85°	68	44	39	37	37	77
90°	1	5	8	10	11	4
95°	20	8	8	10	10	25
105°	108	110	112	114	102	113
115°	202	203	202	203	203	199
125°	284	285	284	285	286	253
135°	352	352	353	354	354	271
145°	406	407	407	407	408	253
155°	445	445	444	445	444	205
165°	469	468	468	470	467	133
175°	480	478	478	481	477	46
180°	480	480	480	480	480	



TEST NUMBER: P333097-927

CATALOG NUMBER: S124RDIW-S1195D470U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1652.0	1652.0	1652.0	1652.0	1652.0	1652.0	1652.0	1652.0	1652.0	1652.0	1652.0
2.5°	1656.1	1655.2	1654.3	1653.4	1652.5	1650.8	1648.4	1645.8	1643.4	1640.9	1643.4
5°	1649.5	1648.4	1647.3	1646.2	1645.0	1642.7	1639.4	1636.0	1632.7	1629.3	1632.1
7.5°	1634.6	1633.4	1632.2	1631.0	1629.8	1627.1	1622.7	1618.3	1613.9	1609.6	1611.4
10°	1620.4	1619.0	1617.6	1616.2	1614.8	1611.5	1606.5	1601.5	1596.4	1591.3	1592.4
12.5°	1602.2	1600.6	1598.9	1597.3	1595.7	1591.9	1585.9	1580.0	1574.0	1568.0	1568.8
15°	1571.1	1568.5	1566.1	1563.5	1561.0	1556.2	1549.2	1542.1	1535.1	1528.0	1527.5
17.5°	1533.4	1529.7	1526.1	1522.4	1518.8	1512.8	1504.3	1495.9	1487.4	1479.0	1477.4
20°	1504.0	1500.4	1496.7	1493.1	1489.5	1482.8	1473.3	1463.7	1454.1	1444.6	1442.3
22.5°	1471.6	1467.6	1463.5	1459.4	1455.2	1448.1	1437.8	1427.6	1417.4	1407.2	1403.7
25°	1420.5	1415.5	1410.4	1405.4	1400.3	1392.0	1380.5	1369.0	1357.5	1345.9	1341.2
27.5°	1366.9	1360.6	1354.2	1347.9	1341.5	1332.2	1319.9	1307.6	1295.2	1282.9	1277.0
30°	1329.5	1322.5	1315.4	1308.4	1301.4	1291.3	1278.0	1264.8	1251.6	1238.4	1231.4
32.5°	1290.0	1282.1	1274.1	1266.2	1258.3	1247.5	1233.8	1220.2	1206.5	1192.9	1184.7
35°	1228.3	1219.2	1210.3	1201.3	1192.3	1180.7	1166.7	1152.7	1138.6	1124.6	1115.0
37.5°	1162.3	1152.9	1143.7	1134.4	1125.1	1112.7	1097.2	1081.6	1066.0	1050.4	1039.7
40°	1115.7	1106.4	1097.2	1087.9	1078.6	1066.0	1050.0	1033.9	1017.9	1001.9	990.1
42.5°	1071.2	1061.4	1051.7	1042.0	1032.3	1019.1	1002.3	985.6	969.0	952.3	940.2
45°	1001.9	991.4	981.0	970.7	960.3	946.6	929.8	912.9	896.0	879.2	865.4
47.5°	930.3	919.5	908.8	898.0	887.3	873.1	855.6	838.0	820.5	803.0	788.7
50°	881.7	870.7	859.8	848.8	837.8	823.3	805.3	787.3	769.4	751.4	737.4
52.5°	832.1	821.3	810.6	799.9	789.2	774.5	756.1	737.7	719.2	700.8	686.5
55°	759.0	747.7	736.5	725.2	714.0	699.3	681.0	662.7	644.4	626.1	611.6
57.5°	686.6	674.9	663.2	651.6	639.8	625.0	607.0	589.0	571.0	553.0	538.2
60°	635.0	623.8	612.5	601.3	590.0	575.4	557.5	539.5	521.4	503.4	488.9
62.5°	588.4	576.8	565.1	553.4	541.7	526.6	508.2	489.7	471.3	452.9	439.3
65°	516.1	504.0	491.9	479.8	467.8	452.7	434.7	416.8	398.8	380.7	368.7
67.5°	440.9	429.4	417.8	406.2	394.7	380.5	363.8	347.1	330.4	313.7	303.3
70°	393.4	381.6	369.8	358.0	346.2	332.2	316.2	300.2	284.2	268.2	258.9
72.5°	342.8	332.2	321.5	310.8	300.1	287.2	272.0	256.9	241.8	226.6	218.7
75°	274.5	264.1	253.7	243.3	232.9	221.1	207.9	194.6	181.5	168.3	161.8
77.5°	205.2	196.4	187.5	178.7	169.8	160.1	149.4	138.8	128.1	117.4	113.6
80°	160.7	152.5	144.3	136.2	128.0	119.8	111.3	102.9	94.4	86.0	85.2
82.5°	122.2	114.7	107.3	99.7	92.3	86.1	81.3	76.4	71.6	66.8	66.1
85°	68.3	62.7	57.0	51.4	45.8	42.6	41.7	40.9	40.1	39.2	38.7
87.5°	23.5	21.9	20.3	18.6	17.0	16.2	16.0	15.9	15.8	15.8	15.6
90°	1.1	2.0	2.9	3.7	4.6	5.3	6.0	6.7	7.3	7.9	8.4
92.5°	4.5	4.6	4.6	4.7	4.8	5.1	5.7	6.3	7.0	7.6	8.1
95°	19.7	17.0	14.3	11.6	8.9	7.6	7.7	7.8	7.8	7.9	8.4
97.5°	41.9	43.6	45.3	47.0	48.7	45.1	36.2	27.3	18.4	9.5	9.5
100°	58.9	60.3	61.8	63.2	64.6	59.8	48.8	37.8	26.8	15.8	14.4
102.5°	77.9	78.9	79.9	81.0	82.1	81.8	80.4	79.0	77.6	76.1	61.5
105°	108.1	108.5	109.0	109.5	110.0	110.4	110.8	111.2	111.6	112.0	112.7
107.5°	136.2	136.4	136.7	136.9	137.1	137.5	138.0	138.6	139.1	139.7	140.0
110°	155.1	155.3	155.6	155.8	156.1	156.4	156.9	157.4	157.9	158.4	158.5



TEST NUMBER: P333097-927

CATALOG NUMBER: S124RDIW-S1195D470U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	173.5	173.9	174.4	174.8	175.2	175.5	175.8	175.9	176.2	176.4	176.4
115°	201.8	202.0	202.2	202.5	202.7	202.8	202.7	202.6	202.6	202.5	202.6
117.5°	227.3	227.6	227.9	228.2	228.5	228.8	228.9	229.1	229.3	229.5	229.4
120°	244.5	244.8	245.1	245.4	245.7	245.9	245.8	245.7	245.7	245.6	245.7
122.5°	260.5	260.8	260.9	261.2	261.3	261.5	261.6	261.7	261.8	262.0	262.1
125°	283.6	283.9	284.2	284.6	284.9	284.9	284.8	284.6	284.5	284.3	284.6
127.5°	305.5	305.5	305.6	305.7	305.8	306.0	306.3	306.7	307.1	307.4	307.4
130°	319.5	319.6	319.7	319.8	319.9	320.0	320.3	320.5	320.8	321.0	321.1
132.5°	332.5	332.6	332.7	332.9	333.0	333.3	333.6	333.8	334.1	334.5	334.5
135°	351.8	351.7	351.6	351.6	351.5	351.6	352.0	352.3	352.6	352.9	353.1
137.5°	369.0	369.0	369.1	369.1	369.2	369.3	369.6	370.0	370.3	370.7	370.9
140°	380.2	380.3	380.5	380.6	380.8	381.0	381.1	381.4	381.5	381.7	381.9
142.5°	390.2	390.5	390.9	391.1	391.4	391.6	391.7	391.8	391.9	392.0	392.1
145°	405.7	405.9	406.2	406.4	406.6	406.8	406.8	406.8	406.8	406.8	406.9
147.5°	418.0	418.4	418.8	419.3	419.8	419.9	419.9	419.8	419.7	419.6	419.7
150°	426.9	427.2	427.5	427.9	428.2	428.3	428.2	428.1	428.0	427.9	427.9
152.5°	434.4	434.6	434.8	435.1	435.4	435.4	435.3	435.1	435.0	434.8	435.0
155°	444.8	444.9	445.0	445.0	445.1	445.0	444.8	444.6	444.3	444.1	444.4
157.5°	453.7	453.6	453.5	453.5	453.4	453.3	453.0	452.7	452.5	452.3	452.7
160°	458.8	458.6	458.4	458.1	457.9	457.7	457.6	457.6	457.5	457.4	457.9
162.5°	463.4	463.1	462.8	462.5	462.2	462.0	461.9	461.8	461.8	461.7	462.2
165°	469.2	468.8	468.4	468.0	467.6	467.5	467.5	467.5	467.5	467.5	468.1
167.5°	473.8	473.4	473.0	472.6	472.1	471.9	471.9	471.8	471.8	471.7	472.5
170°	476.4	475.9	475.5	475.0	474.5	474.3	474.4	474.4	474.5	474.6	475.2
172.5°	478.2	477.7	477.2	476.7	476.3	476.0	476.1	476.2	476.3	476.3	477.0
175°	480.0	479.5	479.0	478.6	478.1	477.9	478.0	478.1	478.2	478.2	479.0
177.5°	480.9	480.5	480.0	479.5	479.1	479.0	479.0	479.2	479.3	479.4	479.9
180°	480.0	480.0	480.0	480.0	480.0	480.0	480.0	480.0	480.0	480.0	480.0



TEST NUMBER: P333097-927

CATALOG NUMBER: S124RDIW-S1195D470U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1652.0	1652.0	1652.0	1652.0	1652.0	1652.0	1652.0	1652.0
2.5°	1645.8	1648.4	1650.8	1651.9	1651.7	1651.5	1651.2	1651.1
5°	1634.9	1637.7	1640.5	1641.6	1641.1	1640.5	1640.0	1639.4
7.5°	1613.1	1614.9	1616.8	1617.2	1616.3	1615.4	1614.5	1613.6
10°	1593.6	1594.7	1595.9	1595.9	1594.7	1593.6	1592.4	1591.3
12.5°	1569.4	1570.1	1570.7	1570.3	1568.8	1567.2	1565.6	1564.0
15°	1526.9	1526.4	1525.8	1524.6	1522.6	1520.6	1518.7	1516.7
17.5°	1475.8	1474.3	1472.7	1470.4	1467.4	1464.4	1461.5	1458.5
20°	1440.1	1437.8	1435.6	1432.7	1429.0	1425.4	1421.7	1418.0
22.5°	1400.4	1397.0	1393.7	1390.5	1387.5	1384.5	1381.6	1378.6
25°	1336.3	1331.6	1326.8	1323.0	1320.2	1317.4	1314.5	1311.8
27.5°	1271.1	1265.2	1259.3	1254.3	1250.3	1246.3	1242.2	1238.2
30°	1224.3	1217.3	1210.3	1204.5	1200.0	1195.6	1191.0	1186.5
32.5°	1176.5	1168.4	1160.2	1154.1	1149.8	1145.5	1141.2	1136.9
35°	1105.4	1095.9	1086.3	1079.0	1074.0	1068.9	1063.8	1058.8
37.5°	1029.0	1018.4	1007.7	999.8	994.7	989.7	984.7	979.6
40°	978.3	966.5	954.7	946.2	941.1	936.0	931.1	926.0
42.5°	928.2	916.2	904.1	895.5	890.2	884.9	879.6	874.3
45°	851.6	837.8	824.0	814.6	809.6	804.5	799.5	794.4
47.5°	774.4	760.2	745.9	735.9	730.4	724.8	719.2	713.7
50°	723.3	709.2	695.1	685.5	680.2	674.8	669.5	664.1
52.5°	672.2	658.0	643.6	633.7	628.2	622.7	617.0	611.5
55°	596.9	582.3	567.7	557.7	552.4	547.0	541.7	536.3
57.5°	523.4	508.5	493.7	484.3	480.2	476.1	472.1	468.0
60°	474.2	459.6	445.0	435.5	430.9	426.4	421.9	417.4
62.5°	425.9	412.4	398.9	390.3	386.7	383.2	379.5	376.0
65°	356.6	344.5	332.4	324.6	321.3	317.9	314.6	311.2
67.5°	292.9	282.5	272.1	265.1	261.3	257.6	253.9	250.2
70°	249.6	240.3	231.1	225.1	222.2	219.4	216.6	213.8
72.5°	210.8	202.9	195.0	189.7	187.1	184.6	182.0	179.4
75°	155.3	148.9	142.4	138.3	136.7	134.9	133.2	131.6
77.5°	109.9	106.1	102.3	100.2	99.7	99.2	98.7	98.2
80°	84.4	83.5	82.6	82.1	81.8	81.5	81.3	81.0
82.5°	65.6	65.0	64.3	63.8	63.6	63.3	63.1	62.7
85°	38.1	37.5	37.0	36.7	36.7	36.7	36.7	36.7
87.5°	15.5	15.4	15.2	15.3	15.5	15.8	16.1	16.3
90°	8.9	9.3	9.8	10.1	10.3	10.5	10.6	10.8
92.5°	8.6	9.0	9.5	9.7	9.8	9.8	9.9	9.9
95°	8.9	9.3	9.8	10.1	10.1	10.2	10.3	10.4
97.5°	9.6	9.6	9.7	9.7	9.8	9.9	10.0	10.1
100°	13.1	11.7	10.4	9.7	9.8	9.9	10.0	10.1
102.5°	46.8	32.2	17.6	10.3	10.3	10.3	10.3	10.4
105°	113.4	114.2	114.9	113.8	110.9	108.1	105.2	102.3
107.5°	140.4	140.7	141.1	141.4	141.7	142.0	142.3	142.6
110°	158.7	158.8	159.0	159.1	159.4	159.6	159.9	160.1





TEST NUMBER: P333097-927

CATALOG NUMBER: S124RDIW-S1195D470U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	176.3	176.3	176.3	176.4	176.7	177.1	177.4	177.6
115°	202.8	203.0	203.1	203.2	203.2	203.2	203.2	203.2
117.5°	229.4	229.4	229.3	229.3	229.3	229.3	229.3	229.2
120°	245.9	246.1	246.2	246.2	246.1	245.9	245.7	245.6
122.5°	262.1	262.2	262.3	262.3	262.1	262.0	261.8	261.7
125°	284.8	285.0	285.3	285.4	285.5	285.6	285.7	285.7
127.5°	307.4	307.3	307.3	307.2	307.1	307.0	307.0	307.0
130°	321.2	321.2	321.3	321.3	321.3	321.3	321.3	321.3
132.5°	334.6	334.7	334.8	334.8	334.7	334.7	334.6	334.5
135°	353.2	353.4	353.6	353.7	353.9	354.0	354.2	354.3
137.5°	371.1	371.2	371.5	371.5	371.5	371.4	371.4	371.3
140°	382.1	382.4	382.6	382.8	382.9	382.9	383.0	383.1
142.5°	392.3	392.5	392.7	392.8	392.8	392.8	392.8	392.8
145°	406.9	407.0	407.1	407.2	407.3	407.5	407.7	407.8
147.5°	419.8	419.8	419.9	419.9	420.0	420.1	420.2	420.3
150°	427.9	427.9	427.9	428.0	428.1	428.2	428.3	428.3
152.5°	435.1	435.2	435.4	435.4	435.4	435.3	435.2	435.2
155°	444.7	445.0	445.4	445.4	445.2	445.0	444.7	444.5
157.5°	453.0	453.4	453.8	453.8	453.4	453.0	452.7	452.3
160°	458.4	458.8	459.3	459.3	458.8	458.4	457.9	457.4
162.5°	462.6	463.1	463.6	463.6	463.0	462.5	461.9	461.4
165°	468.7	469.4	470.0	469.9	469.2	468.5	467.8	467.1
167.5°	473.2	473.9	474.6	474.5	473.7	472.9	472.1	471.3
170°	475.9	476.5	477.2	477.1	476.3	475.5	474.7	473.9
172.5°	477.6	478.2	478.9	478.8	477.9	477.1	476.2	475.3
175°	479.7	480.4	481.1	480.9	480.0	479.0	478.1	477.1
177.5°	480.5	480.9	481.5	481.3	480.6	479.8	479.0	478.3
180°	480.0	480.0	480.0	480.0	480.0	480.0	480.0	480.0

(END OF REPORT)