

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333098-927

Luminaire Tested: **S124RDIW-S1195D470U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333098-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S1195D470U927-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 470 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5106.0 lumens
Efficiency: N/A
Efficacy: 97.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 52.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333098-927

CATALOG NUMBER: S124RDIW-S1195D470U927-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333098-927

CATALOG NUMBER: S124RDIW-S1195D470U927-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	113	113	113	113	107	107	107	107	97	97	97	88	88	88	79	79	79	75
1	104	99	96	92	99	95	91	88	86	83	81	78	76	74	70	69	68	64
2	95	87	81	76	90	83	78	73	76	71	68	69	65	62	62	60	57	54
3	87	77	70	64	82	74	67	62	67	62	57	61	57	53	56	52	49	46
4	80	69	61	54	76	66	58	53	60	54	49	55	50	46	50	46	43	40
5	73	61	53	47	70	59	51	46	54	48	43	49	44	40	45	41	38	35
6	68	55	47	41	64	53	46	40	49	43	38	45	40	35	41	37	33	31
7	63	50	42	36	60	48	41	35	45	38	34	41	36	32	38	33	30	27
8	59	46	38	33	56	44	37	32	41	35	30	38	32	28	35	30	27	25
9	55	42	34	29	52	41	33	29	38	31	27	35	29	26	32	28	24	22
10	51	39	31	26	49	37	31	26	35	29	25	32	27	23	30	25	22	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13337	13337	13337
5°	13367	13203	13285
10°	13283	13045	13045
15°	13131	12771	12676
20°	12921	12411	12182
25°	12653	11989	11685
30°	12393	11544	11060
35°	12105	11083	10435
40°	11758	10559	9759
45°	11439	10038	9070
50°	11074	9437	8341
55°	10683	8812	7548
60°	10253	8128	6739
65°	9859	7272	5945
70°	9286	6331	5046
75°	8562	5250	4105
80°	7471	3998	3766
85°	6326	3631	3399



TEST NUMBER: P333098-927

CATALOG NUMBER: S124RDIW-S1195D470U927-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	155.2	3.0
10°-20°	432.8	8.5
20°-30°	624.9	12.2
30°-40°	708.3	13.9
40°-50°	684.0	13.4
50°-60°	568.8	11.1
60°-70°	392.8	7.7
70°-80°	199.1	3.9
80°-90°	52.5	1.0
90°-100°	30.6	0.6
100°-110°	90.7	1.8
110°-120°	153.9	3.0
120°-130°	203.0	4.0
130°-140°	227.9	4.5
140°-150°	224.0	4.4
150°-160°	188.4	3.7
160°-170°	125.3	2.5
170°-180°	43.9	0.9
0°-30°	1212.9	23.8
0°-40°	1921.2	37.6
0°-60°	3174.0	62.2
0°-90°	3818.3	74.8
90°-120°	275.2	5.4
90°-150°	930.1	18.2
90°-180°	1288.0	25.2
0°-180°	5106.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1652	1652	1652	1652	1652	
5°	1650	1644	1629	1641	1639	156
15°	1571	1559	1528	1525	1517	442
25°	1420	1396	1346	1325	1312	654
35°	1228	1186	1125	1083	1059	767
45°	1002	953	879	819	794	772
55°	759	707	626	563	536	679
65°	516	460	381	328	311	509
75°	274	227	168	140	132	290
85°	68	44	39	37	37	77
90°	1	5	8	10	11	5
95°	22	25	27	28	28	24
105°	84	84	85	87	88	89
115°	156	156	156	155	155	154
125°	228	228	228	227	226	203
135°	294	296	296	295	294	227
145°	357	359	359	359	358	223
155°	409	409	409	410	409	188
165°	445	444	444	446	444	126
175°	463	462	461	464	461	44
180°	464	464	464	464	464	



TEST NUMBER: P333098-927

CATALOG NUMBER: S124RDIW-S1195D470U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1652.0	1652.0	1652.0	1652.0	1652.0	1652.0	1652.0	1652.0	1652.0	1652.0	1652.0
2.5°	1656.1	1655.2	1654.3	1653.4	1652.5	1650.8	1648.4	1645.8	1643.4	1640.9	1643.4
5°	1649.5	1648.4	1647.3	1646.2	1645.0	1642.7	1639.4	1636.0	1632.7	1629.3	1632.1
7.5°	1634.6	1633.4	1632.2	1631.0	1629.8	1627.1	1622.7	1618.3	1613.9	1609.6	1611.4
10°	1620.4	1619.0	1617.6	1616.2	1614.8	1611.5	1606.5	1601.5	1596.4	1591.3	1592.4
12.5°	1602.2	1600.6	1598.9	1597.3	1595.7	1591.9	1585.9	1580.0	1574.0	1568.0	1568.8
15°	1571.1	1568.5	1566.1	1563.5	1561.0	1556.2	1549.2	1542.1	1535.1	1528.0	1527.5
17.5°	1533.4	1529.7	1526.1	1522.4	1518.8	1512.8	1504.3	1495.9	1487.4	1479.0	1477.4
20°	1504.0	1500.4	1496.7	1493.1	1489.5	1482.8	1473.3	1463.7	1454.1	1444.6	1442.3
22.5°	1471.6	1467.6	1463.5	1459.4	1455.2	1448.1	1437.8	1427.6	1417.4	1407.2	1403.7
25°	1420.5	1415.5	1410.4	1405.4	1400.3	1392.0	1380.5	1369.0	1357.5	1345.9	1341.2
27.5°	1366.9	1360.6	1354.2	1347.9	1341.5	1332.2	1319.9	1307.6	1295.2	1282.9	1277.0
30°	1329.5	1322.5	1315.4	1308.4	1301.4	1291.3	1278.0	1264.8	1251.6	1238.4	1231.4
32.5°	1290.0	1282.1	1274.1	1266.2	1258.3	1247.5	1233.8	1220.2	1206.5	1192.9	1184.7
35°	1228.3	1219.2	1210.3	1201.3	1192.3	1180.7	1166.7	1152.7	1138.6	1124.6	1115.0
37.5°	1162.3	1152.9	1143.7	1134.4	1125.1	1112.7	1097.2	1081.6	1066.0	1050.4	1039.7
40°	1115.7	1106.4	1097.2	1087.9	1078.6	1066.0	1050.0	1033.9	1017.9	1001.9	990.1
42.5°	1071.2	1061.4	1051.7	1042.0	1032.3	1019.1	1002.3	985.6	969.0	952.3	940.2
45°	1001.9	991.4	981.0	970.7	960.3	946.6	929.8	912.9	896.0	879.2	865.4
47.5°	930.3	919.5	908.8	898.0	887.3	873.1	855.6	838.0	820.5	803.0	788.7
50°	881.7	870.7	859.8	848.8	837.8	823.3	805.3	787.3	769.4	751.4	737.4
52.5°	832.1	821.3	810.6	799.9	789.2	774.5	756.1	737.7	719.2	700.8	686.5
55°	759.0	747.7	736.5	725.2	714.0	699.3	681.0	662.7	644.4	626.1	611.6
57.5°	686.6	674.9	663.2	651.6	639.8	625.0	607.0	589.0	571.0	553.0	538.2
60°	635.0	623.8	612.5	601.3	590.0	575.4	557.5	539.5	521.4	503.4	488.9
62.5°	588.4	576.8	565.1	553.4	541.7	526.6	508.2	489.7	471.3	452.9	439.3
65°	516.1	504.0	491.9	479.8	467.8	452.7	434.7	416.8	398.8	380.7	368.7
67.5°	440.9	429.4	417.8	406.2	394.7	380.5	363.8	347.1	330.4	313.7	303.3
70°	393.4	381.6	369.8	358.0	346.2	332.2	316.2	300.2	284.2	268.2	258.9
72.5°	342.8	332.2	321.5	310.8	300.1	287.2	272.0	256.9	241.8	226.6	218.7
75°	274.5	264.1	253.7	243.3	232.9	221.1	207.9	194.6	181.5	168.3	161.8
77.5°	205.2	196.4	187.5	178.7	169.8	160.1	149.4	138.8	128.1	117.4	113.6
80°	160.7	152.5	144.3	136.2	128.0	119.8	111.3	102.9	94.4	86.0	85.2
82.5°	122.2	114.7	107.3	99.7	92.3	86.1	81.3	76.4	71.6	66.8	66.1
85°	68.3	62.7	57.0	51.4	45.8	42.6	41.7	40.9	40.1	39.2	38.7
87.5°	23.5	21.9	20.3	18.6	17.0	16.2	16.0	15.9	15.8	15.8	15.6
90°	1.1	2.0	2.9	3.7	4.6	5.3	6.0	6.7	7.3	7.9	8.4
92.5°	7.7	8.7	9.7	10.7	11.7	12.4	12.9	13.3	13.8	14.2	14.5
95°	21.5	22.3	23.0	23.7	24.4	25.0	25.6	26.1	26.7	27.3	27.5
97.5°	37.6	38.2	38.7	39.4	39.9	40.6	41.2	41.8	42.5	43.2	43.4
100°	50.2	50.5	50.9	51.2	51.6	52.0	52.8	53.5	54.2	54.9	55.1
102.5°	63.5	63.6	63.7	63.8	64.0	64.4	65.0	65.7	66.3	67.0	67.2
105°	83.7	83.7	83.8	83.9	84.0	84.1	84.4	84.8	85.1	85.4	85.6
107.5°	104.8	104.9	105.0	105.1	105.2	105.3	105.4	105.4	105.4	105.4	105.7
110°	119.1	119.3	119.5	119.6	119.8	119.9	119.8	119.7	119.6	119.5	119.4



TEST NUMBER: P333098-927

CATALOG NUMBER: S124RDIW-S1195D470U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	134.1	134.1	134.2	134.2	134.3	134.2	134.0	133.9	133.7	133.6	133.6
115°	156.5	156.5	156.5	156.5	156.5	156.5	156.3	156.1	156.0	155.8	155.7
117.5°	177.6	177.7	177.8	177.8	177.8	177.8	177.8	177.6	177.5	177.4	177.1
120°	191.7	192.0	192.3	192.7	193.0	193.0	192.7	192.5	192.3	192.0	191.6
122.5°	206.4	206.4	206.6	206.7	206.8	206.8	206.8	206.6	206.5	206.4	206.1
125°	227.9	227.9	227.9	227.9	227.9	227.9	227.8	227.8	227.7	227.6	227.4
127.5°	247.6	247.8	248.0	248.3	248.5	248.6	248.4	248.3	248.2	248.0	247.9
130°	261.3	261.6	261.8	262.1	262.3	262.4	262.4	262.4	262.4	262.4	262.2
132.5°	275.4	275.6	275.8	275.9	276.1	276.2	276.1	276.0	276.0	275.9	275.8
135°	294.0	294.5	294.9	295.4	295.9	296.1	296.1	296.1	296.1	296.1	296.0
137.5°	314.3	314.5	314.7	314.9	315.1	315.3	315.4	315.6	315.7	315.8	315.6
140°	327.7	327.9	328.0	328.2	328.4	328.4	328.4	328.4	328.4	328.4	328.4
142.5°	340.1	340.2	340.4	340.6	340.7	340.8	340.7	340.6	340.6	340.5	340.5
145°	357.2	357.5	357.8	358.1	358.5	358.6	358.7	358.8	358.9	358.9	358.9
147.5°	374.1	374.5	374.9	375.3	375.7	375.8	375.7	375.7	375.7	375.6	375.5
150°	384.4	384.8	385.1	385.4	385.7	385.9	385.9	385.9	385.9	385.9	385.9
152.5°	394.2	394.4	394.6	394.8	395.0	395.1	395.1	395.2	395.3	395.4	395.5
155°	409.2	409.2	409.2	409.2	409.2	409.2	409.1	409.0	408.9	408.8	409.2
157.5°	421.8	421.7	421.6	421.4	421.3	421.2	421.2	421.2	421.1	421.1	421.4
160°	429.4	429.3	429.2	429.1	429.0	429.0	428.9	428.8	428.7	428.6	428.9
162.5°	436.3	436.0	435.8	435.6	435.4	435.2	435.1	435.1	435.0	434.9	435.4
165°	445.4	445.2	445.0	444.7	444.5	444.3	444.2	444.0	443.9	443.7	444.2
167.5°	452.6	452.3	451.9	451.6	451.2	451.1	451.1	451.1	451.1	451.1	451.6
170°	456.6	456.2	455.8	455.4	455.0	454.9	455.0	455.0	455.1	455.2	455.7
172.5°	459.5	459.1	458.8	458.5	458.1	458.0	458.0	458.0	458.0	458.0	458.6
175°	463.4	463.0	462.6	462.2	461.8	461.6	461.5	461.4	461.4	461.3	461.8
177.5°	464.7	464.4	464.1	463.7	463.4	463.3	463.3	463.3	463.3	463.3	463.7
180°	464.1	464.1	464.1	464.1	464.1	464.1	464.1	464.1	464.1	464.1	464.1



TEST NUMBER: P333098-927

CATALOG NUMBER: S124RDIW-S1195D470U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1652.0	1652.0	1652.0	1652.0	1652.0	1652.0	1652.0	1652.0
2.5°	1645.8	1648.4	1650.8	1651.9	1651.7	1651.5	1651.2	1651.1
5°	1634.9	1637.7	1640.5	1641.6	1641.1	1640.5	1640.0	1639.4
7.5°	1613.1	1614.9	1616.8	1617.2	1616.3	1615.4	1614.5	1613.6
10°	1593.6	1594.7	1595.9	1595.9	1594.7	1593.6	1592.4	1591.3
12.5°	1569.4	1570.1	1570.7	1570.3	1568.8	1567.2	1565.6	1564.0
15°	1526.9	1526.4	1525.8	1524.6	1522.6	1520.6	1518.7	1516.7
17.5°	1475.8	1474.3	1472.7	1470.4	1467.4	1464.4	1461.5	1458.5
20°	1440.1	1437.8	1435.6	1432.7	1429.0	1425.4	1421.7	1418.0
22.5°	1400.4	1397.0	1393.7	1390.5	1387.5	1384.5	1381.6	1378.6
25°	1336.3	1331.6	1326.8	1323.0	1320.2	1317.4	1314.5	1311.8
27.5°	1271.1	1265.2	1259.3	1254.3	1250.3	1246.3	1242.2	1238.2
30°	1224.3	1217.3	1210.3	1204.5	1200.0	1195.6	1191.0	1186.5
32.5°	1176.5	1168.4	1160.2	1154.1	1149.8	1145.5	1141.2	1136.9
35°	1105.4	1095.9	1086.3	1079.0	1074.0	1068.9	1063.8	1058.8
37.5°	1029.0	1018.4	1007.7	999.8	994.7	989.7	984.7	979.6
40°	978.3	966.5	954.7	946.2	941.1	936.0	931.1	926.0
42.5°	928.2	916.2	904.1	895.5	890.2	884.9	879.6	874.3
45°	851.6	837.8	824.0	814.6	809.6	804.5	799.5	794.4
47.5°	774.4	760.2	745.9	735.9	730.4	724.8	719.2	713.7
50°	723.3	709.2	695.1	685.5	680.2	674.8	669.5	664.1
52.5°	672.2	658.0	643.6	633.7	628.2	622.7	617.0	611.5
55°	596.9	582.3	567.7	557.7	552.4	547.0	541.7	536.3
57.5°	523.4	508.5	493.7	484.3	480.2	476.1	472.1	468.0
60°	474.2	459.6	445.0	435.5	430.9	426.4	421.9	417.4
62.5°	425.9	412.4	398.9	390.3	386.7	383.2	379.5	376.0
65°	356.6	344.5	332.4	324.6	321.3	317.9	314.6	311.2
67.5°	292.9	282.5	272.1	265.1	261.3	257.6	253.9	250.2
70°	249.6	240.3	231.1	225.1	222.2	219.4	216.6	213.8
72.5°	210.8	202.9	195.0	189.7	187.1	184.6	182.0	179.4
75°	155.3	148.9	142.4	138.3	136.7	134.9	133.2	131.6
77.5°	109.9	106.1	102.3	100.2	99.7	99.2	98.7	98.2
80°	84.4	83.5	82.6	82.1	81.8	81.5	81.3	81.0
82.5°	65.6	65.0	64.3	63.8	63.6	63.3	63.1	62.7
85°	38.1	37.5	37.0	36.7	36.7	36.7	36.7	36.7
87.5°	15.5	15.4	15.2	15.3	15.5	15.8	16.1	16.3
90°	8.9	9.3	9.8	10.1	10.3	10.5	10.6	10.8
92.5°	14.8	15.1	15.4	15.5	15.7	15.8	15.8	15.9
95°	27.7	28.0	28.2	28.4	28.4	28.4	28.4	28.4
97.5°	43.7	44.0	44.3	44.4	44.4	44.4	44.4	44.4
100°	55.2	55.4	55.5	55.6	55.6	55.6	55.6	55.6
102.5°	67.4	67.7	67.9	68.0	68.0	68.1	68.2	68.3
105°	86.0	86.2	86.4	86.7	86.9	87.1	87.4	87.6
107.5°	105.9	106.2	106.4	106.5	106.5	106.5	106.4	106.4
110°	119.2	119.1	118.9	118.9	119.1	119.4	119.6	119.9



TEST NUMBER: P333098-927

CATALOG NUMBER: S124RDIW-S1195D470U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	133.6	133.5	133.5	133.5	133.6	133.6	133.6	133.6
115°	155.7	155.6	155.5	155.4	155.3	155.3	155.2	155.1
117.5°	176.9	176.6	176.3	176.1	175.9	175.8	175.6	175.5
120°	191.2	190.8	190.4	190.4	190.5	190.7	190.8	191.0
122.5°	205.9	205.6	205.3	205.0	204.8	204.5	204.1	203.9
125°	227.3	227.1	227.0	226.8	226.6	226.5	226.3	226.2
127.5°	247.7	247.6	247.4	247.2	247.2	247.0	246.9	246.8
130°	262.1	261.9	261.7	261.5	261.2	260.9	260.5	260.2
132.5°	275.6	275.4	275.3	275.1	275.0	274.9	274.7	274.6
135°	295.8	295.6	295.5	295.3	295.1	294.9	294.6	294.4
137.5°	315.4	315.2	315.0	314.9	315.0	315.0	315.1	315.1
140°	328.3	328.2	328.1	328.0	328.0	327.9	327.8	327.7
142.5°	340.5	340.5	340.5	340.4	340.4	340.4	340.4	340.4
145°	358.8	358.7	358.6	358.5	358.2	358.0	357.7	357.5
147.5°	375.4	375.3	375.3	375.3	375.2	375.1	375.0	374.9
150°	385.9	385.9	385.9	385.9	385.8	385.7	385.6	385.6
152.5°	395.8	395.9	396.2	396.1	395.9	395.7	395.5	395.3
155°	409.5	409.8	410.1	410.1	409.8	409.5	409.2	408.8
157.5°	421.6	421.8	422.1	422.1	421.8	421.5	421.3	421.0
160°	429.1	429.4	429.6	429.5	429.1	428.7	428.3	427.9
162.5°	435.8	436.3	436.7	436.7	436.3	435.9	435.5	435.1
165°	444.7	445.1	445.6	445.7	445.4	445.0	444.7	444.4
167.5°	452.1	452.6	453.0	453.0	452.6	452.1	451.5	451.1
170°	456.1	456.6	457.1	457.0	456.5	455.9	455.3	454.8
172.5°	459.1	459.7	460.2	460.2	459.6	459.1	458.5	458.0
175°	462.4	463.0	463.5	463.5	463.0	462.4	461.8	461.3
177.5°	464.2	464.6	465.1	465.0	464.5	464.1	463.5	463.0
180°	464.1	464.1	464.1	464.1	464.1	464.1	464.1	464.1

(END OF REPORT)