

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333028

Luminaire Tested: **S124RDIW-S350D1340U835-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333028
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S350D1340U835-4F0-1E-UDD-A1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6142.2 lumens
Efficiency: N/A
Efficacy: 131.8 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 46.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333028

CATALOG NUMBER: S124RDIW-S350D1340U835-4F0-1E-UDD-A1

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - · - 90°-270° - · - 135°-315°



TEST NUMBER: P333028

CATALOG NUMBER: S124RDIW-S350D1340U835-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	32	32	32	24				24
1	92	88	84	81	82	79	76	73	61	59	57	44	43	42	29	28	28	21				21
2	84	77	71	67	75	69	64	60	53	50	47	39	37	35	26	25	24	18				18
3	77	68	61	56	68	61	55	50	47	43	40	35	32	30	23	22	20	15				15
4	70	60	53	47	62	54	48	43	42	38	34	31	28	26	21	19	18	13				13
5	64	53	46	40	57	48	41	37	37	33	29	28	25	22	19	17	15	12				12
6	59	48	40	35	53	43	36	32	34	29	26	25	22	20	17	15	14	10				10
7	55	43	36	30	49	39	32	28	30	26	22	23	20	17	15	14	12	9				9
8	51	39	32	27	45	35	29	24	28	23	20	21	18	15	14	12	11	8				8
9	47	35	28	24	42	32	26	22	25	21	18	19	16	14	13	11	10	8				8
10	44	32	26	21	39	29	23	19	23	19	16	18	14	12	12	10	9	7				7

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4742	4742	4742	4742
5°	5501	4756	4204	4756
10°	6507	4736	3752	4736
15°	7516	4692	3224	4692
20°	8369	4631	2916	4631
25°	8639	4572	2707	4572
30°	7563	4501	2581	4501
35°	5887	4394	2505	4394
40°	4415	4272	2464	4272
45°	3486	4077	2442	4077
50°	2943	3852	2372	3852
55°	2564	3605	2245	3605
60°	2307	3347	1988	3347
65°	2034	3070	1710	3070
70°	1832	2783	1541	2783
75°	1535	2464	1313	2464
80°	1297	2101	1232	2101
85°	1093	1649	1093	1649



TEST NUMBER: P333028

CATALOG NUMBER: S124RDIW-S350D1340U835-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.9	0.9
10°-20°	171.7	2.8
20°-30°	268.5	4.4
30°-40°	298.5	4.9
40°-50°	264.9	4.3
50°-60°	206.4	3.4
60°-70°	135.1	2.2
70°-80°	66.4	1.1
80°-90°	21.4	0.3
90°-100°	110.6	1.8
100°-110°	327.6	5.3
110°-120°	556.1	9.1
120°-130°	733.3	11.9
130°-140°	823.5	13.4
140°-150°	809.2	13.2
150°-160°	680.6	11.1
160°-170°	452.8	7.4
170°-180°	158.6	2.6
0°-30°	497.1	8.1
0°-40°	795.6	13.0
0°-60°	1266.9	20.6
0°-90°	1489.8	24.3
90°-120°	994.3	16.2
90°-150°	3360.3	54.7
90°-180°	4652.0	75.7
0°-180°	6142.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	587	587	587	587	587	
5°	679	587	519	587	679	69
15°	899	561	386	561	899	256
25°	970	513	304	513	970	430
35°	597	446	254	446	597	374
45°	305	357	214	357	305	242
55°	182	256	160	256	182	166
65°	106	161	90	161	106	107
75°	49	79	42	79	49	54
85°	12	18	12	18	12	14
90°	39	4	39	4	39	20
95°	102	78	102	78	102	107
105°	316	302	316	302	316	333
115°	560	565	560	565	560	554
125°	817	824	817	824	817	729
135°	1063	1062	1063	1062	1063	821
145°	1292	1290	1292	1290	1292	808
155°	1477	1478	1477	1478	1477	680
165°	1606	1609	1606	1609	1606	452
175°	1666	1674	1666	1674	1666	158
180°	1677	1677	1677	1677	1677	



TEST NUMBER: P333028

CATALOG NUMBER: S124RDIW-S350D1340U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4
2.5°	619.6	621.3	619.6	619.4	617.5	616.9	616.2	613.7	609.2	606.5	607.1
5°	678.8	684.7	681.4	680.9	675.7	670.5	667.2	659.6	651.5	646.1	641.6
7.5°	747.2	750.6	748.5	745.2	736.8	732.0	724.3	714.4	699.9	688.9	678.8
10°	793.8	796.6	795.7	789.5	783.4	770.8	763.7	749.8	731.5	717.1	703.6
12.5°	839.6	842.6	834.3	834.6	822.9	813.0	801.8	784.2	763.2	744.6	727.7
15°	899.3	895.5	895.5	890.8	877.8	864.1	852.5	834.0	807.5	785.3	761.8
17.5°	946.1	947.4	945.5	934.3	924.1	909.9	888.6	867.1	842.5	812.6	788.7
20°	974.1	974.1	972.0	964.4	951.2	936.0	913.1	889.6	858.4	828.3	801.4
22.5°	985.5	986.2	983.7	977.5	965.6	950.8	931.2	907.4	875.2	841.4	808.0
25°	969.9	974.4	974.8	973.2	969.6	960.6	943.8	919.5	890.6	853.9	817.9
27.5°	890.4	896.1	901.1	909.3	920.2	925.8	926.6	914.2	889.0	853.7	817.5
30°	811.3	816.0	831.4	851.5	867.1	881.3	893.7	897.0	882.8	851.1	813.0
32.5°	723.4	729.9	745.3	766.9	792.9	817.0	844.6	858.7	858.3	839.3	804.1
35°	597.3	602.1	616.3	639.0	670.2	706.0	749.8	783.8	807.0	805.4	783.8
37.5°	481.8	487.1	501.4	520.3	550.6	594.8	637.2	684.2	727.0	751.1	743.9
40°	418.9	419.1	433.1	452.5	480.9	519.5	565.6	617.7	665.5	704.6	712.1
42.5°	369.3	369.3	378.6	399.5	419.9	456.2	500.3	552.0	608.0	653.1	673.1
45°	305.3	307.4	315.0	327.5	343.6	374.4	409.7	457.7	520.4	573.9	607.3
47.5°	258.5	261.7	266.5	276.7	289.5	310.0	339.2	382.4	433.4	492.2	539.7
50°	234.3	234.8	240.9	246.6	257.7	274.1	299.6	335.6	382.5	439.0	491.8
52.5°	213.5	213.4	217.1	224.3	233.3	246.0	266.7	299.4	341.0	391.7	446.2
55°	182.2	183.4	186.3	191.9	198.8	207.8	224.1	248.7	281.4	324.7	374.2
57.5°	158.5	159.1	161.3	163.7	170.0	176.6	188.8	205.9	233.4	268.9	315.0
60°	142.9	143.2	143.9	147.4	152.4	158.6	166.9	181.3	204.5	236.9	273.4
62.5°	127.8	128.2	129.3	131.9	135.8	140.0	148.7	160.3	179.5	207.2	240.0
65°	106.5	106.7	108.4	109.3	112.4	116.2	122.6	130.4	143.7	166.9	191.7
67.5°	89.0	89.0	89.1	90.4	92.5	95.0	98.8	105.1	115.1	129.3	151.2
70°	77.6	77.6	78.1	78.8	80.0	82.1	84.3	89.0	96.3	107.9	124.7
72.5°	67.0	67.2	67.7	67.8	68.4	70.2	71.8	74.8	80.2	89.0	102.6
75°	49.2	49.9	51.1	52.1	53.3	53.0	54.7	56.6	58.2	63.4	71.2
77.5°	36.6	36.3	36.4	37.2	37.3	37.6	38.8	40.2	41.5	43.9	46.7
80°	27.9	27.9	28.6	28.9	28.6	28.9	30.1	30.8	31.2	32.2	34.8
82.5°	21.1	21.5	21.3	21.5	21.6	21.9	22.9	23.0	23.5	23.9	24.9
85°	11.8	12.1	12.3	11.8	11.8	11.8	12.3	12.5	13.0	12.8	13.3
87.5°	11.9	11.6	11.7	11.6	11.7	11.3	11.1	11.1	10.4	10.3	9.8
90°	38.9	38.3	37.8	37.2	36.6	35.4	33.7	32.0	30.3	28.5	26.2
92.5°	57.6	57.2	56.9	56.5	56.2	55.5	54.5	53.4	52.4	51.4	49.7
95°	102.5	102.5	102.5	102.5	102.5	102.0	101.2	100.3	99.4	98.6	96.5
97.5°	160.6	160.6	160.6	160.6	160.6	160.0	159.0	158.0	156.9	155.9	153.5
100°	201.0	201.0	201.0	201.0	201.0	200.7	200.2	199.6	199.0	198.4	195.8
102.5°	246.7	246.4	246.2	246.0	245.7	245.2	244.4	243.6	242.8	242.0	239.6
105°	316.4	315.6	314.7	313.8	313.0	312.1	311.3	310.4	309.5	308.7	307.5
107.5°	384.4	384.5	384.5	384.6	384.6	384.3	383.4	382.6	381.8	381.0	380.9
110°	433.2	432.3	431.4	430.6	429.7	429.6	430.1	430.7	431.3	431.9	432.2



TEST NUMBER: P333028

CATALOG NUMBER: S124RDIW-S350D1340U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	483.0	482.8	482.6	482.4	482.3	482.2	482.4	482.5	482.6	482.7	483.2
115°	560.3	560.5	560.8	561.1	561.4	561.7	562.0	562.3	562.6	562.8	563.4
117.5°	633.9	634.5	635.1	635.6	636.2	637.0	638.0	639.0	639.9	640.9	641.3
120°	689.9	689.4	688.8	688.2	687.6	688.1	689.5	691.0	692.4	693.8	694.7
122.5°	736.6	737.7	738.7	739.7	740.8	741.8	742.8	743.7	744.7	745.7	746.1
125°	817.0	817.6	818.2	818.8	819.3	819.9	820.5	821.1	821.6	822.2	822.5
127.5°	891.5	891.9	892.4	892.9	893.3	893.8	894.4	895.0	895.6	896.1	896.6
130°	940.2	941.4	942.5	943.7	944.9	945.7	946.3	946.9	947.4	948.0	948.0
132.5°	992.1	992.6	993.0	993.5	994.0	994.5	995.1	995.6	996.2	996.8	997.0
135°	1063.4	1064.3	1065.2	1066.0	1066.9	1067.6	1068.2	1068.8	1069.4	1069.9	1069.9
137.5°	1138.4	1138.2	1138.1	1137.9	1137.7	1138.0	1138.8	1139.5	1140.2	1141.0	1140.5
140°	1184.1	1184.3	1184.6	1184.9	1185.2	1185.5	1185.8	1186.1	1186.4	1186.6	1186.6
142.5°	1229.7	1229.8	1229.8	1229.9	1229.9	1230.0	1230.1	1230.1	1230.2	1230.2	1230.5
145°	1291.7	1292.6	1293.4	1294.3	1295.2	1295.7	1296.0	1296.3	1296.6	1296.9	1296.6
147.5°	1354.5	1354.8	1355.0	1355.3	1355.6	1355.9	1356.1	1356.3	1356.6	1356.8	1357.0
150°	1392.9	1393.1	1393.4	1393.7	1394.0	1394.1	1394.1	1394.1	1394.1	1394.1	1394.1
152.5°	1428.1	1428.9	1429.6	1430.4	1431.1	1431.2	1430.5	1429.8	1429.1	1428.4	1428.2
155°	1477.2	1478.3	1479.5	1480.6	1481.8	1481.8	1480.6	1479.5	1478.3	1477.2	1477.4
157.5°	1521.0	1522.0	1522.9	1523.9	1524.9	1525.0	1524.1	1523.2	1522.4	1521.5	1521.6
160°	1545.9	1547.3	1548.8	1550.2	1551.6	1551.9	1551.1	1550.2	1549.3	1548.5	1548.8
162.5°	1571.8	1573.3	1574.7	1576.1	1577.6	1577.5	1576.0	1574.4	1572.9	1571.3	1571.6
165°	1605.5	1606.7	1607.8	1609.0	1610.2	1609.9	1608.1	1606.4	1604.7	1602.9	1603.5
167.5°	1629.7	1631.5	1633.2	1635.0	1636.8	1636.8	1635.1	1633.4	1631.7	1629.9	1629.9
170°	1643.2	1645.2	1647.2	1649.2	1651.2	1651.4	1649.6	1647.9	1646.2	1644.4	1644.2
172.5°	1654.6	1656.6	1658.6	1660.6	1662.6	1662.7	1660.7	1658.7	1656.8	1654.8	1654.8
175°	1666.5	1668.5	1670.5	1672.5	1674.6	1674.6	1672.5	1670.5	1668.5	1666.5	1666.8
177.5°	1672.7	1674.6	1676.4	1678.3	1680.1	1680.2	1678.6	1677.0	1675.4	1673.8	1673.8
180°	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9



TEST NUMBER: P333028

CATALOG NUMBER: S124RDIW-S350D1340U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4
2.5°	605.2	602.6	601.2	598.2	594.6	592.7	591.0	588.5	585.3	581.9	579.5
5°	635.9	630.2	623.1	614.6	607.1	599.7	593.3	586.9	579.6	572.0	564.5
7.5°	667.4	656.3	644.2	630.2	616.7	604.3	592.9	582.1	569.8	558.7	548.7
10°	689.4	674.3	657.5	639.7	622.0	606.6	591.4	577.7	562.6	549.1	537.7
12.5°	707.2	689.4	669.2	647.1	625.7	607.1	589.7	571.8	554.6	540.0	524.8
15°	736.7	712.4	685.2	658.6	631.0	605.6	582.2	561.4	541.7	521.1	506.7
17.5°	757.1	728.1	695.0	663.2	630.5	600.6	573.6	548.8	526.1	505.1	487.9
20°	769.2	737.2	700.5	664.3	627.6	595.7	566.6	539.1	515.7	493.0	475.2
22.5°	776.0	740.6	700.5	662.6	624.6	590.0	558.1	529.5	504.0	481.2	461.6
25°	778.2	740.3	699.4	655.8	614.2	577.5	544.3	513.3	484.9	462.2	441.4
27.5°	775.1	730.5	688.6	643.9	600.9	562.3	527.5	494.9	466.5	442.1	420.7
30°	770.6	722.8	677.8	631.4	587.9	550.7	514.0	482.8	453.2	427.9	406.4
32.5°	760.7	713.3	664.9	617.4	573.3	535.0	500.2	468.8	439.8	413.9	391.0
35°	741.2	693.2	640.7	591.9	548.6	508.8	476.2	445.9	418.2	390.5	366.4
37.5°	715.5	666.5	614.2	560.8	517.4	479.9	450.0	421.5	394.5	369.2	342.5
40°	691.3	646.6	592.6	539.6	495.1	458.9	431.2	405.4	378.2	353.1	326.4
42.5°	662.0	623.9	569.3	516.1	472.2	437.3	411.5	386.3	361.5	337.2	309.3
45°	613.0	584.1	533.0	481.9	437.6	403.0	379.4	357.1	335.4	312.2	285.9
47.5°	556.8	537.3	493.2	440.8	399.9	368.8	345.9	327.7	309.3	286.1	263.1
50°	517.8	505.3	462.7	414.9	375.8	347.2	323.8	306.7	291.3	269.1	248.5
52.5°	476.2	469.5	433.5	387.8	350.1	322.0	302.0	286.7	271.1	252.6	233.4
55°	412.7	416.3	385.8	346.2	310.7	287.1	268.9	256.1	242.8	227.2	212.3
57.5°	347.9	360.9	340.4	305.7	272.4	250.5	236.8	226.1	214.9	202.0	189.2
60°	309.1	320.0	308.4	277.8	248.7	228.4	215.6	207.3	196.2	184.4	174.7
62.5°	271.2	282.9	276.0	251.3	224.3	206.8	195.5	187.8	179.5	169.2	159.1
65°	223.7	231.2	227.9	210.9	191.7	176.8	166.4	160.7	153.1	145.6	136.6
67.5°	171.3	185.9	184.0	174.9	158.4	146.7	139.9	134.9	128.0	122.4	116.3
70°	140.8	154.3	154.1	146.7	137.7	126.9	122.1	117.9	111.7	106.3	101.3
72.5°	115.3	127.6	129.5	123.8	117.7	109.4	104.9	102.0	96.0	92.3	88.2
75°	80.7	89.7	92.1	92.1	89.2	85.0	80.9	79.0	74.8	71.5	69.1
77.5°	52.9	58.6	62.3	63.1	63.6	62.1	58.8	57.5	54.2	53.1	50.8
80°	37.4	41.2	45.4	46.9	48.0	47.6	46.2	45.2	42.1	40.9	40.0
82.5°	25.8	27.9	31.4	34.6	34.2	35.5	34.2	33.5	31.1	30.7	29.8
85°	13.5	13.7	14.2	16.3	17.5	18.0	18.2	17.8	17.0	17.0	15.4
87.5°	9.3	8.7	8.6	8.0	7.6	7.7	7.7	7.2	7.3	7.3	7.4
90°	23.9	21.6	19.3	16.6	13.4	10.2	7.1	3.9	7.1	10.2	13.4
92.5°	48.1	46.5	44.9	42.3	38.6	35.0	31.4	27.8	31.4	35.0	38.6
95°	94.5	92.5	90.5	88.2	85.6	83.0	80.4	77.8	80.4	83.0	85.6
97.5°	151.2	148.8	146.4	144.2	142.1	140.1	138.0	135.9	138.0	140.1	142.1
100°	193.2	190.6	188.0	186.2	185.0	183.9	182.7	181.6	182.7	183.9	185.0
102.5°	237.3	234.9	232.5	231.1	230.7	230.2	229.8	229.3	229.8	230.2	230.7
105°	306.4	305.2	304.0	303.3	303.0	302.8	302.5	302.2	302.5	302.8	303.0
107.5°	380.7	380.5	380.3	380.1	379.7	379.4	379.0	378.7	379.0	379.4	379.7
110°	432.4	432.7	433.0	432.9	432.3	431.7	431.1	430.6	431.1	431.7	432.3



TEST NUMBER: P333028

CATALOG NUMBER: S124RDIW-S350D1340U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	483.7	484.3	484.8	485.0	484.9	484.7	484.6	484.5	484.6	484.7	484.9
115°	564.0	564.6	565.2	565.4	565.4	565.4	565.4	565.4	565.4	565.4	565.4
117.5°	641.7	642.1	642.5	642.6	642.4	642.2	641.9	641.7	641.9	642.2	642.4
120°	695.6	696.4	697.3	697.1	696.0	694.8	693.7	692.5	693.7	694.8	696.0
122.5°	746.5	746.9	747.3	747.3	746.8	746.4	745.9	745.4	745.9	746.4	746.8
125°	822.8	823.1	823.4	823.5	823.5	823.5	823.5	823.5	823.5	823.5	823.5
127.5°	897.1	897.5	898.0	897.8	896.9	896.1	895.2	894.3	895.2	896.1	896.9
130°	948.0	948.0	948.0	947.6	946.7	945.9	945.0	944.1	945.0	945.9	946.7
132.5°	997.2	997.5	997.7	997.5	996.9	996.2	995.6	995.0	995.6	996.2	996.9
135°	1069.9	1069.9	1069.9	1069.1	1067.3	1065.6	1063.9	1062.1	1063.9	1065.6	1067.3
137.5°	1140.1	1139.6	1139.2	1138.5	1137.7	1136.9	1136.1	1135.3	1136.1	1136.9	1137.7
140°	1186.6	1186.6	1186.6	1186.4	1185.8	1185.2	1184.6	1184.1	1184.6	1185.2	1185.8
142.5°	1230.7	1230.9	1231.1	1231.0	1230.4	1229.8	1229.2	1228.7	1229.2	1229.8	1230.4
145°	1296.3	1296.0	1295.7	1295.0	1293.9	1292.7	1291.6	1290.4	1291.6	1292.7	1293.9
147.5°	1357.3	1357.5	1357.7	1357.1	1355.8	1354.4	1353.0	1351.6	1353.0	1354.4	1355.8
150°	1394.1	1394.1	1394.1	1393.6	1392.4	1391.3	1390.1	1389.0	1390.1	1391.3	1392.4
152.5°	1427.9	1427.7	1427.5	1427.0	1426.3	1425.6	1424.9	1424.2	1424.9	1425.6	1426.3
155°	1477.7	1478.0	1478.3	1478.4	1478.4	1478.4	1478.4	1478.4	1478.4	1478.4	1478.4
157.5°	1521.6	1521.7	1521.7	1522.0	1522.5	1523.1	1523.6	1524.1	1523.6	1523.1	1522.5
160°	1549.1	1549.3	1549.6	1549.9	1550.2	1550.5	1550.8	1551.1	1550.8	1550.5	1550.2
162.5°	1571.9	1572.2	1572.5	1573.0	1573.7	1574.5	1575.2	1576.0	1575.2	1574.5	1573.7
165°	1604.1	1604.7	1605.3	1606.0	1606.8	1607.7	1608.6	1609.4	1608.6	1607.7	1606.8
167.5°	1629.8	1629.8	1629.7	1630.3	1631.5	1632.7	1633.9	1635.1	1633.9	1632.7	1631.5
170°	1643.9	1643.6	1643.3	1643.9	1645.3	1646.8	1648.2	1649.6	1648.2	1646.8	1645.3
172.5°	1654.7	1654.7	1654.6	1655.2	1656.4	1657.6	1658.8	1660.0	1658.8	1657.6	1656.4
175°	1667.1	1667.4	1667.6	1668.5	1670.0	1671.4	1672.8	1674.3	1672.8	1671.4	1670.0
177.5°	1673.8	1673.8	1673.8	1674.3	1675.5	1676.6	1677.8	1678.9	1677.8	1676.6	1675.5
180°	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9



TEST NUMBER: P333028

CATALOG NUMBER: S124RDIW-S350D1340U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4
2.5°	576.8	574.9	572.5	569.6	566.2	563.2	561.8	563.0	563.6	562.0	561.8
5°	559.2	553.3	548.6	541.5	535.8	531.1	527.8	526.3	526.8	523.0	522.1
7.5°	539.5	532.5	524.7	516.3	508.5	501.5	497.9	495.9	491.8	490.1	487.2
10°	526.8	517.4	509.8	499.8	490.8	482.6	478.5	475.2	471.2	469.3	465.3
12.5°	513.8	502.8	494.4	484.1	474.9	465.0	461.1	455.0	448.7	444.7	439.5
15°	495.3	482.1	471.9	459.6	448.7	437.4	427.2	415.8	411.6	402.6	397.4
17.5°	473.8	460.4	447.8	431.3	414.5	400.3	389.5	378.6	372.1	366.4	363.7
20°	459.6	447.3	429.8	410.6	391.9	376.3	367.5	360.4	353.3	349.3	346.5
22.5°	446.2	430.4	410.1	389.4	370.7	358.5	351.1	343.8	338.0	334.2	330.4
25°	423.6	403.0	381.5	357.8	345.1	334.4	326.4	320.4	316.9	311.9	310.0
27.5°	400.5	375.5	351.8	335.9	322.6	312.8	305.8	301.4	296.9	293.7	291.2
30°	382.7	357.4	336.1	320.9	307.4	299.4	293.7	288.5	284.9	282.3	280.5
32.5°	365.1	339.8	321.9	305.6	294.9	287.1	281.0	277.1	274.3	271.0	269.8
35°	339.6	317.1	301.5	286.8	276.0	268.9	264.1	260.1	257.7	256.8	256.1
37.5°	315.1	296.7	279.9	267.9	258.2	252.6	247.0	245.0	243.4	241.7	242.5
40°	299.6	282.3	267.4	254.7	246.8	240.7	237.4	235.0	233.6	233.6	233.6
42.5°	286.2	269.3	254.7	243.3	235.5	230.3	226.6	224.6	224.1	223.9	225.1
45°	265.3	249.7	235.0	225.5	218.9	213.7	211.6	209.9	209.9	210.9	211.1
47.5°	244.6	230.0	218.2	207.6	201.5	198.3	196.4	195.6	195.7	196.6	197.7
50°	231.9	217.5	205.9	196.4	190.8	187.7	186.0	185.5	186.0	186.0	187.7
52.5°	218.1	205.2	193.8	185.8	179.4	176.5	175.6	174.9	175.2	176.0	176.7
55°	197.9	186.3	175.4	167.8	163.1	161.2	159.0	159.3	158.8	159.3	159.3
57.5°	177.5	167.1	157.0	151.0	146.8	144.1	141.8	142.4	141.7	141.6	141.2
60°	164.5	153.1	145.1	139.6	134.9	132.5	130.4	130.9	130.2	129.7	128.7
62.5°	150.3	140.8	133.1	127.9	124.1	121.4	119.2	118.8	117.1	115.5	113.4
65°	129.7	121.9	115.0	110.1	106.5	104.4	102.7	101.3	97.7	94.0	92.1
67.5°	109.7	104.0	97.6	93.4	90.5	87.8	84.6	82.2	78.9	76.8	75.6
70°	96.8	91.4	85.9	81.9	78.8	76.2	72.7	71.0	68.6	67.7	66.5
72.5°	84.5	79.4	74.4	70.7	67.5	65.4	62.6	61.0	59.9	59.5	58.4
75°	65.8	61.8	58.0	54.7	52.1	50.6	49.5	48.3	47.8	45.7	44.5
77.5°	48.0	45.3	43.0	40.6	38.8	37.8	35.5	34.2	33.4	32.4	32.1
80°	37.4	35.5	33.1	31.7	29.1	28.2	27.2	27.0	26.7	26.5	26.3
82.5°	28.1	26.2	23.9	23.0	22.3	21.7	21.2	20.9	20.7	20.8	20.8
85°	14.2	13.3	13.3	13.0	12.8	12.5	12.3	12.3	12.1	12.3	12.1
87.5°	8.0	8.4	8.9	8.9	9.6	10.1	10.2	10.6	11.1	11.1	11.3
90°	16.6	19.3	21.6	23.9	26.2	28.5	30.3	32.0	33.7	35.4	36.6
92.5°	42.3	44.9	46.5	48.1	49.7	51.4	52.4	53.4	54.5	55.5	56.2
95°	88.2	90.5	92.5	94.5	96.5	98.6	99.4	100.3	101.2	102.0	102.5
97.5°	144.2	146.4	148.8	151.2	153.5	155.9	156.9	158.0	159.0	160.0	160.6
100°	186.2	188.0	190.6	193.2	195.8	198.4	199.0	199.6	200.2	200.7	201.0
102.5°	231.1	232.5	234.9	237.3	239.6	242.0	242.8	243.6	244.4	245.2	245.7
105°	303.3	304.0	305.2	306.4	307.5	308.7	309.5	310.4	311.3	312.1	313.0
107.5°	380.1	380.3	380.5	380.7	380.9	381.0	381.8	382.6	383.4	384.3	384.6
110°	432.9	433.0	432.7	432.4	432.2	431.9	431.3	430.7	430.1	429.6	429.7



TEST NUMBER: P333028

CATALOG NUMBER: S124RDIW-S350D1340U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	485.0	484.8	484.3	483.7	483.2	482.7	482.6	482.5	482.4	482.2	482.3
115°	565.4	565.2	564.6	564.0	563.4	562.8	562.6	562.3	562.0	561.7	561.4
117.5°	642.6	642.5	642.1	641.7	641.3	640.9	639.9	639.0	638.0	637.0	636.2
120°	697.1	697.3	696.4	695.6	694.7	693.8	692.4	691.0	689.5	688.1	687.6
122.5°	747.3	747.3	746.9	746.5	746.1	745.7	744.7	743.7	742.8	741.8	740.8
125°	823.5	823.4	823.1	822.8	822.5	822.2	821.6	821.1	820.5	819.9	819.3
127.5°	897.8	898.0	897.5	897.1	896.6	896.1	895.6	895.0	894.4	893.8	893.3
130°	947.6	948.0	948.0	948.0	948.0	948.0	947.4	946.9	946.3	945.7	944.9
132.5°	997.5	997.7	997.5	997.2	997.0	996.8	996.2	995.6	995.1	994.5	994.0
135°	1069.1	1069.9	1069.9	1069.9	1069.9	1069.9	1069.4	1068.8	1068.2	1067.6	1066.9
137.5°	1138.5	1139.2	1139.6	1140.1	1140.5	1141.0	1140.2	1139.5	1138.8	1138.0	1137.7
140°	1186.4	1186.6	1186.6	1186.6	1186.6	1186.6	1186.4	1186.1	1185.8	1185.5	1185.2
142.5°	1231.0	1231.1	1230.9	1230.7	1230.5	1230.2	1230.2	1230.1	1230.1	1230.0	1229.9
145°	1295.0	1295.7	1296.0	1296.3	1296.6	1296.9	1296.6	1296.3	1296.0	1295.7	1295.2
147.5°	1357.1	1357.7	1357.5	1357.3	1357.0	1356.8	1356.6	1356.3	1356.1	1355.9	1355.6
150°	1393.6	1394.1	1394.1	1394.1	1394.1	1394.1	1394.1	1394.1	1394.1	1394.1	1394.0
152.5°	1427.0	1427.5	1427.7	1427.9	1428.2	1428.4	1429.1	1429.8	1430.5	1431.2	1431.1
155°	1478.4	1478.3	1478.0	1477.7	1477.4	1477.2	1478.3	1479.5	1480.6	1481.8	1481.8
157.5°	1522.0	1521.7	1521.7	1521.6	1521.6	1521.5	1522.4	1523.2	1524.1	1525.0	1524.9
160°	1549.9	1549.6	1549.3	1549.1	1548.8	1548.5	1549.3	1550.2	1551.1	1551.9	1551.6
162.5°	1573.0	1572.5	1572.2	1571.9	1571.6	1571.3	1572.9	1574.4	1576.0	1577.5	1577.6
165°	1606.0	1605.3	1604.7	1604.1	1603.5	1602.9	1604.7	1606.4	1608.1	1609.9	1610.2
167.5°	1630.3	1629.7	1629.8	1629.8	1629.9	1629.9	1631.7	1633.4	1635.1	1636.8	1636.8
170°	1643.9	1643.3	1643.6	1643.9	1644.2	1644.4	1646.2	1647.9	1649.6	1651.4	1651.2
172.5°	1655.2	1654.6	1654.7	1654.7	1654.8	1654.8	1656.8	1658.7	1660.7	1662.7	1662.6
175°	1668.5	1667.6	1667.4	1667.1	1666.8	1666.5	1668.5	1670.5	1672.5	1674.6	1674.6
177.5°	1674.3	1673.8	1673.8	1673.8	1673.8	1673.8	1675.4	1677.0	1678.6	1680.2	1680.1
180°	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9



TEST NUMBER: P333028

CATALOG NUMBER: S124RDIW-S350D1340U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4
2.5°	560.7	561.1	559.8	559.4	559.8	561.1	560.7	561.8	562.0	563.6	563.0
5°	520.2	519.7	518.5	518.8	518.5	519.7	520.2	522.1	523.0	526.8	526.3
7.5°	485.5	483.7	484.2	482.3	484.2	483.7	485.5	487.2	490.1	491.8	495.9
10°	464.3	461.7	459.6	457.7	459.6	461.7	464.3	465.3	469.3	471.2	475.2
12.5°	435.4	433.1	430.3	430.8	430.3	433.1	435.4	439.5	444.7	448.7	455.0
15°	394.3	390.7	385.1	385.8	385.1	390.7	394.3	397.4	402.6	411.6	415.8
17.5°	359.5	359.5	356.9	357.6	356.9	359.5	359.5	363.7	366.4	372.1	378.6
20°	341.5	339.9	340.1	339.4	340.1	339.9	341.5	346.5	349.3	353.3	360.4
22.5°	329.0	327.0	325.3	323.9	325.3	327.0	329.0	330.4	334.2	338.0	343.8
25°	307.9	306.5	304.4	303.9	304.4	306.5	307.9	310.0	311.9	316.9	320.4
27.5°	289.3	289.1	288.2	287.1	288.2	289.1	289.3	291.2	293.7	296.9	301.4
30°	278.6	278.1	277.6	276.9	277.6	278.1	278.6	280.5	282.3	284.9	288.5
32.5°	268.9	268.6	268.1	268.2	268.1	268.6	268.9	269.8	271.0	274.3	277.1
35°	255.1	254.9	254.4	254.2	254.4	254.9	255.1	256.1	256.8	257.7	260.1
37.5°	242.3	242.9	242.6	242.5	242.6	242.9	242.3	242.5	241.7	243.4	245.0
40°	233.4	233.6	234.1	233.8	234.1	233.6	233.4	233.6	233.6	233.6	235.0
42.5°	226.0	226.0	226.7	225.9	226.7	226.0	226.0	225.1	223.9	224.1	224.6
45°	212.8	214.2	213.9	213.9	213.9	214.2	212.8	211.1	210.9	209.9	209.9
47.5°	198.3	199.6	199.9	199.8	199.9	199.6	198.3	197.7	196.6	195.7	195.6
50°	188.9	188.4	189.1	188.9	189.1	188.4	188.9	187.7	186.0	186.0	185.5
52.5°	177.3	177.4	177.4	177.1	177.4	177.4	177.3	176.7	176.0	175.2	174.9
55°	159.5	159.8	159.3	159.5	159.3	159.8	159.5	159.3	159.3	158.8	159.3
57.5°	140.2	139.1	139.5	139.0	139.5	139.1	140.2	141.2	141.6	141.7	142.4
60°	126.4	124.5	124.0	123.1	124.0	124.5	126.4	128.7	129.7	130.2	130.9
62.5°	110.9	109.5	107.9	108.7	107.9	109.5	110.9	113.4	115.5	117.1	118.8
65°	90.2	89.2	88.5	89.5	88.5	89.2	90.2	92.1	94.0	97.7	101.3
67.5°	74.6	74.1	74.1	73.7	74.1	74.1	74.6	75.6	76.8	78.9	82.2
70°	66.5	65.8	65.8	65.3	65.8	65.8	66.5	66.5	67.7	68.6	71.0
72.5°	58.2	57.5	57.7	57.4	57.7	57.5	58.2	58.4	59.5	59.9	61.0
75°	43.1	41.9	41.9	42.1	41.9	41.9	43.1	44.5	45.7	47.8	48.3
77.5°	32.1	31.9	32.2	31.8	32.2	31.9	32.1	32.1	32.4	33.4	34.2
80°	26.3	26.0	25.8	26.5	25.8	26.0	26.3	26.3	26.5	26.7	27.0
82.5°	20.4	20.4	20.3	21.2	20.3	20.4	20.4	20.8	20.8	20.7	20.9
85°	12.3	11.8	12.3	11.8	12.3	11.8	12.3	12.1	12.3	12.1	12.3
87.5°	11.8	11.7	11.6	11.9	11.6	11.7	11.8	11.3	11.1	11.1	10.6
90°	37.2	37.8	38.3	38.9	38.3	37.8	37.2	36.6	35.4	33.7	32.0
92.5°	56.5	56.9	57.2	57.6	57.2	56.9	56.5	56.2	55.5	54.5	53.4
95°	102.5	102.5	102.5	102.5	102.5	102.5	102.5	102.5	102.0	101.2	100.3
97.5°	160.6	160.6	160.6	160.6	160.6	160.6	160.6	160.6	160.0	159.0	158.0
100°	201.0	201.0	201.0	201.0	201.0	201.0	201.0	201.0	200.7	200.2	199.6
102.5°	246.0	246.2	246.4	246.7	246.4	246.2	246.0	245.7	245.2	244.4	243.6
105°	313.8	314.7	315.6	316.4	315.6	314.7	313.8	313.0	312.1	311.3	310.4
107.5°	384.6	384.5	384.5	384.4	384.5	384.5	384.6	384.6	384.3	383.4	382.6
110°	430.6	431.4	432.3	433.2	432.3	431.4	430.6	429.7	429.6	430.1	430.7



TEST NUMBER: P333028

CATALOG NUMBER: S124RDIW-S350D1340U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	482.4	482.6	482.8	483.0	482.8	482.6	482.4	482.3	482.2	482.4	482.5
115°	561.1	560.8	560.5	560.3	560.5	560.8	561.1	561.4	561.7	562.0	562.3
117.5°	635.6	635.1	634.5	633.9	634.5	635.1	635.6	636.2	637.0	638.0	639.0
120°	688.2	688.8	689.4	689.9	689.4	688.8	688.2	687.6	688.1	689.5	691.0
122.5°	739.7	738.7	737.7	736.6	737.7	738.7	739.7	740.8	741.8	742.8	743.7
125°	818.8	818.2	817.6	817.0	817.6	818.2	818.8	819.3	819.9	820.5	821.1
127.5°	892.9	892.4	891.9	891.5	891.9	892.4	892.9	893.3	893.8	894.4	895.0
130°	943.7	942.5	941.4	940.2	941.4	942.5	943.7	944.9	945.7	946.3	946.9
132.5°	993.5	993.0	992.6	992.1	992.6	993.0	993.5	994.0	994.5	995.1	995.6
135°	1066.0	1065.2	1064.3	1063.4	1064.3	1065.2	1066.0	1066.9	1067.6	1068.2	1068.8
137.5°	1137.9	1138.1	1138.2	1138.4	1138.2	1138.1	1137.9	1137.7	1138.0	1138.8	1139.5
140°	1184.9	1184.6	1184.3	1184.1	1184.3	1184.6	1184.9	1185.2	1185.5	1185.8	1186.1
142.5°	1229.9	1229.8	1229.8	1229.7	1229.8	1229.8	1229.9	1229.9	1230.0	1230.1	1230.1
145°	1294.3	1293.4	1292.6	1291.7	1292.6	1293.4	1294.3	1295.2	1295.7	1296.0	1296.3
147.5°	1355.3	1355.0	1354.8	1354.5	1354.8	1355.0	1355.3	1355.6	1355.9	1356.1	1356.3
150°	1393.7	1393.4	1393.1	1392.9	1393.1	1393.4	1393.7	1394.0	1394.1	1394.1	1394.1
152.5°	1430.4	1429.6	1428.9	1428.1	1428.9	1429.6	1430.4	1431.1	1431.2	1430.5	1429.8
155°	1480.6	1479.5	1478.3	1477.2	1478.3	1479.5	1480.6	1481.8	1481.8	1480.6	1479.5
157.5°	1523.9	1522.9	1522.0	1521.0	1522.0	1522.9	1523.9	1524.9	1525.0	1524.1	1523.2
160°	1550.2	1548.8	1547.3	1545.9	1547.3	1548.8	1550.2	1551.6	1551.9	1551.1	1550.2
162.5°	1576.1	1574.7	1573.3	1571.8	1573.3	1574.7	1576.1	1577.6	1577.5	1576.0	1574.4
165°	1609.0	1607.8	1606.7	1605.5	1606.7	1607.8	1609.0	1610.2	1609.9	1608.1	1606.4
167.5°	1635.0	1633.2	1631.5	1629.7	1631.5	1633.2	1635.0	1636.8	1636.8	1635.1	1633.4
170°	1649.2	1647.2	1645.2	1643.2	1645.2	1647.2	1649.2	1651.2	1651.4	1649.6	1647.9
172.5°	1660.6	1658.6	1656.6	1654.6	1656.6	1658.6	1660.6	1662.6	1662.7	1660.7	1658.7
175°	1672.5	1670.5	1668.5	1666.5	1668.5	1670.5	1672.5	1674.6	1674.6	1672.5	1670.5
177.5°	1678.3	1676.4	1674.6	1672.7	1674.6	1676.4	1678.3	1680.1	1680.2	1678.6	1677.0
180°	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9



TEST NUMBER: P333028

CATALOG NUMBER: S124RDIW-S350D1340U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4
2.5°	561.8	563.2	566.2	569.6	572.5	574.9	576.8	579.5	581.9	585.3	588.5
5°	527.8	531.1	535.8	541.5	548.6	553.3	559.2	564.5	572.0	579.6	586.9
7.5°	497.9	501.5	508.5	516.3	524.7	532.5	539.5	548.7	558.7	569.8	582.1
10°	478.5	482.6	490.8	499.8	509.8	517.4	526.8	537.7	549.1	562.6	577.7
12.5°	461.1	465.0	474.9	484.1	494.4	502.8	513.8	524.8	540.0	554.6	571.8
15°	427.2	437.4	448.7	459.6	471.9	482.1	495.3	506.7	521.1	541.7	561.4
17.5°	389.5	400.3	414.5	431.3	447.8	460.4	473.8	487.9	505.1	526.1	548.8
20°	367.5	376.3	391.9	410.6	429.8	447.3	459.6	475.2	493.0	515.7	539.1
22.5°	351.1	358.5	370.7	389.4	410.1	430.4	446.2	461.6	481.2	504.0	529.5
25°	326.4	334.4	345.1	357.8	381.5	403.0	423.6	441.4	462.2	484.9	513.3
27.5°	305.8	312.8	322.6	335.9	351.8	375.5	400.5	420.7	442.1	466.5	494.9
30°	293.7	299.4	307.4	320.9	336.1	357.4	382.7	406.4	427.9	453.2	482.8
32.5°	281.0	287.1	294.9	305.6	321.9	339.8	365.1	391.0	413.9	439.8	468.8
35°	264.1	268.9	276.0	286.8	301.5	317.1	339.6	366.4	390.5	418.2	445.9
37.5°	247.0	252.6	258.2	267.9	279.9	296.7	315.1	342.5	369.2	394.5	421.5
40°	237.4	240.7	246.8	254.7	267.4	282.3	299.6	326.4	353.1	378.2	405.4
42.5°	226.6	230.3	235.5	243.3	254.7	269.3	286.2	309.3	337.2	361.5	386.3
45°	211.6	213.7	218.9	225.5	235.0	249.7	265.3	285.9	312.2	335.4	357.1
47.5°	196.4	198.3	201.5	207.6	218.2	230.0	244.6	263.1	286.1	309.3	327.7
50°	186.0	187.7	190.8	196.4	205.9	217.5	231.9	248.5	269.1	291.3	306.7
52.5°	175.6	176.5	179.4	185.8	193.8	205.2	218.1	233.4	252.6	271.1	286.7
55°	159.0	161.2	163.1	167.8	175.4	186.3	197.9	212.3	227.2	242.8	256.1
57.5°	141.8	144.1	146.8	151.0	157.0	167.1	177.5	189.2	202.0	214.9	226.1
60°	130.4	132.5	134.9	139.6	145.1	153.1	164.5	174.7	184.4	196.2	207.3
62.5°	119.2	121.4	124.1	127.9	133.1	140.8	150.3	159.1	169.2	179.5	187.8
65°	102.7	104.4	106.5	110.1	115.0	121.9	129.7	136.6	145.6	153.1	160.7
67.5°	84.6	87.8	90.5	93.4	97.6	104.0	109.7	116.3	122.4	128.0	134.9
70°	72.7	76.2	78.8	81.9	85.9	91.4	96.8	101.3	106.3	111.7	117.9
72.5°	62.6	65.4	67.5	70.7	74.4	79.4	84.5	88.2	92.3	96.0	102.0
75°	49.5	50.6	52.1	54.7	58.0	61.8	65.8	69.1	71.5	74.8	79.0
77.5°	35.5	37.8	38.8	40.6	43.0	45.3	48.0	50.8	53.1	54.2	57.5
80°	27.2	28.2	29.1	31.7	33.1	35.5	37.4	40.0	40.9	42.1	45.2
82.5°	21.2	21.7	22.3	23.0	23.9	26.2	28.1	29.8	30.7	31.1	33.5
85°	12.3	12.5	12.8	13.0	13.3	13.3	14.2	15.4	17.0	17.0	17.8
87.5°	10.2	10.1	9.6	8.9	8.9	8.4	8.0	7.4	7.3	7.3	7.2
90°	30.3	28.5	26.2	23.9	21.6	19.3	16.6	13.4	10.2	7.1	3.9
92.5°	52.4	51.4	49.7	48.1	46.5	44.9	42.3	38.6	35.0	31.4	27.8
95°	99.4	98.6	96.5	94.5	92.5	90.5	88.2	85.6	83.0	80.4	77.8
97.5°	156.9	155.9	153.5	151.2	148.8	146.4	144.2	142.1	140.1	138.0	135.9
100°	199.0	198.4	195.8	193.2	190.6	188.0	186.2	185.0	183.9	182.7	181.6
102.5°	242.8	242.0	239.6	237.3	234.9	232.5	231.1	230.7	230.2	229.8	229.3
105°	309.5	308.7	307.5	306.4	305.2	304.0	303.3	303.0	302.8	302.5	302.2
107.5°	381.8	381.0	380.9	380.7	380.5	380.3	380.1	379.7	379.4	379.0	378.7
110°	431.3	431.9	432.2	432.4	432.7	433.0	432.9	432.3	431.7	431.1	430.6



TEST NUMBER: P333028

CATALOG NUMBER: S124RDIW-S350D1340U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	482.6	482.7	483.2	483.7	484.3	484.8	485.0	484.9	484.7	484.6	484.5
115°	562.6	562.8	563.4	564.0	564.6	565.2	565.4	565.4	565.4	565.4	565.4
117.5°	639.9	640.9	641.3	641.7	642.1	642.5	642.6	642.4	642.2	641.9	641.7
120°	692.4	693.8	694.7	695.6	696.4	697.3	697.1	696.0	694.8	693.7	692.5
122.5°	744.7	745.7	746.1	746.5	746.9	747.3	747.3	746.8	746.4	745.9	745.4
125°	821.6	822.2	822.5	822.8	823.1	823.4	823.5	823.5	823.5	823.5	823.5
127.5°	895.6	896.1	896.6	897.1	897.5	898.0	897.8	896.9	896.1	895.2	894.3
130°	947.4	948.0	948.0	948.0	948.0	948.0	947.6	946.7	945.9	945.0	944.1
132.5°	996.2	996.8	997.0	997.2	997.5	997.7	997.5	996.9	996.2	995.6	995.0
135°	1069.4	1069.9	1069.9	1069.9	1069.9	1069.9	1069.1	1067.3	1065.6	1063.9	1062.1
137.5°	1140.2	1141.0	1140.5	1140.1	1139.6	1139.2	1138.5	1137.7	1136.9	1136.1	1135.3
140°	1186.4	1186.6	1186.6	1186.6	1186.6	1186.6	1186.4	1185.8	1185.2	1184.6	1184.1
142.5°	1230.2	1230.2	1230.5	1230.7	1230.9	1231.1	1231.0	1230.4	1229.8	1229.2	1228.7
145°	1296.6	1296.9	1296.6	1296.3	1296.0	1295.7	1295.0	1293.9	1292.7	1291.6	1290.4
147.5°	1356.6	1356.8	1357.0	1357.3	1357.5	1357.7	1357.1	1355.8	1354.4	1353.0	1351.6
150°	1394.1	1394.1	1394.1	1394.1	1394.1	1394.1	1393.6	1392.4	1391.3	1390.1	1389.0
152.5°	1429.1	1428.4	1428.2	1427.9	1427.7	1427.5	1427.0	1426.3	1425.6	1424.9	1424.2
155°	1478.3	1477.2	1477.4	1477.7	1478.0	1478.3	1478.4	1478.4	1478.4	1478.4	1478.4
157.5°	1522.4	1521.5	1521.6	1521.6	1521.7	1521.7	1522.0	1522.5	1523.1	1523.6	1524.1
160°	1549.3	1548.5	1548.8	1549.1	1549.3	1549.6	1549.9	1550.2	1550.5	1550.8	1551.1
162.5°	1572.9	1571.3	1571.6	1571.9	1572.2	1572.5	1573.0	1573.7	1574.5	1575.2	1576.0
165°	1604.7	1602.9	1603.5	1604.1	1604.7	1605.3	1606.0	1606.8	1607.7	1608.6	1609.4
167.5°	1631.7	1629.9	1629.9	1629.8	1629.8	1629.7	1630.3	1631.5	1632.7	1633.9	1635.1
170°	1646.2	1644.4	1644.2	1643.9	1643.6	1643.3	1643.9	1645.3	1646.8	1648.2	1649.6
172.5°	1656.8	1654.8	1654.8	1654.7	1654.7	1654.6	1655.2	1656.4	1657.6	1658.8	1660.0
175°	1668.5	1666.5	1666.8	1667.1	1667.4	1667.6	1668.5	1670.0	1671.4	1672.8	1674.3
177.5°	1675.4	1673.8	1673.8	1673.8	1673.8	1673.8	1674.3	1675.5	1676.6	1677.8	1678.9
180°	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9



TEST NUMBER: P333028

CATALOG NUMBER: S124RDIW-S350D1340U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4
2.5°	591.0	592.7	594.6	598.2	601.2	602.6	605.2	607.1	606.5	609.2	613.7
5°	593.3	599.7	607.1	614.6	623.1	630.2	635.9	641.6	646.1	651.5	659.6
7.5°	592.9	604.3	616.7	630.2	644.2	656.3	667.4	678.8	688.9	699.9	714.4
10°	591.4	606.6	622.0	639.7	657.5	674.3	689.4	703.6	717.1	731.5	749.8
12.5°	589.7	607.1	625.7	647.1	669.2	689.4	707.2	727.7	744.6	763.2	784.2
15°	582.2	605.6	631.0	658.6	685.2	712.4	736.7	761.8	785.3	807.5	834.0
17.5°	573.6	600.6	630.5	663.2	695.0	728.1	757.1	788.7	812.6	842.5	867.1
20°	566.6	595.7	627.6	664.3	700.5	737.2	769.2	801.4	828.3	858.4	889.6
22.5°	558.1	590.0	624.6	662.6	700.5	740.6	776.0	808.0	841.4	875.2	907.4
25°	544.3	577.5	614.2	655.8	699.4	740.3	778.2	817.9	853.9	890.6	919.5
27.5°	527.5	562.3	600.9	643.9	688.6	730.5	775.1	817.5	853.7	889.0	914.2
30°	514.0	550.7	587.9	631.4	677.8	722.8	770.6	813.0	851.1	882.8	897.0
32.5°	500.2	535.0	573.3	617.4	664.9	713.3	760.7	804.1	839.3	858.3	858.7
35°	476.2	508.8	548.6	591.9	640.7	693.2	741.2	783.8	805.4	807.0	783.8
37.5°	450.0	479.9	517.4	560.8	614.2	666.5	715.5	743.9	751.1	727.0	684.2
40°	431.2	458.9	495.1	539.6	592.6	646.6	691.3	712.1	704.6	665.5	617.7
42.5°	411.5	437.3	472.2	516.1	569.3	623.9	662.0	673.1	653.1	608.0	552.0
45°	379.4	403.0	437.6	481.9	533.0	584.1	613.0	607.3	573.9	520.4	457.7
47.5°	345.9	368.8	399.9	440.8	493.2	537.3	556.8	539.7	492.2	433.4	382.4
50°	323.8	347.2	375.8	414.9	462.7	505.3	517.8	491.8	439.0	382.5	335.6
52.5°	302.0	322.0	350.1	387.8	433.5	469.5	476.2	446.2	391.7	341.0	299.4
55°	268.9	287.1	310.7	346.2	385.8	416.3	412.7	374.2	324.7	281.4	248.7
57.5°	236.8	250.5	272.4	305.7	340.4	360.9	347.9	315.0	268.9	233.4	205.9
60°	215.6	228.4	248.7	277.8	308.4	320.0	309.1	273.4	236.9	204.5	181.3
62.5°	195.5	206.8	224.3	251.3	276.0	282.9	271.2	240.0	207.2	179.5	160.3
65°	166.4	176.8	191.7	210.9	227.9	231.2	223.7	191.7	166.9	143.7	130.4
67.5°	139.9	146.7	158.4	174.9	184.0	185.9	171.3	151.2	129.3	115.1	105.1
70°	122.1	126.9	137.7	146.7	154.1	154.3	140.8	124.7	107.9	96.3	89.0
72.5°	104.9	109.4	117.7	123.8	129.5	127.6	115.3	102.6	89.0	80.2	74.8
75°	80.9	85.0	89.2	92.1	92.1	89.7	80.7	71.2	63.4	58.2	56.6
77.5°	58.8	62.1	63.6	63.1	62.3	58.6	52.9	46.7	43.9	41.5	40.2
80°	46.2	47.6	48.0	46.9	45.4	41.2	37.4	34.8	32.2	31.2	30.8
82.5°	34.2	35.5	34.2	34.6	31.4	27.9	25.8	24.9	23.9	23.5	23.0
85°	18.2	18.0	17.5	16.3	14.2	13.7	13.5	13.3	12.8	13.0	12.5
87.5°	7.7	7.7	7.6	8.0	8.6	8.7	9.3	9.8	10.3	10.4	11.1
90°	7.1	10.2	13.4	16.6	19.3	21.6	23.9	26.2	28.5	30.3	32.0
92.5°	31.4	35.0	38.6	42.3	44.9	46.5	48.1	49.7	51.4	52.4	53.4
95°	80.4	83.0	85.6	88.2	90.5	92.5	94.5	96.5	98.6	99.4	100.3
97.5°	138.0	140.1	142.1	144.2	146.4	148.8	151.2	153.5	155.9	156.9	158.0
100°	182.7	183.9	185.0	186.2	188.0	190.6	193.2	195.8	198.4	199.0	199.6
102.5°	229.8	230.2	230.7	231.1	232.5	234.9	237.3	239.6	242.0	242.8	243.6
105°	302.5	302.8	303.0	303.3	304.0	305.2	306.4	307.5	308.7	309.5	310.4
107.5°	379.0	379.4	379.7	380.1	380.3	380.5	380.7	380.9	381.0	381.8	382.6
110°	431.1	431.7	432.3	432.9	433.0	432.7	432.4	432.2	431.9	431.3	430.7



TEST NUMBER: P333028

CATALOG NUMBER: S124RDIW-S350D1340U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	484.6	484.7	484.9	485.0	484.8	484.3	483.7	483.2	482.7	482.6	482.5
115°	565.4	565.4	565.4	565.4	565.2	564.6	564.0	563.4	562.8	562.6	562.3
117.5°	641.9	642.2	642.4	642.6	642.5	642.1	641.7	641.3	640.9	639.9	639.0
120°	693.7	694.8	696.0	697.1	697.3	696.4	695.6	694.7	693.8	692.4	691.0
122.5°	745.9	746.4	746.8	747.3	747.3	746.9	746.5	746.1	745.7	744.7	743.7
125°	823.5	823.5	823.5	823.5	823.4	823.1	822.8	822.5	822.2	821.6	821.1
127.5°	895.2	896.1	896.9	897.8	898.0	897.5	897.1	896.6	896.1	895.6	895.0
130°	945.0	945.9	946.7	947.6	948.0	948.0	948.0	948.0	948.0	947.4	946.9
132.5°	995.6	996.2	996.9	997.5	997.7	997.5	997.2	997.0	996.8	996.2	995.6
135°	1063.9	1065.6	1067.3	1069.1	1069.9	1069.9	1069.9	1069.9	1069.9	1069.4	1068.8
137.5°	1136.1	1136.9	1137.7	1138.5	1139.2	1139.6	1140.1	1140.5	1141.0	1140.2	1139.5
140°	1184.6	1185.2	1185.8	1186.4	1186.6	1186.6	1186.6	1186.6	1186.6	1186.4	1186.1
142.5°	1229.2	1229.8	1230.4	1231.0	1231.1	1230.9	1230.7	1230.5	1230.2	1230.2	1230.1
145°	1291.6	1292.7	1293.9	1295.0	1295.7	1296.0	1296.3	1296.6	1296.9	1296.6	1296.3
147.5°	1353.0	1354.4	1355.8	1357.1	1357.7	1357.5	1357.3	1357.0	1356.8	1356.6	1356.3
150°	1390.1	1391.3	1392.4	1393.6	1394.1	1394.1	1394.1	1394.1	1394.1	1394.1	1394.1
152.5°	1424.9	1425.6	1426.3	1427.0	1427.5	1427.7	1427.9	1428.2	1428.4	1429.1	1429.8
155°	1478.4	1478.4	1478.4	1478.4	1478.3	1478.0	1477.7	1477.4	1477.2	1478.3	1479.5
157.5°	1523.6	1523.1	1522.5	1522.0	1521.7	1521.7	1521.6	1521.6	1521.5	1522.4	1523.2
160°	1550.8	1550.5	1550.2	1549.9	1549.6	1549.3	1549.1	1548.8	1548.5	1549.3	1550.2
162.5°	1575.2	1574.5	1573.7	1573.0	1572.5	1572.2	1571.9	1571.6	1571.3	1572.9	1574.4
165°	1608.6	1607.7	1606.8	1606.0	1605.3	1604.7	1604.1	1603.5	1602.9	1604.7	1606.4
167.5°	1633.9	1632.7	1631.5	1630.3	1629.7	1629.8	1629.8	1629.9	1629.9	1631.7	1633.4
170°	1648.2	1646.8	1645.3	1643.9	1643.3	1643.6	1643.9	1644.2	1644.4	1646.2	1647.9
172.5°	1658.8	1657.6	1656.4	1655.2	1654.6	1654.7	1654.7	1654.8	1654.8	1656.8	1658.7
175°	1672.8	1671.4	1670.0	1668.5	1667.6	1667.4	1667.1	1666.8	1666.5	1668.5	1670.5
177.5°	1677.8	1676.6	1675.5	1674.3	1673.8	1673.8	1673.8	1673.8	1673.8	1675.4	1677.0
180°	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9



TEST NUMBER: P333028

CATALOG NUMBER: S124RDIW-S350D1340U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	587.4	587.4	587.4	587.4	587.4	587.4	587.4
2.5°	616.2	616.9	617.5	619.4	619.6	621.3	619.6
5°	667.2	670.5	675.7	680.9	681.4	684.7	678.8
7.5°	724.3	732.0	736.8	745.2	748.5	750.6	747.2
10°	763.7	770.8	783.4	789.5	795.7	796.6	793.8
12.5°	801.8	813.0	822.9	834.6	834.3	842.6	839.6
15°	852.5	864.1	877.8	890.8	895.5	895.5	899.3
17.5°	888.6	909.9	924.1	934.3	945.5	947.4	946.1
20°	913.1	936.0	951.2	964.4	972.0	974.1	974.1
22.5°	931.2	950.8	965.6	977.5	983.7	986.2	985.5
25°	943.8	960.6	969.6	973.2	974.8	974.4	969.9
27.5°	926.6	925.8	920.2	909.3	901.1	896.1	890.4
30°	893.7	881.3	867.1	851.5	831.4	816.0	811.3
32.5°	844.6	817.0	792.9	766.9	745.3	729.9	723.4
35°	749.8	706.0	670.2	639.0	616.3	602.1	597.3
37.5°	637.2	594.8	550.6	520.3	501.4	487.1	481.8
40°	565.6	519.5	480.9	452.5	433.1	419.1	418.9
42.5°	500.3	456.2	419.9	399.5	378.6	369.3	369.3
45°	409.7	374.4	343.6	327.5	315.0	307.4	305.3
47.5°	339.2	310.0	289.5	276.7	266.5	261.7	258.5
50°	299.6	274.1	257.7	246.6	240.9	234.8	234.3
52.5°	266.7	246.0	233.3	224.3	217.1	213.4	213.5
55°	224.1	207.8	198.8	191.9	186.3	183.4	182.2
57.5°	188.8	176.6	170.0	163.7	161.3	159.1	158.5
60°	166.9	158.6	152.4	147.4	143.9	143.2	142.9
62.5°	148.7	140.0	135.8	131.9	129.3	128.2	127.8
65°	122.6	116.2	112.4	109.3	108.4	106.7	106.5
67.5°	98.8	95.0	92.5	90.4	89.1	89.0	89.0
70°	84.3	82.1	80.0	78.8	78.1	77.6	77.6
72.5°	71.8	70.2	68.4	67.8	67.7	67.2	67.0
75°	54.7	53.0	53.3	52.1	51.1	49.9	49.2
77.5°	38.8	37.6	37.3	37.2	36.4	36.3	36.6
80°	30.1	28.9	28.6	28.9	28.6	27.9	27.9
82.5°	22.9	21.9	21.6	21.5	21.3	21.5	21.1
85°	12.3	11.8	11.8	11.8	12.3	12.1	11.8
87.5°	11.1	11.3	11.7	11.6	11.7	11.6	11.9
90°	33.7	35.4	36.6	37.2	37.8	38.3	38.9
92.5°	54.5	55.5	56.2	56.5	56.9	57.2	57.6
95°	101.2	102.0	102.5	102.5	102.5	102.5	102.5
97.5°	159.0	160.0	160.6	160.6	160.6	160.6	160.6
100°	200.2	200.7	201.0	201.0	201.0	201.0	201.0
102.5°	244.4	245.2	245.7	246.0	246.2	246.4	246.7
105°	311.3	312.1	313.0	313.8	314.7	315.6	316.4
107.5°	383.4	384.3	384.6	384.6	384.5	384.5	384.4
110°	430.1	429.6	429.7	430.6	431.4	432.3	433.2



TEST NUMBER: P333028

CATALOG NUMBER: S124RDIW-S350D1340U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	482.4	482.2	482.3	482.4	482.6	482.8	483.0
115°	562.0	561.7	561.4	561.1	560.8	560.5	560.3
117.5°	638.0	637.0	636.2	635.6	635.1	634.5	633.9
120°	689.5	688.1	687.6	688.2	688.8	689.4	689.9
122.5°	742.8	741.8	740.8	739.7	738.7	737.7	736.6
125°	820.5	819.9	819.3	818.8	818.2	817.6	817.0
127.5°	894.4	893.8	893.3	892.9	892.4	891.9	891.5
130°	946.3	945.7	944.9	943.7	942.5	941.4	940.2
132.5°	995.1	994.5	994.0	993.5	993.0	992.6	992.1
135°	1068.2	1067.6	1066.9	1066.0	1065.2	1064.3	1063.4
137.5°	1138.8	1138.0	1137.7	1137.9	1138.1	1138.2	1138.4
140°	1185.8	1185.5	1185.2	1184.9	1184.6	1184.3	1184.1
142.5°	1230.1	1230.0	1229.9	1229.9	1229.8	1229.8	1229.7
145°	1296.0	1295.7	1295.2	1294.3	1293.4	1292.6	1291.7
147.5°	1356.1	1355.9	1355.6	1355.3	1355.0	1354.8	1354.5
150°	1394.1	1394.1	1394.0	1393.7	1393.4	1393.1	1392.9
152.5°	1430.5	1431.2	1431.1	1430.4	1429.6	1428.9	1428.1
155°	1480.6	1481.8	1481.8	1480.6	1479.5	1478.3	1477.2
157.5°	1524.1	1525.0	1524.9	1523.9	1522.9	1522.0	1521.0
160°	1551.1	1551.9	1551.6	1550.2	1548.8	1547.3	1545.9
162.5°	1576.0	1577.5	1577.6	1576.1	1574.7	1573.3	1571.8
165°	1608.1	1609.9	1610.2	1609.0	1607.8	1606.7	1605.5
167.5°	1635.1	1636.8	1636.8	1635.0	1633.2	1631.5	1629.7
170°	1649.6	1651.4	1651.2	1649.2	1647.2	1645.2	1643.2
172.5°	1660.7	1662.7	1662.6	1660.6	1658.6	1656.6	1654.6
175°	1672.5	1674.6	1674.6	1672.5	1670.5	1668.5	1666.5
177.5°	1678.6	1680.2	1680.1	1678.3	1676.4	1674.6	1672.7
180°	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9

(END OF REPORT)