

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333029

Luminaire Tested: **S124RDIW-S350D1340U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333029
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S350D1340U835-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1340 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6797.5 lumens
Efficiency: N/A
Efficacy: 145.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 46.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333029

CATALOG NUMBER: S124RDIW-S350D1340U835-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333029

CATALOG NUMBER: S124RDIW-S350D1340U835-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	100	100	100	100	89	89	89	89	67	67	67	48	48	48	30	30	30	21
1	91	87	84	80	81	77	74	72	59	57	55	42	41	40	26	26	25	18
2	83	76	71	66	73	68	63	59	52	48	46	37	35	33	23	22	21	15
3	76	67	60	55	67	60	54	49	46	42	38	33	30	28	21	19	18	13
4	69	59	52	46	61	53	46	42	40	36	33	29	26	24	18	17	16	11
5	64	53	45	39	56	47	40	36	36	32	28	26	23	21	17	15	14	10
6	58	47	39	34	52	42	35	31	32	28	24	23	20	18	15	13	12	9
7	54	42	35	30	48	38	31	27	29	25	21	21	18	16	14	12	11	8
8	50	38	31	26	44	34	28	24	27	22	19	19	16	14	13	11	10	7
9	46	35	28	23	41	31	25	21	24	20	17	18	15	13	12	10	9	6
10	43	32	25	20	38	28	23	19	22	18	15	16	13	11	11	9	8	6

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4991	4991	4991
5°	5002	4941	4971
10°	4970	4882	4882
15°	4914	4779	4743
20°	4835	4643	4558
25°	4735	4486	4372
30°	4638	4320	4139
35°	4529	4147	3905
40°	4400	3951	3652
45°	4280	3756	3394
50°	4143	3532	3121
55°	3997	3298	2825
60°	3836	3042	2522
65°	3689	2722	2223
70°	3474	2367	1888
75°	3203	1965	1535
80°	2794	1497	1409
85°	2371	1362	1269



TEST NUMBER: P333029

CATALOG NUMBER: S124RDIW-S350D1340U835-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	58.1	0.9
10°-20°	161.9	2.4
20°-30°	233.8	3.4
30°-40°	265.1	3.9
40°-50°	255.9	3.8
50°-60°	212.8	3.1
60°-70°	147.0	2.2
70°-80°	74.5	1.1
80°-90°	24.1	0.4
90°-100°	59.3	0.9
100°-110°	378.2	5.6
110°-120°	723.4	10.6
120°-130°	918.4	13.5
130°-140°	982.6	14.5
140°-150°	918.8	13.5
150°-160°	741.0	10.9
160°-170°	477.9	7.0
170°-180°	164.7	2.4
0°-30°	453.8	6.7
0°-40°	718.9	10.6
0°-60°	1187.7	17.5
0°-90°	1433.2	21.1
90°-120°	1160.9	17.1
90°-150°	3980.7	58.6
90°-180°	5364.0	78.9
0°-180°	6797.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	618	618	618	618	618	
5°	617	615	610	614	613	59
15°	588	583	572	571	568	166
25°	532	522	504	496	491	245
35°	460	444	421	405	396	287
45°	375	357	329	307	297	289
55°	284	264	234	211	201	254
65°	193	172	142	123	116	191
75°	103	85	63	53	49	108
85°	26	16	15	14	14	29
90°	4	18	28	36	39	5
95°	71	30	28	36	38	92
105°	390	398	405	413	370	408
115°	729	733	732	734	734	717
125°	1025	1029	1027	1031	1032	914
135°	1271	1270	1275	1278	1280	979
145°	1466	1469	1470	1471	1474	916
155°	1607	1608	1604	1609	1606	741
165°	1695	1689	1689	1698	1688	479
175°	1734	1727	1728	1738	1724	165
180°	1734	1734	1734	1734	1734	



TEST NUMBER: P333029

CATALOG NUMBER: S124RDIW-S350D1340U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	618.2	618.2	618.2	618.2	618.2	618.2	618.2	618.2	618.2	618.2	618.2
2.5°	619.7	619.3	619.0	618.7	618.3	617.7	616.8	615.9	614.9	614.0	614.9
5°	617.2	616.8	616.4	616.0	615.5	614.7	613.4	612.2	610.9	609.7	610.7
7.5°	611.6	611.2	610.8	610.3	609.9	608.8	607.2	605.5	603.9	602.3	602.9
10°	606.3	605.8	605.3	604.8	604.2	603.0	601.1	599.2	597.3	595.5	595.9
12.5°	599.5	598.9	598.3	597.7	597.1	595.7	593.4	591.2	589.0	586.7	587.0
15°	587.9	586.9	586.0	585.0	584.1	582.3	579.7	577.0	574.4	571.8	571.6
17.5°	573.8	572.4	571.0	569.7	568.3	566.0	562.9	559.7	556.6	553.4	552.8
20°	562.8	561.4	560.1	558.7	557.3	554.9	551.3	547.7	544.1	540.5	539.7
22.5°	550.7	549.1	547.6	546.1	544.5	541.8	538.0	534.2	530.4	526.5	525.3
25°	531.6	529.7	527.8	525.9	524.0	520.9	516.6	512.3	507.9	503.6	501.8
27.5°	511.5	509.1	506.7	504.4	502.0	498.5	493.9	489.3	484.7	480.1	477.8
30°	497.5	494.8	492.2	489.6	487.0	483.2	478.2	473.3	468.3	463.4	460.8
32.5°	482.7	479.7	476.8	473.8	470.8	466.8	461.7	456.6	451.5	446.4	443.3
35°	459.6	456.2	452.9	449.5	446.1	441.8	436.6	431.3	426.1	420.8	417.2
37.5°	434.9	431.4	428.0	424.5	421.0	416.4	410.5	404.7	398.9	393.1	389.1
40°	417.5	414.0	410.5	407.1	403.6	398.9	392.9	386.9	380.9	374.9	370.5
42.5°	400.8	397.2	393.5	389.9	386.3	381.3	375.1	368.8	362.6	356.3	351.8
45°	374.9	371.0	367.1	363.2	359.3	354.2	347.9	341.6	335.3	329.0	323.8
47.5°	348.1	344.1	340.1	336.0	332.0	326.7	320.2	313.6	307.0	300.5	295.1
50°	329.9	325.8	321.7	317.6	313.5	308.1	301.4	294.6	287.9	281.2	275.9
52.5°	311.4	307.3	303.3	299.3	295.3	289.8	282.9	276.0	269.1	262.2	256.9
55°	284.0	279.8	275.6	271.4	267.2	261.6	254.8	248.0	241.1	234.3	228.8
57.5°	256.9	252.5	248.2	243.8	239.4	233.9	227.1	220.4	213.7	206.9	201.4
60°	237.6	233.4	229.2	225.0	220.8	215.3	208.6	201.8	195.1	188.4	182.9
62.5°	220.2	215.8	211.4	207.1	202.7	197.1	190.2	183.3	176.4	169.5	164.4
65°	193.1	188.6	184.1	179.6	175.0	169.4	162.7	155.9	149.2	142.5	138.0
67.5°	165.0	160.7	156.3	152.0	147.7	142.4	136.1	129.9	123.6	117.4	113.5
70°	147.2	142.8	138.4	134.0	129.5	124.3	118.3	112.3	106.3	100.3	96.9
72.5°	128.3	124.3	120.3	116.3	112.3	107.5	101.8	96.1	90.5	84.8	81.9
75°	102.7	98.8	94.9	91.0	87.1	82.7	77.8	72.8	67.9	63.0	60.5
77.5°	76.8	73.5	70.2	66.9	63.6	59.9	55.9	51.9	47.9	43.9	42.5
80°	60.1	57.1	54.0	51.0	47.9	44.8	41.7	38.5	35.3	32.2	31.9
82.5°	45.7	42.9	40.1	37.3	34.5	32.2	30.4	28.6	26.8	25.0	24.8
85°	25.6	23.5	21.4	19.2	17.1	15.9	15.6	15.3	15.0	14.7	14.5
87.5°	9.5	9.4	9.4	9.4	9.3	9.5	9.9	10.3	10.6	11.0	11.3
90°	3.9	7.1	10.2	13.4	16.6	19.3	21.6	23.9	26.2	28.5	30.3
92.5°	16.3	16.5	16.7	16.9	17.0	18.3	20.6	22.9	25.2	27.5	29.2
95°	71.3	61.5	51.7	41.9	32.1	27.4	27.7	28.0	28.2	28.5	30.3
97.5°	151.5	157.6	163.7	169.8	175.9	162.9	130.7	98.6	66.4	34.2	34.4
100°	212.7	217.9	223.1	228.3	233.5	216.2	176.4	136.6	96.8	57.1	52.2
102.5°	281.2	285.0	288.8	292.6	296.4	295.7	290.5	285.4	280.2	275.0	222.1
105°	390.4	392.1	393.9	395.6	397.3	398.9	400.4	401.8	403.2	404.7	407.3
107.5°	491.8	492.7	493.6	494.4	495.3	496.7	498.7	500.6	502.6	504.6	505.8
110°	560.3	561.2	562.1	562.9	563.8	565.1	566.8	568.5	570.3	572.0	572.6



TEST NUMBER: P333029

CATALOG NUMBER: S124RDIW-S350D1340U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	626.7	628.3	629.9	631.4	633.0	634.1	635.0	635.8	636.6	637.4	637.3
115°	728.9	729.8	730.7	731.5	732.4	732.7	732.4	732.1	731.8	731.5	732.1
117.5°	821.0	822.2	823.3	824.5	825.6	826.5	827.2	827.8	828.4	829.1	829.0
120°	883.3	884.4	885.6	886.8	887.9	888.3	888.1	887.8	887.5	887.2	887.8
122.5°	941.4	942.1	942.8	943.5	944.2	944.7	945.1	945.5	945.9	946.3	946.7
125°	1024.7	1025.8	1027.0	1028.1	1029.3	1029.6	1029.0	1028.4	1027.8	1027.3	1028.1
127.5°	1103.5	1103.8	1104.1	1104.4	1104.7	1105.5	1106.8	1108.1	1109.5	1110.8	1110.6
130°	1154.4	1154.7	1155.0	1155.2	1155.5	1156.1	1157.0	1157.8	1158.7	1159.6	1159.9
132.5°	1201.1	1201.6	1202.1	1202.6	1203.1	1204.0	1205.1	1206.1	1207.2	1208.3	1208.6
135°	1271.1	1270.8	1270.5	1270.3	1270.0	1270.4	1271.5	1272.7	1273.9	1275.0	1275.6
137.5°	1333.1	1333.2	1333.3	1333.5	1333.6	1334.3	1335.5	1336.8	1338.1	1339.3	1340.0
140°	1373.6	1374.2	1374.7	1375.3	1375.9	1376.5	1377.0	1377.6	1378.2	1378.8	1379.6
142.5°	1409.9	1410.9	1412.0	1413.0	1414.1	1414.7	1415.1	1415.4	1415.8	1416.1	1416.8
145°	1465.7	1466.5	1467.4	1468.3	1469.1	1469.6	1469.6	1469.6	1469.6	1469.6	1469.9
147.5°	1510.0	1511.6	1513.3	1514.9	1516.5	1517.2	1516.9	1516.6	1516.3	1516.0	1516.2
150°	1542.2	1543.4	1544.5	1545.7	1546.8	1547.2	1547.0	1546.7	1546.4	1546.1	1546.1
152.5°	1569.2	1570.1	1571.0	1571.9	1572.9	1573.1	1572.6	1572.0	1571.5	1571.0	1571.5
155°	1607.1	1607.3	1607.6	1607.9	1608.2	1607.9	1607.1	1606.2	1605.3	1604.5	1605.6
157.5°	1639.0	1638.8	1638.6	1638.4	1638.3	1637.7	1636.7	1635.7	1634.8	1633.8	1635.3
160°	1657.6	1656.8	1655.9	1655.0	1654.2	1653.6	1653.3	1653.0	1652.7	1652.5	1654.2
162.5°	1674.2	1673.1	1672.1	1671.0	1669.9	1669.2	1668.9	1668.6	1668.3	1668.0	1669.7
165°	1695.3	1693.8	1692.4	1690.9	1689.5	1688.8	1688.8	1688.8	1688.8	1688.8	1691.1
167.5°	1711.9	1710.4	1708.9	1707.4	1705.9	1705.0	1704.9	1704.7	1704.5	1704.3	1706.9
170°	1721.2	1719.5	1717.7	1716.0	1714.3	1713.6	1713.8	1714.1	1714.4	1714.7	1717.0
172.5°	1727.4	1725.7	1724.0	1722.2	1720.5	1719.8	1720.1	1720.4	1720.6	1720.9	1723.2
175°	1734.2	1732.4	1730.7	1729.0	1727.2	1726.5	1726.8	1727.1	1727.4	1727.7	1730.3
177.5°	1737.3	1735.7	1734.0	1732.4	1730.8	1730.2	1730.7	1731.2	1731.6	1732.1	1733.9
180°	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2



TEST NUMBER: P333029

CATALOG NUMBER: S124RDIW-S350D1340U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	618.2	618.2	618.2	618.2	618.2	618.2	618.2	618.2
2.5°	615.9	616.8	617.7	618.1	618.0	618.0	617.9	617.8
5°	611.8	612.8	613.9	614.3	614.1	613.9	613.6	613.4
7.5°	603.6	604.3	605.0	605.1	604.8	604.5	604.1	603.8
10°	596.3	596.7	597.1	597.1	596.7	596.3	595.9	595.5
12.5°	587.2	587.5	587.8	587.6	587.0	586.4	585.8	585.2
15°	571.4	571.2	570.9	570.5	569.7	569.0	568.3	567.5
17.5°	552.2	551.7	551.1	550.2	549.1	548.0	546.9	545.8
20°	538.9	538.0	537.2	536.1	534.7	533.3	532.0	530.6
22.5°	524.0	522.7	521.5	520.3	519.2	518.1	517.0	515.8
25°	500.0	498.3	496.5	495.1	494.0	492.9	491.9	490.8
27.5°	475.6	473.4	471.2	469.4	467.8	466.3	464.8	463.3
30°	458.1	455.5	452.9	450.7	449.0	447.4	445.7	444.0
32.5°	440.3	437.2	434.2	431.8	430.2	428.6	427.0	425.4
35°	413.6	410.1	406.5	403.8	401.9	400.0	398.1	396.2
37.5°	385.1	381.1	377.1	374.1	372.2	370.3	368.4	366.5
40°	366.0	361.6	357.2	354.1	352.2	350.3	348.4	346.5
42.5°	347.3	342.8	338.3	335.1	333.1	331.1	329.1	327.2
45°	318.7	313.5	308.3	304.8	302.9	301.0	299.1	297.3
47.5°	289.8	284.4	279.1	275.4	273.3	271.2	269.1	267.1
50°	270.6	265.4	260.1	256.5	254.5	252.5	250.5	248.5
52.5°	251.5	246.2	240.9	237.1	235.1	233.0	230.9	228.8
55°	223.4	217.9	212.4	208.7	206.7	204.7	202.7	200.7
57.5°	195.8	190.3	184.7	181.2	179.7	178.2	176.6	175.1
60°	177.4	172.0	166.5	162.9	161.2	159.6	157.9	156.2
62.5°	159.4	154.3	149.3	146.1	144.7	143.4	142.0	140.7
65°	133.4	128.9	124.4	121.5	120.2	119.0	117.7	116.4
67.5°	109.6	105.7	101.8	99.2	97.8	96.4	95.0	93.6
70°	93.4	89.9	86.5	84.2	83.1	82.1	81.0	80.0
72.5°	78.9	75.9	73.0	71.0	70.0	69.1	68.1	67.1
75°	58.1	55.7	53.3	51.8	51.1	50.5	49.9	49.2
77.5°	41.1	39.7	38.3	37.5	37.3	37.1	36.9	36.7
80°	31.6	31.2	30.9	30.7	30.6	30.5	30.4	30.3
82.5°	24.5	24.3	24.1	23.9	23.8	23.7	23.6	23.5
85°	14.3	14.0	13.8	13.7	13.7	13.7	13.7	13.7
87.5°	11.5	11.8	12.1	12.3	12.5	12.7	12.9	13.1
90°	32.0	33.7	35.5	36.6	37.2	37.8	38.3	38.9
92.5°	31.0	32.7	34.4	35.3	35.5	35.6	35.7	35.8
95°	32.0	33.7	35.5	36.5	36.7	37.0	37.3	37.6
97.5°	34.6	34.8	34.9	35.2	35.5	35.7	36.0	36.3
100°	47.3	42.4	37.5	35.2	35.5	35.7	36.0	36.3
102.5°	169.3	116.4	63.5	37.1	37.2	37.2	37.3	37.4
105°	409.9	412.5	415.1	411.2	400.8	390.4	380.0	369.7
107.5°	507.1	508.4	509.6	510.8	511.9	513.0	514.1	515.2
110°	573.2	573.7	574.3	575.0	575.9	576.8	577.6	578.5



TEST NUMBER: P333029

CATALOG NUMBER: S124RDIW-S350D1340U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	637.1	637.0	636.9	637.4	638.5	639.6	640.7	641.8
115°	732.7	733.3	733.8	734.1	734.1	734.1	734.1	734.1
117.5°	828.8	828.7	828.6	828.5	828.4	828.3	828.2	828.0
120°	888.3	888.9	889.5	889.5	888.9	888.3	887.8	887.2
122.5°	947.0	947.4	947.7	947.6	947.0	946.4	945.9	945.3
125°	1029.0	1029.9	1030.7	1031.3	1031.6	1031.9	1032.2	1032.5
127.5°	1110.5	1110.3	1110.1	1109.9	1109.7	1109.4	1109.2	1109.0
130°	1160.1	1160.4	1160.7	1160.9	1160.9	1160.9	1160.9	1160.9
132.5°	1208.9	1209.2	1209.5	1209.5	1209.3	1209.1	1208.8	1208.6
135°	1276.2	1276.7	1277.3	1277.9	1278.5	1279.0	1279.6	1280.2
137.5°	1340.6	1341.2	1341.9	1342.1	1341.9	1341.8	1341.6	1341.4
140°	1380.5	1381.4	1382.2	1382.8	1383.1	1383.4	1383.7	1384.0
142.5°	1417.4	1418.0	1418.7	1419.0	1419.1	1419.1	1419.2	1419.2
145°	1470.1	1470.4	1470.7	1471.2	1471.7	1472.3	1472.9	1473.5
147.5°	1516.5	1516.7	1516.9	1517.2	1517.5	1517.8	1518.0	1518.3
150°	1546.1	1546.1	1546.1	1546.2	1546.5	1546.8	1547.1	1547.4
152.5°	1571.9	1572.4	1572.8	1573.0	1572.8	1572.6	1572.5	1572.3
155°	1606.8	1607.9	1609.1	1609.2	1608.4	1607.5	1606.6	1605.8
157.5°	1636.8	1638.3	1639.8	1639.8	1638.3	1636.8	1635.3	1633.8
160°	1655.9	1657.6	1659.4	1659.4	1657.6	1655.9	1654.2	1652.5
162.5°	1671.5	1673.2	1674.9	1674.8	1672.9	1670.9	1668.9	1667.0
165°	1693.4	1695.7	1698.0	1697.8	1695.3	1692.7	1690.1	1687.5
167.5°	1709.4	1711.9	1714.5	1714.3	1711.4	1708.5	1705.7	1702.8
170°	1719.3	1721.6	1723.9	1723.6	1720.8	1717.9	1715.0	1712.1
172.5°	1725.5	1727.9	1730.2	1729.8	1726.6	1723.5	1720.4	1717.3
175°	1732.9	1735.5	1738.1	1737.6	1734.2	1730.7	1727.2	1723.8
177.5°	1735.8	1737.6	1739.5	1739.0	1736.2	1733.5	1730.7	1727.9
180°	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2

(END OF REPORT)