

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333026-927

Luminaire Tested: **S124RDIW-S350D1050U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333026-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S350D1050U927-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1050 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4013.4 lumens
Efficiency: N/A
Efficacy: 105.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 38
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333026-927

CATALOG NUMBER: S124RDIW-S350D1050U927-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333026-927

CATALOG NUMBER: S124RDIW-S350D1050U927-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36	28				
1	93	89	85	82	83	80	77	74	63	60	59	47	45	44	32	31	31	24				
2	85	78	72	67	76	70	65	61	55	52	49	41	39	37	28	27	26	20				
3	77	68	61	56	69	62	56	51	49	44	41	36	34	32	25	24	22	17				
4	71	61	53	47	63	54	48	43	43	39	35	33	29	27	23	21	19	15				
5	65	54	46	40	58	49	42	37	39	34	30	29	26	23	20	18	17	13				
6	60	48	40	35	53	44	37	32	35	30	26	26	23	20	19	17	15	12				
7	55	43	36	30	49	39	33	28	31	26	23	24	21	18	17	15	13	10				
8	51	39	32	27	46	36	29	25	28	24	20	22	18	16	16	13	12	9				
9	47	36	29	24	42	32	26	22	26	21	18	20	17	14	14	12	11	8				
10	44	33	26	21	40	30	24	20	24	19	16	18	15	13	13	11	10	8				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3953	3953	3953
5°	3962	3914	3938
10°	3937	3867	3867
15°	3892	3786	3758
20°	3830	3679	3611
25°	3751	3553	3463
30°	3674	3422	3278
35°	3588	3286	3094
40°	3485	3130	2893
45°	3391	2975	2689
50°	3282	2798	2473
55°	3167	2612	2238
60°	3039	2409	1997
65°	2923	2157	1761
70°	2752	1876	1496
75°	2539	1556	1216
80°	2213	1186	1116
85°	1880	1074	1010



TEST NUMBER: P333026-927

CATALOG NUMBER: S124RDIW-S350D1050U927-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.0	1.1
10°-20°	128.3	3.2
20°-30°	185.2	4.6
30°-40°	210.0	5.2
40°-50°	202.8	5.1
50°-60°	168.6	4.2
60°-70°	116.4	2.9
70°-80°	59.0	1.5
80°-90°	18.2	0.5
90°-100°	68.4	1.7
100°-110°	202.7	5.1
110°-120°	344.1	8.6
120°-130°	453.7	11.3
130°-140°	509.6	12.7
140°-150°	500.8	12.5
150°-160°	421.2	10.5
160°-170°	280.2	7.0
170°-180°	98.1	2.4
0°-30°	359.5	9.0
0°-40°	569.5	14.2
0°-60°	940.8	23.4
0°-90°	1134.5	28.3
90°-120°	615.3	15.3
90°-150°	2079.4	51.8
90°-180°	2879.0	71.7
0°-180°	4013.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	490	490	490	490	490	
5°	489	487	483	486	486	46
15°	466	462	453	452	450	131
25°	421	414	399	393	389	194
35°	364	352	333	321	314	227
45°	297	283	261	243	236	229
55°	225	209	186	167	159	201
65°	153	136	113	97	92	151
75°	81	67	50	42	39	86
85°	20	13	12	11	11	23
90°	2	11	18	22	24	4
95°	48	55	61	63	63	54
105°	187	188	191	193	196	198
115°	350	350	348	348	347	345
125°	510	510	509	507	506	454
135°	657	662	662	660	658	508
145°	798	802	802	802	799	500
155°	915	915	914	917	914	421
165°	996	994	992	996	994	281
175°	1036	1032	1031	1036	1031	98
180°	1038	1038	1038	1038	1038	



TEST NUMBER: P333026-927

CATALOG NUMBER: S124RDIW-S350D1050U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	489.7	489.7	489.7	489.7	489.7	489.7	489.7	489.7	489.7	489.7	489.7
2.5°	490.9	490.6	490.4	490.1	489.8	489.3	488.6	487.9	487.1	486.4	487.1
5°	488.9	488.6	488.3	488.0	487.6	487.0	485.9	485.0	483.9	483.0	483.8
7.5°	484.5	484.2	483.9	483.5	483.2	482.3	481.0	479.7	478.4	477.1	477.6
10°	480.3	479.9	479.5	479.1	478.6	477.7	476.2	474.7	473.2	471.7	472.1
12.5°	474.9	474.4	474.0	473.5	473.0	471.9	470.1	468.3	466.6	464.8	465.0
15°	465.7	464.9	464.2	463.4	462.7	461.3	459.2	457.1	455.0	453.0	452.8
17.5°	454.6	453.4	452.3	451.3	450.2	448.4	445.9	443.4	440.9	438.4	437.9
20°	445.8	444.7	443.7	442.6	441.5	439.6	436.7	433.9	431.0	428.2	427.5
22.5°	436.3	435.0	433.8	432.6	431.3	429.2	426.2	423.2	420.2	417.1	416.1
25°	421.1	419.6	418.1	416.6	415.1	412.6	409.2	405.8	402.3	398.9	397.5
27.5°	405.2	403.3	401.4	399.6	397.7	394.9	391.3	387.6	384.0	380.3	378.5
30°	394.1	392.0	389.9	387.9	385.8	382.8	378.8	374.9	371.0	367.1	365.0
32.5°	382.4	380.0	377.7	375.3	373.0	369.8	365.8	361.7	357.7	353.6	351.2
35°	364.1	361.4	358.8	356.1	353.4	350.0	345.9	341.7	337.5	333.4	330.5
37.5°	344.5	341.7	339.1	336.3	333.5	329.9	325.2	320.6	316.0	311.4	308.2
40°	330.7	328.0	325.2	322.5	319.7	316.0	311.2	306.5	301.7	297.0	293.5
42.5°	317.5	314.7	311.7	308.9	306.0	302.1	297.1	292.2	287.2	282.3	278.7
45°	297.0	293.9	290.8	287.7	284.6	280.6	275.6	270.6	265.6	260.6	256.5
47.5°	275.8	272.6	269.4	266.2	263.0	258.8	253.7	248.4	243.2	238.1	233.8
50°	261.3	258.1	254.8	251.6	248.3	244.1	238.8	233.4	228.1	222.8	218.6
52.5°	246.7	243.4	240.3	237.1	233.9	229.6	224.1	218.6	213.2	207.7	203.5
55°	225.0	221.7	218.3	215.0	211.7	207.2	201.8	196.5	191.0	185.6	181.3
57.5°	203.5	200.0	196.6	193.1	189.6	185.3	179.9	174.6	169.3	163.9	159.5
60°	188.2	184.9	181.6	178.2	174.9	170.6	165.2	159.9	154.6	149.2	144.9
62.5°	174.4	171.0	167.5	164.1	160.6	156.1	150.7	145.2	139.7	134.3	130.2
65°	153.0	149.4	145.8	142.3	138.6	134.2	128.9	123.5	118.2	112.9	109.3
67.5°	130.7	127.3	123.8	120.4	117.0	112.8	107.8	102.9	97.9	93.0	89.9
70°	116.6	113.1	109.6	106.2	102.6	98.5	93.7	89.0	84.2	79.5	76.8
72.5°	101.6	98.5	95.3	92.1	89.0	85.2	80.6	76.1	71.7	67.2	64.9
75°	81.4	78.3	75.2	72.1	69.0	65.5	61.6	57.7	53.8	49.9	47.9
77.5°	60.8	58.2	55.6	53.0	50.4	47.5	44.3	41.1	37.9	34.8	33.7
80°	47.6	45.2	42.8	40.4	37.9	35.5	33.0	30.5	28.0	25.5	25.3
82.5°	36.2	34.0	31.8	29.5	27.3	25.5	24.1	22.7	21.2	19.8	19.6
85°	20.3	18.6	17.0	15.2	13.5	12.6	12.4	12.1	11.9	11.6	11.5
87.5°	7.4	7.2	7.1	7.0	6.8	6.9	7.1	7.3	7.5	7.8	7.8
90°	2.4	4.4	6.3	8.3	10.2	12.0	13.4	14.8	16.2	17.7	18.7
92.5°	17.2	19.4	21.7	23.9	26.1	27.8	28.8	29.8	30.8	31.8	32.4
95°	48.2	49.7	51.3	53.0	54.6	56.0	57.3	58.5	59.7	61.0	61.6
97.5°	84.1	85.4	86.7	87.9	89.3	90.6	92.1	93.6	95.0	96.5	97.1
100°	112.3	113.0	113.8	114.5	115.2	116.4	118.0	119.5	121.2	122.8	123.1
102.5°	141.9	142.2	142.4	142.8	143.0	143.9	145.4	146.8	148.3	149.7	150.3
105°	187.0	187.2	187.4	187.5	187.7	188.1	188.9	189.6	190.3	191.0	191.5
107.5°	234.3	234.6	234.7	235.0	235.2	235.4	235.4	235.6	235.7	235.8	236.3
110°	266.4	266.8	267.1	267.5	267.8	267.9	267.8	267.6	267.4	267.2	266.9



TEST NUMBER: P333026-927

CATALOG NUMBER: S124RDIW-S350D1050U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	299.8	299.9	300.0	300.0	300.1	300.0	299.7	299.4	299.0	298.7	298.7
115°	349.9	349.9	349.9	349.9	349.9	349.7	349.4	349.0	348.6	348.3	348.1
117.5°	397.1	397.2	397.4	397.5	397.7	397.6	397.4	397.1	396.9	396.6	396.0
120°	428.6	429.3	430.0	430.7	431.4	431.5	430.9	430.4	429.9	429.4	428.5
122.5°	461.3	461.6	461.8	462.2	462.4	462.5	462.2	461.9	461.7	461.4	460.8
125°	509.6	509.6	509.6	509.6	509.6	509.5	509.3	509.1	509.0	508.8	508.4
127.5°	553.4	554.0	554.4	555.0	555.6	555.7	555.4	555.1	554.8	554.5	554.2
130°	584.2	584.8	585.3	585.8	586.4	586.6	586.6	586.6	586.6	586.6	586.3
132.5°	615.7	616.1	616.5	616.9	617.3	617.3	617.3	617.1	617.0	616.8	616.5
135°	657.3	658.3	659.4	660.4	661.6	662.1	662.1	662.1	662.1	662.1	661.7
137.5°	702.5	703.0	703.5	704.0	704.5	704.9	705.2	705.5	705.8	706.1	705.6
140°	732.7	733.1	733.4	733.8	734.1	734.3	734.3	734.3	734.3	734.3	734.1
142.5°	760.3	760.7	761.0	761.4	761.8	761.8	761.7	761.5	761.4	761.3	761.2
145°	798.5	799.2	799.9	800.7	801.4	801.8	802.0	802.2	802.3	802.5	802.3
147.5°	836.4	837.3	838.1	838.9	839.8	840.2	840.0	839.9	839.7	839.6	839.5
150°	859.5	860.2	860.9	861.7	862.4	862.7	862.7	862.7	862.7	862.7	862.7
152.5°	881.3	881.8	882.2	882.6	883.0	883.3	883.4	883.6	883.8	883.9	884.3
155°	914.9	914.9	914.9	914.9	914.9	914.8	914.6	914.4	914.3	914.1	914.8
157.5°	943.1	942.8	942.5	942.1	941.8	941.7	941.6	941.6	941.5	941.5	942.1
160°	959.8	959.6	959.4	959.3	959.1	958.9	958.7	958.5	958.4	958.2	958.7
162.5°	975.2	974.8	974.3	973.8	973.4	973.0	972.9	972.7	972.5	972.3	973.3
165°	995.9	995.4	994.8	994.3	993.8	993.3	993.0	992.6	992.3	991.9	993.0
167.5°	1011.8	1011.1	1010.3	1009.6	1008.8	1008.4	1008.5	1008.5	1008.5	1008.6	1009.6
170°	1020.8	1019.9	1019.0	1018.1	1017.2	1016.8	1017.1	1017.2	1017.4	1017.6	1018.7
172.5°	1027.2	1026.4	1025.7	1025.0	1024.2	1023.9	1023.9	1024.0	1024.0	1024.0	1025.2
175°	1036.0	1035.1	1034.3	1033.4	1032.5	1032.0	1031.7	1031.6	1031.4	1031.3	1032.5
177.5°	1038.9	1038.2	1037.5	1036.8	1036.1	1035.7	1035.7	1035.7	1035.7	1035.7	1036.7
180°	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7



TEST NUMBER: P333026-927

CATALOG NUMBER: S124RDIW-S350D1050U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	489.7	489.7	489.7	489.7	489.7	489.7	489.7	489.7
2.5°	487.9	488.6	489.3	489.6	489.6	489.6	489.5	489.4
5°	484.7	485.4	486.3	486.6	486.5	486.3	486.1	485.9
7.5°	478.2	478.7	479.3	479.3	479.1	478.9	478.6	478.3
10°	472.4	472.7	473.0	473.0	472.7	472.4	472.1	471.7
12.5°	465.2	465.4	465.6	465.5	465.0	464.5	464.1	463.6
15°	452.7	452.5	452.3	451.9	451.3	450.8	450.2	449.6
17.5°	437.4	437.0	436.6	435.9	435.0	434.1	433.2	432.4
20°	426.9	426.2	425.6	424.7	423.6	422.5	421.4	420.3
22.5°	415.1	414.1	413.1	412.2	411.3	410.4	409.6	408.6
25°	396.1	394.7	393.3	392.2	391.3	390.5	389.7	388.8
27.5°	376.8	375.0	373.3	371.9	370.6	369.4	368.2	367.0
30°	362.9	360.8	358.8	357.0	355.7	354.4	353.1	351.7
32.5°	348.8	346.3	344.0	342.1	340.8	339.5	338.3	337.0
35°	327.6	324.9	322.0	319.9	318.4	316.9	315.4	313.9
37.5°	305.1	301.9	298.7	296.4	294.9	293.3	291.8	290.3
40°	289.9	286.5	283.0	280.5	279.0	277.5	276.0	274.5
42.5°	275.1	271.6	268.0	265.5	263.9	262.3	260.7	259.2
45°	252.5	248.3	244.2	241.5	240.0	238.4	236.9	235.5
47.5°	229.6	225.3	221.1	218.2	216.5	214.8	213.2	211.6
50°	214.4	210.2	206.0	203.2	201.6	200.0	198.4	196.9
52.5°	199.2	195.0	190.8	187.8	186.2	184.6	182.9	181.3
55°	177.0	172.6	168.3	165.3	163.7	162.2	160.6	159.0
57.5°	155.1	150.8	146.3	143.5	142.4	141.2	139.9	138.7
60°	140.5	136.3	131.9	129.0	127.7	126.4	125.1	123.7
62.5°	126.3	122.2	118.3	115.7	114.6	113.6	112.5	111.5
65°	105.7	102.1	98.5	96.3	95.2	94.3	93.2	92.2
67.5°	86.8	83.7	80.6	78.6	77.5	76.4	75.3	74.1
70°	74.0	71.2	68.5	66.7	65.8	65.0	64.2	63.4
72.5°	62.5	60.1	57.8	56.2	55.5	54.7	53.9	53.2
75°	46.0	44.1	42.2	41.0	40.5	40.0	39.5	39.0
77.5°	32.6	31.4	30.3	29.7	29.5	29.4	29.2	29.1
80°	25.0	24.7	24.5	24.3	24.2	24.2	24.1	24.0
82.5°	19.4	19.3	19.1	18.9	18.9	18.8	18.7	18.6
85°	11.3	11.1	10.9	10.9	10.9	10.9	10.9	10.9
87.5°	8.0	8.2	8.3	8.5	8.6	8.7	8.9	9.0
90°	19.8	20.8	21.9	22.7	23.0	23.4	23.7	24.1
92.5°	33.0	33.7	34.4	34.8	35.0	35.2	35.4	35.6
95°	62.0	62.6	63.1	63.4	63.4	63.4	63.4	63.4
97.5°	97.8	98.4	99.0	99.3	99.3	99.3	99.3	99.3
100°	123.5	123.8	124.2	124.4	124.4	124.4	124.4	124.4
102.5°	150.8	151.2	151.8	152.1	152.2	152.3	152.5	152.7
105°	192.1	192.6	193.1	193.7	194.2	194.7	195.3	195.8
107.5°	236.8	237.3	237.8	238.0	238.0	238.0	237.9	237.9
110°	266.5	266.2	265.8	265.9	266.4	267.0	267.5	268.1



TEST NUMBER: P333026-927

CATALOG NUMBER: S124RDIW-S350D1050U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	298.6	298.5	298.4	298.4	298.6	298.7	298.7	298.9
115°	347.9	347.8	347.6	347.4	347.2	347.1	346.9	346.7
117.5°	395.4	394.7	394.2	393.7	393.3	393.0	392.6	392.3
120°	427.5	426.7	425.8	425.5	425.9	426.2	426.6	426.9
122.5°	460.3	459.6	459.0	458.4	457.7	457.1	456.5	455.8
125°	508.1	507.7	507.4	507.0	506.7	506.3	506.0	505.6
127.5°	553.8	553.5	553.1	552.8	552.5	552.2	551.9	551.7
130°	585.9	585.6	585.2	584.7	584.0	583.3	582.6	581.9
132.5°	616.1	615.8	615.4	615.1	614.8	614.5	614.2	613.9
135°	661.4	661.0	660.7	660.2	659.7	659.1	658.6	658.1
137.5°	705.1	704.6	704.2	704.0	704.1	704.3	704.3	704.4
140°	734.0	733.8	733.6	733.4	733.2	733.1	732.8	732.7
142.5°	761.2	761.1	761.1	761.0	761.0	761.0	761.0	761.0
145°	802.2	802.0	801.8	801.5	800.9	800.3	799.9	799.3
147.5°	839.3	839.2	839.0	838.8	838.7	838.5	838.3	838.1
150°	862.7	862.7	862.7	862.6	862.4	862.3	862.1	861.9
152.5°	884.7	885.2	885.6	885.6	885.1	884.6	884.2	883.8
155°	915.5	916.2	917.0	917.0	916.2	915.5	914.8	914.1
157.5°	942.6	943.1	943.6	943.6	943.0	942.4	941.8	941.2
160°	959.3	959.8	960.4	960.1	959.3	958.4	957.5	956.6
162.5°	974.2	975.2	976.2	976.2	975.3	974.5	973.5	972.6
165°	994.0	995.1	996.2	996.3	995.6	994.9	994.2	993.5
167.5°	1010.7	1011.8	1012.9	1012.9	1011.8	1010.7	1009.6	1008.4
170°	1019.7	1020.8	1021.8	1021.8	1020.6	1019.3	1018.0	1016.8
172.5°	1026.4	1027.6	1028.9	1028.8	1027.6	1026.4	1025.1	1023.8
175°	1033.7	1035.0	1036.3	1036.3	1035.0	1033.7	1032.5	1031.3
177.5°	1037.8	1038.7	1039.7	1039.7	1038.5	1037.4	1036.3	1035.1
180°	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7

(END OF REPORT)