

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333031-927

Luminaire Tested: **S124RDIW-S350D1560U927-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333031-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S350D1560U927-4F0-1E-UDD-A
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1560 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6121.6 lumens
Efficiency: N/A
Efficacy: 114.6 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333031-927

CATALOG NUMBER: S124RDIW-S350D1560U927-4F0-1E-UDD-A

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - - - 90°-270° - - - 135°-315°



TEST NUMBER: P333031-927

CATALOG NUMBER: S124RDIW-S350D1560U927-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	100	100	100	100	88	88	88	88	66	66	66	46	46	46	28	28	28	19				
1	91	87	83	80	80	77	74	71	58	56	54	41	40	39	25	24	24	17				
2	83	76	70	66	73	67	63	59	51	48	45	36	34	32	22	21	20	14				
3	76	67	60	55	67	59	54	49	45	41	38	32	30	28	20	18	17	12				
4	69	59	52	46	61	53	46	42	40	36	32	28	26	24	18	16	15	11				
5	63	53	45	39	56	47	40	36	36	31	28	25	23	20	16	14	13	9				
6	58	47	39	34	51	42	35	31	32	28	24	23	20	18	14	13	12	8				
7	54	42	35	30	47	38	31	27	29	24	21	21	18	16	13	12	10	7				
8	50	38	31	26	44	34	28	23	26	22	19	19	16	14	12	10	9	7				
9	46	35	28	23	41	31	25	21	24	20	17	17	14	12	11	10	8	6				
10	43	32	25	20	38	28	22	18	22	18	15	16	13	11	10	9	8	5				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	3756	3756	3756	3756
5°	4357	3767	3331	3767
10°	5155	3751	2972	3751
15°	5954	3717	2554	3717
20°	6630	3669	2310	3669
25°	6844	3622	2144	3622
30°	5991	3566	2045	3566
35°	4664	3481	1985	3481
40°	3497	3385	1952	3385
45°	2762	3230	1934	3230
50°	2331	3052	1879	3052
55°	2031	2856	1779	2856
60°	1828	2651	1574	2651
65°	1612	2432	1354	2432
70°	1452	2205	1220	2205
75°	1216	1953	1042	1953
80°	1027	1664	976	1664
85°	861	1306	861	1306



TEST NUMBER: P333031-927

CATALOG NUMBER: S124RDIW-S350D1560U927-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	45.1	0.7
10°-20°	136.0	2.2
20°-30°	212.7	3.5
30°-40°	236.5	3.9
40°-50°	209.8	3.4
50°-60°	163.5	2.7
60°-70°	107.0	1.7
70°-80°	52.6	0.9
80°-90°	17.6	0.3
90°-100°	54.6	0.9
100°-110°	348.3	5.7
110°-120°	666.3	10.9
120°-130°	845.9	13.8
130°-140°	905.0	14.8
140°-150°	846.3	13.8
150°-160°	682.5	11.1
160°-170°	440.2	7.2
170°-180°	151.7	2.5
0°-30°	393.8	6.4
0°-40°	630.3	10.3
0°-60°	1003.6	16.4
0°-90°	1180.9	19.3
90°-120°	1069.3	17.5
90°-150°	3666.4	59.9
90°-180°	4941.0	80.7
0°-180°	6121.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	465	465	465	465	465	
5°	538	465	411	465	538	54
15°	712	445	306	445	712	203
25°	768	407	241	407	768	341
35°	473	353	201	353	473	297
45°	242	283	169	283	242	192
55°	144	203	126	203	144	131
65°	84	127	71	127	84	85
75°	39	63	33	63	39	43
85°	9	14	9	14	9	12
90°	36	4	36	4	36	16
95°	35	66	35	66	35	28
105°	340	360	340	360	340	297
115°	676	671	676	671	676	669
125°	951	944	951	944	951	847
135°	1179	1171	1179	1171	1179	908
145°	1357	1350	1357	1350	1357	848
155°	1479	1480	1479	1480	1479	682
165°	1554	1561	1554	1561	1554	439
175°	1588	1597	1588	1597	1588	151
180°	1597	1597	1597	1597	1597	



TEST NUMBER: P333031-927

CATALOG NUMBER: S124RDIW-S350D1560U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3
2.5°	490.8	492.2	490.8	490.7	489.2	488.7	488.1	486.2	482.6	480.5	480.9
5°	537.7	542.4	539.8	539.4	535.3	531.2	528.5	522.5	516.1	511.8	508.3
7.5°	591.9	594.6	592.9	590.3	583.7	579.9	573.8	565.9	554.4	545.7	537.7
10°	628.8	631.1	630.3	625.4	620.6	610.6	605.0	594.0	579.5	568.1	557.4
12.5°	665.1	667.5	660.9	661.2	651.9	644.0	635.2	621.2	604.6	589.9	576.5
15°	712.4	709.4	709.4	705.7	695.4	684.5	675.3	660.7	639.7	622.1	603.5
17.5°	749.5	750.5	749.0	740.1	732.1	720.8	703.9	686.9	667.4	643.7	624.8
20°	771.7	771.7	770.0	764.0	753.5	741.5	723.3	704.7	680.0	656.2	634.9
22.5°	780.7	781.3	779.3	774.4	764.9	753.2	737.7	718.8	693.3	666.5	640.1
25°	768.3	771.9	772.2	771.0	768.1	761.0	747.7	728.4	705.5	676.4	647.9
27.5°	705.4	709.9	713.8	720.3	729.0	733.4	734.0	724.2	704.3	676.3	647.6
30°	642.7	646.4	658.6	674.5	686.9	698.2	708.0	710.6	699.3	674.2	644.0
32.5°	573.1	578.2	590.4	607.5	628.1	647.2	669.1	680.2	679.9	664.9	637.0
35°	473.2	477.0	488.2	506.2	530.9	559.3	594.0	620.9	639.3	638.0	620.9
37.5°	381.7	385.9	397.2	412.2	436.2	471.2	504.8	542.0	575.9	595.0	589.3
40°	331.8	332.0	343.1	358.5	381.0	411.5	448.1	489.3	527.2	558.2	564.1
42.5°	292.6	292.6	299.9	316.5	332.6	361.4	396.3	437.3	481.6	517.4	533.2
45°	241.9	243.5	249.5	259.4	272.2	296.6	324.6	362.6	412.3	454.6	481.1
47.5°	204.8	207.3	211.1	219.2	229.3	245.6	268.7	302.9	343.3	389.9	427.5
50°	185.6	186.0	190.8	195.4	204.1	217.1	237.3	265.9	303.0	347.8	389.6
52.5°	169.1	169.1	172.0	177.7	184.8	194.9	211.3	237.2	270.1	310.3	353.5
55°	144.3	145.3	147.6	152.0	157.5	164.6	177.5	197.0	222.9	257.2	296.4
57.5°	125.6	126.0	127.8	129.7	134.7	139.9	149.6	163.1	184.9	213.0	249.5
60°	113.2	113.4	114.0	116.8	120.7	125.6	132.2	143.6	162.0	187.7	216.6
62.5°	101.2	101.6	102.4	104.5	107.6	110.9	117.8	127.0	142.2	164.1	190.1
65°	84.4	84.5	85.9	86.6	89.0	92.1	97.1	103.3	113.8	132.2	151.9
67.5°	70.5	70.5	70.6	71.6	73.3	75.3	78.3	83.3	91.2	102.4	119.8
70°	61.5	61.5	61.9	62.4	63.4	65.0	66.8	70.5	76.3	85.5	98.8
72.5°	53.1	53.2	53.6	53.7	54.2	55.6	56.9	59.3	63.5	70.5	81.3
75°	39.0	39.5	40.5	41.3	42.2	42.0	43.3	44.8	46.1	50.2	56.4
77.5°	29.0	28.8	28.8	29.5	29.5	29.8	30.7	31.8	32.9	34.8	37.0
80°	22.1	22.1	22.7	22.9	22.7	22.9	23.8	24.4	24.7	25.5	27.6
82.5°	16.7	17.0	16.9	17.0	17.1	17.3	18.1	18.2	18.6	18.9	19.7
85°	9.3	9.6	9.7	9.3	9.3	9.3	9.7	9.9	10.3	10.1	10.5
87.5°	10.5	10.2	10.2	10.1	10.2	9.8	9.7	9.7	9.0	8.9	8.4
90°	35.8	35.3	34.8	34.2	33.7	32.6	31.1	29.5	27.9	26.3	24.2
92.5°	33.0	32.9	32.8	32.6	32.6	31.7	30.1	28.5	26.9	25.3	23.2
95°	34.6	34.4	34.1	33.8	33.6	32.6	31.1	29.5	27.9	26.3	26.0
97.5°	33.4	33.2	33.0	32.6	32.4	32.2	32.0	31.8	31.7	31.5	31.2
100°	33.4	33.2	33.0	32.6	32.4	34.5	39.1	43.6	48.1	52.6	89.2
102.5°	34.4	34.4	34.3	34.2	34.2	58.5	107.2	155.9	204.5	253.3	258.0
105°	340.5	350.1	359.6	369.2	378.7	382.3	379.9	377.5	375.1	372.7	371.4
107.5°	474.5	473.5	472.5	471.5	470.5	469.4	468.3	467.1	465.9	464.7	462.9
110°	532.8	532.0	531.2	530.4	529.7	528.9	528.5	527.9	527.4	526.8	525.2



TEST NUMBER: P333031-927

CATALOG NUMBER: S124RDIW-S350D1560U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	591.1	590.1	589.1	588.1	587.1	586.6	586.7	586.8	586.9	587.1	586.3
115°	676.2	676.2	676.2	676.2	676.2	675.9	675.3	674.9	674.3	673.8	674.1
117.5°	762.6	762.8	762.9	763.0	763.1	763.2	763.3	763.4	763.5	763.6	763.0
120°	817.1	817.7	818.2	818.7	819.3	819.3	818.7	818.2	817.7	817.1	817.4
122.5°	870.7	871.2	871.7	872.3	872.7	872.9	872.6	872.3	872.0	871.6	871.2
125°	950.9	950.7	950.4	950.1	949.9	949.4	948.6	947.8	947.0	946.2	946.7
127.5°	1021.4	1021.6	1021.8	1022.1	1022.2	1022.5	1022.6	1022.8	1022.9	1023.1	1021.8
130°	1069.2	1069.2	1069.2	1069.2	1069.2	1069.1	1068.8	1068.6	1068.3	1068.0	1067.2
132.5°	1113.2	1113.4	1113.6	1113.8	1114.0	1114.0	1113.7	1113.5	1113.2	1112.9	1111.9
135°	1179.1	1178.6	1178.1	1177.5	1177.0	1176.5	1175.9	1175.4	1174.9	1174.3	1173.3
137.5°	1235.5	1235.6	1235.8	1236.0	1236.1	1236.0	1235.3	1234.8	1234.1	1233.6	1232.4
140°	1274.7	1274.4	1274.1	1273.9	1273.6	1273.1	1272.3	1271.5	1270.7	1269.9	1269.4
142.5°	1307.2	1307.1	1307.1	1307.0	1306.9	1306.6	1306.1	1305.5	1304.9	1304.3	1304.0
145°	1357.1	1356.6	1356.1	1355.5	1355.0	1354.6	1354.3	1354.1	1353.8	1353.5	1353.5
147.5°	1398.4	1398.2	1397.9	1397.6	1397.4	1397.2	1396.9	1396.7	1396.5	1396.3	1396.5
150°	1425.2	1425.0	1424.7	1424.4	1424.2	1424.0	1424.0	1424.0	1424.0	1424.0	1424.3
152.5°	1448.1	1448.3	1448.4	1448.6	1448.7	1448.7	1448.2	1447.8	1447.4	1446.9	1447.4
155°	1479.0	1479.8	1480.6	1481.4	1482.2	1482.0	1481.0	1479.9	1478.8	1477.7	1478.6
157.5°	1504.8	1506.2	1507.5	1508.9	1510.3	1510.3	1508.9	1507.5	1506.2	1504.8	1505.7
160°	1521.9	1523.6	1525.2	1526.8	1528.4	1528.4	1526.8	1525.2	1523.6	1521.9	1522.3
162.5°	1535.3	1537.2	1539.0	1540.8	1542.5	1542.7	1541.1	1539.5	1537.9	1536.3	1536.6
165°	1554.3	1556.6	1559.0	1561.4	1563.8	1563.9	1561.8	1559.6	1557.5	1555.4	1555.4
167.5°	1568.4	1571.0	1573.7	1576.3	1579.0	1579.1	1576.8	1574.5	1572.1	1569.8	1569.9
170°	1576.9	1579.6	1582.2	1584.9	1587.5	1587.9	1585.7	1583.6	1581.4	1579.3	1579.1
172.5°	1581.7	1584.6	1587.5	1590.3	1593.2	1593.6	1591.4	1589.3	1587.1	1585.1	1584.8
175°	1587.7	1590.9	1594.0	1597.2	1600.4	1600.8	1598.5	1596.0	1593.6	1591.3	1591.0
177.5°	1591.5	1594.0	1596.6	1599.2	1601.7	1602.1	1600.4	1598.7	1597.0	1595.3	1594.9
180°	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2



TEST NUMBER: P333031-927

CATALOG NUMBER: S124RDIW-S350D1560U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3
2.5°	479.4	477.4	476.3	473.9	471.0	469.5	468.2	466.2	463.7	461.0	459.1
5°	503.7	499.2	493.6	486.9	480.9	475.1	470.0	464.9	459.1	453.1	447.2
7.5°	528.7	519.9	510.3	499.2	488.5	478.7	469.7	461.1	451.4	442.6	434.7
10°	546.1	534.2	520.9	506.8	492.7	480.5	468.5	457.6	445.7	435.0	426.0
12.5°	560.2	546.1	530.1	512.6	495.7	480.9	467.1	453.0	439.3	427.8	415.7
15°	583.6	564.4	542.8	521.7	499.9	479.7	461.2	444.7	429.1	412.8	401.4
17.5°	599.8	576.8	550.6	525.4	499.5	475.8	454.4	434.7	416.8	400.1	386.5
20°	609.3	584.0	554.9	526.2	497.2	471.9	448.9	427.1	408.5	390.5	376.4
22.5°	614.7	586.7	554.9	524.9	494.8	467.4	442.1	419.5	399.3	381.2	365.7
25°	616.5	586.5	554.1	519.5	486.6	457.5	431.2	406.6	384.1	366.1	349.7
27.5°	614.0	578.7	545.5	510.1	476.0	445.4	417.9	392.1	369.6	350.2	333.3
30°	610.5	572.6	536.9	500.2	465.7	436.3	407.2	382.5	359.0	339.0	321.9
32.5°	602.6	565.1	526.7	489.1	454.2	423.8	396.2	371.4	348.4	327.9	309.7
35°	587.2	549.1	507.6	468.9	434.6	403.1	377.2	353.2	331.3	309.3	290.3
37.5°	566.8	528.0	486.6	444.3	409.9	380.2	356.5	333.9	312.5	292.5	271.3
40°	547.6	512.2	469.4	427.5	392.2	363.5	341.6	321.2	299.6	279.7	258.6
42.5°	524.4	494.2	451.0	408.8	374.1	346.4	326.0	306.0	286.4	267.1	245.0
45°	485.6	462.7	422.2	381.8	346.7	319.2	300.6	282.9	265.7	247.3	226.5
47.5°	441.1	425.6	390.7	349.2	316.8	292.2	274.0	259.6	245.0	226.6	208.4
50°	410.2	400.3	366.5	328.7	297.7	275.0	256.5	243.0	230.8	213.2	196.9
52.5°	377.2	371.9	343.4	307.2	277.3	255.1	239.2	227.1	214.8	200.1	184.9
55°	326.9	329.8	305.6	274.3	246.1	227.4	213.0	202.9	192.3	180.0	168.2
57.5°	275.6	285.9	269.7	242.2	215.8	198.4	187.6	179.1	170.2	160.0	149.9
60°	244.9	253.5	244.3	220.1	197.0	180.9	170.8	164.2	155.4	146.1	138.4
62.5°	214.8	224.1	218.6	199.1	177.7	163.8	154.9	148.8	142.2	134.0	126.0
65°	177.2	183.2	180.5	167.1	151.9	140.1	131.8	127.3	121.3	115.3	108.2
67.5°	135.7	147.3	145.8	138.6	125.5	116.2	110.8	106.9	101.4	97.0	92.1
70°	111.5	122.2	122.1	116.2	109.1	100.5	96.7	93.4	88.5	84.2	80.2
72.5°	91.3	101.1	102.6	98.1	93.2	86.7	83.1	80.8	76.0	73.1	69.9
75°	63.9	71.1	73.0	73.0	70.7	67.3	64.1	62.6	59.3	56.6	54.7
77.5°	41.9	46.4	49.4	50.0	50.4	49.2	46.6	45.6	42.9	42.1	40.2
80°	29.6	32.6	36.0	37.2	38.0	37.7	36.6	35.8	33.4	32.4	31.7
82.5°	20.4	22.1	24.9	27.4	27.1	28.1	27.1	26.5	24.6	24.3	23.6
85°	10.7	10.9	11.2	12.9	13.9	14.3	14.4	14.1	13.5	13.5	12.2
87.5°	8.0	7.4	7.3	6.8	6.3	6.4	6.3	5.8	5.9	6.1	6.2
90°	22.0	19.9	17.8	15.3	12.4	9.4	6.5	3.6	6.5	9.4	12.4
92.5°	21.1	18.9	16.8	15.7	15.5	15.4	15.2	15.1	15.2	15.4	15.5
95°	25.7	25.5	25.2	29.6	38.7	47.7	56.6	65.7	56.6	47.7	38.7
97.5°	90.8	120.4	150.0	162.1	156.5	150.8	145.1	139.5	145.1	150.8	156.5
100°	125.8	162.5	199.1	215.0	210.2	205.5	200.7	195.9	200.7	205.5	210.2
102.5°	262.8	267.6	272.4	273.0	269.5	266.0	262.5	259.0	262.5	266.0	269.5
105°	370.1	368.8	367.4	366.0	364.4	362.7	361.2	359.6	361.2	362.7	364.4
107.5°	461.1	459.3	457.5	456.2	455.4	454.6	453.8	453.0	453.8	454.6	455.4
110°	523.6	522.0	520.5	519.3	518.5	517.7	516.9	516.1	516.9	517.7	518.5



TEST NUMBER: P333031-927

CATALOG NUMBER: S124RDIW-S350D1560U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	585.6	584.8	584.1	583.0	581.5	580.1	578.7	577.3	578.7	580.1	581.5
115°	674.3	674.5	674.9	674.5	673.8	673.0	672.2	671.4	672.2	673.0	673.8
117.5°	762.5	761.8	761.3	760.5	759.4	758.4	757.2	756.2	757.2	758.4	759.4
120°	817.7	817.9	818.2	817.8	816.7	815.7	814.6	813.6	814.6	815.7	816.7
122.5°	870.8	870.5	870.1	869.7	868.9	868.3	867.7	867.0	867.7	868.3	868.9
125°	947.2	947.8	948.2	948.0	947.0	945.9	944.8	943.8	944.8	945.9	947.0
127.5°	1020.6	1019.5	1018.2	1017.5	1017.2	1016.9	1016.7	1016.4	1016.7	1016.9	1017.2
130°	1066.4	1065.6	1064.9	1064.3	1064.1	1063.7	1063.5	1063.3	1063.5	1063.7	1064.1
132.5°	1110.9	1109.9	1108.9	1108.2	1107.7	1107.2	1106.7	1106.2	1106.7	1107.2	1107.7
135°	1172.2	1171.2	1170.1	1169.7	1170.0	1170.2	1170.4	1170.8	1170.4	1170.2	1170.0
137.5°	1231.3	1230.1	1228.9	1228.3	1228.2	1228.0	1228.0	1227.9	1228.0	1228.0	1228.2
140°	1268.8	1268.3	1267.8	1267.3	1266.7	1266.2	1265.7	1265.1	1265.7	1266.2	1266.7
142.5°	1303.7	1303.4	1303.1	1302.4	1301.5	1300.5	1299.5	1298.5	1299.5	1300.5	1301.5
145°	1353.5	1353.5	1353.5	1353.1	1352.3	1351.5	1350.8	1350.0	1350.8	1351.5	1352.3
147.5°	1396.9	1397.1	1397.3	1396.8	1395.3	1393.8	1392.3	1390.8	1392.3	1393.8	1395.3
150°	1424.6	1424.8	1425.1	1424.7	1423.6	1422.5	1421.5	1420.5	1421.5	1422.5	1423.6
152.5°	1447.9	1448.3	1448.9	1448.7	1447.8	1447.0	1446.1	1445.3	1446.1	1447.0	1447.8
155°	1479.4	1480.2	1481.0	1481.2	1481.0	1480.7	1480.4	1480.2	1480.4	1480.7	1481.0
157.5°	1506.6	1507.4	1508.4	1508.9	1509.1	1509.3	1509.4	1509.6	1509.4	1509.3	1509.1
160°	1522.5	1522.7	1523.0	1523.6	1524.4	1525.2	1526.0	1526.8	1526.0	1525.2	1524.4
162.5°	1536.8	1537.1	1537.4	1538.0	1539.1	1540.0	1541.0	1542.1	1541.0	1540.0	1539.1
165°	1555.4	1555.4	1555.4	1556.1	1557.4	1558.8	1560.0	1561.4	1560.0	1558.8	1557.4
167.5°	1570.1	1570.3	1570.4	1571.1	1572.6	1573.9	1575.3	1576.7	1575.3	1573.9	1572.6
170°	1578.8	1578.5	1578.3	1578.9	1580.5	1582.1	1583.7	1585.3	1583.7	1582.1	1580.5
172.5°	1584.5	1584.3	1584.0	1584.7	1586.3	1587.9	1589.4	1591.0	1589.4	1587.9	1586.3
175°	1590.7	1590.5	1590.2	1590.9	1592.4	1594.0	1595.6	1597.2	1595.6	1594.0	1592.4
177.5°	1594.5	1594.0	1593.6	1594.2	1595.6	1597.1	1598.6	1600.1	1598.6	1597.1	1595.6
180°	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2



TEST NUMBER: P333031-927

CATALOG NUMBER: S124RDIW-S350D1560U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3
2.5°	456.9	455.4	453.5	451.2	448.5	446.2	445.0	446.0	446.5	445.2	445.0
5°	443.0	438.3	434.6	429.0	424.5	420.7	418.1	416.9	417.3	414.3	413.6
7.5°	427.4	421.8	415.7	409.0	402.8	397.3	394.4	392.8	389.6	388.2	386.0
10°	417.3	409.9	403.9	395.9	388.8	382.3	379.1	376.4	373.3	371.8	368.6
12.5°	407.0	398.3	391.7	383.5	376.2	368.4	365.3	360.4	355.5	352.3	348.2
15°	392.4	381.9	373.8	364.1	355.5	346.5	338.4	329.4	326.1	318.9	314.8
17.5°	375.3	364.7	354.7	341.7	328.4	317.1	308.6	299.9	294.8	290.3	288.1
20°	364.1	354.3	340.5	325.3	310.5	298.1	291.1	285.5	279.9	276.7	274.5
22.5°	353.5	341.0	324.9	308.5	293.7	284.0	278.1	272.4	267.8	264.7	261.7
25°	335.6	319.2	302.2	283.4	273.4	264.9	258.6	253.8	251.0	247.1	245.6
27.5°	317.3	297.5	278.7	266.1	255.6	247.8	242.2	238.8	235.2	232.7	230.7
30°	303.2	283.1	266.3	254.2	243.5	237.2	232.7	228.5	225.7	223.6	222.2
32.5°	289.2	269.2	255.0	242.1	233.6	227.4	222.6	219.5	217.3	214.7	213.7
35°	269.0	251.2	238.8	227.2	218.6	213.0	209.2	206.0	204.1	203.4	202.9
37.5°	249.6	235.0	221.7	212.2	204.5	200.1	195.7	194.1	192.8	191.5	192.1
40°	237.3	223.6	211.8	201.8	195.5	190.7	188.1	186.2	185.1	185.1	185.1
42.5°	226.7	213.3	201.8	192.7	186.6	182.4	179.5	177.9	177.5	177.4	178.3
45°	210.2	197.8	186.2	178.6	173.4	169.3	167.6	166.3	166.3	167.1	167.2
47.5°	193.8	182.2	172.9	164.5	159.6	157.1	155.6	155.0	155.0	155.7	156.6
50°	183.7	172.3	163.1	155.6	151.1	148.7	147.3	146.9	147.3	147.3	148.7
52.5°	172.8	162.6	153.5	147.2	142.1	139.8	139.1	138.6	138.8	139.4	140.0
55°	156.8	147.6	138.9	132.9	129.2	127.7	126.0	126.2	125.8	126.2	126.2
57.5°	140.6	132.4	124.4	119.6	116.3	114.2	112.3	112.8	112.3	112.2	111.9
60°	130.3	121.3	114.9	110.6	106.9	105.0	103.3	103.7	103.1	102.7	102.0
62.5°	119.1	111.5	105.4	101.3	98.3	96.2	94.4	94.1	92.8	91.5	89.8
65°	102.7	96.6	91.1	87.2	84.4	82.7	81.4	80.2	77.4	74.5	73.0
67.5°	86.9	82.4	77.3	74.0	71.7	69.6	67.0	65.1	62.5	60.8	59.9
70°	76.7	72.4	68.0	64.9	62.4	60.4	57.6	56.2	54.3	53.6	52.7
72.5°	66.9	62.9	58.9	56.0	53.5	51.8	49.6	48.3	47.5	47.1	46.3
75°	52.1	49.0	45.9	43.3	41.3	40.1	39.2	38.3	37.9	36.2	35.3
77.5°	38.0	35.9	34.1	32.2	30.7	29.9	28.1	27.1	26.5	25.7	25.4
80°	29.6	28.1	26.2	25.1	23.1	22.3	21.5	21.4	21.2	21.0	20.8
82.5°	22.3	20.8	18.9	18.2	17.7	17.2	16.8	16.6	16.4	16.5	16.5
85°	11.2	10.5	10.5	10.3	10.1	9.9	9.7	9.7	9.6	9.7	9.6
87.5°	6.8	7.1	7.6	7.7	8.3	8.7	8.9	9.2	9.7	9.7	9.9
90°	15.3	17.8	19.9	22.0	24.2	26.3	27.9	29.5	31.1	32.6	33.7
92.5°	15.7	16.8	18.9	21.1	23.2	25.3	26.9	28.5	30.1	31.7	32.6
95°	29.6	25.2	25.5	25.7	26.0	26.3	27.9	29.5	31.1	32.6	33.6
97.5°	162.1	150.0	120.4	90.8	61.2	31.5	31.7	31.8	32.0	32.2	32.4
100°	215.0	199.1	162.5	125.8	89.2	52.6	48.1	43.6	39.1	34.5	32.4
102.5°	273.0	272.4	267.6	262.8	258.0	253.3	204.5	155.9	107.2	58.5	34.2
105°	366.0	367.4	368.8	370.1	371.4	372.7	375.1	377.5	379.9	382.3	378.7
107.5°	456.2	457.5	459.3	461.1	462.9	464.7	465.9	467.1	468.3	469.4	470.5
110°	519.3	520.5	522.0	523.6	525.2	526.8	527.4	527.9	528.5	528.9	529.7



TEST NUMBER: P333031-927

CATALOG NUMBER: S124RDIW-S350D1560U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	583.0	584.1	584.8	585.6	586.3	587.1	586.9	586.8	586.7	586.6	587.1
115°	674.5	674.9	674.5	674.3	674.1	673.8	674.3	674.9	675.3	675.9	676.2
117.5°	760.5	761.3	761.8	762.5	763.0	763.6	763.5	763.4	763.3	763.2	763.1
120°	817.8	818.2	817.9	817.7	817.4	817.1	817.7	818.2	818.7	819.3	819.3
122.5°	869.7	870.1	870.5	870.8	871.2	871.6	872.0	872.3	872.6	872.9	872.7
125°	948.0	948.2	947.8	947.2	946.7	946.2	947.0	947.8	948.6	949.4	949.9
127.5°	1017.5	1018.2	1019.5	1020.6	1021.8	1023.1	1022.9	1022.8	1022.6	1022.5	1022.2
130°	1064.3	1064.9	1065.6	1066.4	1067.2	1068.0	1068.3	1068.6	1068.8	1069.1	1069.2
132.5°	1108.2	1108.9	1109.9	1110.9	1111.9	1112.9	1113.2	1113.5	1113.7	1114.0	1114.0
135°	1169.7	1170.1	1171.2	1172.2	1173.3	1174.3	1174.9	1175.4	1175.9	1176.5	1177.0
137.5°	1228.3	1228.9	1230.1	1231.3	1232.4	1233.6	1234.1	1234.8	1235.3	1236.0	1236.1
140°	1267.3	1267.8	1268.3	1268.8	1269.4	1269.9	1270.7	1271.5	1272.3	1273.1	1273.6
142.5°	1302.4	1303.1	1303.4	1303.7	1304.0	1304.3	1304.9	1305.5	1306.1	1306.6	1306.9
145°	1353.1	1353.5	1353.5	1353.5	1353.5	1353.5	1353.8	1354.1	1354.3	1354.6	1355.0
147.5°	1396.8	1397.3	1397.1	1396.9	1396.5	1396.3	1396.5	1396.7	1396.9	1397.2	1397.4
150°	1424.7	1425.1	1424.8	1424.6	1424.3	1424.0	1424.0	1424.0	1424.0	1424.0	1424.2
152.5°	1448.7	1448.9	1448.3	1447.9	1447.4	1446.9	1447.4	1447.8	1448.2	1448.7	1448.7
155°	1481.2	1481.0	1480.2	1479.4	1478.6	1477.7	1478.8	1479.9	1481.0	1482.0	1482.2
157.5°	1508.9	1508.4	1507.4	1506.6	1505.7	1504.8	1506.2	1507.5	1508.9	1510.3	1510.3
160°	1523.6	1523.0	1522.7	1522.5	1522.3	1521.9	1523.6	1525.2	1526.8	1528.4	1528.4
162.5°	1538.0	1537.4	1537.1	1536.8	1536.6	1536.3	1537.9	1539.5	1541.1	1542.7	1542.5
165°	1556.1	1555.4	1555.4	1555.4	1555.4	1555.4	1557.5	1559.6	1561.8	1563.9	1563.8
167.5°	1571.1	1570.4	1570.3	1570.1	1569.9	1569.8	1572.1	1574.5	1576.8	1579.1	1579.0
170°	1578.9	1578.3	1578.5	1578.8	1579.1	1579.3	1581.4	1583.6	1585.7	1587.9	1587.5
172.5°	1584.7	1584.0	1584.3	1584.5	1584.8	1585.1	1587.1	1589.3	1591.4	1593.6	1593.2
175°	1590.9	1590.2	1590.5	1590.7	1591.0	1591.3	1593.6	1596.0	1598.5	1600.8	1600.4
177.5°	1594.2	1593.6	1594.0	1594.5	1594.9	1595.3	1597.0	1598.7	1600.4	1602.1	1601.7
180°	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2



TEST NUMBER: P333031-927

CATALOG NUMBER: S124RDIW-S350D1560U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3
2.5°	444.2	444.5	443.5	443.1	443.5	444.5	444.2	445.0	445.2	446.5	446.0
5°	412.1	411.7	410.7	411.0	410.7	411.7	412.1	413.6	414.3	417.3	416.9
7.5°	384.6	383.2	383.6	382.1	383.6	383.2	384.6	386.0	388.2	389.6	392.8
10°	367.8	365.8	364.1	362.6	364.1	365.8	367.8	368.6	371.8	373.3	376.4
12.5°	344.9	343.1	340.9	341.3	340.9	343.1	344.9	348.2	352.3	355.5	360.4
15°	312.4	309.5	305.1	305.6	305.1	309.5	312.4	314.8	318.9	326.1	329.4
17.5°	284.8	284.8	282.7	283.3	282.7	284.8	284.8	288.1	290.3	294.8	299.9
20°	270.5	269.3	269.4	268.9	269.4	269.3	270.5	274.5	276.7	279.9	285.5
22.5°	260.6	259.0	257.7	256.6	257.7	259.0	260.6	261.7	264.7	267.8	272.4
25°	243.9	242.8	241.1	240.7	241.1	242.8	243.9	245.6	247.1	251.0	253.8
27.5°	229.2	229.0	228.3	227.4	228.3	229.0	229.2	230.7	232.7	235.2	238.8
30°	220.7	220.3	219.9	219.4	219.9	220.3	220.7	222.2	223.6	225.7	228.5
32.5°	213.0	212.8	212.4	212.5	212.4	212.8	213.0	213.7	214.7	217.3	219.5
35°	202.1	201.9	201.5	201.4	201.5	201.9	202.1	202.9	203.4	204.1	206.0
37.5°	191.9	192.4	192.2	192.1	192.2	192.4	191.9	192.1	191.5	192.8	194.1
40°	184.9	185.1	185.4	185.2	185.4	185.1	184.9	185.1	185.1	185.1	186.2
42.5°	179.0	179.0	179.6	179.0	179.6	179.0	179.0	178.3	177.4	177.5	177.9
45°	168.6	169.7	169.4	169.4	169.4	169.7	168.6	167.2	167.1	166.3	166.3
47.5°	157.1	158.1	158.4	158.3	158.4	158.1	157.1	156.6	155.7	155.0	155.0
50°	149.6	149.2	149.8	149.6	149.8	149.2	149.6	148.7	147.3	147.3	146.9
52.5°	140.5	140.5	140.5	140.3	140.5	140.5	140.5	140.0	139.4	138.8	138.6
55°	126.4	126.6	126.2	126.4	126.2	126.6	126.4	126.2	126.2	125.8	126.2
57.5°	111.1	110.2	110.5	110.1	110.5	110.2	111.1	111.9	112.2	112.3	112.8
60°	100.1	98.6	98.2	97.5	98.2	98.6	100.1	102.0	102.7	103.1	103.7
62.5°	87.9	86.7	85.5	86.1	85.5	86.7	87.9	89.8	91.5	92.8	94.1
65°	71.5	70.7	70.1	70.9	70.1	70.7	71.5	73.0	74.5	77.4	80.2
67.5°	59.1	58.7	58.7	58.4	58.7	58.7	59.1	59.9	60.8	62.5	65.1
70°	52.7	52.1	52.1	51.7	52.1	52.1	52.7	52.7	53.6	54.3	56.2
72.5°	46.1	45.6	45.7	45.5	45.7	45.6	46.1	46.3	47.1	47.5	48.3
75°	34.1	33.2	33.2	33.4	33.2	33.2	34.1	35.3	36.2	37.9	38.3
77.5°	25.4	25.3	25.5	25.2	25.5	25.3	25.4	25.4	25.7	26.5	27.1
80°	20.8	20.6	20.4	21.0	20.4	20.6	20.8	20.8	21.0	21.2	21.4
82.5°	16.2	16.2	16.1	16.8	16.1	16.2	16.2	16.5	16.5	16.4	16.6
85°	9.7	9.3	9.7	9.3	9.7	9.3	9.7	9.6	9.7	9.6	9.7
87.5°	10.3	10.2	10.2	10.5	10.2	10.2	10.3	9.9	9.7	9.7	9.2
90°	34.2	34.8	35.3	35.8	35.3	34.8	34.2	33.7	32.6	31.1	29.5
92.5°	32.6	32.8	32.9	33.0	32.9	32.8	32.6	32.6	31.7	30.1	28.5
95°	33.8	34.1	34.4	34.6	34.4	34.1	33.8	33.6	32.6	31.1	29.5
97.5°	32.6	33.0	33.2	33.4	33.2	33.0	32.6	32.4	32.2	32.0	31.8
100°	32.6	33.0	33.2	33.4	33.2	33.0	32.6	32.4	34.5	39.1	43.6
102.5°	34.2	34.3	34.4	34.4	34.4	34.3	34.2	34.2	58.5	107.2	155.9
105°	369.2	359.6	350.1	340.5	350.1	359.6	369.2	378.7	382.3	379.9	377.5
107.5°	471.5	472.5	473.5	474.5	473.5	472.5	471.5	470.5	469.4	468.3	467.1
110°	530.4	531.2	532.0	532.8	532.0	531.2	530.4	529.7	528.9	528.5	527.9



TEST NUMBER: P333031-927

CATALOG NUMBER: S124RDIW-S350D1560U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	588.1	589.1	590.1	591.1	590.1	589.1	588.1	587.1	586.6	586.7	586.8
115°	676.2	676.2	676.2	676.2	676.2	676.2	676.2	676.2	675.9	675.3	674.9
117.5°	763.0	762.9	762.8	762.6	762.8	762.9	763.0	763.1	763.2	763.3	763.4
120°	818.7	818.2	817.7	817.1	817.7	818.2	818.7	819.3	819.3	818.7	818.2
122.5°	872.3	871.7	871.2	870.7	871.2	871.7	872.3	872.7	872.9	872.6	872.3
125°	950.1	950.4	950.7	950.9	950.7	950.4	950.1	949.9	949.4	948.6	947.8
127.5°	1022.1	1021.8	1021.6	1021.4	1021.6	1021.8	1022.1	1022.2	1022.5	1022.6	1022.8
130°	1069.2	1069.2	1069.2	1069.2	1069.2	1069.2	1069.2	1069.2	1069.1	1068.8	1068.6
132.5°	1113.8	1113.6	1113.4	1113.2	1113.4	1113.6	1113.8	1114.0	1114.0	1113.7	1113.5
135°	1177.5	1178.1	1178.6	1179.1	1178.6	1178.1	1177.5	1177.0	1176.5	1175.9	1175.4
137.5°	1236.0	1235.8	1235.6	1235.5	1235.6	1235.8	1236.0	1236.1	1236.0	1235.3	1234.8
140°	1273.9	1274.1	1274.4	1274.7	1274.4	1274.1	1273.9	1273.6	1273.1	1272.3	1271.5
142.5°	1307.0	1307.1	1307.1	1307.2	1307.1	1307.1	1307.0	1306.9	1306.6	1306.1	1305.5
145°	1355.5	1356.1	1356.6	1357.1	1356.6	1356.1	1355.5	1355.0	1354.6	1354.3	1354.1
147.5°	1397.6	1397.9	1398.2	1398.4	1398.2	1397.9	1397.6	1397.4	1397.2	1396.9	1396.7
150°	1424.4	1424.7	1425.0	1425.2	1425.0	1424.7	1424.4	1424.2	1424.0	1424.0	1424.0
152.5°	1448.6	1448.4	1448.3	1448.1	1448.3	1448.4	1448.6	1448.7	1448.7	1448.2	1447.8
155°	1481.4	1480.6	1479.8	1479.0	1479.8	1480.6	1481.4	1482.2	1482.0	1481.0	1479.9
157.5°	1508.9	1507.5	1506.2	1504.8	1506.2	1507.5	1508.9	1510.3	1510.3	1508.9	1507.5
160°	1526.8	1525.2	1523.6	1521.9	1523.6	1525.2	1526.8	1528.4	1528.4	1526.8	1525.2
162.5°	1540.8	1539.0	1537.2	1535.3	1537.2	1539.0	1540.8	1542.5	1542.7	1541.1	1539.5
165°	1561.4	1559.0	1556.6	1554.3	1556.6	1559.0	1561.4	1563.8	1563.9	1561.8	1559.6
167.5°	1576.3	1573.7	1571.0	1568.4	1571.0	1573.7	1576.3	1579.0	1579.1	1576.8	1574.5
170°	1584.9	1582.2	1579.6	1576.9	1579.6	1582.2	1584.9	1587.5	1587.9	1585.7	1583.6
172.5°	1590.3	1587.5	1584.6	1581.7	1584.6	1587.5	1590.3	1593.2	1593.6	1591.4	1589.3
175°	1597.2	1594.0	1590.9	1587.7	1590.9	1594.0	1597.2	1600.4	1600.8	1598.5	1596.0
177.5°	1599.2	1596.6	1594.0	1591.5	1594.0	1596.6	1599.2	1601.7	1602.1	1600.4	1598.7
180°	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2



TEST NUMBER: P333031-927

CATALOG NUMBER: S124RDIW-S350D1560U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3
2.5°	445.0	446.2	448.5	451.2	453.5	455.4	456.9	459.1	461.0	463.7	466.2
5°	418.1	420.7	424.5	429.0	434.6	438.3	443.0	447.2	453.1	459.1	464.9
7.5°	394.4	397.3	402.8	409.0	415.7	421.8	427.4	434.7	442.6	451.4	461.1
10°	379.1	382.3	388.8	395.9	403.9	409.9	417.3	426.0	435.0	445.7	457.6
12.5°	365.3	368.4	376.2	383.5	391.7	398.3	407.0	415.7	427.8	439.3	453.0
15°	338.4	346.5	355.5	364.1	373.8	381.9	392.4	401.4	412.8	429.1	444.7
17.5°	308.6	317.1	328.4	341.7	354.7	364.7	375.3	386.5	400.1	416.8	434.7
20°	291.1	298.1	310.5	325.3	340.5	354.3	364.1	376.4	390.5	408.5	427.1
22.5°	278.1	284.0	293.7	308.5	324.9	341.0	353.5	365.7	381.2	399.3	419.5
25°	258.6	264.9	273.4	283.4	302.2	319.2	335.6	349.7	366.1	384.1	406.6
27.5°	242.2	247.8	255.6	266.1	278.7	297.5	317.3	333.3	350.2	369.6	392.1
30°	232.7	237.2	243.5	254.2	266.3	283.1	303.2	321.9	339.0	359.0	382.5
32.5°	222.6	227.4	233.6	242.1	255.0	269.2	289.2	309.7	327.9	348.4	371.4
35°	209.2	213.0	218.6	227.2	238.8	251.2	269.0	290.3	309.3	331.3	353.2
37.5°	195.7	200.1	204.5	212.2	221.7	235.0	249.6	271.3	292.5	312.5	333.9
40°	188.1	190.7	195.5	201.8	211.8	223.6	237.3	258.6	279.7	299.6	321.2
42.5°	179.5	182.4	186.6	192.7	201.8	213.3	226.7	245.0	267.1	286.4	306.0
45°	167.6	169.3	173.4	178.6	186.2	197.8	210.2	226.5	247.3	265.7	282.9
47.5°	155.6	157.1	159.6	164.5	172.9	182.2	193.8	208.4	226.6	245.0	259.6
50°	147.3	148.7	151.1	155.6	163.1	172.3	183.7	196.9	213.2	230.8	243.0
52.5°	139.1	139.8	142.1	147.2	153.5	162.6	172.8	184.9	200.1	214.8	227.1
55°	126.0	127.7	129.2	132.9	138.9	147.6	156.8	168.2	180.0	192.3	202.9
57.5°	112.3	114.2	116.3	119.6	124.4	132.4	140.6	149.9	160.0	170.2	179.1
60°	103.3	105.0	106.9	110.6	114.9	121.3	130.3	138.4	146.1	155.4	164.2
62.5°	94.4	96.2	98.3	101.3	105.4	111.5	119.1	126.0	134.0	142.2	148.8
65°	81.4	82.7	84.4	87.2	91.1	96.6	102.7	108.2	115.3	121.3	127.3
67.5°	67.0	69.6	71.7	74.0	77.3	82.4	86.9	92.1	97.0	101.4	106.9
70°	57.6	60.4	62.4	64.9	68.0	72.4	76.7	80.2	84.2	88.5	93.4
72.5°	49.6	51.8	53.5	56.0	58.9	62.9	66.9	69.9	73.1	76.0	80.8
75°	39.2	40.1	41.3	43.3	45.9	49.0	52.1	54.7	56.6	59.3	62.6
77.5°	28.1	29.9	30.7	32.2	34.1	35.9	38.0	40.2	42.1	42.9	45.6
80°	21.5	22.3	23.1	25.1	26.2	28.1	29.6	31.7	32.4	33.4	35.8
82.5°	16.8	17.2	17.7	18.2	18.9	20.8	22.3	23.6	24.3	24.6	26.5
85°	9.7	9.9	10.1	10.3	10.5	10.5	11.2	12.2	13.5	13.5	14.1
87.5°	8.9	8.7	8.3	7.7	7.6	7.1	6.8	6.2	6.1	5.9	5.8
90°	27.9	26.3	24.2	22.0	19.9	17.8	15.3	12.4	9.4	6.5	3.6
92.5°	26.9	25.3	23.2	21.1	18.9	16.8	15.7	15.5	15.4	15.2	15.1
95°	27.9	26.3	26.0	25.7	25.5	25.2	29.6	38.7	47.7	56.6	65.7
97.5°	31.7	31.5	61.2	90.8	120.4	150.0	162.1	156.5	150.8	145.1	139.5
100°	48.1	52.6	89.2	125.8	162.5	199.1	215.0	210.2	205.5	200.7	195.9
102.5°	204.5	253.3	258.0	262.8	267.6	272.4	273.0	269.5	266.0	262.5	259.0
105°	375.1	372.7	371.4	370.1	368.8	367.4	366.0	364.4	362.7	361.2	359.6
107.5°	465.9	464.7	462.9	461.1	459.3	457.5	456.2	455.4	454.6	453.8	453.0
110°	527.4	526.8	525.2	523.6	522.0	520.5	519.3	518.5	517.7	516.9	516.1



TEST NUMBER: P333031-927

CATALOG NUMBER: S124RDIW-S350D1560U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	586.9	587.1	586.3	585.6	584.8	584.1	583.0	581.5	580.1	578.7	577.3
115°	674.3	673.8	674.1	674.3	674.5	674.9	674.5	673.8	673.0	672.2	671.4
117.5°	763.5	763.6	763.0	762.5	761.8	761.3	760.5	759.4	758.4	757.2	756.2
120°	817.7	817.1	817.4	817.7	817.9	818.2	817.8	816.7	815.7	814.6	813.6
122.5°	872.0	871.6	871.2	870.8	870.5	870.1	869.7	868.9	868.3	867.7	867.0
125°	947.0	946.2	946.7	947.2	947.8	948.2	948.0	947.0	945.9	944.8	943.8
127.5°	1022.9	1023.1	1021.8	1020.6	1019.5	1018.2	1017.5	1017.2	1016.9	1016.7	1016.4
130°	1068.3	1068.0	1067.2	1066.4	1065.6	1064.9	1064.3	1064.1	1063.7	1063.5	1063.3
132.5°	1113.2	1112.9	1111.9	1110.9	1109.9	1108.9	1108.2	1107.7	1107.2	1106.7	1106.2
135°	1174.9	1174.3	1173.3	1172.2	1171.2	1170.1	1169.7	1170.0	1170.2	1170.4	1170.8
137.5°	1234.1	1233.6	1232.4	1231.3	1230.1	1228.9	1228.3	1228.2	1228.0	1228.0	1227.9
140°	1270.7	1269.9	1269.4	1268.8	1268.3	1267.8	1267.3	1266.7	1266.2	1265.7	1265.1
142.5°	1304.9	1304.3	1304.0	1303.7	1303.4	1303.1	1302.4	1301.5	1300.5	1299.5	1298.5
145°	1353.8	1353.5	1353.5	1353.5	1353.5	1353.5	1353.1	1352.3	1351.5	1350.8	1350.0
147.5°	1396.5	1396.3	1396.5	1396.9	1397.1	1397.3	1396.8	1395.3	1393.8	1392.3	1390.8
150°	1424.0	1424.0	1424.3	1424.6	1424.8	1425.1	1424.7	1423.6	1422.5	1421.5	1420.5
152.5°	1447.4	1446.9	1447.4	1447.9	1448.3	1448.9	1448.7	1447.8	1447.0	1446.1	1445.3
155°	1478.8	1477.7	1478.6	1479.4	1480.2	1481.0	1481.2	1481.0	1480.7	1480.4	1480.2
157.5°	1506.2	1504.8	1505.7	1506.6	1507.4	1508.4	1508.9	1509.1	1509.3	1509.4	1509.6
160°	1523.6	1521.9	1522.3	1522.5	1522.7	1523.0	1523.6	1524.4	1525.2	1526.0	1526.8
162.5°	1537.9	1536.3	1536.6	1536.8	1537.1	1537.4	1538.0	1539.1	1540.0	1541.0	1542.1
165°	1557.5	1555.4	1555.4	1555.4	1555.4	1555.4	1556.1	1557.4	1558.8	1560.0	1561.4
167.5°	1572.1	1569.8	1569.9	1570.1	1570.3	1570.4	1571.1	1572.6	1573.9	1575.3	1576.7
170°	1581.4	1579.3	1579.1	1578.8	1578.5	1578.3	1578.9	1580.5	1582.1	1583.7	1585.3
172.5°	1587.1	1585.1	1584.8	1584.5	1584.3	1584.0	1584.7	1586.3	1587.9	1589.4	1591.0
175°	1593.6	1591.3	1591.0	1590.7	1590.5	1590.2	1590.9	1592.4	1594.0	1595.6	1597.2
177.5°	1597.0	1595.3	1594.9	1594.5	1594.0	1593.6	1594.2	1595.6	1597.1	1598.6	1600.1
180°	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2



TEST NUMBER: P333031-927

CATALOG NUMBER: S124RDIW-S350D1560U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3
2.5°	468.2	469.5	471.0	473.9	476.3	477.4	479.4	480.9	480.5	482.6	486.2
5°	470.0	475.1	480.9	486.9	493.6	499.2	503.7	508.3	511.8	516.1	522.5
7.5°	469.7	478.7	488.5	499.2	510.3	519.9	528.7	537.7	545.7	554.4	565.9
10°	468.5	480.5	492.7	506.8	520.9	534.2	546.1	557.4	568.1	579.5	594.0
12.5°	467.1	480.9	495.7	512.6	530.1	546.1	560.2	576.5	589.9	604.6	621.2
15°	461.2	479.7	499.9	521.7	542.8	564.4	583.6	603.5	622.1	639.7	660.7
17.5°	454.4	475.8	499.5	525.4	550.6	576.8	599.8	624.8	643.7	667.4	686.9
20°	448.9	471.9	497.2	526.2	554.9	584.0	609.3	634.9	656.2	680.0	704.7
22.5°	442.1	467.4	494.8	524.9	554.9	586.7	614.7	640.1	666.5	693.3	718.8
25°	431.2	457.5	486.6	519.5	554.1	586.5	616.5	647.9	676.4	705.5	728.4
27.5°	417.9	445.4	476.0	510.1	545.5	578.7	614.0	647.6	676.3	704.3	724.2
30°	407.2	436.3	465.7	500.2	536.9	572.6	610.5	644.0	674.2	699.3	710.6
32.5°	396.2	423.8	454.2	489.1	526.7	565.1	602.6	637.0	664.9	679.9	680.2
35°	377.2	403.1	434.6	468.9	507.6	549.1	587.2	620.9	638.0	639.3	620.9
37.5°	356.5	380.2	409.9	444.3	486.6	528.0	566.8	589.3	595.0	575.9	542.0
40°	341.6	363.5	392.2	427.5	469.4	512.2	547.6	564.1	558.2	527.2	489.3
42.5°	326.0	346.4	374.1	408.8	451.0	494.2	524.4	533.2	517.4	481.6	437.3
45°	300.6	319.2	346.7	381.8	422.2	462.7	485.6	481.1	454.6	412.3	362.6
47.5°	274.0	292.2	316.8	349.2	390.7	425.6	441.1	427.5	389.9	343.3	302.9
50°	256.5	275.0	297.7	328.7	366.5	400.3	410.2	389.6	347.8	303.0	265.9
52.5°	239.2	255.1	277.3	307.2	343.4	371.9	377.2	353.5	310.3	270.1	237.2
55°	213.0	227.4	246.1	274.3	305.6	329.8	326.9	296.4	257.2	222.9	197.0
57.5°	187.6	198.4	215.8	242.2	269.7	285.9	275.6	249.5	213.0	184.9	163.1
60°	170.8	180.9	197.0	220.1	244.3	253.5	244.9	216.6	187.7	162.0	143.6
62.5°	154.9	163.8	177.7	199.1	218.6	224.1	214.8	190.1	164.1	142.2	127.0
65°	131.8	140.1	151.9	167.1	180.5	183.2	177.2	151.9	132.2	113.8	103.3
67.5°	110.8	116.2	125.5	138.6	145.8	147.3	135.7	119.8	102.4	91.2	83.3
70°	96.7	100.5	109.1	116.2	122.1	122.2	111.5	98.8	85.5	76.3	70.5
72.5°	83.1	86.7	93.2	98.1	102.6	101.1	91.3	81.3	70.5	63.5	59.3
75°	64.1	67.3	70.7	73.0	73.0	71.1	63.9	56.4	50.2	46.1	44.8
77.5°	46.6	49.2	50.4	50.0	49.4	46.4	41.9	37.0	34.8	32.9	31.8
80°	36.6	37.7	38.0	37.2	36.0	32.6	29.6	27.6	25.5	24.7	24.4
82.5°	27.1	28.1	27.1	27.4	24.9	22.1	20.4	19.7	18.9	18.6	18.2
85°	14.4	14.3	13.9	12.9	11.2	10.9	10.7	10.5	10.1	10.3	9.9
87.5°	6.3	6.4	6.3	6.8	7.3	7.4	8.0	8.4	8.9	9.0	9.7
90°	6.5	9.4	12.4	15.3	17.8	19.9	22.0	24.2	26.3	27.9	29.5
92.5°	15.2	15.4	15.5	15.7	16.8	18.9	21.1	23.2	25.3	26.9	28.5
95°	56.6	47.7	38.7	29.6	25.2	25.5	25.7	26.0	26.3	27.9	29.5
97.5°	145.1	150.8	156.5	162.1	150.0	120.4	90.8	61.2	31.5	31.7	31.8
100°	200.7	205.5	210.2	215.0	199.1	162.5	125.8	89.2	52.6	48.1	43.6
102.5°	262.5	266.0	269.5	273.0	272.4	267.6	262.8	258.0	253.3	204.5	155.9
105°	361.2	362.7	364.4	366.0	367.4	368.8	370.1	371.4	372.7	375.1	377.5
107.5°	453.8	454.6	455.4	456.2	457.5	459.3	461.1	462.9	464.7	465.9	467.1
110°	516.9	517.7	518.5	519.3	520.5	522.0	523.6	525.2	526.8	527.4	527.9



TEST NUMBER: P333031-927

CATALOG NUMBER: S124RDIW-S350D1560U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	578.7	580.1	581.5	583.0	584.1	584.8	585.6	586.3	587.1	586.9	586.8
115°	672.2	673.0	673.8	674.5	674.9	674.5	674.3	674.1	673.8	674.3	674.9
117.5°	757.2	758.4	759.4	760.5	761.3	761.8	762.5	763.0	763.6	763.5	763.4
120°	814.6	815.7	816.7	817.8	818.2	817.9	817.7	817.4	817.1	817.7	818.2
122.5°	867.7	868.3	868.9	869.7	870.1	870.5	870.8	871.2	871.6	872.0	872.3
125°	944.8	945.9	947.0	948.0	948.2	947.8	947.2	946.7	946.2	947.0	947.8
127.5°	1016.7	1016.9	1017.2	1017.5	1018.2	1019.5	1020.6	1021.8	1023.1	1022.9	1022.8
130°	1063.5	1063.7	1064.1	1064.3	1064.9	1065.6	1066.4	1067.2	1068.0	1068.3	1068.6
132.5°	1106.7	1107.2	1107.7	1108.2	1108.9	1109.9	1110.9	1111.9	1112.9	1113.2	1113.5
135°	1170.4	1170.2	1170.0	1169.7	1170.1	1171.2	1172.2	1173.3	1174.3	1174.9	1175.4
137.5°	1228.0	1228.0	1228.2	1228.3	1228.9	1230.1	1231.3	1232.4	1233.6	1234.1	1234.8
140°	1265.7	1266.2	1266.7	1267.3	1267.8	1268.3	1268.8	1269.4	1269.9	1270.7	1271.5
142.5°	1299.5	1300.5	1301.5	1302.4	1303.1	1303.4	1303.7	1304.0	1304.3	1304.9	1305.5
145°	1350.8	1351.5	1352.3	1353.1	1353.5	1353.5	1353.5	1353.5	1353.5	1353.8	1354.1
147.5°	1392.3	1393.8	1395.3	1396.8	1397.3	1397.1	1396.9	1396.5	1396.3	1396.5	1396.7
150°	1421.5	1422.5	1423.6	1424.7	1425.1	1424.8	1424.6	1424.3	1424.0	1424.0	1424.0
152.5°	1446.1	1447.0	1447.8	1448.7	1448.9	1448.3	1447.9	1447.4	1446.9	1447.4	1447.8
155°	1480.4	1480.7	1481.0	1481.2	1481.0	1480.2	1479.4	1478.6	1477.7	1478.8	1479.9
157.5°	1509.4	1509.3	1509.1	1508.9	1508.4	1507.4	1506.6	1505.7	1504.8	1506.2	1507.5
160°	1526.0	1525.2	1524.4	1523.6	1523.0	1522.7	1522.5	1522.3	1521.9	1523.6	1525.2
162.5°	1541.0	1540.0	1539.1	1538.0	1537.4	1537.1	1536.8	1536.6	1536.3	1537.9	1539.5
165°	1560.0	1558.8	1557.4	1556.1	1555.4	1555.4	1555.4	1555.4	1555.4	1557.5	1559.6
167.5°	1575.3	1573.9	1572.6	1571.1	1570.4	1570.3	1570.1	1569.9	1569.8	1572.1	1574.5
170°	1583.7	1582.1	1580.5	1578.9	1578.3	1578.5	1578.8	1579.1	1579.3	1581.4	1583.6
172.5°	1589.4	1587.9	1586.3	1584.7	1584.0	1584.3	1584.5	1584.8	1585.1	1587.1	1589.3
175°	1595.6	1594.0	1592.4	1590.9	1590.2	1590.5	1590.7	1591.0	1591.3	1593.6	1596.0
177.5°	1598.6	1597.1	1595.6	1594.2	1593.6	1594.0	1594.5	1594.9	1595.3	1597.0	1598.7
180°	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2



TEST NUMBER: P333031-927

CATALOG NUMBER: S124RDIW-S350D1560U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	465.3	465.3	465.3	465.3	465.3	465.3	465.3
2.5°	488.1	488.7	489.2	490.7	490.8	492.2	490.8
5°	528.5	531.2	535.3	539.4	539.8	542.4	537.7
7.5°	573.8	579.9	583.7	590.3	592.9	594.6	591.9
10°	605.0	610.6	620.6	625.4	630.3	631.1	628.8
12.5°	635.2	644.0	651.9	661.2	660.9	667.5	665.1
15°	675.3	684.5	695.4	705.7	709.4	709.4	712.4
17.5°	703.9	720.8	732.1	740.1	749.0	750.5	749.5
20°	723.3	741.5	753.5	764.0	770.0	771.7	771.7
22.5°	737.7	753.2	764.9	774.4	779.3	781.3	780.7
25°	747.7	761.0	768.1	771.0	772.2	771.9	768.3
27.5°	734.0	733.4	729.0	720.3	713.8	709.9	705.4
30°	708.0	698.2	686.9	674.5	658.6	646.4	642.7
32.5°	669.1	647.2	628.1	607.5	590.4	578.2	573.1
35°	594.0	559.3	530.9	506.2	488.2	477.0	473.2
37.5°	504.8	471.2	436.2	412.2	397.2	385.9	381.7
40°	448.1	411.5	381.0	358.5	343.1	332.0	331.8
42.5°	396.3	361.4	332.6	316.5	299.9	292.6	292.6
45°	324.6	296.6	272.2	259.4	249.5	243.5	241.9
47.5°	268.7	245.6	229.3	219.2	211.1	207.3	204.8
50°	237.3	217.1	204.1	195.4	190.8	186.0	185.6
52.5°	211.3	194.9	184.8	177.7	172.0	169.1	169.1
55°	177.5	164.6	157.5	152.0	147.6	145.3	144.3
57.5°	149.6	139.9	134.7	129.7	127.8	126.0	125.6
60°	132.2	125.6	120.7	116.8	114.0	113.4	113.2
62.5°	117.8	110.9	107.6	104.5	102.4	101.6	101.2
65°	97.1	92.1	89.0	86.6	85.9	84.5	84.4
67.5°	78.3	75.3	73.3	71.6	70.6	70.5	70.5
70°	66.8	65.0	63.4	62.4	61.9	61.5	61.5
72.5°	56.9	55.6	54.2	53.7	53.6	53.2	53.1
75°	43.3	42.0	42.2	41.3	40.5	39.5	39.0
77.5°	30.7	29.8	29.5	29.5	28.8	28.8	29.0
80°	23.8	22.9	22.7	22.9	22.7	22.1	22.1
82.5°	18.1	17.3	17.1	17.0	16.9	17.0	16.7
85°	9.7	9.3	9.3	9.3	9.7	9.6	9.3
87.5°	9.7	9.8	10.2	10.1	10.2	10.2	10.5
90°	31.1	32.6	33.7	34.2	34.8	35.3	35.8
92.5°	30.1	31.7	32.6	32.6	32.8	32.9	33.0
95°	31.1	32.6	33.6	33.8	34.1	34.4	34.6
97.5°	32.0	32.2	32.4	32.6	33.0	33.2	33.4
100°	39.1	34.5	32.4	32.6	33.0	33.2	33.4
102.5°	107.2	58.5	34.2	34.2	34.3	34.4	34.4
105°	379.9	382.3	378.7	369.2	359.6	350.1	340.5
107.5°	468.3	469.4	470.5	471.5	472.5	473.5	474.5
110°	528.5	528.9	529.7	530.4	531.2	532.0	532.8



TEST NUMBER: P333031-927

CATALOG NUMBER: S124RDIW-S350D1560U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	586.7	586.6	587.1	588.1	589.1	590.1	591.1
115°	675.3	675.9	676.2	676.2	676.2	676.2	676.2
117.5°	763.3	763.2	763.1	763.0	762.9	762.8	762.6
120°	818.7	819.3	819.3	818.7	818.2	817.7	817.1
122.5°	872.6	872.9	872.7	872.3	871.7	871.2	870.7
125°	948.6	949.4	949.9	950.1	950.4	950.7	950.9
127.5°	1022.6	1022.5	1022.2	1022.1	1021.8	1021.6	1021.4
130°	1068.8	1069.1	1069.2	1069.2	1069.2	1069.2	1069.2
132.5°	1113.7	1114.0	1114.0	1113.8	1113.6	1113.4	1113.2
135°	1175.9	1176.5	1177.0	1177.5	1178.1	1178.6	1179.1
137.5°	1235.3	1236.0	1236.1	1236.0	1235.8	1235.6	1235.5
140°	1272.3	1273.1	1273.6	1273.9	1274.1	1274.4	1274.7
142.5°	1306.1	1306.6	1306.9	1307.0	1307.1	1307.1	1307.2
145°	1354.3	1354.6	1355.0	1355.5	1356.1	1356.6	1357.1
147.5°	1396.9	1397.2	1397.4	1397.6	1397.9	1398.2	1398.4
150°	1424.0	1424.0	1424.2	1424.4	1424.7	1425.0	1425.2
152.5°	1448.2	1448.7	1448.7	1448.6	1448.4	1448.3	1448.1
155°	1481.0	1482.0	1482.2	1481.4	1480.6	1479.8	1479.0
157.5°	1508.9	1510.3	1510.3	1508.9	1507.5	1506.2	1504.8
160°	1526.8	1528.4	1528.4	1526.8	1525.2	1523.6	1521.9
162.5°	1541.1	1542.7	1542.5	1540.8	1539.0	1537.2	1535.3
165°	1561.8	1563.9	1563.8	1561.4	1559.0	1556.6	1554.3
167.5°	1576.8	1579.1	1579.0	1576.3	1573.7	1571.0	1568.4
170°	1585.7	1587.9	1587.5	1584.9	1582.2	1579.6	1576.9
172.5°	1591.4	1593.6	1593.2	1590.3	1587.5	1584.6	1581.7
175°	1598.5	1600.8	1600.4	1597.2	1594.0	1590.9	1587.7
177.5°	1600.4	1602.1	1601.7	1599.2	1596.6	1594.0	1591.5
180°	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2

(END OF REPORT)