

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333017

Luminaire Tested: **S124RDIW-S350D470U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333017
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S350D470U835-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 470 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3304.3 lumens
Efficiency: N/A
Efficacy: 143.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 23
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333017

CATALOG NUMBER: S124RDIW-S350D470U835-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333017

CATALOG NUMBER: S124RDIW-S350D470U835-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	96	96	96	96	80	80	80	64	64	64	50	50	50	43
1	97	92	89	85	88	85	81	78	70	68	66	57	55	54	44	44	43	37
2	88	81	75	70	80	74	69	65	62	58	55	50	48	45	39	38	36	31
3	80	71	64	58	73	65	59	54	55	50	46	44	41	39	35	33	31	27
4	74	63	55	50	67	58	51	46	49	44	40	40	36	33	31	29	27	23
5	68	56	48	43	62	52	45	40	44	38	34	36	32	29	28	26	24	20
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	26	23	21	18
7	58	46	38	32	53	42	35	30	36	30	26	29	25	22	24	21	19	16
8	53	41	34	29	49	38	32	27	32	27	23	27	23	20	22	19	17	14
9	50	38	30	26	46	35	28	24	30	25	21	25	21	18	20	17	15	13
10	47	35	28	23	43	32	26	22	27	22	19	23	19	16	19	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4991	4991	4991
5°	5002	4941	4971
10°	4970	4882	4882
15°	4914	4779	4743
20°	4835	4643	4558
25°	4735	4486	4372
30°	4638	4320	4139
35°	4529	4147	3905
40°	4400	3951	3652
45°	4280	3756	3394
50°	4143	3532	3121
55°	3997	3298	2825
60°	3836	3042	2522
65°	3689	2722	2223
70°	3474	2367	1888
75°	3203	1965	1535
80°	2794	1497	1409
85°	2371	1362	1269



TEST NUMBER: P333017

CATALOG NUMBER: S124RDIW-S350D470U835-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	58.1	1.8
10°-20°	161.9	4.9
20°-30°	233.8	7.1
30°-40°	265.1	8.0
40°-50°	255.9	7.7
50°-60°	212.8	6.4
60°-70°	147.0	4.4
70°-80°	74.5	2.3
80°-90°	20.9	0.6
90°-100°	20.7	0.6
100°-110°	132.1	4.0
110°-120°	252.8	7.6
120°-130°	320.9	9.7
130°-140°	343.3	10.4
140°-150°	321.0	9.7
150°-160°	258.9	7.8
160°-170°	167.0	5.1
170°-180°	57.6	1.7
0°-30°	453.8	13.7
0°-40°	718.9	21.8
0°-60°	1187.7	35.9
0°-90°	1430.0	43.3
90°-120°	405.6	12.3
90°-150°	1390.9	42.1
90°-180°	1874.0	56.7
0°-180°	3304.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	618	618	618	618	618	
5°	617	615	610	614	613	59
15°	588	583	572	571	568	166
25°	532	522	504	496	491	245
35°	460	444	421	405	396	287
45°	375	357	329	307	297	289
55°	284	264	234	211	201	254
65°	193	172	142	123	116	191
75°	103	85	63	53	49	108
85°	26	16	15	14	14	29
90°	1	6	10	13	14	2
95°	25	10	10	13	13	32
105°	136	139	141	144	129	143
115°	255	256	256	256	256	251
125°	358	360	359	360	361	320
135°	444	444	446	446	447	342
145°	512	513	514	514	515	320
155°	562	562	561	562	561	259
165°	592	590	590	593	590	167
175°	606	603	604	607	602	58
180°	606	606	606	606	606	



TEST NUMBER: P333017

CATALOG NUMBER: S124RDIW-S350D470U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	618.2	618.2	618.2	618.2	618.2	618.2	618.2	618.2	618.2	618.2	618.2
2.5°	619.7	619.3	619.0	618.7	618.3	617.7	616.8	615.9	614.9	614.0	614.9
5°	617.2	616.8	616.4	616.0	615.5	614.7	613.4	612.2	610.9	609.7	610.7
7.5°	611.6	611.2	610.8	610.3	609.9	608.8	607.2	605.5	603.9	602.3	602.9
10°	606.3	605.8	605.3	604.8	604.2	603.0	601.1	599.2	597.3	595.5	595.9
12.5°	599.5	598.9	598.3	597.7	597.1	595.7	593.4	591.2	589.0	586.7	587.0
15°	587.9	586.9	586.0	585.0	584.1	582.3	579.7	577.0	574.4	571.8	571.6
17.5°	573.8	572.4	571.0	569.7	568.3	566.0	562.9	559.7	556.6	553.4	552.8
20°	562.8	561.4	560.1	558.7	557.3	554.9	551.3	547.7	544.1	540.5	539.7
22.5°	550.7	549.1	547.6	546.1	544.5	541.8	538.0	534.2	530.4	526.5	525.3
25°	531.6	529.7	527.8	525.9	524.0	520.9	516.6	512.3	507.9	503.6	501.8
27.5°	511.5	509.1	506.7	504.4	502.0	498.5	493.9	489.3	484.7	480.1	477.8
30°	497.5	494.8	492.2	489.6	487.0	483.2	478.2	473.3	468.3	463.4	460.8
32.5°	482.7	479.7	476.8	473.8	470.8	466.8	461.7	456.6	451.5	446.4	443.3
35°	459.6	456.2	452.9	449.5	446.1	441.8	436.6	431.3	426.1	420.8	417.2
37.5°	434.9	431.4	428.0	424.5	421.0	416.4	410.5	404.7	398.9	393.1	389.1
40°	417.5	414.0	410.5	407.1	403.6	398.9	392.9	386.9	380.9	374.9	370.5
42.5°	400.8	397.2	393.5	389.9	386.3	381.3	375.1	368.8	362.6	356.3	351.8
45°	374.9	371.0	367.1	363.2	359.3	354.2	347.9	341.6	335.3	329.0	323.8
47.5°	348.1	344.1	340.1	336.0	332.0	326.7	320.2	313.6	307.0	300.5	295.1
50°	329.9	325.8	321.7	317.6	313.5	308.1	301.4	294.6	287.9	281.2	275.9
52.5°	311.4	307.3	303.3	299.3	295.3	289.8	282.9	276.0	269.1	262.2	256.9
55°	284.0	279.8	275.6	271.4	267.2	261.6	254.8	248.0	241.1	234.3	228.8
57.5°	256.9	252.5	248.2	243.8	239.4	233.9	227.1	220.4	213.7	206.9	201.4
60°	237.6	233.4	229.2	225.0	220.8	215.3	208.6	201.8	195.1	188.4	182.9
62.5°	220.2	215.8	211.4	207.1	202.7	197.1	190.2	183.3	176.4	169.5	164.4
65°	193.1	188.6	184.1	179.6	175.0	169.4	162.7	155.9	149.2	142.5	138.0
67.5°	165.0	160.7	156.3	152.0	147.7	142.4	136.1	129.9	123.6	117.4	113.5
70°	147.2	142.8	138.4	134.0	129.5	124.3	118.3	112.3	106.3	100.3	96.9
72.5°	128.3	124.3	120.3	116.3	112.3	107.5	101.8	96.1	90.5	84.8	81.9
75°	102.7	98.8	94.9	91.0	87.1	82.7	77.8	72.8	67.9	63.0	60.5
77.5°	76.8	73.5	70.2	66.9	63.6	59.9	55.9	51.9	47.9	43.9	42.5
80°	60.1	57.1	54.0	51.0	47.9	44.8	41.7	38.5	35.3	32.2	31.9
82.5°	45.7	42.9	40.1	37.3	34.5	32.2	30.4	28.6	26.8	25.0	24.8
85°	25.6	23.5	21.4	19.2	17.1	15.9	15.6	15.3	15.0	14.7	14.5
87.5°	9.0	8.5	8.1	7.6	7.2	7.0	7.1	7.1	7.2	7.3	7.3
90°	1.4	2.5	3.6	4.7	5.8	6.7	7.6	8.4	9.2	10.0	10.6
92.5°	5.7	5.8	5.8	5.9	6.0	6.4	7.2	8.0	8.8	9.6	10.2
95°	24.9	21.5	18.1	14.7	11.2	9.6	9.7	9.8	9.9	10.0	10.6
97.5°	52.9	55.1	57.2	59.3	61.5	56.9	45.7	34.4	23.2	12.0	12.0
100°	74.3	76.1	78.0	79.8	81.6	75.5	61.6	47.7	33.8	19.9	18.2
102.5°	98.3	99.6	100.9	102.2	103.6	103.3	101.5	99.7	97.9	96.1	77.6
105°	136.4	137.0	137.6	138.2	138.8	139.4	139.9	140.4	140.9	141.4	142.3
107.5°	171.9	172.2	172.5	172.8	173.1	173.6	174.2	174.9	175.6	176.3	176.7
110°	195.8	196.1	196.4	196.7	197.0	197.4	198.0	198.7	199.3	199.9	200.1



TEST NUMBER: P333017

CATALOG NUMBER: S124RDIW-S350D470U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	219.0	219.5	220.1	220.6	221.2	221.6	221.9	222.1	222.4	222.7	222.7
115°	254.7	255.0	255.3	255.6	255.9	256.0	255.9	255.8	255.7	255.6	255.8
117.5°	286.9	287.3	287.7	288.1	288.5	288.8	289.0	289.2	289.5	289.7	289.6
120°	308.6	309.0	309.4	309.8	310.2	310.4	310.3	310.2	310.1	310.0	310.2
122.5°	328.9	329.2	329.4	329.7	329.9	330.1	330.2	330.4	330.5	330.7	330.8
125°	358.0	358.4	358.8	359.2	359.6	359.7	359.5	359.3	359.1	358.9	359.2
127.5°	385.6	385.7	385.8	385.9	386.0	386.3	386.7	387.2	387.7	388.1	388.1
130°	403.3	403.4	403.6	403.7	403.8	404.0	404.3	404.6	404.9	405.2	405.3
132.5°	419.7	419.8	420.0	420.2	420.4	420.7	421.1	421.4	421.8	422.2	422.3
135°	444.1	444.0	443.9	443.8	443.7	443.9	444.3	444.7	445.1	445.5	445.7
137.5°	465.8	465.8	465.9	465.9	466.0	466.2	466.6	467.1	467.5	468.0	468.2
140°	479.9	480.1	480.3	480.5	480.7	480.9	481.1	481.4	481.6	481.8	482.1
142.5°	492.6	493.0	493.4	493.7	494.1	494.3	494.4	494.6	494.7	494.8	495.0
145°	512.1	512.4	512.7	513.0	513.3	513.5	513.5	513.5	513.5	513.5	513.6
147.5°	527.6	528.2	528.7	529.3	529.9	530.1	530.0	529.9	529.8	529.7	529.8
150°	538.9	539.3	539.7	540.1	540.5	540.6	540.5	540.4	540.3	540.2	540.2
152.5°	548.3	548.6	548.9	549.2	549.6	549.6	549.5	549.3	549.1	548.9	549.1
155°	561.5	561.6	561.7	561.8	561.9	561.8	561.5	561.2	560.9	560.6	561.0
157.5°	572.7	572.6	572.5	572.5	572.4	572.2	571.9	571.5	571.2	570.9	571.4
160°	579.2	578.9	578.6	578.3	578.0	577.8	577.7	577.6	577.5	577.4	578.0
162.5°	585.0	584.6	584.2	583.8	583.5	583.2	583.1	583.0	582.9	582.8	583.4
165°	592.3	591.8	591.3	590.8	590.3	590.1	590.1	590.1	590.1	590.1	590.9
167.5°	598.1	597.6	597.1	596.6	596.0	595.7	595.7	595.6	595.6	595.5	596.4
170°	601.4	600.8	600.2	599.6	599.0	598.7	598.8	598.9	599.0	599.1	599.9
172.5°	603.6	603.0	602.4	601.8	601.2	600.9	601.0	601.1	601.2	601.3	602.1
175°	605.9	605.3	604.7	604.1	603.5	603.3	603.4	603.5	603.6	603.7	604.6
177.5°	607.0	606.5	605.9	605.3	604.8	604.6	604.7	604.9	605.0	605.2	605.8
180°	605.9	605.9	605.9	605.9	605.9	605.9	605.9	605.9	605.9	605.9	605.9



TEST NUMBER: P333017

CATALOG NUMBER: S124RDIW-S350D470U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	618.2	618.2	618.2	618.2	618.2	618.2	618.2	618.2
2.5°	615.9	616.8	617.7	618.1	618.0	618.0	617.9	617.8
5°	611.8	612.8	613.9	614.3	614.1	613.9	613.6	613.4
7.5°	603.6	604.3	605.0	605.1	604.8	604.5	604.1	603.8
10°	596.3	596.7	597.1	597.1	596.7	596.3	595.9	595.5
12.5°	587.2	587.5	587.8	587.6	587.0	586.4	585.8	585.2
15°	571.4	571.2	570.9	570.5	569.7	569.0	568.3	567.5
17.5°	552.2	551.7	551.1	550.2	549.1	548.0	546.9	545.8
20°	538.9	538.0	537.2	536.1	534.7	533.3	532.0	530.6
22.5°	524.0	522.7	521.5	520.3	519.2	518.1	517.0	515.8
25°	500.0	498.3	496.5	495.1	494.0	492.9	491.9	490.8
27.5°	475.6	473.4	471.2	469.4	467.8	466.3	464.8	463.3
30°	458.1	455.5	452.9	450.7	449.0	447.4	445.7	444.0
32.5°	440.3	437.2	434.2	431.8	430.2	428.6	427.0	425.4
35°	413.6	410.1	406.5	403.8	401.9	400.0	398.1	396.2
37.5°	385.1	381.1	377.1	374.1	372.2	370.3	368.4	366.5
40°	366.0	361.6	357.2	354.1	352.2	350.3	348.4	346.5
42.5°	347.3	342.8	338.3	335.1	333.1	331.1	329.1	327.2
45°	318.7	313.5	308.3	304.8	302.9	301.0	299.1	297.3
47.5°	289.8	284.4	279.1	275.4	273.3	271.2	269.1	267.1
50°	270.6	265.4	260.1	256.5	254.5	252.5	250.5	248.5
52.5°	251.5	246.2	240.9	237.1	235.1	233.0	230.9	228.8
55°	223.4	217.9	212.4	208.7	206.7	204.7	202.7	200.7
57.5°	195.8	190.3	184.7	181.2	179.7	178.2	176.6	175.1
60°	177.4	172.0	166.5	162.9	161.2	159.6	157.9	156.2
62.5°	159.4	154.3	149.3	146.1	144.7	143.4	142.0	140.7
65°	133.4	128.9	124.4	121.5	120.2	119.0	117.7	116.4
67.5°	109.6	105.7	101.8	99.2	97.8	96.4	95.0	93.6
70°	93.4	89.9	86.5	84.2	83.1	82.1	81.0	80.0
72.5°	78.9	75.9	73.0	71.0	70.0	69.1	68.1	67.1
75°	58.1	55.7	53.3	51.8	51.1	50.5	49.9	49.2
77.5°	41.1	39.7	38.3	37.5	37.3	37.1	36.9	36.7
80°	31.6	31.2	30.9	30.7	30.6	30.5	30.4	30.3
82.5°	24.5	24.3	24.1	23.9	23.8	23.7	23.6	23.5
85°	14.3	14.0	13.8	13.7	13.7	13.7	13.7	13.7
87.5°	7.4	7.4	7.4	7.5	7.6	7.8	7.9	8.0
90°	11.2	11.8	12.4	12.8	13.0	13.2	13.4	13.6
92.5°	10.8	11.4	12.0	12.3	12.4	12.4	12.5	12.5
95°	11.2	11.8	12.4	12.7	12.8	12.9	13.0	13.1
97.5°	12.1	12.1	12.2	12.3	12.4	12.5	12.6	12.7
100°	16.5	14.8	13.1	12.3	12.4	12.5	12.6	12.7
102.5°	59.1	40.7	22.2	13.0	13.0	13.0	13.0	13.1
105°	143.2	144.1	145.0	143.7	140.0	136.4	132.8	129.2
107.5°	177.2	177.6	178.1	178.5	178.9	179.2	179.6	180.0
110°	200.3	200.5	200.7	200.9	201.2	201.5	201.8	202.1



TEST NUMBER: P333017

CATALOG NUMBER: S124RDIW-S350D470U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	222.6	222.6	222.5	222.7	223.1	223.5	223.9	224.2
115°	256.0	256.2	256.4	256.5	256.5	256.5	256.5	256.5
117.5°	289.6	289.6	289.5	289.5	289.4	289.4	289.4	289.3
120°	310.4	310.6	310.8	310.8	310.6	310.4	310.2	310.0
122.5°	330.9	331.0	331.1	331.1	330.9	330.7	330.5	330.3
125°	359.5	359.8	360.1	360.3	360.4	360.5	360.6	360.7
127.5°	388.0	387.9	387.9	387.8	387.7	387.6	387.6	387.5
130°	405.4	405.5	405.6	405.6	405.6	405.6	405.6	405.6
132.5°	422.4	422.5	422.6	422.6	422.5	422.5	422.4	422.3
135°	445.9	446.1	446.3	446.5	446.7	446.9	447.1	447.3
137.5°	468.4	468.6	468.9	468.9	468.9	468.8	468.8	468.7
140°	482.4	482.7	483.0	483.2	483.3	483.4	483.5	483.6
142.5°	495.2	495.5	495.7	495.8	495.8	495.9	495.9	495.9
145°	513.7	513.8	513.9	514.0	514.2	514.4	514.6	514.8
147.5°	529.9	529.9	530.0	530.1	530.2	530.3	530.4	530.5
150°	540.2	540.2	540.2	540.3	540.4	540.5	540.6	540.7
152.5°	549.2	549.4	549.6	549.6	549.6	549.5	549.4	549.4
155°	561.4	561.8	562.2	562.3	562.0	561.7	561.4	561.1
157.5°	571.9	572.4	572.9	572.9	572.4	571.9	571.4	570.9
160°	578.6	579.2	579.8	579.8	579.2	578.6	578.0	577.4
162.5°	584.0	584.6	585.2	585.2	584.5	583.8	583.1	582.5
165°	591.7	592.5	593.3	593.2	592.3	591.4	590.5	589.6
167.5°	597.3	598.2	599.1	599.0	598.0	597.0	596.0	595.0
170°	600.7	601.5	602.4	602.3	601.2	600.2	599.2	598.2
172.5°	602.9	603.7	604.5	604.4	603.3	602.2	601.1	600.0
175°	605.5	606.4	607.3	607.1	605.9	604.7	603.5	602.3
177.5°	606.5	607.1	607.8	607.6	606.7	605.7	604.7	603.8
180°	605.9	605.9	605.9	605.9	605.9	605.9	605.9	605.9

(END OF REPORT)