

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333017-927

Luminaire Tested: **S124RDIW-S350D470U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333017-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S350D470U927-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 470 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2617.6 lumens
Efficiency: N/A
Efficacy: 113.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 23
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333017-927

CATALOG NUMBER: S124RDIW-S350D470U927-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333017-927

CATALOG NUMBER: S124RDIW-S350D470U927-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	96	96	96	96	80	80	80	64	64	64	50	50	50	43				43
1	97	92	89	85	88	85	81	78	70	68	66	57	55	54	44	44	43	37				37
2	88	81	75	70	80	74	69	65	62	58	55	50	48	45	39	38	36	31				31
3	80	71	64	58	73	65	59	54	55	50	46	44	41	39	35	33	31	27				27
4	74	63	55	50	67	58	51	46	49	44	40	40	36	33	31	29	27	23				23
5	68	56	48	43	62	52	45	40	44	38	34	36	32	29	28	26	24	20				20
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	26	23	21	18				18
7	58	46	38	32	53	42	35	30	36	30	26	29	25	22	24	21	19	16				16
8	53	41	34	29	49	38	32	27	32	27	23	27	23	20	22	19	17	14				14
9	50	38	30	26	46	35	28	24	30	25	21	25	21	18	20	17	15	13				13
10	47	35	28	23	43	32	26	22	27	22	19	23	19	16	19	16	14	12				12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3953	3953	3953
5°	3962	3914	3938
10°	3937	3867	3867
15°	3892	3786	3758
20°	3830	3679	3611
25°	3751	3553	3463
30°	3674	3422	3278
35°	3588	3286	3094
40°	3485	3130	2893
45°	3391	2975	2689
50°	3282	2798	2473
55°	3167	2612	2238
60°	3039	2409	1997
65°	2923	2157	1761
70°	2752	1876	1496
75°	2539	1556	1216
80°	2213	1186	1116
85°	1880	1074	1010



TEST NUMBER: P333017-927

CATALOG NUMBER: S124RDIW-S350D470U927-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.0	1.8
10°-20°	128.3	4.9
20°-30°	185.2	7.1
30°-40°	210.0	8.0
40°-50°	202.8	7.7
50°-60°	168.6	6.4
60°-70°	116.4	4.4
70°-80°	59.0	2.3
80°-90°	16.5	0.6
90°-100°	16.4	0.6
100°-110°	104.7	4.0
110°-120°	200.2	7.6
120°-130°	254.2	9.7
130°-140°	272.0	10.4
140°-150°	254.3	9.7
150°-160°	205.1	7.8
160°-170°	132.3	5.1
170°-180°	45.6	1.7
0°-30°	359.5	13.7
0°-40°	569.5	21.8
0°-60°	940.8	35.9
0°-90°	1132.8	43.3
90°-120°	321.3	12.3
90°-150°	1101.8	42.1
90°-180°	1485.0	56.7
0°-180°	2617.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	490	490	490	490	490	
5°	489	487	483	486	486	46
15°	466	462	453	452	450	131
25°	421	414	399	393	389	194
35°	364	352	333	321	314	227
45°	297	283	261	243	236	229
55°	225	209	186	167	159	201
65°	153	136	113	97	92	151
75°	81	67	50	42	39	86
85°	20	13	12	11	11	23
90°	1	5	8	10	11	2
95°	20	8	8	10	10	25
105°	108	110	112	114	102	113
115°	202	203	202	203	203	199
125°	284	285	284	285	286	253
135°	352	352	353	354	354	271
145°	406	407	407	407	408	253
155°	445	445	444	445	444	205
165°	469	468	468	470	467	133
175°	480	478	478	481	477	46
180°	480	480	480	480	480	



TEST NUMBER: P333017-927

CATALOG NUMBER: S124RDIW-S350D470U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	489.7	489.7	489.7	489.7	489.7	489.7	489.7	489.7	489.7	489.7	489.7
2.5°	490.9	490.6	490.4	490.1	489.8	489.3	488.6	487.9	487.1	486.4	487.1
5°	488.9	488.6	488.3	488.0	487.6	487.0	485.9	485.0	483.9	483.0	483.8
7.5°	484.5	484.2	483.9	483.5	483.2	482.3	481.0	479.7	478.4	477.1	477.6
10°	480.3	479.9	479.5	479.1	478.6	477.7	476.2	474.7	473.2	471.7	472.1
12.5°	474.9	474.4	474.0	473.5	473.0	471.9	470.1	468.3	466.6	464.8	465.0
15°	465.7	464.9	464.2	463.4	462.7	461.3	459.2	457.1	455.0	453.0	452.8
17.5°	454.6	453.4	452.3	451.3	450.2	448.4	445.9	443.4	440.9	438.4	437.9
20°	445.8	444.7	443.7	442.6	441.5	439.6	436.7	433.9	431.0	428.2	427.5
22.5°	436.3	435.0	433.8	432.6	431.3	429.2	426.2	423.2	420.2	417.1	416.1
25°	421.1	419.6	418.1	416.6	415.1	412.6	409.2	405.8	402.3	398.9	397.5
27.5°	405.2	403.3	401.4	399.6	397.7	394.9	391.3	387.6	384.0	380.3	378.5
30°	394.1	392.0	389.9	387.9	385.8	382.8	378.8	374.9	371.0	367.1	365.0
32.5°	382.4	380.0	377.7	375.3	373.0	369.8	365.8	361.7	357.7	353.6	351.2
35°	364.1	361.4	358.8	356.1	353.4	350.0	345.9	341.7	337.5	333.4	330.5
37.5°	344.5	341.7	339.1	336.3	333.5	329.9	325.2	320.6	316.0	311.4	308.2
40°	330.7	328.0	325.2	322.5	319.7	316.0	311.2	306.5	301.7	297.0	293.5
42.5°	317.5	314.7	311.7	308.9	306.0	302.1	297.1	292.2	287.2	282.3	278.7
45°	297.0	293.9	290.8	287.7	284.6	280.6	275.6	270.6	265.6	260.6	256.5
47.5°	275.8	272.6	269.4	266.2	263.0	258.8	253.7	248.4	243.2	238.1	233.8
50°	261.3	258.1	254.8	251.6	248.3	244.1	238.8	233.4	228.1	222.8	218.6
52.5°	246.7	243.4	240.3	237.1	233.9	229.6	224.1	218.6	213.2	207.7	203.5
55°	225.0	221.7	218.3	215.0	211.7	207.2	201.8	196.5	191.0	185.6	181.3
57.5°	203.5	200.0	196.6	193.1	189.6	185.3	179.9	174.6	169.3	163.9	159.5
60°	188.2	184.9	181.6	178.2	174.9	170.6	165.2	159.9	154.6	149.2	144.9
62.5°	174.4	171.0	167.5	164.1	160.6	156.1	150.7	145.2	139.7	134.3	130.2
65°	153.0	149.4	145.8	142.3	138.6	134.2	128.9	123.5	118.2	112.9	109.3
67.5°	130.7	127.3	123.8	120.4	117.0	112.8	107.8	102.9	97.9	93.0	89.9
70°	116.6	113.1	109.6	106.2	102.6	98.5	93.7	89.0	84.2	79.5	76.8
72.5°	101.6	98.5	95.3	92.1	89.0	85.2	80.6	76.1	71.7	67.2	64.9
75°	81.4	78.3	75.2	72.1	69.0	65.5	61.6	57.7	53.8	49.9	47.9
77.5°	60.8	58.2	55.6	53.0	50.4	47.5	44.3	41.1	37.9	34.8	33.7
80°	47.6	45.2	42.8	40.4	37.9	35.5	33.0	30.5	28.0	25.5	25.3
82.5°	36.2	34.0	31.8	29.5	27.3	25.5	24.1	22.7	21.2	19.8	19.6
85°	20.3	18.6	17.0	15.2	13.5	12.6	12.4	12.1	11.9	11.6	11.5
87.5°	7.1	6.7	6.4	6.0	5.7	5.5	5.6	5.6	5.7	5.8	5.8
90°	1.1	2.0	2.9	3.7	4.6	5.3	6.0	6.7	7.3	7.9	8.4
92.5°	4.5	4.6	4.6	4.7	4.8	5.1	5.7	6.3	7.0	7.6	8.1
95°	19.7	17.0	14.3	11.6	8.9	7.6	7.7	7.8	7.8	7.9	8.4
97.5°	41.9	43.6	45.3	47.0	48.7	45.1	36.2	27.3	18.4	9.5	9.5
100°	58.9	60.3	61.8	63.2	64.6	59.8	48.8	37.8	26.8	15.8	14.4
102.5°	77.9	78.9	79.9	81.0	82.1	81.8	80.4	79.0	77.6	76.1	61.5
105°	108.1	108.5	109.0	109.5	110.0	110.4	110.8	111.2	111.6	112.0	112.7
107.5°	136.2	136.4	136.7	136.9	137.1	137.5	138.0	138.6	139.1	139.7	140.0
110°	155.1	155.3	155.6	155.8	156.1	156.4	156.9	157.4	157.9	158.4	158.5



TEST NUMBER: P333017-927

CATALOG NUMBER: S124RDIW-S350D470U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	173.5	173.9	174.4	174.8	175.2	175.5	175.8	175.9	176.2	176.4	176.4
115°	201.8	202.0	202.2	202.5	202.7	202.8	202.7	202.6	202.6	202.5	202.6
117.5°	227.3	227.6	227.9	228.2	228.5	228.8	228.9	229.1	229.3	229.5	229.4
120°	244.5	244.8	245.1	245.4	245.7	245.9	245.8	245.7	245.7	245.6	245.7
122.5°	260.5	260.8	260.9	261.2	261.3	261.5	261.6	261.7	261.8	262.0	262.1
125°	283.6	283.9	284.2	284.6	284.9	284.9	284.8	284.6	284.5	284.3	284.6
127.5°	305.5	305.5	305.6	305.7	305.8	306.0	306.3	306.7	307.1	307.4	307.4
130°	319.5	319.6	319.7	319.8	319.9	320.0	320.3	320.5	320.8	321.0	321.1
132.5°	332.5	332.6	332.7	332.9	333.0	333.3	333.6	333.8	334.1	334.5	334.5
135°	351.8	351.7	351.6	351.6	351.5	351.6	352.0	352.3	352.6	352.9	353.1
137.5°	369.0	369.0	369.1	369.1	369.2	369.3	369.6	370.0	370.3	370.7	370.9
140°	380.2	380.3	380.5	380.6	380.8	381.0	381.1	381.4	381.5	381.7	381.9
142.5°	390.2	390.5	390.9	391.1	391.4	391.6	391.7	391.8	391.9	392.0	392.1
145°	405.7	405.9	406.2	406.4	406.6	406.8	406.8	406.8	406.8	406.8	406.9
147.5°	418.0	418.4	418.8	419.3	419.8	419.9	419.9	419.8	419.7	419.6	419.7
150°	426.9	427.2	427.5	427.9	428.2	428.3	428.2	428.1	428.0	427.9	427.9
152.5°	434.4	434.6	434.8	435.1	435.4	435.4	435.3	435.1	435.0	434.8	435.0
155°	444.8	444.9	445.0	445.0	445.1	445.0	444.8	444.6	444.3	444.1	444.4
157.5°	453.7	453.6	453.5	453.5	453.4	453.3	453.0	452.7	452.5	452.3	452.7
160°	458.8	458.6	458.4	458.1	457.9	457.7	457.6	457.6	457.5	457.4	457.9
162.5°	463.4	463.1	462.8	462.5	462.2	462.0	461.9	461.8	461.8	461.7	462.2
165°	469.2	468.8	468.4	468.0	467.6	467.5	467.5	467.5	467.5	467.5	468.1
167.5°	473.8	473.4	473.0	472.6	472.1	471.9	471.9	471.8	471.8	471.7	472.5
170°	476.4	475.9	475.5	475.0	474.5	474.3	474.4	474.4	474.5	474.6	475.2
172.5°	478.2	477.7	477.2	476.7	476.3	476.0	476.1	476.2	476.3	476.3	477.0
175°	480.0	479.5	479.0	478.6	478.1	477.9	478.0	478.1	478.2	478.2	479.0
177.5°	480.9	480.5	480.0	479.5	479.1	479.0	479.0	479.2	479.3	479.4	479.9
180°	480.0	480.0	480.0	480.0	480.0	480.0	480.0	480.0	480.0	480.0	480.0



TEST NUMBER: P333017-927

CATALOG NUMBER: S124RDIW-S350D470U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	489.7	489.7	489.7	489.7	489.7	489.7	489.7	489.7
2.5°	487.9	488.6	489.3	489.6	489.6	489.6	489.5	489.4
5°	484.7	485.4	486.3	486.6	486.5	486.3	486.1	485.9
7.5°	478.2	478.7	479.3	479.3	479.1	478.9	478.6	478.3
10°	472.4	472.7	473.0	473.0	472.7	472.4	472.1	471.7
12.5°	465.2	465.4	465.6	465.5	465.0	464.5	464.1	463.6
15°	452.7	452.5	452.3	451.9	451.3	450.8	450.2	449.6
17.5°	437.4	437.0	436.6	435.9	435.0	434.1	433.2	432.4
20°	426.9	426.2	425.6	424.7	423.6	422.5	421.4	420.3
22.5°	415.1	414.1	413.1	412.2	411.3	410.4	409.6	408.6
25°	396.1	394.7	393.3	392.2	391.3	390.5	389.7	388.8
27.5°	376.8	375.0	373.3	371.9	370.6	369.4	368.2	367.0
30°	362.9	360.8	358.8	357.0	355.7	354.4	353.1	351.7
32.5°	348.8	346.3	344.0	342.1	340.8	339.5	338.3	337.0
35°	327.6	324.9	322.0	319.9	318.4	316.9	315.4	313.9
37.5°	305.1	301.9	298.7	296.4	294.9	293.3	291.8	290.3
40°	289.9	286.5	283.0	280.5	279.0	277.5	276.0	274.5
42.5°	275.1	271.6	268.0	265.5	263.9	262.3	260.7	259.2
45°	252.5	248.3	244.2	241.5	240.0	238.4	236.9	235.5
47.5°	229.6	225.3	221.1	218.2	216.5	214.8	213.2	211.6
50°	214.4	210.2	206.0	203.2	201.6	200.0	198.4	196.9
52.5°	199.2	195.0	190.8	187.8	186.2	184.6	182.9	181.3
55°	177.0	172.6	168.3	165.3	163.7	162.2	160.6	159.0
57.5°	155.1	150.8	146.3	143.5	142.4	141.2	139.9	138.7
60°	140.5	136.3	131.9	129.0	127.7	126.4	125.1	123.7
62.5°	126.3	122.2	118.3	115.7	114.6	113.6	112.5	111.5
65°	105.7	102.1	98.5	96.3	95.2	94.3	93.2	92.2
67.5°	86.8	83.7	80.6	78.6	77.5	76.4	75.3	74.1
70°	74.0	71.2	68.5	66.7	65.8	65.0	64.2	63.4
72.5°	62.5	60.1	57.8	56.2	55.5	54.7	53.9	53.2
75°	46.0	44.1	42.2	41.0	40.5	40.0	39.5	39.0
77.5°	32.6	31.4	30.3	29.7	29.5	29.4	29.2	29.1
80°	25.0	24.7	24.5	24.3	24.2	24.2	24.1	24.0
82.5°	19.4	19.3	19.1	18.9	18.9	18.8	18.7	18.6
85°	11.3	11.1	10.9	10.9	10.9	10.9	10.9	10.9
87.5°	5.9	5.9	5.9	5.9	6.0	6.2	6.3	6.3
90°	8.9	9.3	9.8	10.1	10.3	10.5	10.6	10.8
92.5°	8.6	9.0	9.5	9.7	9.8	9.8	9.9	9.9
95°	8.9	9.3	9.8	10.1	10.1	10.2	10.3	10.4
97.5°	9.6	9.6	9.7	9.7	9.8	9.9	10.0	10.1
100°	13.1	11.7	10.4	9.7	9.8	9.9	10.0	10.1
102.5°	46.8	32.2	17.6	10.3	10.3	10.3	10.3	10.4
105°	113.4	114.2	114.9	113.8	110.9	108.1	105.2	102.3
107.5°	140.4	140.7	141.1	141.4	141.7	142.0	142.3	142.6
110°	158.7	158.8	159.0	159.1	159.4	159.6	159.9	160.1



TEST NUMBER: P333017-927

CATALOG NUMBER: S124RDIW-S350D470U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	176.3	176.3	176.3	176.4	176.7	177.1	177.4	177.6
115°	202.8	203.0	203.1	203.2	203.2	203.2	203.2	203.2
117.5°	229.4	229.4	229.3	229.3	229.3	229.3	229.3	229.2
120°	245.9	246.1	246.2	246.2	246.1	245.9	245.7	245.6
122.5°	262.1	262.2	262.3	262.3	262.1	262.0	261.8	261.7
125°	284.8	285.0	285.3	285.4	285.5	285.6	285.7	285.7
127.5°	307.4	307.3	307.3	307.2	307.1	307.0	307.0	307.0
130°	321.2	321.2	321.3	321.3	321.3	321.3	321.3	321.3
132.5°	334.6	334.7	334.8	334.8	334.7	334.7	334.6	334.5
135°	353.2	353.4	353.6	353.7	353.9	354.0	354.2	354.3
137.5°	371.1	371.2	371.5	371.5	371.5	371.4	371.4	371.3
140°	382.1	382.4	382.6	382.8	382.9	382.9	383.0	383.1
142.5°	392.3	392.5	392.7	392.8	392.8	392.8	392.8	392.8
145°	406.9	407.0	407.1	407.2	407.3	407.5	407.7	407.8
147.5°	419.8	419.8	419.9	419.9	420.0	420.1	420.2	420.3
150°	427.9	427.9	427.9	428.0	428.1	428.2	428.3	428.3
152.5°	435.1	435.2	435.4	435.4	435.4	435.3	435.2	435.2
155°	444.7	445.0	445.4	445.4	445.2	445.0	444.7	444.5
157.5°	453.0	453.4	453.8	453.8	453.4	453.0	452.7	452.3
160°	458.4	458.8	459.3	459.3	458.8	458.4	457.9	457.4
162.5°	462.6	463.1	463.6	463.6	463.0	462.5	461.9	461.4
165°	468.7	469.4	470.0	469.9	469.2	468.5	467.8	467.1
167.5°	473.2	473.9	474.6	474.5	473.7	472.9	472.1	471.3
170°	475.9	476.5	477.2	477.1	476.3	475.5	474.7	473.9
172.5°	477.6	478.2	478.9	478.8	477.9	477.1	476.2	475.3
175°	479.7	480.4	481.1	480.9	480.0	479.0	478.1	477.1
177.5°	480.5	480.9	481.5	481.3	480.6	479.8	479.0	478.3
180°	480.0	480.0	480.0	480.0	480.0	480.0	480.0	480.0

(END OF REPORT)