

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333022-927

Luminaire Tested: **S124RDIW-S350D770U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333022-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S350D770U927-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 770 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3242.9 lumens
Efficiency: N/A
Efficacy: 106.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 30.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333022-927

CATALOG NUMBER: S124RDIW-S350D770U927-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333022-927

CATALOG NUMBER: S124RDIW-S350D770U927-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	42	42	42	35				
1	95	90	87	83	85	82	79	76	66	64	62	51	50	49	38	37	36	30				
2	86	79	73	68	78	72	67	63	58	54	51	45	43	41	33	32	31	25				
3	79	70	63	57	71	63	57	52	51	47	43	40	37	35	30	28	26	22				
4	72	62	54	48	65	56	50	44	46	41	37	36	32	30	27	24	23	19				
5	66	55	47	41	60	50	43	38	41	36	32	32	29	26	24	22	20	16				
6	61	49	41	36	55	45	38	33	37	32	28	29	25	23	22	19	18	14				
7	56	44	37	31	51	41	34	29	33	28	24	26	23	20	20	17	16	13				
8	52	40	33	28	47	37	30	26	30	25	22	24	20	18	18	16	14	12				
9	48	37	29	25	44	34	27	23	28	23	19	22	19	16	17	14	13	10				
10	45	34	27	22	41	31	25	20	25	21	17	20	17	14	16	13	12	9				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3953	3953	3953
5°	3962	3914	3938
10°	3937	3867	3867
15°	3892	3786	3758
20°	3830	3679	3611
25°	3751	3553	3463
30°	3674	3422	3278
35°	3588	3286	3094
40°	3485	3130	2893
45°	3391	2975	2689
50°	3282	2798	2473
55°	3167	2612	2238
60°	3039	2409	1997
65°	2923	2157	1761
70°	2752	1876	1496
75°	2539	1556	1216
80°	2213	1186	1116
85°	1880	1074	1010



TEST NUMBER: P333022-927

CATALOG NUMBER: S124RDIW-S350D770U927-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.0	1.4
10°-20°	128.3	4.0
20°-30°	185.2	5.7
30°-40°	210.0	6.5
40°-50°	202.8	6.3
50°-60°	168.6	5.2
60°-70°	116.4	3.6
70°-80°	59.0	1.8
80°-90°	17.4	0.5
90°-100°	50.1	1.5
100°-110°	148.5	4.6
110°-120°	252.1	7.8
120°-130°	332.4	10.3
130°-140°	373.3	11.5
140°-150°	366.9	11.3
150°-160°	308.6	9.5
160°-170°	205.3	6.3
170°-180°	71.9	2.2
0°-30°	359.5	11.1
0°-40°	569.5	17.6
0°-60°	940.8	29.0
0°-90°	1133.7	35.0
90°-120°	450.8	13.9
90°-150°	1523.4	47.0
90°-180°	2109.0	65.0
0°-180°	3242.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	490	490	490	490	490	
5°	489	487	483	486	486	46
15°	466	462	453	452	450	131
25°	421	414	399	393	389	194
35°	364	352	333	321	314	227
45°	297	283	261	243	236	229
55°	225	209	186	167	159	201
65°	153	136	113	97	92	151
75°	81	67	50	42	39	86
85°	20	13	12	11	11	23
90°	2	8	13	16	18	3
95°	35	40	45	46	46	39
105°	137	138	140	142	144	145
115°	256	256	255	255	254	253
125°	373	373	373	372	370	333
135°	482	485	485	484	482	372
145°	585	587	588	587	586	366
155°	670	670	670	672	670	308
165°	730	728	727	730	728	206
175°	759	756	756	759	756	72
180°	760	760	760	760	760	



TEST NUMBER: P333022-927

CATALOG NUMBER: S124RDIW-S350D770U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	489.7	489.7	489.7	489.7	489.7	489.7	489.7	489.7	489.7	489.7	489.7
2.5°	490.9	490.6	490.4	490.1	489.8	489.3	488.6	487.9	487.1	486.4	487.1
5°	488.9	488.6	488.3	488.0	487.6	487.0	485.9	485.0	483.9	483.0	483.8
7.5°	484.5	484.2	483.9	483.5	483.2	482.3	481.0	479.7	478.4	477.1	477.6
10°	480.3	479.9	479.5	479.1	478.6	477.7	476.2	474.7	473.2	471.7	472.1
12.5°	474.9	474.4	474.0	473.5	473.0	471.9	470.1	468.3	466.6	464.8	465.0
15°	465.7	464.9	464.2	463.4	462.7	461.3	459.2	457.1	455.0	453.0	452.8
17.5°	454.6	453.4	452.3	451.3	450.2	448.4	445.9	443.4	440.9	438.4	437.9
20°	445.8	444.7	443.7	442.6	441.5	439.6	436.7	433.9	431.0	428.2	427.5
22.5°	436.3	435.0	433.8	432.6	431.3	429.2	426.2	423.2	420.2	417.1	416.1
25°	421.1	419.6	418.1	416.6	415.1	412.6	409.2	405.8	402.3	398.9	397.5
27.5°	405.2	403.3	401.4	399.6	397.7	394.9	391.3	387.6	384.0	380.3	378.5
30°	394.1	392.0	389.9	387.9	385.8	382.8	378.8	374.9	371.0	367.1	365.0
32.5°	382.4	380.0	377.7	375.3	373.0	369.8	365.8	361.7	357.7	353.6	351.2
35°	364.1	361.4	358.8	356.1	353.4	350.0	345.9	341.7	337.5	333.4	330.5
37.5°	344.5	341.7	339.1	336.3	333.5	329.9	325.2	320.6	316.0	311.4	308.2
40°	330.7	328.0	325.2	322.5	319.7	316.0	311.2	306.5	301.7	297.0	293.5
42.5°	317.5	314.7	311.7	308.9	306.0	302.1	297.1	292.2	287.2	282.3	278.7
45°	297.0	293.9	290.8	287.7	284.6	280.6	275.6	270.6	265.6	260.6	256.5
47.5°	275.8	272.6	269.4	266.2	263.0	258.8	253.7	248.4	243.2	238.1	233.8
50°	261.3	258.1	254.8	251.6	248.3	244.1	238.8	233.4	228.1	222.8	218.6
52.5°	246.7	243.4	240.3	237.1	233.9	229.6	224.1	218.6	213.2	207.7	203.5
55°	225.0	221.7	218.3	215.0	211.7	207.2	201.8	196.5	191.0	185.6	181.3
57.5°	203.5	200.0	196.6	193.1	189.6	185.3	179.9	174.6	169.3	163.9	159.5
60°	188.2	184.9	181.6	178.2	174.9	170.6	165.2	159.9	154.6	149.2	144.9
62.5°	174.4	171.0	167.5	164.1	160.6	156.1	150.7	145.2	139.7	134.3	130.2
65°	153.0	149.4	145.8	142.3	138.6	134.2	128.9	123.5	118.2	112.9	109.3
67.5°	130.7	127.3	123.8	120.4	117.0	112.8	107.8	102.9	97.9	93.0	89.9
70°	116.6	113.1	109.6	106.2	102.6	98.5	93.7	89.0	84.2	79.5	76.8
72.5°	101.6	98.5	95.3	92.1	89.0	85.2	80.6	76.1	71.7	67.2	64.9
75°	81.4	78.3	75.2	72.1	69.0	65.5	61.6	57.7	53.8	49.9	47.9
77.5°	60.8	58.2	55.6	53.0	50.4	47.5	44.3	41.1	37.9	34.8	33.7
80°	47.6	45.2	42.8	40.4	37.9	35.5	33.0	30.5	28.0	25.5	25.3
82.5°	36.2	34.0	31.8	29.5	27.3	25.5	24.1	22.7	21.2	19.8	19.6
85°	20.3	18.6	17.0	15.2	13.5	12.6	12.4	12.1	11.9	11.6	11.5
87.5°	7.3	7.0	6.7	6.5	6.3	6.2	6.3	6.5	6.7	6.8	6.9
90°	1.7	3.2	4.7	6.1	7.5	8.8	9.8	10.9	11.9	12.9	13.7
92.5°	12.6	14.3	15.8	17.5	19.2	20.4	21.1	21.8	22.6	23.3	23.8
95°	35.3	36.4	37.6	38.8	40.0	41.0	41.9	42.9	43.8	44.7	45.1
97.5°	61.6	62.6	63.5	64.4	65.4	66.4	67.5	68.5	69.6	70.7	71.1
100°	82.3	82.9	83.3	83.9	84.4	85.2	86.4	87.6	88.8	90.0	90.2
102.5°	103.9	104.2	104.3	104.6	104.8	105.4	106.5	107.6	108.6	109.7	110.1
105°	137.0	137.1	137.3	137.4	137.5	137.8	138.4	138.9	139.4	139.9	140.3
107.5°	171.7	171.8	172.0	172.1	172.3	172.5	172.5	172.6	172.7	172.8	173.1
110°	195.2	195.4	195.7	196.0	196.2	196.3	196.1	196.1	195.9	195.7	195.5



TEST NUMBER: P333022-927

CATALOG NUMBER: S124RDIW-S350D770U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	219.7	219.7	219.8	219.8	219.8	219.8	219.5	219.3	219.0	218.8	218.8
115°	256.4	256.4	256.4	256.4	256.4	256.2	256.0	255.7	255.4	255.2	255.0
117.5°	290.9	291.0	291.1	291.2	291.4	291.3	291.1	291.0	290.7	290.6	290.1
120°	313.9	314.5	315.0	315.5	316.1	316.1	315.8	315.4	315.0	314.6	313.9
122.5°	337.9	338.2	338.3	338.6	338.8	338.8	338.7	338.4	338.3	338.1	337.6
125°	373.4	373.4	373.4	373.4	373.4	373.3	373.1	373.0	372.9	372.7	372.5
127.5°	405.4	405.8	406.2	406.6	407.0	407.1	406.9	406.7	406.5	406.3	406.0
130°	428.0	428.4	428.8	429.2	429.6	429.8	429.8	429.8	429.8	429.8	429.5
132.5°	451.1	451.4	451.6	451.9	452.3	452.3	452.2	452.1	452.0	451.9	451.6
135°	481.6	482.3	483.1	483.9	484.7	485.1	485.1	485.1	485.1	485.1	484.8
137.5°	514.7	515.1	515.4	515.8	516.2	516.4	516.7	516.8	517.1	517.3	516.9
140°	536.8	537.0	537.3	537.6	537.8	538.0	538.0	538.0	538.0	538.0	537.8
142.5°	557.0	557.3	557.5	557.8	558.1	558.2	558.0	557.9	557.9	557.7	557.7
145°	585.0	585.5	586.1	586.6	587.1	587.4	587.6	587.7	587.8	588.0	587.8
147.5°	612.8	613.4	614.0	614.7	615.3	615.5	615.4	615.3	615.2	615.1	615.0
150°	629.7	630.2	630.7	631.3	631.8	632.1	632.1	632.1	632.1	632.1	632.1
152.5°	645.7	646.0	646.3	646.7	647.0	647.1	647.2	647.4	647.5	647.5	647.8
155°	670.3	670.3	670.3	670.3	670.3	670.2	670.0	669.9	669.8	669.7	670.2
157.5°	690.9	690.7	690.5	690.2	690.0	689.9	689.8	689.8	689.8	689.8	690.1
160°	703.2	703.1	702.9	702.8	702.7	702.5	702.4	702.3	702.1	702.0	702.4
162.5°	714.5	714.2	713.8	713.4	713.1	712.9	712.7	712.6	712.5	712.3	713.0
165°	729.7	729.3	728.9	728.5	728.1	727.8	727.5	727.2	727.0	726.7	727.5
167.5°	741.2	740.8	740.2	739.7	739.1	738.8	738.9	738.9	738.9	738.9	739.7
170°	747.9	747.2	746.6	745.9	745.3	745.0	745.1	745.3	745.4	745.5	746.3
172.5°	752.6	752.0	751.5	750.9	750.4	750.1	750.1	750.2	750.2	750.2	751.1
175°	759.1	758.4	757.7	757.1	756.5	756.1	755.9	755.7	755.7	755.5	756.5
177.5°	761.1	760.7	760.1	759.6	759.1	758.8	758.8	758.8	758.8	758.8	759.5
180°	760.2	760.2	760.2	760.2	760.2	760.2	760.2	760.2	760.2	760.2	760.2



TEST NUMBER: P333022-927

CATALOG NUMBER: S124RDIW-S350D770U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	489.7	489.7	489.7	489.7	489.7	489.7	489.7	489.7
2.5°	487.9	488.6	489.3	489.6	489.6	489.6	489.5	489.4
5°	484.7	485.4	486.3	486.6	486.5	486.3	486.1	485.9
7.5°	478.2	478.7	479.3	479.3	479.1	478.9	478.6	478.3
10°	472.4	472.7	473.0	473.0	472.7	472.4	472.1	471.7
12.5°	465.2	465.4	465.6	465.5	465.0	464.5	464.1	463.6
15°	452.7	452.5	452.3	451.9	451.3	450.8	450.2	449.6
17.5°	437.4	437.0	436.6	435.9	435.0	434.1	433.2	432.4
20°	426.9	426.2	425.6	424.7	423.6	422.5	421.4	420.3
22.5°	415.1	414.1	413.1	412.2	411.3	410.4	409.6	408.6
25°	396.1	394.7	393.3	392.2	391.3	390.5	389.7	388.8
27.5°	376.8	375.0	373.3	371.9	370.6	369.4	368.2	367.0
30°	362.9	360.8	358.8	357.0	355.7	354.4	353.1	351.7
32.5°	348.8	346.3	344.0	342.1	340.8	339.5	338.3	337.0
35°	327.6	324.9	322.0	319.9	318.4	316.9	315.4	313.9
37.5°	305.1	301.9	298.7	296.4	294.9	293.3	291.8	290.3
40°	289.9	286.5	283.0	280.5	279.0	277.5	276.0	274.5
42.5°	275.1	271.6	268.0	265.5	263.9	262.3	260.7	259.2
45°	252.5	248.3	244.2	241.5	240.0	238.4	236.9	235.5
47.5°	229.6	225.3	221.1	218.2	216.5	214.8	213.2	211.6
50°	214.4	210.2	206.0	203.2	201.6	200.0	198.4	196.9
52.5°	199.2	195.0	190.8	187.8	186.2	184.6	182.9	181.3
55°	177.0	172.6	168.3	165.3	163.7	162.2	160.6	159.0
57.5°	155.1	150.8	146.3	143.5	142.4	141.2	139.9	138.7
60°	140.5	136.3	131.9	129.0	127.7	126.4	125.1	123.7
62.5°	126.3	122.2	118.3	115.7	114.6	113.6	112.5	111.5
65°	105.7	102.1	98.5	96.3	95.2	94.3	93.2	92.2
67.5°	86.8	83.7	80.6	78.6	77.5	76.4	75.3	74.1
70°	74.0	71.2	68.5	66.7	65.8	65.0	64.2	63.4
72.5°	62.5	60.1	57.8	56.2	55.5	54.7	53.9	53.2
75°	46.0	44.1	42.2	41.0	40.5	40.0	39.5	39.0
77.5°	32.6	31.4	30.3	29.7	29.5	29.4	29.2	29.1
80°	25.0	24.7	24.5	24.3	24.2	24.2	24.1	24.0
82.5°	19.4	19.3	19.1	18.9	18.9	18.8	18.7	18.6
85°	11.3	11.1	10.9	10.9	10.9	10.9	10.9	10.9
87.5°	7.0	7.1	7.1	7.3	7.4	7.5	7.6	7.8
90°	14.5	15.3	16.1	16.6	16.9	17.1	17.3	17.7
92.5°	24.2	24.7	25.2	25.5	25.7	25.8	26.0	26.1
95°	45.5	45.9	46.3	46.4	46.4	46.4	46.4	46.4
97.5°	71.6	72.1	72.6	72.8	72.8	72.8	72.8	72.8
100°	90.5	90.7	91.0	91.1	91.1	91.1	91.1	91.1
102.5°	110.4	110.8	111.1	111.4	111.5	111.6	111.7	111.9
105°	140.7	141.1	141.5	141.9	142.3	142.7	143.1	143.5
107.5°	173.5	173.8	174.2	174.4	174.4	174.4	174.3	174.3
110°	195.3	195.0	194.7	194.8	195.2	195.6	196.0	196.4



TEST NUMBER: P333022-927

CATALOG NUMBER: S124RDIW-S350D770U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	218.7	218.6	218.6	218.6	218.7	218.8	218.9	219.0
115°	254.9	254.8	254.6	254.5	254.4	254.3	254.1	254.0
117.5°	289.7	289.2	288.8	288.4	288.2	287.9	287.6	287.4
120°	313.2	312.6	312.0	311.7	312.0	312.3	312.5	312.8
122.5°	337.2	336.8	336.3	335.8	335.3	334.9	334.5	334.0
125°	372.2	372.0	371.7	371.5	371.2	370.9	370.7	370.4
127.5°	405.8	405.5	405.2	405.0	404.8	404.6	404.3	404.2
130°	429.3	429.0	428.7	428.3	427.9	427.3	426.7	426.3
132.5°	451.4	451.1	450.8	450.6	450.4	450.2	450.0	449.8
135°	484.5	484.3	484.0	483.7	483.3	482.9	482.5	482.1
137.5°	516.6	516.3	515.9	515.8	515.9	515.9	516.0	516.1
140°	537.7	537.6	537.4	537.3	537.2	537.0	536.9	536.8
142.5°	557.7	557.6	557.6	557.6	557.5	557.5	557.5	557.5
145°	587.7	587.6	587.4	587.2	586.8	586.4	586.0	585.6
147.5°	614.9	614.8	614.7	614.6	614.4	614.3	614.2	614.0
150°	632.1	632.1	632.1	632.0	631.8	631.7	631.6	631.4
152.5°	648.2	648.5	648.8	648.8	648.5	648.2	647.8	647.5
155°	670.7	671.2	671.8	671.8	671.2	670.7	670.2	669.7
157.5°	690.5	690.9	691.3	691.3	690.9	690.5	690.0	689.5
160°	702.8	703.2	703.6	703.5	702.8	702.1	701.5	700.8
162.5°	713.8	714.5	715.2	715.2	714.5	713.9	713.3	712.6
165°	728.3	729.0	729.8	730.0	729.4	728.9	728.4	727.9
167.5°	740.5	741.2	742.0	742.0	741.2	740.5	739.7	738.8
170°	747.1	747.9	748.7	748.6	747.7	746.8	745.8	745.0
172.5°	752.0	752.9	753.8	753.8	752.8	751.9	751.0	750.1
175°	757.3	758.3	759.1	759.1	758.3	757.3	756.5	755.5
177.5°	760.3	761.0	761.8	761.7	760.8	760.0	759.1	758.4
180°	760.2	760.2	760.2	760.2	760.2	760.2	760.2	760.2

(END OF REPORT)