

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333050

Luminaire Tested: **S124RDIW-S575D1340U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333050
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S575D1340U835-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7005.4 lumens
Efficiency: N/A
Efficacy: 130.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333050

CATALOG NUMBER: S124RDIW-S575D1340U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333050

CATALOG NUMBER: S124RDIW-S575D1340U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	34
1	94	90	86	83	85	81	78	75	65	63	61	50	49	48	37	36	35	29
2	86	79	73	68	77	71	66	62	57	54	51	44	42	40	32	31	30	24
3	78	69	62	57	71	63	57	52	51	46	43	39	36	34	29	27	25	21
4	72	61	54	48	65	56	49	44	45	40	37	35	32	29	26	24	22	18
5	66	55	47	41	59	50	43	38	40	35	32	31	28	25	23	21	19	16
6	61	49	41	36	55	45	38	33	36	31	27	28	25	22	21	19	17	14
7	56	44	37	31	50	40	34	29	33	28	24	26	22	20	19	17	15	12
8	52	40	33	27	47	37	30	25	30	25	21	24	20	17	18	15	14	11
9	48	36	29	24	44	33	27	23	27	23	19	22	18	16	16	14	12	10
10	45	33	26	22	41	31	24	20	25	20	17	20	17	14	15	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8205	8205	8205
5°	8223	8122	8173
10°	8171	8025	8025
15°	8078	7856	7798
20°	7948	7635	7494
25°	7784	7375	7187
30°	7623	7101	6804
35°	7447	6818	6419
40°	7233	6495	6003
45°	7036	6174	5579
50°	6812	5805	5130
55°	6572	5422	4643
60°	6307	5000	4146
65°	6065	4474	3656
70°	5712	3895	3104
75°	5268	3228	2523
80°	4593	2459	2315
85°	3890	2232	2093



TEST NUMBER: P333050

CATALOG NUMBER: S124RDIW-S575D1340U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	95.5	1.4
10°-20°	266.2	3.8
20°-30°	384.4	5.5
30°-40°	435.7	6.2
40°-50°	420.8	6.0
50°-60°	349.9	5.0
60°-70°	241.6	3.4
70°-80°	122.5	1.7
80°-90°	36.4	0.5
90°-100°	110.6	1.6
100°-110°	327.6	4.7
110°-120°	556.1	7.9
120°-130°	733.3	10.5
130°-140°	823.5	11.8
140°-150°	809.2	11.6
150°-160°	680.6	9.7
160°-170°	452.8	6.5
170°-180°	158.6	2.3
0°-30°	746.1	10.7
0°-40°	1181.8	16.9
0°-60°	1952.5	27.9
0°-90°	2353.0	33.6
90°-120°	994.3	14.2
90°-150°	3360.3	48.0
90°-180°	4652.0	66.4
0°-180°	7005.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1016	1016	1016	1016	1016	
5°	1015	1011	1002	1010	1008	96
15°	966	959	940	938	933	272
25°	874	859	828	815	807	402
35°	756	730	692	666	651	472
45°	616	586	541	504	489	475
55°	467	435	385	346	330	418
65°	318	283	234	202	191	313
75°	169	140	104	86	81	178
85°	42	27	24	23	23	47
90°	4	18	28	36	39	7
95°	78	89	99	102	102	87
105°	302	304	309	313	316	321
115°	565	565	563	562	560	557
125°	824	823	822	820	817	734
135°	1062	1070	1070	1067	1063	821
145°	1290	1295	1297	1295	1292	807
155°	1478	1478	1477	1482	1477	680
165°	1609	1606	1603	1610	1606	453
175°	1674	1668	1666	1675	1666	159
180°	1677	1677	1677	1677	1677	



TEST NUMBER: P333050

CATALOG NUMBER: S124RDIW-S575D1340U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3
2.5°	1018.8	1018.2	1017.7	1017.1	1016.6	1015.5	1014.0	1012.5	1010.9	1009.4	1010.9
5°	1014.7	1014.0	1013.3	1012.6	1012.0	1010.6	1008.5	1006.4	1004.3	1002.3	1004.0
7.5°	1005.5	1004.8	1004.1	1003.4	1002.6	1000.9	998.2	995.5	992.8	990.1	991.2
10°	996.8	996.0	995.1	994.2	993.4	991.4	988.3	985.1	982.0	978.9	979.6
12.5°	985.6	984.6	983.6	982.6	981.6	979.3	975.6	971.9	968.3	964.6	965.0
15°	966.5	964.9	963.4	961.8	960.2	957.3	953.0	948.7	944.3	940.0	939.7
17.5°	943.3	941.0	938.8	936.5	934.3	930.6	925.4	920.2	915.0	909.8	908.9
20°	925.2	923.0	920.7	918.5	916.2	912.2	906.3	900.4	894.5	888.7	887.3
22.5°	905.3	902.8	900.3	897.7	895.2	890.8	884.5	878.2	871.9	865.6	863.5
25°	873.9	870.8	867.6	864.5	861.4	856.3	849.2	842.1	835.0	828.0	825.0
27.5°	840.9	837.0	833.1	829.2	825.2	819.5	811.9	804.4	796.8	789.2	785.6
30°	817.8	813.5	809.2	804.9	800.6	794.3	786.2	778.1	769.9	761.8	757.5
32.5°	793.6	788.7	783.8	778.9	774.1	767.4	759.0	750.6	742.2	733.8	728.8
35°	755.6	750.1	744.5	739.0	733.5	726.4	717.7	709.1	700.4	691.8	685.9
37.5°	715.0	709.3	703.6	697.9	692.1	684.5	674.9	665.3	655.8	646.2	639.6
40°	686.3	680.6	674.9	669.2	663.5	655.7	645.9	636.0	626.2	616.3	609.0
42.5°	658.9	653.0	647.0	641.0	635.0	626.9	616.6	606.3	596.1	585.8	578.4
45°	616.3	609.9	603.5	597.1	590.7	582.3	571.9	561.6	551.2	540.8	532.3
47.5°	572.3	565.7	559.0	552.4	545.8	537.1	526.3	515.6	504.8	494.0	485.2
50°	542.4	535.6	528.9	522.1	515.4	506.5	495.4	484.4	473.3	462.2	453.6
52.5°	511.9	505.3	498.7	492.1	485.4	476.5	465.1	453.8	442.4	431.1	422.3
55°	466.9	460.0	453.1	446.1	439.2	430.1	418.9	407.7	396.4	385.2	376.2
57.5°	422.4	415.2	408.0	400.8	393.6	384.5	373.4	362.3	351.3	340.2	331.1
60°	390.6	383.7	376.8	369.9	363.0	354.0	342.9	331.8	320.8	309.7	300.7
62.5°	362.0	354.8	347.6	340.4	333.2	324.0	312.6	301.3	289.9	278.6	270.3
65°	317.5	310.1	302.6	295.2	287.7	278.5	267.4	256.4	245.3	234.2	226.8
67.5°	271.3	264.1	257.0	249.9	242.8	234.1	223.8	213.5	203.3	193.0	186.6
70°	242.0	234.7	227.5	220.2	213.0	204.4	194.5	184.7	174.8	165.0	159.3
72.5°	210.9	204.3	197.7	191.2	184.6	176.7	167.4	158.1	148.7	139.4	134.6
75°	168.9	162.5	156.1	149.7	143.3	136.0	127.9	119.7	111.6	103.5	99.5
77.5°	126.2	120.8	115.4	109.9	104.5	98.5	91.9	85.4	78.8	72.2	69.9
80°	98.8	93.8	88.8	83.8	78.8	73.7	68.5	63.3	58.1	52.9	52.4
82.5°	75.2	70.6	66.0	61.4	56.8	53.0	50.0	47.0	44.1	41.1	40.7
85°	42.0	38.6	35.1	31.6	28.2	26.2	25.7	25.2	24.6	24.1	23.8
87.5°	15.1	14.6	14.2	13.7	13.2	13.1	13.5	13.8	14.1	14.4	14.6
90°	3.9	7.1	10.2	13.4	16.6	19.3	21.6	23.9	26.2	28.5	30.3
92.5°	27.8	31.4	35.0	38.6	42.3	44.9	46.5	48.1	49.7	51.4	52.4
95°	77.8	80.4	83.0	85.6	88.2	90.5	92.5	94.5	96.5	98.6	99.4
97.5°	135.9	138.0	140.1	142.1	144.2	146.4	148.8	151.2	153.5	155.9	156.9
100°	181.6	182.7	183.9	185.0	186.2	188.0	190.6	193.2	195.8	198.4	199.0
102.5°	229.3	229.8	230.2	230.7	231.1	232.5	234.9	237.3	239.6	242.0	242.8
105°	302.2	302.5	302.8	303.0	303.3	304.0	305.2	306.4	307.5	308.7	309.5
107.5°	378.7	379.0	379.4	379.7	380.1	380.3	380.5	380.7	380.9	381.0	381.8
110°	430.6	431.1	431.7	432.3	432.9	433.0	432.7	432.4	432.2	431.9	431.3



TEST NUMBER: P333050

CATALOG NUMBER: S124RDIW-S575D1340U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	484.5	484.6	484.7	484.9	485.0	484.8	484.3	483.7	483.2	482.7	482.6
115°	565.4	565.4	565.4	565.4	565.4	565.2	564.6	564.0	563.4	562.8	562.6
117.5°	641.7	641.9	642.2	642.4	642.6	642.5	642.1	641.7	641.3	640.9	639.9
120°	692.5	693.7	694.8	696.0	697.1	697.3	696.4	695.6	694.7	693.8	692.4
122.5°	745.4	745.9	746.4	746.8	747.3	747.3	746.9	746.5	746.1	745.7	744.7
125°	823.5	823.5	823.5	823.5	823.5	823.4	823.1	822.8	822.5	822.2	821.6
127.5°	894.3	895.2	896.1	896.9	897.8	898.0	897.5	897.1	896.6	896.1	895.6
130°	944.1	945.0	945.9	946.7	947.6	948.0	948.0	948.0	948.0	948.0	947.4
132.5°	995.0	995.6	996.2	996.9	997.5	997.7	997.5	997.2	997.0	996.8	996.2
135°	1062.1	1063.9	1065.6	1067.3	1069.1	1069.9	1069.9	1069.9	1069.9	1069.9	1069.4
137.5°	1135.3	1136.1	1136.9	1137.7	1138.5	1139.2	1139.6	1140.1	1140.5	1141.0	1140.2
140°	1184.1	1184.6	1185.2	1185.8	1186.4	1186.6	1186.6	1186.6	1186.6	1186.6	1186.4
142.5°	1228.7	1229.2	1229.8	1230.4	1231.0	1231.1	1230.9	1230.7	1230.5	1230.2	1230.2
145°	1290.4	1291.6	1292.7	1293.9	1295.0	1295.7	1296.0	1296.3	1296.6	1296.9	1296.6
147.5°	1351.6	1353.0	1354.4	1355.8	1357.1	1357.7	1357.5	1357.3	1357.0	1356.8	1356.6
150°	1389.0	1390.1	1391.3	1392.4	1393.6	1394.1	1394.1	1394.1	1394.1	1394.1	1394.1
152.5°	1424.2	1424.9	1425.6	1426.3	1427.0	1427.5	1427.7	1427.9	1428.2	1428.4	1429.1
155°	1478.4	1478.4	1478.4	1478.4	1478.4	1478.3	1478.0	1477.7	1477.4	1477.2	1478.3
157.5°	1524.1	1523.6	1523.1	1522.5	1522.0	1521.7	1521.7	1521.6	1521.6	1521.5	1522.4
160°	1551.1	1550.8	1550.5	1550.2	1549.9	1549.6	1549.3	1549.1	1548.8	1548.5	1549.3
162.5°	1576.0	1575.2	1574.5	1573.7	1573.0	1572.5	1572.2	1571.9	1571.6	1571.3	1572.9
165°	1609.4	1608.6	1607.7	1606.8	1606.0	1605.3	1604.7	1604.1	1603.5	1602.9	1604.7
167.5°	1635.1	1633.9	1632.7	1631.5	1630.3	1629.7	1629.8	1629.8	1629.9	1629.9	1631.7
170°	1649.6	1648.2	1646.8	1645.3	1643.9	1643.3	1643.6	1643.9	1644.2	1644.4	1646.2
172.5°	1660.0	1658.8	1657.6	1656.4	1655.2	1654.6	1654.7	1654.7	1654.8	1654.8	1656.8
175°	1674.3	1672.8	1671.4	1670.0	1668.5	1667.6	1667.4	1667.1	1666.8	1666.5	1668.5
177.5°	1678.9	1677.8	1676.6	1675.5	1674.3	1673.8	1673.8	1673.8	1673.8	1673.8	1675.4
180°	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9



TEST NUMBER: P333050

CATALOG NUMBER: S124RDIW-S575D1340U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3
2.5°	1012.5	1014.0	1015.5	1016.2	1016.1	1015.9	1015.8	1015.7
5°	1005.7	1007.5	1009.2	1009.9	1009.5	1009.2	1008.8	1008.5
7.5°	992.3	993.4	994.6	994.8	994.3	993.7	993.2	992.6
10°	980.3	981.0	981.7	981.7	981.0	980.3	979.6	978.9
12.5°	965.4	965.8	966.3	966.0	965.0	964.1	963.1	962.1
15°	939.3	939.0	938.6	937.9	936.6	935.4	934.2	933.0
17.5°	907.9	906.9	905.9	904.5	902.7	900.9	899.0	897.2
20°	885.9	884.5	883.1	881.3	879.1	876.8	874.6	872.3
22.5°	861.5	859.4	857.3	855.4	853.5	851.7	849.9	848.0
25°	822.1	819.1	816.2	813.9	812.1	810.4	808.7	806.9
27.5°	781.9	778.3	774.7	771.6	769.1	766.6	764.2	761.7
30°	753.2	748.8	744.5	741.0	738.2	735.4	732.7	729.9
32.5°	723.8	718.8	713.7	709.9	707.3	704.7	702.0	699.4
35°	680.0	674.1	668.3	663.8	660.7	657.5	654.4	651.3
37.5°	633.0	626.5	619.9	615.1	611.9	608.8	605.7	602.6
40°	601.8	594.5	587.2	582.1	578.9	575.8	572.7	569.6
42.5°	571.0	563.6	556.2	550.9	547.6	544.4	541.1	537.9
45°	523.9	515.4	506.9	501.1	498.0	494.9	491.8	488.7
47.5°	476.4	467.6	458.8	452.7	449.3	445.9	442.5	439.0
50°	444.9	436.3	427.6	421.7	418.4	415.1	411.8	408.5
52.5°	413.5	404.7	396.0	389.9	386.4	383.0	379.6	376.2
55°	367.2	358.2	349.2	343.1	339.8	336.5	333.2	329.9
57.5°	321.9	312.8	303.7	297.9	295.4	292.9	290.4	287.9
60°	291.7	282.7	273.7	267.9	265.1	262.3	259.6	256.8
62.5°	262.0	253.7	245.4	240.1	237.9	235.7	233.5	231.3
65°	219.4	211.9	204.5	199.7	197.7	195.6	193.5	191.4
67.5°	180.2	173.8	167.4	163.1	160.8	158.5	156.2	153.9
70°	153.6	147.9	142.1	138.4	136.7	135.0	133.2	131.5
72.5°	129.7	124.8	119.9	116.7	115.1	113.5	111.9	110.3
75°	95.5	91.6	87.6	85.1	84.0	83.0	82.0	80.9
77.5°	67.6	65.3	62.9	61.6	61.3	61.0	60.7	60.4
80°	51.9	51.4	50.8	50.5	50.3	50.1	50.0	49.8
82.5°	40.3	39.9	39.6	39.3	39.1	38.9	38.8	38.6
85°	23.4	23.1	22.7	22.6	22.6	22.6	22.6	22.6
87.5°	14.8	15.0	15.3	15.5	15.7	16.0	16.2	16.5
90°	32.0	33.7	35.4	36.6	37.2	37.8	38.3	38.9
92.5°	53.4	54.5	55.5	56.2	56.5	56.9	57.2	57.6
95°	100.3	101.2	102.0	102.5	102.5	102.5	102.5	102.5
97.5°	158.0	159.0	160.0	160.6	160.6	160.6	160.6	160.6
100°	199.6	200.2	200.7	201.0	201.0	201.0	201.0	201.0
102.5°	243.6	244.4	245.2	245.7	246.0	246.2	246.4	246.7
105°	310.4	311.3	312.1	313.0	313.8	314.7	315.6	316.4
107.5°	382.6	383.4	384.3	384.6	384.6	384.5	384.5	384.4
110°	430.7	430.1	429.6	429.7	430.6	431.4	432.3	433.2



TEST NUMBER: P333050

CATALOG NUMBER: S124RDIW-S575D1340U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	482.5	482.4	482.2	482.3	482.4	482.6	482.8	483.0
115°	562.3	562.0	561.7	561.4	561.1	560.8	560.5	560.3
117.5°	639.0	638.0	637.0	636.2	635.6	635.1	634.5	633.9
120°	691.0	689.5	688.1	687.6	688.2	688.8	689.4	689.9
122.5°	743.7	742.8	741.8	740.8	739.7	738.7	737.7	736.6
125°	821.1	820.5	819.9	819.3	818.8	818.2	817.6	817.0
127.5°	895.0	894.4	893.8	893.3	892.9	892.4	891.9	891.5
130°	946.9	946.3	945.7	944.9	943.7	942.5	941.4	940.2
132.5°	995.6	995.1	994.5	994.0	993.5	993.0	992.6	992.1
135°	1068.8	1068.2	1067.6	1066.9	1066.0	1065.2	1064.3	1063.4
137.5°	1139.5	1138.8	1138.0	1137.7	1137.9	1138.1	1138.2	1138.4
140°	1186.1	1185.8	1185.5	1185.2	1184.9	1184.6	1184.3	1184.1
142.5°	1230.1	1230.1	1230.0	1229.9	1229.9	1229.8	1229.8	1229.7
145°	1296.3	1296.0	1295.7	1295.2	1294.3	1293.4	1292.6	1291.7
147.5°	1356.3	1356.1	1355.9	1355.6	1355.3	1355.0	1354.8	1354.5
150°	1394.1	1394.1	1394.1	1394.0	1393.7	1393.4	1393.1	1392.9
152.5°	1429.8	1430.5	1431.2	1431.1	1430.4	1429.6	1428.9	1428.1
155°	1479.5	1480.6	1481.8	1481.8	1480.6	1479.5	1478.3	1477.2
157.5°	1523.2	1524.1	1525.0	1524.9	1523.9	1522.9	1522.0	1521.0
160°	1550.2	1551.1	1551.9	1551.6	1550.2	1548.8	1547.3	1545.9
162.5°	1574.4	1576.0	1577.5	1577.6	1576.1	1574.7	1573.3	1571.8
165°	1606.4	1608.1	1609.9	1610.2	1609.0	1607.8	1606.7	1605.5
167.5°	1633.4	1635.1	1636.8	1636.8	1635.0	1633.2	1631.5	1629.7
170°	1647.9	1649.6	1651.4	1651.2	1649.2	1647.2	1645.2	1643.2
172.5°	1658.7	1660.7	1662.7	1662.6	1660.6	1658.6	1656.6	1654.6
175°	1670.5	1672.5	1674.6	1674.6	1672.5	1670.5	1668.5	1666.5
177.5°	1677.0	1678.6	1680.2	1680.1	1678.3	1676.4	1674.6	1672.7
180°	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9

(END OF REPORT)