

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333050-927

Luminaire Tested: **S124RDIW-S575D1340U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333050-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIW-S575D1340U927-4F0-1E-UDD-F1  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5549.5 lumens  
Efficiency: N/A  
Efficacy: 103.2 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 53.8  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333050-927

CATALOG NUMBER: S124RDIW-S575D1340U927-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P333050-927

CATALOG NUMBER: S124RDIW-S575D1340U927-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	34
1	94	90	86	83	85	81	78	75	65	63	61	50	49	48	37	36	35	29
2	86	79	73	68	77	71	66	62	57	54	51	44	42	40	32	31	30	24
3	78	69	62	57	71	63	57	52	51	46	43	39	36	34	29	27	25	21
4	72	61	54	48	65	56	49	44	45	40	37	35	32	29	26	24	22	18
5	66	55	47	41	59	50	43	38	40	35	32	31	28	25	23	21	19	16
6	61	49	41	36	55	45	38	33	36	31	27	28	25	22	21	19	17	14
7	56	44	37	31	50	40	34	29	33	28	24	26	22	20	19	17	15	12
8	52	40	33	27	47	37	30	25	30	25	21	24	20	17	18	15	14	11
9	48	36	29	24	44	33	27	23	27	23	19	22	18	16	16	14	12	10
10	45	33	26	22	41	31	24	20	25	20	17	20	17	14	15	13	11	9

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6500	6500	6500
5°	6514	6434	6474
10°	6473	6357	6357
15°	6399	6224	6177
20°	6296	6048	5936
25°	6167	5842	5694
30°	6039	5626	5390
35°	5899	5401	5084
40°	5730	5145	4755
45°	5574	4891	4419
50°	5397	4598	4064
55°	5206	4294	3678
60°	4996	3961	3284
65°	4804	3543	2896
70°	4525	3085	2460
75°	4173	2558	1999
80°	3640	1948	1836
85°	3084	1769	1658



TEST NUMBER: P333050-927

CATALOG NUMBER: S124RDIW-S575D1340U927-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	75.6	1.4
10°-20°	210.9	3.8
20°-30°	304.5	5.5
30°-40°	345.2	6.2
40°-50°	333.3	6.0
50°-60°	277.2	5.0
60°-70°	191.4	3.4
70°-80°	97.0	1.7
80°-90°	28.9	0.5
90°-100°	87.6	1.6
100°-110°	259.5	4.7
110°-120°	440.5	7.9
120°-130°	580.9	10.5
130°-140°	652.4	11.8
140°-150°	641.1	11.6
150°-160°	539.2	9.7
160°-170°	358.7	6.5
170°-180°	125.6	2.3
0°-30°	591.0	10.7
0°-40°	936.2	16.9
0°-60°	1546.7	27.9
0°-90°	1864.0	33.6
90°-120°	787.7	14.2
90°-150°	2662.0	48.0
90°-180°	3686.0	66.4
0°-180°	5549.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	805	805	805	805	805	
5°	804	801	794	800	799	76
15°	766	760	745	743	739	216
25°	692	680	656	646	639	319
35°	599	578	548	528	516	374
45°	488	465	428	399	387	376
55°	370	344	305	274	261	331
65°	252	224	186	160	152	248
75°	134	111	82	68	64	141
85°	33	22	19	18	18	38
90°	3	14	23	28	31	6
95°	62	71	78	81	81	69
105°	239	241	244	248	251	254
115°	448	448	446	445	444	442
125°	652	652	651	649	647	581
135°	841	847	848	845	842	651
145°	1022	1026	1027	1026	1023	639
155°	1171	1171	1170	1174	1170	539
165°	1275	1272	1270	1275	1272	359
175°	1326	1321	1320	1327	1320	126
180°	1328	1328	1328	1328	1328	



TEST NUMBER: P333050-927

CATALOG NUMBER: S124RDIW-S575D1340U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	805.1	805.1	805.1	805.1	805.1	805.1	805.1	805.1	805.1	805.1	805.1
2.5°	807.1	806.6	806.2	805.7	805.3	804.5	803.3	802.1	800.8	799.6	800.8
5°	803.8	803.3	802.7	802.2	801.7	800.6	798.9	797.3	795.6	794.0	795.4
7.5°	796.5	796.0	795.4	794.9	794.2	792.9	790.8	788.6	786.5	784.3	785.2
10°	789.6	789.0	788.3	787.6	787.0	785.4	782.9	780.4	777.9	775.5	776.0
12.5°	780.8	780.0	779.2	778.4	777.6	775.8	772.9	769.9	767.1	764.1	764.5
15°	765.6	764.4	763.2	761.9	760.7	758.4	754.9	751.5	748.1	744.7	744.4
17.5°	747.3	745.4	743.7	741.9	740.1	737.2	733.1	729.0	724.8	720.7	720.0
20°	732.9	731.2	729.4	727.6	725.8	722.6	718.0	713.3	708.6	704.0	702.9
22.5°	717.2	715.2	713.2	711.1	709.2	705.7	700.7	695.7	690.7	685.7	684.0
25°	692.3	689.8	687.3	684.8	682.4	678.3	672.7	667.1	661.5	655.9	653.6
27.5°	666.1	663.1	660.0	656.9	653.7	649.2	643.2	637.2	631.2	625.2	622.3
30°	647.8	644.4	641.0	637.6	634.2	629.2	622.8	616.4	609.9	603.5	600.1
32.5°	628.7	624.8	620.9	617.0	613.2	607.9	601.3	594.6	588.0	581.3	577.3
35°	598.6	594.2	589.8	585.4	581.1	575.4	568.5	561.7	554.8	548.0	543.4
37.5°	566.4	561.9	557.4	552.9	548.3	542.2	534.6	527.0	519.5	511.9	506.7
40°	543.7	539.2	534.6	530.1	525.6	519.4	511.7	503.8	496.1	488.2	482.4
42.5°	522.0	517.3	512.5	507.8	503.0	496.6	488.5	480.3	472.2	464.1	458.2
45°	488.2	483.2	478.1	473.0	467.9	461.3	453.0	444.9	436.7	428.4	421.7
47.5°	453.4	448.1	442.8	437.6	432.4	425.5	416.9	408.4	399.9	391.3	384.4
50°	429.7	424.3	419.0	413.6	408.3	401.2	392.4	383.7	374.9	366.1	359.3
52.5°	405.5	400.3	395.1	389.8	384.5	377.5	368.4	359.5	350.5	341.5	334.5
55°	369.9	364.4	358.9	353.4	347.9	340.7	331.8	323.0	314.0	305.1	298.0
57.5°	334.6	328.9	323.2	317.5	311.8	304.6	295.8	287.0	278.3	269.5	262.3
60°	309.4	304.0	298.5	293.0	287.6	280.4	271.6	262.8	254.1	245.3	238.2
62.5°	286.8	281.1	275.4	269.7	264.0	256.7	247.6	238.7	229.7	220.7	214.1
65°	251.5	245.7	239.7	233.9	227.9	220.6	211.8	203.1	194.3	185.5	179.7
67.5°	214.9	209.2	203.6	198.0	192.3	185.4	177.3	169.1	161.1	152.9	147.8
70°	191.7	185.9	180.2	174.4	168.7	161.9	154.1	146.3	138.5	130.7	126.2
72.5°	167.1	161.8	156.6	151.5	146.2	140.0	132.6	125.2	117.8	110.4	106.6
75°	133.8	128.7	123.7	118.6	113.5	107.7	101.3	94.8	88.4	82.0	78.8
77.5°	100.0	95.7	91.4	87.1	82.8	78.0	72.8	67.7	62.4	57.2	55.4
80°	78.3	74.3	70.3	66.4	62.4	58.4	54.3	50.1	46.0	41.9	41.5
82.5°	59.6	55.9	52.3	48.6	45.0	42.0	39.6	37.2	34.9	32.6	32.2
85°	33.3	30.6	27.8	25.0	22.3	20.8	20.4	20.0	19.5	19.1	18.9
87.5°	12.0	11.6	11.2	10.9	10.5	10.4	10.7	10.9	11.2	11.4	11.6
90°	3.1	5.6	8.1	10.6	13.2	15.3	17.1	18.9	20.8	22.6	24.0
92.5°	22.0	24.9	27.7	30.6	33.5	35.6	36.8	38.1	39.4	40.7	41.5
95°	61.6	63.7	65.8	67.8	69.9	71.7	73.3	74.9	76.4	78.1	78.7
97.5°	107.7	109.3	111.0	112.6	114.2	116.0	117.9	119.8	121.6	123.5	124.3
100°	143.9	144.7	145.7	146.6	147.5	148.9	151.0	153.0	155.1	157.2	157.6
102.5°	181.6	182.0	182.4	182.8	183.1	184.2	186.1	188.0	189.8	191.7	192.3
105°	239.4	239.6	239.9	240.0	240.3	240.8	241.8	242.7	243.6	244.5	245.2
107.5°	300.0	300.2	300.6	300.8	301.1	301.3	301.4	301.6	301.7	301.8	302.5
110°	341.1	341.5	342.0	342.5	342.9	343.0	342.8	342.5	342.4	342.1	341.7



TEST NUMBER: P333050-927

CATALOG NUMBER: S124RDIW-S575D1340U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	383.8	383.9	384.0	384.1	384.2	384.0	383.7	383.2	382.8	382.4	382.3
115°	447.9	447.9	447.9	447.9	447.9	447.7	447.3	446.8	446.3	445.8	445.7
117.5°	508.3	508.5	508.7	508.9	509.1	509.0	508.7	508.3	508.0	507.7	506.9
120°	548.6	549.5	550.4	551.4	552.2	552.4	551.7	551.0	550.3	549.6	548.5
122.5°	590.5	590.9	591.3	591.6	592.0	592.0	591.7	591.4	591.0	590.7	589.9
125°	652.4	652.4	652.4	652.4	652.4	652.3	652.0	651.8	651.6	651.3	650.9
127.5°	708.4	709.2	709.9	710.5	711.2	711.4	711.0	710.7	710.3	709.9	709.5
130°	747.9	748.6	749.3	750.0	750.7	751.0	751.0	751.0	751.0	751.0	750.5
132.5°	788.2	788.7	789.2	789.7	790.2	790.4	790.2	790.0	789.8	789.6	789.2
135°	841.4	842.8	844.1	845.5	846.9	847.6	847.6	847.6	847.6	847.6	847.2
137.5°	899.4	900.0	900.6	901.3	901.9	902.5	902.8	903.2	903.5	903.9	903.2
140°	938.0	938.4	938.9	939.4	939.8	940.0	940.0	940.0	940.0	940.0	939.8
142.5°	973.4	973.8	974.2	974.7	975.2	975.3	975.1	974.9	974.8	974.5	974.5
145°	1022.2	1023.2	1024.1	1025.0	1025.9	1026.4	1026.7	1026.9	1027.1	1027.4	1027.1
147.5°	1070.7	1071.8	1072.9	1074.0	1075.1	1075.5	1075.4	1075.2	1075.0	1074.8	1074.7
150°	1100.3	1101.2	1102.2	1103.0	1104.0	1104.4	1104.4	1104.4	1104.4	1104.4	1104.4
152.5°	1128.2	1128.8	1129.3	1129.9	1130.4	1130.8	1131.0	1131.2	1131.4	1131.6	1132.1
155°	1171.2	1171.2	1171.2	1171.2	1171.2	1171.1	1170.8	1170.6	1170.4	1170.2	1171.1
157.5°	1207.4	1207.0	1206.6	1206.1	1205.7	1205.5	1205.5	1205.4	1205.4	1205.3	1206.0
160°	1228.8	1228.5	1228.3	1228.0	1227.8	1227.6	1227.3	1227.2	1226.9	1226.7	1227.3
162.5°	1248.5	1247.8	1247.3	1246.7	1246.1	1245.7	1245.5	1245.2	1245.0	1244.8	1246.0
165°	1274.9	1274.3	1273.6	1272.9	1272.2	1271.7	1271.2	1270.7	1270.3	1269.8	1271.2
167.5°	1295.3	1294.3	1293.4	1292.4	1291.5	1291.0	1291.1	1291.1	1291.2	1291.2	1292.6
170°	1306.8	1305.7	1304.6	1303.4	1302.3	1301.8	1302.0	1302.3	1302.5	1302.7	1304.1
172.5°	1315.0	1314.1	1313.1	1312.2	1311.2	1310.7	1310.8	1310.8	1310.9	1310.9	1312.5
175°	1326.4	1325.2	1324.1	1322.9	1321.8	1321.0	1320.9	1320.6	1320.4	1320.2	1321.8
177.5°	1330.0	1329.1	1328.2	1327.3	1326.4	1326.0	1326.0	1326.0	1326.0	1326.0	1327.2
180°	1328.4	1328.4	1328.4	1328.4	1328.4	1328.4	1328.4	1328.4	1328.4	1328.4	1328.4



TEST NUMBER: P333050-927

CATALOG NUMBER: S124RDIW-S575D1340U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	805.1	805.1	805.1	805.1	805.1	805.1	805.1	805.1
2.5°	802.1	803.3	804.5	805.0	804.9	804.8	804.7	804.6
5°	796.7	798.1	799.5	800.0	799.7	799.5	799.2	798.9
7.5°	786.1	787.0	787.9	788.1	787.7	787.2	786.8	786.3
10°	776.6	777.1	777.7	777.7	777.1	776.6	776.0	775.5
12.5°	764.8	765.1	765.5	765.2	764.5	763.7	763.0	762.2
15°	744.1	743.9	743.5	743.0	742.0	741.0	740.1	739.1
17.5°	719.2	718.4	717.6	716.5	715.1	713.7	712.2	710.7
20°	701.8	700.7	699.6	698.2	696.4	694.6	692.8	691.0
22.5°	682.5	680.8	679.1	677.6	676.1	674.7	673.3	671.8
25°	651.3	648.9	646.6	644.8	643.3	642.0	640.6	639.2
27.5°	619.4	616.6	613.7	611.2	609.3	607.3	605.4	603.4
30°	596.7	593.2	589.8	587.0	584.8	582.6	580.4	578.2
32.5°	573.4	569.4	565.4	562.4	560.3	558.3	556.1	554.1
35°	538.7	534.0	529.4	525.9	523.4	520.9	518.4	515.9
37.5°	501.5	496.3	491.1	487.3	484.7	482.3	479.8	477.4
40°	476.7	471.0	465.2	461.1	458.6	456.1	453.7	451.2
42.5°	452.3	446.5	440.6	436.4	433.8	431.3	428.6	426.1
45°	415.0	408.3	401.6	397.0	394.5	392.1	389.6	387.1
47.5°	377.4	370.4	363.5	358.6	355.9	353.2	350.5	347.8
50°	352.4	345.6	338.7	334.1	331.4	328.8	326.2	323.6
52.5°	327.6	320.6	313.7	308.9	306.1	303.4	300.7	298.0
55°	290.9	283.8	276.6	271.8	269.2	266.6	264.0	261.3
57.5°	255.0	247.8	240.6	236.0	234.0	232.0	230.0	228.1
60°	231.1	223.9	216.8	212.2	210.0	207.8	205.7	203.4
62.5°	207.6	201.0	194.4	190.2	188.5	186.7	185.0	183.2
65°	173.8	167.9	162.0	158.2	156.6	155.0	153.3	151.6
67.5°	142.8	137.7	132.6	129.2	127.4	125.6	123.7	121.9
70°	121.7	117.2	112.6	109.6	108.3	106.9	105.5	104.2
72.5°	102.7	98.9	95.0	92.4	91.2	89.9	88.6	87.4
75°	75.7	72.6	69.4	67.4	66.5	65.8	65.0	64.1
77.5°	53.6	51.7	49.8	48.8	48.6	48.3	48.1	47.8
80°	41.1	40.7	40.2	40.0	39.8	39.7	39.6	39.5
82.5°	31.9	31.6	31.4	31.1	31.0	30.8	30.7	30.6
85°	18.5	18.3	18.0	17.9	17.9	17.9	17.9	17.9
87.5°	11.7	11.9	12.1	12.3	12.4	12.7	12.8	13.1
90°	25.3	26.7	28.0	29.0	29.5	29.9	30.3	30.8
92.5°	42.3	43.2	44.0	44.5	44.8	45.1	45.3	45.6
95°	79.5	80.2	80.8	81.2	81.2	81.2	81.2	81.2
97.5°	125.2	126.0	126.7	127.2	127.2	127.2	127.2	127.2
100°	158.1	158.6	159.0	159.2	159.2	159.2	159.2	159.2
102.5°	193.0	193.6	194.2	194.6	194.9	195.0	195.2	195.4
105°	245.9	246.6	247.2	248.0	248.6	249.3	250.0	250.6
107.5°	303.1	303.7	304.4	304.7	304.7	304.6	304.6	304.5
110°	341.2	340.7	340.3	340.4	341.1	341.7	342.5	343.2





TEST NUMBER: P333050-927

CATALOG NUMBER: S124RDIW-S575D1340U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	382.2	382.1	382.0	382.1	382.1	382.3	382.5	382.6
115°	445.4	445.2	445.0	444.7	444.5	444.3	444.0	443.9
117.5°	506.2	505.4	504.6	504.0	503.5	503.1	502.6	502.2
120°	547.4	546.2	545.1	544.7	545.2	545.7	546.1	546.5
122.5°	589.1	588.4	587.6	586.8	586.0	585.2	584.4	583.5
125°	650.5	650.0	649.5	649.0	648.6	648.2	647.7	647.2
127.5°	709.0	708.5	708.1	707.7	707.3	706.9	706.5	706.2
130°	750.1	749.6	749.2	748.5	747.6	746.6	745.8	744.8
132.5°	788.7	788.3	787.8	787.4	787.0	786.6	786.3	785.9
135°	846.7	846.2	845.7	845.2	844.5	843.8	843.1	842.4
137.5°	902.7	902.1	901.5	901.3	901.4	901.6	901.7	901.8
140°	939.6	939.4	939.1	938.9	938.7	938.4	938.2	938.0
142.5°	974.5	974.5	974.4	974.3	974.3	974.2	974.2	974.1
145°	1026.9	1026.7	1026.4	1026.0	1025.3	1024.6	1024.0	1023.3
147.5°	1074.4	1074.3	1074.1	1073.9	1073.6	1073.4	1073.2	1073.0
150°	1104.4	1104.4	1104.4	1104.3	1104.1	1103.8	1103.6	1103.4
152.5°	1132.7	1133.2	1133.8	1133.7	1133.1	1132.5	1131.9	1131.3
155°	1172.0	1172.9	1173.9	1173.9	1172.9	1172.0	1171.1	1170.2
157.5°	1206.7	1207.4	1208.1	1208.0	1207.2	1206.4	1205.7	1204.9
160°	1228.0	1228.8	1229.4	1229.2	1228.0	1226.9	1225.7	1224.6
162.5°	1247.2	1248.5	1249.7	1249.7	1248.6	1247.4	1246.3	1245.2
165°	1272.6	1273.9	1275.3	1275.6	1274.6	1273.7	1272.8	1271.8
167.5°	1294.0	1295.3	1296.6	1296.6	1295.2	1293.8	1292.4	1291.0
170°	1305.4	1306.8	1308.2	1308.1	1306.5	1304.9	1303.3	1301.7
172.5°	1314.0	1315.6	1317.2	1317.1	1315.5	1313.9	1312.3	1310.7
175°	1323.3	1324.9	1326.6	1326.6	1324.9	1323.3	1321.8	1320.2
177.5°	1328.5	1329.8	1331.0	1330.9	1329.5	1328.0	1326.6	1325.1
180°	1328.4	1328.4	1328.4	1328.4	1328.4	1328.4	1328.4	1328.4

(END OF REPORT)