

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: NEO-RAY

Report Number: P333042

Luminaire Tested: **S124RDIW-S575D770U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333042  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIW-S575D770U835-4F0-1E-UDD-F1  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 770 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5013.4 lumens  
Efficiency: N/A  
Efficacy: 133.3 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 37.6  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333042

CATALOG NUMBER: S124RDIW-S575D770U835-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P333042

CATALOG NUMBER: S124RDIW-S575D770U835-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	53	53	53	47																				
1	97	93	89	86	89	86	83	80	72	70	67	59	58	56	47	46	45	40																				
2	89	82	76	71	81	75	70	66	63	60	56	52	50	47	42	40	39	34																				
3	81	72	65	59	74	66	60	55	56	51	48	46	43	40	37	35	33	29																				
4	74	64	56	50	68	59	52	47	50	45	41	41	38	35	34	31	29	25																				
5	68	57	49	43	63	53	46	40	45	39	35	37	33	30	30	27	25	22																				
6	63	51	43	37	58	47	40	35	40	35	31	34	30	26	28	25	22	19																				
7	58	46	38	33	53	43	36	31	37	31	27	31	27	23	25	22	20	17																				
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	23	20	18	15																				
9	50	38	31	26	46	36	29	25	31	25	22	26	22	19	21	18	16	14																				
10	47	35	28	23	43	33	26	22	28	23	20	24	20	17	20	17	15	13																				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	8205	8205	8205
5°	8223	8122	8173
10°	8171	8025	8025
15°	8078	7856	7798
20°	7948	7635	7494
25°	7784	7375	7187
30°	7623	7101	6804
35°	7447	6818	6419
40°	7233	6495	6003
45°	7036	6174	5579
50°	6812	5805	5130
55°	6572	5422	4643
60°	6307	5000	4146
65°	6065	4474	3656
70°	5712	3895	3104
75°	5268	3228	2523
80°	4593	2459	2315
85°	3890	2232	2093



TEST NUMBER: P333042

CATALOG NUMBER: S124RDIW-S575D770U835-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	95.5	1.9
10°-20°	266.2	5.3
20°-30°	384.4	7.7
30°-40°	435.7	8.7
40°-50°	420.8	8.4
50°-60°	349.9	7.0
60°-70°	241.6	4.8
70°-80°	122.5	2.4
80°-90°	34.3	0.7
90°-100°	63.3	1.3
100°-110°	187.5	3.7
110°-120°	318.2	6.3
120°-130°	419.6	8.4
130°-140°	471.3	9.4
140°-150°	463.1	9.2
150°-160°	389.5	7.8
160°-170°	259.1	5.2
170°-180°	90.7	1.8
0°-30°	746.1	14.9
0°-40°	1181.8	23.6
0°-60°	1952.5	38.9
0°-90°	2350.9	46.9
90°-120°	569.0	11.4
90°-150°	1923.1	38.4
90°-180°	2662.0	53.1
0°-180°	5013.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1016	1016	1016	1016	1016	
5°	1015	1011	1002	1010	1008	96
15°	966	959	940	938	933	272
25°	874	859	828	815	807	402
35°	756	730	692	666	651	472
45°	616	586	541	504	489	475
55°	467	435	385	346	330	418
65°	318	283	234	202	191	313
75°	169	140	104	86	81	178
85°	42	27	24	23	23	47
90°	2	10	16	21	22	5
95°	44	51	56	58	59	50
105°	173	174	177	179	181	183
115°	324	324	322	321	321	319
125°	471	471	470	469	468	420
135°	608	612	612	611	609	470
145°	738	741	742	741	739	462
155°	846	846	845	848	845	389
165°	921	919	917	921	919	260
175°	958	955	954	958	954	91
180°	960	960	960	960	960	



TEST NUMBER: P333042

CATALOG NUMBER: S124RDIW-S575D770U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3
2.5°	1018.8	1018.2	1017.7	1017.1	1016.6	1015.5	1014.0	1012.5	1010.9	1009.4	1010.9
5°	1014.7	1014.0	1013.3	1012.6	1012.0	1010.6	1008.5	1006.4	1004.3	1002.3	1004.0
7.5°	1005.5	1004.8	1004.1	1003.4	1002.6	1000.9	998.2	995.5	992.8	990.1	991.2
10°	996.8	996.0	995.1	994.2	993.4	991.4	988.3	985.1	982.0	978.9	979.6
12.5°	985.6	984.6	983.6	982.6	981.6	979.3	975.6	971.9	968.3	964.6	965.0
15°	966.5	964.9	963.4	961.8	960.2	957.3	953.0	948.7	944.3	940.0	939.7
17.5°	943.3	941.0	938.8	936.5	934.3	930.6	925.4	920.2	915.0	909.8	908.9
20°	925.2	923.0	920.7	918.5	916.2	912.2	906.3	900.4	894.5	888.7	887.3
22.5°	905.3	902.8	900.3	897.7	895.2	890.8	884.5	878.2	871.9	865.6	863.5
25°	873.9	870.8	867.6	864.5	861.4	856.3	849.2	842.1	835.0	828.0	825.0
27.5°	840.9	837.0	833.1	829.2	825.2	819.5	811.9	804.4	796.8	789.2	785.6
30°	817.8	813.5	809.2	804.9	800.6	794.3	786.2	778.1	769.9	761.8	757.5
32.5°	793.6	788.7	783.8	778.9	774.1	767.4	759.0	750.6	742.2	733.8	728.8
35°	755.6	750.1	744.5	739.0	733.5	726.4	717.7	709.1	700.4	691.8	685.9
37.5°	715.0	709.3	703.6	697.9	692.1	684.5	674.9	665.3	655.8	646.2	639.6
40°	686.3	680.6	674.9	669.2	663.5	655.7	645.9	636.0	626.2	616.3	609.0
42.5°	658.9	653.0	647.0	641.0	635.0	626.9	616.6	606.3	596.1	585.8	578.4
45°	616.3	609.9	603.5	597.1	590.7	582.3	571.9	561.6	551.2	540.8	532.3
47.5°	572.3	565.7	559.0	552.4	545.8	537.1	526.3	515.6	504.8	494.0	485.2
50°	542.4	535.6	528.9	522.1	515.4	506.5	495.4	484.4	473.3	462.2	453.6
52.5°	511.9	505.3	498.7	492.1	485.4	476.5	465.1	453.8	442.4	431.1	422.3
55°	466.9	460.0	453.1	446.1	439.2	430.1	418.9	407.7	396.4	385.2	376.2
57.5°	422.4	415.2	408.0	400.8	393.6	384.5	373.4	362.3	351.3	340.2	331.1
60°	390.6	383.7	376.8	369.9	363.0	354.0	342.9	331.8	320.8	309.7	300.7
62.5°	362.0	354.8	347.6	340.4	333.2	324.0	312.6	301.3	289.9	278.6	270.3
65°	317.5	310.1	302.6	295.2	287.7	278.5	267.4	256.4	245.3	234.2	226.8
67.5°	271.3	264.1	257.0	249.9	242.8	234.1	223.8	213.5	203.3	193.0	186.6
70°	242.0	234.7	227.5	220.2	213.0	204.4	194.5	184.7	174.8	165.0	159.3
72.5°	210.9	204.3	197.7	191.2	184.6	176.7	167.4	158.1	148.7	139.4	134.6
75°	168.9	162.5	156.1	149.7	143.3	136.0	127.9	119.7	111.6	103.5	99.5
77.5°	126.2	120.8	115.4	109.9	104.5	98.5	91.9	85.4	78.8	72.2	69.9
80°	98.8	93.8	88.8	83.8	78.8	73.7	68.5	63.3	58.1	52.9	52.4
82.5°	75.2	70.6	66.0	61.4	56.8	53.0	50.0	47.0	44.1	41.1	40.7
85°	42.0	38.6	35.1	31.6	28.2	26.2	25.7	25.2	24.6	24.1	23.8
87.5°	14.8	14.0	13.3	12.5	11.8	11.5	11.6	11.7	11.9	12.0	12.0
90°	2.2	4.0	5.9	7.7	9.5	11.1	12.4	13.7	15.0	16.3	17.3
92.5°	15.9	18.0	20.0	22.1	24.2	25.7	26.6	27.5	28.5	29.4	30.0
95°	44.5	46.0	47.5	49.0	50.5	51.8	52.9	54.1	55.3	56.4	56.9
97.5°	77.8	79.0	80.2	81.3	82.5	83.8	85.2	86.5	87.9	89.2	89.8
100°	103.9	104.6	105.2	105.9	106.5	107.6	109.1	110.6	112.1	113.6	113.9
102.5°	131.2	131.5	131.7	132.0	132.3	133.1	134.4	135.8	137.1	138.5	139.0
105°	172.9	173.1	173.3	173.4	173.6	174.0	174.7	175.3	176.0	176.6	177.1
107.5°	216.7	216.9	217.1	217.3	217.5	217.7	217.8	217.9	218.0	218.1	218.5
110°	246.4	246.7	247.1	247.4	247.7	247.8	247.6	247.5	247.3	247.1	246.8



TEST NUMBER: P333042

CATALOG NUMBER: S124RDIW-S575D770U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	277.3	277.3	277.4	277.5	277.5	277.4	277.1	276.8	276.5	276.2	276.2
115°	323.6	323.6	323.6	323.6	323.6	323.4	323.1	322.8	322.4	322.1	321.9
117.5°	367.2	367.4	367.5	367.6	367.8	367.7	367.5	367.3	367.0	366.8	366.2
120°	396.3	397.0	397.6	398.3	399.0	399.0	398.6	398.1	397.6	397.1	396.2
122.5°	426.6	426.9	427.1	427.4	427.7	427.7	427.5	427.2	427.0	426.8	426.2
125°	471.3	471.3	471.3	471.3	471.3	471.2	471.0	470.9	470.7	470.5	470.2
127.5°	511.8	512.3	512.8	513.3	513.8	513.9	513.6	513.4	513.1	512.9	512.5
130°	540.3	540.8	541.3	541.8	542.3	542.5	542.5	542.5	542.5	542.5	542.2
132.5°	569.4	569.8	570.1	570.5	570.9	571.0	570.8	570.7	570.6	570.4	570.1
135°	607.9	608.8	609.8	610.8	611.8	612.3	612.3	612.3	612.3	612.3	612.0
137.5°	649.7	650.2	650.6	651.1	651.6	651.9	652.2	652.4	652.7	653.0	652.5
140°	677.6	677.9	678.3	678.6	678.9	679.1	679.1	679.1	679.1	679.1	678.9
142.5°	703.1	703.5	703.8	704.1	704.5	704.6	704.4	704.3	704.2	704.0	704.0
145°	738.5	739.1	739.8	740.5	741.1	741.5	741.7	741.9	742.0	742.2	742.0
147.5°	773.5	774.3	775.1	775.9	776.7	777.0	776.9	776.7	776.6	776.5	776.3
150°	794.9	795.5	796.2	796.9	797.5	797.9	797.9	797.9	797.9	797.9	797.9
152.5°	815.1	815.5	815.9	816.3	816.7	816.9	817.0	817.2	817.3	817.4	817.8
155°	846.1	846.1	846.1	846.1	846.1	846.0	845.8	845.7	845.5	845.4	846.0
157.5°	872.2	871.9	871.6	871.3	871.0	870.9	870.8	870.8	870.8	870.7	871.2
160°	887.7	887.5	887.3	887.2	887.0	886.8	886.7	886.5	886.3	886.2	886.7
162.5°	901.9	901.5	901.0	900.6	900.2	899.9	899.7	899.6	899.4	899.2	900.1
165°	921.1	920.6	920.1	919.6	919.1	918.7	918.3	918.0	917.7	917.3	918.3
167.5°	935.7	935.1	934.4	933.7	933.0	932.6	932.7	932.7	932.7	932.8	933.8
170°	944.1	943.2	942.4	941.6	940.8	940.4	940.6	940.8	940.9	941.1	942.1
172.5°	950.0	949.3	948.6	947.9	947.2	946.9	946.9	947.0	947.0	947.0	948.2
175°	958.2	957.3	956.5	955.7	954.9	954.4	954.2	954.0	953.9	953.7	954.9
177.5°	960.8	960.2	959.5	958.9	958.2	957.9	957.9	957.9	957.9	957.9	958.8
180°	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6



TEST NUMBER: P333042

CATALOG NUMBER: S124RDIW-S575D770U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3
2.5°	1012.5	1014.0	1015.5	1016.2	1016.1	1015.9	1015.8	1015.7
5°	1005.7	1007.5	1009.2	1009.9	1009.5	1009.2	1008.8	1008.5
7.5°	992.3	993.4	994.6	994.8	994.3	993.7	993.2	992.6
10°	980.3	981.0	981.7	981.7	981.0	980.3	979.6	978.9
12.5°	965.4	965.8	966.3	966.0	965.0	964.1	963.1	962.1
15°	939.3	939.0	938.6	937.9	936.6	935.4	934.2	933.0
17.5°	907.9	906.9	905.9	904.5	902.7	900.9	899.0	897.2
20°	885.9	884.5	883.1	881.3	879.1	876.8	874.6	872.3
22.5°	861.5	859.4	857.3	855.4	853.5	851.7	849.9	848.0
25°	822.1	819.1	816.2	813.9	812.1	810.4	808.7	806.9
27.5°	781.9	778.3	774.7	771.6	769.1	766.6	764.2	761.7
30°	753.2	748.8	744.5	741.0	738.2	735.4	732.7	729.9
32.5°	723.8	718.8	713.7	709.9	707.3	704.7	702.0	699.4
35°	680.0	674.1	668.3	663.8	660.7	657.5	654.4	651.3
37.5°	633.0	626.5	619.9	615.1	611.9	608.8	605.7	602.6
40°	601.8	594.5	587.2	582.1	578.9	575.8	572.7	569.6
42.5°	571.0	563.6	556.2	550.9	547.6	544.4	541.1	537.9
45°	523.9	515.4	506.9	501.1	498.0	494.9	491.8	488.7
47.5°	476.4	467.6	458.8	452.7	449.3	445.9	442.5	439.0
50°	444.9	436.3	427.6	421.7	418.4	415.1	411.8	408.5
52.5°	413.5	404.7	396.0	389.9	386.4	383.0	379.6	376.2
55°	367.2	358.2	349.2	343.1	339.8	336.5	333.2	329.9
57.5°	321.9	312.8	303.7	297.9	295.4	292.9	290.4	287.9
60°	291.7	282.7	273.7	267.9	265.1	262.3	259.6	256.8
62.5°	262.0	253.7	245.4	240.1	237.9	235.7	233.5	231.3
65°	219.4	211.9	204.5	199.7	197.7	195.6	193.5	191.4
67.5°	180.2	173.8	167.4	163.1	160.8	158.5	156.2	153.9
70°	153.6	147.9	142.1	138.4	136.7	135.0	133.2	131.5
72.5°	129.7	124.8	119.9	116.7	115.1	113.5	111.9	110.3
75°	95.5	91.6	87.6	85.1	84.0	83.0	82.0	80.9
77.5°	67.6	65.3	62.9	61.6	61.3	61.0	60.7	60.4
80°	51.9	51.4	50.8	50.5	50.3	50.1	50.0	49.8
82.5°	40.3	39.9	39.6	39.3	39.1	38.9	38.8	38.6
85°	23.4	23.1	22.7	22.6	22.6	22.6	22.6	22.6
87.5°	12.1	12.2	12.2	12.4	12.6	12.8	13.0	13.2
90°	18.3	19.3	20.3	20.9	21.3	21.6	21.9	22.3
92.5°	30.6	31.2	31.8	32.2	32.4	32.6	32.8	33.0
95°	57.4	57.9	58.4	58.6	58.6	58.6	58.6	58.6
97.5°	90.4	91.0	91.6	91.9	91.9	91.9	91.9	91.9
100°	114.2	114.5	114.9	115.0	115.0	115.0	115.0	115.0
102.5°	139.4	139.9	140.3	140.6	140.8	140.9	141.0	141.2
105°	177.6	178.1	178.6	179.1	179.6	180.1	180.6	181.1
107.5°	219.0	219.4	219.9	220.1	220.1	220.1	220.0	220.0
110°	246.5	246.2	245.8	245.9	246.4	246.9	247.4	247.9





TEST NUMBER: P333042

CATALOG NUMBER: S124RDIW-S575D770U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	276.1	276.0	276.0	276.0	276.1	276.2	276.3	276.4
115°	321.8	321.6	321.4	321.3	321.1	321.0	320.8	320.6
117.5°	365.7	365.1	364.5	364.1	363.8	363.4	363.1	362.8
120°	395.4	394.6	393.8	393.5	393.9	394.2	394.5	394.8
122.5°	425.6	425.1	424.5	423.9	423.3	422.7	422.2	421.6
125°	469.9	469.6	469.2	468.9	468.6	468.2	467.9	467.6
127.5°	512.2	511.9	511.5	511.2	511.0	510.7	510.4	510.2
130°	541.9	541.5	541.2	540.7	540.1	539.4	538.7	538.1
132.5°	569.8	569.5	569.1	568.8	568.6	568.3	568.0	567.8
135°	611.6	611.3	611.0	610.6	610.1	609.6	609.1	608.6
137.5°	652.1	651.7	651.3	651.1	651.2	651.3	651.4	651.5
140°	678.8	678.6	678.4	678.3	678.1	677.9	677.8	677.6
142.5°	704.0	703.9	703.9	703.9	703.8	703.8	703.8	703.7
145°	741.9	741.7	741.5	741.2	740.7	740.2	739.7	739.2
147.5°	776.2	776.1	775.9	775.8	775.6	775.5	775.3	775.1
150°	797.9	797.9	797.9	797.8	797.6	797.4	797.3	797.1
152.5°	818.2	818.6	819.0	819.0	818.6	818.2	817.7	817.3
155°	846.7	847.3	848.0	848.0	847.3	846.7	846.0	845.4
157.5°	871.7	872.2	872.7	872.7	872.1	871.6	871.0	870.4
160°	887.2	887.7	888.2	888.0	887.2	886.3	885.5	884.7
162.5°	901.0	901.9	902.8	902.8	902.0	901.2	900.4	899.5
165°	919.3	920.3	921.3	921.5	920.8	920.1	919.5	918.8
167.5°	934.8	935.7	936.7	936.7	935.7	934.7	933.7	932.6
170°	943.1	944.1	945.1	945.0	943.8	942.7	941.5	940.4
172.5°	949.3	950.4	951.5	951.5	950.3	949.2	948.0	946.9
175°	956.0	957.2	958.3	958.3	957.2	956.0	954.9	953.7
177.5°	959.7	960.6	961.6	961.5	960.4	959.4	958.3	957.3
180°	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6

(END OF REPORT)