

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333070

Luminaire Tested: **S124RDIW-S795D1340U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333070  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIW-S795D1340U835-4F0-1E-UDD-F1  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7866.9 lumens  
Efficiency: N/A  
Efficacy: 128.1 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 61.4  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333070

CATALOG NUMBER: S124RDIW-S795D1340U835-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P333070

CATALOG NUMBER: S124RDIW-S795D1340U835-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	48	48	48	41																				
1	96	92	88	85	87	84	81	78	69	67	65	55	54	52	42	42	41	35																				
2	88	80	74	69	80	73	68	64	61	57	54	49	46	44	38	36	35	30																				
3	80	71	64	58	73	65	59	54	54	49	45	43	40	37	34	31	30	25																				
4	73	63	55	49	66	58	51	46	48	43	39	39	35	32	30	28	26	22																				
5	67	56	48	42	61	51	44	39	43	38	34	35	31	28	27	25	22	19																				
6	62	50	42	37	56	46	39	34	38	33	29	31	27	25	25	22	20	17																				
7	57	45	38	32	52	42	35	30	35	30	26	29	25	22	23	20	18	15																				
8	53	41	34	28	48	38	31	27	32	27	23	26	22	19	21	18	16	13																				
9	49	37	30	25	45	35	28	24	29	24	21	24	20	17	19	16	14	12																				
10	46	34	27	23	42	32	25	21	27	22	18	22	18	16	18	15	13	11																				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	11215	11215	11215
5°	11240	11102	11171
10°	11170	10969	10969
15°	11041	10739	10659
20°	10865	10436	10244
25°	10640	10081	9825
30°	10421	9707	9300
35°	10178	9319	8774
40°	9887	8878	8205
45°	9618	8440	7626
50°	9311	7935	7013
55°	8983	7410	6348
60°	8622	6835	5667
65°	8290	6117	4999
70°	7808	5323	4244
75°	7199	4414	3450
80°	6281	3361	3166
85°	5317	3057	2853



TEST NUMBER: P333070

CATALOG NUMBER: S124RDIW-S795D1340U835-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	130.5	1.7
10°-20°	363.9	4.6
20°-30°	525.5	6.7
30°-40°	595.6	7.6
40°-50°	575.2	7.3
50°-60°	478.3	6.1
60°-70°	330.3	4.2
70°-80°	167.4	2.1
80°-90°	48.0	0.6
90°-100°	110.6	1.4
100°-110°	327.6	4.2
110°-120°	556.1	7.1
120°-130°	733.3	9.3
130°-140°	823.5	10.5
140°-150°	809.2	10.3
150°-160°	680.6	8.7
160°-170°	452.8	5.8
170°-180°	158.6	2.0
0°-30°	1019.8	13.0
0°-40°	1615.5	20.5
0°-60°	2668.9	33.9
0°-90°	3214.5	40.9
90°-120°	994.3	12.6
90°-150°	3360.3	42.7
90°-180°	4652.0	59.1
0°-180°	7866.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1389	1389	1389	1389	1389	
5°	1387	1382	1370	1380	1378	132
15°	1321	1311	1285	1282	1275	372
25°	1194	1174	1132	1114	1103	550
35°	1033	998	946	910	890	645
45°	842	802	739	689	668	649
55°	638	594	526	473	451	571
65°	434	387	320	276	262	428
75°	231	191	142	118	111	244
85°	57	37	33	31	31	65
90°	4	18	28	36	39	8
95°	78	89	99	102	102	87
105°	302	304	309	313	316	321
115°	565	565	563	562	560	557
125°	824	823	822	820	817	734
135°	1062	1070	1070	1067	1063	821
145°	1290	1295	1297	1295	1292	807
155°	1478	1478	1477	1482	1477	680
165°	1609	1606	1603	1610	1606	453
175°	1674	1668	1666	1675	1666	159
180°	1677	1677	1677	1677	1677	



TEST NUMBER: P333070

CATALOG NUMBER: S124RDIW-S795D1340U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1389.2	1389.2	1389.2	1389.2	1389.2	1389.2	1389.2	1389.2	1389.2	1389.2	1389.2
2.5°	1392.6	1391.8	1391.0	1390.3	1389.5	1388.1	1386.0	1384.0	1381.9	1379.8	1381.9
5°	1387.0	1386.1	1385.1	1384.2	1383.2	1381.4	1378.5	1375.7	1372.8	1370.0	1372.4
7.5°	1374.5	1373.5	1372.5	1371.5	1370.5	1368.2	1364.5	1360.8	1357.1	1353.4	1354.9
10°	1362.6	1361.4	1360.2	1359.0	1357.8	1355.1	1350.9	1346.6	1342.4	1338.1	1339.0
12.5°	1347.2	1345.9	1344.5	1343.1	1341.8	1338.6	1333.6	1328.5	1323.5	1318.5	1319.1
15°	1321.1	1319.0	1316.8	1314.7	1312.6	1308.6	1302.6	1296.7	1290.8	1284.9	1284.4
17.5°	1289.4	1286.3	1283.2	1280.2	1277.1	1272.0	1264.9	1257.8	1250.7	1243.6	1242.3
20°	1264.7	1261.6	1258.6	1255.5	1252.4	1246.9	1238.8	1230.8	1222.7	1214.7	1212.8
22.5°	1237.5	1234.0	1230.6	1227.1	1223.7	1217.6	1209.0	1200.4	1191.8	1183.2	1180.4
25°	1194.5	1190.2	1186.0	1181.7	1177.5	1170.5	1160.8	1151.1	1141.4	1131.7	1127.7
27.5°	1149.4	1144.1	1138.7	1133.4	1128.0	1120.2	1109.8	1099.5	1089.1	1078.8	1073.8
30°	1117.9	1112.0	1106.1	1100.2	1094.3	1085.8	1074.7	1063.6	1052.4	1041.3	1035.4
32.5°	1084.7	1078.1	1071.4	1064.7	1058.1	1049.0	1037.5	1026.0	1014.5	1003.0	996.2
35°	1032.8	1025.3	1017.7	1010.1	1002.6	992.9	981.1	969.2	957.4	945.6	937.6
37.5°	977.3	969.5	961.7	953.9	946.1	935.7	922.6	909.5	896.4	883.3	874.3
40°	938.2	930.4	922.6	914.8	907.0	896.3	882.8	869.4	855.9	842.4	832.5
42.5°	900.7	892.5	884.4	876.2	868.0	856.9	842.9	828.8	814.8	800.7	790.6
45°	842.4	833.7	824.9	816.2	807.4	796.0	781.8	767.6	753.4	739.3	727.7
47.5°	782.2	773.2	764.2	755.1	746.1	734.2	719.5	704.7	690.0	675.2	663.2
50°	741.4	732.2	722.9	713.7	704.5	692.3	677.2	662.1	646.9	631.8	620.0
52.5°	699.7	690.7	681.6	672.6	663.6	651.3	635.8	620.3	604.8	589.3	577.3
55°	638.2	628.7	619.3	609.8	600.4	588.0	572.6	557.2	541.9	526.5	514.2
57.5°	577.4	567.5	557.7	547.9	538.0	525.5	510.4	495.3	480.2	465.0	452.6
60°	534.0	524.5	515.1	505.6	496.1	483.9	468.7	453.6	438.5	423.3	411.0
62.5°	494.8	485.0	475.2	465.3	455.5	442.8	427.3	411.8	396.3	380.8	369.4
65°	434.0	423.8	413.6	403.5	393.3	380.7	365.5	350.4	335.3	320.2	310.0
67.5°	370.8	361.1	351.3	341.6	331.8	320.0	305.9	291.9	277.8	263.8	255.0
70°	330.8	320.9	310.9	301.0	291.1	279.4	265.9	252.4	239.0	225.5	217.7
72.5°	288.3	279.3	270.3	261.3	252.3	241.5	228.8	216.0	203.3	190.6	183.9
75°	230.8	222.1	213.3	204.6	195.8	185.9	174.8	163.7	152.6	141.5	136.0
77.5°	172.5	165.1	157.7	150.3	142.8	134.6	125.7	116.7	107.7	98.7	95.5
80°	135.1	128.2	121.4	114.5	107.7	100.7	93.6	86.5	79.4	72.3	71.6
82.5°	102.8	96.5	90.2	83.9	77.6	72.4	68.4	64.3	60.2	56.2	55.6
85°	57.4	52.7	48.0	43.3	38.5	35.8	35.1	34.4	33.7	33.0	32.5
87.5°	20.3	19.5	18.6	17.7	16.8	16.5	16.8	17.1	17.3	17.6	17.8
90°	3.9	7.1	10.2	13.4	16.6	19.3	21.6	23.9	26.2	28.5	30.3
92.5°	27.8	31.4	35.0	38.6	42.3	44.9	46.5	48.1	49.7	51.4	52.4
95°	77.8	80.4	83.0	85.6	88.2	90.5	92.5	94.5	96.5	98.6	99.4
97.5°	135.9	138.0	140.1	142.1	144.2	146.4	148.8	151.2	153.5	155.9	156.9
100°	181.6	182.7	183.9	185.0	186.2	188.0	190.6	193.2	195.8	198.4	199.0
102.5°	229.3	229.8	230.2	230.7	231.1	232.5	234.9	237.3	239.6	242.0	242.8
105°	302.2	302.5	302.8	303.0	303.3	304.0	305.2	306.4	307.5	308.7	309.5
107.5°	378.7	379.0	379.4	379.7	380.1	380.3	380.5	380.7	380.9	381.0	381.8
110°	430.6	431.1	431.7	432.3	432.9	433.0	432.7	432.4	432.2	431.9	431.3



TEST NUMBER: P333070

CATALOG NUMBER: S124RDIW-S795D1340U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	484.5	484.6	484.7	484.9	485.0	484.8	484.3	483.7	483.2	482.7	482.6
115°	565.4	565.4	565.4	565.4	565.4	565.2	564.6	564.0	563.4	562.8	562.6
117.5°	641.7	641.9	642.2	642.4	642.6	642.5	642.1	641.7	641.3	640.9	639.9
120°	692.5	693.7	694.8	696.0	697.1	697.3	696.4	695.6	694.7	693.8	692.4
122.5°	745.4	745.9	746.4	746.8	747.3	747.3	746.9	746.5	746.1	745.7	744.7
125°	823.5	823.5	823.5	823.5	823.5	823.4	823.1	822.8	822.5	822.2	821.6
127.5°	894.3	895.2	896.1	896.9	897.8	898.0	897.5	897.1	896.6	896.1	895.6
130°	944.1	945.0	945.9	946.7	947.6	948.0	948.0	948.0	948.0	948.0	947.4
132.5°	995.0	995.6	996.2	996.9	997.5	997.7	997.5	997.2	997.0	996.8	996.2
135°	1062.1	1063.9	1065.6	1067.3	1069.1	1069.9	1069.9	1069.9	1069.9	1069.9	1069.4
137.5°	1135.3	1136.1	1136.9	1137.7	1138.5	1139.2	1139.6	1140.1	1140.5	1141.0	1140.2
140°	1184.1	1184.6	1185.2	1185.8	1186.4	1186.6	1186.6	1186.6	1186.6	1186.6	1186.4
142.5°	1228.7	1229.2	1229.8	1230.4	1231.0	1231.1	1230.9	1230.7	1230.5	1230.2	1230.2
145°	1290.4	1291.6	1292.7	1293.9	1295.0	1295.7	1296.0	1296.3	1296.6	1296.9	1296.6
147.5°	1351.6	1353.0	1354.4	1355.8	1357.1	1357.7	1357.5	1357.3	1357.0	1356.8	1356.6
150°	1389.0	1390.1	1391.3	1392.4	1393.6	1394.1	1394.1	1394.1	1394.1	1394.1	1394.1
152.5°	1424.2	1424.9	1425.6	1426.3	1427.0	1427.5	1427.7	1427.9	1428.2	1428.4	1429.1
155°	1478.4	1478.4	1478.4	1478.4	1478.4	1478.3	1478.0	1477.7	1477.4	1477.2	1478.3
157.5°	1524.1	1523.6	1523.1	1522.5	1522.0	1521.7	1521.7	1521.6	1521.6	1521.5	1522.4
160°	1551.1	1550.8	1550.5	1550.2	1549.9	1549.6	1549.3	1549.1	1548.8	1548.5	1549.3
162.5°	1576.0	1575.2	1574.5	1573.7	1573.0	1572.5	1572.2	1571.9	1571.6	1571.3	1572.9
165°	1609.4	1608.6	1607.7	1606.8	1606.0	1605.3	1604.7	1604.1	1603.5	1602.9	1604.7
167.5°	1635.1	1633.9	1632.7	1631.5	1630.3	1629.7	1629.8	1629.8	1629.9	1629.9	1631.7
170°	1649.6	1648.2	1646.8	1645.3	1643.9	1643.3	1643.6	1643.9	1644.2	1644.4	1646.2
172.5°	1660.0	1658.8	1657.6	1656.4	1655.2	1654.6	1654.7	1654.7	1654.8	1654.8	1656.8
175°	1674.3	1672.8	1671.4	1670.0	1668.5	1667.6	1667.4	1667.1	1666.8	1666.5	1668.5
177.5°	1678.9	1677.8	1676.6	1675.5	1674.3	1673.8	1673.8	1673.8	1673.8	1673.8	1675.4
180°	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9



TEST NUMBER: P333070

CATALOG NUMBER: S124RDIW-S795D1340U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1389.2	1389.2	1389.2	1389.2	1389.2	1389.2	1389.2	1389.2
2.5°	1384.0	1386.0	1388.1	1389.1	1388.9	1388.7	1388.5	1388.3
5°	1374.7	1377.1	1379.5	1380.4	1379.9	1379.5	1379.0	1378.5
7.5°	1356.4	1358.0	1359.5	1359.8	1359.1	1358.3	1357.6	1356.8
10°	1340.0	1340.9	1341.9	1341.9	1340.9	1340.0	1339.0	1338.1
12.5°	1319.7	1320.2	1320.8	1320.4	1319.1	1317.8	1316.4	1315.1
15°	1284.0	1283.5	1283.0	1282.0	1280.3	1278.6	1277.0	1275.3
17.5°	1241.0	1239.7	1238.3	1236.4	1233.9	1231.4	1228.9	1226.4
20°	1210.9	1209.0	1207.1	1204.7	1201.6	1198.5	1195.4	1192.4
22.5°	1177.6	1174.7	1171.9	1169.2	1166.7	1164.2	1161.7	1159.2
25°	1123.7	1119.7	1115.7	1112.5	1110.1	1107.8	1105.4	1103.0
27.5°	1068.8	1063.9	1058.9	1054.7	1051.3	1047.9	1044.5	1041.1
30°	1029.5	1023.6	1017.7	1012.8	1009.1	1005.3	1001.5	997.7
32.5°	989.3	982.5	975.6	970.4	966.8	963.2	959.6	956.0
35°	929.5	921.5	913.5	907.3	903.1	898.8	894.5	890.3
37.5°	865.3	856.3	847.3	840.7	836.5	832.2	828.0	823.7
40°	822.6	812.6	802.7	795.6	791.4	787.1	782.9	778.6
42.5°	780.5	770.4	760.3	753.0	748.5	744.1	739.7	735.2
45°	716.1	704.5	692.9	685.0	680.7	676.5	672.2	668.0
47.5°	651.2	639.2	627.2	618.8	614.2	609.5	604.8	600.1
50°	608.2	596.4	584.5	576.4	571.9	567.4	562.9	558.4
52.5°	565.3	553.3	541.2	532.9	528.2	523.5	518.9	514.2
55°	501.9	489.6	477.4	469.0	464.5	460.0	455.5	451.0
57.5°	440.1	427.6	415.1	407.2	403.8	400.4	397.0	393.6
60°	398.8	386.5	374.2	366.1	362.4	358.6	354.8	351.0
62.5°	358.1	346.8	335.4	328.2	325.2	322.2	319.1	316.1
65°	299.8	289.7	279.5	273.0	270.2	267.3	264.5	261.7
67.5°	246.3	237.6	228.8	222.9	219.8	216.6	213.5	210.4
70°	209.9	202.1	194.3	189.2	186.9	184.5	182.1	179.8
72.5°	177.3	170.6	163.9	159.5	157.4	155.2	153.0	150.8
75°	130.6	125.2	119.7	116.3	114.9	113.5	112.0	110.6
77.5°	92.4	89.2	86.0	84.2	83.8	83.4	83.0	82.5
80°	70.9	70.2	69.5	69.0	68.8	68.5	68.3	68.1
82.5°	55.1	54.6	54.1	53.7	53.5	53.2	53.0	52.8
85°	32.0	31.6	31.1	30.8	30.8	30.8	30.8	30.8
87.5°	17.9	18.1	18.2	18.5	18.8	19.1	19.4	19.7
90°	32.0	33.7	35.4	36.6	37.2	37.8	38.3	38.9
92.5°	53.4	54.5	55.5	56.2	56.5	56.9	57.2	57.6
95°	100.3	101.2	102.0	102.5	102.5	102.5	102.5	102.5
97.5°	158.0	159.0	160.0	160.6	160.6	160.6	160.6	160.6
100°	199.6	200.2	200.7	201.0	201.0	201.0	201.0	201.0
102.5°	243.6	244.4	245.2	245.7	246.0	246.2	246.4	246.7
105°	310.4	311.3	312.1	313.0	313.8	314.7	315.6	316.4
107.5°	382.6	383.4	384.3	384.6	384.6	384.5	384.5	384.4
110°	430.7	430.1	429.6	429.7	430.6	431.4	432.3	433.2





TEST NUMBER: P333070

CATALOG NUMBER: S124RDIW-S795D1340U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	482.5	482.4	482.2	482.3	482.4	482.6	482.8	483.0
115°	562.3	562.0	561.7	561.4	561.1	560.8	560.5	560.3
117.5°	639.0	638.0	637.0	636.2	635.6	635.1	634.5	633.9
120°	691.0	689.5	688.1	687.6	688.2	688.8	689.4	689.9
122.5°	743.7	742.8	741.8	740.8	739.7	738.7	737.7	736.6
125°	821.1	820.5	819.9	819.3	818.8	818.2	817.6	817.0
127.5°	895.0	894.4	893.8	893.3	892.9	892.4	891.9	891.5
130°	946.9	946.3	945.7	944.9	943.7	942.5	941.4	940.2
132.5°	995.6	995.1	994.5	994.0	993.5	993.0	992.6	992.1
135°	1068.8	1068.2	1067.6	1066.9	1066.0	1065.2	1064.3	1063.4
137.5°	1139.5	1138.8	1138.0	1137.7	1137.9	1138.1	1138.2	1138.4
140°	1186.1	1185.8	1185.5	1185.2	1184.9	1184.6	1184.3	1184.1
142.5°	1230.1	1230.1	1230.0	1229.9	1229.9	1229.8	1229.8	1229.7
145°	1296.3	1296.0	1295.7	1295.2	1294.3	1293.4	1292.6	1291.7
147.5°	1356.3	1356.1	1355.9	1355.6	1355.3	1355.0	1354.8	1354.5
150°	1394.1	1394.1	1394.1	1394.0	1393.7	1393.4	1393.1	1392.9
152.5°	1429.8	1430.5	1431.2	1431.1	1430.4	1429.6	1428.9	1428.1
155°	1479.5	1480.6	1481.8	1481.8	1480.6	1479.5	1478.3	1477.2
157.5°	1523.2	1524.1	1525.0	1524.9	1523.9	1522.9	1522.0	1521.0
160°	1550.2	1551.1	1551.9	1551.6	1550.2	1548.8	1547.3	1545.9
162.5°	1574.4	1576.0	1577.5	1577.6	1576.1	1574.7	1573.3	1571.8
165°	1606.4	1608.1	1609.9	1610.2	1609.0	1607.8	1606.7	1605.5
167.5°	1633.4	1635.1	1636.8	1636.8	1635.0	1633.2	1631.5	1629.7
170°	1647.9	1649.6	1651.4	1651.2	1649.2	1647.2	1645.2	1643.2
172.5°	1658.7	1660.7	1662.7	1662.6	1660.6	1658.6	1656.6	1654.6
175°	1670.5	1672.5	1674.6	1674.6	1672.5	1670.5	1668.5	1666.5
177.5°	1677.0	1678.6	1680.2	1680.1	1678.3	1676.4	1674.6	1672.7
180°	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9

(END OF REPORT)