

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333072-927

Luminaire Tested: **S124RDIW-S795D1560U927-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333072-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S795D1560U927-4F0-1E-UDD-A1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 795 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6932.9 lumens
Efficiency: N/A
Efficacy: 101.8 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 68.1
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333072-927

CATALOG NUMBER: S124RDIW-S795D1560U927-4F0-1E-UDD-A1

Luminous Intensity Polar Plot



— 0°-180° - - - 45°-225° ···· 90°-270° - · - · 135°-315°



TEST NUMBER: P333072-927

CATALOG NUMBER: S124RDIW-S795D1560U927-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	95	95	95	95	77	77	77	60	60	60	45	45	45	38
1	95	91	88	84	87	83	80	77	68	66	64	54	52	51	41	40	39	33
2	87	80	74	69	79	73	68	64	60	56	53	47	45	43	36	35	33	28
3	80	71	64	58	72	65	59	54	53	49	45	42	39	37	32	30	29	24
4	73	63	55	49	66	57	51	46	47	42	39	38	34	32	29	27	25	21
5	67	56	48	42	61	51	44	39	42	37	33	34	30	28	26	24	22	18
6	62	50	42	37	56	46	39	34	38	33	29	31	27	24	24	21	19	16
7	57	45	38	32	52	42	35	30	35	29	26	28	24	21	22	19	17	15
8	53	41	34	28	48	38	31	27	32	26	23	26	22	19	20	17	16	13
9	49	37	30	25	45	35	28	24	29	24	20	24	20	17	19	16	14	12
10	46	34	27	23	42	32	25	21	27	22	18	22	18	16	17	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	8442	8442	8442	8442
5°	9792	8468	7484	8468
10°	11584	8430	6679	8430
15°	13381	8352	5739	8352
20°	14898	8245	5191	8245
25°	15380	8141	4819	8141
30°	13463	8011	4595	8011
35°	10480	7823	4459	7823
40°	7860	7606	4387	7606
45°	6205	7258	4349	7258
50°	5238	6859	4222	6859
55°	4566	6415	3997	6415
60°	4108	5959	3538	5959
65°	3622	5465	3041	5465
70°	3262	4952	2745	4952
75°	2732	4389	2339	4389
80°	2311	3742	2194	3742
85°	1954	2927	1954	2927



TEST NUMBER: P333072-927

CATALOG NUMBER: S124RDIW-S795D1560U927-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	101.3	1.5
10°-20°	305.6	4.4
20°-30°	478.0	6.9
30°-40°	531.4	7.7
40°-50°	471.5	6.8
50°-60°	367.4	5.3
60°-70°	240.5	3.5
70°-80°	118.3	1.7
80°-90°	33.8	0.5
90°-100°	101.9	1.5
100°-110°	301.8	4.4
110°-120°	512.2	7.4
120°-130°	675.4	9.7
130°-140°	758.5	10.9
140°-150°	745.3	10.8
150°-160°	626.9	9.0
160°-170°	417.1	6.0
170°-180°	146.1	2.1
0°-30°	885.0	12.8
0°-40°	1416.4	20.4
0°-60°	2255.3	32.5
0°-90°	2647.9	38.2
90°-120°	915.8	13.2
90°-150°	3095.0	44.6
90°-180°	4285.0	61.8
0°-180°	6932.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1046	1046	1046	1046	1046	
5°	1208	1045	924	1045	1208	122
15°	1601	999	687	999	1601	455
25°	1727	914	541	914	1727	766
35°	1063	794	452	794	1063	667
45°	544	636	381	636	544	430
55°	324	456	284	456	324	295
65°	190	286	159	286	190	191
75°	88	141	75	141	88	96
85°	21	32	21	32	21	25
90°	36	4	36	4	36	19
95°	94	72	94	72	94	98
105°	291	278	291	278	291	307
115°	516	521	516	521	516	510
125°	752	758	752	758	752	671
135°	980	978	980	978	980	756
145°	1190	1188	1190	1188	1190	744
155°	1360	1362	1360	1362	1360	626
165°	1479	1482	1479	1482	1479	416
175°	1535	1542	1535	1542	1535	146
180°	1544	1544	1544	1544	1544	



TEST NUMBER: P333072-927

CATALOG NUMBER: S124RDIW-S795D1560U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7
2.5°	1103.0	1106.0	1103.0	1102.6	1099.3	1098.3	1096.9	1092.6	1084.4	1079.7	1080.8
5°	1208.3	1218.9	1213.0	1212.1	1202.8	1193.6	1187.6	1174.2	1159.8	1150.2	1142.2
7.5°	1330.2	1336.3	1332.5	1326.6	1311.6	1303.1	1289.4	1271.7	1246.0	1226.4	1208.4
10°	1413.1	1418.2	1416.4	1405.5	1394.6	1372.2	1359.5	1334.7	1302.3	1276.6	1252.6
12.5°	1494.6	1500.1	1485.2	1485.7	1465.0	1447.4	1427.4	1396.1	1358.6	1325.5	1295.4
15°	1601.0	1594.3	1594.3	1585.8	1562.7	1538.2	1517.6	1484.7	1437.5	1397.9	1356.2
17.5°	1684.3	1686.6	1683.1	1663.3	1645.0	1619.8	1581.9	1543.6	1499.8	1446.6	1404.0
20°	1734.1	1734.1	1730.4	1716.8	1693.3	1666.3	1625.4	1583.7	1528.1	1474.6	1426.6
22.5°	1754.4	1755.7	1751.2	1740.1	1718.9	1692.6	1657.8	1615.4	1558.1	1497.9	1438.4
25°	1726.6	1734.6	1735.4	1732.4	1726.1	1710.1	1680.2	1636.8	1585.4	1520.1	1456.0
27.5°	1585.2	1595.2	1604.1	1618.7	1638.1	1648.1	1649.5	1627.5	1582.6	1519.7	1455.3
30°	1444.2	1452.7	1480.0	1515.8	1543.7	1569.0	1590.9	1596.8	1571.5	1515.0	1447.2
32.5°	1287.9	1299.3	1326.7	1365.2	1411.6	1454.4	1503.6	1528.7	1528.0	1494.1	1431.4
35°	1063.4	1071.8	1097.1	1137.6	1193.2	1256.8	1334.7	1395.3	1436.7	1433.7	1395.3
37.5°	857.6	867.1	892.7	926.2	980.2	1058.9	1134.3	1217.9	1294.3	1337.1	1324.4
40°	745.8	746.2	771.0	805.6	856.1	924.8	1006.9	1099.6	1184.7	1254.3	1267.7
42.5°	657.4	657.5	673.9	711.1	747.6	812.2	890.7	982.7	1082.3	1162.6	1198.3
45°	543.5	547.3	560.8	583.1	611.7	666.5	729.3	814.8	926.5	1021.7	1081.1
47.5°	460.3	465.8	474.4	492.6	515.4	551.9	603.8	680.6	771.5	876.2	960.8
50°	417.1	418.0	428.9	439.0	458.8	487.9	533.4	597.4	680.8	781.6	875.5
52.5°	380.0	379.9	386.4	399.3	415.3	438.0	474.8	533.1	607.0	697.3	794.2
55°	324.4	326.5	331.6	341.7	353.9	369.9	398.9	442.8	501.0	578.1	666.1
57.5°	282.1	283.2	287.2	291.4	302.7	314.3	336.1	366.5	415.6	478.7	560.8
60°	254.4	254.9	256.2	262.4	271.3	282.3	297.0	322.7	364.0	421.8	486.6
62.5°	227.5	228.2	230.2	234.8	241.7	249.2	264.7	285.3	319.5	368.8	427.3
65°	189.6	190.0	193.0	194.6	200.1	206.8	218.2	232.1	255.7	297.0	341.3
67.5°	158.4	158.4	158.6	160.9	164.6	169.1	175.9	187.0	204.9	230.2	269.2
70°	138.2	138.2	139.0	140.3	142.4	146.2	150.0	158.4	171.5	192.1	222.0
72.5°	119.3	119.6	120.5	120.7	121.8	124.9	127.8	133.2	142.8	158.4	182.6
75°	87.6	88.9	91.0	92.7	94.8	94.3	97.4	100.7	103.6	112.9	126.8
77.5°	65.2	64.6	64.8	66.2	66.5	66.9	69.0	71.6	73.8	78.2	83.2
80°	49.7	49.7	51.0	51.4	51.0	51.4	53.5	54.7	55.6	57.3	61.9
82.5°	37.5	38.3	37.9	38.3	38.5	38.9	40.7	41.0	41.8	42.5	44.4
85°	21.1	21.5	21.9	21.1	21.1	21.1	21.9	22.3	23.2	22.7	23.6
87.5°	14.6	14.1	14.3	14.3	14.5	13.9	13.9	14.3	13.3	13.3	12.9
90°	35.8	35.3	34.8	34.2	33.7	32.6	31.1	29.5	27.9	26.3	24.2
92.5°	53.0	52.7	52.4	52.0	51.7	51.1	50.1	49.2	48.2	47.3	45.8
95°	94.3	94.3	94.3	94.3	94.3	94.0	93.2	92.4	91.6	90.8	89.0
97.5°	147.9	147.9	147.9	147.9	147.9	147.4	146.5	145.5	144.5	143.5	141.4
100°	185.1	185.1	185.1	185.1	185.1	184.9	184.3	183.8	183.3	182.8	180.4
102.5°	227.2	227.0	226.8	226.6	226.3	225.9	225.1	224.3	223.6	222.9	220.7
105°	291.4	290.7	289.9	289.1	288.3	287.5	286.7	285.9	285.1	284.3	283.2
107.5°	354.0	354.1	354.2	354.2	354.3	353.9	353.2	352.4	351.6	350.9	350.8
110°	398.9	398.2	397.4	396.6	395.8	395.6	396.2	396.7	397.2	397.8	398.0



TEST NUMBER: P333072-927

CATALOG NUMBER: S124RDIW-S795D1560U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	444.8	444.7	444.5	444.3	444.2	444.2	444.3	444.3	444.5	444.6	445.0
115°	516.0	516.3	516.6	516.8	517.1	517.4	517.6	517.8	518.2	518.4	519.0
117.5°	583.8	584.4	584.9	585.4	586.0	586.7	587.6	588.5	589.4	590.3	590.7
120°	635.5	634.9	634.4	633.9	633.3	633.7	635.1	636.4	637.7	639.1	639.8
122.5°	678.5	679.5	680.4	681.4	682.3	683.3	684.1	685.0	686.0	686.8	687.2
125°	752.5	753.0	753.6	754.1	754.6	755.2	755.7	756.2	756.8	757.3	757.6
127.5°	821.1	821.5	822.0	822.4	822.8	823.2	823.8	824.3	824.8	825.4	825.9
130°	866.0	867.0	868.2	869.2	870.2	871.0	871.6	872.1	872.7	873.1	873.1
132.5°	913.8	914.2	914.7	915.0	915.4	915.9	916.5	917.0	917.6	918.1	918.3
135°	979.5	980.2	981.0	981.8	982.6	983.3	983.9	984.4	984.9	985.5	985.5
137.5°	1048.5	1048.4	1048.2	1048.1	1047.9	1048.1	1048.8	1049.6	1050.2	1050.9	1050.5
140°	1090.6	1090.8	1091.1	1091.4	1091.6	1091.9	1092.2	1092.4	1092.7	1093.0	1093.0
142.5°	1132.6	1132.7	1132.7	1132.7	1132.8	1132.9	1132.9	1133.0	1133.1	1133.1	1133.3
145°	1189.7	1190.5	1191.3	1192.1	1192.9	1193.4	1193.7	1194.0	1194.2	1194.5	1194.2
147.5°	1247.5	1247.8	1248.1	1248.3	1248.6	1248.8	1249.0	1249.3	1249.4	1249.7	1249.9
150°	1282.9	1283.2	1283.4	1283.7	1284.0	1284.0	1284.0	1284.0	1284.0	1284.0	1284.0
152.5°	1315.3	1316.1	1316.8	1317.4	1318.1	1318.1	1317.5	1316.8	1316.2	1315.6	1315.4
155°	1360.5	1361.6	1362.6	1363.7	1364.8	1364.8	1363.7	1362.6	1361.6	1360.5	1360.8
157.5°	1400.9	1401.8	1402.7	1403.6	1404.5	1404.5	1403.7	1403.0	1402.2	1401.4	1401.4
160°	1423.8	1425.1	1426.5	1427.8	1429.1	1429.4	1428.6	1427.8	1427.0	1426.2	1426.5
162.5°	1447.7	1449.1	1450.4	1451.7	1453.0	1452.9	1451.5	1450.1	1448.7	1447.2	1447.5
165°	1478.8	1479.8	1480.9	1481.9	1483.0	1482.7	1481.1	1479.6	1478.0	1476.4	1476.9
167.5°	1500.9	1502.6	1504.3	1505.9	1507.6	1507.6	1506.0	1504.4	1502.8	1501.3	1501.2
170°	1513.4	1515.3	1517.1	1519.0	1520.8	1521.0	1519.4	1517.8	1516.2	1514.6	1514.3
172.5°	1523.9	1525.7	1527.6	1529.5	1531.4	1531.4	1529.5	1527.8	1526.0	1524.2	1524.1
175°	1534.9	1536.8	1538.7	1540.5	1542.4	1542.4	1540.5	1538.7	1536.8	1534.9	1535.2
177.5°	1540.6	1542.4	1544.0	1545.7	1547.4	1547.5	1546.0	1544.6	1543.1	1541.6	1541.6
180°	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4



TEST NUMBER: P333072-927

CATALOG NUMBER: S124RDIW-S795D1560U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7
2.5°	1077.4	1072.7	1070.3	1064.9	1058.5	1055.1	1052.1	1047.7	1042.0	1035.9	1031.5
5°	1132.0	1122.0	1109.3	1094.2	1080.7	1067.6	1056.2	1044.9	1031.8	1018.3	1004.8
7.5°	1188.2	1168.3	1146.8	1122.0	1097.8	1075.8	1055.6	1036.2	1014.2	994.7	976.8
10°	1227.2	1200.3	1170.4	1138.8	1107.2	1079.8	1052.9	1028.4	1001.5	977.5	957.2
12.5°	1258.9	1227.2	1191.3	1151.9	1114.0	1080.9	1049.8	1018.0	987.3	961.2	934.3
15°	1311.5	1268.1	1219.7	1172.5	1123.2	1078.2	1036.4	999.3	964.4	927.7	902.1
17.5°	1347.7	1296.2	1237.3	1180.6	1122.4	1069.2	1021.1	976.9	936.6	899.1	868.5
20°	1369.3	1312.4	1247.1	1182.6	1117.3	1060.4	1008.6	959.7	918.1	877.6	846.0
22.5°	1381.4	1318.4	1247.1	1179.6	1111.9	1050.4	993.5	942.5	897.1	856.7	821.7
25°	1385.3	1317.9	1245.0	1167.4	1093.3	1028.0	969.0	913.9	863.2	822.8	785.8
27.5°	1379.9	1300.5	1225.8	1146.3	1069.8	1000.9	939.1	881.1	830.4	787.0	749.0
30°	1371.8	1286.7	1206.7	1124.0	1046.6	980.4	915.0	859.4	806.8	761.8	723.4
32.5°	1354.2	1269.9	1183.7	1099.2	1020.6	952.4	890.5	834.6	782.9	736.8	696.1
35°	1319.5	1234.1	1140.5	1053.7	976.6	905.8	847.7	793.8	744.5	695.1	652.2
37.5°	1273.8	1186.5	1093.4	998.3	921.1	854.4	801.0	750.4	702.3	657.3	609.7
40°	1230.7	1151.0	1054.9	960.6	881.4	816.9	767.6	721.7	673.3	628.6	581.0
42.5°	1178.4	1110.6	1013.5	918.8	840.6	778.5	732.6	687.7	643.6	600.3	550.6
45°	1091.2	1039.8	948.8	857.8	779.0	717.5	675.3	635.7	597.0	555.7	509.0
47.5°	991.3	956.5	877.9	784.7	711.9	656.5	615.8	583.4	550.6	509.4	468.3
50°	921.9	899.5	823.6	738.6	669.1	618.1	576.4	546.1	518.6	479.0	442.4
52.5°	847.7	835.8	771.7	690.4	623.2	573.2	537.6	510.3	482.6	449.7	415.4
55°	734.7	741.1	686.7	616.4	553.2	511.0	478.6	455.8	432.3	404.5	378.0
57.5°	619.3	642.4	605.9	544.2	484.9	446.0	421.6	402.4	382.6	359.6	336.9
60°	550.2	569.6	549.0	494.6	442.8	406.5	383.8	369.1	349.3	328.2	310.9
62.5°	482.8	503.6	491.3	447.4	399.3	368.1	348.1	334.4	319.6	301.3	283.3
65°	398.2	411.6	405.8	375.4	341.3	314.7	296.2	286.1	272.6	259.1	243.1
67.5°	304.9	331.0	327.6	311.4	281.9	261.2	249.1	240.1	227.8	217.9	206.9
70°	250.6	274.7	274.3	261.2	245.2	225.9	217.4	209.8	198.8	189.2	180.3
72.5°	205.2	227.2	230.4	220.5	209.5	194.8	186.7	181.5	170.9	164.2	157.1
75°	143.7	159.7	163.9	163.9	158.8	151.2	144.1	140.7	133.2	127.2	123.0
77.5°	94.2	104.3	110.9	112.4	113.2	110.7	104.7	102.3	96.6	94.4	90.4
80°	66.5	73.3	80.9	83.4	85.6	84.7	82.1	80.5	75.0	72.9	71.2
82.5°	46.0	49.7	55.9	61.5	60.9	63.1	60.9	59.6	55.5	54.7	53.0
85°	24.0	24.4	25.3	29.1	31.2	32.0	32.5	31.6	30.3	30.3	27.4
87.5°	12.5	11.7	12.0	11.5	11.2	12.0	12.4	12.2	11.7	11.3	10.9
90°	22.0	19.9	17.8	15.3	12.4	9.4	6.5	3.6	6.5	9.4	12.4
92.5°	44.4	42.9	41.4	39.0	35.6	32.2	28.9	25.6	28.9	32.2	35.6
95°	87.1	85.2	83.3	81.2	78.8	76.4	74.1	71.7	74.1	76.4	78.8
97.5°	139.2	137.0	134.9	132.8	130.9	129.0	127.1	125.2	127.1	129.0	130.9
100°	178.0	175.6	173.2	171.5	170.4	169.4	168.3	167.2	168.3	169.4	170.4
102.5°	218.6	216.3	214.2	212.9	212.5	212.1	211.6	211.2	211.6	212.1	212.5
105°	282.2	281.1	280.0	279.4	279.1	278.8	278.6	278.3	278.6	278.8	279.1
107.5°	350.6	350.5	350.3	350.1	349.7	349.4	349.1	348.8	349.1	349.4	349.7
110°	398.3	398.5	398.9	398.7	398.2	397.6	397.1	396.6	397.1	397.6	398.2



TEST NUMBER: P333072-927

CATALOG NUMBER: S124RDIW-S795D1560U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	445.5	446.0	446.5	446.7	446.6	446.5	446.4	446.2	446.4	446.5	446.6
115°	519.4	520.0	520.5	520.8	520.8	520.8	520.8	520.8	520.8	520.8	520.8
117.5°	591.0	591.4	591.8	591.9	591.7	591.4	591.2	591.0	591.2	591.4	591.7
120°	640.6	641.4	642.2	642.1	641.0	640.0	638.9	637.9	638.9	640.0	641.0
122.5°	687.5	687.9	688.3	688.2	687.9	687.5	687.0	686.6	687.0	687.5	687.9
125°	757.8	758.1	758.4	758.5	758.5	758.5	758.5	758.5	758.5	758.5	758.5
127.5°	826.2	826.6	827.1	826.9	826.1	825.3	824.5	823.7	824.5	825.3	826.1
130°	873.1	873.1	873.1	872.7	872.0	871.2	870.4	869.6	870.4	871.2	872.0
132.5°	918.5	918.7	918.9	918.8	918.1	917.6	917.0	916.4	917.0	917.6	918.1
135°	985.5	985.5	985.5	984.7	983.1	981.4	979.9	978.3	979.9	981.4	983.1
137.5°	1050.0	1049.6	1049.2	1048.6	1047.9	1047.1	1046.4	1045.7	1046.4	1047.1	1047.9
140°	1093.0	1093.0	1093.0	1092.7	1092.2	1091.6	1091.1	1090.6	1091.1	1091.6	1092.2
142.5°	1133.5	1133.7	1133.9	1133.8	1133.2	1132.7	1132.2	1131.6	1132.2	1132.7	1133.2
145°	1194.0	1193.7	1193.4	1192.8	1191.7	1190.6	1189.5	1188.5	1189.5	1190.6	1191.7
147.5°	1250.1	1250.3	1250.5	1250.0	1248.7	1247.4	1246.2	1244.9	1246.2	1247.4	1248.7
150°	1284.0	1284.0	1284.0	1283.6	1282.5	1281.4	1280.3	1279.3	1280.3	1281.4	1282.5
152.5°	1315.2	1314.9	1314.8	1314.3	1313.7	1313.0	1312.4	1311.8	1312.4	1313.0	1313.7
155°	1361.0	1361.3	1361.6	1361.7	1361.7	1361.7	1361.7	1361.7	1361.7	1361.7	1361.7
157.5°	1401.4	1401.5	1401.6	1401.8	1402.3	1402.8	1403.3	1403.7	1403.3	1402.8	1402.3
160°	1426.7	1427.0	1427.3	1427.5	1427.8	1428.1	1428.3	1428.6	1428.3	1428.1	1427.8
162.5°	1447.8	1448.0	1448.3	1448.7	1449.5	1450.2	1450.9	1451.5	1450.9	1450.2	1449.5
165°	1477.4	1478.0	1478.5	1479.2	1480.0	1480.7	1481.5	1482.3	1481.5	1480.7	1480.0
167.5°	1501.1	1501.1	1501.0	1501.6	1502.7	1503.8	1504.9	1506.0	1504.9	1503.8	1502.7
170°	1514.1	1513.8	1513.5	1514.1	1515.4	1516.7	1518.1	1519.4	1518.1	1516.7	1515.4
172.5°	1524.1	1524.0	1523.9	1524.5	1525.6	1526.7	1527.8	1528.9	1527.8	1526.7	1525.6
175°	1535.4	1535.7	1536.0	1536.8	1538.1	1539.4	1540.7	1542.1	1540.7	1539.4	1538.1
177.5°	1541.6	1541.6	1541.6	1542.1	1543.2	1544.3	1545.3	1546.3	1545.3	1544.3	1543.2
180°	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4



TEST NUMBER: P333072-927

CATALOG NUMBER: S124RDIW-S795D1560U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7
2.5°	1026.8	1023.4	1019.1	1014.0	1008.0	1002.6	1000.2	1002.2	1003.2	1000.5	1000.2
5°	995.5	985.0	976.6	963.9	953.9	945.4	939.5	937.0	937.9	931.1	929.4
7.5°	960.4	947.9	934.1	919.2	905.1	892.8	886.3	882.7	875.6	872.5	867.4
10°	937.9	921.0	907.5	889.8	873.8	859.0	851.9	846.0	838.8	835.4	828.3
12.5°	914.6	895.0	880.2	861.8	845.5	827.7	820.9	809.9	798.8	791.6	782.4
15°	881.8	858.3	840.1	818.2	798.8	778.6	760.5	740.2	732.7	716.7	707.4
17.5°	843.4	819.5	797.1	767.7	737.8	712.7	693.4	674.0	662.4	652.2	647.5
20°	818.2	796.3	765.1	730.9	697.7	669.9	654.3	641.7	629.0	621.9	616.8
22.5°	794.2	766.3	730.1	693.2	660.0	638.2	625.0	612.0	601.7	594.9	588.1
25°	754.2	717.5	679.1	637.0	614.3	595.3	581.0	570.5	564.1	555.3	551.9
27.5°	713.0	668.5	626.2	597.9	574.3	556.9	544.4	536.5	528.5	522.8	518.5
30°	681.3	636.2	598.3	571.3	547.3	533.0	522.8	513.6	507.2	502.6	499.2
32.5°	649.9	604.8	573.0	544.0	525.1	511.0	500.3	493.4	488.4	482.4	480.4
35°	604.6	564.6	536.8	510.6	491.2	478.6	470.2	463.0	458.8	457.1	455.8
37.5°	561.0	528.2	498.4	476.9	459.6	449.7	439.7	436.3	433.3	430.3	431.7
40°	533.4	502.6	476.1	453.4	439.4	428.5	422.6	418.4	415.8	415.8	415.8
42.5°	509.5	479.3	453.5	433.1	419.2	410.0	403.4	399.8	398.9	398.6	400.7
45°	472.3	444.5	418.4	401.5	389.7	380.4	376.7	373.7	373.7	375.4	375.8
47.5°	435.5	409.4	388.5	369.6	358.8	353.0	349.7	348.2	348.3	350.1	352.0
50°	412.9	387.2	366.5	349.7	339.6	334.1	331.1	330.3	331.1	331.1	334.1
52.5°	388.2	365.3	345.0	330.8	319.3	314.2	312.6	311.4	312.0	313.3	314.6
55°	352.2	331.6	312.2	298.7	290.3	286.9	283.1	283.5	282.7	283.5	283.5
57.5°	316.1	297.5	279.5	268.8	261.4	256.5	252.4	253.6	252.3	252.2	251.4
60°	292.8	272.6	258.3	248.6	240.1	235.9	232.1	233.0	231.7	230.8	229.2
62.5°	267.5	250.6	237.0	227.7	220.9	216.0	212.2	211.4	208.5	205.6	201.9
65°	230.8	217.0	204.8	195.9	189.6	185.8	182.8	180.3	174.0	167.2	163.9
67.5°	195.3	185.2	173.8	166.4	161.2	156.2	150.6	146.3	140.4	136.7	134.6
70°	172.3	162.6	153.0	145.8	140.3	135.7	129.4	126.4	122.2	120.5	118.4
72.5°	150.4	141.4	132.4	125.9	120.1	116.5	111.5	108.5	106.7	106.0	103.9
75°	117.2	110.0	103.2	97.4	92.7	90.2	88.1	86.0	85.1	81.3	79.2
77.5°	85.5	80.7	76.5	72.3	69.0	67.3	63.3	60.8	59.4	57.7	57.2
80°	66.5	63.2	59.0	56.5	51.8	50.1	48.5	48.0	47.6	47.2	46.7
82.5°	50.1	46.7	42.5	41.0	39.7	38.7	37.6	37.2	36.8	37.1	37.0
85°	25.3	23.6	23.6	23.2	22.7	22.3	21.9	21.9	21.5	21.9	21.5
87.5°	11.5	11.6	12.0	11.8	12.6	13.0	13.0	13.3	13.9	13.6	13.8
90°	15.3	17.8	19.9	22.0	24.2	26.3	27.9	29.5	31.1	32.6	33.7
92.5°	39.0	41.4	42.9	44.4	45.8	47.3	48.2	49.2	50.1	51.1	51.7
95°	81.2	83.3	85.2	87.1	89.0	90.8	91.6	92.4	93.2	94.0	94.3
97.5°	132.8	134.9	137.0	139.2	141.4	143.5	144.5	145.5	146.5	147.4	147.9
100°	171.5	173.2	175.6	178.0	180.4	182.8	183.3	183.8	184.3	184.9	185.1
102.5°	212.9	214.2	216.3	218.6	220.7	222.9	223.6	224.3	225.1	225.9	226.3
105°	279.4	280.0	281.1	282.2	283.2	284.3	285.1	285.9	286.7	287.5	288.3
107.5°	350.1	350.3	350.5	350.6	350.8	350.9	351.6	352.4	353.2	353.9	354.3
110°	398.7	398.9	398.5	398.3	398.0	397.8	397.2	396.7	396.2	395.6	395.8



TEST NUMBER: P333072-927

CATALOG NUMBER: S124RDIW-S795D1560U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	446.7	446.5	446.0	445.5	445.0	444.6	444.5	444.3	444.3	444.2	444.2
115°	520.8	520.5	520.0	519.4	519.0	518.4	518.2	517.8	517.6	517.4	517.1
117.5°	591.9	591.8	591.4	591.0	590.7	590.3	589.4	588.5	587.6	586.7	586.0
120°	642.1	642.2	641.4	640.6	639.8	639.1	637.7	636.4	635.1	633.7	633.3
122.5°	688.2	688.3	687.9	687.5	687.2	686.8	686.0	685.0	684.1	683.3	682.3
125°	758.5	758.4	758.1	757.8	757.6	757.3	756.8	756.2	755.7	755.2	754.6
127.5°	826.9	827.1	826.6	826.2	825.9	825.4	824.8	824.3	823.8	823.2	822.8
130°	872.7	873.1	873.1	873.1	873.1	873.1	872.7	872.1	871.6	871.0	870.2
132.5°	918.8	918.9	918.7	918.5	918.3	918.1	917.6	917.0	916.5	915.9	915.4
135°	984.7	985.5	985.5	985.5	985.5	985.5	984.9	984.4	983.9	983.3	982.6
137.5°	1048.6	1049.2	1049.6	1050.0	1050.5	1050.9	1050.2	1049.6	1048.8	1048.1	1047.9
140°	1092.7	1093.0	1093.0	1093.0	1093.0	1093.0	1092.7	1092.4	1092.2	1091.9	1091.6
142.5°	1133.8	1133.9	1133.7	1133.5	1133.3	1133.1	1133.1	1133.0	1132.9	1132.9	1132.8
145°	1192.8	1193.4	1193.7	1194.0	1194.2	1194.5	1194.2	1194.0	1193.7	1193.4	1192.9
147.5°	1250.0	1250.5	1250.3	1250.1	1249.9	1249.7	1249.4	1249.3	1249.0	1248.8	1248.6
150°	1283.6	1284.0	1284.0	1284.0	1284.0	1284.0	1284.0	1284.0	1284.0	1284.0	1284.0
152.5°	1314.3	1314.8	1314.9	1315.2	1315.4	1315.6	1316.2	1316.8	1317.5	1318.1	1318.1
155°	1361.7	1361.6	1361.3	1361.0	1360.8	1360.5	1361.6	1362.6	1363.7	1364.8	1364.8
157.5°	1401.8	1401.6	1401.5	1401.4	1401.4	1401.4	1402.2	1403.0	1403.7	1404.5	1404.5
160°	1427.5	1427.3	1427.0	1426.7	1426.5	1426.2	1427.0	1427.8	1428.6	1429.4	1429.1
162.5°	1448.7	1448.3	1448.0	1447.8	1447.5	1447.2	1448.7	1450.1	1451.5	1452.9	1453.0
165°	1479.2	1478.5	1478.0	1477.4	1476.9	1476.4	1478.0	1479.6	1481.1	1482.7	1483.0
167.5°	1501.6	1501.0	1501.1	1501.1	1501.2	1501.3	1502.8	1504.4	1506.0	1507.6	1507.6
170°	1514.1	1513.5	1513.8	1514.1	1514.3	1514.6	1516.2	1517.8	1519.4	1521.0	1520.8
172.5°	1524.5	1523.9	1524.0	1524.1	1524.1	1524.2	1526.0	1527.8	1529.5	1531.4	1531.4
175°	1536.8	1536.0	1535.7	1535.4	1535.2	1534.9	1536.8	1538.7	1540.5	1542.4	1542.4
177.5°	1542.1	1541.6	1541.6	1541.6	1541.6	1541.6	1543.1	1544.6	1546.0	1547.5	1547.4
180°	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4



TEST NUMBER: P333072-927

CATALOG NUMBER: S124RDIW-S795D1560U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7
2.5°	998.1	998.9	996.5	995.8	996.5	998.9	998.1	1000.2	1000.5	1003.2	1002.2
5°	926.1	925.2	923.1	923.5	923.1	925.2	926.1	929.4	931.1	937.9	937.0
7.5°	864.4	861.1	862.0	858.6	862.0	861.1	864.4	867.4	872.5	875.6	882.7
10°	826.6	822.0	818.2	814.8	818.2	822.0	826.6	828.3	835.4	838.8	846.0
12.5°	775.1	771.1	766.0	767.0	766.0	771.1	775.1	782.4	791.6	798.8	809.9
15°	701.9	695.6	685.5	686.7	685.5	695.6	701.9	707.4	716.7	732.7	740.2
17.5°	640.0	640.1	635.4	636.5	635.4	640.1	640.0	647.5	652.2	662.4	674.0
20°	607.9	605.0	605.4	604.2	605.4	605.0	607.9	616.8	621.9	629.0	641.7
22.5°	585.7	582.1	579.2	576.6	579.2	582.1	585.7	588.1	594.9	601.7	612.0
25°	548.1	545.6	541.8	541.0	541.8	545.6	548.1	551.9	555.3	564.1	570.5
27.5°	515.1	514.6	513.1	511.1	513.1	514.6	515.1	518.5	522.8	528.5	536.5
30°	495.9	495.0	494.2	492.9	494.2	495.0	495.9	499.2	502.6	507.2	513.6
32.5°	478.7	478.2	477.4	477.4	477.4	478.2	478.7	480.4	482.4	488.4	493.4
35°	454.2	453.8	452.9	452.5	452.9	453.8	454.2	455.8	457.1	458.8	463.0
37.5°	431.3	432.4	431.8	431.7	431.8	432.4	431.3	431.7	430.3	433.3	436.3
40°	415.4	415.8	416.7	416.3	416.7	415.8	415.4	415.8	415.8	415.8	418.4
42.5°	402.3	402.3	403.5	402.1	403.5	402.3	402.3	400.7	398.6	398.9	399.8
45°	378.7	381.3	380.9	380.9	380.9	381.3	378.7	375.8	375.4	373.7	373.7
47.5°	353.1	355.2	355.8	355.8	355.8	355.2	353.1	352.0	350.1	348.3	348.2
50°	336.2	335.3	336.6	336.2	336.6	335.3	336.2	334.1	331.1	331.1	330.3
52.5°	315.7	315.8	315.8	315.3	315.8	315.8	315.7	314.6	313.3	312.0	311.4
55°	284.0	284.4	283.5	284.0	283.5	284.4	284.0	283.5	283.5	282.7	283.5
57.5°	249.6	247.6	248.4	247.4	248.4	247.6	249.6	251.4	252.2	252.3	253.6
60°	225.0	221.6	220.8	219.1	220.8	221.6	225.0	229.2	230.8	231.7	233.0
62.5°	197.3	195.0	192.1	193.5	192.1	195.0	197.3	201.9	205.6	208.5	211.4
65°	160.5	158.8	157.6	159.2	157.6	158.8	160.5	163.9	167.2	174.0	180.3
67.5°	132.8	132.0	132.0	131.1	132.0	132.0	132.8	134.6	136.7	140.4	146.3
70°	118.4	117.2	117.2	116.3	117.2	117.2	118.4	118.4	120.5	122.2	126.4
72.5°	103.5	102.3	102.7	102.1	102.7	102.3	103.5	103.9	106.0	106.7	108.5
75°	76.7	74.5	74.5	75.0	74.5	74.5	76.7	79.2	81.3	85.1	86.0
77.5°	57.2	56.8	57.4	56.6	57.4	56.8	57.2	57.2	57.7	59.4	60.8
80°	46.7	46.3	45.9	47.2	45.9	46.3	46.7	46.7	47.2	47.6	48.0
82.5°	36.3	36.2	36.1	37.8	36.1	36.2	36.3	37.0	37.1	36.8	37.2
85°	21.9	21.1	21.9	21.1	21.9	21.1	21.9	21.5	21.9	21.5	21.9
87.5°	14.6	14.3	14.1	14.6	14.1	14.3	14.6	13.8	13.6	13.9	13.3
90°	34.2	34.8	35.3	35.8	35.3	34.8	34.2	33.7	32.6	31.1	29.5
92.5°	52.0	52.4	52.7	53.0	52.7	52.4	52.0	51.7	51.1	50.1	49.2
95°	94.3	94.3	94.3	94.3	94.3	94.3	94.3	94.3	94.0	93.2	92.4
97.5°	147.9	147.9	147.9	147.9	147.9	147.9	147.9	147.9	147.4	146.5	145.5
100°	185.1	185.1	185.1	185.1	185.1	185.1	185.1	185.1	184.9	184.3	183.8
102.5°	226.6	226.8	227.0	227.2	227.0	226.8	226.6	226.3	225.9	225.1	224.3
105°	289.1	289.9	290.7	291.4	290.7	289.9	289.1	288.3	287.5	286.7	285.9
107.5°	354.2	354.2	354.1	354.0	354.1	354.2	354.2	354.3	353.9	353.2	352.4
110°	396.6	397.4	398.2	398.9	398.2	397.4	396.6	395.8	395.6	396.2	396.7



TEST NUMBER: P333072-927

CATALOG NUMBER: S124RDIW-S795D1560U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	444.3	444.5	444.7	444.8	444.7	444.5	444.3	444.2	444.2	444.3	444.3
115°	516.8	516.6	516.3	516.0	516.3	516.6	516.8	517.1	517.4	517.6	517.8
117.5°	585.4	584.9	584.4	583.8	584.4	584.9	585.4	586.0	586.7	587.6	588.5
120°	633.9	634.4	634.9	635.5	634.9	634.4	633.9	633.3	633.7	635.1	636.4
122.5°	681.4	680.4	679.5	678.5	679.5	680.4	681.4	682.3	683.3	684.1	685.0
125°	754.1	753.6	753.0	752.5	753.0	753.6	754.1	754.6	755.2	755.7	756.2
127.5°	822.4	822.0	821.5	821.1	821.5	822.0	822.4	822.8	823.2	823.8	824.3
130°	869.2	868.2	867.0	866.0	867.0	868.2	869.2	870.2	871.0	871.6	872.1
132.5°	915.0	914.7	914.2	913.8	914.2	914.7	915.0	915.4	915.9	916.5	917.0
135°	981.8	981.0	980.2	979.5	980.2	981.0	981.8	982.6	983.3	983.9	984.4
137.5°	1048.1	1048.2	1048.4	1048.5	1048.4	1048.2	1048.1	1047.9	1048.1	1048.8	1049.6
140°	1091.4	1091.1	1090.8	1090.6	1090.8	1091.1	1091.4	1091.6	1091.9	1092.2	1092.4
142.5°	1132.7	1132.7	1132.7	1132.6	1132.7	1132.7	1132.7	1132.8	1132.9	1132.9	1133.0
145°	1192.1	1191.3	1190.5	1189.7	1190.5	1191.3	1192.1	1192.9	1193.4	1193.7	1194.0
147.5°	1248.3	1248.1	1247.8	1247.5	1247.8	1248.1	1248.3	1248.6	1248.8	1249.0	1249.3
150°	1283.7	1283.4	1283.2	1282.9	1283.2	1283.4	1283.7	1284.0	1284.0	1284.0	1284.0
152.5°	1317.4	1316.8	1316.1	1315.3	1316.1	1316.8	1317.4	1318.1	1318.1	1317.5	1316.8
155°	1363.7	1362.6	1361.6	1360.5	1361.6	1362.6	1363.7	1364.8	1364.8	1363.7	1362.6
157.5°	1403.6	1402.7	1401.8	1400.9	1401.8	1402.7	1403.6	1404.5	1404.5	1403.7	1403.0
160°	1427.8	1426.5	1425.1	1423.8	1425.1	1426.5	1427.8	1429.1	1429.4	1428.6	1427.8
162.5°	1451.7	1450.4	1449.1	1447.7	1449.1	1450.4	1451.7	1453.0	1452.9	1451.5	1450.1
165°	1481.9	1480.9	1479.8	1478.8	1479.8	1480.9	1481.9	1483.0	1482.7	1481.1	1479.6
167.5°	1505.9	1504.3	1502.6	1500.9	1502.6	1504.3	1505.9	1507.6	1507.6	1506.0	1504.4
170°	1519.0	1517.1	1515.3	1513.4	1515.3	1517.1	1519.0	1520.8	1521.0	1519.4	1517.8
172.5°	1529.5	1527.6	1525.7	1523.9	1525.7	1527.6	1529.5	1531.4	1531.4	1529.5	1527.8
175°	1540.5	1538.7	1536.8	1534.9	1536.8	1538.7	1540.5	1542.4	1542.4	1540.5	1538.7
177.5°	1545.7	1544.0	1542.4	1540.6	1542.4	1544.0	1545.7	1547.4	1547.5	1546.0	1544.6
180°	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4



TEST NUMBER: P333072-927

CATALOG NUMBER: S124RDIW-S795D1560U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7
2.5°	1000.2	1002.6	1008.0	1014.0	1019.1	1023.4	1026.8	1031.5	1035.9	1042.0	1047.7
5°	939.5	945.4	953.9	963.9	976.6	985.0	995.5	1004.8	1018.3	1031.8	1044.9
7.5°	886.3	892.8	905.1	919.2	934.1	947.9	960.4	976.8	994.7	1014.2	1036.2
10°	851.9	859.0	873.8	889.8	907.5	921.0	937.9	957.2	977.5	1001.5	1028.4
12.5°	820.9	827.7	845.5	861.8	880.2	895.0	914.6	934.3	961.2	987.3	1018.0
15°	760.5	778.6	798.8	818.2	840.1	858.3	881.8	902.1	927.7	964.4	999.3
17.5°	693.4	712.7	737.8	767.7	797.1	819.5	843.4	868.5	899.1	936.6	976.9
20°	654.3	669.9	697.7	730.9	765.1	796.3	818.2	846.0	877.6	918.1	959.7
22.5°	625.0	638.2	660.0	693.2	730.1	766.3	794.2	821.7	856.7	897.1	942.5
25°	581.0	595.3	614.3	637.0	679.1	717.5	754.2	785.8	822.8	863.2	913.9
27.5°	544.4	556.9	574.3	597.9	626.2	668.5	713.0	749.0	787.0	830.4	881.1
30°	522.8	533.0	547.3	571.3	598.3	636.2	681.3	723.4	761.8	806.8	859.4
32.5°	500.3	511.0	525.1	544.0	573.0	604.8	649.9	696.1	736.8	782.9	834.6
35°	470.2	478.6	491.2	510.6	536.8	564.6	604.6	652.2	695.1	744.5	793.8
37.5°	439.7	449.7	459.6	476.9	498.4	528.2	561.0	609.7	657.3	702.3	750.4
40°	422.6	428.5	439.4	453.4	476.1	502.6	533.4	581.0	628.6	673.3	721.7
42.5°	403.4	410.0	419.2	433.1	453.5	479.3	509.5	550.6	600.3	643.6	687.7
45°	376.7	380.4	389.7	401.5	418.4	444.5	472.3	509.0	555.7	597.0	635.7
47.5°	349.7	353.0	358.8	369.6	388.5	409.4	435.5	468.3	509.4	550.6	583.4
50°	331.1	334.1	339.6	349.7	366.5	387.2	412.9	442.4	479.0	518.6	546.1
52.5°	312.6	314.2	319.3	330.8	345.0	365.3	388.2	415.4	449.7	482.6	510.3
55°	283.1	286.9	290.3	298.7	312.2	331.6	352.2	378.0	404.5	432.3	455.8
57.5°	252.4	256.5	261.4	268.8	279.5	297.5	316.1	336.9	359.6	382.6	402.4
60°	232.1	235.9	240.1	248.6	258.3	272.6	292.8	310.9	328.2	349.3	369.1
62.5°	212.2	216.0	220.9	227.7	237.0	250.6	267.5	283.3	301.3	319.6	334.4
65°	182.8	185.8	189.6	195.9	204.8	217.0	230.8	243.1	259.1	272.6	286.1
67.5°	150.6	156.2	161.2	166.4	173.8	185.2	195.3	206.9	217.9	227.8	240.1
70°	129.4	135.7	140.3	145.8	153.0	162.6	172.3	180.3	189.2	198.8	209.8
72.5°	111.5	116.5	120.1	125.9	132.4	141.4	150.4	157.1	164.2	170.9	181.5
75°	88.1	90.2	92.7	97.4	103.2	110.0	117.2	123.0	127.2	133.2	140.7
77.5°	63.3	67.3	69.0	72.3	76.5	80.7	85.5	90.4	94.4	96.6	102.3
80°	48.5	50.1	51.8	56.5	59.0	63.2	66.5	71.2	72.9	75.0	80.5
82.5°	37.6	38.7	39.7	41.0	42.5	46.7	50.1	53.0	54.7	55.5	59.6
85°	21.9	22.3	22.7	23.2	23.6	23.6	25.3	27.4	30.3	30.3	31.6
87.5°	13.0	13.0	12.6	11.8	12.0	11.6	11.5	10.9	11.3	11.7	12.2
90°	27.9	26.3	24.2	22.0	19.9	17.8	15.3	12.4	9.4	6.5	3.6
92.5°	48.2	47.3	45.8	44.4	42.9	41.4	39.0	35.6	32.2	28.9	25.6
95°	91.6	90.8	89.0	87.1	85.2	83.3	81.2	78.8	76.4	74.1	71.7
97.5°	144.5	143.5	141.4	139.2	137.0	134.9	132.8	130.9	129.0	127.1	125.2
100°	183.3	182.8	180.4	178.0	175.6	173.2	171.5	170.4	169.4	168.3	167.2
102.5°	223.6	222.9	220.7	218.6	216.3	214.2	212.9	212.5	212.1	211.6	211.2
105°	285.1	284.3	283.2	282.2	281.1	280.0	279.4	279.1	278.8	278.6	278.3
107.5°	351.6	350.9	350.8	350.6	350.5	350.3	350.1	349.7	349.4	349.1	348.8
110°	397.2	397.8	398.0	398.3	398.5	398.9	398.7	398.2	397.6	397.1	396.6



TEST NUMBER: P333072-927

CATALOG NUMBER: S124RDIW-S795D1560U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	444.5	444.6	445.0	445.5	446.0	446.5	446.7	446.6	446.5	446.4	446.2
115°	518.2	518.4	519.0	519.4	520.0	520.5	520.8	520.8	520.8	520.8	520.8
117.5°	589.4	590.3	590.7	591.0	591.4	591.8	591.9	591.7	591.4	591.2	591.0
120°	637.7	639.1	639.8	640.6	641.4	642.2	642.1	641.0	640.0	638.9	637.9
122.5°	686.0	686.8	687.2	687.5	687.9	688.3	688.2	687.9	687.5	687.0	686.6
125°	756.8	757.3	757.6	757.8	758.1	758.4	758.5	758.5	758.5	758.5	758.5
127.5°	824.8	825.4	825.9	826.2	826.6	827.1	826.9	826.1	825.3	824.5	823.7
130°	872.7	873.1	873.1	873.1	873.1	873.1	872.7	872.0	871.2	870.4	869.6
132.5°	917.6	918.1	918.3	918.5	918.7	918.9	918.8	918.1	917.6	917.0	916.4
135°	984.9	985.5	985.5	985.5	985.5	985.5	984.7	983.1	981.4	979.9	978.3
137.5°	1050.2	1050.9	1050.5	1050.0	1049.6	1049.2	1048.6	1047.9	1047.1	1046.4	1045.7
140°	1092.7	1093.0	1093.0	1093.0	1093.0	1093.0	1092.7	1092.2	1091.6	1091.1	1090.6
142.5°	1133.1	1133.1	1133.3	1133.5	1133.7	1133.9	1133.8	1133.2	1132.7	1132.2	1131.6
145°	1194.2	1194.5	1194.2	1194.0	1193.7	1193.4	1192.8	1191.7	1190.6	1189.5	1188.5
147.5°	1249.4	1249.7	1249.9	1250.1	1250.3	1250.5	1250.0	1248.7	1247.4	1246.2	1244.9
150°	1284.0	1284.0	1284.0	1284.0	1284.0	1284.0	1283.6	1282.5	1281.4	1280.3	1279.3
152.5°	1316.2	1315.6	1315.4	1315.2	1314.9	1314.8	1314.3	1313.7	1313.0	1312.4	1311.8
155°	1361.6	1360.5	1360.8	1361.0	1361.3	1361.6	1361.7	1361.7	1361.7	1361.7	1361.7
157.5°	1402.2	1401.4	1401.4	1401.4	1401.5	1401.6	1401.8	1402.3	1402.8	1403.3	1403.7
160°	1427.0	1426.2	1426.5	1426.7	1427.0	1427.3	1427.5	1427.8	1428.1	1428.3	1428.6
162.5°	1448.7	1447.2	1447.5	1447.8	1448.0	1448.3	1448.7	1449.5	1450.2	1450.9	1451.5
165°	1478.0	1476.4	1476.9	1477.4	1478.0	1478.5	1479.2	1480.0	1480.7	1481.5	1482.3
167.5°	1502.8	1501.3	1501.2	1501.1	1501.1	1501.0	1501.6	1502.7	1503.8	1504.9	1506.0
170°	1516.2	1514.6	1514.3	1514.1	1513.8	1513.5	1514.1	1515.4	1516.7	1518.1	1519.4
172.5°	1526.0	1524.2	1524.1	1524.1	1524.0	1523.9	1524.5	1525.6	1526.7	1527.8	1528.9
175°	1536.8	1534.9	1535.2	1535.4	1535.7	1536.0	1536.8	1538.1	1539.4	1540.7	1542.1
177.5°	1543.1	1541.6	1541.6	1541.6	1541.6	1541.6	1542.1	1543.2	1544.3	1545.3	1546.3
180°	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4



TEST NUMBER: P333072-927

CATALOG NUMBER: S124RDIW-S795D1560U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7
2.5°	1052.1	1055.1	1058.5	1064.9	1070.3	1072.7	1077.4	1080.8	1079.7	1084.4	1092.6
5°	1056.2	1067.6	1080.7	1094.2	1109.3	1122.0	1132.0	1142.2	1150.2	1159.8	1174.2
7.5°	1055.6	1075.8	1097.8	1122.0	1146.8	1168.3	1188.2	1208.4	1226.4	1246.0	1271.7
10°	1052.9	1079.8	1107.2	1138.8	1170.4	1200.3	1227.2	1252.6	1276.6	1302.3	1334.7
12.5°	1049.8	1080.9	1114.0	1151.9	1191.3	1227.2	1258.9	1295.4	1325.5	1358.6	1396.1
15°	1036.4	1078.2	1123.2	1172.5	1219.7	1268.1	1311.5	1356.2	1397.9	1437.5	1484.7
17.5°	1021.1	1069.2	1122.4	1180.6	1237.3	1296.2	1347.7	1404.0	1446.6	1499.8	1543.6
20°	1008.6	1060.4	1117.3	1182.6	1247.1	1312.4	1369.3	1426.6	1474.6	1528.1	1583.7
22.5°	993.5	1050.4	1111.9	1179.6	1247.1	1318.4	1381.4	1438.4	1497.9	1558.1	1615.4
25°	969.0	1028.0	1093.3	1167.4	1245.0	1317.9	1385.3	1456.0	1520.1	1585.4	1636.8
27.5°	939.1	1000.9	1069.8	1146.3	1225.8	1300.5	1379.9	1455.3	1519.7	1582.6	1627.5
30°	915.0	980.4	1046.6	1124.0	1206.7	1286.7	1371.8	1447.2	1515.0	1571.5	1596.8
32.5°	890.5	952.4	1020.6	1099.2	1183.7	1269.9	1354.2	1431.4	1494.1	1528.0	1528.7
35°	847.7	905.8	976.6	1053.7	1140.5	1234.1	1319.5	1395.3	1433.7	1436.7	1395.3
37.5°	801.0	854.4	921.1	998.3	1093.4	1186.5	1273.8	1324.4	1337.1	1294.3	1217.9
40°	767.6	816.9	881.4	960.6	1054.9	1151.0	1230.7	1267.7	1254.3	1184.7	1099.6
42.5°	732.6	778.5	840.6	918.8	1013.5	1110.6	1178.4	1198.3	1162.6	1082.3	982.7
45°	675.3	717.5	779.0	857.8	948.8	1039.8	1091.2	1081.1	1021.7	926.5	814.8
47.5°	615.8	656.5	711.9	784.7	877.9	956.5	991.3	960.8	876.2	771.5	680.6
50°	576.4	618.1	669.1	738.6	823.6	899.5	921.9	875.5	781.6	680.8	597.4
52.5°	537.6	573.2	623.2	690.4	771.7	835.8	847.7	794.2	697.3	607.0	533.1
55°	478.6	511.0	553.2	616.4	686.7	741.1	734.7	666.1	578.1	501.0	442.8
57.5°	421.6	446.0	484.9	544.2	605.9	642.4	619.3	560.8	478.7	415.6	366.5
60°	383.8	406.5	442.8	494.6	549.0	569.6	550.2	486.6	421.8	364.0	322.7
62.5°	348.1	368.1	399.3	447.4	491.3	503.6	482.8	427.3	368.8	319.5	285.3
65°	296.2	314.7	341.3	375.4	405.8	411.6	398.2	341.3	297.0	255.7	232.1
67.5°	249.1	261.2	281.9	311.4	327.6	331.0	304.9	269.2	230.2	204.9	187.0
70°	217.4	225.9	245.2	261.2	274.3	274.7	250.6	222.0	192.1	171.5	158.4
72.5°	186.7	194.8	209.5	220.5	230.4	227.2	205.2	182.6	158.4	142.8	133.2
75°	144.1	151.2	158.8	163.9	163.9	159.7	143.7	126.8	112.9	103.6	100.7
77.5°	104.7	110.7	113.2	112.4	110.9	104.3	94.2	83.2	78.2	73.8	71.6
80°	82.1	84.7	85.6	83.4	80.9	73.3	66.5	61.9	57.3	55.6	54.7
82.5°	60.9	63.1	60.9	61.5	55.9	49.7	46.0	44.4	42.5	41.8	41.0
85°	32.5	32.0	31.2	29.1	25.3	24.4	24.0	23.6	22.7	23.2	22.3
87.5°	12.4	12.0	11.2	11.5	12.0	11.7	12.5	12.9	13.3	13.3	14.3
90°	6.5	9.4	12.4	15.3	17.8	19.9	22.0	24.2	26.3	27.9	29.5
92.5°	28.9	32.2	35.6	39.0	41.4	42.9	44.4	45.8	47.3	48.2	49.2
95°	74.1	76.4	78.8	81.2	83.3	85.2	87.1	89.0	90.8	91.6	92.4
97.5°	127.1	129.0	130.9	132.8	134.9	137.0	139.2	141.4	143.5	144.5	145.5
100°	168.3	169.4	170.4	171.5	173.2	175.6	178.0	180.4	182.8	183.3	183.8
102.5°	211.6	212.1	212.5	212.9	214.2	216.3	218.6	220.7	222.9	223.6	224.3
105°	278.6	278.8	279.1	279.4	280.0	281.1	282.2	283.2	284.3	285.1	285.9
107.5°	349.1	349.4	349.7	350.1	350.3	350.5	350.6	350.8	350.9	351.6	352.4
110°	397.1	397.6	398.2	398.7	398.9	398.5	398.3	398.0	397.8	397.2	396.7



TEST NUMBER: P333072-927

CATALOG NUMBER: S124RDIW-S795D1560U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	446.4	446.5	446.6	446.7	446.5	446.0	445.5	445.0	444.6	444.5	444.3
115°	520.8	520.8	520.8	520.8	520.5	520.0	519.4	519.0	518.4	518.2	517.8
117.5°	591.2	591.4	591.7	591.9	591.8	591.4	591.0	590.7	590.3	589.4	588.5
120°	638.9	640.0	641.0	642.1	642.2	641.4	640.6	639.8	639.1	637.7	636.4
122.5°	687.0	687.5	687.9	688.2	688.3	687.9	687.5	687.2	686.8	686.0	685.0
125°	758.5	758.5	758.5	758.5	758.4	758.1	757.8	757.6	757.3	756.8	756.2
127.5°	824.5	825.3	826.1	826.9	827.1	826.6	826.2	825.9	825.4	824.8	824.3
130°	870.4	871.2	872.0	872.7	873.1	873.1	873.1	873.1	873.1	872.7	872.1
132.5°	917.0	917.6	918.1	918.8	918.9	918.7	918.5	918.3	918.1	917.6	917.0
135°	979.9	981.4	983.1	984.7	985.5	985.5	985.5	985.5	985.5	984.9	984.4
137.5°	1046.4	1047.1	1047.9	1048.6	1049.2	1049.6	1050.0	1050.5	1050.9	1050.2	1049.6
140°	1091.1	1091.6	1092.2	1092.7	1093.0	1093.0	1093.0	1093.0	1093.0	1092.7	1092.4
142.5°	1132.2	1132.7	1133.2	1133.8	1133.9	1133.7	1133.5	1133.3	1133.1	1133.1	1133.0
145°	1189.5	1190.6	1191.7	1192.8	1193.4	1193.7	1194.0	1194.2	1194.5	1194.2	1194.0
147.5°	1246.2	1247.4	1248.7	1250.0	1250.5	1250.3	1250.1	1249.9	1249.7	1249.4	1249.3
150°	1280.3	1281.4	1282.5	1283.6	1284.0	1284.0	1284.0	1284.0	1284.0	1284.0	1284.0
152.5°	1312.4	1313.0	1313.7	1314.3	1314.8	1314.9	1315.2	1315.4	1315.6	1316.2	1316.8
155°	1361.7	1361.7	1361.7	1361.7	1361.6	1361.3	1361.0	1360.8	1360.5	1361.6	1362.6
157.5°	1403.3	1402.8	1402.3	1401.8	1401.6	1401.5	1401.4	1401.4	1401.4	1402.2	1403.0
160°	1428.3	1428.1	1427.8	1427.5	1427.3	1427.0	1426.7	1426.5	1426.2	1427.0	1427.8
162.5°	1450.9	1450.2	1449.5	1448.7	1448.3	1448.0	1447.8	1447.5	1447.2	1448.7	1450.1
165°	1481.5	1480.7	1480.0	1479.2	1478.5	1478.0	1477.4	1476.9	1476.4	1478.0	1479.6
167.5°	1504.9	1503.8	1502.7	1501.6	1501.0	1501.1	1501.1	1501.2	1501.3	1502.8	1504.4
170°	1518.1	1516.7	1515.4	1514.1	1513.5	1513.8	1514.1	1514.3	1514.6	1516.2	1517.8
172.5°	1527.8	1526.7	1525.6	1524.5	1523.9	1524.0	1524.1	1524.1	1524.2	1526.0	1527.8
175°	1540.7	1539.4	1538.1	1536.8	1536.0	1535.7	1535.4	1535.2	1534.9	1536.8	1538.7
177.5°	1545.3	1544.3	1543.2	1542.1	1541.6	1541.6	1541.6	1541.6	1541.6	1543.1	1544.6
180°	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4



TEST NUMBER: P333072-927

CATALOG NUMBER: S124RDIW-S795D1560U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7
2.5°	1096.9	1098.3	1099.3	1102.6	1103.0	1106.0	1103.0
5°	1187.6	1193.6	1202.8	1212.1	1213.0	1218.9	1208.3
7.5°	1289.4	1303.1	1311.6	1326.6	1332.5	1336.3	1330.2
10°	1359.5	1372.2	1394.6	1405.5	1416.4	1418.2	1413.1
12.5°	1427.4	1447.4	1465.0	1485.7	1485.2	1500.1	1494.6
15°	1517.6	1538.2	1562.7	1585.8	1594.3	1594.3	1601.0
17.5°	1581.9	1619.8	1645.0	1663.3	1683.1	1686.6	1684.3
20°	1625.4	1666.3	1693.3	1716.8	1730.4	1734.1	1734.1
22.5°	1657.8	1692.6	1718.9	1740.1	1751.2	1755.7	1754.4
25°	1680.2	1710.1	1726.1	1732.4	1735.4	1734.6	1726.6
27.5°	1649.5	1648.1	1638.1	1618.7	1604.1	1595.2	1585.2
30°	1590.9	1569.0	1543.7	1515.8	1480.0	1452.7	1444.2
32.5°	1503.6	1454.4	1411.6	1365.2	1326.7	1299.3	1287.9
35°	1334.7	1256.8	1193.2	1137.6	1097.1	1071.8	1063.4
37.5°	1134.3	1058.9	980.2	926.2	892.7	867.1	857.6
40°	1006.9	924.8	856.1	805.6	771.0	746.2	745.8
42.5°	890.7	812.2	747.6	711.1	673.9	657.5	657.4
45°	729.3	666.5	611.7	583.1	560.8	547.3	543.5
47.5°	603.8	551.9	515.4	492.6	474.4	465.8	460.3
50°	533.4	487.9	458.8	439.0	428.9	418.0	417.1
52.5°	474.8	438.0	415.3	399.3	386.4	379.9	380.0
55°	398.9	369.9	353.9	341.7	331.6	326.5	324.4
57.5°	336.1	314.3	302.7	291.4	287.2	283.2	282.1
60°	297.0	282.3	271.3	262.4	256.2	254.9	254.4
62.5°	264.7	249.2	241.7	234.8	230.2	228.2	227.5
65°	218.2	206.8	200.1	194.6	193.0	190.0	189.6
67.5°	175.9	169.1	164.6	160.9	158.6	158.4	158.4
70°	150.0	146.2	142.4	140.3	139.0	138.2	138.2
72.5°	127.8	124.9	121.8	120.7	120.5	119.6	119.3
75°	97.4	94.3	94.8	92.7	91.0	88.9	87.6
77.5°	69.0	66.9	66.5	66.2	64.8	64.6	65.2
80°	53.5	51.4	51.0	51.4	51.0	49.7	49.7
82.5°	40.7	38.9	38.5	38.3	37.9	38.3	37.5
85°	21.9	21.1	21.1	21.1	21.9	21.5	21.1
87.5°	13.9	13.9	14.5	14.3	14.3	14.1	14.6
90°	31.1	32.6	33.7	34.2	34.8	35.3	35.8
92.5°	50.1	51.1	51.7	52.0	52.4	52.7	53.0
95°	93.2	94.0	94.3	94.3	94.3	94.3	94.3
97.5°	146.5	147.4	147.9	147.9	147.9	147.9	147.9
100°	184.3	184.9	185.1	185.1	185.1	185.1	185.1
102.5°	225.1	225.9	226.3	226.6	226.8	227.0	227.2
105°	286.7	287.5	288.3	289.1	289.9	290.7	291.4
107.5°	353.2	353.9	354.3	354.2	354.2	354.1	354.0
110°	396.2	395.6	395.8	396.6	397.4	398.2	398.9



TEST NUMBER: P333072-927

CATALOG NUMBER: S124RDIW-S795D1560U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	444.3	444.2	444.2	444.3	444.5	444.7	444.8
115°	517.6	517.4	517.1	516.8	516.6	516.3	516.0
117.5°	587.6	586.7	586.0	585.4	584.9	584.4	583.8
120°	635.1	633.7	633.3	633.9	634.4	634.9	635.5
122.5°	684.1	683.3	682.3	681.4	680.4	679.5	678.5
125°	755.7	755.2	754.6	754.1	753.6	753.0	752.5
127.5°	823.8	823.2	822.8	822.4	822.0	821.5	821.1
130°	871.6	871.0	870.2	869.2	868.2	867.0	866.0
132.5°	916.5	915.9	915.4	915.0	914.7	914.2	913.8
135°	983.9	983.3	982.6	981.8	981.0	980.2	979.5
137.5°	1048.8	1048.1	1047.9	1048.1	1048.2	1048.4	1048.5
140°	1092.2	1091.9	1091.6	1091.4	1091.1	1090.8	1090.6
142.5°	1132.9	1132.9	1132.8	1132.7	1132.7	1132.7	1132.6
145°	1193.7	1193.4	1192.9	1192.1	1191.3	1190.5	1189.7
147.5°	1249.0	1248.8	1248.6	1248.3	1248.1	1247.8	1247.5
150°	1284.0	1284.0	1284.0	1283.7	1283.4	1283.2	1282.9
152.5°	1317.5	1318.1	1318.1	1317.4	1316.8	1316.1	1315.3
155°	1363.7	1364.8	1364.8	1363.7	1362.6	1361.6	1360.5
157.5°	1403.7	1404.5	1404.5	1403.6	1402.7	1401.8	1400.9
160°	1428.6	1429.4	1429.1	1427.8	1426.5	1425.1	1423.8
162.5°	1451.5	1452.9	1453.0	1451.7	1450.4	1449.1	1447.7
165°	1481.1	1482.7	1483.0	1481.9	1480.9	1479.8	1478.8
167.5°	1506.0	1507.6	1507.6	1505.9	1504.3	1502.6	1500.9
170°	1519.4	1521.0	1520.8	1519.0	1517.1	1515.3	1513.4
172.5°	1529.5	1531.4	1531.4	1529.5	1527.6	1525.7	1523.9
175°	1540.5	1542.4	1542.4	1540.5	1538.7	1536.8	1534.9
177.5°	1546.0	1547.5	1547.4	1545.7	1544.0	1542.4	1540.6
180°	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4

(END OF REPORT)