

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333055-927

Luminaire Tested: **S124RDIW-S795D470U927-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333055-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S795D470U927-4F0-1E-UDD-A
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 795 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 470 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4129.5 lumens
Efficiency: N/A
Efficacy: 109.5 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 37.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333055-927

CATALOG NUMBER: S124RDIW-S795D470U927-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P333055-927

CATALOG NUMBER: S124RDIW-S795D470U927-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	104	104	104	104	91	91	91	80	80	80	69	69	69	64
1	102	97	94	90	95	92	88	85	81	78	76	71	69	68	62	61	60	55
2	93	86	80	75	87	81	76	71	72	68	64	63	60	57	55	53	51	47
3	85	76	69	63	80	72	65	60	64	59	55	56	52	49	49	47	44	41
4	78	68	60	54	73	64	57	51	57	51	47	51	46	43	45	41	38	35
5	72	61	52	47	68	57	50	45	51	45	41	46	41	37	40	37	34	31
6	67	55	46	41	62	52	44	39	46	40	36	41	37	33	37	33	30	27
7	62	49	42	36	58	47	40	35	42	36	32	38	33	29	34	30	27	24
8	57	45	37	32	54	43	36	31	39	33	29	35	30	26	31	27	24	22
9	54	41	34	29	50	39	32	28	36	30	26	32	27	24	29	25	22	20
10	50	38	31	26	47	36	30	25	33	27	23	30	25	22	27	23	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	8442	8442	8442	8442
5°	9792	8468	7484	8468
10°	11584	8430	6679	8430
15°	13381	8352	5739	8352
20°	14898	8245	5191	8245
25°	15380	8141	4819	8141
30°	13463	8011	4595	8011
35°	10480	7823	4459	7823
40°	7860	7606	4387	7606
45°	6205	7258	4349	7258
50°	5238	6859	4222	6859
55°	4566	6415	3997	6415
60°	4108	5959	3538	5959
65°	3622	5465	3041	5465
70°	3262	4952	2745	4952
75°	2732	4389	2339	4389
80°	2311	3742	2194	3742
85°	1954	2927	1954	2927



TEST NUMBER: P333055-927

CATALOG NUMBER: S124RDIW-S795D470U927-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	101.3	2.5
10°-20°	305.6	7.4
20°-30°	478.0	11.6
30°-40°	531.4	12.9
40°-50°	471.5	11.4
50°-60°	367.4	8.9
60°-70°	240.5	5.8
70°-80°	118.3	2.9
80°-90°	30.6	0.7
90°-100°	16.4	0.4
100°-110°	104.7	2.5
110°-120°	200.2	4.8
120°-130°	254.2	6.2
130°-140°	272.0	6.6
140°-150°	254.3	6.2
150°-160°	205.1	5.0
160°-170°	132.3	3.2
170°-180°	45.6	1.1
0°-30°	885.0	21.4
0°-40°	1416.4	34.3
0°-60°	2255.3	54.6
0°-90°	2644.7	64.0
90°-120°	321.3	7.8
90°-150°	1101.8	26.7
90°-180°	1485.0	36.0
0°-180°	4129.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1046	1046	1046	1046	1046	
5°	1208	1045	924	1045	1208	122
15°	1601	999	687	999	1601	455
25°	1727	914	541	914	1727	766
35°	1063	794	452	794	1063	667
45°	544	636	381	636	544	430
55°	324	456	284	456	324	295
65°	190	286	159	286	190	191
75°	88	141	75	141	88	96
85°	21	32	21	32	21	24
90°	11	1	11	1	11	6
95°	10	20	10	20	10	8
105°	102	108	102	108	102	89
115°	203	202	203	202	203	201
125°	286	284	286	284	286	255
135°	354	352	354	352	354	273
145°	408	406	408	406	408	255
155°	444	445	444	445	444	205
165°	467	469	467	469	467	132
175°	477	480	477	480	477	45
180°	480	480	480	480	480	



TEST NUMBER: P333055-927

CATALOG NUMBER: S124RDIW-S795D470U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7
2.5°	1103.0	1106.0	1103.0	1102.6	1099.3	1098.3	1096.9	1092.6	1084.4	1079.7	1080.8
5°	1208.3	1218.9	1213.0	1212.1	1202.8	1193.6	1187.6	1174.2	1159.8	1150.2	1142.2
7.5°	1330.2	1336.3	1332.5	1326.6	1311.6	1303.1	1289.4	1271.7	1246.0	1226.4	1208.4
10°	1413.1	1418.2	1416.4	1405.5	1394.6	1372.2	1359.5	1334.7	1302.3	1276.6	1252.6
12.5°	1494.6	1500.1	1485.2	1485.7	1465.0	1447.4	1427.4	1396.1	1358.6	1325.5	1295.4
15°	1601.0	1594.3	1594.3	1585.8	1562.7	1538.2	1517.6	1484.7	1437.5	1397.9	1356.2
17.5°	1684.3	1686.6	1683.1	1663.3	1645.0	1619.8	1581.9	1543.6	1499.8	1446.6	1404.0
20°	1734.1	1734.1	1730.4	1716.8	1693.3	1666.3	1625.4	1583.7	1528.1	1474.6	1426.6
22.5°	1754.4	1755.7	1751.2	1740.1	1718.9	1692.6	1657.8	1615.4	1558.1	1497.9	1438.4
25°	1726.6	1734.6	1735.4	1732.4	1726.1	1710.1	1680.2	1636.8	1585.4	1520.1	1456.0
27.5°	1585.2	1595.2	1604.1	1618.7	1638.1	1648.1	1649.5	1627.5	1582.6	1519.7	1455.3
30°	1444.2	1452.7	1480.0	1515.8	1543.7	1569.0	1590.9	1596.8	1571.5	1515.0	1447.2
32.5°	1287.9	1299.3	1326.7	1365.2	1411.6	1454.4	1503.6	1528.7	1528.0	1494.1	1431.4
35°	1063.4	1071.8	1097.1	1137.6	1193.2	1256.8	1334.7	1395.3	1436.7	1433.7	1395.3
37.5°	857.6	867.1	892.7	926.2	980.2	1058.9	1134.3	1217.9	1294.3	1337.1	1324.4
40°	745.8	746.2	771.0	805.6	856.1	924.8	1006.9	1099.6	1184.7	1254.3	1267.7
42.5°	657.4	657.5	673.9	711.1	747.6	812.2	890.7	982.7	1082.3	1162.6	1198.3
45°	543.5	547.3	560.8	583.1	611.7	666.5	729.3	814.8	926.5	1021.7	1081.1
47.5°	460.3	465.8	474.4	492.6	515.4	551.9	603.8	680.6	771.5	876.2	960.8
50°	417.1	418.0	428.9	439.0	458.8	487.9	533.4	597.4	680.8	781.6	875.5
52.5°	380.0	379.9	386.4	399.3	415.3	438.0	474.8	533.1	607.0	697.3	794.2
55°	324.4	326.5	331.6	341.7	353.9	369.9	398.9	442.8	501.0	578.1	666.1
57.5°	282.1	283.2	287.2	291.4	302.7	314.3	336.1	366.5	415.6	478.7	560.8
60°	254.4	254.9	256.2	262.4	271.3	282.3	297.0	322.7	364.0	421.8	486.6
62.5°	227.5	228.2	230.2	234.8	241.7	249.2	264.7	285.3	319.5	368.8	427.3
65°	189.6	190.0	193.0	194.6	200.1	206.8	218.2	232.1	255.7	297.0	341.3
67.5°	158.4	158.4	158.6	160.9	164.6	169.1	175.9	187.0	204.9	230.2	269.2
70°	138.2	138.2	139.0	140.3	142.4	146.2	150.0	158.4	171.5	192.1	222.0
72.5°	119.3	119.6	120.5	120.7	121.8	124.9	127.8	133.2	142.8	158.4	182.6
75°	87.6	88.9	91.0	92.7	94.8	94.3	97.4	100.7	103.6	112.9	126.8
77.5°	65.2	64.6	64.8	66.2	66.5	66.9	69.0	71.6	73.8	78.2	83.2
80°	49.7	49.7	51.0	51.4	51.0	51.4	53.5	54.7	55.6	57.3	61.9
82.5°	37.5	38.3	37.9	38.3	38.5	38.9	40.7	41.0	41.8	42.5	44.4
85°	21.1	21.5	21.9	21.1	21.1	21.1	21.9	22.3	23.2	22.7	23.6
87.5°	9.6	9.2	9.5	9.5	9.7	9.3	9.6	10.2	9.4	9.7	9.5
90°	10.8	10.6	10.5	10.3	10.1	9.8	9.3	8.9	8.4	7.9	7.3
92.5°	9.9	9.9	9.8	9.8	9.7	9.5	9.0	8.6	8.1	7.6	7.0
95°	10.4	10.3	10.2	10.1	10.1	9.8	9.3	8.9	8.4	7.9	7.8
97.5°	10.1	10.0	9.9	9.8	9.7	9.7	9.6	9.6	9.5	9.5	18.4
100°	10.1	10.0	9.9	9.8	9.7	10.4	11.7	13.1	14.4	15.8	26.8
102.5°	10.4	10.3	10.3	10.3	10.3	17.6	32.2	46.8	61.5	76.1	77.6
105°	102.3	105.2	108.1	110.9	113.8	114.9	114.2	113.4	112.7	112.0	111.6
107.5°	142.6	142.3	142.0	141.7	141.4	141.1	140.7	140.4	140.0	139.7	139.1
110°	160.1	159.9	159.6	159.4	159.1	159.0	158.8	158.7	158.5	158.4	157.9



TEST NUMBER: P333055-927

CATALOG NUMBER: S124RDIW-S795D470U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	177.6	177.4	177.1	176.7	176.4	176.3	176.3	176.3	176.4	176.4	176.2
115°	203.2	203.2	203.2	203.2	203.2	203.1	203.0	202.8	202.6	202.5	202.6
117.5°	229.2	229.3	229.3	229.3	229.3	229.3	229.4	229.4	229.4	229.5	229.3
120°	245.6	245.7	245.9	246.1	246.2	246.2	246.1	245.9	245.7	245.6	245.7
122.5°	261.7	261.8	262.0	262.1	262.3	262.3	262.2	262.1	262.1	262.0	261.8
125°	285.7	285.7	285.6	285.5	285.4	285.3	285.0	284.8	284.6	284.3	284.5
127.5°	307.0	307.0	307.0	307.1	307.2	307.3	307.3	307.4	307.4	307.4	307.1
130°	321.3	321.3	321.3	321.3	321.3	321.3	321.2	321.2	321.1	321.0	320.8
132.5°	334.5	334.6	334.7	334.7	334.8	334.8	334.7	334.6	334.5	334.5	334.1
135°	354.3	354.2	354.0	353.9	353.7	353.6	353.4	353.2	353.1	352.9	352.6
137.5°	371.3	371.4	371.4	371.5	371.5	371.5	371.2	371.1	370.9	370.7	370.3
140°	383.1	383.0	382.9	382.9	382.8	382.6	382.4	382.1	381.9	381.7	381.5
142.5°	392.8	392.8	392.8	392.8	392.8	392.7	392.5	392.3	392.1	392.0	391.9
145°	407.8	407.7	407.5	407.3	407.2	407.1	407.0	406.9	406.9	406.8	406.8
147.5°	420.3	420.2	420.1	420.0	419.9	419.9	419.8	419.8	419.7	419.6	419.7
150°	428.3	428.3	428.2	428.1	428.0	427.9	427.9	427.9	427.9	427.9	428.0
152.5°	435.2	435.2	435.3	435.4	435.4	435.4	435.2	435.1	435.0	434.8	435.0
155°	444.5	444.7	445.0	445.2	445.4	445.4	445.0	444.7	444.4	444.1	444.3
157.5°	452.3	452.7	453.0	453.4	453.8	453.8	453.4	453.0	452.7	452.3	452.5
160°	457.4	457.9	458.4	458.8	459.3	459.3	458.8	458.4	457.9	457.4	457.5
162.5°	461.4	461.9	462.5	463.0	463.6	463.6	463.1	462.6	462.2	461.7	461.8
165°	467.1	467.8	468.5	469.2	469.9	470.0	469.4	468.7	468.1	467.5	467.5
167.5°	471.3	472.1	472.9	473.7	474.5	474.6	473.9	473.2	472.5	471.7	471.8
170°	473.9	474.7	475.5	476.3	477.1	477.2	476.5	475.9	475.2	474.6	474.5
172.5°	475.3	476.2	477.1	477.9	478.8	478.9	478.2	477.6	477.0	476.3	476.3
175°	477.1	478.1	479.0	480.0	480.9	481.1	480.4	479.7	479.0	478.2	478.2
177.5°	478.3	479.0	479.8	480.6	481.3	481.5	480.9	480.5	479.9	479.4	479.3
180°	480.0	480.0	480.0	480.0	480.0	480.0	480.0	480.0	480.0	480.0	480.0



TEST NUMBER: P333055-927

CATALOG NUMBER: S124RDIW-S795D470U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7
2.5°	1077.4	1072.7	1070.3	1064.9	1058.5	1055.1	1052.1	1047.7	1042.0	1035.9	1031.5
5°	1132.0	1122.0	1109.3	1094.2	1080.7	1067.6	1056.2	1044.9	1031.8	1018.3	1004.8
7.5°	1188.2	1168.3	1146.8	1122.0	1097.8	1075.8	1055.6	1036.2	1014.2	994.7	976.8
10°	1227.2	1200.3	1170.4	1138.8	1107.2	1079.8	1052.9	1028.4	1001.5	977.5	957.2
12.5°	1258.9	1227.2	1191.3	1151.9	1114.0	1080.9	1049.8	1018.0	987.3	961.2	934.3
15°	1311.5	1268.1	1219.7	1172.5	1123.2	1078.2	1036.4	999.3	964.4	927.7	902.1
17.5°	1347.7	1296.2	1237.3	1180.6	1122.4	1069.2	1021.1	976.9	936.6	899.1	868.5
20°	1369.3	1312.4	1247.1	1182.6	1117.3	1060.4	1008.6	959.7	918.1	877.6	846.0
22.5°	1381.4	1318.4	1247.1	1179.6	1111.9	1050.4	993.5	942.5	897.1	856.7	821.7
25°	1385.3	1317.9	1245.0	1167.4	1093.3	1028.0	969.0	913.9	863.2	822.8	785.8
27.5°	1379.9	1300.5	1225.8	1146.3	1069.8	1000.9	939.1	881.1	830.4	787.0	749.0
30°	1371.8	1286.7	1206.7	1124.0	1046.6	980.4	915.0	859.4	806.8	761.8	723.4
32.5°	1354.2	1269.9	1183.7	1099.2	1020.6	952.4	890.5	834.6	782.9	736.8	696.1
35°	1319.5	1234.1	1140.5	1053.7	976.6	905.8	847.7	793.8	744.5	695.1	652.2
37.5°	1273.8	1186.5	1093.4	998.3	921.1	854.4	801.0	750.4	702.3	657.3	609.7
40°	1230.7	1151.0	1054.9	960.6	881.4	816.9	767.6	721.7	673.3	628.6	581.0
42.5°	1178.4	1110.6	1013.5	918.8	840.6	778.5	732.6	687.7	643.6	600.3	550.6
45°	1091.2	1039.8	948.8	857.8	779.0	717.5	675.3	635.7	597.0	555.7	509.0
47.5°	991.3	956.5	877.9	784.7	711.9	656.5	615.8	583.4	550.6	509.4	468.3
50°	921.9	899.5	823.6	738.6	669.1	618.1	576.4	546.1	518.6	479.0	442.4
52.5°	847.7	835.8	771.7	690.4	623.2	573.2	537.6	510.3	482.6	449.7	415.4
55°	734.7	741.1	686.7	616.4	553.2	511.0	478.6	455.8	432.3	404.5	378.0
57.5°	619.3	642.4	605.9	544.2	484.9	446.0	421.6	402.4	382.6	359.6	336.9
60°	550.2	569.6	549.0	494.6	442.8	406.5	383.8	369.1	349.3	328.2	310.9
62.5°	482.8	503.6	491.3	447.4	399.3	368.1	348.1	334.4	319.6	301.3	283.3
65°	398.2	411.6	405.8	375.4	341.3	314.7	296.2	286.1	272.6	259.1	243.1
67.5°	304.9	331.0	327.6	311.4	281.9	261.2	249.1	240.1	227.8	217.9	206.9
70°	250.6	274.7	274.3	261.2	245.2	225.9	217.4	209.8	198.8	189.2	180.3
72.5°	205.2	227.2	230.4	220.5	209.5	194.8	186.7	181.5	170.9	164.2	157.1
75°	143.7	159.7	163.9	163.9	158.8	151.2	144.1	140.7	133.2	127.2	123.0
77.5°	94.2	104.3	110.9	112.4	113.2	110.7	104.7	102.3	96.6	94.4	90.4
80°	66.5	73.3	80.9	83.4	85.6	84.7	82.1	80.5	75.0	72.9	71.2
82.5°	46.0	49.7	55.9	61.5	60.9	63.1	60.9	59.6	55.5	54.7	53.0
85°	24.0	24.4	25.3	29.1	31.2	32.0	32.5	31.6	30.3	30.3	27.4
87.5°	9.4	9.0	9.5	9.3	9.5	10.7	11.5	11.6	10.9	10.0	9.2
90°	6.7	6.0	5.3	4.6	3.7	2.9	2.0	1.1	2.0	2.9	3.7
92.5°	6.3	5.7	5.1	4.8	4.7	4.6	4.6	4.5	4.6	4.6	4.7
95°	7.8	7.7	7.6	8.9	11.6	14.3	17.0	19.7	17.0	14.3	11.6
97.5°	27.3	36.2	45.1	48.7	47.0	45.3	43.6	41.9	43.6	45.3	47.0
100°	37.8	48.8	59.8	64.6	63.2	61.8	60.3	58.9	60.3	61.8	63.2
102.5°	79.0	80.4	81.8	82.1	81.0	79.9	78.9	77.9	78.9	79.9	81.0
105°	111.2	110.8	110.4	110.0	109.5	109.0	108.5	108.1	108.5	109.0	109.5
107.5°	138.6	138.0	137.5	137.1	136.9	136.7	136.4	136.2	136.4	136.7	136.9
110°	157.4	156.9	156.4	156.1	155.8	155.6	155.3	155.1	155.3	155.6	155.8



TEST NUMBER: P333055-927

CATALOG NUMBER: S124RDIW-S795D470U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	175.9	175.8	175.5	175.2	174.8	174.4	173.9	173.5	173.9	174.4	174.8
115°	202.6	202.7	202.8	202.7	202.5	202.2	202.0	201.8	202.0	202.2	202.5
117.5°	229.1	228.9	228.8	228.5	228.2	227.9	227.6	227.3	227.6	227.9	228.2
120°	245.7	245.8	245.9	245.7	245.4	245.1	244.8	244.5	244.8	245.1	245.4
122.5°	261.7	261.6	261.5	261.3	261.2	260.9	260.8	260.5	260.8	260.9	261.2
125°	284.6	284.8	284.9	284.9	284.6	284.2	283.9	283.6	283.9	284.2	284.6
127.5°	306.7	306.3	306.0	305.8	305.7	305.6	305.5	305.5	305.5	305.6	305.7
130°	320.5	320.3	320.0	319.9	319.8	319.7	319.6	319.5	319.6	319.7	319.8
132.5°	333.8	333.6	333.3	333.0	332.9	332.7	332.6	332.5	332.6	332.7	332.9
135°	352.3	352.0	351.6	351.5	351.6	351.6	351.7	351.8	351.7	351.6	351.6
137.5°	370.0	369.6	369.3	369.2	369.1	369.1	369.0	369.0	369.0	369.1	369.1
140°	381.4	381.1	381.0	380.8	380.6	380.5	380.3	380.2	380.3	380.5	380.6
142.5°	391.8	391.7	391.6	391.4	391.1	390.9	390.5	390.2	390.5	390.9	391.1
145°	406.8	406.8	406.8	406.6	406.4	406.2	405.9	405.7	405.9	406.2	406.4
147.5°	419.8	419.9	419.9	419.8	419.3	418.8	418.4	418.0	418.4	418.8	419.3
150°	428.1	428.2	428.3	428.2	427.9	427.5	427.2	426.9	427.2	427.5	427.9
152.5°	435.1	435.3	435.4	435.4	435.1	434.8	434.6	434.4	434.6	434.8	435.1
155°	444.6	444.8	445.0	445.1	445.0	445.0	444.9	444.8	444.9	445.0	445.0
157.5°	452.7	453.0	453.3	453.4	453.5	453.5	453.6	453.7	453.6	453.5	453.5
160°	457.6	457.6	457.7	457.9	458.1	458.4	458.6	458.8	458.6	458.4	458.1
162.5°	461.8	461.9	462.0	462.2	462.5	462.8	463.1	463.4	463.1	462.8	462.5
165°	467.5	467.5	467.5	467.6	468.0	468.4	468.8	469.2	468.8	468.4	468.0
167.5°	471.8	471.9	471.9	472.1	472.6	473.0	473.4	473.8	473.4	473.0	472.6
170°	474.4	474.4	474.3	474.5	475.0	475.5	475.9	476.4	475.9	475.5	475.0
172.5°	476.2	476.1	476.0	476.3	476.7	477.2	477.7	478.2	477.7	477.2	476.7
175°	478.1	478.0	477.9	478.1	478.6	479.0	479.5	480.0	479.5	479.0	478.6
177.5°	479.2	479.0	479.0	479.1	479.5	480.0	480.5	480.9	480.5	480.0	479.5
180°	480.0	480.0	480.0	480.0	480.0	480.0	480.0	480.0	480.0	480.0	480.0



TEST NUMBER: P333055-927

CATALOG NUMBER: S124RDIW-S795D470U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7
2.5°	1026.8	1023.4	1019.1	1014.0	1008.0	1002.6	1000.2	1002.2	1003.2	1000.5	1000.2
5°	995.5	985.0	976.6	963.9	953.9	945.4	939.5	937.0	937.9	931.1	929.4
7.5°	960.4	947.9	934.1	919.2	905.1	892.8	886.3	882.7	875.6	872.5	867.4
10°	937.9	921.0	907.5	889.8	873.8	859.0	851.9	846.0	838.8	835.4	828.3
12.5°	914.6	895.0	880.2	861.8	845.5	827.7	820.9	809.9	798.8	791.6	782.4
15°	881.8	858.3	840.1	818.2	798.8	778.6	760.5	740.2	732.7	716.7	707.4
17.5°	843.4	819.5	797.1	767.7	737.8	712.7	693.4	674.0	662.4	652.2	647.5
20°	818.2	796.3	765.1	730.9	697.7	669.9	654.3	641.7	629.0	621.9	616.8
22.5°	794.2	766.3	730.1	693.2	660.0	638.2	625.0	612.0	601.7	594.9	588.1
25°	754.2	717.5	679.1	637.0	614.3	595.3	581.0	570.5	564.1	555.3	551.9
27.5°	713.0	668.5	626.2	597.9	574.3	556.9	544.4	536.5	528.5	522.8	518.5
30°	681.3	636.2	598.3	571.3	547.3	533.0	522.8	513.6	507.2	502.6	499.2
32.5°	649.9	604.8	573.0	544.0	525.1	511.0	500.3	493.4	488.4	482.4	480.4
35°	604.6	564.6	536.8	510.6	491.2	478.6	470.2	463.0	458.8	457.1	455.8
37.5°	561.0	528.2	498.4	476.9	459.6	449.7	439.7	436.3	433.3	430.3	431.7
40°	533.4	502.6	476.1	453.4	439.4	428.5	422.6	418.4	415.8	415.8	415.8
42.5°	509.5	479.3	453.5	433.1	419.2	410.0	403.4	399.8	398.9	398.6	400.7
45°	472.3	444.5	418.4	401.5	389.7	380.4	376.7	373.7	373.7	375.4	375.8
47.5°	435.5	409.4	388.5	369.6	358.8	353.0	349.7	348.2	348.3	350.1	352.0
50°	412.9	387.2	366.5	349.7	339.6	334.1	331.1	330.3	331.1	331.1	334.1
52.5°	388.2	365.3	345.0	330.8	319.3	314.2	312.6	311.4	312.0	313.3	314.6
55°	352.2	331.6	312.2	298.7	290.3	286.9	283.1	283.5	282.7	283.5	283.5
57.5°	316.1	297.5	279.5	268.8	261.4	256.5	252.4	253.6	252.3	252.2	251.4
60°	292.8	272.6	258.3	248.6	240.1	235.9	232.1	233.0	231.7	230.8	229.2
62.5°	267.5	250.6	237.0	227.7	220.9	216.0	212.2	211.4	208.5	205.6	201.9
65°	230.8	217.0	204.8	195.9	189.6	185.8	182.8	180.3	174.0	167.2	163.9
67.5°	195.3	185.2	173.8	166.4	161.2	156.2	150.6	146.3	140.4	136.7	134.6
70°	172.3	162.6	153.0	145.8	140.3	135.7	129.4	126.4	122.2	120.5	118.4
72.5°	150.4	141.4	132.4	125.9	120.1	116.5	111.5	108.5	106.7	106.0	103.9
75°	117.2	110.0	103.2	97.4	92.7	90.2	88.1	86.0	85.1	81.3	79.2
77.5°	85.5	80.7	76.5	72.3	69.0	67.3	63.3	60.8	59.4	57.7	57.2
80°	66.5	63.2	59.0	56.5	51.8	50.1	48.5	48.0	47.6	47.2	46.7
82.5°	50.1	46.7	42.5	41.0	39.7	38.7	37.6	37.2	36.8	37.1	37.0
85°	25.3	23.6	23.6	23.2	22.7	22.3	21.9	21.9	21.5	21.9	21.5
87.5°	9.3	9.2	9.3	8.7	9.2	9.3	9.1	9.2	9.6	9.0	9.1
90°	4.6	5.3	6.0	6.7	7.3	7.9	8.4	8.9	9.3	9.8	10.1
92.5°	4.8	5.1	5.7	6.3	7.0	7.6	8.1	8.6	9.0	9.5	9.7
95°	8.9	7.6	7.7	7.8	7.8	7.9	8.4	8.9	9.3	9.8	10.1
97.5°	48.7	45.1	36.2	27.3	18.4	9.5	9.5	9.6	9.6	9.7	9.7
100°	64.6	59.8	48.8	37.8	26.8	15.8	14.4	13.1	11.7	10.4	9.7
102.5°	82.1	81.8	80.4	79.0	77.6	76.1	61.5	46.8	32.2	17.6	10.3
105°	110.0	110.4	110.8	111.2	111.6	112.0	112.7	113.4	114.2	114.9	113.8
107.5°	137.1	137.5	138.0	138.6	139.1	139.7	140.0	140.4	140.7	141.1	141.4
110°	156.1	156.4	156.9	157.4	157.9	158.4	158.5	158.7	158.8	159.0	159.1



TEST NUMBER: P333055-927

CATALOG NUMBER: S124RDIW-S795D470U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	175.2	175.5	175.8	175.9	176.2	176.4	176.4	176.3	176.3	176.3	176.4
115°	202.7	202.8	202.7	202.6	202.6	202.5	202.6	202.8	203.0	203.1	203.2
117.5°	228.5	228.8	228.9	229.1	229.3	229.5	229.4	229.4	229.4	229.3	229.3
120°	245.7	245.9	245.8	245.7	245.7	245.6	245.7	245.9	246.1	246.2	246.2
122.5°	261.3	261.5	261.6	261.7	261.8	262.0	262.1	262.1	262.2	262.3	262.3
125°	284.9	284.9	284.8	284.6	284.5	284.3	284.6	284.8	285.0	285.3	285.4
127.5°	305.8	306.0	306.3	306.7	307.1	307.4	307.4	307.4	307.3	307.3	307.2
130°	319.9	320.0	320.3	320.5	320.8	321.0	321.1	321.2	321.2	321.3	321.3
132.5°	333.0	333.3	333.6	333.8	334.1	334.5	334.5	334.6	334.7	334.8	334.8
135°	351.5	351.6	352.0	352.3	352.6	352.9	353.1	353.2	353.4	353.6	353.7
137.5°	369.2	369.3	369.6	370.0	370.3	370.7	370.9	371.1	371.2	371.5	371.5
140°	380.8	381.0	381.1	381.4	381.5	381.7	381.9	382.1	382.4	382.6	382.8
142.5°	391.4	391.6	391.7	391.8	391.9	392.0	392.1	392.3	392.5	392.7	392.8
145°	406.6	406.8	406.8	406.8	406.8	406.8	406.9	406.9	407.0	407.1	407.2
147.5°	419.8	419.9	419.9	419.8	419.7	419.6	419.7	419.8	419.8	419.9	419.9
150°	428.2	428.3	428.2	428.1	428.0	427.9	427.9	427.9	427.9	427.9	428.0
152.5°	435.4	435.4	435.3	435.1	435.0	434.8	435.0	435.1	435.2	435.4	435.4
155°	445.1	445.0	444.8	444.6	444.3	444.1	444.4	444.7	445.0	445.4	445.4
157.5°	453.4	453.3	453.0	452.7	452.5	452.3	452.7	453.0	453.4	453.8	453.8
160°	457.9	457.7	457.6	457.6	457.5	457.4	457.9	458.4	458.8	459.3	459.3
162.5°	462.2	462.0	461.9	461.8	461.8	461.7	462.2	462.6	463.1	463.6	463.6
165°	467.6	467.5	467.5	467.5	467.5	467.5	468.1	468.7	469.4	470.0	469.9
167.5°	472.1	471.9	471.9	471.8	471.8	471.7	472.5	473.2	473.9	474.6	474.5
170°	474.5	474.3	474.4	474.4	474.5	474.6	475.2	475.9	476.5	477.2	477.1
172.5°	476.3	476.0	476.1	476.2	476.3	476.3	477.0	477.6	478.2	478.9	478.8
175°	478.1	477.9	478.0	478.1	478.2	478.2	479.0	479.7	480.4	481.1	480.9
177.5°	479.1	479.0	479.0	479.2	479.3	479.4	479.9	480.5	480.9	481.5	481.3
180°	480.0	480.0	480.0	480.0	480.0	480.0	480.0	480.0	480.0	480.0	480.0



TEST NUMBER: P333055-927

CATALOG NUMBER: S124RDIW-S795D470U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7
2.5°	998.1	998.9	996.5	995.8	996.5	998.9	998.1	1000.2	1000.5	1003.2	1002.2
5°	926.1	925.2	923.1	923.5	923.1	925.2	926.1	929.4	931.1	937.9	937.0
7.5°	864.4	861.1	862.0	858.6	862.0	861.1	864.4	867.4	872.5	875.6	882.7
10°	826.6	822.0	818.2	814.8	818.2	822.0	826.6	828.3	835.4	838.8	846.0
12.5°	775.1	771.1	766.0	767.0	766.0	771.1	775.1	782.4	791.6	798.8	809.9
15°	701.9	695.6	685.5	686.7	685.5	695.6	701.9	707.4	716.7	732.7	740.2
17.5°	640.0	640.1	635.4	636.5	635.4	640.1	640.0	647.5	652.2	662.4	674.0
20°	607.9	605.0	605.4	604.2	605.4	605.0	607.9	616.8	621.9	629.0	641.7
22.5°	585.7	582.1	579.2	576.6	579.2	582.1	585.7	588.1	594.9	601.7	612.0
25°	548.1	545.6	541.8	541.0	541.8	545.6	548.1	551.9	555.3	564.1	570.5
27.5°	515.1	514.6	513.1	511.1	513.1	514.6	515.1	518.5	522.8	528.5	536.5
30°	495.9	495.0	494.2	492.9	494.2	495.0	495.9	499.2	502.6	507.2	513.6
32.5°	478.7	478.2	477.4	477.4	477.4	478.2	478.7	480.4	482.4	488.4	493.4
35°	454.2	453.8	452.9	452.5	452.9	453.8	454.2	455.8	457.1	458.8	463.0
37.5°	431.3	432.4	431.8	431.7	431.8	432.4	431.3	431.7	430.3	433.3	436.3
40°	415.4	415.8	416.7	416.3	416.7	415.8	415.4	415.8	415.8	415.8	418.4
42.5°	402.3	402.3	403.5	402.1	403.5	402.3	402.3	400.7	398.6	398.9	399.8
45°	378.7	381.3	380.9	380.9	380.9	381.3	378.7	375.8	375.4	373.7	373.7
47.5°	353.1	355.2	355.8	355.8	355.8	355.2	353.1	352.0	350.1	348.3	348.2
50°	336.2	335.3	336.6	336.2	336.6	335.3	336.2	334.1	331.1	331.1	330.3
52.5°	315.7	315.8	315.8	315.3	315.8	315.8	315.7	314.6	313.3	312.0	311.4
55°	284.0	284.4	283.5	284.0	283.5	284.4	284.0	283.5	283.5	282.7	283.5
57.5°	249.6	247.6	248.4	247.4	248.4	247.6	249.6	251.4	252.2	252.3	253.6
60°	225.0	221.6	220.8	219.1	220.8	221.6	225.0	229.2	230.8	231.7	233.0
62.5°	197.3	195.0	192.1	193.5	192.1	195.0	197.3	201.9	205.6	208.5	211.4
65°	160.5	158.8	157.6	159.2	157.6	158.8	160.5	163.9	167.2	174.0	180.3
67.5°	132.8	132.0	132.0	131.1	132.0	132.0	132.8	134.6	136.7	140.4	146.3
70°	118.4	117.2	117.2	116.3	117.2	117.2	118.4	118.4	120.5	122.2	126.4
72.5°	103.5	102.3	102.7	102.1	102.7	102.3	103.5	103.9	106.0	106.7	108.5
75°	76.7	74.5	74.5	75.0	74.5	74.5	76.7	79.2	81.3	85.1	86.0
77.5°	57.2	56.8	57.4	56.6	57.4	56.8	57.2	57.2	57.7	59.4	60.8
80°	46.7	46.3	45.9	47.2	45.9	46.3	46.7	46.7	47.2	47.6	48.0
82.5°	36.3	36.2	36.1	37.8	36.1	36.2	36.3	37.0	37.1	36.8	37.2
85°	21.9	21.1	21.9	21.1	21.9	21.1	21.9	21.5	21.9	21.5	21.9
87.5°	9.8	9.5	9.2	9.6	9.2	9.5	9.8	9.1	9.0	9.6	9.2
90°	10.3	10.5	10.6	10.8	10.6	10.5	10.3	10.1	9.8	9.3	8.9
92.5°	9.8	9.8	9.9	9.9	9.9	9.8	9.8	9.7	9.5	9.0	8.6
95°	10.1	10.2	10.3	10.4	10.3	10.2	10.1	10.1	9.8	9.3	8.9
97.5°	9.8	9.9	10.0	10.1	10.0	9.9	9.8	9.7	9.7	9.6	9.6
100°	9.8	9.9	10.0	10.1	10.0	9.9	9.8	9.7	10.4	11.7	13.1
102.5°	10.3	10.3	10.3	10.4	10.3	10.3	10.3	10.3	17.6	32.2	46.8
105°	110.9	108.1	105.2	102.3	105.2	108.1	110.9	113.8	114.9	114.2	113.4
107.5°	141.7	142.0	142.3	142.6	142.3	142.0	141.7	141.4	141.1	140.7	140.4
110°	159.4	159.6	159.9	160.1	159.9	159.6	159.4	159.1	159.0	158.8	158.7



TEST NUMBER: P333055-927

CATALOG NUMBER: S124RDIW-S795D470U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	176.7	177.1	177.4	177.6	177.4	177.1	176.7	176.4	176.3	176.3	176.3
115°	203.2	203.2	203.2	203.2	203.2	203.2	203.2	203.2	203.1	203.0	202.8
117.5°	229.3	229.3	229.3	229.2	229.3	229.3	229.3	229.3	229.3	229.4	229.4
120°	246.1	245.9	245.7	245.6	245.7	245.9	246.1	246.2	246.2	246.1	245.9
122.5°	262.1	262.0	261.8	261.7	261.8	262.0	262.1	262.3	262.3	262.2	262.1
125°	285.5	285.6	285.7	285.7	285.7	285.6	285.5	285.4	285.3	285.0	284.8
127.5°	307.1	307.0	307.0	307.0	307.0	307.0	307.1	307.2	307.3	307.3	307.4
130°	321.3	321.3	321.3	321.3	321.3	321.3	321.3	321.3	321.3	321.2	321.2
132.5°	334.7	334.7	334.6	334.5	334.6	334.7	334.7	334.8	334.8	334.7	334.6
135°	353.9	354.0	354.2	354.3	354.2	354.0	353.9	353.7	353.6	353.4	353.2
137.5°	371.5	371.4	371.4	371.3	371.4	371.4	371.5	371.5	371.5	371.2	371.1
140°	382.9	382.9	383.0	383.1	383.0	382.9	382.9	382.8	382.6	382.4	382.1
142.5°	392.8	392.8	392.8	392.8	392.8	392.8	392.8	392.8	392.7	392.5	392.3
145°	407.3	407.5	407.7	407.8	407.7	407.5	407.3	407.2	407.1	407.0	406.9
147.5°	420.0	420.1	420.2	420.3	420.2	420.1	420.0	419.9	419.9	419.8	419.8
150°	428.1	428.2	428.3	428.3	428.3	428.2	428.1	428.0	427.9	427.9	427.9
152.5°	435.4	435.3	435.2	435.2	435.2	435.3	435.4	435.4	435.4	435.2	435.1
155°	445.2	445.0	444.7	444.5	444.7	445.0	445.2	445.4	445.4	445.0	444.7
157.5°	453.4	453.0	452.7	452.3	452.7	453.0	453.4	453.8	453.8	453.4	453.0
160°	458.8	458.4	457.9	457.4	457.9	458.4	458.8	459.3	459.3	458.8	458.4
162.5°	463.0	462.5	461.9	461.4	461.9	462.5	463.0	463.6	463.6	463.1	462.6
165°	469.2	468.5	467.8	467.1	467.8	468.5	469.2	469.9	470.0	469.4	468.7
167.5°	473.7	472.9	472.1	471.3	472.1	472.9	473.7	474.5	474.6	473.9	473.2
170°	476.3	475.5	474.7	473.9	474.7	475.5	476.3	477.1	477.2	476.5	475.9
172.5°	477.9	477.1	476.2	475.3	476.2	477.1	477.9	478.8	478.9	478.2	477.6
175°	480.0	479.0	478.1	477.1	478.1	479.0	480.0	480.9	481.1	480.4	479.7
177.5°	480.6	479.8	479.0	478.3	479.0	479.8	480.6	481.3	481.5	480.9	480.5
180°	480.0	480.0	480.0	480.0	480.0	480.0	480.0	480.0	480.0	480.0	480.0



TEST NUMBER: P333055-927

CATALOG NUMBER: S124RDIW-S795D470U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7
2.5°	1000.2	1002.6	1008.0	1014.0	1019.1	1023.4	1026.8	1031.5	1035.9	1042.0	1047.7
5°	939.5	945.4	953.9	963.9	976.6	985.0	995.5	1004.8	1018.3	1031.8	1044.9
7.5°	886.3	892.8	905.1	919.2	934.1	947.9	960.4	976.8	994.7	1014.2	1036.2
10°	851.9	859.0	873.8	889.8	907.5	921.0	937.9	957.2	977.5	1001.5	1028.4
12.5°	820.9	827.7	845.5	861.8	880.2	895.0	914.6	934.3	961.2	987.3	1018.0
15°	760.5	778.6	798.8	818.2	840.1	858.3	881.8	902.1	927.7	964.4	999.3
17.5°	693.4	712.7	737.8	767.7	797.1	819.5	843.4	868.5	899.1	936.6	976.9
20°	654.3	669.9	697.7	730.9	765.1	796.3	818.2	846.0	877.6	918.1	959.7
22.5°	625.0	638.2	660.0	693.2	730.1	766.3	794.2	821.7	856.7	897.1	942.5
25°	581.0	595.3	614.3	637.0	679.1	717.5	754.2	785.8	822.8	863.2	913.9
27.5°	544.4	556.9	574.3	597.9	626.2	668.5	713.0	749.0	787.0	830.4	881.1
30°	522.8	533.0	547.3	571.3	598.3	636.2	681.3	723.4	761.8	806.8	859.4
32.5°	500.3	511.0	525.1	544.0	573.0	604.8	649.9	696.1	736.8	782.9	834.6
35°	470.2	478.6	491.2	510.6	536.8	564.6	604.6	652.2	695.1	744.5	793.8
37.5°	439.7	449.7	459.6	476.9	498.4	528.2	561.0	609.7	657.3	702.3	750.4
40°	422.6	428.5	439.4	453.4	476.1	502.6	533.4	581.0	628.6	673.3	721.7
42.5°	403.4	410.0	419.2	433.1	453.5	479.3	509.5	550.6	600.3	643.6	687.7
45°	376.7	380.4	389.7	401.5	418.4	444.5	472.3	509.0	555.7	597.0	635.7
47.5°	349.7	353.0	358.8	369.6	388.5	409.4	435.5	468.3	509.4	550.6	583.4
50°	331.1	334.1	339.6	349.7	366.5	387.2	412.9	442.4	479.0	518.6	546.1
52.5°	312.6	314.2	319.3	330.8	345.0	365.3	388.2	415.4	449.7	482.6	510.3
55°	283.1	286.9	290.3	298.7	312.2	331.6	352.2	378.0	404.5	432.3	455.8
57.5°	252.4	256.5	261.4	268.8	279.5	297.5	316.1	336.9	359.6	382.6	402.4
60°	232.1	235.9	240.1	248.6	258.3	272.6	292.8	310.9	328.2	349.3	369.1
62.5°	212.2	216.0	220.9	227.7	237.0	250.6	267.5	283.3	301.3	319.6	334.4
65°	182.8	185.8	189.6	195.9	204.8	217.0	230.8	243.1	259.1	272.6	286.1
67.5°	150.6	156.2	161.2	166.4	173.8	185.2	195.3	206.9	217.9	227.8	240.1
70°	129.4	135.7	140.3	145.8	153.0	162.6	172.3	180.3	189.2	198.8	209.8
72.5°	111.5	116.5	120.1	125.9	132.4	141.4	150.4	157.1	164.2	170.9	181.5
75°	88.1	90.2	92.7	97.4	103.2	110.0	117.2	123.0	127.2	133.2	140.7
77.5°	63.3	67.3	69.0	72.3	76.5	80.7	85.5	90.4	94.4	96.6	102.3
80°	48.5	50.1	51.8	56.5	59.0	63.2	66.5	71.2	72.9	75.0	80.5
82.5°	37.6	38.7	39.7	41.0	42.5	46.7	50.1	53.0	54.7	55.5	59.6
85°	21.9	22.3	22.7	23.2	23.6	23.6	25.3	27.4	30.3	30.3	31.6
87.5°	9.1	9.3	9.2	8.7	9.3	9.2	9.3	9.2	10.0	10.9	11.6
90°	8.4	7.9	7.3	6.7	6.0	5.3	4.6	3.7	2.9	2.0	1.1
92.5°	8.1	7.6	7.0	6.3	5.7	5.1	4.8	4.7	4.6	4.6	4.5
95°	8.4	7.9	7.8	7.8	7.7	7.6	8.9	11.6	14.3	17.0	19.7
97.5°	9.5	9.5	18.4	27.3	36.2	45.1	48.7	47.0	45.3	43.6	41.9
100°	14.4	15.8	26.8	37.8	48.8	59.8	64.6	63.2	61.8	60.3	58.9
102.5°	61.5	76.1	77.6	79.0	80.4	81.8	82.1	81.0	79.9	78.9	77.9
105°	112.7	112.0	111.6	111.2	110.8	110.4	110.0	109.5	109.0	108.5	108.1
107.5°	140.0	139.7	139.1	138.6	138.0	137.5	137.1	136.9	136.7	136.4	136.2
110°	158.5	158.4	157.9	157.4	156.9	156.4	156.1	155.8	155.6	155.3	155.1



TEST NUMBER: P333055-927

CATALOG NUMBER: S124RDIW-S795D470U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	176.4	176.4	176.2	175.9	175.8	175.5	175.2	174.8	174.4	173.9	173.5
115°	202.6	202.5	202.6	202.6	202.7	202.8	202.7	202.5	202.2	202.0	201.8
117.5°	229.4	229.5	229.3	229.1	228.9	228.8	228.5	228.2	227.9	227.6	227.3
120°	245.7	245.6	245.7	245.7	245.8	245.9	245.7	245.4	245.1	244.8	244.5
122.5°	262.1	262.0	261.8	261.7	261.6	261.5	261.3	261.2	260.9	260.8	260.5
125°	284.6	284.3	284.5	284.6	284.8	284.9	284.9	284.6	284.2	283.9	283.6
127.5°	307.4	307.4	307.1	306.7	306.3	306.0	305.8	305.7	305.6	305.5	305.5
130°	321.1	321.0	320.8	320.5	320.3	320.0	319.9	319.8	319.7	319.6	319.5
132.5°	334.5	334.5	334.1	333.8	333.6	333.3	333.0	332.9	332.7	332.6	332.5
135°	353.1	352.9	352.6	352.3	352.0	351.6	351.5	351.6	351.6	351.7	351.8
137.5°	370.9	370.7	370.3	370.0	369.6	369.3	369.2	369.1	369.1	369.0	369.0
140°	381.9	381.7	381.5	381.4	381.1	381.0	380.8	380.6	380.5	380.3	380.2
142.5°	392.1	392.0	391.9	391.8	391.7	391.6	391.4	391.1	390.9	390.5	390.2
145°	406.9	406.8	406.8	406.8	406.8	406.8	406.6	406.4	406.2	405.9	405.7
147.5°	419.7	419.6	419.7	419.8	419.9	419.9	419.8	419.3	418.8	418.4	418.0
150°	427.9	427.9	428.0	428.1	428.2	428.3	428.2	427.9	427.5	427.2	426.9
152.5°	435.0	434.8	435.0	435.1	435.3	435.4	435.4	435.1	434.8	434.6	434.4
155°	444.4	444.1	444.3	444.6	444.8	445.0	445.1	445.0	445.0	444.9	444.8
157.5°	452.7	452.3	452.5	452.7	453.0	453.3	453.4	453.5	453.5	453.6	453.7
160°	457.9	457.4	457.5	457.6	457.6	457.7	457.9	458.1	458.4	458.6	458.8
162.5°	462.2	461.7	461.8	461.8	461.9	462.0	462.2	462.5	462.8	463.1	463.4
165°	468.1	467.5	467.5	467.5	467.5	467.5	467.6	468.0	468.4	468.8	469.2
167.5°	472.5	471.7	471.8	471.8	471.9	471.9	472.1	472.6	473.0	473.4	473.8
170°	475.2	474.6	474.5	474.4	474.4	474.3	474.5	475.0	475.5	475.9	476.4
172.5°	477.0	476.3	476.3	476.2	476.1	476.0	476.3	476.7	477.2	477.7	478.2
175°	479.0	478.2	478.2	478.1	478.0	477.9	478.1	478.6	479.0	479.5	480.0
177.5°	479.9	479.4	479.3	479.2	479.0	479.0	479.1	479.5	480.0	480.5	480.9
180°	480.0	480.0	480.0	480.0	480.0	480.0	480.0	480.0	480.0	480.0	480.0



TEST NUMBER: P333055-927

CATALOG NUMBER: S124RDIW-S795D470U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7
2.5°	1052.1	1055.1	1058.5	1064.9	1070.3	1072.7	1077.4	1080.8	1079.7	1084.4	1092.6
5°	1056.2	1067.6	1080.7	1094.2	1109.3	1122.0	1132.0	1142.2	1150.2	1159.8	1174.2
7.5°	1055.6	1075.8	1097.8	1122.0	1146.8	1168.3	1188.2	1208.4	1226.4	1246.0	1271.7
10°	1052.9	1079.8	1107.2	1138.8	1170.4	1200.3	1227.2	1252.6	1276.6	1302.3	1334.7
12.5°	1049.8	1080.9	1114.0	1151.9	1191.3	1227.2	1258.9	1295.4	1325.5	1358.6	1396.1
15°	1036.4	1078.2	1123.2	1172.5	1219.7	1268.1	1311.5	1356.2	1397.9	1437.5	1484.7
17.5°	1021.1	1069.2	1122.4	1180.6	1237.3	1296.2	1347.7	1404.0	1446.6	1499.8	1543.6
20°	1008.6	1060.4	1117.3	1182.6	1247.1	1312.4	1369.3	1426.6	1474.6	1528.1	1583.7
22.5°	993.5	1050.4	1111.9	1179.6	1247.1	1318.4	1381.4	1438.4	1497.9	1558.1	1615.4
25°	969.0	1028.0	1093.3	1167.4	1245.0	1317.9	1385.3	1456.0	1520.1	1585.4	1636.8
27.5°	939.1	1000.9	1069.8	1146.3	1225.8	1300.5	1379.9	1455.3	1519.7	1582.6	1627.5
30°	915.0	980.4	1046.6	1124.0	1206.7	1286.7	1371.8	1447.2	1515.0	1571.5	1596.8
32.5°	890.5	952.4	1020.6	1099.2	1183.7	1269.9	1354.2	1431.4	1494.1	1528.0	1528.7
35°	847.7	905.8	976.6	1053.7	1140.5	1234.1	1319.5	1395.3	1433.7	1436.7	1395.3
37.5°	801.0	854.4	921.1	998.3	1093.4	1186.5	1273.8	1324.4	1337.1	1294.3	1217.9
40°	767.6	816.9	881.4	960.6	1054.9	1151.0	1230.7	1267.7	1254.3	1184.7	1099.6
42.5°	732.6	778.5	840.6	918.8	1013.5	1110.6	1178.4	1198.3	1162.6	1082.3	982.7
45°	675.3	717.5	779.0	857.8	948.8	1039.8	1091.2	1081.1	1021.7	926.5	814.8
47.5°	615.8	656.5	711.9	784.7	877.9	956.5	991.3	960.8	876.2	771.5	680.6
50°	576.4	618.1	669.1	738.6	823.6	899.5	921.9	875.5	781.6	680.8	597.4
52.5°	537.6	573.2	623.2	690.4	771.7	835.8	847.7	794.2	697.3	607.0	533.1
55°	478.6	511.0	553.2	616.4	686.7	741.1	734.7	666.1	578.1	501.0	442.8
57.5°	421.6	446.0	484.9	544.2	605.9	642.4	619.3	560.8	478.7	415.6	366.5
60°	383.8	406.5	442.8	494.6	549.0	569.6	550.2	486.6	421.8	364.0	322.7
62.5°	348.1	368.1	399.3	447.4	491.3	503.6	482.8	427.3	368.8	319.5	285.3
65°	296.2	314.7	341.3	375.4	405.8	411.6	398.2	341.3	297.0	255.7	232.1
67.5°	249.1	261.2	281.9	311.4	327.6	331.0	304.9	269.2	230.2	204.9	187.0
70°	217.4	225.9	245.2	261.2	274.3	274.7	250.6	222.0	192.1	171.5	158.4
72.5°	186.7	194.8	209.5	220.5	230.4	227.2	205.2	182.6	158.4	142.8	133.2
75°	144.1	151.2	158.8	163.9	163.9	159.7	143.7	126.8	112.9	103.6	100.7
77.5°	104.7	110.7	113.2	112.4	110.9	104.3	94.2	83.2	78.2	73.8	71.6
80°	82.1	84.7	85.6	83.4	80.9	73.3	66.5	61.9	57.3	55.6	54.7
82.5°	60.9	63.1	60.9	61.5	55.9	49.7	46.0	44.4	42.5	41.8	41.0
85°	32.5	32.0	31.2	29.1	25.3	24.4	24.0	23.6	22.7	23.2	22.3
87.5°	11.5	10.7	9.5	9.3	9.5	9.0	9.4	9.5	9.7	9.4	10.2
90°	2.0	2.9	3.7	4.6	5.3	6.0	6.7	7.3	7.9	8.4	8.9
92.5°	4.6	4.6	4.7	4.8	5.1	5.7	6.3	7.0	7.6	8.1	8.6
95°	17.0	14.3	11.6	8.9	7.6	7.7	7.8	7.8	7.9	8.4	8.9
97.5°	43.6	45.3	47.0	48.7	45.1	36.2	27.3	18.4	9.5	9.5	9.6
100°	60.3	61.8	63.2	64.6	59.8	48.8	37.8	26.8	15.8	14.4	13.1
102.5°	78.9	79.9	81.0	82.1	81.8	80.4	79.0	77.6	76.1	61.5	46.8
105°	108.5	109.0	109.5	110.0	110.4	110.8	111.2	111.6	112.0	112.7	113.4
107.5°	136.4	136.7	136.9	137.1	137.5	138.0	138.6	139.1	139.7	140.0	140.4
110°	155.3	155.6	155.8	156.1	156.4	156.9	157.4	157.9	158.4	158.5	158.7



TEST NUMBER: P333055-927

CATALOG NUMBER: S124RDIW-S795D470U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	173.9	174.4	174.8	175.2	175.5	175.8	175.9	176.2	176.4	176.4	176.3
115°	202.0	202.2	202.5	202.7	202.8	202.7	202.6	202.6	202.5	202.6	202.8
117.5°	227.6	227.9	228.2	228.5	228.8	228.9	229.1	229.3	229.5	229.4	229.4
120°	244.8	245.1	245.4	245.7	245.9	245.8	245.7	245.7	245.6	245.7	245.9
122.5°	260.8	260.9	261.2	261.3	261.5	261.6	261.7	261.8	262.0	262.1	262.1
125°	283.9	284.2	284.6	284.9	284.9	284.8	284.6	284.5	284.3	284.6	284.8
127.5°	305.5	305.6	305.7	305.8	306.0	306.3	306.7	307.1	307.4	307.4	307.4
130°	319.6	319.7	319.8	319.9	320.0	320.3	320.5	320.8	321.0	321.1	321.2
132.5°	332.6	332.7	332.9	333.0	333.3	333.6	333.8	334.1	334.5	334.5	334.6
135°	351.7	351.6	351.6	351.5	351.6	352.0	352.3	352.6	352.9	353.1	353.2
137.5°	369.0	369.1	369.1	369.2	369.3	369.6	370.0	370.3	370.7	370.9	371.1
140°	380.3	380.5	380.6	380.8	381.0	381.1	381.4	381.5	381.7	381.9	382.1
142.5°	390.5	390.9	391.1	391.4	391.6	391.7	391.8	391.9	392.0	392.1	392.3
145°	405.9	406.2	406.4	406.6	406.8	406.8	406.8	406.8	406.8	406.9	406.9
147.5°	418.4	418.8	419.3	419.8	419.9	419.9	419.8	419.7	419.6	419.7	419.8
150°	427.2	427.5	427.9	428.2	428.3	428.2	428.1	428.0	427.9	427.9	427.9
152.5°	434.6	434.8	435.1	435.4	435.4	435.3	435.1	435.0	434.8	435.0	435.1
155°	444.9	445.0	445.0	445.1	445.0	444.8	444.6	444.3	444.1	444.4	444.7
157.5°	453.6	453.5	453.5	453.4	453.3	453.0	452.7	452.5	452.3	452.7	453.0
160°	458.6	458.4	458.1	457.9	457.7	457.6	457.6	457.5	457.4	457.9	458.4
162.5°	463.1	462.8	462.5	462.2	462.0	461.9	461.8	461.8	461.7	462.2	462.6
165°	468.8	468.4	468.0	467.6	467.5	467.5	467.5	467.5	467.5	468.1	468.7
167.5°	473.4	473.0	472.6	472.1	471.9	471.9	471.8	471.8	471.7	472.5	473.2
170°	475.9	475.5	475.0	474.5	474.3	474.4	474.4	474.5	474.6	475.2	475.9
172.5°	477.7	477.2	476.7	476.3	476.0	476.1	476.2	476.3	476.3	477.0	477.6
175°	479.5	479.0	478.6	478.1	477.9	478.0	478.1	478.2	478.2	479.0	479.7
177.5°	480.5	480.0	479.5	479.1	479.0	479.0	479.2	479.3	479.4	479.9	480.5
180°	480.0	480.0	480.0	480.0	480.0	480.0	480.0	480.0	480.0	480.0	480.0



TEST NUMBER: P333055-927

CATALOG NUMBER: S124RDIW-S795D470U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7
2.5°	1096.9	1098.3	1099.3	1102.6	1103.0	1106.0	1103.0
5°	1187.6	1193.6	1202.8	1212.1	1213.0	1218.9	1208.3
7.5°	1289.4	1303.1	1311.6	1326.6	1332.5	1336.3	1330.2
10°	1359.5	1372.2	1394.6	1405.5	1416.4	1418.2	1413.1
12.5°	1427.4	1447.4	1465.0	1485.7	1485.2	1500.1	1494.6
15°	1517.6	1538.2	1562.7	1585.8	1594.3	1594.3	1601.0
17.5°	1581.9	1619.8	1645.0	1663.3	1683.1	1686.6	1684.3
20°	1625.4	1666.3	1693.3	1716.8	1730.4	1734.1	1734.1
22.5°	1657.8	1692.6	1718.9	1740.1	1751.2	1755.7	1754.4
25°	1680.2	1710.1	1726.1	1732.4	1735.4	1734.6	1726.6
27.5°	1649.5	1648.1	1638.1	1618.7	1604.1	1595.2	1585.2
30°	1590.9	1569.0	1543.7	1515.8	1480.0	1452.7	1444.2
32.5°	1503.6	1454.4	1411.6	1365.2	1326.7	1299.3	1287.9
35°	1334.7	1256.8	1193.2	1137.6	1097.1	1071.8	1063.4
37.5°	1134.3	1058.9	980.2	926.2	892.7	867.1	857.6
40°	1006.9	924.8	856.1	805.6	771.0	746.2	745.8
42.5°	890.7	812.2	747.6	711.1	673.9	657.5	657.4
45°	729.3	666.5	611.7	583.1	560.8	547.3	543.5
47.5°	603.8	551.9	515.4	492.6	474.4	465.8	460.3
50°	533.4	487.9	458.8	439.0	428.9	418.0	417.1
52.5°	474.8	438.0	415.3	399.3	386.4	379.9	380.0
55°	398.9	369.9	353.9	341.7	331.6	326.5	324.4
57.5°	336.1	314.3	302.7	291.4	287.2	283.2	282.1
60°	297.0	282.3	271.3	262.4	256.2	254.9	254.4
62.5°	264.7	249.2	241.7	234.8	230.2	228.2	227.5
65°	218.2	206.8	200.1	194.6	193.0	190.0	189.6
67.5°	175.9	169.1	164.6	160.9	158.6	158.4	158.4
70°	150.0	146.2	142.4	140.3	139.0	138.2	138.2
72.5°	127.8	124.9	121.8	120.7	120.5	119.6	119.3
75°	97.4	94.3	94.8	92.7	91.0	88.9	87.6
77.5°	69.0	66.9	66.5	66.2	64.8	64.6	65.2
80°	53.5	51.4	51.0	51.4	51.0	49.7	49.7
82.5°	40.7	38.9	38.5	38.3	37.9	38.3	37.5
85°	21.9	21.1	21.1	21.1	21.9	21.5	21.1
87.5°	9.6	9.3	9.7	9.5	9.5	9.2	9.6
90°	9.3	9.8	10.1	10.3	10.5	10.6	10.8
92.5°	9.0	9.5	9.7	9.8	9.8	9.9	9.9
95°	9.3	9.8	10.1	10.1	10.2	10.3	10.4
97.5°	9.6	9.7	9.7	9.8	9.9	10.0	10.1
100°	11.7	10.4	9.7	9.8	9.9	10.0	10.1
102.5°	32.2	17.6	10.3	10.3	10.3	10.3	10.4
105°	114.2	114.9	113.8	110.9	108.1	105.2	102.3
107.5°	140.7	141.1	141.4	141.7	142.0	142.3	142.6
110°	158.8	159.0	159.1	159.4	159.6	159.9	160.1



TEST NUMBER: P333055-927

CATALOG NUMBER: S124RDIW-S795D470U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	176.3	176.3	176.4	176.7	177.1	177.4	177.6
115°	203.0	203.1	203.2	203.2	203.2	203.2	203.2
117.5°	229.4	229.3	229.3	229.3	229.3	229.3	229.2
120°	246.1	246.2	246.2	246.1	245.9	245.7	245.6
122.5°	262.2	262.3	262.3	262.1	262.0	261.8	261.7
125°	285.0	285.3	285.4	285.5	285.6	285.7	285.7
127.5°	307.3	307.3	307.2	307.1	307.0	307.0	307.0
130°	321.2	321.3	321.3	321.3	321.3	321.3	321.3
132.5°	334.7	334.8	334.8	334.7	334.7	334.6	334.5
135°	353.4	353.6	353.7	353.9	354.0	354.2	354.3
137.5°	371.2	371.5	371.5	371.5	371.4	371.4	371.3
140°	382.4	382.6	382.8	382.9	382.9	383.0	383.1
142.5°	392.5	392.7	392.8	392.8	392.8	392.8	392.8
145°	407.0	407.1	407.2	407.3	407.5	407.7	407.8
147.5°	419.8	419.9	419.9	420.0	420.1	420.2	420.3
150°	427.9	427.9	428.0	428.1	428.2	428.3	428.3
152.5°	435.2	435.4	435.4	435.4	435.3	435.2	435.2
155°	445.0	445.4	445.4	445.2	445.0	444.7	444.5
157.5°	453.4	453.8	453.8	453.4	453.0	452.7	452.3
160°	458.8	459.3	459.3	458.8	458.4	457.9	457.4
162.5°	463.1	463.6	463.6	463.0	462.5	461.9	461.4
165°	469.4	470.0	469.9	469.2	468.5	467.8	467.1
167.5°	473.9	474.6	474.5	473.7	472.9	472.1	471.3
170°	476.5	477.2	477.1	476.3	475.5	474.7	473.9
172.5°	478.2	478.9	478.8	477.9	477.1	476.2	475.3
175°	480.4	481.1	480.9	480.0	479.0	478.1	477.1
177.5°	480.9	481.5	481.3	480.6	479.8	479.0	478.3
180°	480.0	480.0	480.0	480.0	480.0	480.0	480.0

(END OF REPORT)