

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332834-935

Luminaire Tested: **S124DIW-S1020D1560U935-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332834-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S1020D1560U935-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8474.7 lumens
Efficiency: N/A
Efficacy: 110.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 76.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332834-935

CATALOG NUMBER: S124DIW-S1020D1560U935-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332834-935

CATALOG NUMBER: S124DIW-S1020D1560U935-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	106	106	106	106	97	97	97	97	81	81	81		65	65	65		52	52	52	45
1	97	92	88	85	88	85	81	78	71	68	66		58	56	54		45	44	43	38
2	88	81	74	69	80	74	69	64	62	58	55		50	48	45		40	38	37	32
3	80	71	64	58	73	65	59	54	54	50	46		45	41	38		35	33	31	27
4	73	63	55	49	67	58	51	46	48	43	39		40	36	33		32	29	27	23
5	67	56	48	42	61	51	44	39	43	38	34		36	32	28		29	26	23	20
6	62	50	42	36	57	46	39	34	39	33	29		32	28	25		26	23	21	18
7	57	45	37	32	52	42	35	30	35	30	26		29	25	22		24	21	18	16
8	53	41	33	28	49	38	31	26	32	27	23		27	23	20		22	19	16	14
9	49	37	30	25	45	35	28	23	29	24	20		25	21	18		20	17	15	13
10	46	34	27	22	42	32	25	21	27	22	18		23	19	16		19	16	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11994	11994	11994
5°	12030	11885	11972
10°	11954	11788	11847
15°	11810	11621	11651
20°	11618	11413	11424
25°	11399	11176	11144
30°	11130	10897	10797
35°	10852	10606	10465
40°	10564	10275	10086
45°	10261	9949	9758
50°	9928	9658	9359
55°	9568	9282	8981
60°	9206	8861	8591
65°	8800	8458	8118
70°	8344	7924	7615
75°	7648	7277	7093
80°	6811	6527	6365
85°	5956	5734	5622



TEST NUMBER: P332834-935

CATALOG NUMBER: S124DIW-S1020D1560U935-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	139.9	1.7
10°-20°	394.2	4.7
20°-30°	580.2	6.8
30°-40°	674.5	8.0
40°-50°	674.5	8.0
50°-60°	590.0	7.0
60°-70°	438.2	5.2
70°-80°	248.9	2.9
80°-90°	76.9	0.9
90°-100°	110.7	1.3
100°-110°	328.0	3.9
110°-120°	556.7	6.6
120°-130°	734.0	8.7
130°-140°	824.4	9.7
140°-150°	810.1	9.6
150°-160°	681.3	8.0
160°-170°	453.3	5.3
170°-180°	158.7	1.9
0°-30°	1114.3	13.1
0°-40°	1788.8	21.1
0°-60°	3053.4	36.0
0°-90°	3817.4	45.0
90°-120°	995.4	11.7
90°-150°	3363.9	39.7
90°-180°	4657.0	55.0
0°-180°	8474.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1486	1486	1486	1486	1486	
5°	1484	1479	1467	1479	1477	141
15°	1413	1408	1390	1397	1394	398
25°	1280	1271	1255	1256	1251	588
35°	1101	1092	1076	1068	1062	688
45°	899	890	871	859	855	693
55°	680	675	660	646	638	609
65°	461	454	443	431	425	456
75°	245	239	233	229	227	261
85°	64	64	62	62	61	71
90°	4	18	29	36	39	8
95°	78	89	99	102	102	87
105°	302	304	309	313	317	321
115°	566	566	563	562	561	558
125°	824	824	823	820	818	734
135°	1063	1071	1071	1068	1064	822
145°	1292	1297	1298	1297	1293	808
155°	1480	1480	1479	1483	1479	681
165°	1611	1607	1605	1612	1607	454
175°	1676	1670	1668	1676	1668	159
180°	1679	1679	1679	1679	1679	



TEST NUMBER: P332834-935

CATALOG NUMBER: S124DIW-S1020D1560U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1485.7	1485.7	1485.7	1485.7	1485.7	1485.7	1485.7	1485.7	1485.7	1485.7	1485.7
2.5°	1489.4	1488.8	1488.2	1487.5	1486.9	1485.4	1483.1	1480.7	1478.4	1476.1	1478.3
5°	1484.5	1483.4	1482.4	1481.3	1480.2	1478.3	1475.3	1472.4	1469.6	1466.6	1469.6
7.5°	1470.7	1469.6	1468.5	1467.5	1466.5	1464.3	1461.0	1457.8	1454.6	1451.4	1453.7
10°	1458.3	1457.2	1456.1	1455.1	1454.1	1451.8	1448.4	1444.9	1441.5	1438.0	1440.1
12.5°	1442.1	1441.1	1439.9	1438.9	1437.9	1435.5	1431.8	1428.2	1424.5	1420.9	1423.2
15°	1413.1	1412.0	1410.9	1409.9	1408.8	1406.3	1402.3	1398.4	1394.4	1390.4	1392.0
17.5°	1378.0	1376.7	1375.4	1374.1	1372.8	1370.2	1366.4	1362.7	1358.9	1355.2	1356.2
20°	1352.3	1351.0	1349.7	1348.3	1347.0	1344.4	1340.4	1336.4	1332.5	1328.5	1329.3
22.5°	1324.7	1322.9	1321.2	1319.5	1317.8	1314.8	1310.9	1306.9	1303.0	1299.0	1300.5
25°	1279.7	1277.9	1276.0	1274.1	1272.3	1269.5	1265.8	1262.1	1258.4	1254.7	1255.0
27.5°	1228.3	1226.4	1224.4	1222.5	1220.6	1218.0	1214.5	1211.1	1207.6	1204.2	1203.6
30°	1194.0	1191.9	1189.7	1187.7	1185.5	1182.8	1179.3	1175.9	1172.4	1169.0	1167.9
32.5°	1157.8	1155.9	1154.0	1152.1	1150.2	1147.4	1143.8	1140.1	1136.4	1132.8	1131.5
35°	1101.1	1099.3	1097.4	1095.6	1093.7	1091.0	1087.3	1083.6	1079.9	1076.2	1074.3
37.5°	1041.4	1039.7	1038.0	1036.3	1034.6	1031.8	1027.8	1023.8	1019.9	1015.9	1013.9
40°	1002.4	1000.2	998.1	996.0	993.9	990.8	986.9	982.9	979.0	975.0	972.3
42.5°	960.4	959.2	957.9	956.7	955.4	952.5	948.1	943.7	939.4	935.0	931.9
45°	898.8	896.9	895.1	893.2	891.4	888.3	884.1	879.9	875.6	871.4	868.5
47.5°	834.2	833.0	831.7	830.4	829.1	826.6	822.7	818.7	814.9	810.9	807.6
50°	790.5	789.4	788.3	787.3	786.2	783.9	780.2	776.4	772.7	769.0	765.3
52.5°	747.6	746.3	745.0	743.8	742.5	739.9	736.0	732.1	728.1	724.3	721.0
55°	679.8	678.9	678.1	677.3	676.6	674.3	670.6	666.9	663.2	659.5	656.3
57.5°	615.0	614.1	613.2	612.3	611.4	609.1	605.5	601.8	598.1	594.5	591.5
60°	570.2	568.9	567.6	566.3	564.9	562.6	559.1	555.7	552.2	548.8	546.4
62.5°	526.4	525.3	524.2	523.1	521.9	519.6	515.9	512.3	508.6	505.0	502.8
65°	460.7	459.3	458.1	456.8	455.4	453.4	450.7	448.2	445.5	442.8	440.2
67.5°	394.5	393.3	392.1	390.9	389.6	387.8	385.2	382.7	380.1	377.6	375.1
70°	353.5	351.7	349.8	348.0	346.1	344.1	342.1	339.9	337.9	335.7	333.6
72.5°	309.8	307.9	306.1	304.2	302.4	300.6	298.9	297.2	295.5	293.8	292.1
75°	245.2	243.9	242.5	241.3	240.0	238.6	237.3	236.0	234.6	233.3	232.3
77.5°	183.6	183.0	182.4	181.8	181.2	180.4	179.2	178.1	176.8	175.7	175.4
80°	146.5	145.6	144.8	144.0	143.3	142.6	142.1	141.5	141.0	140.4	139.9
82.5°	110.2	109.9	109.5	109.1	108.7	108.5	108.4	108.3	108.2	108.1	107.8
85°	64.3	64.3	64.3	64.3	64.3	64.1	63.5	62.9	62.4	61.9	61.9
87.5°	25.6	26.0	26.3	26.8	27.2	27.6	27.8	28.1	28.3	28.6	28.9
90°	3.9	7.1	10.2	13.4	16.6	19.4	21.6	23.9	26.3	28.6	30.3
92.5°	27.8	31.4	35.0	38.7	42.4	44.9	46.6	48.2	49.8	51.4	52.4
95°	77.9	80.5	83.1	85.7	88.3	90.6	92.6	94.6	96.7	98.7	99.5
97.5°	136.0	138.1	140.2	142.3	144.4	146.6	149.0	151.3	153.7	156.0	157.0
100°	181.8	182.9	184.1	185.2	186.4	188.2	190.9	193.5	196.0	198.6	199.2
102.5°	229.5	230.0	230.5	230.9	231.4	232.8	235.1	237.5	239.9	242.3	243.1
105°	302.5	302.8	303.1	303.3	303.7	304.4	305.5	306.7	307.8	309.0	309.9
107.5°	379.1	379.4	379.8	380.1	380.5	380.7	380.9	381.1	381.3	381.4	382.2
110°	431.0	431.6	432.1	432.7	433.3	433.5	433.2	432.9	432.6	432.3	431.7



TEST NUMBER: P332834-935

CATALOG NUMBER: S124DIW-S1020D1560U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	485.0	485.2	485.3	485.3	485.5	485.3	484.7	484.2	483.7	483.2	483.1
115°	566.0	566.0	566.0	566.0	566.0	565.8	565.2	564.6	564.0	563.4	563.2
117.5°	642.4	642.6	642.8	643.1	643.3	643.3	642.8	642.4	642.0	641.6	640.6
120°	693.3	694.4	695.6	696.7	697.8	698.0	697.2	696.3	695.4	694.6	693.1
122.5°	746.2	746.7	747.2	747.6	748.0	748.1	747.7	747.3	746.9	746.5	745.5
125°	824.4	824.4	824.4	824.4	824.4	824.2	824.0	823.6	823.4	823.1	822.5
127.5°	895.3	896.1	897.0	897.9	898.7	899.0	898.5	898.0	897.6	897.1	896.5
130°	945.1	946.0	946.8	947.7	948.6	949.0	949.0	949.0	949.0	949.0	948.5
132.5°	996.0	996.7	997.3	997.9	998.6	998.8	998.5	998.3	998.1	997.8	997.3
135°	1063.2	1065.0	1066.7	1068.5	1070.2	1071.1	1071.1	1071.1	1071.1	1071.1	1070.5
137.5°	1136.5	1137.3	1138.1	1138.9	1139.7	1140.4	1140.8	1141.3	1141.8	1142.2	1141.4
140°	1185.3	1185.9	1186.5	1187.1	1187.6	1187.9	1187.9	1187.9	1187.9	1187.9	1187.6
142.5°	1229.9	1230.5	1231.1	1231.7	1232.3	1232.4	1232.2	1232.0	1231.7	1231.5	1231.5
145°	1291.8	1292.9	1294.1	1295.2	1296.4	1297.1	1297.4	1297.7	1298.0	1298.2	1298.0
147.5°	1353.1	1354.4	1355.8	1357.2	1358.6	1359.2	1358.9	1358.7	1358.5	1358.2	1358.0
150°	1390.4	1391.5	1392.8	1393.9	1395.1	1395.6	1395.6	1395.6	1395.6	1395.6	1395.6
152.5°	1425.7	1426.4	1427.1	1427.8	1428.5	1429.0	1429.2	1429.4	1429.7	1429.9	1430.6
155°	1480.0	1480.0	1480.0	1480.0	1480.0	1479.9	1479.5	1479.3	1479.0	1478.7	1479.9
157.5°	1525.7	1525.2	1524.7	1524.1	1523.6	1523.4	1523.3	1523.2	1523.2	1523.1	1524.0
160°	1552.7	1552.4	1552.1	1551.9	1551.5	1551.3	1551.0	1550.7	1550.4	1550.1	1551.0
162.5°	1577.6	1576.9	1576.1	1575.4	1574.6	1574.1	1573.8	1573.6	1573.2	1573.0	1574.5
165°	1611.1	1610.2	1609.4	1608.5	1607.7	1607.0	1606.4	1605.8	1605.2	1604.6	1606.4
167.5°	1636.8	1635.6	1634.4	1633.2	1632.0	1631.4	1631.5	1631.5	1631.6	1631.7	1633.4
170°	1651.4	1649.9	1648.5	1647.0	1645.6	1645.0	1645.3	1645.6	1645.9	1646.1	1647.9
172.5°	1661.7	1660.5	1659.3	1658.1	1656.9	1656.3	1656.4	1656.5	1656.5	1656.6	1658.5
175°	1676.0	1674.6	1673.2	1671.7	1670.3	1669.4	1669.1	1668.8	1668.5	1668.3	1670.3
177.5°	1680.7	1679.6	1678.4	1677.2	1676.1	1675.5	1675.5	1675.5	1675.5	1675.5	1677.1
180°	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6



TEST NUMBER: P332834-935

CATALOG NUMBER: S124DIW-S1020D1560U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1485.7	1485.7	1485.7	1485.7	1485.7	1485.7	1485.7	1485.7
2.5°	1480.3	1482.5	1484.6	1485.6	1485.3	1485.1	1484.9	1484.7
5°	1472.4	1475.3	1478.3	1479.5	1478.9	1478.3	1477.8	1477.3
7.5°	1456.0	1458.4	1460.7	1461.7	1461.4	1461.0	1460.7	1460.4
10°	1442.3	1444.4	1446.5	1447.3	1446.7	1446.2	1445.7	1445.2
12.5°	1425.6	1427.9	1430.2	1431.0	1430.3	1429.5	1428.7	1428.1
15°	1393.6	1395.2	1396.8	1397.1	1396.4	1395.6	1394.8	1394.0
17.5°	1357.2	1358.2	1359.2	1359.4	1358.9	1358.4	1357.9	1357.3
20°	1330.1	1330.9	1331.7	1331.8	1331.3	1330.8	1330.2	1329.7
22.5°	1301.8	1303.3	1304.7	1304.9	1304.0	1303.0	1302.1	1301.1
25°	1255.3	1255.5	1255.8	1255.3	1254.3	1253.3	1252.2	1251.1
27.5°	1203.0	1202.3	1201.7	1200.8	1199.4	1198.1	1196.7	1195.4
30°	1166.9	1165.8	1164.8	1163.6	1162.3	1160.9	1159.6	1158.3
32.5°	1130.2	1129.0	1127.7	1126.4	1125.1	1123.8	1122.5	1121.1
35°	1072.5	1070.6	1068.8	1067.1	1065.8	1064.5	1063.2	1061.9
37.5°	1011.8	1009.9	1007.9	1006.0	1004.3	1002.5	1000.7	999.0
40°	969.7	967.0	964.4	962.4	961.0	959.8	958.5	957.1
42.5°	928.8	925.7	922.6	920.7	919.8	918.9	918.0	917.1
45°	865.6	862.6	859.7	857.9	857.1	856.4	855.5	854.7
47.5°	804.3	801.1	797.8	795.1	793.2	791.1	789.1	787.1
50°	761.6	757.9	754.2	751.6	749.9	748.4	746.8	745.2
52.5°	717.7	714.4	711.1	708.5	706.5	704.5	702.5	700.4
55°	653.2	650.0	646.8	644.5	642.8	641.3	639.6	638.1
57.5°	588.5	585.5	582.5	580.1	578.6	577.1	575.6	574.0
60°	544.1	541.7	539.2	537.4	536.1	534.8	533.5	532.1
62.5°	500.7	498.4	496.3	494.6	493.3	491.9	490.6	489.3
65°	437.6	434.9	432.2	430.2	429.0	427.7	426.3	425.0
67.5°	372.6	370.0	367.5	366.0	365.6	365.2	364.9	364.5
70°	331.5	329.3	327.3	325.8	325.0	324.2	323.4	322.6
72.5°	290.4	288.7	287.1	285.8	285.0	284.2	283.4	282.6
75°	231.2	230.1	229.1	228.4	228.2	227.9	227.6	227.4
77.5°	175.0	174.8	174.4	173.9	173.2	172.5	171.9	171.2
80°	139.4	138.9	138.4	137.9	137.7	137.4	137.2	136.9
82.5°	107.5	107.1	106.9	106.5	106.2	106.0	105.7	105.5
85°	61.9	61.9	61.9	61.7	61.5	61.2	61.0	60.7
87.5°	29.3	29.6	30.0	30.2	30.3	30.4	30.6	30.7
90°	32.0	33.8	35.5	36.7	37.2	37.8	38.4	38.9
92.5°	53.5	54.5	55.5	56.2	56.6	56.9	57.3	57.6
95°	100.4	101.3	102.1	102.5	102.5	102.5	102.5	102.5
97.5°	158.2	159.2	160.2	160.7	160.7	160.7	160.7	160.7
100°	199.8	200.4	201.0	201.2	201.2	201.2	201.2	201.2
102.5°	243.8	244.7	245.5	246.0	246.2	246.5	246.7	246.9
105°	310.7	311.6	312.5	313.3	314.2	315.0	315.9	316.8
107.5°	383.1	383.8	384.7	385.0	385.0	385.0	384.9	384.8
110°	431.2	430.6	430.0	430.2	431.0	431.9	432.7	433.6



TEST NUMBER: P332834-935

CATALOG NUMBER: S124DIW-S1020D1560U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	482.9	482.8	482.8	482.8	482.9	483.1	483.3	483.5
115°	562.8	562.6	562.3	562.0	561.7	561.5	561.1	560.9
117.5°	639.6	638.7	637.7	636.9	636.3	635.8	635.2	634.6
120°	691.6	690.3	688.8	688.4	689.0	689.5	690.1	690.7
122.5°	744.5	743.6	742.6	741.6	740.5	739.5	738.5	737.4
125°	821.9	821.4	820.8	820.2	819.6	819.1	818.5	817.9
127.5°	896.0	895.4	894.8	894.2	893.8	893.4	892.9	892.4
130°	947.9	947.3	946.7	945.8	944.7	943.6	942.4	941.2
132.5°	996.7	996.1	995.5	995.0	994.5	994.1	993.6	993.2
135°	1069.9	1069.4	1068.8	1068.0	1067.1	1066.3	1065.4	1064.5
137.5°	1140.7	1140.0	1139.2	1138.9	1139.1	1139.3	1139.4	1139.6
140°	1187.3	1187.1	1186.7	1186.5	1186.2	1185.9	1185.6	1185.3
142.5°	1231.4	1231.3	1231.3	1231.2	1231.1	1231.1	1231.1	1231.0
145°	1297.7	1297.4	1297.1	1296.5	1295.6	1294.8	1293.9	1293.0
147.5°	1357.8	1357.5	1357.3	1357.0	1356.8	1356.5	1356.2	1355.9
150°	1395.6	1395.6	1395.6	1395.5	1395.2	1394.9	1394.6	1394.3
152.5°	1431.2	1431.9	1432.6	1432.6	1431.8	1431.2	1430.4	1429.6
155°	1481.0	1482.1	1483.3	1483.3	1482.1	1481.0	1479.9	1478.7
157.5°	1524.8	1525.7	1526.6	1526.5	1525.5	1524.6	1523.5	1522.6
160°	1551.9	1552.7	1553.6	1553.2	1551.9	1550.4	1548.9	1547.5
162.5°	1576.1	1577.6	1579.2	1579.2	1577.8	1576.4	1574.9	1573.5
165°	1608.1	1609.8	1611.5	1611.9	1610.7	1609.6	1608.3	1607.2
167.5°	1635.1	1636.8	1638.6	1638.6	1636.8	1635.0	1633.1	1631.3
170°	1649.7	1651.4	1653.1	1652.9	1651.0	1648.9	1646.9	1644.9
172.5°	1660.5	1662.4	1664.4	1664.4	1662.3	1660.4	1658.3	1656.3
175°	1672.3	1674.3	1676.4	1676.4	1674.3	1672.3	1670.3	1668.3
177.5°	1678.8	1680.3	1682.0	1681.9	1680.0	1678.2	1676.4	1674.5
180°	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6

(END OF REPORT)