

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332863-830

Luminaire Tested: **S124DIW-S1195D1560U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332863-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S1195D1560U830-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1560 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10704.1 lumens
Efficiency: N/A
Efficacy: 129.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 82.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332863-830

CATALOG NUMBER: S124DIW-S1195D1560U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332863-830

CATALOG NUMBER: S124DIW-S1195D1560U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	81	81	81	65	65	65	52	52	52	45
1	97	92	88	85	88	85	81	78	71	68	66	58	56	54	46	44	43	38
2	88	81	74	69	80	74	69	64	62	58	55	51	48	45	40	38	37	32
3	80	71	64	58	73	65	59	54	55	50	46	45	41	38	35	33	31	27
4	73	63	55	49	67	58	51	46	48	43	39	40	36	33	32	29	27	23
5	67	56	48	42	61	51	44	39	43	38	34	36	32	28	29	26	23	20
6	62	50	42	36	57	46	39	34	39	33	29	32	28	25	26	23	21	18
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	24	21	18	16
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	16	14
9	49	37	30	25	45	35	28	23	29	24	20	25	21	18	20	17	15	13
10	46	34	27	22	42	32	25	21	27	22	18	23	19	16	19	16	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15163	15163	15163
5°	15209	15027	15135
10°	15114	14905	14978
15°	14931	14692	14730
20°	14689	14430	14442
25°	14412	14130	14091
30°	14072	13778	13651
35°	13720	13409	13232
40°	13354	12991	12752
45°	12973	12578	12337
50°	12552	12210	11833
55°	12096	11736	11354
60°	11641	11202	10863
65°	11127	10695	10264
70°	10551	10017	9626
75°	9669	9201	8968
80°	8605	8257	8047
85°	7521	7243	7104



TEST NUMBER: P332863-830

CATALOG NUMBER: S124DIW-S1195D1560U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	176.9	1.7
10°-20°	498.4	4.7
20°-30°	733.6	6.9
30°-40°	852.8	8.0
40°-50°	852.8	8.0
50°-60°	746.0	7.0
60°-70°	554.0	5.2
70°-80°	314.7	2.9
80°-90°	96.3	0.9
90°-100°	65.0	0.6
100°-110°	414.4	3.9
110°-120°	792.8	7.4
120°-130°	1006.4	9.4
130°-140°	1076.8	10.1
140°-150°	1006.9	9.4
150°-160°	812.0	7.6
160°-170°	523.7	4.9
170°-180°	180.5	1.7
0°-30°	1408.8	13.2
0°-40°	2261.6	21.1
0°-60°	3860.5	36.1
0°-90°	4825.5	45.1
90°-120°	1272.2	11.9
90°-150°	4362.3	40.8
90°-180°	5879.0	54.9
0°-180°	10704.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1878	1878	1878	1878	1878	
5°	1877	1870	1854	1870	1868	178
15°	1786	1780	1758	1766	1762	503
25°	1618	1607	1586	1587	1582	744
35°	1392	1381	1361	1350	1343	870
45°	1136	1125	1102	1086	1081	876
55°	859	854	834	816	807	769
65°	582	575	560	545	537	577
75°	310	302	295	289	288	329
85°	81	81	78	78	77	90
90°	4	20	31	40	43	8
95°	78	33	31	39	41	100
105°	428	436	444	453	405	448
115°	799	803	802	804	805	786
125°	1123	1128	1126	1130	1131	1002
135°	1393	1392	1397	1400	1403	1073
145°	1606	1610	1610	1612	1615	1003
155°	1761	1762	1758	1763	1760	812
165°	1858	1851	1851	1861	1849	525
175°	1900	1892	1893	1904	1889	181
180°	1900	1900	1900	1900	1900	



TEST NUMBER: P332863-830

CATALOG NUMBER: S124DIW-S1195D1560U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1878.3	1878.3	1878.3	1878.3	1878.3	1878.3	1878.3	1878.3	1878.3	1878.3	1878.3
2.5°	1883.1	1882.4	1881.5	1880.7	1879.9	1878.0	1875.1	1872.2	1869.3	1866.3	1869.0
5°	1876.8	1875.5	1874.2	1872.8	1871.5	1869.0	1865.3	1861.6	1857.9	1854.3	1857.9
7.5°	1859.4	1858.0	1856.7	1855.3	1854.0	1851.3	1847.2	1843.1	1839.1	1834.9	1838.0
10°	1843.7	1842.4	1841.1	1839.7	1838.3	1835.5	1831.2	1826.8	1822.5	1818.2	1820.8
12.5°	1823.3	1821.9	1820.5	1819.2	1817.9	1814.9	1810.3	1805.7	1801.1	1796.5	1799.4
15°	1786.5	1785.2	1783.9	1782.5	1781.1	1778.0	1772.9	1767.9	1762.9	1757.9	1759.9
17.5°	1742.3	1740.6	1738.9	1737.3	1735.6	1732.4	1727.6	1722.9	1718.2	1713.4	1714.7
20°	1709.8	1708.1	1706.4	1704.8	1703.1	1699.7	1694.7	1689.7	1684.7	1679.6	1680.6
22.5°	1674.8	1672.6	1670.5	1668.2	1666.0	1662.4	1657.4	1652.4	1647.4	1642.3	1644.2
25°	1618.0	1615.6	1613.3	1610.9	1608.5	1605.1	1600.3	1595.7	1591.0	1586.3	1586.7
27.5°	1552.9	1550.5	1548.1	1545.7	1543.3	1539.9	1535.6	1531.3	1526.9	1522.5	1521.7
30°	1509.6	1506.9	1504.2	1501.6	1498.9	1495.3	1491.0	1486.7	1482.3	1478.0	1476.7
32.5°	1463.9	1461.4	1459.1	1456.6	1454.2	1450.7	1446.0	1441.4	1436.8	1432.2	1430.6
35°	1392.2	1389.9	1387.5	1385.2	1382.8	1379.3	1374.6	1370.0	1365.3	1360.6	1358.2
37.5°	1316.6	1314.5	1312.4	1310.2	1308.1	1304.5	1299.5	1294.5	1289.4	1284.4	1281.9
40°	1267.2	1264.6	1261.9	1259.2	1256.6	1252.7	1247.7	1242.6	1237.7	1232.7	1229.3
42.5°	1214.3	1212.7	1211.1	1209.5	1207.9	1204.3	1198.7	1193.2	1187.6	1182.0	1178.2
45°	1136.3	1134.0	1131.6	1129.3	1127.0	1123.1	1117.8	1112.4	1107.0	1101.7	1098.1
47.5°	1054.7	1053.1	1051.5	1049.9	1048.3	1045.1	1040.1	1035.2	1030.2	1025.3	1021.2
50°	999.4	998.1	996.6	995.3	994.0	991.0	986.3	981.7	976.9	972.2	967.6
52.5°	945.2	943.6	942.0	940.4	938.8	935.5	930.6	925.6	920.7	915.7	911.5
55°	859.4	858.4	857.4	856.4	855.4	852.5	847.8	843.2	838.5	833.8	829.8
57.5°	777.5	776.4	775.2	774.1	773.0	770.1	765.4	760.8	756.2	751.6	747.8
60°	721.0	719.3	717.6	716.0	714.3	711.2	706.9	702.6	698.1	693.8	690.8
62.5°	665.5	664.1	662.7	661.3	660.0	657.0	652.3	647.7	643.1	638.5	635.7
65°	582.5	580.8	579.1	577.4	575.8	573.3	570.0	566.6	563.3	559.9	556.6
67.5°	498.8	497.3	495.7	494.2	492.7	490.2	487.0	483.8	480.6	477.4	474.2
70°	447.0	444.7	442.3	440.0	437.6	435.2	432.4	429.8	427.1	424.4	421.8
72.5°	391.6	389.3	386.9	384.6	382.3	380.0	377.9	375.7	373.6	371.5	369.3
75°	310.0	308.4	306.7	305.0	303.3	301.7	300.0	298.3	296.7	295.0	293.7
77.5°	232.1	231.3	230.6	229.9	229.1	228.0	226.6	225.1	223.7	222.2	221.8
80°	185.1	184.1	183.1	182.1	181.2	180.3	179.6	178.9	178.2	177.6	176.9
82.5°	139.4	138.9	138.5	138.0	137.5	137.2	137.0	137.0	136.8	136.7	136.3
85°	81.2	81.2	81.2	81.2	81.2	81.0	80.3	79.6	78.9	78.2	78.2
87.5°	32.1	32.6	33.0	33.5	33.8	34.2	34.4	34.7	34.9	35.2	35.5
90°	4.2	7.7	11.2	14.7	18.2	21.2	23.7	26.2	28.7	31.3	33.2
92.5°	17.9	18.1	18.3	18.5	18.7	20.0	22.5	25.1	27.6	30.2	32.0
95°	78.1	67.4	56.7	46.0	35.3	30.0	30.3	30.6	30.9	31.3	33.2
97.5°	166.0	172.7	179.4	186.2	192.8	178.5	143.3	108.0	72.8	37.5	37.7
100°	233.1	238.8	244.5	250.2	255.8	236.9	193.3	149.7	106.1	62.6	57.2
102.5°	308.1	312.4	316.5	320.7	324.8	324.0	318.4	312.7	307.0	301.3	243.4
105°	427.8	429.7	431.6	433.6	435.5	437.2	438.8	440.4	441.9	443.5	446.3
107.5°	538.9	540.0	540.9	541.9	542.8	544.3	546.5	548.7	550.7	552.9	554.3
110°	614.1	615.0	616.0	616.9	617.8	619.3	621.1	623.0	624.9	626.8	627.5



TEST NUMBER: P332863-830

CATALOG NUMBER: S124DIW-S1195D1560U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	686.8	688.5	690.2	691.9	693.6	694.9	695.8	696.7	697.6	698.5	698.3
115°	798.8	799.7	800.7	801.6	802.6	803.0	802.6	802.3	802.0	801.6	802.3
117.5°	899.8	901.0	902.3	903.5	904.8	905.8	906.4	907.2	907.9	908.5	908.4
120°	968.0	969.2	970.5	971.8	973.0	973.5	973.2	972.9	972.5	972.2	972.9
122.5°	1031.6	1032.4	1033.1	1033.9	1034.7	1035.3	1035.8	1036.1	1036.6	1037.1	1037.5
125°	1122.9	1124.2	1125.4	1126.7	1127.9	1128.2	1127.7	1127.0	1126.3	1125.8	1126.7
127.5°	1209.3	1209.7	1209.9	1210.2	1210.6	1211.4	1213.0	1214.4	1215.8	1217.3	1217.1
130°	1265.1	1265.4	1265.6	1266.0	1266.3	1267.0	1267.9	1268.9	1269.8	1270.7	1271.0
132.5°	1316.2	1316.7	1317.4	1318.0	1318.5	1319.4	1320.6	1321.7	1323.0	1324.2	1324.5
135°	1393.0	1392.6	1392.3	1392.0	1391.7	1392.1	1393.5	1394.7	1396.0	1397.2	1397.9
137.5°	1460.9	1461.0	1461.1	1461.3	1461.4	1462.2	1463.6	1465.0	1466.3	1467.7	1468.4
140°	1505.2	1505.9	1506.6	1507.1	1507.8	1508.4	1509.0	1509.7	1510.3	1510.9	1511.9
142.5°	1545.0	1546.1	1547.4	1548.5	1549.6	1550.4	1550.8	1551.1	1551.5	1551.9	1552.6
145°	1606.2	1607.1	1608.1	1609.0	1610.0	1610.4	1610.4	1610.4	1610.4	1610.4	1610.7
147.5°	1654.8	1656.5	1658.3	1660.1	1661.9	1662.6	1662.3	1662.0	1661.6	1661.3	1661.6
150°	1690.1	1691.3	1692.5	1693.8	1695.1	1695.5	1695.3	1695.0	1694.6	1694.3	1694.3
152.5°	1719.6	1720.6	1721.6	1722.6	1723.6	1723.9	1723.3	1722.7	1722.1	1721.6	1722.1
155°	1761.1	1761.4	1761.7	1762.1	1762.4	1762.1	1761.1	1760.2	1759.3	1758.2	1759.5
157.5°	1796.1	1795.9	1795.7	1795.5	1795.4	1794.7	1793.6	1792.5	1791.5	1790.4	1792.1
160°	1816.6	1815.6	1814.7	1813.7	1812.8	1812.1	1811.8	1811.5	1811.2	1810.8	1812.8
162.5°	1834.8	1833.5	1832.3	1831.2	1829.9	1829.2	1828.8	1828.5	1828.2	1827.9	1829.8
165°	1857.8	1856.1	1854.6	1853.0	1851.4	1850.7	1850.7	1850.7	1850.7	1850.7	1853.1
167.5°	1875.9	1874.3	1872.6	1871.0	1869.3	1868.5	1868.3	1868.1	1867.9	1867.7	1870.5
170°	1886.2	1884.3	1882.4	1880.5	1878.6	1877.8	1878.1	1878.5	1878.8	1879.1	1881.6
172.5°	1893.0	1891.1	1889.2	1887.3	1885.5	1884.6	1885.0	1885.3	1885.6	1885.9	1888.4
175°	1900.4	1898.5	1896.6	1894.7	1892.8	1892.1	1892.3	1892.6	1893.0	1893.3	1896.1
177.5°	1903.8	1902.1	1900.3	1898.5	1896.8	1896.1	1896.6	1897.1	1897.6	1898.1	1900.2
180°	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4



TEST NUMBER: P332863-830

CATALOG NUMBER: S124DIW-S1195D1560U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1878.3	1878.3	1878.3	1878.3	1878.3	1878.3	1878.3	1878.3
2.5°	1871.6	1874.3	1877.0	1878.2	1877.9	1877.6	1877.4	1877.1
5°	1861.6	1865.3	1869.0	1870.5	1869.8	1869.2	1868.5	1867.7
7.5°	1840.9	1843.8	1846.7	1848.0	1847.7	1847.2	1846.8	1846.4
10°	1823.4	1826.2	1828.8	1829.9	1829.2	1828.5	1827.8	1827.1
12.5°	1802.3	1805.3	1808.3	1809.2	1808.3	1807.3	1806.4	1805.4
15°	1761.9	1764.0	1765.9	1766.4	1765.5	1764.4	1763.4	1762.5
17.5°	1715.9	1717.2	1718.4	1718.7	1718.1	1717.4	1716.7	1716.1
20°	1681.7	1682.6	1683.7	1683.9	1683.2	1682.5	1681.9	1681.1
22.5°	1646.0	1647.8	1649.5	1649.8	1648.7	1647.5	1646.2	1645.0
25°	1587.1	1587.3	1587.7	1587.1	1585.8	1584.5	1583.2	1581.9
27.5°	1520.9	1520.1	1519.3	1518.1	1516.4	1514.8	1513.1	1511.4
30°	1475.3	1473.9	1472.6	1471.1	1469.4	1467.8	1466.1	1464.4
32.5°	1429.0	1427.4	1425.8	1424.2	1422.5	1420.8	1419.2	1417.5
35°	1355.9	1353.6	1351.2	1349.2	1347.6	1345.9	1344.2	1342.6
37.5°	1279.3	1276.8	1274.2	1271.9	1269.7	1267.4	1265.3	1263.0
40°	1226.0	1222.6	1219.3	1216.7	1215.1	1213.4	1211.7	1210.0
42.5°	1174.3	1170.4	1166.6	1164.0	1162.9	1161.8	1160.6	1159.5
45°	1094.4	1090.7	1087.0	1084.7	1083.6	1082.6	1081.7	1080.6
47.5°	1017.0	1012.9	1008.7	1005.3	1002.8	1000.2	997.7	995.1
50°	962.9	958.2	953.6	950.2	948.2	946.2	944.1	942.2
52.5°	907.4	903.2	899.1	895.8	893.2	890.7	888.2	885.6
55°	825.8	821.8	817.7	814.7	812.8	810.8	808.7	806.7
57.5°	744.0	740.2	736.4	733.5	731.6	729.6	727.6	725.8
60°	687.8	684.9	681.8	679.5	677.8	676.1	674.5	672.8
62.5°	632.9	630.2	627.5	625.3	623.6	621.9	620.3	618.6
65°	553.2	549.9	546.5	544.0	542.3	540.6	538.9	537.3
67.5°	471.0	467.8	464.6	462.7	462.2	461.8	461.3	460.8
70°	419.1	416.4	413.7	411.9	410.9	409.9	408.9	407.8
72.5°	367.2	365.0	362.9	361.3	360.3	359.3	358.3	357.3
75°	292.3	291.0	289.6	288.8	288.5	288.1	287.8	287.5
77.5°	221.3	220.9	220.6	219.9	219.0	218.2	217.3	216.4
80°	176.3	175.6	174.9	174.5	174.1	173.7	173.4	173.1
82.5°	135.8	135.4	135.1	134.7	134.3	134.0	133.7	133.4
85°	78.2	78.2	78.2	78.1	77.8	77.4	77.1	76.7
87.5°	35.9	36.3	36.7	36.9	37.0	37.1	37.3	37.4
90°	35.1	36.9	38.8	40.2	40.7	41.4	42.0	42.6
92.5°	33.9	35.8	37.7	38.7	38.8	39.0	39.1	39.2
95°	35.1	36.9	38.8	40.0	40.2	40.6	40.9	41.2
97.5°	37.9	38.1	38.3	38.5	38.8	39.2	39.5	39.8
100°	51.8	46.5	41.1	38.5	38.8	39.2	39.5	39.8
102.5°	185.5	127.5	69.7	40.7	40.7	40.8	40.9	40.9
105°	449.1	452.0	454.9	450.5	439.2	427.8	416.5	405.1
107.5°	555.7	557.1	558.5	559.8	561.0	562.1	563.4	564.6
110°	628.1	628.8	629.3	630.2	631.1	632.1	633.0	634.0



TEST NUMBER: P332863-830

CATALOG NUMBER: S124DIW-S1195D1560U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	698.2	698.0	698.0	698.5	699.7	700.9	702.1	703.3
115°	803.0	803.5	804.2	804.6	804.6	804.6	804.6	804.6
117.5°	908.3	908.1	908.0	908.0	907.8	907.7	907.6	907.4
120°	973.5	974.1	974.8	974.8	974.1	973.5	972.9	972.2
122.5°	1037.8	1038.2	1038.6	1038.4	1037.8	1037.2	1036.5	1035.9
125°	1127.7	1128.6	1129.5	1130.2	1130.5	1130.8	1131.1	1131.4
127.5°	1216.9	1216.7	1216.5	1216.3	1216.1	1215.8	1215.5	1215.3
130°	1271.4	1271.7	1272.0	1272.1	1272.1	1272.1	1272.1	1272.1
132.5°	1324.8	1325.1	1325.4	1325.5	1325.2	1324.9	1324.7	1324.5
135°	1398.5	1399.1	1399.8	1400.4	1401.0	1401.7	1402.3	1402.9
137.5°	1469.1	1469.8	1470.6	1470.7	1470.6	1470.4	1470.2	1470.0
140°	1512.9	1513.8	1514.8	1515.3	1515.7	1516.0	1516.3	1516.6
142.5°	1553.3	1554.0	1554.6	1555.0	1555.1	1555.2	1555.2	1555.3
145°	1611.1	1611.4	1611.7	1612.2	1612.8	1613.4	1614.1	1614.7
147.5°	1661.8	1662.1	1662.4	1662.6	1662.9	1663.2	1663.6	1663.9
150°	1694.3	1694.3	1694.3	1694.5	1694.8	1695.1	1695.4	1695.7
152.5°	1722.6	1723.1	1723.6	1723.7	1723.5	1723.3	1723.2	1723.0
155°	1760.8	1762.1	1763.3	1763.5	1762.6	1761.6	1760.7	1759.7
157.5°	1793.7	1795.4	1797.0	1797.0	1795.4	1793.7	1792.1	1790.4
160°	1814.7	1816.6	1818.4	1818.4	1816.6	1814.7	1812.8	1810.8
162.5°	1831.7	1833.6	1835.5	1835.3	1833.2	1831.1	1828.9	1826.7
165°	1855.7	1858.2	1860.8	1860.6	1857.8	1854.9	1852.1	1849.3
167.5°	1873.3	1876.0	1878.9	1878.7	1875.5	1872.4	1869.2	1866.0
170°	1884.1	1886.7	1889.2	1888.9	1885.7	1882.5	1879.4	1876.2
172.5°	1890.9	1893.5	1896.0	1895.5	1892.2	1888.8	1885.4	1881.9
175°	1898.9	1901.9	1904.7	1904.2	1900.4	1896.6	1892.8	1889.0
177.5°	1902.1	1904.2	1906.2	1905.7	1902.7	1899.6	1896.6	1893.6
180°	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4

(END OF REPORT)