

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332841-830

Luminaire Tested: **S124DIW-S1195D770U830-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332841-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S1195D770U830-4F0-1E-UDD-A
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 770 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7908.3 lumens
Efficiency: N/A
Efficacy: 132.2 lumens/watt
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 59.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332841-830

CATALOG NUMBER: S124DIW-S1195D770U830-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332841-830

CATALOG NUMBER: S124DIW-S1195D770U830-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	110	110	110	110	104	104	104	104	91	91	91	79	79	79	68	68	68	63				
1	101	97	93	89	95	91	88	85	80	78	75	70	68	67	61	60	58	54				
2	92	85	79	74	86	80	74	70	71	66	63	62	59	56	54	52	50	46				
3	84	75	67	62	79	71	64	59	63	57	53	55	51	48	48	45	43	39				
4	77	67	59	52	72	63	56	50	56	50	46	49	45	41	43	40	37	34				
5	71	59	51	45	67	56	49	43	50	44	40	44	40	36	39	35	32	29				
6	66	54	45	39	62	51	43	38	45	39	35	40	35	32	36	32	29	26				
7	61	48	40	35	57	46	39	33	41	35	31	37	32	28	33	29	26	23				
8	57	44	36	31	53	42	35	30	38	32	27	34	29	25	30	26	23	21				
9	53	40	33	28	50	38	31	27	35	29	25	31	26	23	28	24	21	19				
10	49	37	30	25	46	35	29	24	32	26	22	29	24	21	26	22	19	17				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	14666	14666	14666	14666
5°	17271	14704	12977	14704
10°	20678	14638	11684	14638
15°	24466	14491	10730	14491
20°	27244	14339	9879	14339
25°	27684	14118	9291	14118
30°	23557	13904	9106	13904
35°	18111	13557	9107	13557
40°	14116	13149	9278	13149
45°	11771	12536	9434	12536
50°	10359	11786	9755	11786
55°	9491	10888	10148	10888
60°	8893	10085	10619	10085
65°	8281	9186	11012	9186
70°	7567	8297	11261	8297
75°	6759	7299	11126	7299
80°	5667	5983	10776	5983
85°	4177	4326	10319	4326



TEST NUMBER: P332841-830

CATALOG NUMBER: S124DIW-S1195D770U830-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	177.0	2.2
10°-20°	545.5	6.9
20°-30°	865.0	10.9
30°-40°	962.7	12.2
40°-50°	876.3	11.1
50°-60°	716.1	9.1
60°-70°	511.2	6.5
70°-80°	281.5	3.6
80°-90°	79.6	1.0
90°-100°	32.0	0.4
100°-110°	204.0	2.6
110°-120°	390.2	4.9
120°-130°	495.4	6.3
130°-140°	530.0	6.7
140°-150°	495.6	6.3
150°-160°	399.7	5.1
160°-170°	257.8	3.3
170°-180°	88.8	1.1
0°-30°	1587.5	20.1
0°-40°	2550.2	32.2
0°-60°	4142.6	52.4
0°-90°	5014.8	63.4
90°-120°	626.2	7.9
90°-150°	2147.2	27.2
90°-180°	2894.0	36.6
0°-180°	7908.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1817	1817	1817	1817	1817	
5°	2131	1814	1601	1814	2131	217
15°	2927	1734	1284	1734	2927	827
25°	3108	1585	1043	1585	3108	1370
35°	1838	1376	924	1376	1838	1166
45°	1031	1098	826	1098	1031	812
55°	674	774	721	774	674	609
65°	434	481	576	481	434	429
75°	217	234	357	234	217	230
85°	45	47	111	47	45	55
90°	21	2	21	2	21	11
95°	20	38	20	38	20	16
105°	199	211	199	211	199	174
115°	396	393	396	393	396	392
125°	557	553	557	553	557	496
135°	690	686	690	686	690	532
145°	795	791	795	791	795	497
155°	866	867	866	867	866	399
165°	910	914	910	914	910	257
175°	930	935	930	935	930	89
180°	935	935	935	935	935	



TEST NUMBER: P332841-830

CATALOG NUMBER: S124DIW-S1195D770U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1816.7	1816.7	1816.7	1816.7	1816.7	1816.7	1816.7	1816.7	1816.7	1816.7	1816.7
2.5°	1933.4	1932.8	1926.8	1925.6	1921.4	1916.0	1914.8	1905.2	1885.8	1876.8	1874.4
5°	2131.2	2146.3	2126.7	2122.9	2120.6	2095.8	2083.0	2067.9	2033.3	2013.1	1997.2
7.5°	2367.2	2369.0	2360.4	2353.5	2334.4	2312.7	2280.2	2245.6	2204.3	2161.4	2129.1
10°	2522.5	2528.6	2518.8	2517.2	2478.9	2454.8	2406.6	2366.0	2319.3	2267.4	2220.0
12.5°	2686.2	2677.9	2672.9	2640.6	2633.6	2589.6	2533.6	2491.8	2419.9	2360.1	2297.1
15°	2927.3	2910.9	2900.3	2855.9	2834.0	2773.1	2713.7	2667.8	2573.7	2484.2	2416.4
17.5°	3068.8	3085.4	3061.0	3042.8	2986.4	2943.7	2882.9	2786.5	2712.9	2601.7	2516.2
20°	3171.2	3172.7	3159.1	3140.4	3096.0	3041.8	2975.5	2870.1	2782.1	2671.5	2554.1
22.5°	3198.9	3199.2	3193.4	3175.9	3142.2	3098.3	3031.5	2943.7	2837.0	2716.7	2599.2
25°	3107.9	3104.9	3111.7	3131.3	3118.5	3104.9	3066.6	3001.1	2901.8	2774.6	2648.2
27.5°	2770.2	2791.0	2829.2	2877.4	2923.8	2959.1	2969.1	2955.6	2894.1	2789.5	2657.0
30°	2527.1	2552.6	2581.2	2629.3	2722.7	2776.1	2834.8	2879.2	2854.4	2770.9	2647.4
32.5°	2259.7	2266.1	2308.5	2363.2	2448.7	2551.6	2644.6	2734.7	2764.7	2720.8	2617.9
35°	1837.7	1848.2	1894.1	1948.3	2053.0	2178.6	2318.6	2443.4	2546.6	2587.9	2535.3
37.5°	1499.7	1529.9	1562.3	1620.5	1712.6	1825.8	1971.2	2132.9	2286.5	2389.4	2406.9
40°	1339.5	1358.3	1381.7	1426.1	1504.3	1615.7	1740.6	1925.7	2089.1	2236.6	2284.7
42.5°	1213.1	1224.1	1238.4	1278.6	1338.1	1449.0	1563.0	1725.9	1889.8	2066.1	2146.8
45°	1031.0	1042.3	1066.3	1089.7	1134.8	1211.5	1317.7	1451.6	1616.5	1786.5	1935.5
47.5°	899.5	906.6	921.0	945.9	984.3	1034.9	1121.2	1233.1	1385.9	1551.0	1709.8
50°	824.8	830.8	842.1	864.7	894.0	939.1	1009.9	1114.5	1234.2	1400.4	1556.2
52.5°	765.8	768.2	776.5	791.8	815.1	853.1	911.2	997.7	1108.9	1257.2	1412.4
55°	674.3	677.3	684.9	696.1	716.4	740.5	784.9	849.6	946.7	1075.3	1210.0
57.5°	599.0	601.2	607.5	611.8	628.5	648.1	682.2	728.5	802.0	911.2	1031.4
60°	550.8	549.3	556.9	560.6	571.9	588.5	614.8	659.2	723.2	811.2	921.9
62.5°	503.9	501.8	508.1	513.1	519.5	533.7	555.3	590.0	641.9	721.5	817.1
65°	433.5	430.5	434.2	440.3	446.3	453.7	469.6	500.4	541.9	599.0	672.0
67.5°	362.7	365.9	366.5	369.5	373.0	383.2	394.0	415.8	445.1	490.8	552.7
70°	320.6	321.3	324.3	324.3	326.6	335.6	344.7	357.4	386.1	428.2	478.6
72.5°	278.4	281.6	280.4	282.8	284.5	290.5	297.1	309.2	333.7	365.0	407.6
75°	216.7	219.0	219.0	219.7	222.0	224.2	229.5	238.6	255.9	279.2	308.5
77.5°	158.1	158.3	159.4	162.1	162.1	165.7	169.7	176.8	185.4	201.4	219.3
80°	121.9	123.4	122.6	124.1	124.1	127.1	128.7	137.7	141.5	152.0	166.3
82.5°	89.4	90.9	90.8	92.8	94.1	94.6	96.8	100.4	104.2	113.5	119.3
85°	45.1	46.7	45.1	46.7	48.9	49.7	51.9	52.7	55.7	58.0	63.2
87.5°	17.4	19.2	19.1	19.7	20.8	21.3	21.7	20.9	23.1	23.6	25.7
90°	21.0	20.6	20.4	20.1	19.7	19.1	18.2	17.2	16.3	15.4	14.1
92.5°	19.3	19.2	19.2	19.1	19.0	18.6	17.6	16.7	15.7	14.8	13.6
95°	20.3	20.2	20.0	19.8	19.7	19.1	18.2	17.2	16.3	15.4	15.3
97.5°	19.6	19.4	19.3	19.1	18.9	18.9	18.8	18.7	18.6	18.5	35.8
100°	19.6	19.4	19.3	19.1	18.9	20.2	22.8	25.5	28.2	30.8	52.2
102.5°	20.2	20.1	20.1	20.1	20.0	34.3	62.8	91.3	119.8	148.4	151.1
105°	199.4	205.0	210.6	216.2	221.8	223.9	222.4	221.1	219.7	218.3	217.5
107.5°	277.9	277.3	276.7	276.2	275.5	274.9	274.2	273.5	272.9	272.1	271.1
110°	312.1	311.6	311.1	310.7	310.2	309.8	309.4	309.2	308.9	308.5	307.6



TEST NUMBER: P332841-830

CATALOG NUMBER: S124DIW-S1195D770U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	346.2	345.6	345.0	344.4	343.8	343.6	343.7	343.7	343.7	343.8	343.4
115°	396.0	396.0	396.0	396.0	396.0	395.9	395.5	395.2	394.9	394.5	394.7
117.5°	446.7	446.7	446.8	446.9	446.9	447.0	447.0	447.0	447.1	447.2	446.9
120°	478.5	478.9	479.2	479.5	479.8	479.8	479.5	479.2	478.9	478.5	478.7
122.5°	509.9	510.2	510.5	510.9	511.1	511.2	511.0	510.9	510.7	510.5	510.2
125°	556.9	556.8	556.6	556.5	556.3	556.0	555.5	555.1	554.6	554.1	554.4
127.5°	598.2	598.3	598.4	598.6	598.7	598.8	598.9	599.0	599.1	599.2	598.4
130°	626.1	626.1	626.1	626.1	626.1	626.1	625.9	625.8	625.7	625.5	625.0
132.5°	652.0	652.1	652.1	652.3	652.4	652.4	652.2	652.1	652.0	651.8	651.2
135°	690.5	690.2	689.9	689.6	689.3	689.0	688.7	688.3	688.1	687.8	687.1
137.5°	723.6	723.7	723.8	723.9	724.0	723.8	723.5	723.1	722.7	722.5	721.8
140°	746.5	746.4	746.2	746.0	745.9	745.6	745.1	744.6	744.1	743.8	743.4
142.5°	765.5	765.5	765.4	765.4	765.4	765.3	764.9	764.6	764.2	763.8	763.6
145°	794.8	794.5	794.2	793.8	793.5	793.3	793.1	793.0	792.9	792.7	792.7
147.5°	819.0	818.9	818.7	818.5	818.4	818.2	818.1	817.9	817.8	817.7	817.8
150°	834.6	834.5	834.3	834.2	834.1	834.0	834.0	834.0	834.0	834.0	834.2
152.5°	848.1	848.2	848.3	848.4	848.5	848.4	848.1	847.9	847.6	847.4	847.7
155°	866.2	866.6	867.0	867.5	868.0	867.9	867.3	866.7	866.1	865.4	865.9
157.5°	881.3	882.0	882.9	883.7	884.5	884.5	883.7	882.9	882.0	881.3	881.7
160°	891.4	892.3	893.2	894.1	895.0	895.0	894.1	893.2	892.3	891.4	891.5
162.5°	899.2	900.2	901.3	902.4	903.4	903.4	902.5	901.6	900.7	899.8	899.8
165°	910.2	911.6	913.0	914.5	915.9	915.9	914.6	913.4	912.2	911.0	911.0
167.5°	918.5	920.0	921.6	923.1	924.7	924.8	923.4	922.1	920.7	919.4	919.5
170°	923.5	925.1	926.6	928.2	929.7	929.9	928.7	927.4	926.1	924.9	924.7
172.5°	926.3	928.0	929.7	931.3	933.0	933.2	932.0	930.8	929.5	928.3	928.1
175°	929.8	931.7	933.6	935.4	937.3	937.5	936.1	934.7	933.3	931.9	931.8
177.5°	932.1	933.6	935.0	936.5	938.0	938.3	937.3	936.3	935.3	934.2	934.1
180°	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4



TEST NUMBER: P332841-830

CATALOG NUMBER: S124DIW-S1195D770U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1816.7	1816.7	1816.7	1816.7	1816.7	1816.7	1816.7	1816.7	1816.7	1816.7	1816.7
2.5°	1875.0	1866.6	1860.6	1855.8	1842.5	1834.7	1828.6	1820.2	1810.6	1800.4	1787.7
5°	1981.4	1955.9	1937.0	1908.5	1881.3	1858.8	1835.4	1814.4	1788.8	1761.0	1740.6
7.5°	2093.3	2055.2	2006.4	1964.2	1916.6	1875.2	1838.1	1800.3	1760.8	1722.6	1687.5
10°	2164.3	2115.3	2061.2	1997.2	1937.0	1883.6	1833.9	1785.7	1739.1	1692.4	1652.6
12.5°	2240.8	2179.8	2099.7	2025.0	1957.5	1886.0	1826.1	1767.1	1710.8	1661.8	1615.2
15°	2343.4	2255.3	2162.8	2062.7	1973.9	1890.4	1808.4	1733.8	1670.7	1605.9	1560.8
17.5°	2406.5	2297.5	2191.7	2087.1	1979.6	1874.2	1785.7	1699.9	1620.7	1556.4	1499.5
20°	2448.0	2339.7	2207.9	2103.4	1975.4	1867.1	1764.7	1669.1	1586.4	1517.9	1459.2
22.5°	2484.2	2358.9	2227.2	2089.5	1962.2	1847.2	1735.2	1639.0	1554.4	1482.3	1426.1
25°	2503.7	2359.9	2217.0	2080.0	1935.5	1799.3	1697.7	1584.9	1494.5	1418.5	1358.3
27.5°	2505.8	2352.1	2190.4	2038.2	1889.0	1762.2	1633.9	1533.0	1439.3	1359.0	1301.2
30°	2499.2	2338.9	2165.0	2000.3	1850.5	1712.8	1601.4	1491.6	1396.0	1316.2	1255.9
32.5°	2478.1	2311.2	2132.5	1958.1	1802.9	1668.2	1553.2	1448.8	1355.7	1277.1	1213.8
35°	2417.2	2252.3	2061.9	1880.6	1721.8	1585.6	1481.8	1375.6	1282.3	1207.9	1146.9
37.5°	2321.9	2172.8	1979.3	1791.7	1635.7	1498.9	1396.0	1300.0	1216.0	1140.3	1077.8
40°	2238.8	2107.9	1913.7	1730.8	1562.3	1432.1	1335.8	1247.7	1164.1	1092.7	1033.2
42.5°	2143.1	2029.0	1849.9	1656.1	1493.6	1362.8	1268.9	1189.9	1111.2	1045.1	985.7
45°	1972.4	1897.1	1728.6	1549.4	1380.2	1256.7	1167.2	1098.0	1031.7	967.0	917.4
47.5°	1776.1	1738.8	1596.9	1426.8	1266.0	1144.4	1066.8	1002.9	944.7	889.9	846.1
50°	1644.3	1626.3	1503.5	1339.5	1186.0	1071.6	993.3	938.4	888.7	840.6	799.2
52.5°	1514.3	1513.6	1403.1	1252.8	1110.8	1000.6	922.9	871.6	828.6	789.4	752.2
55°	1315.4	1336.5	1250.0	1116.0	988.8	889.5	819.5	773.6	743.5	711.1	683.3
57.5°	1132.8	1167.8	1096.5	978.5	872.3	780.8	719.9	685.4	653.4	633.8	613.5
60°	1013.7	1046.8	991.1	891.7	791.6	713.4	655.4	624.6	596.7	583.2	568.9
62.5°	907.7	937.2	896.0	803.9	717.0	641.8	592.9	563.2	544.4	529.6	520.2
65°	756.3	781.2	745.7	678.8	604.3	544.1	504.2	480.9	462.8	456.8	446.3
67.5°	611.3	634.0	614.8	557.9	498.1	452.6	421.4	399.0	388.3	383.0	375.5
70°	525.3	547.8	527.5	477.9	432.0	393.6	364.2	351.5	340.2	337.9	327.3
72.5°	452.4	467.8	447.4	408.6	369.4	337.0	314.2	300.9	295.0	291.0	285.2
75°	339.4	353.0	339.4	309.2	281.4	258.9	239.3	234.0	227.2	225.0	221.2
77.5°	240.3	251.9	241.6	222.7	202.0	184.5	174.0	167.2	165.7	161.8	163.6
80°	183.6	191.1	181.3	168.5	152.0	140.0	132.4	128.7	124.1	122.6	125.6
82.5°	131.9	135.2	130.2	121.6	109.2	101.4	96.3	92.0	91.0	91.3	91.3
85°	68.5	67.8	67.0	59.5	55.7	50.4	47.4	46.7	45.9	47.4	48.9
87.5°	25.4	25.8	25.0	22.2	20.1	18.0	17.1	16.1	17.1	18.0	18.9
90°	12.9	11.7	10.5	9.0	7.3	5.6	3.8	2.1	3.8	5.6	7.3
92.5°	12.3	11.1	9.9	9.1	9.0	9.0	9.0	8.9	9.0	9.0	9.0
95°	15.1	14.9	14.8	17.3	22.6	27.9	33.2	38.5	33.2	27.9	22.6
97.5°	53.2	70.5	87.8	94.9	91.6	88.3	85.0	81.7	85.0	88.3	91.6
100°	73.7	95.2	116.6	125.9	123.1	120.4	117.5	114.7	117.5	120.4	123.1
102.5°	153.9	156.7	159.5	159.9	157.9	155.8	153.7	151.7	153.7	155.8	157.9
105°	216.7	215.9	215.2	214.3	213.4	212.4	211.5	210.6	211.5	212.4	213.4
107.5°	270.0	269.0	268.0	267.2	266.7	266.3	265.8	265.3	265.8	266.3	266.7
110°	306.7	305.8	304.8	304.1	303.7	303.2	302.7	302.3	302.7	303.2	303.7



TEST NUMBER: P332841-830

CATALOG NUMBER: S124DIW-S1195D770U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	342.9	342.5	342.0	341.4	340.5	339.8	338.9	338.1	338.9	339.8	340.5
115°	394.9	395.0	395.2	395.0	394.5	394.2	393.7	393.2	393.7	394.2	394.5
117.5°	446.5	446.2	445.8	445.4	444.7	444.1	443.5	442.9	443.5	444.1	444.7
120°	478.9	479.0	479.2	478.9	478.3	477.7	477.1	476.5	477.1	477.7	478.3
122.5°	510.0	509.8	509.5	509.3	508.9	508.5	508.1	507.8	508.1	508.5	508.9
125°	554.8	555.1	555.3	555.2	554.6	553.9	553.4	552.7	553.4	553.9	554.6
127.5°	597.8	597.0	596.3	595.9	595.7	595.6	595.4	595.2	595.4	595.6	595.7
130°	624.5	624.1	623.6	623.3	623.1	623.0	622.8	622.6	622.8	623.0	623.1
132.5°	650.6	650.0	649.4	648.9	648.7	648.5	648.2	647.9	648.2	648.5	648.7
135°	686.5	685.9	685.2	685.0	685.1	685.3	685.5	685.6	685.5	685.3	685.1
137.5°	721.0	720.4	719.7	719.3	719.3	719.3	719.2	719.1	719.2	719.3	719.3
140°	743.1	742.8	742.4	742.2	741.9	741.5	741.2	740.9	741.2	741.5	741.9
142.5°	763.5	763.3	763.1	762.7	762.1	761.7	761.1	760.5	761.1	761.7	762.1
145°	792.7	792.7	792.7	792.5	792.0	791.5	791.1	790.6	791.1	791.5	792.0
147.5°	818.0	818.2	818.3	818.0	817.1	816.2	815.4	814.5	815.4	816.2	817.1
150°	834.2	834.4	834.6	834.3	833.8	833.1	832.5	831.9	832.5	833.1	833.8
152.5°	848.0	848.2	848.5	848.4	847.9	847.4	846.9	846.4	846.9	847.4	847.9
155°	866.4	866.9	867.3	867.5	867.3	867.1	867.0	866.9	867.0	867.1	867.3
157.5°	882.3	882.9	883.4	883.7	883.8	883.9	884.0	884.1	884.0	883.9	883.8
160°	891.6	891.8	891.9	892.3	892.8	893.2	893.6	894.1	893.6	893.2	892.8
162.5°	900.0	900.2	900.3	900.7	901.4	901.9	902.5	903.1	902.5	901.9	901.4
165°	911.0	911.0	911.0	911.3	912.1	912.9	913.6	914.5	913.6	912.9	912.1
167.5°	919.5	919.6	919.7	920.1	921.0	921.8	922.6	923.4	922.6	921.8	921.0
170°	924.6	924.4	924.3	924.7	925.6	926.5	927.5	928.4	927.5	926.5	925.6
172.5°	927.9	927.8	927.7	928.0	929.0	929.9	930.9	931.8	930.9	929.9	929.0
175°	931.6	931.4	931.3	931.7	932.6	933.6	934.4	935.4	934.4	933.6	932.6
177.5°	933.8	933.6	933.3	933.6	934.4	935.4	936.2	937.1	936.2	935.4	934.4
180°	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4



TEST NUMBER: P332841-830

CATALOG NUMBER: S124DIW-S1195D770U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1816.7	1816.7	1816.7	1816.7	1816.7	1816.7	1816.7	1816.7	1816.7	1816.7	1816.7
2.5°	1781.7	1776.3	1768.5	1757.7	1748.6	1739.0	1736.5	1733.0	1740.1	1734.2	1732.3
5°	1723.3	1707.5	1687.2	1663.9	1650.3	1630.8	1627.0	1619.5	1611.9	1611.2	1603.6
7.5°	1661.4	1638.2	1611.7	1587.8	1565.8	1544.5	1530.5	1527.5	1516.4	1509.9	1502.3
10°	1621.7	1593.1	1562.3	1539.7	1514.1	1491.6	1475.7	1466.7	1459.2	1450.9	1443.4
12.5°	1574.8	1544.4	1518.9	1494.5	1464.1	1447.0	1421.0	1405.3	1403.8	1403.9	1384.4
15°	1520.1	1490.1	1450.9	1416.3	1399.7	1366.6	1352.3	1334.3	1323.0	1311.6	1302.7
17.5°	1457.6	1420.2	1389.6	1349.9	1318.3	1291.9	1273.2	1262.3	1245.3	1229.4	1217.8
20°	1418.5	1378.7	1346.3	1304.1	1269.5	1237.2	1221.3	1206.4	1193.5	1180.0	1167.2
22.5°	1378.8	1337.1	1297.5	1256.6	1224.4	1190.2	1175.0	1154.5	1142.4	1134.8	1122.0
25°	1316.2	1271.0	1225.9	1186.8	1153.7	1123.5	1103.2	1087.4	1073.8	1067.8	1059.6
27.5°	1248.1	1203.3	1159.7	1115.2	1077.6	1055.8	1039.5	1027.7	1019.8	1011.8	1008.1
30°	1204.9	1158.2	1111.5	1070.1	1035.5	1013.7	998.6	990.3	984.3	980.5	976.8
32.5°	1160.8	1114.8	1065.7	1027.9	996.9	977.5	966.1	957.8	954.8	953.5	952.2
35°	1090.4	1043.8	998.6	964.8	935.4	927.8	918.1	913.6	912.1	917.4	919.6
37.5°	1022.3	978.9	937.4	904.6	885.3	874.3	871.0	871.1	876.6	881.2	886.6
40°	978.3	936.1	897.0	868.5	850.4	843.6	842.1	845.8	851.9	857.1	863.2
42.5°	935.6	894.0	858.5	831.7	819.1	812.8	813.8	817.6	826.0	832.5	841.5
45°	869.2	834.5	799.9	778.2	767.6	769.1	769.1	775.9	784.1	793.9	803.7
47.5°	806.7	771.8	743.4	725.0	719.5	718.2	722.5	731.3	743.2	755.3	768.9
50°	764.6	731.5	706.6	690.0	684.1	686.4	692.3	700.6	714.9	730.0	744.2
52.5°	721.8	691.7	668.7	653.4	649.1	653.2	659.2	672.3	684.9	701.1	718.4
55°	655.4	629.9	611.8	600.5	599.0	601.2	608.0	622.4	640.4	660.7	677.3
57.5°	589.4	568.0	551.5	543.7	544.4	546.5	557.6	574.7	593.9	615.6	637.0
60°	544.8	525.3	511.7	505.7	506.4	511.0	524.5	540.4	564.4	585.5	608.0
62.5°	502.7	485.5	472.6	467.2	466.1	476.1	489.0	505.4	529.5	553.0	577.3
65°	435.0	421.4	410.9	407.8	410.1	417.6	434.2	456.0	476.4	501.1	526.8
67.5°	368.7	357.6	350.3	351.8	354.5	365.6	379.5	398.2	421.3	447.0	472.3
70°	326.6	316.0	310.0	310.8	315.3	328.9	340.9	359.7	384.6	410.9	432.0
72.5°	283.2	276.4	270.9	274.1	278.6	287.9	302.9	321.8	343.7	368.2	390.4
75°	217.4	217.4	214.4	216.7	223.5	232.5	243.8	263.3	285.2	304.8	322.8
77.5°	161.4	159.7	161.6	164.4	168.2	179.0	191.9	205.9	222.3	241.9	256.7
80°	123.4	124.1	127.9	132.4	133.9	142.2	155.8	168.5	181.3	197.9	212.3
82.5°	92.7	93.5	95.4	101.1	102.6	111.5	120.3	133.1	144.7	155.8	167.7
85°	50.4	50.4	54.2	56.5	60.2	66.3	71.4	79.0	89.5	97.1	108.4
87.5°	21.0	21.3	24.0	25.4	27.5	30.7	32.1	38.9	41.6	44.8	50.3
90°	9.0	10.5	11.7	12.9	14.1	15.4	16.3	17.2	18.2	19.1	19.7
92.5°	9.1	9.9	11.1	12.3	13.6	14.8	15.7	16.7	17.6	18.6	19.0
95°	17.3	14.8	14.9	15.1	15.3	15.4	16.3	17.2	18.2	19.1	19.7
97.5°	94.9	87.8	70.5	53.2	35.8	18.5	18.6	18.7	18.8	18.9	18.9
100°	125.9	116.6	95.2	73.7	52.2	30.8	28.2	25.5	22.8	20.2	18.9
102.5°	159.9	159.5	156.7	153.9	151.1	148.4	119.8	91.3	62.8	34.3	20.0
105°	214.3	215.2	215.9	216.7	217.5	218.3	219.7	221.1	222.4	223.9	221.8
107.5°	267.2	268.0	269.0	270.0	271.1	272.1	272.9	273.5	274.2	274.9	275.5
110°	304.1	304.8	305.8	306.7	307.6	308.5	308.9	309.2	309.4	309.8	310.2



TEST NUMBER: P332841-830

CATALOG NUMBER: S124DIW-S1195D770U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	341.4	342.0	342.5	342.9	343.4	343.8	343.7	343.7	343.7	343.6	343.8
115°	395.0	395.2	395.0	394.9	394.7	394.5	394.9	395.2	395.5	395.9	396.0
117.5°	445.4	445.8	446.2	446.5	446.9	447.2	447.1	447.0	447.0	447.0	446.9
120°	478.9	479.2	479.0	478.9	478.7	478.5	478.9	479.2	479.5	479.8	479.8
122.5°	509.3	509.5	509.8	510.0	510.2	510.5	510.7	510.9	511.0	511.2	511.1
125°	555.2	555.3	555.1	554.8	554.4	554.1	554.6	555.1	555.5	556.0	556.3
127.5°	595.9	596.3	597.0	597.8	598.4	599.2	599.1	599.0	598.9	598.8	598.7
130°	623.3	623.6	624.1	624.5	625.0	625.5	625.7	625.8	625.9	626.1	626.1
132.5°	648.9	649.4	650.0	650.6	651.2	651.8	652.0	652.1	652.2	652.4	652.4
135°	685.0	685.2	685.9	686.5	687.1	687.8	688.1	688.3	688.7	689.0	689.3
137.5°	719.3	719.7	720.4	721.0	721.8	722.5	722.7	723.1	723.5	723.8	724.0
140°	742.2	742.4	742.8	743.1	743.4	743.8	744.1	744.6	745.1	745.6	745.9
142.5°	762.7	763.1	763.3	763.5	763.6	763.8	764.2	764.6	764.9	765.3	765.4
145°	792.5	792.7	792.7	792.7	792.7	792.7	792.9	793.0	793.1	793.3	793.5
147.5°	818.0	818.3	818.2	818.0	817.8	817.7	817.8	817.9	818.1	818.2	818.4
150°	834.3	834.6	834.4	834.2	834.2	834.0	834.0	834.0	834.0	834.0	834.1
152.5°	848.4	848.5	848.2	848.0	847.7	847.4	847.6	847.9	848.1	848.4	848.5
155°	867.5	867.3	866.9	866.4	865.9	865.4	866.1	866.7	867.3	867.9	868.0
157.5°	883.7	883.4	882.9	882.3	881.7	881.3	882.0	882.9	883.7	884.5	884.5
160°	892.3	891.9	891.8	891.6	891.5	891.4	892.3	893.2	894.1	895.0	895.0
162.5°	900.7	900.3	900.2	900.0	899.8	899.8	900.7	901.6	902.5	903.4	903.4
165°	911.3	911.0	911.0	911.0	911.0	911.0	912.2	913.4	914.6	915.9	915.9
167.5°	920.1	919.7	919.6	919.5	919.5	919.4	920.7	922.1	923.4	924.8	924.7
170°	924.7	924.3	924.4	924.6	924.7	924.9	926.1	927.4	928.7	929.9	929.7
172.5°	928.0	927.7	927.8	927.9	928.1	928.3	929.5	930.8	932.0	933.2	933.0
175°	931.7	931.3	931.4	931.6	931.8	931.9	933.3	934.7	936.1	937.5	937.3
177.5°	933.6	933.3	933.6	933.8	934.1	934.2	935.3	936.3	937.3	938.3	938.0
180°	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4



TEST NUMBER: P332841-830

CATALOG NUMBER: S124DIW-S1195D770U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1816.7	1816.7	1816.7	1816.7	1816.7	1816.7	1816.7	1816.7	1816.7	1816.7	1816.7
2.5°	1731.2	1729.9	1725.7	1725.1	1725.7	1729.9	1731.2	1732.3	1734.2	1740.1	1733.0
5°	1599.1	1595.3	1593.1	1601.4	1593.1	1595.3	1599.1	1603.6	1611.2	1611.9	1619.5
7.5°	1499.7	1496.7	1490.1	1487.9	1490.1	1496.7	1499.7	1502.3	1509.9	1516.4	1527.5
10°	1435.9	1432.9	1426.8	1425.3	1426.8	1432.9	1435.9	1443.4	1450.9	1459.2	1466.7
12.5°	1374.4	1368.4	1367.3	1368.8	1367.3	1368.4	1374.4	1384.4	1403.9	1403.8	1405.3
15°	1292.9	1289.9	1281.6	1283.8	1281.6	1289.9	1292.9	1302.7	1311.6	1323.0	1334.3
17.5°	1212.5	1208.9	1198.8	1207.7	1198.8	1208.9	1212.5	1217.8	1229.4	1245.3	1262.3
20°	1161.9	1155.9	1150.7	1149.9	1150.7	1155.9	1161.9	1167.2	1180.0	1193.5	1206.4
22.5°	1113.7	1108.3	1107.9	1103.0	1107.9	1108.3	1113.7	1122.0	1134.8	1142.4	1154.5
25°	1053.6	1048.3	1046.8	1043.0	1046.8	1048.3	1053.6	1059.6	1067.8	1073.8	1087.4
27.5°	1007.4	1004.8	1002.1	1003.2	1002.1	1004.8	1007.4	1008.1	1011.8	1019.8	1027.7
30°	979.0	978.3	976.8	976.8	976.8	978.3	979.0	976.8	980.5	984.3	990.3
32.5°	955.5	955.5	956.3	956.3	956.3	955.5	955.5	952.2	953.5	954.8	957.8
35°	922.7	924.8	926.3	924.1	926.3	924.8	922.7	919.6	917.4	912.1	913.6
37.5°	892.8	895.0	897.2	899.8	897.2	895.0	892.8	886.6	881.2	876.6	871.1
40°	870.0	875.2	876.7	880.4	876.7	875.2	870.0	863.2	857.1	851.9	845.8
42.5°	848.3	854.1	858.0	858.8	858.0	854.1	848.3	841.5	832.5	826.0	817.6
45°	815.0	821.0	826.3	826.3	826.3	821.0	815.0	803.7	793.9	784.1	775.9
47.5°	780.5	789.3	794.6	795.9	794.6	789.3	780.5	768.9	755.3	743.2	731.3
50°	757.1	767.6	772.9	776.7	772.9	767.6	757.1	744.2	730.0	714.9	700.6
52.5°	734.1	744.7	751.8	753.8	751.8	744.7	734.1	718.4	701.1	684.9	672.3
55°	694.6	709.6	717.9	721.0	717.9	709.6	694.6	677.3	660.7	640.4	622.4
57.5°	657.2	671.1	680.7	683.0	680.7	671.1	657.2	637.0	615.6	593.9	574.7
60°	628.4	643.4	655.4	657.7	655.4	643.4	628.4	608.0	585.5	564.4	540.4
62.5°	598.9	614.5	625.4	631.2	625.4	614.5	598.9	577.3	553.0	529.5	505.4
65°	547.8	563.6	574.2	576.5	574.2	563.6	547.8	526.8	501.1	476.4	456.0
67.5°	492.2	507.9	514.9	519.2	514.9	507.9	492.2	472.3	447.0	421.3	398.2
70°	453.0	465.8	473.3	477.1	473.3	465.8	453.0	432.0	410.9	384.6	359.7
72.5°	408.5	421.9	430.6	431.3	430.6	421.9	408.5	390.4	368.2	343.7	321.8
75°	340.2	352.2	356.7	356.7	356.7	352.2	340.2	322.8	304.8	285.2	263.3
77.5°	269.3	275.4	281.2	282.4	281.2	275.4	269.3	256.7	241.9	222.3	205.9
80°	223.5	227.2	231.8	231.8	231.8	227.2	223.5	212.3	197.9	181.3	168.5
82.5°	176.5	179.7	184.3	183.6	184.3	179.7	176.5	167.7	155.8	144.7	133.1
85°	106.9	113.7	112.9	111.4	112.9	113.7	106.9	108.4	97.1	89.5	79.0
87.5°	52.2	52.9	54.7	56.0	54.7	52.9	52.2	50.3	44.8	41.6	38.9
90°	20.1	20.4	20.6	21.0	20.6	20.4	20.1	19.7	19.1	18.2	17.2
92.5°	19.1	19.2	19.2	19.3	19.2	19.2	19.1	19.0	18.6	17.6	16.7
95°	19.8	20.0	20.2	20.3	20.2	20.0	19.8	19.7	19.1	18.2	17.2
97.5°	19.1	19.3	19.4	19.6	19.4	19.3	19.1	18.9	18.9	18.8	18.7
100°	19.1	19.3	19.4	19.6	19.4	19.3	19.1	18.9	20.2	22.8	25.5
102.5°	20.1	20.1	20.1	20.2	20.1	20.1	20.1	20.0	34.3	62.8	91.3
105°	216.2	210.6	205.0	199.4	205.0	210.6	216.2	221.8	223.9	222.4	221.1
107.5°	276.2	276.7	277.3	277.9	277.3	276.7	276.2	275.5	274.9	274.2	273.5
110°	310.7	311.1	311.6	312.1	311.6	311.1	310.7	310.2	309.8	309.4	309.2



TEST NUMBER: P332841-830

CATALOG NUMBER: S124DIW-S1195D770U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	344.4	345.0	345.6	346.2	345.6	345.0	344.4	343.8	343.6	343.7	343.7
115°	396.0	396.0	396.0	396.0	396.0	396.0	396.0	396.0	395.9	395.5	395.2
117.5°	446.9	446.8	446.7	446.7	446.7	446.8	446.9	446.9	447.0	447.0	447.0
120°	479.5	479.2	478.9	478.5	478.9	479.2	479.5	479.8	479.8	479.5	479.2
122.5°	510.9	510.5	510.2	509.9	510.2	510.5	510.9	511.1	511.2	511.0	510.9
125°	556.5	556.6	556.8	556.9	556.8	556.6	556.5	556.3	556.0	555.5	555.1
127.5°	598.6	598.4	598.3	598.2	598.3	598.4	598.6	598.7	598.8	598.9	599.0
130°	626.1	626.1	626.1	626.1	626.1	626.1	626.1	626.1	626.1	625.9	625.8
132.5°	652.3	652.1	652.1	652.0	652.1	652.1	652.3	652.4	652.4	652.2	652.1
135°	689.6	689.9	690.2	690.5	690.2	689.9	689.6	689.3	689.0	688.7	688.3
137.5°	723.9	723.8	723.7	723.6	723.7	723.8	723.9	724.0	723.8	723.5	723.1
140°	746.0	746.2	746.4	746.5	746.4	746.2	746.0	745.9	745.6	745.1	744.6
142.5°	765.4	765.4	765.5	765.5	765.5	765.4	765.4	765.4	765.3	764.9	764.6
145°	793.8	794.2	794.5	794.8	794.5	794.2	793.8	793.5	793.3	793.1	793.0
147.5°	818.5	818.7	818.9	819.0	818.9	818.7	818.5	818.4	818.2	818.1	817.9
150°	834.2	834.3	834.5	834.6	834.5	834.3	834.2	834.1	834.0	834.0	834.0
152.5°	848.4	848.3	848.2	848.1	848.2	848.3	848.4	848.5	848.4	848.1	847.9
155°	867.5	867.0	866.6	866.2	866.6	867.0	867.5	868.0	867.9	867.3	866.7
157.5°	883.7	882.9	882.0	881.3	882.0	882.9	883.7	884.5	884.5	883.7	882.9
160°	894.1	893.2	892.3	891.4	892.3	893.2	894.1	895.0	895.0	894.1	893.2
162.5°	902.4	901.3	900.2	899.2	900.2	901.3	902.4	903.4	903.4	902.5	901.6
165°	914.5	913.0	911.6	910.2	911.6	913.0	914.5	915.9	915.9	914.6	913.4
167.5°	923.1	921.6	920.0	918.5	920.0	921.6	923.1	924.7	924.8	923.4	922.1
170°	928.2	926.6	925.1	923.5	925.1	926.6	928.2	929.7	929.9	928.7	927.4
172.5°	931.3	929.7	928.0	926.3	928.0	929.7	931.3	933.0	933.2	932.0	930.8
175°	935.4	933.6	931.7	929.8	931.7	933.6	935.4	937.3	937.5	936.1	934.7
177.5°	936.5	935.0	933.6	932.1	933.6	935.0	936.5	938.0	938.3	937.3	936.3
180°	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4



TEST NUMBER: P332841-830

CATALOG NUMBER: S124DIW-S1195D770U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1816.7	1816.7	1816.7	1816.7	1816.7	1816.7	1816.7	1816.7	1816.7	1816.7	1816.7
2.5°	1736.5	1739.0	1748.6	1757.7	1768.5	1776.3	1781.7	1787.7	1800.4	1810.6	1820.2
5°	1627.0	1630.8	1650.3	1663.9	1687.2	1707.5	1723.3	1740.6	1761.0	1788.8	1814.4
7.5°	1530.5	1544.5	1565.8	1587.8	1611.7	1638.2	1661.4	1687.5	1722.6	1760.8	1800.3
10°	1475.7	1491.6	1514.1	1539.7	1562.3	1593.1	1621.7	1652.6	1692.4	1739.1	1785.7
12.5°	1421.0	1447.0	1464.1	1494.5	1518.9	1544.4	1574.8	1615.2	1661.8	1710.8	1767.1
15°	1352.3	1366.6	1399.7	1416.3	1450.9	1490.1	1520.1	1560.8	1605.9	1670.7	1733.8
17.5°	1273.2	1291.9	1318.3	1349.9	1389.6	1420.2	1457.6	1499.5	1556.4	1620.7	1699.9
20°	1221.3	1237.2	1269.5	1304.1	1346.3	1378.7	1418.5	1459.2	1517.9	1586.4	1669.1
22.5°	1175.0	1190.2	1224.4	1256.6	1297.5	1337.1	1378.8	1426.1	1482.3	1554.4	1639.0
25°	1103.2	1123.5	1153.7	1186.8	1225.9	1271.0	1316.2	1358.3	1418.5	1494.5	1584.9
27.5°	1039.5	1055.8	1077.6	1115.2	1159.7	1203.3	1248.1	1301.2	1359.0	1439.3	1533.0
30°	998.6	1013.7	1035.5	1070.1	1111.5	1158.2	1204.9	1255.9	1316.2	1396.0	1491.6
32.5°	966.1	977.5	996.9	1027.9	1065.7	1114.8	1160.8	1213.8	1277.1	1355.7	1448.8
35°	918.1	927.8	935.4	964.8	998.6	1043.8	1090.4	1146.9	1207.9	1282.3	1375.6
37.5°	871.0	874.3	885.3	904.6	937.4	978.9	1022.3	1077.8	1140.3	1216.0	1300.0
40°	842.1	843.6	850.4	868.5	897.0	936.1	978.3	1033.2	1092.7	1164.1	1247.7
42.5°	813.8	812.8	819.1	831.7	858.5	894.0	935.6	985.7	1045.1	1111.2	1189.9
45°	769.1	769.1	767.6	778.2	799.9	834.5	869.2	917.4	967.0	1031.7	1098.0
47.5°	722.5	718.2	719.5	725.0	743.4	771.8	806.7	846.1	889.9	944.7	1002.9
50°	692.3	686.4	684.1	690.0	706.6	731.5	764.6	799.2	840.6	888.7	938.4
52.5°	659.2	653.2	649.1	653.4	668.7	691.7	721.8	752.2	789.4	828.6	871.6
55°	608.0	601.2	599.0	600.5	611.8	629.9	655.4	683.3	711.1	743.5	773.6
57.5°	557.6	546.5	544.4	543.7	551.5	568.0	589.4	613.5	633.8	653.4	685.4
60°	524.5	511.0	506.4	505.7	511.7	525.3	544.8	568.9	583.2	596.7	624.6
62.5°	489.0	476.1	466.1	467.2	472.6	485.5	502.7	520.2	529.6	544.4	563.2
65°	434.2	417.6	410.1	407.8	410.9	421.4	435.0	446.3	456.8	462.8	480.9
67.5°	379.5	365.6	354.5	351.8	350.3	357.6	368.7	375.5	383.0	388.3	399.0
70°	340.9	328.9	315.3	310.8	310.0	316.0	326.6	327.3	337.9	340.2	351.5
72.5°	302.9	287.9	278.6	274.1	270.9	276.4	283.2	285.2	291.0	295.0	300.9
75°	243.8	232.5	223.5	216.7	214.4	217.4	217.4	221.2	225.0	227.2	234.0
77.5°	191.9	179.0	168.2	164.4	161.6	159.7	161.4	163.6	161.8	165.7	167.2
80°	155.8	142.2	133.9	132.4	127.9	124.1	123.4	125.6	122.6	124.1	128.7
82.5°	120.3	111.5	102.6	101.1	95.4	93.5	92.7	91.3	91.3	91.0	92.0
85°	71.4	66.3	60.2	56.5	54.2	50.4	50.4	48.9	47.4	45.9	46.7
87.5°	32.1	30.7	27.5	25.4	24.0	21.3	21.0	18.9	18.0	17.1	16.1
90°	16.3	15.4	14.1	12.9	11.7	10.5	9.0	7.3	5.6	3.8	2.1
92.5°	15.7	14.8	13.6	12.3	11.1	9.9	9.1	9.0	9.0	9.0	8.9
95°	16.3	15.4	15.3	15.1	14.9	14.8	17.3	22.6	27.9	33.2	38.5
97.5°	18.6	18.5	35.8	53.2	70.5	87.8	94.9	91.6	88.3	85.0	81.7
100°	28.2	30.8	52.2	73.7	95.2	116.6	125.9	123.1	120.4	117.5	114.7
102.5°	119.8	148.4	151.1	153.9	156.7	159.5	159.9	157.9	155.8	153.7	151.7
105°	219.7	218.3	217.5	216.7	215.9	215.2	214.3	213.4	212.4	211.5	210.6
107.5°	272.9	272.1	271.1	270.0	269.0	268.0	267.2	266.7	266.3	265.8	265.3
110°	308.9	308.5	307.6	306.7	305.8	304.8	304.1	303.7	303.2	302.7	302.3



TEST NUMBER: P332841-830

CATALOG NUMBER: S124DIW-S1195D770U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	343.7	343.8	343.4	342.9	342.5	342.0	341.4	340.5	339.8	338.9	338.1
115°	394.9	394.5	394.7	394.9	395.0	395.2	395.0	394.5	394.2	393.7	393.2
117.5°	447.1	447.2	446.9	446.5	446.2	445.8	445.4	444.7	444.1	443.5	442.9
120°	478.9	478.5	478.7	478.9	479.0	479.2	478.9	478.3	477.7	477.1	476.5
122.5°	510.7	510.5	510.2	510.0	509.8	509.5	509.3	508.9	508.5	508.1	507.8
125°	554.6	554.1	554.4	554.8	555.1	555.3	555.2	554.6	553.9	553.4	552.7
127.5°	599.1	599.2	598.4	597.8	597.0	596.3	595.9	595.7	595.6	595.4	595.2
130°	625.7	625.5	625.0	624.5	624.1	623.6	623.3	623.1	623.0	622.8	622.6
132.5°	652.0	651.8	651.2	650.6	650.0	649.4	648.9	648.7	648.5	648.2	647.9
135°	688.1	687.8	687.1	686.5	685.9	685.2	685.0	685.1	685.3	685.5	685.6
137.5°	722.7	722.5	721.8	721.0	720.4	719.7	719.3	719.3	719.3	719.2	719.1
140°	744.1	743.8	743.4	743.1	742.8	742.4	742.2	741.9	741.5	741.2	740.9
142.5°	764.2	763.8	763.6	763.5	763.3	763.1	762.7	762.1	761.7	761.1	760.5
145°	792.9	792.7	792.7	792.7	792.7	792.7	792.5	792.0	791.5	791.1	790.6
147.5°	817.8	817.7	817.8	818.0	818.2	818.3	818.0	817.1	816.2	815.4	814.5
150°	834.0	834.0	834.2	834.2	834.4	834.6	834.3	833.8	833.1	832.5	831.9
152.5°	847.6	847.4	847.7	848.0	848.2	848.5	848.4	847.9	847.4	846.9	846.4
155°	866.1	865.4	865.9	866.4	866.9	867.3	867.5	867.3	867.1	867.0	866.9
157.5°	882.0	881.3	881.7	882.3	882.9	883.4	883.7	883.8	883.9	884.0	884.1
160°	892.3	891.4	891.5	891.6	891.8	891.9	892.3	892.8	893.2	893.6	894.1
162.5°	900.7	899.8	899.8	900.0	900.2	900.3	900.7	901.4	901.9	902.5	903.1
165°	912.2	911.0	911.0	911.0	911.0	911.0	911.3	912.1	912.9	913.6	914.5
167.5°	920.7	919.4	919.5	919.5	919.6	919.7	920.1	921.0	921.8	922.6	923.4
170°	926.1	924.9	924.7	924.6	924.4	924.3	924.7	925.6	926.5	927.5	928.4
172.5°	929.5	928.3	928.1	927.9	927.8	927.7	928.0	929.0	929.9	930.9	931.8
175°	933.3	931.9	931.8	931.6	931.4	931.3	931.7	932.6	933.6	934.4	935.4
177.5°	935.3	934.2	934.1	933.8	933.6	933.3	933.6	934.4	935.4	936.2	937.1
180°	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4



TEST NUMBER: P332841-830

CATALOG NUMBER: S124DIW-S1195D770U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1816.7	1816.7	1816.7	1816.7	1816.7	1816.7	1816.7	1816.7	1816.7	1816.7	1816.7
2.5°	1828.6	1834.7	1842.5	1855.8	1860.6	1866.6	1875.0	1874.4	1876.8	1885.8	1905.2
5°	1835.4	1858.8	1881.3	1908.5	1937.0	1955.9	1981.4	1997.2	2013.1	2033.3	2067.9
7.5°	1838.1	1875.2	1916.6	1964.2	2006.4	2055.2	2093.3	2129.1	2161.4	2204.3	2245.6
10°	1833.9	1883.6	1937.0	1997.2	2061.2	2115.3	2164.3	2220.0	2267.4	2319.3	2366.0
12.5°	1826.1	1886.0	1957.5	2025.0	2099.7	2179.8	2240.8	2297.1	2360.1	2419.9	2491.8
15°	1808.4	1890.4	1973.9	2062.7	2162.8	2255.3	2343.4	2416.4	2484.2	2573.7	2667.8
17.5°	1785.7	1874.2	1979.6	2087.1	2191.7	2297.5	2406.5	2516.2	2601.7	2712.9	2786.5
20°	1764.7	1867.1	1975.4	2103.4	2207.9	2339.7	2448.0	2554.1	2671.5	2782.1	2870.1
22.5°	1735.2	1847.2	1962.2	2089.5	2227.2	2358.9	2484.2	2599.2	2716.7	2837.0	2943.7
25°	1697.7	1799.3	1935.5	2080.0	2217.0	2359.9	2503.7	2648.2	2774.6	2901.8	3001.1
27.5°	1633.9	1762.2	1889.0	2038.2	2190.4	2352.1	2505.8	2657.0	2789.5	2894.1	2955.6
30°	1601.4	1712.8	1850.5	2000.3	2165.0	2338.9	2499.2	2647.4	2770.9	2854.4	2879.2
32.5°	1553.2	1668.2	1802.9	1958.1	2132.5	2311.2	2478.1	2617.9	2720.8	2764.7	2734.7
35°	1481.8	1585.6	1721.8	1880.6	2061.9	2252.3	2417.2	2535.3	2587.9	2546.6	2443.4
37.5°	1396.0	1498.9	1635.7	1791.7	1979.3	2172.8	2321.9	2406.9	2389.4	2286.5	2132.9
40°	1335.8	1432.1	1562.3	1730.8	1913.7	2107.9	2238.8	2284.7	2236.6	2089.1	1925.7
42.5°	1268.9	1362.8	1493.6	1656.1	1849.9	2029.0	2143.1	2146.8	2066.1	1889.8	1725.9
45°	1167.2	1256.7	1380.2	1549.4	1728.6	1897.1	1972.4	1935.5	1786.5	1616.5	1451.6
47.5°	1066.8	1144.4	1266.0	1426.8	1596.9	1738.8	1776.1	1709.8	1551.0	1385.9	1233.1
50°	993.3	1071.6	1186.0	1339.5	1503.5	1626.3	1644.3	1556.2	1400.4	1234.2	1114.5
52.5°	922.9	1000.6	1110.8	1252.8	1403.1	1513.6	1514.3	1412.4	1257.2	1108.9	997.7
55°	819.5	889.5	988.8	1116.0	1250.0	1336.5	1315.4	1210.0	1075.3	946.7	849.6
57.5°	719.9	780.8	872.3	978.5	1096.5	1167.8	1132.8	1031.4	911.2	802.0	728.5
60°	655.4	713.4	791.6	891.7	991.1	1046.8	1013.7	921.9	811.2	723.2	659.2
62.5°	592.9	641.8	717.0	803.9	896.0	937.2	907.7	817.1	721.5	641.9	590.0
65°	504.2	544.1	604.3	678.8	745.7	781.2	756.3	672.0	599.0	541.9	500.4
67.5°	421.4	452.6	498.1	557.9	614.8	634.0	611.3	552.7	490.8	445.1	415.8
70°	364.2	393.6	432.0	477.9	527.5	547.8	525.3	478.6	428.2	386.1	357.4
72.5°	314.2	337.0	369.4	408.6	447.4	467.8	452.4	407.6	365.0	333.7	309.2
75°	239.3	258.9	281.4	309.2	339.4	353.0	339.4	308.5	279.2	255.9	238.6
77.5°	174.0	184.5	202.0	222.7	241.6	251.9	240.3	219.3	201.4	185.4	176.8
80°	132.4	140.0	152.0	168.5	181.3	191.1	183.6	166.3	152.0	141.5	137.7
82.5°	96.3	101.4	109.2	121.6	130.2	135.2	131.9	119.3	113.5	104.2	100.4
85°	47.4	50.4	55.7	59.5	67.0	67.8	68.5	63.2	58.0	55.7	52.7
87.5°	17.1	18.0	20.1	22.2	25.0	25.8	25.4	25.7	23.6	23.1	20.9
90°	3.8	5.6	7.3	9.0	10.5	11.7	12.9	14.1	15.4	16.3	17.2
92.5°	9.0	9.0	9.0	9.1	9.9	11.1	12.3	13.6	14.8	15.7	16.7
95°	33.2	27.9	22.6	17.3	14.8	14.9	15.1	15.3	15.4	16.3	17.2
97.5°	85.0	88.3	91.6	94.9	87.8	70.5	53.2	35.8	18.5	18.6	18.7
100°	117.5	120.4	123.1	125.9	116.6	95.2	73.7	52.2	30.8	28.2	25.5
102.5°	153.7	155.8	157.9	159.9	159.5	156.7	153.9	151.1	148.4	119.8	91.3
105°	211.5	212.4	213.4	214.3	215.2	215.9	216.7	217.5	218.3	219.7	221.1
107.5°	265.8	266.3	266.7	267.2	268.0	269.0	270.0	271.1	272.1	272.9	273.5
110°	302.7	303.2	303.7	304.1	304.8	305.8	306.7	307.6	308.5	308.9	309.2



TEST NUMBER: P332841-830

CATALOG NUMBER: S124DIW-S1195D770U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	338.9	339.8	340.5	341.4	342.0	342.5	342.9	343.4	343.8	343.7	343.7
115°	393.7	394.2	394.5	395.0	395.2	395.0	394.9	394.7	394.5	394.9	395.2
117.5°	443.5	444.1	444.7	445.4	445.8	446.2	446.5	446.9	447.2	447.1	447.0
120°	477.1	477.7	478.3	478.9	479.2	479.0	478.9	478.7	478.5	478.9	479.2
122.5°	508.1	508.5	508.9	509.3	509.5	509.8	510.0	510.2	510.5	510.7	510.9
125°	553.4	553.9	554.6	555.2	555.3	555.1	554.8	554.4	554.1	554.6	555.1
127.5°	595.4	595.6	595.7	595.9	596.3	597.0	597.8	598.4	599.2	599.1	599.0
130°	622.8	623.0	623.1	623.3	623.6	624.1	624.5	625.0	625.5	625.7	625.8
132.5°	648.2	648.5	648.7	648.9	649.4	650.0	650.6	651.2	651.8	652.0	652.1
135°	685.5	685.3	685.1	685.0	685.2	685.9	686.5	687.1	687.8	688.1	688.3
137.5°	719.2	719.3	719.3	719.3	719.7	720.4	721.0	721.8	722.5	722.7	723.1
140°	741.2	741.5	741.9	742.2	742.4	742.8	743.1	743.4	743.8	744.1	744.6
142.5°	761.1	761.7	762.1	762.7	763.1	763.3	763.5	763.6	763.8	764.2	764.6
145°	791.1	791.5	792.0	792.5	792.7	792.7	792.7	792.7	792.7	792.9	793.0
147.5°	815.4	816.2	817.1	818.0	818.3	818.2	818.0	817.8	817.7	817.8	817.9
150°	832.5	833.1	833.8	834.3	834.6	834.4	834.2	834.2	834.0	834.0	834.0
152.5°	846.9	847.4	847.9	848.4	848.5	848.2	848.0	847.7	847.4	847.6	847.9
155°	867.0	867.1	867.3	867.5	867.3	866.9	866.4	865.9	865.4	866.1	866.7
157.5°	884.0	883.9	883.8	883.7	883.4	882.9	882.3	881.7	881.3	882.0	882.9
160°	893.6	893.2	892.8	892.3	891.9	891.8	891.6	891.5	891.4	892.3	893.2
162.5°	902.5	901.9	901.4	900.7	900.3	900.2	900.0	899.8	899.8	900.7	901.6
165°	913.6	912.9	912.1	911.3	911.0	911.0	911.0	911.0	911.0	912.2	913.4
167.5°	922.6	921.8	921.0	920.1	919.7	919.6	919.5	919.5	919.4	920.7	922.1
170°	927.5	926.5	925.6	924.7	924.3	924.4	924.6	924.7	924.9	926.1	927.4
172.5°	930.9	929.9	929.0	928.0	927.7	927.8	927.9	928.1	928.3	929.5	930.8
175°	934.4	933.6	932.6	931.7	931.3	931.4	931.6	931.8	931.9	933.3	934.7
177.5°	936.2	935.4	934.4	933.6	933.3	933.6	933.8	934.1	934.2	935.3	936.3
180°	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4



TEST NUMBER: P332841-830

CATALOG NUMBER: S124DIW-S1195D770U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1816.7	1816.7	1816.7	1816.7	1816.7	1816.7	1816.7
2.5°	1914.8	1916.0	1921.4	1925.6	1926.8	1932.8	1933.4
5°	2083.0	2095.8	2120.6	2122.9	2126.7	2146.3	2131.2
7.5°	2280.2	2312.7	2334.4	2353.5	2360.4	2369.0	2367.2
10°	2406.6	2454.8	2478.9	2517.2	2518.8	2528.6	2522.5
12.5°	2533.6	2589.6	2633.6	2640.6	2672.9	2677.9	2686.2
15°	2713.7	2773.1	2834.0	2855.9	2900.3	2910.9	2927.3
17.5°	2882.9	2943.7	2986.4	3042.8	3061.0	3085.4	3068.8
20°	2975.5	3041.8	3096.0	3140.4	3159.1	3172.7	3171.2
22.5°	3031.5	3098.3	3142.2	3175.9	3193.4	3199.2	3198.9
25°	3066.6	3104.9	3118.5	3131.3	3111.7	3104.9	3107.9
27.5°	2969.1	2959.1	2923.8	2877.4	2829.2	2791.0	2770.2
30°	2834.8	2776.1	2722.7	2629.3	2581.2	2552.6	2527.1
32.5°	2644.6	2551.6	2448.7	2363.2	2308.5	2266.1	2259.7
35°	2318.6	2178.6	2053.0	1948.3	1894.1	1848.2	1837.7
37.5°	1971.2	1825.8	1712.6	1620.5	1562.3	1529.9	1499.7
40°	1740.6	1615.7	1504.3	1426.1	1381.7	1358.3	1339.5
42.5°	1563.0	1449.0	1338.1	1278.6	1238.4	1224.1	1213.1
45°	1317.7	1211.5	1134.8	1089.7	1066.3	1042.3	1031.0
47.5°	1121.2	1034.9	984.3	945.9	921.0	906.6	899.5
50°	1009.9	939.1	894.0	864.7	842.1	830.8	824.8
52.5°	911.2	853.1	815.1	791.8	776.5	768.2	765.8
55°	784.9	740.5	716.4	696.1	684.9	677.3	674.3
57.5°	682.2	648.1	628.5	611.8	607.5	601.2	599.0
60°	614.8	588.5	571.9	560.6	556.9	549.3	550.8
62.5°	555.3	533.7	519.5	513.1	508.1	501.8	503.9
65°	469.6	453.7	446.3	440.3	434.2	430.5	433.5
67.5°	394.0	383.2	373.0	369.5	366.5	365.9	362.7
70°	344.7	335.6	326.6	324.3	324.3	321.3	320.6
72.5°	297.1	290.5	284.5	282.8	280.4	281.6	278.4
75°	229.5	224.2	222.0	219.7	219.0	219.0	216.7
77.5°	169.7	165.7	162.1	162.1	159.4	158.3	158.1
80°	128.7	127.1	124.1	124.1	122.6	123.4	121.9
82.5°	96.8	94.6	94.1	92.8	90.8	90.9	89.4
85°	51.9	49.7	48.9	46.7	45.1	46.7	45.1
87.5°	21.7	21.3	20.8	19.7	19.1	19.2	17.4
90°	18.2	19.1	19.7	20.1	20.4	20.6	21.0
92.5°	17.6	18.6	19.0	19.1	19.2	19.2	19.3
95°	18.2	19.1	19.7	19.8	20.0	20.2	20.3
97.5°	18.8	18.9	18.9	19.1	19.3	19.4	19.6
100°	22.8	20.2	18.9	19.1	19.3	19.4	19.6
102.5°	62.8	34.3	20.0	20.1	20.1	20.1	20.2
105°	222.4	223.9	221.8	216.2	210.6	205.0	199.4
107.5°	274.2	274.9	275.5	276.2	276.7	277.3	277.9
110°	309.4	309.8	310.2	310.7	311.1	311.6	312.1



TEST NUMBER: P332841-830

CATALOG NUMBER: S124DIW-S1195D770U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	343.7	343.6	343.8	344.4	345.0	345.6	346.2
115°	395.5	395.9	396.0	396.0	396.0	396.0	396.0
117.5°	447.0	447.0	446.9	446.9	446.8	446.7	446.7
120°	479.5	479.8	479.8	479.5	479.2	478.9	478.5
122.5°	511.0	511.2	511.1	510.9	510.5	510.2	509.9
125°	555.5	556.0	556.3	556.5	556.6	556.8	556.9
127.5°	598.9	598.8	598.7	598.6	598.4	598.3	598.2
130°	625.9	626.1	626.1	626.1	626.1	626.1	626.1
132.5°	652.2	652.4	652.4	652.3	652.1	652.1	652.0
135°	688.7	689.0	689.3	689.6	689.9	690.2	690.5
137.5°	723.5	723.8	724.0	723.9	723.8	723.7	723.6
140°	745.1	745.6	745.9	746.0	746.2	746.4	746.5
142.5°	764.9	765.3	765.4	765.4	765.4	765.5	765.5
145°	793.1	793.3	793.5	793.8	794.2	794.5	794.8
147.5°	818.1	818.2	818.4	818.5	818.7	818.9	819.0
150°	834.0	834.0	834.1	834.2	834.3	834.5	834.6
152.5°	848.1	848.4	848.5	848.4	848.3	848.2	848.1
155°	867.3	867.9	868.0	867.5	867.0	866.6	866.2
157.5°	883.7	884.5	884.5	883.7	882.9	882.0	881.3
160°	894.1	895.0	895.0	894.1	893.2	892.3	891.4
162.5°	902.5	903.4	903.4	902.4	901.3	900.2	899.2
165°	914.6	915.9	915.9	914.5	913.0	911.6	910.2
167.5°	923.4	924.8	924.7	923.1	921.6	920.0	918.5
170°	928.7	929.9	929.7	928.2	926.6	925.1	923.5
172.5°	932.0	933.2	933.0	931.3	929.7	928.0	926.3
175°	936.1	937.5	937.3	935.4	933.6	931.7	929.8
177.5°	937.3	938.3	938.0	936.5	935.0	933.6	932.1
180°	935.4	935.4	935.4	935.4	935.4	935.4	935.4

(END OF REPORT)