

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332811-935

Luminaire Tested: **S124DIW-S1020D770U935-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332811-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S1020D770U935-4F0-1E-UDD-A
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 770 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6610.0 lumens
Efficiency: N/A
Efficacy: 123.3 lumens/watt
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 53.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332811-935

CATALOG NUMBER: S124DIW-S1020D770U935-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332811-935

CATALOG NUMBER: S124DIW-S1020D770U935-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	102	102	102	102	89	89	89	77	77	77	65	65	65	60
1	100	96	92	89	94	90	87	83	78	76	74	68	66	64	58	57	56	51
2	92	84	78	73	85	79	74	69	69	65	61	60	57	54	52	49	47	43
3	84	74	67	61	78	70	63	58	61	56	52	53	49	46	46	43	41	37
4	77	66	58	52	71	62	55	49	55	49	45	48	43	40	41	38	35	32
5	71	59	51	45	66	55	48	43	49	43	39	43	38	35	37	34	31	28
6	65	53	45	39	61	50	43	37	44	38	34	39	34	31	34	30	27	25
7	60	48	40	34	56	45	38	33	40	34	30	35	31	27	31	27	24	22
8	56	44	36	31	52	41	34	29	37	31	27	33	28	24	29	25	22	20
9	52	40	32	27	49	38	31	26	34	28	24	30	25	22	26	23	20	18
10	49	37	29	25	46	35	28	24	31	26	22	28	23	20	24	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	11599	11599	11599	11599
5°	13661	11629	10264	11629
10°	16356	11579	9241	11579
15°	19351	11462	8487	11462
20°	21549	11342	7814	11342
25°	21896	11166	7349	11166
30°	18632	10997	7202	10997
35°	14325	10723	7203	10723
40°	11166	10400	7339	10400
45°	9310	9914	7462	9914
50°	8194	9323	7714	9323
55°	7506	8612	8025	8612
60°	7035	7976	8399	7976
65°	6550	7265	8709	7265
70°	5986	6559	8908	6559
75°	5346	5774	8799	5774
80°	4482	4733	8522	4733
85°	3307	3418	8160	3418



TEST NUMBER: P332811-935

CATALOG NUMBER: S124DIW-S1020D770U935-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	140.0	2.1
10°-20°	431.5	6.5
20°-30°	684.2	10.4
30°-40°	761.4	11.5
40°-50°	693.1	10.5
50°-60°	566.4	8.6
60°-70°	404.3	6.1
70°-80°	222.6	3.4
80°-90°	63.3	1.0
90°-100°	29.2	0.4
100°-110°	186.3	2.8
110°-120°	356.5	5.4
120°-130°	452.5	6.8
130°-140°	484.2	7.3
140°-150°	452.7	6.8
150°-160°	365.1	5.5
160°-170°	235.5	3.6
170°-180°	81.2	1.2
0°-30°	1255.6	19.0
0°-40°	2017.1	30.5
0°-60°	3276.5	49.6
0°-90°	3966.8	60.0
90°-120°	572.0	8.7
90°-150°	1961.4	29.7
90°-180°	2643.0	40.0
0°-180°	6610.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1437	1437	1437	1437	1437	
5°	1686	1435	1267	1435	1686	171
15°	2315	1371	1016	1371	2315	654
25°	2458	1254	825	1254	2458	1084
35°	1454	1088	731	1088	1454	923
45°	816	868	654	868	816	642
55°	533	612	570	612	533	482
65°	343	380	456	380	343	339
75°	171	185	282	185	171	182
85°	36	37	88	37	36	44
90°	19	2	19	2	19	10
95°	18	35	18	35	18	15
105°	182	192	182	192	182	159
115°	362	359	362	359	362	358
125°	509	505	509	505	509	453
135°	631	626	631	626	631	486
145°	726	722	726	722	726	454
155°	791	792	791	792	791	365
165°	832	835	832	835	832	235
175°	849	854	849	854	849	81
180°	854	854	854	854	854	



TEST NUMBER: P332811-935

CATALOG NUMBER: S124DIW-S1020D770U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8
2.5°	1529.2	1528.8	1524.0	1523.0	1519.7	1515.4	1514.5	1506.8	1491.6	1484.5	1482.6
5°	1685.7	1697.5	1682.0	1679.1	1677.3	1657.7	1647.5	1635.6	1608.3	1592.2	1579.7
7.5°	1872.3	1873.7	1867.0	1861.5	1846.3	1829.2	1803.5	1776.2	1743.5	1709.6	1683.9
10°	1995.2	1999.9	1992.2	1991.0	1960.7	1941.6	1903.5	1871.4	1834.4	1793.4	1755.9
12.5°	2124.7	2118.0	2114.1	2088.6	2083.0	2048.2	2004.0	1970.9	1914.0	1866.7	1816.8
15°	2315.4	2302.3	2294.0	2258.8	2241.6	2193.4	2146.3	2110.1	2035.7	1964.8	1911.2
17.5°	2427.2	2440.4	2421.1	2406.7	2362.1	2328.2	2280.2	2204.0	2145.8	2057.8	1990.2
20°	2508.3	2509.4	2498.7	2483.8	2448.7	2405.9	2353.5	2270.1	2200.5	2113.0	2020.2
22.5°	2530.1	2530.4	2525.8	2511.9	2485.4	2450.6	2397.8	2328.2	2243.9	2148.7	2055.9
25°	2458.2	2455.8	2461.3	2476.7	2466.6	2455.8	2425.5	2373.7	2295.2	2194.5	2094.6
27.5°	2191.1	2207.5	2237.7	2275.9	2312.6	2340.5	2348.4	2337.8	2289.1	2206.3	2101.6
30°	1998.7	2019.0	2041.6	2079.7	2153.4	2195.7	2242.2	2277.3	2257.6	2191.6	2094.0
32.5°	1787.3	1792.3	1825.9	1869.2	1936.8	2018.1	2091.7	2163.0	2186.7	2152.1	2070.6
35°	1453.5	1461.8	1498.1	1541.0	1623.8	1723.1	1833.8	1932.7	2014.2	2046.9	2005.3
37.5°	1186.1	1210.0	1235.7	1281.8	1354.6	1444.1	1559.1	1687.0	1808.5	1889.9	1903.8
40°	1059.5	1074.4	1092.8	1127.9	1189.8	1277.9	1376.7	1523.2	1652.3	1769.0	1807.1
42.5°	959.5	968.2	979.5	1011.2	1058.4	1146.0	1236.2	1365.0	1494.7	1634.2	1698.1
45°	815.5	824.4	843.4	861.9	897.6	958.3	1042.2	1148.1	1278.5	1413.1	1530.9
47.5°	711.4	717.1	728.4	748.2	778.5	818.6	886.8	975.3	1096.1	1226.8	1352.3
50°	652.4	657.1	666.1	683.9	707.1	742.8	798.7	881.5	976.1	1107.7	1230.9
52.5°	605.7	607.6	614.2	626.3	644.7	674.8	720.7	789.1	877.1	994.4	1117.1
55°	533.3	535.7	541.7	550.6	566.6	585.7	620.8	672.0	748.8	850.6	957.1
57.5°	473.8	475.4	480.4	483.9	497.1	512.6	539.6	576.2	634.4	720.7	815.8
60°	435.7	434.5	440.5	443.4	452.4	465.5	486.3	521.4	572.0	641.6	729.1
62.5°	398.6	396.9	401.9	405.8	411.0	422.1	439.1	466.7	507.7	570.7	646.3
65°	342.9	340.4	343.5	348.2	352.9	359.0	371.4	395.8	428.5	473.8	531.5
67.5°	286.9	289.4	289.9	292.2	295.0	303.1	311.7	328.9	352.0	388.2	437.1
70°	253.6	254.2	256.6	256.6	258.3	265.4	272.6	282.8	305.3	338.7	378.6
72.5°	220.2	222.7	221.8	223.7	225.0	229.7	235.0	244.6	263.9	288.7	322.4
75°	171.4	173.2	173.2	173.8	175.6	177.4	181.5	188.6	202.3	220.8	244.0
77.5°	125.0	125.3	126.1	128.2	128.2	131.0	134.1	139.9	146.6	159.3	173.4
80°	96.4	97.6	97.0	98.2	98.2	100.6	101.8	108.9	111.9	120.2	131.6
82.5°	70.7	71.9	71.8	73.4	74.4	74.9	76.5	79.4	82.4	89.7	94.4
85°	35.7	36.9	35.7	36.9	38.7	39.3	41.1	41.7	44.1	45.8	50.0
87.5°	14.3	15.7	15.6	16.0	17.0	17.3	17.7	17.0	18.7	19.0	20.7
90°	19.2	18.9	18.6	18.3	18.0	17.5	16.6	15.8	14.9	14.0	12.9
92.5°	17.7	17.6	17.6	17.5	17.4	17.0	16.1	15.2	14.4	13.5	12.4
95°	18.5	18.4	18.3	18.1	18.0	17.5	16.6	15.8	14.9	14.0	13.9
97.5°	17.9	17.7	17.7	17.5	17.3	17.2	17.1	17.0	17.0	16.9	32.7
100°	17.9	17.7	17.7	17.5	17.3	18.4	20.8	23.3	25.7	28.2	47.7
102.5°	18.4	18.3	18.3	18.3	18.3	31.3	57.3	83.4	109.4	135.5	138.0
105°	182.2	187.3	192.3	197.5	202.6	204.5	203.2	202.0	200.7	199.4	198.7
107.5°	253.8	253.3	252.8	252.3	251.7	251.2	250.5	249.9	249.3	248.6	247.6
110°	285.1	284.6	284.2	283.8	283.4	283.0	282.7	282.4	282.1	281.8	281.0



TEST NUMBER: P332811-935

CATALOG NUMBER: S124DIW-S1020D770U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	316.2	315.7	315.1	314.6	314.1	313.8	313.9	313.9	314.0	314.1	313.7
115°	361.7	361.7	361.7	361.7	361.7	361.6	361.3	361.0	360.8	360.4	360.6
117.5°	408.0	408.0	408.1	408.2	408.2	408.3	408.4	408.4	408.5	408.5	408.2
120°	437.1	437.5	437.7	438.0	438.2	438.2	438.0	437.7	437.5	437.1	437.3
122.5°	465.8	466.1	466.3	466.7	466.9	467.0	466.8	466.7	466.5	466.3	466.1
125°	508.8	508.6	508.4	508.3	508.2	507.9	507.5	507.0	506.6	506.2	506.4
127.5°	546.5	546.6	546.6	546.8	546.9	547.0	547.1	547.2	547.3	547.3	546.6
130°	572.0	572.0	572.0	572.0	572.0	572.0	571.8	571.6	571.5	571.4	570.9
132.5°	595.6	595.6	595.7	595.9	596.0	596.0	595.8	595.6	595.6	595.4	594.9
135°	630.8	630.5	630.3	629.9	629.6	629.4	629.1	628.8	628.5	628.3	627.7
137.5°	661.0	661.1	661.2	661.2	661.3	661.2	660.9	660.6	660.2	660.0	659.4
140°	681.9	681.8	681.7	681.5	681.4	681.1	680.6	680.2	679.8	679.4	679.1
142.5°	699.3	699.3	699.2	699.2	699.2	699.0	698.7	698.4	698.1	697.8	697.6
145°	726.0	725.7	725.5	725.1	724.9	724.7	724.5	724.4	724.3	724.1	724.1
147.5°	748.1	748.0	747.9	747.7	747.6	747.4	747.3	747.2	747.1	747.0	747.1
150°	762.4	762.3	762.2	762.1	761.9	761.8	761.8	761.8	761.8	761.8	762.0
152.5°	774.7	774.8	774.9	775.0	775.1	775.0	774.7	774.6	774.3	774.1	774.4
155°	791.3	791.6	792.0	792.5	792.9	792.8	792.3	791.7	791.2	790.6	791.0
157.5°	805.0	805.7	806.5	807.3	808.0	808.0	807.3	806.5	805.7	805.0	805.5
160°	814.2	815.1	816.0	816.7	817.6	817.6	816.7	816.0	815.1	814.2	814.3
162.5°	821.4	822.3	823.3	824.3	825.3	825.3	824.4	823.6	822.8	821.9	822.0
165°	831.5	832.8	834.1	835.3	836.6	836.6	835.5	834.4	833.3	832.2	832.2
167.5°	839.0	840.4	841.9	843.3	844.7	844.8	843.5	842.3	841.0	839.8	839.9
170°	843.6	845.1	846.4	847.9	849.3	849.5	848.3	847.1	846.0	844.9	844.7
172.5°	846.2	847.7	849.3	850.8	852.3	852.5	851.4	850.2	849.1	848.0	847.8
175°	849.4	851.1	852.8	854.5	856.2	856.4	855.1	853.9	852.6	851.3	851.2
177.5°	851.4	852.8	854.1	855.5	856.9	857.1	856.2	855.3	854.4	853.4	853.3
180°	854.5	854.5	854.5	854.5	854.5	854.5	854.5	854.5	854.5	854.5	854.5



TEST NUMBER: P332811-935

CATALOG NUMBER: S124DIW-S1020D770U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8
2.5°	1483.1	1476.4	1471.6	1467.8	1457.3	1451.1	1446.4	1439.7	1432.1	1424.0	1414.0
5°	1567.2	1547.0	1532.1	1509.5	1488.1	1470.2	1451.7	1435.0	1414.8	1392.8	1376.7
7.5°	1655.6	1625.6	1587.0	1553.5	1515.9	1483.2	1453.9	1423.8	1392.7	1362.4	1334.7
10°	1711.8	1673.2	1630.3	1579.7	1532.1	1489.8	1450.5	1412.5	1375.5	1338.6	1307.1
12.5°	1772.3	1724.1	1660.8	1601.6	1548.3	1491.8	1444.3	1397.7	1353.1	1314.3	1277.6
15°	1853.5	1783.8	1710.6	1631.5	1561.3	1495.2	1430.3	1371.4	1321.4	1270.1	1234.5
17.5°	1903.4	1817.2	1733.5	1650.8	1565.7	1482.5	1412.5	1344.5	1281.9	1231.1	1186.0
20°	1936.2	1850.5	1746.4	1663.6	1562.5	1476.7	1395.8	1320.2	1254.7	1200.6	1154.1
22.5°	1964.8	1865.8	1761.6	1652.7	1552.0	1461.0	1372.4	1296.4	1229.5	1172.4	1127.9
25°	1980.3	1866.6	1753.5	1645.2	1530.9	1423.1	1342.8	1253.5	1182.1	1122.0	1074.4
27.5°	1981.9	1860.4	1732.4	1612.1	1494.1	1393.8	1292.4	1212.5	1138.4	1074.9	1029.2
30°	1976.7	1849.9	1712.4	1582.1	1463.6	1354.7	1266.6	1179.7	1104.1	1041.0	993.4
32.5°	1960.1	1828.0	1686.7	1548.8	1426.0	1319.5	1228.6	1145.9	1072.2	1010.0	960.1
35°	1911.9	1781.5	1630.9	1487.5	1361.8	1254.1	1172.0	1088.0	1014.3	955.3	907.1
37.5°	1836.5	1718.6	1565.6	1417.1	1293.7	1185.5	1104.1	1028.3	961.7	901.9	852.5
40°	1770.7	1667.2	1513.6	1369.0	1235.7	1132.7	1056.5	986.9	920.8	864.3	817.3
42.5°	1695.1	1604.8	1463.2	1309.9	1181.4	1078.0	1003.7	941.2	878.9	826.6	779.6
45°	1560.0	1500.6	1367.2	1225.5	1091.7	994.0	923.2	868.4	816.1	764.8	725.6
47.5°	1404.8	1375.3	1263.1	1128.5	1001.4	905.2	843.8	793.2	747.3	703.9	669.3
50°	1300.5	1286.2	1189.2	1059.5	938.1	847.6	785.7	742.3	702.9	664.9	632.1
52.5°	1197.7	1197.2	1109.7	990.9	878.6	791.4	730.0	689.4	655.3	624.4	595.0
55°	1040.4	1057.1	988.7	882.7	782.1	703.5	648.2	611.9	588.1	562.5	540.4
57.5°	896.0	923.7	867.2	773.9	690.0	617.6	569.4	542.1	516.8	501.3	485.3
60°	801.8	827.9	783.9	705.3	626.2	564.3	518.4	494.0	472.0	461.3	450.0
62.5°	718.0	741.3	708.7	635.8	567.1	507.6	468.9	445.5	430.6	418.9	411.4
65°	598.2	617.9	589.9	536.9	477.9	430.3	398.8	380.3	366.1	361.3	352.9
67.5°	483.5	501.4	486.3	441.3	394.0	358.0	333.3	315.6	307.1	303.0	297.0
70°	415.4	433.3	417.2	378.0	341.6	311.3	288.1	277.9	269.1	267.3	258.9
72.5°	357.8	370.0	354.0	323.2	292.1	266.6	248.6	238.0	233.3	230.1	225.6
75°	268.5	279.1	268.5	244.6	222.6	204.7	189.2	185.1	179.8	178.0	175.0
77.5°	190.0	199.2	191.1	176.2	159.7	145.9	137.6	132.2	131.0	127.9	129.4
80°	145.3	151.2	143.4	133.4	120.2	110.7	104.8	101.8	98.2	97.0	99.4
82.5°	104.3	106.9	103.0	96.2	86.4	80.2	76.2	72.8	72.0	72.2	72.2
85°	54.2	53.6	53.0	47.0	44.1	39.9	37.5	36.9	36.3	37.5	38.7
87.5°	20.5	20.7	20.0	17.8	16.1	14.4	13.5	12.7	13.5	14.4	15.2
90°	11.8	10.7	9.6	8.2	6.6	5.1	3.4	1.9	3.4	5.1	6.6
92.5°	11.3	10.2	9.0	8.4	8.3	8.3	8.2	8.1	8.2	8.3	8.3
95°	13.8	13.6	13.5	15.8	20.7	25.5	30.3	35.1	30.3	25.5	20.7
97.5°	48.6	64.4	80.2	86.7	83.7	80.7	77.7	74.6	77.7	80.7	83.7
100°	67.3	87.0	106.5	115.0	112.4	109.9	107.4	104.8	107.4	109.9	112.4
102.5°	140.6	143.2	145.7	146.0	144.2	142.3	140.4	138.5	140.4	142.3	144.2
105°	197.9	197.3	196.6	195.8	194.9	194.1	193.2	192.3	193.2	194.1	194.9
107.5°	246.7	245.7	244.8	244.1	243.7	243.2	242.8	242.4	242.8	243.2	243.7
110°	280.2	279.3	278.4	277.8	277.4	277.0	276.6	276.1	276.6	277.0	277.4



TEST NUMBER: P332811-935

CATALOG NUMBER: S124DIW-S1020D770U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	313.2	312.9	312.5	311.9	311.1	310.4	309.6	308.8	309.6	310.4	311.1
115°	360.8	360.8	361.0	360.8	360.4	360.1	359.6	359.2	359.6	360.1	360.4
117.5°	407.9	407.6	407.3	406.8	406.2	405.7	405.1	404.6	405.1	405.7	406.2
120°	437.5	437.6	437.7	437.5	437.0	436.4	435.8	435.2	435.8	436.4	437.0
122.5°	465.9	465.7	465.5	465.2	464.9	464.5	464.2	463.9	464.2	464.5	464.9
125°	506.8	507.0	507.3	507.1	506.6	506.0	505.5	504.9	505.5	506.0	506.6
127.5°	546.0	545.4	544.8	544.3	544.2	544.1	543.9	543.7	543.9	544.1	544.2
130°	570.5	570.1	569.6	569.4	569.2	569.1	568.9	568.8	568.9	569.1	569.2
132.5°	594.3	593.7	593.2	592.8	592.5	592.4	592.1	591.9	592.1	592.4	592.5
135°	627.1	626.5	625.9	625.8	625.9	626.0	626.2	626.3	626.2	626.0	625.9
137.5°	658.7	658.1	657.5	657.1	657.0	657.0	656.9	656.9	656.9	657.0	657.0
140°	678.8	678.6	678.2	678.0	677.7	677.3	677.1	676.8	677.1	677.3	677.7
142.5°	697.4	697.2	697.1	696.7	696.2	695.8	695.3	694.7	695.3	695.8	696.2
145°	724.1	724.1	724.1	723.9	723.5	723.1	722.6	722.2	722.6	723.1	723.5
147.5°	747.3	747.4	747.5	747.3	746.4	745.6	744.9	744.1	744.9	745.6	746.4
150°	762.1	762.2	762.4	762.2	761.6	761.0	760.4	759.9	760.4	761.0	761.6
152.5°	774.6	774.8	775.1	775.0	774.6	774.1	773.6	773.2	773.6	774.1	774.6
155°	791.4	791.9	792.3	792.5	792.3	792.1	792.0	791.9	792.0	792.1	792.3
157.5°	806.0	806.5	806.9	807.3	807.4	807.4	807.5	807.6	807.5	807.4	807.4
160°	814.5	814.7	814.8	815.1	815.5	816.0	816.3	816.7	816.3	816.0	815.5
162.5°	822.2	822.3	822.4	822.8	823.4	823.9	824.4	824.9	824.4	823.9	823.4
165°	832.2	832.2	832.2	832.5	833.2	833.9	834.6	835.3	834.6	833.9	833.2
167.5°	840.0	840.1	840.2	840.5	841.3	842.1	842.7	843.5	842.7	842.1	841.3
170°	844.6	844.5	844.3	844.7	845.5	846.4	847.2	848.1	847.2	846.4	845.5
172.5°	847.7	847.6	847.4	847.7	848.6	849.5	850.3	851.2	850.3	849.5	848.6
175°	851.0	850.8	850.8	851.1	852.0	852.8	853.6	854.5	853.6	852.8	852.0
177.5°	853.0	852.8	852.6	852.8	853.6	854.5	855.2	856.0	855.2	854.5	853.6
180°	854.5	854.5	854.5	854.5	854.5	854.5	854.5	854.5	854.5	854.5	854.5



TEST NUMBER: P332811-935

CATALOG NUMBER: S124DIW-S1020D770U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8
2.5°	1409.2	1405.0	1398.8	1390.2	1383.0	1375.4	1373.6	1370.6	1376.4	1371.6	1370.2
5°	1363.0	1350.6	1334.5	1316.0	1305.3	1289.9	1286.9	1280.9	1275.0	1274.4	1268.4
7.5°	1314.1	1295.8	1274.7	1255.9	1238.5	1221.6	1210.6	1208.2	1199.4	1194.2	1188.3
10°	1282.7	1260.1	1235.7	1217.8	1197.6	1179.7	1167.3	1160.1	1154.1	1147.5	1141.6
12.5°	1245.5	1221.5	1201.4	1182.1	1158.0	1144.4	1123.9	1111.5	1110.3	1110.4	1094.9
15°	1202.3	1178.5	1147.5	1120.2	1107.1	1080.9	1069.6	1055.3	1046.4	1037.4	1030.4
17.5°	1153.0	1123.3	1099.2	1067.7	1042.7	1021.8	1007.0	998.4	985.0	972.3	963.2
20°	1122.0	1090.5	1064.8	1031.5	1004.1	978.5	966.0	954.2	944.0	933.3	923.2
22.5°	1090.5	1057.6	1026.2	993.9	968.5	941.4	929.4	913.2	903.5	897.6	887.4
25°	1041.0	1005.3	969.6	938.7	912.5	888.6	872.6	860.1	849.4	844.6	838.1
27.5°	987.2	951.7	917.2	882.1	852.4	835.1	822.3	812.8	806.7	800.3	797.4
30°	953.0	916.0	879.2	846.4	819.0	801.8	789.9	783.3	778.5	775.6	772.6
32.5°	918.2	881.8	842.9	813.0	788.5	773.2	764.1	757.6	755.2	754.1	753.0
35°	862.5	825.5	789.9	763.1	739.9	733.9	726.2	722.6	721.4	725.6	727.4
37.5°	808.6	774.3	741.4	715.4	700.3	691.6	688.9	689.1	693.3	697.0	701.3
40°	773.8	740.5	709.5	686.9	672.6	667.3	666.1	669.0	673.8	678.0	682.7
42.5°	739.9	707.1	679.0	657.8	647.8	642.9	643.7	646.6	653.3	658.4	665.6
45°	687.5	660.1	632.7	615.4	607.1	608.3	608.3	613.6	620.2	627.9	635.7
47.5°	638.1	610.4	588.0	573.4	569.1	568.1	571.4	578.4	587.8	597.4	608.2
50°	604.8	578.5	558.9	545.8	541.1	542.9	547.6	554.1	565.4	577.4	588.7
52.5°	570.9	547.1	528.9	516.8	513.4	516.7	521.4	531.8	541.7	554.5	568.2
55°	518.4	498.2	483.9	475.0	473.8	475.6	481.0	492.2	506.5	522.6	535.7
57.5°	466.1	449.3	436.2	430.0	430.6	432.2	441.1	454.5	469.8	486.9	503.8
60°	430.9	415.4	404.8	400.0	400.5	404.2	414.8	427.4	446.4	463.0	481.0
62.5°	397.6	384.0	373.8	369.5	368.7	376.5	386.8	399.8	418.8	437.4	456.7
65°	344.1	333.3	325.0	322.6	324.4	330.4	343.5	360.7	376.8	396.4	416.6
67.5°	291.6	282.8	277.2	278.2	280.3	289.1	300.1	315.0	333.2	353.5	373.6
70°	258.3	249.9	245.2	245.8	249.4	260.1	269.7	284.5	304.2	325.0	341.6
72.5°	224.0	218.5	214.3	216.8	220.3	227.7	239.6	254.5	271.8	291.2	308.8
75°	172.0	172.0	169.6	171.4	176.8	183.9	192.9	208.4	225.6	241.1	255.4
77.5°	127.6	126.3	127.9	130.0	133.1	141.5	151.8	162.8	175.8	191.3	203.1
80°	97.6	98.2	101.2	104.8	106.0	112.5	123.2	133.4	143.4	156.5	167.8
82.5°	73.4	74.0	75.5	80.0	81.2	88.3	95.1	105.2	114.4	123.2	132.6
85°	39.9	39.9	42.9	44.6	47.6	52.3	56.6	62.5	70.9	76.8	85.7
87.5°	16.9	17.1	19.3	20.5	22.1	24.7	25.8	31.3	33.3	35.9	40.3
90°	8.2	9.6	10.7	11.8	12.9	14.0	14.9	15.8	16.6	17.5	18.0
92.5°	8.4	9.0	10.2	11.3	12.4	13.5	14.4	15.2	16.1	17.0	17.4
95°	15.8	13.5	13.6	13.8	13.9	14.0	14.9	15.8	16.6	17.5	18.0
97.5°	86.7	80.2	64.4	48.6	32.7	16.9	17.0	17.0	17.1	17.2	17.3
100°	115.0	106.5	87.0	67.3	47.7	28.2	25.7	23.3	20.8	18.4	17.3
102.5°	146.0	145.7	143.2	140.6	138.0	135.5	109.4	83.4	57.3	31.3	18.3
105°	195.8	196.6	197.3	197.9	198.7	199.4	200.7	202.0	203.2	204.5	202.6
107.5°	244.1	244.8	245.7	246.7	247.6	248.6	249.3	249.9	250.5	251.2	251.7
110°	277.8	278.4	279.3	280.2	281.0	281.8	282.1	282.4	282.7	283.0	283.4



TEST NUMBER: P332811-935

CATALOG NUMBER: S124DIW-S1020D770U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	311.9	312.5	312.9	313.2	313.7	314.1	314.0	313.9	313.9	313.8	314.1
115°	360.8	361.0	360.8	360.8	360.6	360.4	360.8	361.0	361.3	361.6	361.7
117.5°	406.8	407.3	407.6	407.9	408.2	408.5	408.5	408.4	408.4	408.3	408.2
120°	437.5	437.7	437.6	437.5	437.3	437.1	437.5	437.7	438.0	438.2	438.2
122.5°	465.2	465.5	465.7	465.9	466.1	466.3	466.5	466.7	466.8	467.0	466.9
125°	507.1	507.3	507.0	506.8	506.4	506.2	506.6	507.0	507.5	507.9	508.2
127.5°	544.3	544.8	545.4	546.0	546.6	547.3	547.3	547.2	547.1	547.0	546.9
130°	569.4	569.6	570.1	570.5	570.9	571.4	571.5	571.6	571.8	572.0	572.0
132.5°	592.8	593.2	593.7	594.3	594.9	595.4	595.6	595.6	595.8	596.0	596.0
135°	625.8	625.9	626.5	627.1	627.7	628.3	628.5	628.8	629.1	629.4	629.6
137.5°	657.1	657.5	658.1	658.7	659.4	660.0	660.2	660.6	660.9	661.2	661.3
140°	678.0	678.2	678.6	678.8	679.1	679.4	679.8	680.2	680.6	681.1	681.4
142.5°	696.7	697.1	697.2	697.4	697.6	697.8	698.1	698.4	698.7	699.0	699.2
145°	723.9	724.1	724.1	724.1	724.1	724.1	724.3	724.4	724.5	724.7	724.9
147.5°	747.3	747.5	747.4	747.3	747.1	747.0	747.1	747.2	747.3	747.4	747.6
150°	762.2	762.4	762.2	762.1	762.0	761.8	761.8	761.8	761.8	761.8	761.9
152.5°	775.0	775.1	774.8	774.6	774.4	774.1	774.3	774.6	774.7	775.0	775.1
155°	792.5	792.3	791.9	791.4	791.0	790.6	791.2	791.7	792.3	792.8	792.9
157.5°	807.3	806.9	806.5	806.0	805.5	805.0	805.7	806.5	807.3	808.0	808.0
160°	815.1	814.8	814.7	814.5	814.3	814.2	815.1	816.0	816.7	817.6	817.6
162.5°	822.8	822.4	822.3	822.2	822.0	821.9	822.8	823.6	824.4	825.3	825.3
165°	832.5	832.2	832.2	832.2	832.2	832.2	833.3	834.4	835.5	836.6	836.6
167.5°	840.5	840.2	840.1	840.0	839.9	839.8	841.0	842.3	843.5	844.8	844.7
170°	844.7	844.3	844.5	844.6	844.7	844.9	846.0	847.1	848.3	849.5	849.3
172.5°	847.7	847.4	847.6	847.7	847.8	848.0	849.1	850.2	851.4	852.5	852.3
175°	851.1	850.8	850.8	851.0	851.2	851.3	852.6	853.9	855.1	856.4	856.2
177.5°	852.8	852.6	852.8	853.0	853.3	853.4	854.4	855.3	856.2	857.1	856.9
180°	854.5	854.5	854.5	854.5	854.5	854.5	854.5	854.5	854.5	854.5	854.5



TEST NUMBER: P332811-935

CATALOG NUMBER: S124DIW-S1020D770U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8
2.5°	1369.2	1368.3	1364.9	1364.5	1364.9	1368.3	1369.2	1370.2	1371.6	1376.4	1370.6
5°	1264.8	1261.9	1260.1	1266.6	1260.1	1261.9	1264.8	1268.4	1274.4	1275.0	1280.9
7.5°	1186.1	1183.8	1178.5	1176.9	1178.5	1183.8	1186.1	1188.3	1194.2	1199.4	1208.2
10°	1135.7	1133.2	1128.5	1127.3	1128.5	1133.2	1135.7	1141.6	1147.5	1154.1	1160.1
12.5°	1087.1	1082.4	1081.4	1082.5	1081.4	1082.4	1087.1	1094.9	1110.4	1110.3	1111.5
15°	1022.6	1020.2	1013.7	1015.5	1013.7	1020.2	1022.6	1030.4	1037.4	1046.4	1055.3
17.5°	959.0	956.1	948.2	955.2	948.2	956.1	959.0	963.2	972.3	985.0	998.4
20°	919.0	914.2	910.1	909.5	910.1	914.2	919.0	923.2	933.3	944.0	954.2
22.5°	880.9	876.7	876.2	872.4	876.2	876.7	880.9	887.4	897.6	903.5	913.2
25°	833.3	829.1	827.9	825.0	827.9	829.1	833.3	838.1	844.6	849.4	860.1
27.5°	796.8	794.7	792.6	793.5	792.6	794.7	796.8	797.4	800.3	806.7	812.8
30°	774.4	773.8	772.6	772.6	772.6	773.8	774.4	772.6	775.6	778.5	783.3
32.5°	755.8	755.7	756.4	756.4	756.4	755.7	755.8	753.0	754.1	755.2	757.6
35°	729.7	731.5	732.7	730.9	732.7	731.5	729.7	727.4	725.6	721.4	722.6
37.5°	706.2	707.9	709.6	711.6	709.6	707.9	706.2	701.3	697.0	693.3	689.1
40°	688.0	692.2	693.4	696.4	693.4	692.2	688.0	682.7	678.0	673.8	669.0
42.5°	670.9	675.5	678.6	679.2	678.6	675.5	670.9	665.6	658.4	653.3	646.6
45°	644.6	649.4	653.6	653.6	653.6	649.4	644.6	635.7	627.9	620.2	613.6
47.5°	617.3	624.2	628.4	629.5	628.4	624.2	617.3	608.2	597.4	587.8	578.4
50°	598.8	607.1	611.3	614.2	611.3	607.1	598.8	588.7	577.4	565.4	554.1
52.5°	580.7	589.0	594.6	596.2	594.6	589.0	580.7	568.2	554.5	541.7	531.8
55°	549.4	561.3	567.8	570.2	567.8	561.3	549.4	535.7	522.6	506.5	492.2
57.5°	519.9	530.8	538.5	540.2	538.5	530.8	519.9	503.8	486.9	469.8	454.5
60°	497.0	508.9	518.4	520.2	518.4	508.9	497.0	481.0	463.0	446.4	427.4
62.5°	473.6	486.0	494.6	499.3	494.6	486.0	473.6	456.7	437.4	418.8	399.8
65°	433.3	445.8	454.2	455.9	454.2	445.8	433.3	416.6	396.4	376.8	360.7
67.5°	389.3	401.7	407.3	410.7	407.3	401.7	389.3	373.6	353.5	333.2	315.0
70°	358.3	368.4	374.4	377.4	374.4	368.4	358.3	341.6	325.0	304.2	284.5
72.5°	323.0	333.6	340.6	341.2	340.6	333.6	323.0	308.8	291.2	271.8	254.5
75°	269.1	278.5	282.1	282.1	282.1	278.5	269.1	255.4	241.1	225.6	208.4
77.5°	212.9	217.8	222.4	223.3	222.4	217.8	212.9	203.1	191.3	175.8	162.8
80°	176.8	179.8	183.3	183.3	183.3	179.8	176.8	167.8	156.5	143.4	133.4
82.5°	139.7	142.2	145.7	145.3	145.7	142.2	139.7	132.6	123.2	114.4	105.2
85°	84.6	89.9	89.3	88.1	89.3	89.9	84.6	85.7	76.8	70.9	62.5
87.5°	41.8	42.3	43.7	44.8	43.7	42.3	41.8	40.3	35.9	33.3	31.3
90°	18.3	18.6	18.9	19.2	18.9	18.6	18.3	18.0	17.5	16.6	15.8
92.5°	17.5	17.6	17.6	17.7	17.6	17.6	17.5	17.4	17.0	16.1	15.2
95°	18.1	18.3	18.4	18.5	18.4	18.3	18.1	18.0	17.5	16.6	15.8
97.5°	17.5	17.7	17.7	17.9	17.7	17.7	17.5	17.3	17.2	17.1	17.0
100°	17.5	17.7	17.7	17.9	17.7	17.7	17.5	17.3	18.4	20.8	23.3
102.5°	18.3	18.3	18.3	18.4	18.3	18.3	18.3	18.3	31.3	57.3	83.4
105°	197.5	192.3	187.3	182.2	187.3	192.3	197.5	202.6	204.5	203.2	202.0
107.5°	252.3	252.8	253.3	253.8	253.3	252.8	252.3	251.7	251.2	250.5	249.9
110°	283.8	284.2	284.6	285.1	284.6	284.2	283.8	283.4	283.0	282.7	282.4



TEST NUMBER: P332811-935

CATALOG NUMBER: S124DIW-S1020D770U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	314.6	315.1	315.7	316.2	315.7	315.1	314.6	314.1	313.8	313.9	313.9
115°	361.7	361.7	361.7	361.7	361.7	361.7	361.7	361.7	361.6	361.3	361.0
117.5°	408.2	408.1	408.0	408.0	408.0	408.1	408.2	408.2	408.3	408.4	408.4
120°	438.0	437.7	437.5	437.1	437.5	437.7	438.0	438.2	438.2	438.0	437.7
122.5°	466.7	466.3	466.1	465.8	466.1	466.3	466.7	466.9	467.0	466.8	466.7
125°	508.3	508.4	508.6	508.8	508.6	508.4	508.3	508.2	507.9	507.5	507.0
127.5°	546.8	546.6	546.6	546.5	546.6	546.6	546.8	546.9	547.0	547.1	547.2
130°	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	571.8	571.6
132.5°	595.9	595.7	595.6	595.6	595.6	595.7	595.9	596.0	596.0	595.8	595.6
135°	629.9	630.3	630.5	630.8	630.5	630.3	629.9	629.6	629.4	629.1	628.8
137.5°	661.2	661.2	661.1	661.0	661.1	661.2	661.2	661.3	661.2	660.9	660.6
140°	681.5	681.7	681.8	681.9	681.8	681.7	681.5	681.4	681.1	680.6	680.2
142.5°	699.2	699.2	699.3	699.3	699.3	699.2	699.2	699.2	699.0	698.7	698.4
145°	725.1	725.5	725.7	726.0	725.7	725.5	725.1	724.9	724.7	724.5	724.4
147.5°	747.7	747.9	748.0	748.1	748.0	747.9	747.7	747.6	747.4	747.3	747.2
150°	762.1	762.2	762.3	762.4	762.3	762.2	762.1	761.9	761.8	761.8	761.8
152.5°	775.0	774.9	774.8	774.7	774.8	774.9	775.0	775.1	775.0	774.7	774.6
155°	792.5	792.0	791.6	791.3	791.6	792.0	792.5	792.9	792.8	792.3	791.7
157.5°	807.3	806.5	805.7	805.0	805.7	806.5	807.3	808.0	808.0	807.3	806.5
160°	816.7	816.0	815.1	814.2	815.1	816.0	816.7	817.6	817.6	816.7	816.0
162.5°	824.3	823.3	822.3	821.4	822.3	823.3	824.3	825.3	825.3	824.4	823.6
165°	835.3	834.1	832.8	831.5	832.8	834.1	835.3	836.6	836.6	835.5	834.4
167.5°	843.3	841.9	840.4	839.0	840.4	841.9	843.3	844.7	844.8	843.5	842.3
170°	847.9	846.4	845.1	843.6	845.1	846.4	847.9	849.3	849.5	848.3	847.1
172.5°	850.8	849.3	847.7	846.2	847.7	849.3	850.8	852.3	852.5	851.4	850.2
175°	854.5	852.8	851.1	849.4	851.1	852.8	854.5	856.2	856.4	855.1	853.9
177.5°	855.5	854.1	852.8	851.4	852.8	854.1	855.5	856.9	857.1	856.2	855.3
180°	854.5	854.5	854.5	854.5	854.5	854.5	854.5	854.5	854.5	854.5	854.5



TEST NUMBER: P332811-935

CATALOG NUMBER: S124DIW-S1020D770U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8
2.5°	1373.6	1375.4	1383.0	1390.2	1398.8	1405.0	1409.2	1414.0	1424.0	1432.1	1439.7
5°	1286.9	1289.9	1305.3	1316.0	1334.5	1350.6	1363.0	1376.7	1392.8	1414.8	1435.0
7.5°	1210.6	1221.6	1238.5	1255.9	1274.7	1295.8	1314.1	1334.7	1362.4	1392.7	1423.8
10°	1167.3	1179.7	1197.6	1217.8	1235.7	1260.1	1282.7	1307.1	1338.6	1375.5	1412.5
12.5°	1123.9	1144.4	1158.0	1182.1	1201.4	1221.5	1245.5	1277.6	1314.3	1353.1	1397.7
15°	1069.6	1080.9	1107.1	1120.2	1147.5	1178.5	1202.3	1234.5	1270.1	1321.4	1371.4
17.5°	1007.0	1021.8	1042.7	1067.7	1099.2	1123.3	1153.0	1186.0	1231.1	1281.9	1344.5
20°	966.0	978.5	1004.1	1031.5	1064.8	1090.5	1122.0	1154.1	1200.6	1254.7	1320.2
22.5°	929.4	941.4	968.5	993.9	1026.2	1057.6	1090.5	1127.9	1172.4	1229.5	1296.4
25°	872.6	888.6	912.5	938.7	969.6	1005.3	1041.0	1074.4	1122.0	1182.1	1253.5
27.5°	822.3	835.1	852.4	882.1	917.2	951.7	987.2	1029.2	1074.9	1138.4	1212.5
30°	789.9	801.8	819.0	846.4	879.2	916.0	953.0	993.4	1041.0	1104.1	1179.7
32.5°	764.1	773.2	788.5	813.0	842.9	881.8	918.2	960.1	1010.0	1072.2	1145.9
35°	726.2	733.9	739.9	763.1	789.9	825.5	862.5	907.1	955.3	1014.3	1088.0
37.5°	688.9	691.6	700.3	715.4	741.4	774.3	808.6	852.5	901.9	961.7	1028.3
40°	666.1	667.3	672.6	686.9	709.5	740.5	773.8	817.3	864.3	920.8	986.9
42.5°	643.7	642.9	647.8	657.8	679.0	707.1	739.9	779.6	826.6	878.9	941.2
45°	608.3	608.3	607.1	615.4	632.7	660.1	687.5	725.6	764.8	816.1	868.4
47.5°	571.4	568.1	569.1	573.4	588.0	610.4	638.1	669.3	703.9	747.3	793.2
50°	547.6	542.9	541.1	545.8	558.9	578.5	604.8	632.1	664.9	702.9	742.3
52.5°	521.4	516.7	513.4	516.8	528.9	547.1	570.9	595.0	624.4	655.3	689.4
55°	481.0	475.6	473.8	475.0	483.9	498.2	518.4	540.4	562.5	588.1	611.9
57.5°	441.1	432.2	430.6	430.0	436.2	449.3	466.1	485.3	501.3	516.8	542.1
60°	414.8	404.2	400.5	400.0	404.8	415.4	430.9	450.0	461.3	472.0	494.0
62.5°	386.8	376.5	368.7	369.5	373.8	384.0	397.6	411.4	418.9	430.6	445.5
65°	343.5	330.4	324.4	322.6	325.0	333.3	344.1	352.9	361.3	366.1	380.3
67.5°	300.1	289.1	280.3	278.2	277.2	282.8	291.6	297.0	303.0	307.1	315.6
70°	269.7	260.1	249.4	245.8	245.2	249.9	258.3	258.9	267.3	269.1	277.9
72.5°	239.6	227.7	220.3	216.8	214.3	218.5	224.0	225.6	230.1	233.3	238.0
75°	192.9	183.9	176.8	171.4	169.6	172.0	172.0	175.0	178.0	179.8	185.1
77.5°	151.8	141.5	133.1	130.0	127.9	126.3	127.6	129.4	127.9	131.0	132.2
80°	123.2	112.5	106.0	104.8	101.2	98.2	97.6	99.4	97.0	98.2	101.8
82.5°	95.1	88.3	81.2	80.0	75.5	74.0	73.4	72.2	72.2	72.0	72.8
85°	56.6	52.3	47.6	44.6	42.9	39.9	39.9	38.7	37.5	36.3	36.9
87.5°	25.8	24.7	22.1	20.5	19.3	17.1	16.9	15.2	14.4	13.5	12.7
90°	14.9	14.0	12.9	11.8	10.7	9.6	8.2	6.6	5.1	3.4	1.9
92.5°	14.4	13.5	12.4	11.3	10.2	9.0	8.4	8.3	8.3	8.2	8.1
95°	14.9	14.0	13.9	13.8	13.6	13.5	15.8	20.7	25.5	30.3	35.1
97.5°	17.0	16.9	32.7	48.6	64.4	80.2	86.7	83.7	80.7	77.7	74.6
100°	25.7	28.2	47.7	67.3	87.0	106.5	115.0	112.4	109.9	107.4	104.8
102.5°	109.4	135.5	138.0	140.6	143.2	145.7	146.0	144.2	142.3	140.4	138.5
105°	200.7	199.4	198.7	197.9	197.3	196.6	195.8	194.9	194.1	193.2	192.3
107.5°	249.3	248.6	247.6	246.7	245.7	244.8	244.1	243.7	243.2	242.8	242.4
110°	282.1	281.8	281.0	280.2	279.3	278.4	277.8	277.4	277.0	276.6	276.1



TEST NUMBER: P332811-935

CATALOG NUMBER: S124DIW-S1020D770U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	314.0	314.1	313.7	313.2	312.9	312.5	311.9	311.1	310.4	309.6	308.8
115°	360.8	360.4	360.6	360.8	360.8	361.0	360.8	360.4	360.1	359.6	359.2
117.5°	408.5	408.5	408.2	407.9	407.6	407.3	406.8	406.2	405.7	405.1	404.6
120°	437.5	437.1	437.3	437.5	437.6	437.7	437.5	437.0	436.4	435.8	435.2
122.5°	466.5	466.3	466.1	465.9	465.7	465.5	465.2	464.9	464.5	464.2	463.9
125°	506.6	506.2	506.4	506.8	507.0	507.3	507.1	506.6	506.0	505.5	504.9
127.5°	547.3	547.3	546.6	546.0	545.4	544.8	544.3	544.2	544.1	543.9	543.7
130°	571.5	571.4	570.9	570.5	570.1	569.6	569.4	569.2	569.1	568.9	568.8
132.5°	595.6	595.4	594.9	594.3	593.7	593.2	592.8	592.5	592.4	592.1	591.9
135°	628.5	628.3	627.7	627.1	626.5	625.9	625.8	625.9	626.0	626.2	626.3
137.5°	660.2	660.0	659.4	658.7	658.1	657.5	657.1	657.0	657.0	656.9	656.9
140°	679.8	679.4	679.1	678.8	678.6	678.2	678.0	677.7	677.3	677.1	676.8
142.5°	698.1	697.8	697.6	697.4	697.2	697.1	696.7	696.2	695.8	695.3	694.7
145°	724.3	724.1	724.1	724.1	724.1	724.1	723.9	723.5	723.1	722.6	722.2
147.5°	747.1	747.0	747.1	747.3	747.4	747.5	747.3	746.4	745.6	744.9	744.1
150°	761.8	761.8	762.0	762.1	762.2	762.4	762.2	761.6	761.0	760.4	759.9
152.5°	774.3	774.1	774.4	774.6	774.8	775.1	775.0	774.6	774.1	773.6	773.2
155°	791.2	790.6	791.0	791.4	791.9	792.3	792.5	792.3	792.1	792.0	791.9
157.5°	805.7	805.0	805.5	806.0	806.5	806.9	807.3	807.4	807.4	807.5	807.6
160°	815.1	814.2	814.3	814.5	814.7	814.8	815.1	815.5	816.0	816.3	816.7
162.5°	822.8	821.9	822.0	822.2	822.3	822.4	822.8	823.4	823.9	824.4	824.9
165°	833.3	832.2	832.2	832.2	832.2	832.2	832.5	833.2	833.9	834.6	835.3
167.5°	841.0	839.8	839.9	840.0	840.1	840.2	840.5	841.3	842.1	842.7	843.5
170°	846.0	844.9	844.7	844.6	844.5	844.3	844.7	845.5	846.4	847.2	848.1
172.5°	849.1	848.0	847.8	847.7	847.6	847.4	847.7	848.6	849.5	850.3	851.2
175°	852.6	851.3	851.2	851.0	850.8	850.8	851.1	852.0	852.8	853.6	854.5
177.5°	854.4	853.4	853.3	853.0	852.8	852.6	852.8	853.6	854.5	855.2	856.0
180°	854.5	854.5	854.5	854.5	854.5	854.5	854.5	854.5	854.5	854.5	854.5



TEST NUMBER: P332811-935

CATALOG NUMBER: S124DIW-S1020D770U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8
2.5°	1446.4	1451.1	1457.3	1467.8	1471.6	1476.4	1483.1	1482.6	1484.5	1491.6	1506.8
5°	1451.7	1470.2	1488.1	1509.5	1532.1	1547.0	1567.2	1579.7	1592.2	1608.3	1635.6
7.5°	1453.9	1483.2	1515.9	1553.5	1587.0	1625.6	1655.6	1683.9	1709.6	1743.5	1776.2
10°	1450.5	1489.8	1532.1	1579.7	1630.3	1673.2	1711.8	1755.9	1793.4	1834.4	1871.4
12.5°	1444.3	1491.8	1548.3	1601.6	1660.8	1724.1	1772.3	1816.8	1866.7	1914.0	1970.9
15°	1430.3	1495.2	1561.3	1631.5	1710.6	1783.8	1853.5	1911.2	1964.8	2035.7	2110.1
17.5°	1412.5	1482.5	1565.7	1650.8	1733.5	1817.2	1903.4	1990.2	2057.8	2145.8	2204.0
20°	1395.8	1476.7	1562.5	1663.6	1746.4	1850.5	1936.2	2020.2	2113.0	2200.5	2270.1
22.5°	1372.4	1461.0	1552.0	1652.7	1761.6	1865.8	1964.8	2055.9	2148.7	2243.9	2328.2
25°	1342.8	1423.1	1530.9	1645.2	1753.5	1866.6	1980.3	2094.6	2194.5	2295.2	2373.7
27.5°	1292.4	1393.8	1494.1	1612.1	1732.4	1860.4	1981.9	2101.6	2206.3	2289.1	2337.8
30°	1266.6	1354.7	1463.6	1582.1	1712.4	1849.9	1976.7	2094.0	2191.6	2257.6	2277.3
32.5°	1228.6	1319.5	1426.0	1548.8	1686.7	1828.0	1960.1	2070.6	2152.1	2186.7	2163.0
35°	1172.0	1254.1	1361.8	1487.5	1630.9	1781.5	1911.9	2005.3	2046.9	2014.2	1932.7
37.5°	1104.1	1185.5	1293.7	1417.1	1565.6	1718.6	1836.5	1903.8	1889.9	1808.5	1687.0
40°	1056.5	1132.7	1235.7	1369.0	1513.6	1667.2	1770.7	1807.1	1769.0	1652.3	1523.2
42.5°	1003.7	1078.0	1181.4	1309.9	1463.2	1604.8	1695.1	1698.1	1634.2	1494.7	1365.0
45°	923.2	994.0	1091.7	1225.5	1367.2	1500.6	1560.0	1530.9	1413.1	1278.5	1148.1
47.5°	843.8	905.2	1001.4	1128.5	1263.1	1375.3	1404.8	1352.3	1226.8	1096.1	975.3
50°	785.7	847.6	938.1	1059.5	1189.2	1286.2	1300.5	1230.9	1107.7	976.1	881.5
52.5°	730.0	791.4	878.6	990.9	1109.7	1197.2	1197.7	1117.1	994.4	877.1	789.1
55°	648.2	703.5	782.1	882.7	988.7	1057.1	1040.4	957.1	850.6	748.8	672.0
57.5°	569.4	617.6	690.0	773.9	867.2	923.7	896.0	815.8	720.7	634.4	576.2
60°	518.4	564.3	626.2	705.3	783.9	827.9	801.8	729.1	641.6	572.0	521.4
62.5°	468.9	507.6	567.1	635.8	708.7	741.3	718.0	646.3	570.7	507.7	466.7
65°	398.8	430.3	477.9	536.9	589.9	617.9	598.2	531.5	473.8	428.5	395.8
67.5°	333.3	358.0	394.0	441.3	486.3	501.4	483.5	437.1	388.2	352.0	328.9
70°	288.1	311.3	341.6	378.0	417.2	433.3	415.4	378.6	338.7	305.3	282.8
72.5°	248.6	266.6	292.1	323.2	354.0	370.0	357.8	322.4	288.7	263.9	244.6
75°	189.2	204.7	222.6	244.6	268.5	279.1	268.5	244.0	220.8	202.3	188.6
77.5°	137.6	145.9	159.7	176.2	191.1	199.2	190.0	173.4	159.3	146.6	139.9
80°	104.8	110.7	120.2	133.4	143.4	151.2	145.3	131.6	120.2	111.9	108.9
82.5°	76.2	80.2	86.4	96.2	103.0	106.9	104.3	94.4	89.7	82.4	79.4
85°	37.5	39.9	44.1	47.0	53.0	53.6	54.2	50.0	45.8	44.1	41.7
87.5°	13.5	14.4	16.1	17.8	20.0	20.7	20.5	20.7	19.0	18.7	17.0
90°	3.4	5.1	6.6	8.2	9.6	10.7	11.8	12.9	14.0	14.9	15.8
92.5°	8.2	8.3	8.3	8.4	9.0	10.2	11.3	12.4	13.5	14.4	15.2
95°	30.3	25.5	20.7	15.8	13.5	13.6	13.8	13.9	14.0	14.9	15.8
97.5°	77.7	80.7	83.7	86.7	80.2	64.4	48.6	32.7	16.9	17.0	17.0
100°	107.4	109.9	112.4	115.0	106.5	87.0	67.3	47.7	28.2	25.7	23.3
102.5°	140.4	142.3	144.2	146.0	145.7	143.2	140.6	138.0	135.5	109.4	83.4
105°	193.2	194.1	194.9	195.8	196.6	197.3	197.9	198.7	199.4	200.7	202.0
107.5°	242.8	243.2	243.7	244.1	244.8	245.7	246.7	247.6	248.6	249.3	249.9
110°	276.6	277.0	277.4	277.8	278.4	279.3	280.2	281.0	281.8	282.1	282.4



TEST NUMBER: P332811-935

CATALOG NUMBER: S124DIW-S1020D770U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	309.6	310.4	311.1	311.9	312.5	312.9	313.2	313.7	314.1	314.0	313.9
115°	359.6	360.1	360.4	360.8	361.0	360.8	360.8	360.6	360.4	360.8	361.0
117.5°	405.1	405.7	406.2	406.8	407.3	407.6	407.9	408.2	408.5	408.5	408.4
120°	435.8	436.4	437.0	437.5	437.7	437.6	437.5	437.3	437.1	437.5	437.7
122.5°	464.2	464.5	464.9	465.2	465.5	465.7	465.9	466.1	466.3	466.5	466.7
125°	505.5	506.0	506.6	507.1	507.3	507.0	506.8	506.4	506.2	506.6	507.0
127.5°	543.9	544.1	544.2	544.3	544.8	545.4	546.0	546.6	547.3	547.3	547.2
130°	568.9	569.1	569.2	569.4	569.6	570.1	570.5	570.9	571.4	571.5	571.6
132.5°	592.1	592.4	592.5	592.8	593.2	593.7	594.3	594.9	595.4	595.6	595.6
135°	626.2	626.0	625.9	625.8	625.9	626.5	627.1	627.7	628.3	628.5	628.8
137.5°	656.9	657.0	657.0	657.1	657.5	658.1	658.7	659.4	660.0	660.2	660.6
140°	677.1	677.3	677.7	678.0	678.2	678.6	678.8	679.1	679.4	679.8	680.2
142.5°	695.3	695.8	696.2	696.7	697.1	697.2	697.4	697.6	697.8	698.1	698.4
145°	722.6	723.1	723.5	723.9	724.1	724.1	724.1	724.1	724.1	724.3	724.4
147.5°	744.9	745.6	746.4	747.3	747.5	747.4	747.3	747.1	747.0	747.1	747.2
150°	760.4	761.0	761.6	762.2	762.4	762.2	762.1	762.0	761.8	761.8	761.8
152.5°	773.6	774.1	774.6	775.0	775.1	774.8	774.6	774.4	774.1	774.3	774.6
155°	792.0	792.1	792.3	792.5	792.3	791.9	791.4	791.0	790.6	791.2	791.7
157.5°	807.5	807.4	807.4	807.3	806.9	806.5	806.0	805.5	805.0	805.7	806.5
160°	816.3	816.0	815.5	815.1	814.8	814.7	814.5	814.3	814.2	815.1	816.0
162.5°	824.4	823.9	823.4	822.8	822.4	822.3	822.2	822.0	821.9	822.8	823.6
165°	834.6	833.9	833.2	832.5	832.2	832.2	832.2	832.2	832.2	833.3	834.4
167.5°	842.7	842.1	841.3	840.5	840.2	840.1	840.0	839.9	839.8	841.0	842.3
170°	847.2	846.4	845.5	844.7	844.3	844.5	844.6	844.7	844.9	846.0	847.1
172.5°	850.3	849.5	848.6	847.7	847.4	847.6	847.7	847.8	848.0	849.1	850.2
175°	853.6	852.8	852.0	851.1	850.8	850.8	851.0	851.2	851.3	852.6	853.9
177.5°	855.2	854.5	853.6	852.8	852.6	852.8	853.0	853.3	853.4	854.4	855.3
180°	854.5	854.5	854.5	854.5	854.5	854.5	854.5	854.5	854.5	854.5	854.5



TEST NUMBER: P332811-935

CATALOG NUMBER: S124DIW-S1020D770U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8
2.5°	1514.5	1515.4	1519.7	1523.0	1524.0	1528.8	1529.2
5°	1647.5	1657.7	1677.3	1679.1	1682.0	1697.5	1685.7
7.5°	1803.5	1829.2	1846.3	1861.5	1867.0	1873.7	1872.3
10°	1903.5	1941.6	1960.7	1991.0	1992.2	1999.9	1995.2
12.5°	2004.0	2048.2	2083.0	2088.6	2114.1	2118.0	2124.7
15°	2146.3	2193.4	2241.6	2258.8	2294.0	2302.3	2315.4
17.5°	2280.2	2328.2	2362.1	2406.7	2421.1	2440.4	2427.2
20°	2353.5	2405.9	2448.7	2483.8	2498.7	2509.4	2508.3
22.5°	2397.8	2450.6	2485.4	2511.9	2525.8	2530.4	2530.1
25°	2425.5	2455.8	2466.6	2476.7	2461.3	2455.8	2458.2
27.5°	2348.4	2340.5	2312.6	2275.9	2237.7	2207.5	2191.1
30°	2242.2	2195.7	2153.4	2079.7	2041.6	2019.0	1998.7
32.5°	2091.7	2018.1	1936.8	1869.2	1825.9	1792.3	1787.3
35°	1833.8	1723.1	1623.8	1541.0	1498.1	1461.8	1453.5
37.5°	1559.1	1444.1	1354.6	1281.8	1235.7	1210.0	1186.1
40°	1376.7	1277.9	1189.8	1127.9	1092.8	1074.4	1059.5
42.5°	1236.2	1146.0	1058.4	1011.2	979.5	968.2	959.5
45°	1042.2	958.3	897.6	861.9	843.4	824.4	815.5
47.5°	886.8	818.6	778.5	748.2	728.4	717.1	711.4
50°	798.7	742.8	707.1	683.9	666.1	657.1	652.4
52.5°	720.7	674.8	644.7	626.3	614.2	607.6	605.7
55°	620.8	585.7	566.6	550.6	541.7	535.7	533.3
57.5°	539.6	512.6	497.1	483.9	480.4	475.4	473.8
60°	486.3	465.5	452.4	443.4	440.5	434.5	435.7
62.5°	439.1	422.1	411.0	405.8	401.9	396.9	398.6
65°	371.4	359.0	352.9	348.2	343.5	340.4	342.9
67.5°	311.7	303.1	295.0	292.2	289.9	289.4	286.9
70°	272.6	265.4	258.3	256.6	256.6	254.2	253.6
72.5°	235.0	229.7	225.0	223.7	221.8	222.7	220.2
75°	181.5	177.4	175.6	173.8	173.2	173.2	171.4
77.5°	134.1	131.0	128.2	128.2	126.1	125.3	125.0
80°	101.8	100.6	98.2	98.2	97.0	97.6	96.4
82.5°	76.5	74.9	74.4	73.4	71.8	71.9	70.7
85°	41.1	39.3	38.7	36.9	35.7	36.9	35.7
87.5°	17.7	17.3	17.0	16.0	15.6	15.7	14.3
90°	16.6	17.5	18.0	18.3	18.6	18.9	19.2
92.5°	16.1	17.0	17.4	17.5	17.6	17.6	17.7
95°	16.6	17.5	18.0	18.1	18.3	18.4	18.5
97.5°	17.1	17.2	17.3	17.5	17.7	17.7	17.9
100°	20.8	18.4	17.3	17.5	17.7	17.7	17.9
102.5°	57.3	31.3	18.3	18.3	18.3	18.3	18.4
105°	203.2	204.5	202.6	197.5	192.3	187.3	182.2
107.5°	250.5	251.2	251.7	252.3	252.8	253.3	253.8
110°	282.7	283.0	283.4	283.8	284.2	284.6	285.1



TEST NUMBER: P332811-935

CATALOG NUMBER: S124DIW-S1020D770U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	313.9	313.8	314.1	314.6	315.1	315.7	316.2
115°	361.3	361.6	361.7	361.7	361.7	361.7	361.7
117.5°	408.4	408.3	408.2	408.2	408.1	408.0	408.0
120°	438.0	438.2	438.2	438.0	437.7	437.5	437.1
122.5°	466.8	467.0	466.9	466.7	466.3	466.1	465.8
125°	507.5	507.9	508.2	508.3	508.4	508.6	508.8
127.5°	547.1	547.0	546.9	546.8	546.6	546.6	546.5
130°	571.8	572.0	572.0	572.0	572.0	572.0	572.0
132.5°	595.8	596.0	596.0	595.9	595.7	595.6	595.6
135°	629.1	629.4	629.6	629.9	630.3	630.5	630.8
137.5°	660.9	661.2	661.3	661.2	661.2	661.1	661.0
140°	680.6	681.1	681.4	681.5	681.7	681.8	681.9
142.5°	698.7	699.0	699.2	699.2	699.2	699.3	699.3
145°	724.5	724.7	724.9	725.1	725.5	725.7	726.0
147.5°	747.3	747.4	747.6	747.7	747.9	748.0	748.1
150°	761.8	761.8	761.9	762.1	762.2	762.3	762.4
152.5°	774.7	775.0	775.1	775.0	774.9	774.8	774.7
155°	792.3	792.8	792.9	792.5	792.0	791.6	791.3
157.5°	807.3	808.0	808.0	807.3	806.5	805.7	805.0
160°	816.7	817.6	817.6	816.7	816.0	815.1	814.2
162.5°	824.4	825.3	825.3	824.3	823.3	822.3	821.4
165°	835.5	836.6	836.6	835.3	834.1	832.8	831.5
167.5°	843.5	844.8	844.7	843.3	841.9	840.4	839.0
170°	848.3	849.5	849.3	847.9	846.4	845.1	843.6
172.5°	851.4	852.5	852.3	850.8	849.3	847.7	846.2
175°	855.1	856.4	856.2	854.5	852.8	851.1	849.4
177.5°	856.2	857.1	856.9	855.5	854.1	852.8	851.4
180°	854.5	854.5	854.5	854.5	854.5	854.5	854.5

(END OF REPORT)