

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332846-830

Luminaire Tested: **S124DIW-S1195D770U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332846-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIW-S1195D770U830-4F0-1E-UDD-F1  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 770 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7332.3 lumens  
Efficiency: N/A  
Efficacy: 122.6 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 59.8  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332846-830

CATALOG NUMBER: S124DIW-S1195D770U830-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332846-830

CATALOG NUMBER: S124DIW-S1195D770U830-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	71	71	71	66
1	101	97	93	89	95	91	88	85	81	78	76	71	69	67	62	61	60	55
2	92	85	78	73	86	80	74	69	71	66	63	63	59	56	55	52	50	46
3	84	74	67	61	79	70	63	58	62	57	53	55	51	48	49	45	43	39
4	77	66	58	51	72	62	55	49	56	50	45	49	45	41	43	40	37	34
5	71	59	50	44	66	56	48	42	50	44	39	44	39	35	39	35	32	29
6	65	53	45	39	61	50	43	37	45	39	34	40	35	31	36	31	28	26
7	60	48	40	34	57	45	38	33	41	35	30	37	31	28	33	28	25	23
8	56	44	36	30	53	41	34	29	37	31	27	33	28	25	30	26	23	20
9	52	40	32	27	49	38	31	26	34	28	24	31	26	22	28	23	20	18
10	49	37	29	24	46	35	28	23	32	26	22	29	24	20	26	22	19	17

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	15163	15163	15163
5°	15209	15027	15135
10°	15114	14905	14978
15°	14931	14692	14730
20°	14689	14430	14442
25°	14412	14130	14091
30°	14072	13778	13651
35°	13720	13409	13232
40°	13354	12991	12752
45°	12973	12578	12337
50°	12552	12210	11833
55°	12096	11736	11354
60°	11641	11202	10863
65°	11127	10695	10264
70°	10551	10017	9626
75°	9669	9201	8968
80°	8605	8257	8047
85°	7521	7243	7104



TEST NUMBER: P332846-830

CATALOG NUMBER: S124DIW-S1195D770U830-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	176.9	2.4
10°-20°	498.4	6.8
20°-30°	733.6	10.0
30°-40°	852.8	11.6
40°-50°	852.8	11.6
50°-60°	746.0	10.2
60°-70°	554.0	7.6
70°-80°	314.7	4.3
80°-90°	93.5	1.3
90°-100°	59.7	0.8
100°-110°	176.7	2.4
110°-120°	300.0	4.1
120°-130°	395.5	5.4
130°-140°	444.2	6.1
140°-150°	436.5	6.0
150°-160°	367.1	5.0
160°-170°	244.3	3.3
170°-180°	85.5	1.2
0°-30°	1408.8	19.2
0°-40°	2261.6	30.8
0°-60°	3860.5	52.7
0°-90°	4822.8	65.8
90°-120°	536.4	7.3
90°-150°	1812.6	24.7
90°-180°	2510.0	34.2
0°-180°	7332.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1878	1878	1878	1878	1878	
5°	1877	1870	1854	1870	1868	178
15°	1786	1780	1758	1766	1762	503
25°	1618	1607	1586	1587	1582	744
35°	1392	1381	1361	1350	1343	870
45°	1136	1125	1102	1086	1081	876
55°	859	854	834	816	807	769
65°	582	575	560	545	537	577
75°	310	302	295	289	288	329
85°	81	81	78	78	77	89
90°	2	10	15	19	21	7
95°	42	48	53	55	55	47
105°	163	164	166	169	171	173
115°	305	305	304	303	302	301
125°	444	444	444	442	441	396
135°	573	577	577	576	574	443
145°	696	699	700	699	697	435
155°	798	797	797	799	797	367
165°	868	866	865	868	866	245
175°	903	900	899	903	899	86
180°	904	904	904	904	904	



TEST NUMBER: P332846-830

CATALOG NUMBER: S124DIW-S1195D770U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1878.3	1878.3	1878.3	1878.3	1878.3	1878.3	1878.3	1878.3	1878.3	1878.3	1878.3
2.5°	1883.1	1882.4	1881.5	1880.7	1879.9	1878.0	1875.1	1872.2	1869.3	1866.3	1869.0
5°	1876.8	1875.5	1874.2	1872.8	1871.5	1869.0	1865.3	1861.6	1857.9	1854.3	1857.9
7.5°	1859.4	1858.0	1856.7	1855.3	1854.0	1851.3	1847.2	1843.1	1839.1	1834.9	1838.0
10°	1843.7	1842.4	1841.1	1839.7	1838.3	1835.5	1831.2	1826.8	1822.5	1818.2	1820.8
12.5°	1823.3	1821.9	1820.5	1819.2	1817.9	1814.9	1810.3	1805.7	1801.1	1796.5	1799.4
15°	1786.5	1785.2	1783.9	1782.5	1781.1	1778.0	1772.9	1767.9	1762.9	1757.9	1759.9
17.5°	1742.3	1740.6	1738.9	1737.3	1735.6	1732.4	1727.6	1722.9	1718.2	1713.4	1714.7
20°	1709.8	1708.1	1706.4	1704.8	1703.1	1699.7	1694.7	1689.7	1684.7	1679.6	1680.6
22.5°	1674.8	1672.6	1670.5	1668.2	1666.0	1662.4	1657.4	1652.4	1647.4	1642.3	1644.2
25°	1618.0	1615.6	1613.3	1610.9	1608.5	1605.1	1600.3	1595.7	1591.0	1586.3	1586.7
27.5°	1552.9	1550.5	1548.1	1545.7	1543.3	1539.9	1535.6	1531.3	1526.9	1522.5	1521.7
30°	1509.6	1506.9	1504.2	1501.6	1498.9	1495.3	1491.0	1486.7	1482.3	1478.0	1476.7
32.5°	1463.9	1461.4	1459.1	1456.6	1454.2	1450.7	1446.0	1441.4	1436.8	1432.2	1430.6
35°	1392.2	1389.9	1387.5	1385.2	1382.8	1379.3	1374.6	1370.0	1365.3	1360.6	1358.2
37.5°	1316.6	1314.5	1312.4	1310.2	1308.1	1304.5	1299.5	1294.5	1289.4	1284.4	1281.9
40°	1267.2	1264.6	1261.9	1259.2	1256.6	1252.7	1247.7	1242.6	1237.7	1232.7	1229.3
42.5°	1214.3	1212.7	1211.1	1209.5	1207.9	1204.3	1198.7	1193.2	1187.6	1182.0	1178.2
45°	1136.3	1134.0	1131.6	1129.3	1127.0	1123.1	1117.8	1112.4	1107.0	1101.7	1098.1
47.5°	1054.7	1053.1	1051.5	1049.9	1048.3	1045.1	1040.1	1035.2	1030.2	1025.3	1021.2
50°	999.4	998.1	996.6	995.3	994.0	991.0	986.3	981.7	976.9	972.2	967.6
52.5°	945.2	943.6	942.0	940.4	938.8	935.5	930.6	925.6	920.7	915.7	911.5
55°	859.4	858.4	857.4	856.4	855.4	852.5	847.8	843.2	838.5	833.8	829.8
57.5°	777.5	776.4	775.2	774.1	773.0	770.1	765.4	760.8	756.2	751.6	747.8
60°	721.0	719.3	717.6	716.0	714.3	711.2	706.9	702.6	698.1	693.8	690.8
62.5°	665.5	664.1	662.7	661.3	660.0	657.0	652.3	647.7	643.1	638.5	635.7
65°	582.5	580.8	579.1	577.4	575.8	573.3	570.0	566.6	563.3	559.9	556.6
67.5°	498.8	497.3	495.7	494.2	492.7	490.2	487.0	483.8	480.6	477.4	474.2
70°	447.0	444.7	442.3	440.0	437.6	435.2	432.4	429.8	427.1	424.4	421.8
72.5°	391.6	389.3	386.9	384.6	382.3	380.0	377.9	375.7	373.6	371.5	369.3
75°	310.0	308.4	306.7	305.0	303.3	301.7	300.0	298.3	296.7	295.0	293.7
77.5°	232.1	231.3	230.6	229.9	229.1	228.0	226.6	225.1	223.7	222.2	221.8
80°	185.1	184.1	183.1	182.1	181.2	180.3	179.6	178.9	178.2	177.6	176.9
82.5°	139.4	138.9	138.5	138.0	137.5	137.2	137.0	137.0	136.8	136.7	136.3
85°	81.2	81.2	81.2	81.2	81.2	81.0	80.3	79.6	78.9	78.2	78.2
87.5°	31.8	31.8	31.9	32.0	32.0	32.0	32.0	32.0	32.0	32.0	32.1
90°	2.1	3.8	5.6	7.3	9.0	10.5	11.7	12.9	14.1	15.4	16.3
92.5°	15.0	17.0	18.9	20.8	22.8	24.2	25.1	25.9	26.9	27.7	28.3
95°	41.9	43.4	44.8	46.2	47.6	48.8	49.9	51.0	52.1	53.2	53.6
97.5°	73.3	74.5	75.6	76.6	77.8	79.0	80.3	81.5	82.8	84.1	84.6
100°	97.9	98.6	99.2	99.8	100.4	101.4	102.8	104.2	105.7	107.1	107.4
102.5°	123.7	123.9	124.1	124.4	124.7	125.5	126.7	128.0	129.2	130.5	131.0
105°	163.0	163.2	163.3	163.4	163.6	164.0	164.7	165.2	165.9	166.5	166.9
107.5°	204.2	204.4	204.6	204.8	205.0	205.2	205.3	205.4	205.5	205.6	205.9
110°	232.2	232.5	232.9	233.2	233.5	233.6	233.4	233.3	233.1	232.9	232.6



TEST NUMBER: P332846-830

CATALOG NUMBER: S124DIW-S1195D770U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	261.4	261.4	261.5	261.6	261.6	261.5	261.2	260.9	260.6	260.3	260.3
115°	305.0	305.0	305.0	305.0	305.0	304.8	304.5	304.3	303.9	303.6	303.4
117.5°	346.1	346.3	346.4	346.5	346.7	346.6	346.4	346.2	345.9	345.7	345.2
120°	373.5	374.2	374.8	375.4	376.1	376.1	375.7	375.2	374.8	374.3	373.4
122.5°	402.1	402.4	402.6	402.8	403.1	403.1	402.9	402.7	402.5	402.3	401.7
125°	444.2	444.2	444.2	444.2	444.2	444.1	443.9	443.8	443.7	443.5	443.2
127.5°	482.4	482.9	483.3	483.8	484.3	484.4	484.1	483.9	483.6	483.4	483.1
130°	509.3	509.7	510.2	510.7	511.1	511.3	511.3	511.3	511.3	511.3	511.0
132.5°	536.7	537.1	537.3	537.7	538.1	538.2	538.0	537.9	537.8	537.6	537.3
135°	573.0	573.8	574.8	575.7	576.6	577.1	577.1	577.1	577.1	577.1	576.8
137.5°	612.4	612.8	613.2	613.7	614.2	614.4	614.7	614.9	615.2	615.5	615.0
140°	638.7	638.9	639.3	639.6	639.9	640.1	640.1	640.1	640.1	640.1	639.9
142.5°	662.7	663.1	663.4	663.6	664.0	664.1	663.9	663.8	663.7	663.5	663.5
145°	696.1	696.6	697.3	698.0	698.5	698.9	699.1	699.3	699.4	699.6	699.4
147.5°	729.1	729.8	730.6	731.3	732.1	732.4	732.3	732.1	732.0	731.9	731.7
150°	749.2	749.8	750.5	751.1	751.7	752.1	752.1	752.1	752.1	752.1	752.1
152.5°	768.3	768.6	769.0	769.4	769.8	770.0	770.1	770.2	770.3	770.4	770.8
155°	797.5	797.5	797.5	797.5	797.5	797.4	797.2	797.1	796.9	796.8	797.4
157.5°	822.1	821.8	821.5	821.2	821.0	820.9	820.8	820.8	820.8	820.7	821.1
160°	836.7	836.5	836.3	836.2	836.0	835.8	835.8	835.6	835.4	835.3	835.8
162.5°	850.1	849.7	849.2	848.9	848.5	848.2	848.0	847.9	847.7	847.5	848.4
165°	868.2	867.7	867.2	866.8	866.3	865.9	865.5	865.3	865.0	864.6	865.5
167.5°	881.9	881.4	880.7	880.1	879.4	879.0	879.1	879.1	879.1	879.2	880.1
170°	889.9	889.0	888.3	887.5	886.7	886.4	886.6	886.7	886.8	887.0	888.0
172.5°	895.4	894.8	894.1	893.4	892.8	892.5	892.5	892.6	892.6	892.6	893.7
175°	903.1	902.3	901.5	900.8	900.0	899.6	899.4	899.2	899.1	898.9	900.0
177.5°	905.6	905.0	904.4	903.8	903.1	902.9	902.9	902.9	902.9	902.9	903.7
180°	904.5	904.5	904.5	904.5	904.5	904.5	904.5	904.5	904.5	904.5	904.5



TEST NUMBER: P332846-830

CATALOG NUMBER: S124DIW-S1195D770U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1878.3	1878.3	1878.3	1878.3	1878.3	1878.3	1878.3	1878.3
2.5°	1871.6	1874.3	1877.0	1878.2	1877.9	1877.6	1877.4	1877.1
5°	1861.6	1865.3	1869.0	1870.5	1869.8	1869.2	1868.5	1867.7
7.5°	1840.9	1843.8	1846.7	1848.0	1847.7	1847.2	1846.8	1846.4
10°	1823.4	1826.2	1828.8	1829.9	1829.2	1828.5	1827.8	1827.1
12.5°	1802.3	1805.3	1808.3	1809.2	1808.3	1807.3	1806.4	1805.4
15°	1761.9	1764.0	1765.9	1766.4	1765.5	1764.4	1763.4	1762.5
17.5°	1715.9	1717.2	1718.4	1718.7	1718.1	1717.4	1716.7	1716.1
20°	1681.7	1682.6	1683.7	1683.9	1683.2	1682.5	1681.9	1681.1
22.5°	1646.0	1647.8	1649.5	1649.8	1648.7	1647.5	1646.2	1645.0
25°	1587.1	1587.3	1587.7	1587.1	1585.8	1584.5	1583.2	1581.9
27.5°	1520.9	1520.1	1519.3	1518.1	1516.4	1514.8	1513.1	1511.4
30°	1475.3	1473.9	1472.6	1471.1	1469.4	1467.8	1466.1	1464.4
32.5°	1429.0	1427.4	1425.8	1424.2	1422.5	1420.8	1419.2	1417.5
35°	1355.9	1353.6	1351.2	1349.2	1347.6	1345.9	1344.2	1342.6
37.5°	1279.3	1276.8	1274.2	1271.9	1269.7	1267.4	1265.3	1263.0
40°	1226.0	1222.6	1219.3	1216.7	1215.1	1213.4	1211.7	1210.0
42.5°	1174.3	1170.4	1166.6	1164.0	1162.9	1161.8	1160.6	1159.5
45°	1094.4	1090.7	1087.0	1084.7	1083.6	1082.6	1081.7	1080.6
47.5°	1017.0	1012.9	1008.7	1005.3	1002.8	1000.2	997.7	995.1
50°	962.9	958.2	953.6	950.2	948.2	946.2	944.1	942.2
52.5°	907.4	903.2	899.1	895.8	893.2	890.7	888.2	885.6
55°	825.8	821.8	817.7	814.7	812.8	810.8	808.7	806.7
57.5°	744.0	740.2	736.4	733.5	731.6	729.6	727.6	725.8
60°	687.8	684.9	681.8	679.5	677.8	676.1	674.5	672.8
62.5°	632.9	630.2	627.5	625.3	623.6	621.9	620.3	618.6
65°	553.2	549.9	546.5	544.0	542.3	540.6	538.9	537.3
67.5°	471.0	467.8	464.6	462.7	462.2	461.8	461.3	460.8
70°	419.1	416.4	413.7	411.9	410.9	409.9	408.9	407.8
72.5°	367.2	365.0	362.9	361.3	360.3	359.3	358.3	357.3
75°	292.3	291.0	289.6	288.8	288.5	288.1	287.8	287.5
77.5°	221.3	220.9	220.6	219.9	219.0	218.2	217.3	216.4
80°	176.3	175.6	174.9	174.5	174.1	173.7	173.4	173.1
82.5°	135.8	135.4	135.1	134.7	134.3	134.0	133.7	133.4
85°	78.2	78.2	78.2	78.1	77.8	77.4	77.1	76.7
87.5°	32.3	32.5	32.7	32.8	32.9	33.0	33.0	33.1
90°	17.2	18.2	19.1	19.7	20.1	20.4	20.6	21.0
92.5°	28.8	29.4	30.0	30.3	30.5	30.7	30.9	31.1
95°	54.1	54.6	55.0	55.2	55.2	55.2	55.2	55.2
97.5°	85.2	85.8	86.3	86.6	86.6	86.6	86.6	86.6
100°	107.6	107.9	108.3	108.4	108.4	108.4	108.4	108.4
102.5°	131.4	131.9	132.2	132.5	132.7	132.8	132.9	133.1
105°	167.4	167.9	168.3	168.8	169.3	169.8	170.2	170.7
107.5°	206.4	206.8	207.3	207.5	207.5	207.5	207.4	207.4
110°	232.3	232.1	231.7	231.8	232.2	232.7	233.2	233.7





TEST NUMBER: P332846-830

CATALOG NUMBER: S124DIW-S1195D770U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	260.2	260.1	260.1	260.1	260.2	260.3	260.4	260.5
115°	303.3	303.1	302.9	302.8	302.7	302.6	302.4	302.2
117.5°	344.7	344.1	343.6	343.2	342.9	342.5	342.2	342.0
120°	372.7	371.9	371.2	370.9	371.3	371.6	371.8	372.1
122.5°	401.1	400.7	400.1	399.5	399.0	398.4	397.9	397.4
125°	442.9	442.6	442.2	442.0	441.7	441.3	441.0	440.7
127.5°	482.8	482.5	482.1	481.8	481.6	481.4	481.1	480.9
130°	510.8	510.4	510.1	509.6	509.1	508.4	507.7	507.2
132.5°	537.1	536.8	536.4	536.1	535.9	535.6	535.4	535.2
135°	576.5	576.2	575.9	575.5	575.0	574.6	574.1	573.6
137.5°	614.6	614.3	613.9	613.7	613.8	613.9	614.0	614.1
140°	639.8	639.6	639.4	639.3	639.1	638.9	638.9	638.7
142.5°	663.5	663.5	663.5	663.5	663.4	663.4	663.4	663.3
145°	699.3	699.1	698.9	698.6	698.1	697.7	697.2	696.7
147.5°	731.6	731.5	731.3	731.2	731.0	730.9	730.8	730.6
150°	752.1	752.1	752.1	752.0	751.8	751.6	751.5	751.3
152.5°	771.2	771.6	771.9	771.9	771.6	771.2	770.7	770.3
155°	798.1	798.6	799.3	799.3	798.6	798.1	797.4	796.8
157.5°	821.6	822.1	822.6	822.6	822.0	821.5	821.0	820.4
160°	836.2	836.7	837.2	837.0	836.2	835.4	834.6	833.9
162.5°	849.2	850.1	850.9	850.9	850.2	849.4	848.7	847.8
165°	866.5	867.4	868.4	868.6	867.9	867.2	866.7	866.0
167.5°	881.1	881.9	882.9	882.9	881.9	881.0	880.1	879.0
170°	888.9	889.9	890.8	890.7	889.6	888.5	887.4	886.4
172.5°	894.8	895.8	896.8	896.8	895.7	894.7	893.5	892.5
175°	901.1	902.2	903.2	903.2	902.2	901.1	900.0	898.9
177.5°	904.6	905.4	906.3	906.3	905.2	904.3	903.2	902.3
180°	904.5	904.5	904.5	904.5	904.5	904.5	904.5	904.5

(END OF REPORT)