

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332851-935

Luminaire Tested: **S124DIW-S1195D1050U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332851-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S1195D1050U935-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1050 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8014.2 lumens
Efficiency: N/A
Efficacy: 118.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 67.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332851-935

CATALOG NUMBER: S124DIW-S1195D1050U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332851-935

CATALOG NUMBER: S124DIW-S1195D1050U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55																				
1	99	94	91	87	92	88	84	81	75	73	71	64	62	61	54	52	51	46																				
2	90	82	76	71	83	77	71	67	66	62	58	56	53	51	47	45	43	39																				
3	82	73	65	59	76	68	61	56	58	53	49	50	46	43	42	39	37	33																				
4	75	64	56	50	69	60	53	47	52	46	42	44	40	37	37	34	32	28																				
5	69	57	49	43	64	53	46	41	46	41	36	40	35	32	34	30	28	24																				
6	64	51	43	37	59	48	41	35	42	36	32	36	31	28	31	27	24	21																				
7	59	46	38	33	54	43	36	31	38	32	28	33	28	25	28	24	22	19																				
8	55	42	34	29	51	40	32	28	35	29	25	30	25	22	26	22	19	17																				
9	51	39	31	26	47	36	29	25	32	26	22	28	23	20	24	20	17	15																				
10	48	35	28	23	44	33	27	22	29	24	20	26	21	18	22	18	16	14																				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13852	13852	13852
5°	13893	13726	13827
10°	13806	13615	13682
15°	13639	13422	13456
20°	13418	13181	13193
25°	13165	12908	12871
30°	12855	12585	12470
35°	12534	12249	12086
40°	12199	11866	11649
45°	11851	11490	11270
50°	11465	11154	10810
55°	11050	10719	10372
60°	10634	10233	9923
65°	10164	9769	9377
70°	9640	9151	8795
75°	8833	8406	8191
80°	7861	7541	7350
85°	6873	6623	6493



TEST NUMBER: P332851-935

CATALOG NUMBER: S124DIW-S1195D1050U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	161.6	2.0
10°-20°	455.3	5.7
20°-30°	670.1	8.4
30°-40°	779.0	9.7
40°-50°	779.1	9.7
50°-60°	681.5	8.5
60°-70°	506.1	6.3
70°-80°	287.5	3.6
80°-90°	86.3	1.1
90°-100°	39.9	0.5
100°-110°	254.3	3.2
110°-120°	486.6	6.1
120°-130°	617.7	7.7
130°-140°	660.8	8.2
140°-150°	618.0	7.7
150°-160°	498.3	6.2
160°-170°	321.4	4.0
170°-180°	110.8	1.4
0°-30°	1287.0	16.1
0°-40°	2066.0	25.8
0°-60°	3526.5	44.0
0°-90°	4406.4	55.0
90°-120°	780.8	9.7
90°-150°	2677.3	33.4
90°-180°	3608.0	45.0
0°-180°	8014.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1716	1716	1716	1716	1716	
5°	1714	1708	1694	1708	1706	163
15°	1632	1626	1606	1613	1610	460
25°	1478	1468	1449	1450	1445	680
35°	1272	1262	1243	1233	1226	795
45°	1038	1028	1006	992	987	800
55°	785	780	762	746	737	703
65°	532	525	511	498	491	527
75°	283	276	270	264	263	301
85°	74	74	72	71	70	82
90°	3	12	19	24	26	6
95°	48	20	19	24	25	62
105°	263	268	272	278	249	275
115°	490	493	492	494	494	482
125°	689	692	691	693	694	615
135°	855	854	858	859	861	658
145°	986	988	988	989	991	616
155°	1081	1082	1079	1082	1080	498
165°	1140	1136	1136	1142	1135	322
175°	1166	1161	1162	1169	1159	111
180°	1166	1166	1166	1166	1166	



TEST NUMBER: P332851-935

CATALOG NUMBER: S124DIW-S1195D1050U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8
2.5°	1720.2	1719.5	1718.7	1718.0	1717.3	1715.5	1712.9	1710.2	1707.5	1704.9	1707.3
5°	1714.4	1713.2	1712.0	1710.8	1709.6	1707.3	1703.9	1700.6	1697.2	1693.8	1697.2
7.5°	1698.5	1697.3	1696.1	1694.8	1693.6	1691.2	1687.4	1683.7	1680.0	1676.2	1679.0
10°	1684.2	1683.0	1681.8	1680.5	1679.3	1676.7	1672.8	1668.8	1664.8	1660.9	1663.3
12.5°	1665.5	1664.3	1663.0	1661.8	1660.6	1657.9	1653.7	1649.5	1645.3	1641.1	1643.7
15°	1631.9	1630.7	1629.5	1628.3	1627.0	1624.2	1619.5	1615.0	1610.4	1605.9	1607.7
17.5°	1591.6	1590.0	1588.5	1587.0	1585.4	1582.5	1578.1	1573.8	1569.5	1565.1	1566.3
20°	1561.9	1560.3	1558.8	1557.3	1555.7	1552.6	1548.1	1543.5	1539.0	1534.3	1535.2
22.5°	1529.9	1527.9	1526.0	1523.9	1521.9	1518.5	1514.0	1509.4	1504.9	1500.2	1501.9
25°	1478.0	1475.8	1473.7	1471.5	1469.4	1466.2	1461.9	1457.7	1453.4	1449.1	1449.4
27.5°	1418.6	1416.3	1414.2	1412.0	1409.8	1406.7	1402.7	1398.8	1394.8	1390.8	1390.1
30°	1379.0	1376.6	1374.1	1371.7	1369.2	1366.0	1362.0	1358.1	1354.1	1350.1	1348.9
32.5°	1337.2	1335.0	1332.8	1330.6	1328.4	1325.2	1320.9	1316.7	1312.5	1308.3	1306.8
35°	1271.8	1269.6	1267.5	1265.3	1263.2	1260.0	1255.7	1251.5	1247.2	1242.9	1240.7
37.5°	1202.7	1200.8	1198.9	1196.9	1194.9	1191.6	1187.1	1182.5	1177.8	1173.3	1171.0
40°	1157.6	1155.2	1152.7	1150.3	1147.9	1144.4	1139.8	1135.1	1130.6	1126.0	1122.9
42.5°	1109.2	1107.8	1106.3	1104.8	1103.4	1100.1	1095.0	1089.9	1084.9	1079.8	1076.2
45°	1038.0	1035.9	1033.7	1031.6	1029.5	1026.0	1021.1	1016.2	1011.2	1006.4	1003.1
47.5°	963.5	962.0	960.5	959.1	957.6	954.7	950.1	945.6	941.1	936.6	932.8
50°	912.9	911.7	910.4	909.2	908.0	905.3	901.0	896.7	892.4	888.1	883.9
52.5°	863.4	861.9	860.5	859.0	857.6	854.5	850.1	845.5	841.0	836.5	832.7
55°	785.1	784.1	783.3	782.3	781.4	778.8	774.5	770.3	765.9	761.6	758.0
57.5°	710.2	709.2	708.2	707.1	706.1	703.4	699.2	695.0	690.8	686.6	683.1
60°	658.6	657.0	655.5	654.0	652.5	649.7	645.8	641.8	637.7	633.8	631.0
62.5°	608.0	606.7	605.4	604.1	602.9	600.1	595.9	591.7	587.5	583.2	580.7
65°	532.1	530.5	529.0	527.4	526.0	523.7	520.6	517.5	514.5	511.4	508.4
67.5°	455.6	454.3	452.8	451.4	450.0	447.8	444.9	442.0	439.0	436.1	433.2
70°	408.4	406.2	404.1	401.9	399.8	397.5	395.0	392.6	390.1	387.7	385.3
72.5°	357.7	355.6	353.4	351.3	349.2	347.2	345.2	343.2	341.3	339.3	337.3
75°	283.2	281.7	280.2	278.6	277.1	275.6	274.1	272.5	271.0	269.5	268.3
77.5°	212.0	211.3	210.7	210.0	209.3	208.3	207.0	205.6	204.3	202.9	202.6
80°	169.1	168.2	167.3	166.3	165.5	164.7	164.1	163.4	162.8	162.2	161.6
82.5°	127.3	126.9	126.5	126.1	125.6	125.4	125.2	125.1	124.9	124.8	124.5
85°	74.2	74.2	74.2	74.2	74.2	74.0	73.4	72.8	72.1	71.5	71.5
87.5°	29.1	29.3	29.4	29.7	29.9	30.0	30.0	30.1	30.1	30.2	30.5
90°	2.6	4.7	6.9	9.0	11.1	13.0	14.6	16.1	17.7	19.2	20.3
92.5°	11.0	11.1	11.2	11.4	11.5	12.3	13.9	15.4	17.0	18.5	19.6
95°	48.0	41.4	34.8	28.2	21.6	18.4	18.6	18.8	19.0	19.2	20.3
97.5°	101.9	106.0	110.1	114.3	118.3	109.6	87.9	66.3	44.7	23.0	23.2
100°	143.1	146.5	150.1	153.5	157.0	145.4	118.6	91.9	65.2	38.4	35.1
102.5°	189.2	191.7	194.2	196.8	199.3	198.9	195.4	191.9	188.4	184.9	149.4
105°	262.6	263.7	264.9	266.0	267.3	268.3	269.2	270.3	271.2	272.2	273.9
107.5°	330.8	331.4	331.9	332.5	333.1	334.1	335.4	336.7	338.0	339.3	340.2
110°	376.9	377.5	378.0	378.6	379.2	380.0	381.3	382.4	383.6	384.7	385.1



TEST NUMBER: P332851-935

CATALOG NUMBER: S124DIW-S1195D1050U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	421.5	422.6	423.6	424.6	425.7	426.5	427.1	427.6	428.1	428.7	428.6
115°	490.3	490.9	491.5	492.0	492.6	492.8	492.6	492.4	492.2	492.0	492.4
117.5°	552.2	552.9	553.7	554.5	555.3	555.9	556.3	556.7	557.2	557.6	557.5
120°	594.1	594.9	595.6	596.4	597.2	597.4	597.3	597.1	596.8	596.7	597.1
122.5°	633.2	633.6	634.0	634.6	635.0	635.4	635.7	635.9	636.2	636.5	636.7
125°	689.1	689.9	690.7	691.5	692.2	692.4	692.1	691.6	691.3	690.9	691.5
127.5°	742.2	742.4	742.6	742.8	743.0	743.5	744.4	745.3	746.1	747.1	747.0
130°	776.4	776.6	776.8	777.0	777.1	777.6	778.2	778.7	779.3	779.9	780.1
132.5°	807.8	808.1	808.5	808.8	809.2	809.8	810.5	811.2	811.9	812.7	812.9
135°	854.9	854.7	854.5	854.3	854.1	854.5	855.2	856.0	856.8	857.6	857.9
137.5°	896.6	896.6	896.7	896.8	896.9	897.3	898.2	899.1	899.9	900.8	901.2
140°	923.9	924.2	924.6	925.0	925.4	925.7	926.2	926.5	927.0	927.3	927.9
142.5°	948.2	948.9	949.6	950.4	951.1	951.5	951.7	951.9	952.2	952.4	952.9
145°	985.8	986.4	986.9	987.5	988.1	988.3	988.3	988.3	988.3	988.3	988.6
147.5°	1015.5	1016.7	1017.8	1018.8	1019.9	1020.4	1020.2	1020.0	1019.8	1019.6	1019.8
150°	1037.2	1038.0	1038.8	1039.6	1040.3	1040.6	1040.4	1040.3	1040.0	1039.8	1039.8
152.5°	1055.3	1056.0	1056.6	1057.2	1057.8	1058.0	1057.7	1057.3	1057.0	1056.6	1056.9
155°	1080.8	1081.1	1081.2	1081.4	1081.6	1081.4	1080.8	1080.3	1079.7	1079.1	1079.9
157.5°	1102.3	1102.2	1102.1	1101.9	1101.8	1101.5	1100.8	1100.1	1099.5	1098.8	1099.8
160°	1114.8	1114.3	1113.7	1113.1	1112.5	1112.2	1112.0	1111.7	1111.6	1111.4	1112.5
162.5°	1126.0	1125.3	1124.6	1123.8	1123.1	1122.6	1122.4	1122.2	1122.1	1121.8	1123.0
165°	1140.1	1139.2	1138.2	1137.2	1136.3	1135.8	1135.8	1135.8	1135.8	1135.8	1137.4
167.5°	1151.3	1150.3	1149.3	1148.3	1147.3	1146.8	1146.6	1146.5	1146.4	1146.2	1148.0
170°	1157.6	1156.4	1155.3	1154.1	1153.0	1152.4	1152.6	1152.9	1153.1	1153.2	1154.8
172.5°	1161.7	1160.6	1159.4	1158.3	1157.1	1156.7	1156.8	1157.0	1157.3	1157.4	1159.0
175°	1166.3	1165.2	1164.0	1162.9	1161.7	1161.2	1161.4	1161.6	1161.7	1162.0	1163.7
177.5°	1168.4	1167.3	1166.2	1165.2	1164.1	1163.7	1164.0	1164.3	1164.6	1164.9	1166.1
180°	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3



TEST NUMBER: P332851-935

CATALOG NUMBER: S124DIW-S1195D1050U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8
2.5°	1709.7	1712.2	1714.6	1715.7	1715.5	1715.2	1714.9	1714.7
5°	1700.6	1703.9	1707.3	1708.7	1708.1	1707.4	1706.8	1706.2
7.5°	1681.6	1684.3	1687.0	1688.2	1687.8	1687.4	1687.0	1686.7
10°	1665.7	1668.2	1670.6	1671.5	1670.9	1670.3	1669.7	1669.0
12.5°	1646.4	1649.1	1651.8	1652.7	1651.8	1651.0	1650.1	1649.2
15°	1609.5	1611.4	1613.2	1613.6	1612.7	1611.8	1610.8	1610.0
17.5°	1567.5	1568.7	1569.8	1570.0	1569.4	1568.8	1568.2	1567.6
20°	1536.2	1537.1	1538.0	1538.2	1537.6	1537.0	1536.4	1535.7
22.5°	1503.6	1505.2	1506.8	1507.1	1506.1	1504.9	1503.8	1502.7
25°	1449.8	1450.0	1450.4	1449.8	1448.6	1447.4	1446.2	1445.0
27.5°	1389.3	1388.6	1387.8	1386.7	1385.2	1383.7	1382.2	1380.6
30°	1347.6	1346.4	1345.2	1343.8	1342.3	1340.8	1339.3	1337.7
32.5°	1305.4	1303.9	1302.4	1301.0	1299.4	1297.9	1296.4	1294.9
35°	1238.6	1236.5	1234.3	1232.5	1231.0	1229.4	1227.9	1226.4
37.5°	1168.6	1166.3	1164.0	1161.8	1159.9	1157.8	1155.8	1153.7
40°	1119.9	1116.8	1113.8	1111.5	1110.0	1108.5	1106.9	1105.4
42.5°	1072.7	1069.2	1065.7	1063.3	1062.3	1061.3	1060.2	1059.2
45°	999.7	996.3	993.0	990.8	989.9	988.9	988.1	987.1
47.5°	929.0	925.2	921.4	918.3	916.0	913.7	911.4	909.0
50°	879.6	875.3	871.1	868.0	866.2	864.4	862.5	860.7
52.5°	828.9	825.1	821.3	818.3	816.0	813.6	811.3	809.0
55°	754.3	750.7	747.0	744.2	742.4	740.6	738.7	736.9
57.5°	679.7	676.1	672.7	670.0	668.3	666.5	664.7	663.0
60°	628.3	625.6	622.8	620.7	619.1	617.6	616.1	614.6
62.5°	578.2	575.7	573.2	571.2	569.6	568.1	566.6	565.1
65°	505.3	502.3	499.2	497.0	495.4	493.9	492.3	490.9
67.5°	430.2	427.3	424.4	422.7	422.2	421.8	421.4	420.9
70°	382.8	380.4	377.9	376.3	375.3	374.4	373.5	372.6
72.5°	335.4	333.5	331.5	330.0	329.2	328.2	327.3	326.4
75°	267.0	265.8	264.6	263.8	263.6	263.2	262.9	262.6
77.5°	202.2	201.8	201.5	200.9	200.1	199.3	198.5	197.7
80°	161.0	160.4	159.8	159.4	159.0	158.7	158.4	158.1
82.5°	124.1	123.7	123.4	123.0	122.7	122.4	122.1	121.8
85°	71.5	71.5	71.5	71.4	71.0	70.7	70.4	70.1
87.5°	30.7	30.9	31.2	31.3	31.4	31.5	31.5	31.6
90°	21.5	22.6	23.8	24.6	25.0	25.4	25.7	26.2
92.5°	20.8	22.0	23.2	23.8	23.8	23.9	24.0	24.1
95°	21.5	22.6	23.8	24.5	24.7	24.9	25.1	25.3
97.5°	23.2	23.4	23.5	23.7	23.8	24.0	24.2	24.5
100°	31.8	28.5	25.2	23.7	23.8	24.0	24.2	24.5
102.5°	113.8	78.3	42.7	25.0	25.0	25.1	25.1	25.1
105°	275.7	277.4	279.1	276.6	269.6	262.6	255.6	248.7
107.5°	341.0	341.9	342.8	343.5	344.3	345.0	345.8	346.5
110°	385.5	385.9	386.2	386.8	387.4	387.9	388.5	389.1



TEST NUMBER: P332851-935

CATALOG NUMBER: S124DIW-S1195D1050U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	428.5	428.4	428.3	428.7	429.5	430.2	430.9	431.6
115°	492.8	493.2	493.5	493.8	493.8	493.8	493.8	493.8
117.5°	557.4	557.4	557.3	557.2	557.2	557.1	557.0	556.9
120°	597.4	597.9	598.2	598.2	597.9	597.4	597.1	596.7
122.5°	637.0	637.1	637.4	637.3	637.0	636.5	636.2	635.8
125°	692.1	692.7	693.2	693.6	693.8	694.0	694.2	694.4
127.5°	746.8	746.7	746.6	746.5	746.3	746.1	746.0	745.9
130°	780.2	780.5	780.7	780.8	780.8	780.8	780.8	780.8
132.5°	813.0	813.3	813.5	813.5	813.3	813.1	813.0	812.9
135°	858.3	858.7	859.1	859.5	859.9	860.2	860.7	861.0
137.5°	901.6	902.1	902.5	902.7	902.5	902.4	902.3	902.2
140°	928.5	929.0	929.6	930.1	930.2	930.4	930.6	930.8
142.5°	953.3	953.7	954.2	954.3	954.4	954.4	954.5	954.5
145°	988.8	988.9	989.1	989.5	989.8	990.2	990.6	991.0
147.5°	1019.9	1020.0	1020.2	1020.4	1020.6	1020.8	1021.0	1021.1
150°	1039.8	1039.8	1039.8	1039.9	1040.1	1040.3	1040.5	1040.7
152.5°	1057.2	1057.5	1057.8	1057.9	1057.8	1057.7	1057.6	1057.5
155°	1080.6	1081.4	1082.2	1082.3	1081.7	1081.2	1080.6	1080.0
157.5°	1100.8	1101.8	1102.9	1102.9	1101.8	1100.8	1099.8	1098.8
160°	1113.7	1114.8	1116.0	1116.0	1114.8	1113.7	1112.5	1111.4
162.5°	1124.1	1125.3	1126.4	1126.4	1125.1	1123.8	1122.5	1121.1
165°	1138.9	1140.5	1142.0	1141.9	1140.1	1138.4	1136.7	1134.9
167.5°	1149.7	1151.4	1153.1	1153.0	1151.1	1149.1	1147.2	1145.2
170°	1156.3	1157.9	1159.4	1159.3	1157.3	1155.4	1153.4	1151.5
172.5°	1160.5	1162.1	1163.6	1163.4	1161.2	1159.2	1157.1	1154.9
175°	1165.4	1167.2	1169.0	1168.6	1166.3	1164.0	1161.7	1159.3
177.5°	1167.4	1168.6	1169.9	1169.6	1167.7	1165.9	1164.0	1162.2
180°	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3

(END OF REPORT)