

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332762-830

Luminaire Tested: **S124DIW-S575D1050U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332762-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S575D1050U830-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1050 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5777.9 lumens
Efficiency: N/A
Efficacy: 127.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 45.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332762-830

CATALOG NUMBER: S124DIW-S575D1050U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332762-830

CATALOG NUMBER: S124DIW-S575D1050U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	48	48	48	41
1	96	91	88	84	87	83	80	77	68	66	64	55	53	52	42	41	40	34
2	87	80	74	69	79	73	68	63	60	56	53	48	45	43	37	35	34	29
3	79	70	63	57	72	64	58	53	53	48	44	42	39	36	33	31	29	24
4	73	62	54	48	66	57	50	45	47	42	38	38	34	31	29	27	25	21
5	67	55	47	41	60	51	44	38	42	37	33	34	30	27	26	24	22	18
6	61	49	41	36	56	45	38	33	38	32	28	31	27	24	24	21	19	16
7	57	45	37	31	51	41	34	29	34	29	25	28	24	21	22	19	17	14
8	52	40	33	27	48	37	30	26	31	26	22	25	21	19	20	17	15	13
9	49	37	29	24	44	34	27	23	28	23	20	23	19	17	18	16	14	11
10	46	34	27	22	42	31	25	20	26	21	18	22	18	15	17	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7389	7389	7389
5°	7412	7323	7376
10°	7365	7263	7299
15°	7276	7160	7178
20°	7158	7032	7039
25°	7023	6886	6866
30°	6858	6715	6652
35°	6686	6535	6447
40°	6509	6330	6215
45°	6322	6130	6012
50°	6116	5951	5766
55°	5895	5719	5533
60°	5672	5459	5293
65°	5421	5213	5001
70°	5141	4881	4692
75°	4713	4482	4370
80°	4193	4021	3924
85°	3668	3538	3464



TEST NUMBER: P332762-830

CATALOG NUMBER: S124DIW-S575D1050U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	86.2	1.5
10°-20°	242.9	4.2
20°-30°	357.5	6.2
30°-40°	415.6	7.2
40°-50°	415.6	7.2
50°-60°	363.5	6.3
60°-70°	270.0	4.7
70°-80°	153.4	2.7
80°-90°	48.0	0.8
90°-100°	81.4	1.4
100°-110°	241.2	4.2
110°-120°	409.4	7.1
120°-130°	539.9	9.3
130°-140°	606.3	10.5
140°-150°	595.8	10.3
150°-160°	501.1	8.7
160°-170°	333.4	5.8
170°-180°	116.7	2.0
0°-30°	686.6	11.9
0°-40°	1102.1	19.1
0°-60°	1881.3	32.6
0°-90°	2352.6	40.7
90°-120°	732.1	12.7
90°-150°	2474.1	42.8
90°-180°	3425.0	59.3
0°-180°	5777.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	915	915	915	915	915	
5°	915	911	904	911	910	87
15°	871	867	857	861	859	245
25°	788	783	773	774	771	363
35°	678	673	663	658	654	424
45°	554	548	537	529	527	427
55°	419	416	406	398	393	375
65°	284	280	273	266	262	281
75°	151	147	144	141	140	161
85°	40	40	38	38	37	44
90°	3	13	21	27	29	6
95°	57	66	73	75	75	64
105°	222	224	227	230	233	236
115°	416	416	414	413	412	410
125°	606	606	605	603	602	540
135°	782	787	788	786	783	605
145°	950	954	955	954	951	594
155°	1088	1088	1088	1091	1088	501
165°	1185	1182	1180	1185	1182	334
175°	1233	1228	1227	1233	1227	117
180°	1235	1235	1235	1235	1235	



TEST NUMBER: P332762-830

CATALOG NUMBER: S124DIW-S575D1050U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	915.3	915.3	915.3	915.3	915.3	915.3	915.3	915.3	915.3	915.3	915.3
2.5°	917.7	917.3	916.9	916.5	916.2	915.2	913.8	912.4	910.9	909.5	910.8
5°	914.6	914.0	913.3	912.7	912.0	910.8	909.0	907.2	905.4	903.6	905.4
7.5°	906.1	905.4	904.8	904.2	903.5	902.2	900.2	898.2	896.2	894.2	895.7
10°	898.4	897.9	897.2	896.5	895.9	894.5	892.4	890.2	888.2	886.0	887.3
12.5°	888.5	887.9	887.2	886.6	885.9	884.5	882.2	880.0	877.7	875.4	876.8
15°	870.6	870.0	869.3	868.6	868.0	866.5	864.0	861.6	859.1	856.7	857.6
17.5°	849.0	848.2	847.4	846.6	845.7	844.2	841.9	839.6	837.3	835.0	835.6
20°	833.2	832.4	831.6	830.8	829.9	828.3	825.9	823.4	821.0	818.5	819.0
22.5°	816.1	815.1	814.1	812.9	811.9	810.1	807.7	805.2	802.8	800.3	801.3
25°	788.4	787.3	786.2	785.0	783.9	782.2	779.9	777.6	775.3	773.1	773.3
27.5°	756.8	755.6	754.4	753.3	752.1	750.5	748.3	746.2	744.0	742.0	741.6
30°	735.7	734.3	733.0	731.7	730.5	728.7	726.6	724.4	722.4	720.3	719.6
32.5°	713.3	712.2	711.0	709.8	708.7	706.9	704.7	702.5	700.2	698.0	697.2
35°	678.4	677.3	676.2	675.0	673.9	672.1	669.9	667.6	665.3	663.1	661.9
37.5°	641.6	640.6	639.5	638.5	637.4	635.7	633.3	630.8	628.4	625.9	624.7
40°	617.6	616.2	614.9	613.7	612.4	610.5	608.0	605.6	603.1	600.7	599.1
42.5°	591.7	591.0	590.2	589.4	588.6	586.8	584.2	581.5	578.7	576.1	574.2
45°	553.7	552.6	551.5	550.4	549.2	547.3	544.7	542.1	539.5	536.9	535.1
47.5°	514.0	513.2	512.5	511.6	510.9	509.3	506.9	504.4	502.0	499.6	497.6
50°	487.0	486.4	485.7	485.0	484.4	483.0	480.7	478.3	476.1	473.8	471.6
52.5°	460.6	459.9	459.0	458.3	457.5	455.9	453.5	451.1	448.7	446.2	444.2
55°	418.8	418.3	417.8	417.4	416.9	415.5	413.2	410.9	408.6	406.3	404.4
57.5°	378.9	378.3	377.8	377.2	376.6	375.3	373.1	370.8	368.5	366.3	364.4
60°	351.3	350.5	349.7	348.8	348.1	346.6	344.5	342.3	340.3	338.1	336.7
62.5°	324.3	323.7	322.9	322.3	321.6	320.1	317.9	315.7	313.4	311.1	309.8
65°	283.8	283.0	282.2	281.4	280.6	279.4	277.8	276.1	274.5	272.9	271.2
67.5°	243.1	242.3	241.6	240.8	240.1	238.9	237.3	235.8	234.2	232.6	231.1
70°	217.8	216.7	215.6	214.4	213.3	212.1	210.8	209.4	208.1	206.8	205.6
72.5°	190.9	189.7	188.6	187.4	186.2	185.2	184.2	183.1	182.1	181.0	179.9
75°	151.1	150.2	149.5	148.6	147.8	147.0	146.2	145.3	144.6	143.7	143.1
77.5°	113.1	112.7	112.4	112.1	111.7	111.1	110.4	109.7	109.0	108.3	108.0
80°	90.2	89.7	89.3	88.8	88.2	87.8	87.6	87.2	86.9	86.5	86.2
82.5°	68.0	67.7	67.5	67.2	67.0	66.8	66.8	66.7	66.6	66.6	66.4
85°	39.6	39.6	39.6	39.6	39.6	39.4	39.1	38.8	38.5	38.2	38.2
87.5°	15.8	16.2	16.5	16.9	17.2	17.4	17.6	17.9	18.1	18.3	18.6
90°	2.8	5.2	7.5	9.9	12.2	14.2	15.9	17.6	19.3	21.0	22.2
92.5°	20.5	23.1	25.8	28.5	31.1	33.1	34.2	35.4	36.7	37.8	38.5
95°	57.3	59.2	61.1	63.1	64.9	66.6	68.1	69.6	71.1	72.6	73.2
97.5°	100.1	101.6	103.1	104.6	106.2	107.8	109.5	111.3	113.0	114.8	115.6
100°	133.7	134.5	135.3	136.2	137.0	138.5	140.3	142.2	144.2	146.1	146.5
102.5°	168.8	169.2	169.5	169.8	170.1	171.2	173.0	174.7	176.4	178.1	178.8
105°	222.4	222.7	222.9	223.1	223.3	223.9	224.7	225.6	226.4	227.2	227.9
107.5°	278.8	279.1	279.3	279.6	279.8	280.0	280.1	280.3	280.4	280.5	281.2
110°	317.0	317.4	317.8	318.3	318.7	318.8	318.8	318.4	318.2	317.9	317.5



TEST NUMBER: P332762-830

CATALOG NUMBER: S124DIW-S575D1050U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	356.8	356.8	356.9	356.9	357.0	356.9	356.6	356.2	355.8	355.4	355.3
115°	416.3	416.3	416.3	416.3	416.3	416.1	415.7	415.3	414.8	414.4	414.2
117.5°	472.5	472.6	472.8	473.0	473.2	473.1	472.8	472.5	472.2	471.8	471.2
120°	509.9	510.8	511.6	512.5	513.3	513.4	512.7	512.1	511.5	510.9	509.8
122.5°	548.8	549.2	549.5	549.9	550.2	550.3	549.9	549.6	549.3	549.0	548.3
125°	606.3	606.3	606.3	606.3	606.3	606.2	606.0	605.8	605.6	605.4	604.9
127.5°	658.5	659.1	659.7	660.3	661.0	661.2	660.8	660.4	660.2	659.8	659.4
130°	695.1	695.8	696.4	697.0	697.7	698.0	698.0	698.0	698.0	698.0	697.6
132.5°	732.5	733.0	733.5	734.0	734.4	734.5	734.4	734.2	734.1	733.9	733.5
135°	782.0	783.3	784.6	785.8	787.1	787.8	787.8	787.8	787.8	787.8	787.3
137.5°	835.8	836.4	837.1	837.6	838.2	838.7	839.1	839.4	839.7	840.1	839.5
140°	871.8	872.2	872.6	873.1	873.5	873.6	873.6	873.6	873.6	873.6	873.5
142.5°	904.7	905.0	905.5	905.9	906.3	906.4	906.3	906.1	906.0	905.8	905.7
145°	950.1	950.9	951.8	952.6	953.5	953.9	954.2	954.4	954.6	954.8	954.6
147.5°	995.1	996.2	997.2	998.2	999.2	999.7	999.5	999.3	999.1	998.9	998.8
150°	1022.7	1023.5	1024.4	1025.2	1026.1	1026.4	1026.4	1026.4	1026.4	1026.4	1026.4
152.5°	1048.6	1049.1	1049.6	1050.1	1050.7	1050.9	1051.1	1051.3	1051.5	1051.7	1052.2
155°	1088.5	1088.5	1088.5	1088.5	1088.5	1088.4	1088.2	1088.0	1087.8	1087.6	1088.4
157.5°	1122.1	1121.7	1121.3	1121.0	1120.6	1120.4	1120.3	1120.3	1120.2	1120.2	1120.9
160°	1142.0	1141.8	1141.5	1141.3	1141.1	1140.9	1140.7	1140.5	1140.3	1140.1	1140.7
162.5°	1160.3	1159.8	1159.2	1158.7	1158.1	1157.7	1157.5	1157.3	1157.1	1156.9	1158.0
165°	1185.0	1184.3	1183.6	1183.1	1182.4	1181.9	1181.5	1181.0	1180.6	1180.2	1181.5
167.5°	1203.8	1203.0	1202.1	1201.2	1200.3	1199.9	1200.0	1200.0	1200.0	1200.0	1201.3
170°	1214.6	1213.5	1212.4	1211.4	1210.3	1209.8	1210.1	1210.3	1210.5	1210.7	1212.0
172.5°	1222.2	1221.3	1220.4	1219.6	1218.6	1218.2	1218.2	1218.3	1218.3	1218.3	1219.8
175°	1232.7	1231.6	1230.6	1229.5	1228.4	1227.9	1227.6	1227.4	1227.2	1227.0	1228.4
177.5°	1236.1	1235.3	1234.4	1233.6	1232.8	1232.3	1232.3	1232.3	1232.3	1232.3	1233.5
180°	1234.6	1234.6	1234.6	1234.6	1234.6	1234.6	1234.6	1234.6	1234.6	1234.6	1234.6



TEST NUMBER: P332762-830

CATALOG NUMBER: S124DIW-S575D1050U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	915.3	915.3	915.3	915.3	915.3	915.3	915.3	915.3
2.5°	912.1	913.4	914.7	915.3	915.1	915.0	914.9	914.7
5°	907.2	909.0	910.8	911.5	911.2	910.9	910.5	910.2
7.5°	897.1	898.5	899.9	900.6	900.4	900.2	900.0	899.8
10°	888.6	889.9	891.3	891.7	891.4	891.1	890.7	890.4
12.5°	878.4	879.8	881.2	881.7	881.2	880.7	880.3	879.9
15°	858.7	859.6	860.5	860.8	860.4	859.9	859.3	858.8
17.5°	836.2	836.8	837.4	837.5	837.3	836.9	836.6	836.3
20°	819.5	820.0	820.5	820.6	820.2	819.9	819.6	819.3
22.5°	802.1	803.0	803.9	804.0	803.4	802.9	802.3	801.6
25°	773.4	773.5	773.7	773.5	772.8	772.1	771.5	770.8
27.5°	741.2	740.7	740.4	739.8	739.0	738.2	737.4	736.5
30°	719.0	718.3	717.7	716.9	716.0	715.3	714.4	713.6
32.5°	696.4	695.6	694.8	694.0	693.2	692.4	691.5	690.8
35°	660.7	659.6	658.5	657.5	656.7	655.8	655.1	654.2
37.5°	623.5	622.2	620.9	619.8	618.8	617.6	616.6	615.5
40°	597.5	595.8	594.2	593.0	592.1	591.4	590.5	589.7
42.5°	572.3	570.3	568.4	567.2	566.8	566.2	565.6	565.1
45°	533.3	531.5	529.7	528.6	528.1	527.6	527.1	526.6
47.5°	495.6	493.5	491.5	489.9	488.7	487.4	486.2	484.9
50°	469.2	466.9	464.7	463.1	462.0	461.1	460.1	459.1
52.5°	442.1	440.2	438.2	436.5	435.3	434.0	432.8	431.6
55°	402.5	400.5	398.5	397.0	396.1	395.1	394.1	393.1
57.5°	362.6	360.7	358.8	357.4	356.5	355.5	354.6	353.6
60°	335.2	333.8	332.2	331.1	330.3	329.5	328.7	327.8
62.5°	308.5	307.1	305.8	304.7	303.9	303.1	302.3	301.4
65°	269.6	268.0	266.4	265.1	264.3	263.4	262.7	261.8
67.5°	229.5	228.0	226.4	225.5	225.3	225.1	224.8	224.6
70°	204.2	202.9	201.6	200.8	200.2	199.7	199.3	198.8
72.5°	178.9	177.9	176.8	176.1	175.6	175.1	174.7	174.1
75°	142.4	141.8	141.2	140.7	140.5	140.4	140.3	140.1
77.5°	107.8	107.6	107.4	107.2	106.7	106.3	105.8	105.5
80°	85.9	85.6	85.2	85.0	84.8	84.6	84.5	84.4
82.5°	66.2	66.0	65.8	65.6	65.5	65.3	65.1	64.9
85°	38.2	38.2	38.2	38.1	37.9	37.7	37.6	37.4
87.5°	18.8	19.0	19.3	19.5	19.5	19.6	19.7	19.8
90°	23.6	24.8	26.1	27.0	27.3	27.8	28.2	28.7
92.5°	39.3	40.1	40.9	41.4	41.7	41.8	42.1	42.4
95°	73.8	74.5	75.1	75.4	75.4	75.4	75.4	75.4
97.5°	116.3	117.1	117.8	118.2	118.2	118.2	118.2	118.2
100°	146.9	147.3	147.8	148.0	148.0	148.0	148.0	148.0
102.5°	179.4	179.9	180.6	181.0	181.1	181.3	181.4	181.6
105°	228.6	229.1	229.8	230.5	231.1	231.7	232.3	233.0
107.5°	281.7	282.3	283.0	283.1	283.1	283.1	283.0	283.0
110°	317.1	316.7	316.2	316.4	317.0	317.6	318.3	319.0



TEST NUMBER: P332762-830

CATALOG NUMBER: S124DIW-S575D1050U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	355.2	355.2	355.1	355.1	355.2	355.3	355.4	355.6
115°	414.0	413.8	413.6	413.3	413.1	412.9	412.7	412.5
117.5°	470.4	469.7	469.0	468.4	468.0	467.6	467.1	466.7
120°	508.7	507.7	506.6	506.2	506.7	507.1	507.6	507.9
122.5°	547.6	546.9	546.1	545.4	544.6	543.8	543.1	542.3
125°	604.5	604.1	603.7	603.2	602.9	602.4	602.0	601.5
127.5°	658.9	658.6	658.1	657.7	657.3	657.0	656.7	656.4
130°	697.1	696.7	696.3	695.7	694.8	694.0	693.1	692.3
132.5°	733.0	732.6	732.2	731.8	731.5	731.1	730.8	730.5
135°	786.9	786.5	786.1	785.5	784.9	784.2	783.6	783.0
137.5°	839.0	838.4	837.8	837.6	837.7	837.9	838.0	838.1
140°	873.3	873.1	872.8	872.6	872.4	872.2	871.9	871.8
142.5°	905.7	905.6	905.6	905.5	905.5	905.5	905.4	905.4
145°	954.4	954.2	953.9	953.6	952.9	952.3	951.7	951.0
147.5°	998.6	998.4	998.2	998.1	997.9	997.7	997.4	997.2
150°	1026.4	1026.4	1026.4	1026.3	1026.1	1026.0	1025.7	1025.5
152.5°	1052.6	1053.2	1053.7	1053.7	1053.1	1052.5	1052.0	1051.5
155°	1089.3	1090.1	1091.0	1091.0	1090.1	1089.3	1088.4	1087.6
157.5°	1121.5	1122.1	1122.8	1122.8	1122.0	1121.2	1120.6	1119.8
160°	1141.3	1142.0	1142.6	1142.4	1141.3	1140.3	1139.3	1138.1
162.5°	1159.1	1160.3	1161.5	1161.5	1160.5	1159.4	1158.3	1157.3
165°	1182.7	1184.0	1185.2	1185.4	1184.6	1183.7	1182.9	1182.0
167.5°	1202.6	1203.8	1205.1	1205.1	1203.8	1202.5	1201.2	1199.9
170°	1213.2	1214.6	1215.8	1215.7	1214.3	1212.8	1211.3	1209.8
172.5°	1221.3	1222.7	1224.2	1224.1	1222.7	1221.2	1219.7	1218.1
175°	1229.9	1231.4	1232.9	1232.9	1231.4	1229.9	1228.4	1227.0
177.5°	1234.7	1235.9	1237.1	1237.0	1235.6	1234.3	1232.9	1231.5
180°	1234.6	1234.6	1234.6	1234.6	1234.6	1234.6	1234.6	1234.6

(END OF REPORT)