

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332750-830

Luminaire Tested: **S124DIW-S575D470U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332750-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S575D470U830-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 470 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3882.7 lumens
Efficiency: N/A
Efficacy: 128.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 30.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332750-830

CATALOG NUMBER: S124DIW-S575D470U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332750-830

CATALOG NUMBER: S124DIW-S575D470U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	89	89	89	77	77	77	66	66	66	61
1	100	96	92	88	93	90	86	83	78	76	73	68	66	64	58	57	55	51
2	91	84	77	72	85	78	73	68	69	64	61	59	56	54	51	49	47	43
3	83	73	66	60	77	69	62	57	60	55	51	53	49	45	45	42	40	36
4	76	65	57	51	71	61	54	48	54	48	44	47	42	39	40	37	34	31
5	70	58	50	44	65	55	47	42	48	42	38	42	37	34	36	33	30	27
6	64	52	44	38	60	49	42	36	43	37	33	38	33	30	33	29	26	24
7	60	47	39	33	56	44	37	32	39	33	29	35	30	26	30	26	23	21
8	55	43	35	30	52	41	33	28	36	30	26	32	27	23	28	24	21	19
9	52	39	32	26	48	37	30	25	33	27	23	29	24	21	26	22	19	17
10	48	36	29	24	45	34	27	23	31	25	21	27	22	19	24	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7389	7389	7389
5°	7412	7323	7376
10°	7365	7263	7299
15°	7276	7160	7178
20°	7158	7032	7039
25°	7023	6886	6866
30°	6858	6715	6652
35°	6686	6535	6447
40°	6509	6330	6215
45°	6322	6130	6012
50°	6116	5951	5766
55°	5895	5719	5533
60°	5672	5459	5293
65°	5421	5213	5001
70°	5141	4881	4692
75°	4713	4482	4370
80°	4193	4021	3924
85°	3668	3538	3464



TEST NUMBER: P332750-830

CATALOG NUMBER: S124DIW-S575D470U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	86.2	2.2
10°-20°	242.9	6.3
20°-30°	357.5	9.2
30°-40°	415.6	10.7
40°-50°	415.6	10.7
50°-60°	363.5	9.4
60°-70°	270.0	7.0
70°-80°	153.4	4.0
80°-90°	45.9	1.2
90°-100°	36.4	0.9
100°-110°	107.9	2.8
110°-120°	183.1	4.7
120°-130°	241.5	6.2
130°-140°	271.2	7.0
140°-150°	266.5	6.9
150°-160°	224.1	5.8
160°-170°	149.1	3.8
170°-180°	52.2	1.3
0°-30°	686.6	17.7
0°-40°	1102.1	28.4
0°-60°	1881.3	48.5
0°-90°	2350.6	60.5
90°-120°	327.5	8.4
90°-150°	1106.7	28.5
90°-180°	1532.0	39.5
0°-180°	3882.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	915	915	915	915	915	
5°	915	911	904	911	910	87
15°	871	867	857	861	859	245
25°	788	783	773	774	771	363
35°	678	673	663	658	654	424
45°	554	548	537	529	527	427
55°	419	416	406	398	393	375
65°	284	280	273	266	262	281
75°	151	147	144	141	140	161
85°	40	40	38	38	37	44
90°	1	6	9	12	13	4
95°	26	29	32	34	34	29
105°	100	100	102	103	104	106
115°	186	186	185	185	184	184
125°	271	271	271	270	269	242
135°	350	352	352	352	350	270
145°	425	427	427	427	425	266
155°	487	487	486	488	486	224
165°	530	529	528	530	529	149
175°	551	549	549	552	549	52
180°	552	552	552	552	552	



TEST NUMBER: P332750-830

CATALOG NUMBER: S124DIW-S575D470U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	915.3	915.3	915.3	915.3	915.3	915.3	915.3	915.3	915.3	915.3	915.3
2.5°	917.7	917.3	916.9	916.5	916.2	915.2	913.8	912.4	910.9	909.5	910.8
5°	914.6	914.0	913.3	912.7	912.0	910.8	909.0	907.2	905.4	903.6	905.4
7.5°	906.1	905.4	904.8	904.2	903.5	902.2	900.2	898.2	896.2	894.2	895.7
10°	898.4	897.9	897.2	896.5	895.9	894.5	892.4	890.2	888.2	886.0	887.3
12.5°	888.5	887.9	887.2	886.6	885.9	884.5	882.2	880.0	877.7	875.4	876.8
15°	870.6	870.0	869.3	868.6	868.0	866.5	864.0	861.6	859.1	856.7	857.6
17.5°	849.0	848.2	847.4	846.6	845.7	844.2	841.9	839.6	837.3	835.0	835.6
20°	833.2	832.4	831.6	830.8	829.9	828.3	825.9	823.4	821.0	818.5	819.0
22.5°	816.1	815.1	814.1	812.9	811.9	810.1	807.7	805.2	802.8	800.3	801.3
25°	788.4	787.3	786.2	785.0	783.9	782.2	779.9	777.6	775.3	773.1	773.3
27.5°	756.8	755.6	754.4	753.3	752.1	750.5	748.3	746.2	744.0	742.0	741.6
30°	735.7	734.3	733.0	731.7	730.5	728.7	726.6	724.4	722.4	720.3	719.6
32.5°	713.3	712.2	711.0	709.8	708.7	706.9	704.7	702.5	700.2	698.0	697.2
35°	678.4	677.3	676.2	675.0	673.9	672.1	669.9	667.6	665.3	663.1	661.9
37.5°	641.6	640.6	639.5	638.5	637.4	635.7	633.3	630.8	628.4	625.9	624.7
40°	617.6	616.2	614.9	613.7	612.4	610.5	608.0	605.6	603.1	600.7	599.1
42.5°	591.7	591.0	590.2	589.4	588.6	586.8	584.2	581.5	578.7	576.1	574.2
45°	553.7	552.6	551.5	550.4	549.2	547.3	544.7	542.1	539.5	536.9	535.1
47.5°	514.0	513.2	512.5	511.6	510.9	509.3	506.9	504.4	502.0	499.6	497.6
50°	487.0	486.4	485.7	485.0	484.4	483.0	480.7	478.3	476.1	473.8	471.6
52.5°	460.6	459.9	459.0	458.3	457.5	455.9	453.5	451.1	448.7	446.2	444.2
55°	418.8	418.3	417.8	417.4	416.9	415.5	413.2	410.9	408.6	406.3	404.4
57.5°	378.9	378.3	377.8	377.2	376.6	375.3	373.1	370.8	368.5	366.3	364.4
60°	351.3	350.5	349.7	348.8	348.1	346.6	344.5	342.3	340.3	338.1	336.7
62.5°	324.3	323.7	322.9	322.3	321.6	320.1	317.9	315.7	313.4	311.1	309.8
65°	283.8	283.0	282.2	281.4	280.6	279.4	277.8	276.1	274.5	272.9	271.2
67.5°	243.1	242.3	241.6	240.8	240.1	238.9	237.3	235.8	234.2	232.6	231.1
70°	217.8	216.7	215.6	214.4	213.3	212.1	210.8	209.4	208.1	206.8	205.6
72.5°	190.9	189.7	188.6	187.4	186.2	185.2	184.2	183.1	182.1	181.0	179.9
75°	151.1	150.2	149.5	148.6	147.8	147.0	146.2	145.3	144.6	143.7	143.1
77.5°	113.1	112.7	112.4	112.1	111.7	111.1	110.4	109.7	109.0	108.3	108.0
80°	90.2	89.7	89.3	88.8	88.2	87.8	87.6	87.2	86.9	86.5	86.2
82.5°	68.0	67.7	67.5	67.2	67.0	66.8	66.8	66.7	66.6	66.6	66.4
85°	39.6	39.6	39.6	39.6	39.6	39.4	39.1	38.8	38.5	38.2	38.2
87.5°	15.6	15.6	15.6	15.7	15.8	15.8	15.9	15.9	15.9	15.9	16.1
90°	1.3	2.4	3.4	4.4	5.5	6.3	7.2	7.9	8.7	9.4	10.0
92.5°	9.1	10.4	11.5	12.7	13.9	14.8	15.4	15.8	16.4	16.9	17.2
95°	25.6	26.5	27.3	28.2	29.0	29.8	30.4	31.1	31.8	32.4	32.7
97.5°	44.8	45.4	46.1	46.8	47.5	48.3	49.0	49.8	50.5	51.4	51.7
100°	59.8	60.1	60.5	60.9	61.4	61.9	62.8	63.6	64.5	65.3	65.5
102.5°	75.5	75.7	75.8	76.0	76.2	76.6	77.4	78.1	78.9	79.7	79.9
105°	99.5	99.6	99.7	99.8	99.9	100.1	100.5	100.9	101.2	101.6	101.9
107.5°	124.7	124.8	125.0	125.1	125.2	125.3	125.4	125.4	125.5	125.5	125.7
110°	141.8	141.9	142.1	142.3	142.5	142.6	142.5	142.4	142.3	142.2	142.0



TEST NUMBER: P332750-830

CATALOG NUMBER: S124DIW-S575D470U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	159.6	159.6	159.7	159.7	159.8	159.7	159.5	159.3	159.1	159.0	158.9
115°	186.2	186.2	186.2	186.2	186.2	186.2	186.0	185.8	185.6	185.4	185.3
117.5°	211.3	211.4	211.5	211.6	211.6	211.6	211.5	211.3	211.2	211.0	210.8
120°	228.1	228.5	228.8	229.2	229.6	229.6	229.3	229.0	228.8	228.5	228.0
122.5°	245.5	245.6	245.8	245.9	246.1	246.1	246.0	245.8	245.7	245.6	245.2
125°	271.2	271.2	271.2	271.2	271.2	271.2	271.1	271.0	270.9	270.8	270.6
127.5°	294.5	294.8	295.1	295.4	295.7	295.8	295.6	295.4	295.3	295.1	294.9
130°	310.9	311.2	311.5	311.8	312.1	312.2	312.2	312.2	312.2	312.2	312.0
132.5°	327.6	327.9	328.1	328.3	328.5	328.6	328.5	328.4	328.4	328.3	328.1
135°	349.8	350.3	350.9	351.5	352.0	352.3	352.3	352.3	352.3	352.3	352.1
137.5°	373.9	374.2	374.4	374.7	374.9	375.1	375.3	375.5	375.6	375.8	375.5
140°	389.9	390.1	390.3	390.5	390.7	390.8	390.8	390.8	390.8	390.8	390.7
142.5°	404.6	404.8	405.0	405.2	405.4	405.5	405.4	405.3	405.2	405.1	405.1
145°	425.0	425.4	425.7	426.1	426.5	426.7	426.8	426.9	427.0	427.1	427.0
147.5°	445.2	445.5	446.0	446.5	447.0	447.1	447.0	447.0	447.0	446.9	446.8
150°	457.4	457.8	458.2	458.5	458.9	459.1	459.1	459.1	459.1	459.1	459.1
152.5°	469.0	469.3	469.5	469.8	470.0	470.1	470.1	470.2	470.3	470.4	470.6
155°	486.9	486.9	486.9	486.9	486.9	486.8	486.7	486.6	486.5	486.4	486.8
157.5°	501.9	501.7	501.6	501.4	501.2	501.1	501.1	501.1	501.1	501.1	501.3
160°	510.9	510.8	510.7	510.6	510.5	510.4	510.3	510.2	510.1	510.0	510.3
162.5°	519.1	518.8	518.5	518.3	518.0	517.8	517.7	517.6	517.6	517.5	518.0
165°	530.0	529.7	529.4	529.1	528.9	528.7	528.5	528.3	528.1	527.9	528.5
167.5°	538.5	538.1	537.7	537.3	536.9	536.7	536.7	536.8	536.8	536.8	537.3
170°	543.3	542.8	542.3	541.9	541.4	541.2	541.3	541.4	541.5	541.6	542.2
172.5°	546.7	546.3	545.9	545.5	545.1	544.9	544.9	545.0	545.0	545.0	545.6
175°	551.4	550.9	550.4	550.0	549.5	549.2	549.1	549.0	548.9	548.8	549.5
177.5°	552.9	552.5	552.1	551.8	551.4	551.2	551.2	551.2	551.2	551.2	551.8
180°	552.2	552.2	552.2	552.2	552.2	552.2	552.2	552.2	552.2	552.2	552.2



TEST NUMBER: P332750-830

CATALOG NUMBER: S124DIW-S575D470U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	915.3	915.3	915.3	915.3	915.3	915.3	915.3	915.3
2.5°	912.1	913.4	914.7	915.3	915.1	915.0	914.9	914.7
5°	907.2	909.0	910.8	911.5	911.2	910.9	910.5	910.2
7.5°	897.1	898.5	899.9	900.6	900.4	900.2	900.0	899.8
10°	888.6	889.9	891.3	891.7	891.4	891.1	890.7	890.4
12.5°	878.4	879.8	881.2	881.7	881.2	880.7	880.3	879.9
15°	858.7	859.6	860.5	860.8	860.4	859.9	859.3	858.8
17.5°	836.2	836.8	837.4	837.5	837.3	836.9	836.6	836.3
20°	819.5	820.0	820.5	820.6	820.2	819.9	819.6	819.3
22.5°	802.1	803.0	803.9	804.0	803.4	802.9	802.3	801.6
25°	773.4	773.5	773.7	773.5	772.8	772.1	771.5	770.8
27.5°	741.2	740.7	740.4	739.8	739.0	738.2	737.4	736.5
30°	719.0	718.3	717.7	716.9	716.0	715.3	714.4	713.6
32.5°	696.4	695.6	694.8	694.0	693.2	692.4	691.5	690.8
35°	660.7	659.6	658.5	657.5	656.7	655.8	655.1	654.2
37.5°	623.5	622.2	620.9	619.8	618.8	617.6	616.6	615.5
40°	597.5	595.8	594.2	593.0	592.1	591.4	590.5	589.7
42.5°	572.3	570.3	568.4	567.2	566.8	566.2	565.6	565.1
45°	533.3	531.5	529.7	528.6	528.1	527.6	527.1	526.6
47.5°	495.6	493.5	491.5	489.9	488.7	487.4	486.2	484.9
50°	469.2	466.9	464.7	463.1	462.0	461.1	460.1	459.1
52.5°	442.1	440.2	438.2	436.5	435.3	434.0	432.8	431.6
55°	402.5	400.5	398.5	397.0	396.1	395.1	394.1	393.1
57.5°	362.6	360.7	358.8	357.4	356.5	355.5	354.6	353.6
60°	335.2	333.8	332.2	331.1	330.3	329.5	328.7	327.8
62.5°	308.5	307.1	305.8	304.7	303.9	303.1	302.3	301.4
65°	269.6	268.0	266.4	265.1	264.3	263.4	262.7	261.8
67.5°	229.5	228.0	226.4	225.5	225.3	225.1	224.8	224.6
70°	204.2	202.9	201.6	200.8	200.2	199.7	199.3	198.8
72.5°	178.9	177.9	176.8	176.1	175.6	175.1	174.7	174.1
75°	142.4	141.8	141.2	140.7	140.5	140.4	140.3	140.1
77.5°	107.8	107.6	107.4	107.2	106.7	106.3	105.8	105.5
80°	85.9	85.6	85.2	85.0	84.8	84.6	84.5	84.4
82.5°	66.2	66.0	65.8	65.6	65.5	65.3	65.1	64.9
85°	38.2	38.2	38.2	38.1	37.9	37.7	37.6	37.4
87.5°	16.2	16.3	16.4	16.5	16.5	16.6	16.6	16.7
90°	10.6	11.1	11.7	12.1	12.3	12.4	12.6	12.8
92.5°	17.6	17.9	18.3	18.5	18.7	18.8	18.9	18.9
95°	33.0	33.3	33.6	33.7	33.7	33.7	33.7	33.7
97.5°	52.0	52.4	52.7	52.9	52.9	52.9	52.9	52.9
100°	65.7	65.9	66.1	66.2	66.2	66.2	66.2	66.2
102.5°	80.2	80.5	80.8	81.0	81.0	81.1	81.2	81.2
105°	102.3	102.5	102.8	103.1	103.4	103.7	104.0	104.2
107.5°	126.0	126.3	126.6	126.7	126.7	126.7	126.6	126.6
110°	141.9	141.7	141.5	141.5	141.8	142.0	142.3	142.6



TEST NUMBER: P332750-830

CATALOG NUMBER: S124DIW-S575D470U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	158.9	158.8	158.8	158.8	158.9	158.9	159.0	159.0
115°	185.2	185.1	185.0	184.9	184.8	184.7	184.6	184.5
117.5°	210.5	210.1	209.8	209.5	209.3	209.2	209.0	208.8
120°	227.5	227.1	226.6	226.5	226.7	226.9	227.1	227.2
122.5°	245.0	244.6	244.3	243.9	243.6	243.3	242.9	242.6
125°	270.4	270.2	270.0	269.8	269.7	269.5	269.3	269.1
127.5°	294.7	294.5	294.4	294.2	294.1	293.9	293.8	293.6
130°	311.8	311.6	311.4	311.1	310.8	310.4	310.0	309.6
132.5°	327.9	327.7	327.5	327.3	327.2	327.1	326.9	326.8
135°	351.9	351.8	351.6	351.4	351.1	350.8	350.5	350.2
137.5°	375.2	375.0	374.8	374.7	374.8	374.8	374.8	374.9
140°	390.6	390.5	390.4	390.3	390.2	390.1	390.0	389.9
142.5°	405.1	405.1	405.1	405.0	405.0	405.0	405.0	405.0
145°	426.9	426.8	426.7	426.5	426.2	425.9	425.7	425.4
147.5°	446.7	446.6	446.6	446.5	446.4	446.3	446.2	446.1
150°	459.1	459.1	459.1	459.1	459.0	458.9	458.8	458.7
152.5°	470.9	471.1	471.4	471.3	471.1	470.8	470.6	470.3
155°	487.2	487.6	488.0	488.0	487.6	487.2	486.8	486.4
157.5°	501.6	501.9	502.2	502.2	501.9	501.5	501.2	500.9
160°	510.6	510.9	511.1	511.0	510.6	510.1	509.5	509.1
162.5°	518.5	519.1	519.5	519.5	519.1	518.6	518.1	517.6
165°	529.0	529.6	530.2	530.3	529.9	529.5	529.1	528.8
167.5°	537.9	538.5	539.0	539.0	538.5	537.9	537.2	536.7
170°	542.7	543.3	543.8	543.8	543.1	542.4	541.8	541.1
172.5°	546.3	547.0	547.5	547.5	546.9	546.2	545.5	544.9
175°	550.2	550.8	551.5	551.5	550.8	550.2	549.5	548.8
177.5°	552.3	552.8	553.4	553.3	552.7	552.1	551.5	550.9
180°	552.2	552.2	552.2	552.2	552.2	552.2	552.2	552.2

(END OF REPORT)