

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332727-935

Luminaire Tested: **S124DIW-S350D1050U935-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332727-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S350D1050U935-4F0-1E-UDD-A
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1050 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4968.4 lumens
Efficiency: N/A
Efficacy: 130.7 lumens/watt
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 38
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332727-935

CATALOG NUMBER: S124DIW-S350D1050U935-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332727-935

CATALOG NUMBER: S124DIW-S350D1050U935-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	102	102	102	102	91	91	91	91	71	71	71	52	52	52	35	35	35	27				
1	93	89	85	82	83	79	76	74	62	60	58	46	45	44	31	31	30	23				
2	85	78	72	67	75	70	65	60	54	51	48	41	38	37	28	27	25	20				
3	77	68	61	56	69	61	55	51	48	44	41	36	33	31	25	23	22	17				
4	71	60	53	47	63	54	48	43	43	38	35	32	29	27	22	20	19	15				
5	65	54	46	40	58	48	42	37	38	33	30	29	26	23	20	18	16	13				
6	60	48	40	35	53	43	37	32	34	29	26	26	23	20	18	16	14	11				
7	55	43	36	30	49	39	32	28	31	26	23	24	20	18	17	14	13	10				
8	51	39	32	27	45	35	29	24	28	23	20	21	18	16	15	13	12	9				
9	47	36	28	24	42	32	26	22	26	21	18	20	16	14	14	12	10	8				
10	44	32	26	21	39	29	23	19	24	19	16	18	15	13	13	11	9	7				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	3971	3971	3971	3971
5°	4676	3981	3514	3981
10°	5599	3963	3163	3963
15°	6624	3924	2906	3924
20°	7377	3882	2674	3882
25°	7496	3822	2515	3822
30°	6378	3765	2466	3765
35°	4904	3671	2466	3671
40°	3822	3561	2512	3561
45°	3186	3394	2555	3394
50°	2804	3191	2641	3191
55°	2570	2949	2747	2949
60°	2407	2730	2876	2730
65°	2243	2487	2982	2487
70°	2049	2245	3050	2245
75°	1831	1978	3013	1978
80°	1534	1623	2920	1623
85°	1130	1176	2788	1176



TEST NUMBER: P332727-935

CATALOG NUMBER: S124DIW-S350D1050U935-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.9	1.0
10°-20°	147.7	3.0
20°-30°	234.2	4.7
30°-40°	260.7	5.2
40°-50°	237.3	4.8
50°-60°	193.9	3.9
60°-70°	138.4	2.8
70°-80°	76.2	1.5
80°-90°	24.2	0.5
90°-100°	39.9	0.8
100°-110°	254.3	5.1
110°-120°	486.6	9.8
120°-130°	617.7	12.4
130°-140°	660.8	13.3
140°-150°	618.0	12.4
150°-160°	498.3	10.0
160°-170°	321.4	6.5
170°-180°	110.8	2.2
0°-30°	429.9	8.7
0°-40°	690.5	13.9
0°-60°	1121.7	22.6
0°-90°	1360.6	27.4
90°-120°	780.8	15.7
90°-150°	2677.3	53.9
90°-180°	3608.0	72.6
0°-180°	4968.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	492	492	492	492	492	
5°	577	491	434	491	577	59
15°	793	470	348	470	793	224
25°	842	429	282	429	842	371
35°	498	372	250	372	498	316
45°	279	297	224	297	279	220
55°	183	210	195	210	183	165
65°	117	130	156	130	117	116
75°	59	63	97	63	59	62
85°	12	13	30	13	12	16
90°	26	3	26	3	26	12
95°	25	48	25	48	25	20
105°	249	263	249	263	249	217
115°	494	490	494	490	494	489
125°	694	689	694	689	694	618
135°	861	855	861	855	861	663
145°	991	986	991	986	991	619
155°	1080	1081	1080	1081	1080	498
165°	1135	1140	1135	1140	1135	321
175°	1159	1166	1159	1166	1159	110
180°	1166	1166	1166	1166	1166	



TEST NUMBER: P332727-935

CATALOG NUMBER: S124DIW-S350D1050U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9
2.5°	523.5	523.4	521.8	521.4	520.3	518.8	518.5	515.8	510.7	508.2	507.6
5°	577.0	581.2	575.8	574.8	574.2	567.5	564.0	560.0	550.6	545.1	540.8
7.5°	641.0	641.4	639.1	637.3	632.1	626.2	617.4	608.0	596.8	585.3	576.5
10°	683.0	684.7	682.0	681.7	671.2	664.7	651.7	640.7	628.0	614.0	601.2
12.5°	727.4	725.1	723.8	715.1	713.1	701.2	686.0	674.8	655.2	639.0	622.0
15°	792.6	788.2	785.3	773.4	767.4	750.9	734.8	722.4	696.9	672.6	654.3
17.5°	831.0	835.4	828.9	823.9	808.7	797.0	780.6	754.5	734.6	704.5	681.3
20°	858.7	859.1	855.4	850.3	838.4	823.6	805.7	777.2	753.4	723.4	691.6
22.5°	866.2	866.3	864.7	860.0	850.8	839.0	820.9	797.0	768.2	735.6	703.8
25°	841.5	840.8	842.6	847.9	844.5	840.8	830.3	812.6	785.7	751.3	717.0
27.5°	750.1	755.8	766.1	779.1	791.7	801.2	803.9	800.3	783.7	755.4	719.5
30°	684.2	691.2	699.0	712.0	737.3	751.7	767.6	779.6	772.9	750.3	716.9
32.5°	611.9	613.6	625.1	639.9	663.1	690.9	716.1	740.5	748.6	736.8	708.9
35°	497.6	500.5	512.9	527.5	555.9	590.0	627.8	661.7	689.6	700.8	686.5
37.5°	406.0	414.2	423.0	438.8	463.7	494.4	533.7	577.6	619.1	647.0	651.8
40°	362.7	367.8	374.1	386.2	407.3	437.5	471.3	521.4	565.7	605.6	618.6
42.5°	328.5	331.5	335.4	346.2	362.3	392.4	423.3	467.4	511.7	559.5	581.3
45°	279.1	282.2	288.8	295.1	307.3	328.0	356.8	393.0	437.7	483.7	524.1
47.5°	243.6	245.5	249.3	256.1	266.6	280.3	303.6	333.9	375.2	420.0	463.0
50°	223.3	225.0	228.0	234.1	242.1	254.3	273.5	301.8	334.2	379.2	421.4
52.5°	207.3	208.0	210.3	214.4	220.8	231.0	246.8	270.2	300.3	340.4	382.5
55°	182.6	183.4	185.5	188.5	194.0	200.5	212.5	230.1	256.3	291.2	327.7
57.5°	162.2	162.8	164.5	165.7	170.2	175.5	184.8	197.3	217.1	246.8	279.3
60°	149.1	148.8	150.8	151.8	154.9	159.4	166.5	178.5	195.8	219.6	249.6
62.5°	136.5	135.9	137.6	139.0	140.7	144.5	150.3	159.7	173.8	195.4	221.3
65°	117.4	116.6	117.6	119.2	120.8	122.9	127.2	135.5	146.7	162.2	181.9
67.5°	98.2	99.1	99.3	100.0	101.0	103.8	106.7	112.6	120.5	132.9	149.6
70°	86.8	87.0	87.8	87.8	88.4	90.9	93.3	96.8	104.5	116.0	129.6
72.5°	75.4	76.3	75.9	76.5	77.1	78.7	80.4	83.8	90.3	98.8	110.4
75°	58.7	59.3	59.3	59.5	60.1	60.7	62.2	64.6	69.3	75.6	83.5
77.5°	42.8	42.9	43.1	43.9	43.9	44.9	45.9	47.9	50.2	54.5	59.4
80°	33.0	33.4	33.2	33.7	33.7	34.4	34.9	37.3	38.3	41.2	45.0
82.5°	24.2	24.6	24.5	25.1	25.5	25.7	26.2	27.2	28.2	30.7	32.3
85°	12.2	12.7	12.2	12.7	13.3	13.4	14.0	14.3	15.1	15.7	17.1
87.5°	8.8	9.2	9.1	9.2	9.5	9.5	9.4	9.0	9.5	9.4	9.7
90°	26.2	25.7	25.4	25.0	24.6	23.8	22.6	21.5	20.3	19.2	17.7
92.5°	24.1	24.0	23.9	23.8	23.8	23.2	22.0	20.8	19.6	18.5	17.0
95°	25.3	25.1	24.9	24.7	24.5	23.8	22.6	21.5	20.3	19.2	19.0
97.5°	24.5	24.2	24.0	23.8	23.7	23.5	23.4	23.2	23.2	23.0	44.7
100°	24.5	24.2	24.0	23.8	23.7	25.2	28.5	31.8	35.1	38.4	65.2
102.5°	25.1	25.1	25.1	25.0	25.0	42.7	78.3	113.8	149.4	184.9	188.4
105°	248.7	255.6	262.6	269.6	276.6	279.1	277.4	275.7	273.9	272.2	271.2
107.5°	346.5	345.8	345.0	344.3	343.5	342.8	341.9	341.0	340.2	339.3	338.0
110°	389.1	388.5	387.9	387.4	386.8	386.2	385.9	385.5	385.1	384.7	383.6



TEST NUMBER: P332727-935

CATALOG NUMBER: S124DIW-S350D1050U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	431.6	430.9	430.2	429.5	428.7	428.3	428.4	428.5	428.6	428.7	428.1
115°	493.8	493.8	493.8	493.8	493.8	493.5	493.2	492.8	492.4	492.0	492.2
117.5°	556.9	557.0	557.1	557.2	557.2	557.3	557.4	557.4	557.5	557.6	557.2
120°	596.7	597.1	597.4	597.9	598.2	598.2	597.9	597.4	597.1	596.7	596.8
122.5°	635.8	636.2	636.5	637.0	637.3	637.4	637.1	637.0	636.7	636.5	636.2
125°	694.4	694.2	694.0	693.8	693.6	693.2	692.7	692.1	691.5	690.9	691.3
127.5°	745.9	746.0	746.1	746.3	746.5	746.6	746.7	746.8	747.0	747.1	746.1
130°	780.8	780.8	780.8	780.8	780.8	780.7	780.5	780.2	780.1	779.9	779.3
132.5°	812.9	813.0	813.1	813.3	813.5	813.5	813.3	813.0	812.9	812.7	811.9
135°	861.0	860.7	860.2	859.9	859.5	859.1	858.7	858.3	857.9	857.6	856.8
137.5°	902.2	902.3	902.4	902.5	902.7	902.5	902.1	901.6	901.2	900.8	899.9
140°	930.8	930.6	930.4	930.2	930.1	929.6	929.0	928.5	927.9	927.3	927.0
142.5°	954.5	954.5	954.4	954.4	954.3	954.2	953.7	953.3	952.9	952.4	952.2
145°	991.0	990.6	990.2	989.8	989.5	989.1	988.9	988.8	988.6	988.3	988.3
147.5°	1021.1	1021.0	1020.8	1020.6	1020.4	1020.2	1020.0	1019.9	1019.8	1019.6	1019.8
150°	1040.7	1040.5	1040.3	1040.1	1039.9	1039.8	1039.8	1039.8	1039.8	1039.8	1040.0
152.5°	1057.5	1057.6	1057.7	1057.8	1057.9	1057.8	1057.5	1057.2	1056.9	1056.6	1057.0
155°	1080.0	1080.6	1081.2	1081.7	1082.3	1082.2	1081.4	1080.6	1079.9	1079.1	1079.7
157.5°	1098.8	1099.8	1100.8	1101.8	1102.9	1102.9	1101.8	1100.8	1099.8	1098.8	1099.5
160°	1111.4	1112.5	1113.7	1114.8	1116.0	1116.0	1114.8	1113.7	1112.5	1111.4	1111.6
162.5°	1121.1	1122.5	1123.8	1125.1	1126.4	1126.4	1125.3	1124.1	1123.0	1121.8	1122.1
165°	1134.9	1136.7	1138.4	1140.1	1141.9	1142.0	1140.5	1138.9	1137.4	1135.8	1135.8
167.5°	1145.2	1147.2	1149.1	1151.1	1153.0	1153.1	1151.4	1149.7	1148.0	1146.2	1146.4
170°	1151.5	1153.4	1155.4	1157.3	1159.3	1159.4	1157.9	1156.3	1154.8	1153.2	1153.1
172.5°	1154.9	1157.1	1159.2	1161.2	1163.4	1163.6	1162.1	1160.5	1159.0	1157.4	1157.3
175°	1159.3	1161.7	1164.0	1166.3	1168.6	1169.0	1167.2	1165.4	1163.7	1162.0	1161.7
177.5°	1162.2	1164.0	1165.9	1167.7	1169.6	1169.9	1168.6	1167.4	1166.1	1164.9	1164.6
180°	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3



TEST NUMBER: P332727-935

CATALOG NUMBER: S124DIW-S350D1050U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9
2.5°	507.7	505.4	503.8	502.5	498.9	496.8	495.2	492.9	490.3	487.5	484.1
5°	536.5	529.6	524.5	516.8	509.5	503.3	497.0	491.3	484.4	476.8	471.3
7.5°	566.8	556.5	543.3	531.8	518.9	507.7	497.7	487.5	476.8	466.4	456.9
10°	586.1	572.8	558.1	540.8	524.5	510.1	496.6	483.5	470.9	458.3	447.5
12.5°	606.7	590.2	568.5	548.3	530.0	510.7	494.5	478.5	463.2	450.0	437.4
15°	634.6	610.7	585.7	558.5	534.5	511.9	489.7	469.5	452.4	434.8	422.6
17.5°	651.6	622.1	593.5	565.2	536.1	507.5	483.5	460.3	438.9	421.5	406.0
20°	662.9	633.5	597.9	569.6	534.9	505.6	477.9	451.9	429.6	411.0	395.1
22.5°	672.6	638.8	603.0	565.8	531.3	500.2	469.8	443.8	420.9	401.4	386.2
25°	678.0	639.0	600.3	563.2	524.1	487.2	459.7	429.1	404.7	384.1	367.8
27.5°	678.6	636.9	593.1	551.9	511.5	477.2	442.5	415.1	389.8	368.0	352.3
30°	676.7	633.4	586.3	541.7	501.1	463.8	433.6	403.9	378.0	356.4	340.1
32.5°	671.0	625.9	577.5	530.2	488.2	451.7	420.6	392.3	367.0	345.8	328.6
35°	654.5	609.8	558.4	509.2	466.2	429.4	401.2	372.5	347.2	327.1	310.6
37.5°	628.7	588.4	536.0	485.2	442.9	405.9	378.0	352.1	329.2	308.8	291.9
40°	606.2	570.8	518.1	468.6	423.0	387.8	361.7	337.9	315.2	295.8	279.7
42.5°	580.3	549.4	500.9	448.5	404.4	369.0	343.6	322.2	300.9	283.0	266.9
45°	534.1	513.7	468.0	419.6	373.7	340.3	316.1	297.3	279.4	261.8	248.4
47.5°	481.0	470.8	432.4	386.3	342.9	309.9	288.9	271.6	255.8	241.0	229.1
50°	445.2	440.3	407.2	362.7	321.2	290.2	269.0	254.1	240.6	227.6	216.4
52.5°	410.0	409.8	379.9	339.2	300.7	271.0	249.9	236.0	224.4	213.8	203.7
55°	356.2	361.9	338.5	302.2	267.8	240.8	221.9	209.5	201.3	192.6	185.0
57.5°	306.8	316.2	296.9	264.9	236.2	211.5	194.9	185.6	176.9	171.6	166.1
60°	274.5	283.4	268.4	241.5	214.4	193.2	177.5	169.1	161.6	157.9	154.0
62.5°	245.8	253.7	242.6	217.7	194.2	173.7	160.5	152.5	147.4	143.4	140.9
65°	204.8	211.5	201.9	183.8	163.6	147.3	136.6	130.2	125.4	123.7	120.8
67.5°	165.6	171.7	166.5	151.1	134.9	122.5	114.1	108.1	105.1	103.8	101.7
70°	142.2	148.4	142.8	129.4	116.9	106.6	98.6	95.1	92.1	91.5	88.7
72.5°	122.5	126.7	121.1	110.6	100.0	91.3	85.1	81.5	79.9	78.8	77.2
75°	91.9	95.6	91.9	83.8	76.2	70.1	64.8	63.4	61.6	61.0	59.9
77.5°	65.0	68.2	65.4	60.4	54.7	49.9	47.1	45.3	44.9	43.8	44.3
80°	49.7	51.7	49.1	45.6	41.2	37.9	35.9	34.9	33.7	33.2	34.0
82.5°	35.7	36.6	35.2	32.9	29.6	27.5	26.1	24.9	24.6	24.7	24.7
85°	18.5	18.3	18.2	16.1	15.1	13.7	12.8	12.7	12.4	12.8	13.3
87.5°	9.4	9.3	8.8	7.7	6.9	5.9	5.3	4.7	5.3	5.9	6.5
90°	16.1	14.6	13.0	11.1	9.0	6.9	4.7	2.6	4.7	6.9	9.0
92.5°	15.4	13.9	12.3	11.5	11.4	11.2	11.1	11.0	11.1	11.2	11.4
95°	18.8	18.6	18.4	21.6	28.2	34.8	41.4	48.0	41.4	34.8	28.2
97.5°	66.3	87.9	109.6	118.3	114.3	110.1	106.0	101.9	106.0	110.1	114.3
100°	91.9	118.6	145.4	157.0	153.5	150.1	146.5	143.1	146.5	150.1	153.5
102.5°	191.9	195.4	198.9	199.3	196.8	194.2	191.7	189.2	191.7	194.2	196.8
105°	270.3	269.2	268.3	267.3	266.0	264.9	263.7	262.6	263.7	264.9	266.0
107.5°	336.7	335.4	334.1	333.1	332.5	331.9	331.4	330.8	331.4	331.9	332.5
110°	382.4	381.3	380.0	379.2	378.6	378.0	377.5	376.9	377.5	378.0	378.6



TEST NUMBER: P332727-935

CATALOG NUMBER: S124DIW-S350D1050U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	427.6	427.1	426.5	425.7	424.6	423.6	422.6	421.5	422.6	423.6	424.6
115°	492.4	492.6	492.8	492.6	492.0	491.5	490.9	490.3	490.9	491.5	492.0
117.5°	556.7	556.3	555.9	555.3	554.5	553.7	552.9	552.2	552.9	553.7	554.5
120°	597.1	597.3	597.4	597.2	596.4	595.6	594.9	594.1	594.9	595.6	596.4
122.5°	635.9	635.7	635.4	635.0	634.6	634.0	633.6	633.2	633.6	634.0	634.6
125°	691.6	692.1	692.4	692.2	691.5	690.7	689.9	689.1	689.9	690.7	691.5
127.5°	745.3	744.4	743.5	743.0	742.8	742.6	742.4	742.2	742.4	742.6	742.8
130°	778.7	778.2	777.6	777.1	777.0	776.8	776.6	776.4	776.6	776.8	777.0
132.5°	811.2	810.5	809.8	809.2	808.8	808.5	808.1	807.8	808.1	808.5	808.8
135°	856.0	855.2	854.5	854.1	854.3	854.5	854.7	854.9	854.7	854.5	854.3
137.5°	899.1	898.2	897.3	896.9	896.8	896.7	896.6	896.6	896.6	896.7	896.8
140°	926.5	926.2	925.7	925.4	925.0	924.6	924.2	923.9	924.2	924.6	925.0
142.5°	951.9	951.7	951.5	951.1	950.4	949.6	948.9	948.2	948.9	949.6	950.4
145°	988.3	988.3	988.3	988.1	987.5	986.9	986.4	985.8	986.4	986.9	987.5
147.5°	1020.0	1020.2	1020.4	1019.9	1018.8	1017.8	1016.7	1015.5	1016.7	1017.8	1018.8
150°	1040.3	1040.4	1040.6	1040.3	1039.6	1038.8	1038.0	1037.2	1038.0	1038.8	1039.6
152.5°	1057.3	1057.7	1058.0	1057.8	1057.2	1056.6	1056.0	1055.3	1056.0	1056.6	1057.2
155°	1080.3	1080.8	1081.4	1081.6	1081.4	1081.2	1081.1	1080.8	1081.1	1081.2	1081.4
157.5°	1100.1	1100.8	1101.5	1101.8	1101.9	1102.1	1102.2	1102.3	1102.2	1102.1	1101.9
160°	1111.7	1112.0	1112.2	1112.5	1113.1	1113.7	1114.3	1114.8	1114.3	1113.7	1113.1
162.5°	1122.2	1122.4	1122.6	1123.1	1123.8	1124.6	1125.3	1126.0	1125.3	1124.6	1123.8
165°	1135.8	1135.8	1135.8	1136.3	1137.2	1138.2	1139.2	1140.1	1139.2	1138.2	1137.2
167.5°	1146.5	1146.6	1146.8	1147.3	1148.3	1149.3	1150.3	1151.3	1150.3	1149.3	1148.3
170°	1152.9	1152.6	1152.4	1153.0	1154.1	1155.3	1156.4	1157.6	1156.4	1155.3	1154.1
172.5°	1157.0	1156.8	1156.7	1157.1	1158.3	1159.4	1160.6	1161.7	1160.6	1159.4	1158.3
175°	1161.6	1161.4	1161.2	1161.7	1162.9	1164.0	1165.2	1166.3	1165.2	1164.0	1162.9
177.5°	1164.3	1164.0	1163.7	1164.1	1165.2	1166.2	1167.3	1168.4	1167.3	1166.2	1165.2
180°	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3



TEST NUMBER: P332727-935

CATALOG NUMBER: S124DIW-S350D1050U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9
2.5°	482.4	481.0	478.9	476.0	473.5	470.9	470.2	469.2	471.2	469.6	469.1
5°	466.7	462.4	456.8	450.6	446.9	441.6	440.6	438.5	436.4	436.3	434.2
7.5°	449.9	443.6	436.4	430.0	424.0	418.2	414.4	413.6	410.6	408.8	406.8
10°	439.1	431.4	423.0	416.9	410.0	403.9	399.6	397.2	395.1	392.9	390.8
12.5°	426.5	418.2	411.3	404.7	396.5	391.8	384.8	380.6	380.1	380.1	374.9
15°	411.6	403.5	392.9	383.5	379.0	370.1	366.2	361.3	358.3	355.2	352.8
17.5°	394.7	384.5	376.3	365.5	357.0	349.8	344.7	341.8	337.2	332.9	329.8
20°	384.1	373.3	364.5	353.1	343.8	335.0	330.7	326.7	323.2	319.5	316.1
22.5°	373.3	362.1	351.4	340.3	331.6	322.3	318.1	312.6	309.4	307.3	303.8
25°	356.4	344.1	331.9	321.3	312.4	304.2	298.8	294.5	290.8	289.1	286.9
27.5°	337.9	325.8	314.0	302.0	291.8	285.9	281.5	278.3	276.1	274.0	272.9
30°	326.2	313.6	301.0	289.7	280.4	274.5	270.4	268.2	266.6	265.5	264.5
32.5°	314.4	301.9	288.6	278.4	269.9	264.7	261.6	259.3	258.6	258.2	257.8
35°	295.2	282.7	270.4	261.2	253.3	251.2	248.6	247.4	246.9	248.4	249.0
37.5°	276.8	265.1	253.8	245.0	239.7	236.8	235.8	235.9	237.4	238.6	240.0
40°	264.9	253.5	242.9	235.1	230.2	228.4	228.0	229.0	230.7	232.1	233.8
42.5°	253.3	242.1	232.5	225.2	221.8	220.1	220.3	221.4	223.7	225.4	227.8
45°	235.4	226.0	216.6	210.7	207.8	208.3	208.3	210.1	212.3	215.0	217.7
47.5°	218.4	209.0	201.3	196.3	194.8	194.5	195.6	198.0	201.2	204.5	208.2
50°	207.1	198.0	191.3	186.8	185.2	185.8	187.4	189.7	193.6	197.7	201.6
52.5°	195.4	187.3	181.1	176.9	175.7	176.8	178.5	182.0	185.5	189.9	194.5
55°	177.5	170.6	165.7	162.6	162.2	162.8	164.6	168.5	173.4	178.9	183.4
57.5°	159.6	153.8	149.3	147.2	147.4	148.0	151.0	155.6	160.8	166.7	172.5
60°	147.5	142.2	138.5	136.9	137.2	138.4	142.1	146.3	152.8	158.5	164.6
62.5°	136.1	131.5	127.9	126.5	126.2	128.9	132.4	136.8	143.4	149.7	156.4
65°	117.8	114.1	111.2	110.5	111.1	113.1	117.6	123.5	129.0	135.7	142.7
67.5°	99.9	96.9	94.9	95.2	96.0	99.0	102.7	107.8	114.1	121.1	127.9
70°	88.4	85.6	83.9	84.1	85.4	89.0	92.3	97.4	104.1	111.2	116.9
72.5°	76.7	74.8	73.4	74.2	75.4	77.9	82.1	87.1	93.1	99.7	105.7
75°	58.9	58.9	58.1	58.7	60.5	62.9	66.0	71.3	77.2	82.6	87.4
77.5°	43.7	43.2	43.7	44.5	45.5	48.5	52.0	55.8	60.2	65.5	69.6
80°	33.4	33.7	34.6	35.9	36.2	38.5	42.2	45.6	49.1	53.6	57.4
82.5°	25.1	25.3	25.8	27.4	27.8	30.2	32.5	36.0	39.2	42.2	45.4
85°	13.7	13.7	14.6	15.3	16.3	17.9	19.4	21.4	24.3	26.3	29.4
87.5°	7.4	7.8	8.8	9.4	10.2	11.4	11.9	13.9	14.8	15.8	17.5
90°	11.1	13.0	14.6	16.1	17.7	19.2	20.3	21.5	22.6	23.8	24.6
92.5°	11.5	12.3	13.9	15.4	17.0	18.5	19.6	20.8	22.0	23.2	23.8
95°	21.6	18.4	18.6	18.8	19.0	19.2	20.3	21.5	22.6	23.8	24.5
97.5°	118.3	109.6	87.9	66.3	44.7	23.0	23.2	23.2	23.4	23.5	23.7
100°	157.0	145.4	118.6	91.9	65.2	38.4	35.1	31.8	28.5	25.2	23.7
102.5°	199.3	198.9	195.4	191.9	188.4	184.9	149.4	113.8	78.3	42.7	25.0
105°	267.3	268.3	269.2	270.3	271.2	272.2	273.9	275.7	277.4	279.1	276.6
107.5°	333.1	334.1	335.4	336.7	338.0	339.3	340.2	341.0	341.9	342.8	343.5
110°	379.2	380.0	381.3	382.4	383.6	384.7	385.1	385.5	385.9	386.2	386.8



TEST NUMBER: P332727-935

CATALOG NUMBER: S124DIW-S350D1050U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	425.7	426.5	427.1	427.6	428.1	428.7	428.6	428.5	428.4	428.3	428.7
115°	492.6	492.8	492.6	492.4	492.2	492.0	492.4	492.8	493.2	493.5	493.8
117.5°	555.3	555.9	556.3	556.7	557.2	557.6	557.5	557.4	557.4	557.3	557.2
120°	597.2	597.4	597.3	597.1	596.8	596.7	597.1	597.4	597.9	598.2	598.2
122.5°	635.0	635.4	635.7	635.9	636.2	636.5	636.7	637.0	637.1	637.4	637.3
125°	692.2	692.4	692.1	691.6	691.3	690.9	691.5	692.1	692.7	693.2	693.6
127.5°	743.0	743.5	744.4	745.3	746.1	747.1	747.0	746.8	746.7	746.6	746.5
130°	777.1	777.6	778.2	778.7	779.3	779.9	780.1	780.2	780.5	780.7	780.8
132.5°	809.2	809.8	810.5	811.2	811.9	812.7	812.9	813.0	813.3	813.5	813.5
135°	854.1	854.5	855.2	856.0	856.8	857.6	857.9	858.3	858.7	859.1	859.5
137.5°	896.9	897.3	898.2	899.1	899.9	900.8	901.2	901.6	902.1	902.5	902.7
140°	925.4	925.7	926.2	926.5	927.0	927.3	927.9	928.5	929.0	929.6	930.1
142.5°	951.1	951.5	951.7	951.9	952.2	952.4	952.9	953.3	953.7	954.2	954.3
145°	988.1	988.3	988.3	988.3	988.3	988.3	988.6	988.8	988.9	989.1	989.5
147.5°	1019.9	1020.4	1020.2	1020.0	1019.8	1019.6	1019.8	1019.9	1020.0	1020.2	1020.4
150°	1040.3	1040.6	1040.4	1040.3	1040.0	1039.8	1039.8	1039.8	1039.8	1039.8	1039.9
152.5°	1057.8	1058.0	1057.7	1057.3	1057.0	1056.6	1056.9	1057.2	1057.5	1057.8	1057.9
155°	1081.6	1081.4	1080.8	1080.3	1079.7	1079.1	1079.9	1080.6	1081.4	1082.2	1082.3
157.5°	1101.8	1101.5	1100.8	1100.1	1099.5	1098.8	1099.8	1100.8	1101.8	1102.9	1102.9
160°	1112.5	1112.2	1112.0	1111.7	1111.6	1111.4	1112.5	1113.7	1114.8	1116.0	1116.0
162.5°	1123.1	1122.6	1122.4	1122.2	1122.1	1121.8	1123.0	1124.1	1125.3	1126.4	1126.4
165°	1136.3	1135.8	1135.8	1135.8	1135.8	1135.8	1137.4	1138.9	1140.5	1142.0	1141.9
167.5°	1147.3	1146.8	1146.6	1146.5	1146.4	1146.2	1148.0	1149.7	1151.4	1153.1	1153.0
170°	1153.0	1152.4	1152.6	1152.9	1153.1	1153.2	1154.8	1156.3	1157.9	1159.4	1159.3
172.5°	1157.1	1156.7	1156.8	1157.0	1157.3	1157.4	1159.0	1160.5	1162.1	1163.6	1163.4
175°	1161.7	1161.2	1161.4	1161.6	1161.7	1162.0	1163.7	1165.4	1167.2	1169.0	1168.6
177.5°	1164.1	1163.7	1164.0	1164.3	1164.6	1164.9	1166.1	1167.4	1168.6	1169.9	1169.6
180°	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3



TEST NUMBER: P332727-935

CATALOG NUMBER: S124DIW-S350D1050U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9
2.5°	468.7	468.5	467.3	467.1	467.3	468.5	468.7	469.1	469.6	471.2	469.2
5°	433.0	432.0	431.4	433.6	431.4	432.0	433.0	434.2	436.3	436.4	438.5
7.5°	406.0	405.3	403.5	402.9	403.5	405.3	406.0	406.8	408.8	410.6	413.6
10°	388.8	388.0	386.3	385.9	386.3	388.0	388.8	390.8	392.9	395.1	397.2
12.5°	372.1	370.6	370.2	370.7	370.2	370.6	372.1	374.9	380.1	380.1	380.6
15°	350.1	349.2	347.0	347.7	347.0	349.2	350.1	352.8	355.2	358.3	361.3
17.5°	328.3	327.4	324.6	327.0	324.6	327.4	328.3	329.8	332.9	337.2	341.8
20°	314.6	313.0	311.6	311.3	311.6	313.0	314.6	316.1	319.5	323.2	326.7
22.5°	301.6	300.1	300.0	298.7	300.0	300.1	301.6	303.8	307.3	309.4	312.6
25°	285.2	283.9	283.4	282.4	283.4	283.9	285.2	286.9	289.1	290.8	294.5
27.5°	272.8	272.1	271.3	271.6	271.3	272.1	272.8	272.9	274.0	276.1	278.3
30°	265.1	264.9	264.5	264.5	264.5	264.9	265.1	264.5	265.5	266.6	268.2
32.5°	258.7	258.7	259.0	259.0	259.0	258.7	258.7	257.8	258.2	258.6	259.3
35°	249.9	250.5	250.8	250.2	250.8	250.5	249.9	249.0	248.4	246.9	247.4
37.5°	241.8	242.4	243.0	243.7	243.0	242.4	241.8	240.0	238.6	237.4	235.9
40°	235.6	236.9	237.4	238.4	237.4	236.9	235.6	233.8	232.1	230.7	229.0
42.5°	229.7	231.3	232.3	232.6	232.3	231.3	229.7	227.8	225.4	223.7	221.4
45°	220.7	222.3	223.8	223.8	223.8	222.3	220.7	217.7	215.0	212.3	210.1
47.5°	211.4	213.7	215.2	215.5	215.2	213.7	211.4	208.2	204.5	201.2	198.0
50°	205.0	207.8	209.3	210.3	209.3	207.8	205.0	201.6	197.7	193.6	189.7
52.5°	198.8	201.6	203.5	204.1	203.5	201.6	198.8	194.5	189.9	185.5	182.0
55°	188.0	192.2	194.4	195.2	194.4	192.2	188.0	183.4	178.9	173.4	168.5
57.5°	178.0	181.8	184.3	184.9	184.3	181.8	178.0	172.5	166.7	160.8	155.6
60°	170.1	174.3	177.5	178.1	177.5	174.3	170.1	164.6	158.5	152.8	146.3
62.5°	162.1	166.4	169.4	170.9	169.4	166.4	162.1	156.4	149.7	143.4	136.8
65°	148.4	152.7	155.5	156.1	155.5	152.7	148.4	142.7	135.7	129.0	123.5
67.5°	133.3	137.6	139.4	140.6	139.4	137.6	133.3	127.9	121.1	114.1	107.8
70°	122.7	126.1	128.2	129.2	128.2	126.1	122.7	116.9	111.2	104.1	97.4
72.5°	110.6	114.3	116.6	116.8	116.6	114.3	110.6	105.7	99.7	93.1	87.1
75°	92.1	95.4	96.6	96.6	96.6	95.4	92.1	87.4	82.6	77.2	71.3
77.5°	72.9	74.6	76.1	76.5	76.1	74.6	72.9	69.6	65.5	60.2	55.8
80°	60.5	61.6	62.8	62.8	62.8	61.6	60.5	57.4	53.6	49.1	45.6
82.5°	47.8	48.6	49.9	49.7	49.9	48.6	47.8	45.4	42.2	39.2	36.0
85°	28.9	30.7	30.6	30.1	30.6	30.7	28.9	29.4	26.3	24.3	21.4
87.5°	18.1	18.3	18.9	19.3	18.9	18.3	18.1	17.5	15.8	14.8	13.9
90°	25.0	25.4	25.7	26.2	25.7	25.4	25.0	24.6	23.8	22.6	21.5
92.5°	23.8	23.9	24.0	24.1	24.0	23.9	23.8	23.8	23.2	22.0	20.8
95°	24.7	24.9	25.1	25.3	25.1	24.9	24.7	24.5	23.8	22.6	21.5
97.5°	23.8	24.0	24.2	24.5	24.2	24.0	23.8	23.7	23.5	23.4	23.2
100°	23.8	24.0	24.2	24.5	24.2	24.0	23.8	23.7	25.2	28.5	31.8
102.5°	25.0	25.1	25.1	25.1	25.1	25.1	25.0	25.0	42.7	78.3	113.8
105°	269.6	262.6	255.6	248.7	255.6	262.6	269.6	276.6	279.1	277.4	275.7
107.5°	344.3	345.0	345.8	346.5	345.8	345.0	344.3	343.5	342.8	341.9	341.0
110°	387.4	387.9	388.5	389.1	388.5	387.9	387.4	386.8	386.2	385.9	385.5



TEST NUMBER: P332727-935

CATALOG NUMBER: S124DIW-S350D1050U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	429.5	430.2	430.9	431.6	430.9	430.2	429.5	428.7	428.3	428.4	428.5
115°	493.8	493.8	493.8	493.8	493.8	493.8	493.8	493.8	493.5	493.2	492.8
117.5°	557.2	557.1	557.0	556.9	557.0	557.1	557.2	557.2	557.3	557.4	557.4
120°	597.9	597.4	597.1	596.7	597.1	597.4	597.9	598.2	598.2	597.9	597.4
122.5°	637.0	636.5	636.2	635.8	636.2	636.5	637.0	637.3	637.4	637.1	637.0
125°	693.8	694.0	694.2	694.4	694.2	694.0	693.8	693.6	693.2	692.7	692.1
127.5°	746.3	746.1	746.0	745.9	746.0	746.1	746.3	746.5	746.6	746.7	746.8
130°	780.8	780.8	780.8	780.8	780.8	780.8	780.8	780.8	780.7	780.5	780.2
132.5°	813.3	813.1	813.0	812.9	813.0	813.1	813.3	813.5	813.5	813.3	813.0
135°	859.9	860.2	860.7	861.0	860.7	860.2	859.9	859.5	859.1	858.7	858.3
137.5°	902.5	902.4	902.3	902.2	902.3	902.4	902.5	902.7	902.5	902.1	901.6
140°	930.2	930.4	930.6	930.8	930.6	930.4	930.2	930.1	929.6	929.0	928.5
142.5°	954.4	954.4	954.5	954.5	954.5	954.4	954.4	954.3	954.2	953.7	953.3
145°	989.8	990.2	990.6	991.0	990.6	990.2	989.8	989.5	989.1	988.9	988.8
147.5°	1020.6	1020.8	1021.0	1021.1	1021.0	1020.8	1020.6	1020.4	1020.2	1020.0	1019.9
150°	1040.1	1040.3	1040.5	1040.7	1040.5	1040.3	1040.1	1039.9	1039.8	1039.8	1039.8
152.5°	1057.8	1057.7	1057.6	1057.5	1057.6	1057.7	1057.8	1057.9	1057.8	1057.5	1057.2
155°	1081.7	1081.2	1080.6	1080.0	1080.6	1081.2	1081.7	1082.3	1082.2	1081.4	1080.6
157.5°	1101.8	1100.8	1099.8	1098.8	1099.8	1100.8	1101.8	1102.9	1102.9	1101.8	1100.8
160°	1114.8	1113.7	1112.5	1111.4	1112.5	1113.7	1114.8	1116.0	1116.0	1114.8	1113.7
162.5°	1125.1	1123.8	1122.5	1121.1	1122.5	1123.8	1125.1	1126.4	1126.4	1125.3	1124.1
165°	1140.1	1138.4	1136.7	1134.9	1136.7	1138.4	1140.1	1141.9	1142.0	1140.5	1138.9
167.5°	1151.1	1149.1	1147.2	1145.2	1147.2	1149.1	1151.1	1153.0	1153.1	1151.4	1149.7
170°	1157.3	1155.4	1153.4	1151.5	1153.4	1155.4	1157.3	1159.3	1159.4	1157.9	1156.3
172.5°	1161.2	1159.2	1157.1	1154.9	1157.1	1159.2	1161.2	1163.4	1163.6	1162.1	1160.5
175°	1166.3	1164.0	1161.7	1159.3	1161.7	1164.0	1166.3	1168.6	1169.0	1167.2	1165.4
177.5°	1167.7	1165.9	1164.0	1162.2	1164.0	1165.9	1167.7	1169.6	1169.9	1168.6	1167.4
180°	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3



TEST NUMBER: P332727-935

CATALOG NUMBER: S124DIW-S350D1050U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9
2.5°	470.2	470.9	473.5	476.0	478.9	481.0	482.4	484.1	487.5	490.3	492.9
5°	440.6	441.6	446.9	450.6	456.8	462.4	466.7	471.3	476.8	484.4	491.3
7.5°	414.4	418.2	424.0	430.0	436.4	443.6	449.9	456.9	466.4	476.8	487.5
10°	399.6	403.9	410.0	416.9	423.0	431.4	439.1	447.5	458.3	470.9	483.5
12.5°	384.8	391.8	396.5	404.7	411.3	418.2	426.5	437.4	450.0	463.2	478.5
15°	366.2	370.1	379.0	383.5	392.9	403.5	411.6	422.6	434.8	452.4	469.5
17.5°	344.7	349.8	357.0	365.5	376.3	384.5	394.7	406.0	421.5	438.9	460.3
20°	330.7	335.0	343.8	353.1	364.5	373.3	384.1	395.1	411.0	429.6	451.9
22.5°	318.1	322.3	331.6	340.3	351.4	362.1	373.3	386.2	401.4	420.9	443.8
25°	298.8	304.2	312.4	321.3	331.9	344.1	356.4	367.8	384.1	404.7	429.1
27.5°	281.5	285.9	291.8	302.0	314.0	325.8	337.9	352.3	368.0	389.8	415.1
30°	270.4	274.5	280.4	289.7	301.0	313.6	326.2	340.1	356.4	378.0	403.9
32.5°	261.6	264.7	269.9	278.4	288.6	301.9	314.4	328.6	345.8	367.0	392.3
35°	248.6	251.2	253.3	261.2	270.4	282.7	295.2	310.6	327.1	347.2	372.5
37.5°	235.8	236.8	239.7	245.0	253.8	265.1	276.8	291.9	308.8	329.2	352.1
40°	228.0	228.4	230.2	235.1	242.9	253.5	264.9	279.7	295.8	315.2	337.9
42.5°	220.3	220.1	221.8	225.2	232.5	242.1	253.3	266.9	283.0	300.9	322.2
45°	208.3	208.3	207.8	210.7	216.6	226.0	235.4	248.4	261.8	279.4	297.3
47.5°	195.6	194.5	194.8	196.3	201.3	209.0	218.4	229.1	241.0	255.8	271.6
50°	187.4	185.8	185.2	186.8	191.3	198.0	207.1	216.4	227.6	240.6	254.1
52.5°	178.5	176.8	175.7	176.9	181.1	187.3	195.4	203.7	213.8	224.4	236.0
55°	164.6	162.8	162.2	162.6	165.7	170.6	177.5	185.0	192.6	201.3	209.5
57.5°	151.0	148.0	147.4	147.2	149.3	153.8	159.6	166.1	171.6	176.9	185.6
60°	142.1	138.4	137.2	136.9	138.5	142.2	147.5	154.0	157.9	161.6	169.1
62.5°	132.4	128.9	126.2	126.5	127.9	131.5	136.1	140.9	143.4	147.4	152.5
65°	117.6	113.1	111.1	110.5	111.2	114.1	117.8	120.8	123.7	125.4	130.2
67.5°	102.7	99.0	96.0	95.2	94.9	96.9	99.9	101.7	103.8	105.1	108.1
70°	92.3	89.0	85.4	84.1	83.9	85.6	88.4	88.7	91.5	92.1	95.1
72.5°	82.1	77.9	75.4	74.2	73.4	74.8	76.7	77.2	78.8	79.9	81.5
75°	66.0	62.9	60.5	58.7	58.1	58.9	58.9	59.9	61.0	61.6	63.4
77.5°	52.0	48.5	45.5	44.5	43.7	43.2	43.7	44.3	43.8	44.9	45.3
80°	42.2	38.5	36.2	35.9	34.6	33.7	33.4	34.0	33.2	33.7	34.9
82.5°	32.5	30.2	27.8	27.4	25.8	25.3	25.1	24.7	24.7	24.6	24.9
85°	19.4	17.9	16.3	15.3	14.6	13.7	13.7	13.3	12.8	12.4	12.7
87.5°	11.9	11.4	10.2	9.4	8.8	7.8	7.4	6.5	5.9	5.3	4.7
90°	20.3	19.2	17.7	16.1	14.6	13.0	11.1	9.0	6.9	4.7	2.6
92.5°	19.6	18.5	17.0	15.4	13.9	12.3	11.5	11.4	11.2	11.1	11.0
95°	20.3	19.2	19.0	18.8	18.6	18.4	21.6	28.2	34.8	41.4	48.0
97.5°	23.2	23.0	44.7	66.3	87.9	109.6	118.3	114.3	110.1	106.0	101.9
100°	35.1	38.4	65.2	91.9	118.6	145.4	157.0	153.5	150.1	146.5	143.1
102.5°	149.4	184.9	188.4	191.9	195.4	198.9	199.3	196.8	194.2	191.7	189.2
105°	273.9	272.2	271.2	270.3	269.2	268.3	267.3	266.0	264.9	263.7	262.6
107.5°	340.2	339.3	338.0	336.7	335.4	334.1	333.1	332.5	331.9	331.4	330.8
110°	385.1	384.7	383.6	382.4	381.3	380.0	379.2	378.6	378.0	377.5	376.9



TEST NUMBER: P332727-935

CATALOG NUMBER: S124DIW-S350D1050U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	428.6	428.7	428.1	427.6	427.1	426.5	425.7	424.6	423.6	422.6	421.5
115°	492.4	492.0	492.2	492.4	492.6	492.8	492.6	492.0	491.5	490.9	490.3
117.5°	557.5	557.6	557.2	556.7	556.3	555.9	555.3	554.5	553.7	552.9	552.2
120°	597.1	596.7	596.8	597.1	597.3	597.4	597.2	596.4	595.6	594.9	594.1
122.5°	636.7	636.5	636.2	635.9	635.7	635.4	635.0	634.6	634.0	633.6	633.2
125°	691.5	690.9	691.3	691.6	692.1	692.4	692.2	691.5	690.7	689.9	689.1
127.5°	747.0	747.1	746.1	745.3	744.4	743.5	743.0	742.8	742.6	742.4	742.2
130°	780.1	779.9	779.3	778.7	778.2	777.6	777.1	777.0	776.8	776.6	776.4
132.5°	812.9	812.7	811.9	811.2	810.5	809.8	809.2	808.8	808.5	808.1	807.8
135°	857.9	857.6	856.8	856.0	855.2	854.5	854.1	854.3	854.5	854.7	854.9
137.5°	901.2	900.8	899.9	899.1	898.2	897.3	896.9	896.8	896.7	896.6	896.6
140°	927.9	927.3	927.0	926.5	926.2	925.7	925.4	925.0	924.6	924.2	923.9
142.5°	952.9	952.4	952.2	951.9	951.7	951.5	951.1	950.4	949.6	948.9	948.2
145°	988.6	988.3	988.3	988.3	988.3	988.3	988.1	987.5	986.9	986.4	985.8
147.5°	1019.8	1019.6	1019.8	1020.0	1020.2	1020.4	1019.9	1018.8	1017.8	1016.7	1015.5
150°	1039.8	1039.8	1040.0	1040.3	1040.4	1040.6	1040.3	1039.6	1038.8	1038.0	1037.2
152.5°	1056.9	1056.6	1057.0	1057.3	1057.7	1058.0	1057.8	1057.2	1056.6	1056.0	1055.3
155°	1079.9	1079.1	1079.7	1080.3	1080.8	1081.4	1081.6	1081.4	1081.2	1081.1	1080.8
157.5°	1099.8	1098.8	1099.5	1100.1	1100.8	1101.5	1101.8	1101.9	1102.1	1102.2	1102.3
160°	1112.5	1111.4	1111.6	1111.7	1112.0	1112.2	1112.5	1113.1	1113.7	1114.3	1114.8
162.5°	1123.0	1121.8	1122.1	1122.2	1122.4	1122.6	1123.1	1123.8	1124.6	1125.3	1126.0
165°	1137.4	1135.8	1135.8	1135.8	1135.8	1135.8	1136.3	1137.2	1138.2	1139.2	1140.1
167.5°	1148.0	1146.2	1146.4	1146.5	1146.6	1146.8	1147.3	1148.3	1149.3	1150.3	1151.3
170°	1154.8	1153.2	1153.1	1152.9	1152.6	1152.4	1153.0	1154.1	1155.3	1156.4	1157.6
172.5°	1159.0	1157.4	1157.3	1157.0	1156.8	1156.7	1157.1	1158.3	1159.4	1160.6	1161.7
175°	1163.7	1162.0	1161.7	1161.6	1161.4	1161.2	1161.7	1162.9	1164.0	1165.2	1166.3
177.5°	1166.1	1164.9	1164.6	1164.3	1164.0	1163.7	1164.1	1165.2	1166.2	1167.3	1168.4
180°	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3



TEST NUMBER: P332727-935

CATALOG NUMBER: S124DIW-S350D1050U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9
2.5°	495.2	496.8	498.9	502.5	503.8	505.4	507.7	507.6	508.2	510.7	515.8
5°	497.0	503.3	509.5	516.8	524.5	529.6	536.5	540.8	545.1	550.6	560.0
7.5°	497.7	507.7	518.9	531.8	543.3	556.5	566.8	576.5	585.3	596.8	608.0
10°	496.6	510.1	524.5	540.8	558.1	572.8	586.1	601.2	614.0	628.0	640.7
12.5°	494.5	510.7	530.0	548.3	568.5	590.2	606.7	622.0	639.0	655.2	674.8
15°	489.7	511.9	534.5	558.5	585.7	610.7	634.6	654.3	672.6	696.9	722.4
17.5°	483.5	507.5	536.1	565.2	593.5	622.1	651.6	681.3	704.5	734.6	754.5
20°	477.9	505.6	534.9	569.6	597.9	633.5	662.9	691.6	723.4	753.4	777.2
22.5°	469.8	500.2	531.3	565.8	603.0	638.8	672.6	703.8	735.6	768.2	797.0
25°	459.7	487.2	524.1	563.2	600.3	639.0	678.0	717.0	751.3	785.7	812.6
27.5°	442.5	477.2	511.5	551.9	593.1	636.9	678.6	719.5	755.4	783.7	800.3
30°	433.6	463.8	501.1	541.7	586.3	633.4	676.7	716.9	750.3	772.9	779.6
32.5°	420.6	451.7	488.2	530.2	577.5	625.9	671.0	708.9	736.8	748.6	740.5
35°	401.2	429.4	466.2	509.2	558.4	609.8	654.5	686.5	700.8	689.6	661.7
37.5°	378.0	405.9	442.9	485.2	536.0	588.4	628.7	651.8	647.0	619.1	577.6
40°	361.7	387.8	423.0	468.6	518.1	570.8	606.2	618.6	605.6	565.7	521.4
42.5°	343.6	369.0	404.4	448.5	500.9	549.4	580.3	581.3	559.5	511.7	467.4
45°	316.1	340.3	373.7	419.6	468.0	513.7	534.1	524.1	483.7	437.7	393.0
47.5°	288.9	309.9	342.9	386.3	432.4	470.8	481.0	463.0	420.0	375.2	333.9
50°	269.0	290.2	321.2	362.7	407.2	440.3	445.2	421.4	379.2	334.2	301.8
52.5°	249.9	271.0	300.7	339.2	379.9	409.8	410.0	382.5	340.4	300.3	270.2
55°	221.9	240.8	267.8	302.2	338.5	361.9	356.2	327.7	291.2	256.3	230.1
57.5°	194.9	211.5	236.2	264.9	296.9	316.2	306.8	279.3	246.8	217.1	197.3
60°	177.5	193.2	214.4	241.5	268.4	283.4	274.5	249.6	219.6	195.8	178.5
62.5°	160.5	173.7	194.2	217.7	242.6	253.7	245.8	221.3	195.4	173.8	159.7
65°	136.6	147.3	163.6	183.8	201.9	211.5	204.8	181.9	162.2	146.7	135.5
67.5°	114.1	122.5	134.9	151.1	166.5	171.7	165.6	149.6	132.9	120.5	112.6
70°	98.6	106.6	116.9	129.4	142.8	148.4	142.2	129.6	116.0	104.5	96.8
72.5°	85.1	91.3	100.0	110.6	121.1	126.7	122.5	110.4	98.8	90.3	83.8
75°	64.8	70.1	76.2	83.8	91.9	95.6	91.9	83.5	75.6	69.3	64.6
77.5°	47.1	49.9	54.7	60.4	65.4	68.2	65.0	59.4	54.5	50.2	47.9
80°	35.9	37.9	41.2	45.6	49.1	51.7	49.7	45.0	41.2	38.3	37.3
82.5°	26.1	27.5	29.6	32.9	35.2	36.6	35.7	32.3	30.7	28.2	27.2
85°	12.8	13.7	15.1	16.1	18.2	18.3	18.5	17.1	15.7	15.1	14.3
87.5°	5.3	5.9	6.9	7.7	8.8	9.3	9.4	9.7	9.4	9.5	9.0
90°	4.7	6.9	9.0	11.1	13.0	14.6	16.1	17.7	19.2	20.3	21.5
92.5°	11.1	11.2	11.4	11.5	12.3	13.9	15.4	17.0	18.5	19.6	20.8
95°	41.4	34.8	28.2	21.6	18.4	18.6	18.8	19.0	19.2	20.3	21.5
97.5°	106.0	110.1	114.3	118.3	109.6	87.9	66.3	44.7	23.0	23.2	23.2
100°	146.5	150.1	153.5	157.0	145.4	118.6	91.9	65.2	38.4	35.1	31.8
102.5°	191.7	194.2	196.8	199.3	198.9	195.4	191.9	188.4	184.9	149.4	113.8
105°	263.7	264.9	266.0	267.3	268.3	269.2	270.3	271.2	272.2	273.9	275.7
107.5°	331.4	331.9	332.5	333.1	334.1	335.4	336.7	338.0	339.3	340.2	341.0
110°	377.5	378.0	378.6	379.2	380.0	381.3	382.4	383.6	384.7	385.1	385.5



TEST NUMBER: P332727-935

CATALOG NUMBER: S124DIW-S350D1050U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	422.6	423.6	424.6	425.7	426.5	427.1	427.6	428.1	428.7	428.6	428.5
115°	490.9	491.5	492.0	492.6	492.8	492.6	492.4	492.2	492.0	492.4	492.8
117.5°	552.9	553.7	554.5	555.3	555.9	556.3	556.7	557.2	557.6	557.5	557.4
120°	594.9	595.6	596.4	597.2	597.4	597.3	597.1	596.8	596.7	597.1	597.4
122.5°	633.6	634.0	634.6	635.0	635.4	635.7	635.9	636.2	636.5	636.7	637.0
125°	689.9	690.7	691.5	692.2	692.4	692.1	691.6	691.3	690.9	691.5	692.1
127.5°	742.4	742.6	742.8	743.0	743.5	744.4	745.3	746.1	747.1	747.0	746.8
130°	776.6	776.8	777.0	777.1	777.6	778.2	778.7	779.3	779.9	780.1	780.2
132.5°	808.1	808.5	808.8	809.2	809.8	810.5	811.2	811.9	812.7	812.9	813.0
135°	854.7	854.5	854.3	854.1	854.5	855.2	856.0	856.8	857.6	857.9	858.3
137.5°	896.6	896.7	896.8	896.9	897.3	898.2	899.1	899.9	900.8	901.2	901.6
140°	924.2	924.6	925.0	925.4	925.7	926.2	926.5	927.0	927.3	927.9	928.5
142.5°	948.9	949.6	950.4	951.1	951.5	951.7	951.9	952.2	952.4	952.9	953.3
145°	986.4	986.9	987.5	988.1	988.3	988.3	988.3	988.3	988.3	988.6	988.8
147.5°	1016.7	1017.8	1018.8	1019.9	1020.4	1020.2	1020.0	1019.8	1019.6	1019.8	1019.9
150°	1038.0	1038.8	1039.6	1040.3	1040.6	1040.4	1040.3	1040.0	1039.8	1039.8	1039.8
152.5°	1056.0	1056.6	1057.2	1057.8	1058.0	1057.7	1057.3	1057.0	1056.6	1056.9	1057.2
155°	1081.1	1081.2	1081.4	1081.6	1081.4	1080.8	1080.3	1079.7	1079.1	1079.9	1080.6
157.5°	1102.2	1102.1	1101.9	1101.8	1101.5	1100.8	1100.1	1099.5	1098.8	1099.8	1100.8
160°	1114.3	1113.7	1113.1	1112.5	1112.2	1112.0	1111.7	1111.6	1111.4	1112.5	1113.7
162.5°	1125.3	1124.6	1123.8	1123.1	1122.6	1122.4	1122.2	1122.1	1121.8	1123.0	1124.1
165°	1139.2	1138.2	1137.2	1136.3	1135.8	1135.8	1135.8	1135.8	1135.8	1137.4	1138.9
167.5°	1150.3	1149.3	1148.3	1147.3	1146.8	1146.6	1146.5	1146.4	1146.2	1148.0	1149.7
170°	1156.4	1155.3	1154.1	1153.0	1152.4	1152.6	1152.9	1153.1	1153.2	1154.8	1156.3
172.5°	1160.6	1159.4	1158.3	1157.1	1156.7	1156.8	1157.0	1157.3	1157.4	1159.0	1160.5
175°	1165.2	1164.0	1162.9	1161.7	1161.2	1161.4	1161.6	1161.7	1162.0	1163.7	1165.4
177.5°	1167.3	1166.2	1165.2	1164.1	1163.7	1164.0	1164.3	1164.6	1164.9	1166.1	1167.4
180°	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3



TEST NUMBER: P332727-935

CATALOG NUMBER: S124DIW-S350D1050U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	491.9	491.9	491.9	491.9	491.9	491.9	491.9
2.5°	518.5	518.8	520.3	521.4	521.8	523.4	523.5
5°	564.0	567.5	574.2	574.8	575.8	581.2	577.0
7.5°	617.4	626.2	632.1	637.3	639.1	641.4	641.0
10°	651.7	664.7	671.2	681.7	682.0	684.7	683.0
12.5°	686.0	701.2	713.1	715.1	723.8	725.1	727.4
15°	734.8	750.9	767.4	773.4	785.3	788.2	792.6
17.5°	780.6	797.0	808.7	823.9	828.9	835.4	831.0
20°	805.7	823.6	838.4	850.3	855.4	859.1	858.7
22.5°	820.9	839.0	850.8	860.0	864.7	866.3	866.2
25°	830.3	840.8	844.5	847.9	842.6	840.8	841.5
27.5°	803.9	801.2	791.7	779.1	766.1	755.8	750.1
30°	767.6	751.7	737.3	712.0	699.0	691.2	684.2
32.5°	716.1	690.9	663.1	639.9	625.1	613.6	611.9
35°	627.8	590.0	555.9	527.5	512.9	500.5	497.6
37.5°	533.7	494.4	463.7	438.8	423.0	414.2	406.0
40°	471.3	437.5	407.3	386.2	374.1	367.8	362.7
42.5°	423.3	392.4	362.3	346.2	335.4	331.5	328.5
45°	356.8	328.0	307.3	295.1	288.8	282.2	279.1
47.5°	303.6	280.3	266.6	256.1	249.3	245.5	243.6
50°	273.5	254.3	242.1	234.1	228.0	225.0	223.3
52.5°	246.8	231.0	220.8	214.4	210.3	208.0	207.3
55°	212.5	200.5	194.0	188.5	185.5	183.4	182.6
57.5°	184.8	175.5	170.2	165.7	164.5	162.8	162.2
60°	166.5	159.4	154.9	151.8	150.8	148.8	149.1
62.5°	150.3	144.5	140.7	139.0	137.6	135.9	136.5
65°	127.2	122.9	120.8	119.2	117.6	116.6	117.4
67.5°	106.7	103.8	101.0	100.0	99.3	99.1	98.2
70°	93.3	90.9	88.4	87.8	87.8	87.0	86.8
72.5°	80.4	78.7	77.1	76.5	75.9	76.3	75.4
75°	62.2	60.7	60.1	59.5	59.3	59.3	58.7
77.5°	45.9	44.9	43.9	43.9	43.1	42.9	42.8
80°	34.9	34.4	33.7	33.7	33.2	33.4	33.0
82.5°	26.2	25.7	25.5	25.1	24.5	24.6	24.2
85°	14.0	13.4	13.3	12.7	12.2	12.7	12.2
87.5°	9.4	9.5	9.5	9.2	9.1	9.2	8.8
90°	22.6	23.8	24.6	25.0	25.4	25.7	26.2
92.5°	22.0	23.2	23.8	23.8	23.9	24.0	24.1
95°	22.6	23.8	24.5	24.7	24.9	25.1	25.3
97.5°	23.4	23.5	23.7	23.8	24.0	24.2	24.5
100°	28.5	25.2	23.7	23.8	24.0	24.2	24.5
102.5°	78.3	42.7	25.0	25.0	25.1	25.1	25.1
105°	277.4	279.1	276.6	269.6	262.6	255.6	248.7
107.5°	341.9	342.8	343.5	344.3	345.0	345.8	346.5
110°	385.9	386.2	386.8	387.4	387.9	388.5	389.1



TEST NUMBER: P332727-935

CATALOG NUMBER: S124DIW-S350D1050U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	428.4	428.3	428.7	429.5	430.2	430.9	431.6
115°	493.2	493.5	493.8	493.8	493.8	493.8	493.8
117.5°	557.4	557.3	557.2	557.2	557.1	557.0	556.9
120°	597.9	598.2	598.2	597.9	597.4	597.1	596.7
122.5°	637.1	637.4	637.3	637.0	636.5	636.2	635.8
125°	692.7	693.2	693.6	693.8	694.0	694.2	694.4
127.5°	746.7	746.6	746.5	746.3	746.1	746.0	745.9
130°	780.5	780.7	780.8	780.8	780.8	780.8	780.8
132.5°	813.3	813.5	813.5	813.3	813.1	813.0	812.9
135°	858.7	859.1	859.5	859.9	860.2	860.7	861.0
137.5°	902.1	902.5	902.7	902.5	902.4	902.3	902.2
140°	929.0	929.6	930.1	930.2	930.4	930.6	930.8
142.5°	953.7	954.2	954.3	954.4	954.4	954.5	954.5
145°	988.9	989.1	989.5	989.8	990.2	990.6	991.0
147.5°	1020.0	1020.2	1020.4	1020.6	1020.8	1021.0	1021.1
150°	1039.8	1039.8	1039.9	1040.1	1040.3	1040.5	1040.7
152.5°	1057.5	1057.8	1057.9	1057.8	1057.7	1057.6	1057.5
155°	1081.4	1082.2	1082.3	1081.7	1081.2	1080.6	1080.0
157.5°	1101.8	1102.9	1102.9	1101.8	1100.8	1099.8	1098.8
160°	1114.8	1116.0	1116.0	1114.8	1113.7	1112.5	1111.4
162.5°	1125.3	1126.4	1126.4	1125.1	1123.8	1122.5	1121.1
165°	1140.5	1142.0	1141.9	1140.1	1138.4	1136.7	1134.9
167.5°	1151.4	1153.1	1153.0	1151.1	1149.1	1147.2	1145.2
170°	1157.9	1159.4	1159.3	1157.3	1155.4	1153.4	1151.5
172.5°	1162.1	1163.6	1163.4	1161.2	1159.2	1157.1	1154.9
175°	1167.2	1169.0	1168.6	1166.3	1164.0	1161.7	1159.3
177.5°	1168.6	1169.9	1169.6	1167.7	1165.9	1164.0	1162.2
180°	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3

(END OF REPORT)