

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332719-935

Luminaire Tested: **S124DIW-S350D470U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332719-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S350D470U935-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 470 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2920.5 lumens
Efficiency: N/A
Efficacy: 127.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 23
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332719-935

CATALOG NUMBER: S124DIW-S350D470U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332719-935

CATALOG NUMBER: S124DIW-S350D470U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	45				45
1	97	92	88	85	88	85	81	78	70	68	66	57	56	54	45	44	43	38				38
2	88	81	74	69	80	74	69	64	62	58	55	50	48	45	40	38	36	31				31
3	80	71	63	58	73	65	59	54	54	50	46	44	41	38	35	33	31	27				27
4	73	63	55	49	67	58	51	45	48	43	39	40	36	33	32	29	27	23				23
5	67	56	48	42	61	51	44	39	43	38	34	36	32	28	28	26	23	20				20
6	62	50	42	36	57	46	39	34	39	33	29	32	28	25	26	23	20	17				17
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	24	20	18	15				15
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	16	14				14
9	49	37	30	25	45	35	28	23	29	24	20	25	20	18	20	17	15	12				12
10	46	34	27	22	42	32	25	21	27	22	18	23	19	16	18	15	13	11				11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4106	4106	4106
5°	4118	4068	4099
10°	4092	4036	4055
15°	4043	3978	3989
20°	3978	3907	3911
25°	3902	3827	3815
30°	3811	3731	3697
35°	3714	3631	3582
40°	3616	3518	3453
45°	3513	3406	3342
50°	3399	3307	3204
55°	3275	3178	3074
60°	3152	3034	2942
65°	3012	2896	2779
70°	2858	2712	2608
75°	2617	2492	2427
80°	2329	2236	2176
85°	2038	1964	1927



TEST NUMBER: P332719-935

CATALOG NUMBER: S124DIW-S350D470U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.9	1.6
10°-20°	135.0	4.6
20°-30°	198.6	6.8
30°-40°	230.9	7.9
40°-50°	230.9	7.9
50°-60°	202.0	6.9
60°-70°	150.0	5.1
70°-80°	85.2	2.9
80°-90°	26.1	0.9
90°-100°	17.8	0.6
100°-110°	113.8	3.9
110°-120°	217.6	7.5
120°-130°	276.3	9.5
130°-140°	295.6	10.1
140°-150°	276.4	9.5
150°-160°	222.9	7.6
160°-170°	143.8	4.9
170°-180°	49.6	1.7
0°-30°	381.5	13.1
0°-40°	612.4	21.0
0°-60°	1045.3	35.8
0°-90°	1306.7	44.7
90°-120°	349.2	12.0
90°-150°	1197.5	41.0
90°-180°	1614.0	55.3
0°-180°	2920.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	509	509	509	509	509	
5°	508	506	502	506	506	48
15°	484	482	476	478	477	136
25°	438	435	430	430	428	201
35°	377	374	368	366	364	236
45°	308	305	298	294	293	237
55°	233	231	226	221	218	208
65°	158	156	152	148	146	156
75°	84	82	80	78	78	89
85°	22	22	21	21	21	24
90°	1	5	9	11	12	2
95°	21	9	9	11	11	28
105°	117	120	122	124	111	123
115°	219	220	220	221	221	216
125°	308	310	309	310	311	275
135°	382	382	384	384	385	295
145°	441	442	442	443	443	275
155°	484	484	483	484	483	223
165°	510	508	508	511	508	144
175°	522	520	520	523	519	50
180°	522	522	522	522	522	



TEST NUMBER: P332719-935

CATALOG NUMBER: S124DIW-S350D470U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6
2.5°	509.9	509.7	509.5	509.3	509.0	508.5	507.7	507.0	506.2	505.3	506.1
5°	508.2	507.8	507.5	507.1	506.8	506.1	505.1	504.1	503.1	502.0	503.1
7.5°	503.5	503.1	502.7	502.4	502.0	501.3	500.2	499.1	498.0	496.9	497.7
10°	499.2	498.9	498.5	498.2	497.8	497.1	495.8	494.6	493.5	492.3	493.0
12.5°	493.7	493.4	493.0	492.6	492.2	491.5	490.2	489.0	487.7	486.5	487.2
15°	483.7	483.4	483.0	482.7	482.3	481.5	480.1	478.7	477.3	476.0	476.6
17.5°	471.7	471.3	470.9	470.5	469.9	469.1	467.8	466.5	465.2	463.9	464.3
20°	463.0	462.5	462.1	461.6	461.2	460.3	458.9	457.5	456.2	454.8	455.1
22.5°	453.5	452.9	452.3	451.7	451.1	450.1	448.8	447.5	446.1	444.7	445.2
25°	438.1	437.5	436.9	436.2	435.6	434.6	433.3	432.0	430.8	429.6	429.6
27.5°	420.5	419.8	419.2	418.5	417.9	417.0	415.8	414.7	413.5	412.2	412.1
30°	408.8	408.0	407.3	406.6	405.9	404.9	403.7	402.5	401.4	400.2	399.8
32.5°	396.4	395.7	395.0	394.4	393.7	392.8	391.6	390.3	389.1	387.8	387.4
35°	376.9	376.3	375.7	375.1	374.4	373.5	372.2	370.9	369.7	368.4	367.8
37.5°	356.5	355.9	355.3	354.8	354.2	353.3	351.9	350.5	349.1	347.8	347.1
40°	343.1	342.4	341.7	341.0	340.3	339.2	337.9	336.5	335.1	333.8	332.9
42.5°	328.8	328.4	328.0	327.5	327.1	326.1	324.6	323.0	321.6	320.1	319.0
45°	307.7	307.0	306.4	305.8	305.1	304.1	302.6	301.2	299.8	298.3	297.3
47.5°	285.6	285.2	284.7	284.3	283.9	283.0	281.6	280.3	279.0	277.6	276.5
50°	270.6	270.3	269.9	269.5	269.1	268.4	267.1	265.8	264.5	263.3	262.0
52.5°	256.0	255.5	255.0	254.6	254.2	253.3	251.9	250.6	249.3	248.0	246.8
55°	232.7	232.5	232.1	231.9	231.6	230.8	229.5	228.3	227.0	225.8	224.7
57.5°	210.5	210.3	209.9	209.7	209.3	208.5	207.2	206.0	204.7	203.5	202.5
60°	195.2	194.8	194.3	193.8	193.4	192.6	191.4	190.2	189.1	187.9	187.1
62.5°	180.2	179.9	179.4	179.1	178.7	177.9	176.6	175.4	174.1	172.9	172.1
65°	157.7	157.3	156.8	156.4	155.9	155.2	154.3	153.4	152.5	151.6	150.7
67.5°	135.1	134.7	134.2	133.8	133.4	132.8	131.9	131.0	130.2	129.2	128.4
70°	121.1	120.4	119.8	119.2	118.5	117.8	117.1	116.4	115.6	114.9	114.2
72.5°	106.1	105.4	104.8	104.2	103.5	102.9	102.3	101.8	101.2	100.6	100.0
75°	83.9	83.5	83.1	82.6	82.1	81.7	81.3	80.8	80.3	79.9	79.6
77.5°	62.9	62.7	62.4	62.3	62.1	61.7	61.4	61.0	60.5	60.2	60.0
80°	50.1	49.9	49.6	49.3	49.1	48.8	48.6	48.5	48.3	48.1	47.9
82.5°	37.7	37.6	37.5	37.4	37.2	37.1	37.1	37.1	37.0	37.0	36.9
85°	22.0	22.0	22.0	22.0	22.0	22.0	21.7	21.5	21.4	21.2	21.2
87.5°	8.7	8.9	9.0	9.0	9.2	9.3	9.4	9.4	9.5	9.6	9.6
90°	1.2	2.2	3.1	4.0	5.0	5.8	6.5	7.2	7.9	8.6	9.1
92.5°	4.9	5.0	5.0	5.1	5.2	5.5	6.2	6.9	7.6	8.3	8.8
95°	21.4	18.5	15.6	12.7	9.6	8.3	8.4	8.4	8.5	8.6	9.1
97.5°	45.5	47.4	49.2	51.1	53.0	49.0	39.3	29.6	20.0	10.3	10.3
100°	64.0	65.5	67.2	68.7	70.3	65.0	53.0	41.1	29.1	17.1	15.7
102.5°	84.6	85.8	86.9	88.0	89.2	88.9	87.4	85.8	84.3	82.7	66.8
105°	117.4	118.0	118.5	119.0	119.5	120.0	120.5	120.9	121.3	121.7	122.5
107.5°	148.0	148.3	148.5	148.8	149.0	149.5	150.0	150.6	151.2	151.8	152.1
110°	168.6	168.8	169.1	169.4	169.6	170.0	170.5	171.1	171.6	172.1	172.3



TEST NUMBER: P332719-935

CATALOG NUMBER: S124DIW-S350D470U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	188.6	189.0	189.5	189.9	190.5	190.8	191.1	191.2	191.5	191.7	191.7
115°	219.3	219.6	219.8	220.1	220.3	220.4	220.3	220.2	220.2	220.1	220.2
117.5°	247.0	247.4	247.7	248.1	248.4	248.7	248.8	249.0	249.3	249.4	249.3
120°	265.7	266.0	266.4	266.7	267.1	267.3	267.2	267.1	267.0	266.9	267.1
122.5°	283.2	283.4	283.6	283.9	284.0	284.2	284.3	284.5	284.6	284.7	284.8
125°	308.2	308.6	308.9	309.3	309.6	309.7	309.5	309.4	309.2	309.0	309.3
127.5°	332.0	332.1	332.2	332.3	332.3	332.6	332.9	333.4	333.8	334.2	334.2
130°	347.2	347.3	347.5	347.6	347.7	347.8	348.1	348.4	348.6	348.9	349.0
132.5°	361.4	361.4	361.6	361.8	362.0	362.2	362.6	362.8	363.2	363.5	363.6
135°	382.4	382.3	382.2	382.1	382.0	382.2	382.5	382.9	383.2	383.6	383.7
137.5°	401.1	401.1	401.1	401.1	401.2	401.4	401.7	402.2	402.5	402.9	403.1
140°	413.2	413.4	413.5	413.7	413.9	414.1	414.2	414.5	414.7	414.8	415.1
142.5°	424.1	424.5	424.8	425.1	425.4	425.6	425.7	425.9	425.9	426.0	426.2
145°	440.9	441.2	441.4	441.7	442.0	442.1	442.1	442.1	442.1	442.1	442.2
147.5°	454.3	454.8	455.2	455.7	456.2	456.4	456.3	456.2	456.2	456.1	456.2
150°	464.0	464.3	464.7	465.0	465.4	465.5	465.4	465.3	465.2	465.1	465.1
152.5°	472.1	472.3	472.6	472.9	473.2	473.2	473.1	472.9	472.8	472.6	472.8
155°	483.5	483.5	483.6	483.7	483.8	483.7	483.5	483.2	482.9	482.7	483.0
157.5°	493.1	493.0	492.9	492.9	492.8	492.7	492.4	492.1	491.8	491.5	492.0
160°	498.7	498.4	498.2	497.9	497.7	497.5	497.4	497.3	497.2	497.1	497.7
162.5°	503.7	503.3	503.0	502.7	502.4	502.1	502.0	502.0	501.9	501.8	502.3
165°	510.0	509.5	509.1	508.7	508.2	508.1	508.1	508.1	508.1	508.1	508.8
167.5°	515.0	514.5	514.1	513.7	513.2	512.9	512.9	512.8	512.8	512.7	513.5
170°	517.8	517.3	516.8	516.3	515.7	515.5	515.6	515.7	515.7	515.8	516.5
172.5°	519.7	519.2	518.7	518.1	517.6	517.4	517.5	517.5	517.6	517.7	518.4
175°	521.7	521.2	520.6	520.1	519.6	519.4	519.5	519.6	519.7	519.8	520.6
177.5°	522.6	522.2	521.7	521.2	520.7	520.6	520.6	520.8	520.9	521.1	521.6
180°	521.7	521.7	521.7	521.7	521.7	521.7	521.7	521.7	521.7	521.7	521.7



TEST NUMBER: P332719-935

CATALOG NUMBER: S124DIW-S350D470U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6
2.5°	506.8	507.6	508.2	508.6	508.5	508.4	508.3	508.2
5°	504.1	505.1	506.1	506.4	506.3	506.1	505.9	505.8
7.5°	498.4	499.3	500.1	500.4	500.3	500.2	500.1	500.0
10°	493.8	494.5	495.2	495.5	495.3	495.1	494.9	494.7
12.5°	488.0	488.8	489.7	489.9	489.7	489.4	489.1	488.9
15°	477.1	477.6	478.2	478.3	478.0	477.8	477.5	477.3
17.5°	464.6	464.9	465.3	465.4	465.2	465.0	464.9	464.7
20°	455.4	455.6	455.9	456.0	455.7	455.6	455.4	455.2
22.5°	445.7	446.2	446.7	446.8	446.4	446.1	445.7	445.5
25°	429.7	429.8	429.9	429.8	429.4	429.0	428.7	428.3
27.5°	411.8	411.6	411.4	411.0	410.6	410.2	409.7	409.2
30°	399.5	399.2	398.7	398.4	397.9	397.4	397.0	396.6
32.5°	386.9	386.5	386.1	385.6	385.2	384.7	384.3	383.8
35°	367.1	366.5	365.8	365.3	364.9	364.5	363.9	363.5
37.5°	346.4	345.7	345.0	344.4	343.8	343.2	342.6	342.0
40°	332.0	331.1	330.2	329.5	329.0	328.6	328.1	327.7
42.5°	318.0	316.9	315.9	315.2	314.9	314.6	314.3	314.0
45°	296.4	295.3	294.4	293.7	293.4	293.2	292.9	292.7
47.5°	275.3	274.2	273.1	272.2	271.6	270.9	270.2	269.5
50°	260.7	259.5	258.2	257.3	256.8	256.2	255.6	255.1
52.5°	245.7	244.6	243.5	242.5	241.9	241.2	240.5	239.8
55°	223.6	222.5	221.4	220.6	220.1	219.6	219.0	218.4
57.5°	201.5	200.4	199.4	198.6	198.1	197.6	197.1	196.5
60°	186.2	185.5	184.6	184.0	183.6	183.0	182.6	182.2
62.5°	171.4	170.7	169.9	169.3	168.8	168.4	168.0	167.5
65°	149.8	148.9	148.0	147.3	146.9	146.4	145.9	145.5
67.5°	127.5	126.7	125.8	125.3	125.2	125.0	124.9	124.8
70°	113.5	112.8	112.0	111.5	111.2	111.0	110.7	110.5
72.5°	99.4	98.8	98.2	97.8	97.6	97.3	97.0	96.8
75°	79.1	78.8	78.4	78.2	78.1	78.0	77.9	77.8
77.5°	59.9	59.8	59.8	59.6	59.3	59.1	58.8	58.6
80°	47.7	47.5	47.4	47.3	47.1	47.0	46.9	46.8
82.5°	36.8	36.7	36.6	36.5	36.4	36.2	36.2	36.1
85°	21.2	21.2	21.2	21.2	21.1	21.0	20.8	20.8
87.5°	9.7	9.8	10.0	10.0	10.1	10.1	10.2	10.2
90°	9.6	10.2	10.7	11.0	11.2	11.4	11.5	11.7
92.5°	9.3	9.8	10.3	10.6	10.7	10.7	10.8	10.8
95°	9.6	10.2	10.7	10.9	11.0	11.1	11.2	11.3
97.5°	10.4	10.4	10.5	10.6	10.7	10.8	10.8	10.9
100°	14.2	12.7	11.3	10.6	10.7	10.8	10.8	10.9
102.5°	50.9	35.0	19.1	11.2	11.2	11.2	11.2	11.3
105°	123.3	124.1	124.8	123.7	120.5	117.4	114.3	111.2
107.5°	152.6	152.9	153.3	153.7	154.0	154.3	154.6	155.0
110°	172.5	172.6	172.8	173.0	173.2	173.5	173.7	174.0



TEST NUMBER: P332719-935

CATALOG NUMBER: S124DIW-S350D470U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	191.7	191.7	191.6	191.7	192.1	192.4	192.8	193.0
115°	220.4	220.6	220.8	220.8	220.8	220.8	220.8	220.8
117.5°	249.3	249.3	249.3	249.3	249.2	249.2	249.2	249.1
120°	267.3	267.4	267.6	267.6	267.4	267.3	267.1	266.9
122.5°	284.9	285.0	285.1	285.1	284.9	284.7	284.6	284.4
125°	309.5	309.8	310.0	310.2	310.3	310.4	310.5	310.6
127.5°	334.1	334.0	334.0	333.9	333.8	333.7	333.7	333.6
130°	349.0	349.1	349.2	349.2	349.2	349.2	349.2	349.2
132.5°	363.7	363.8	363.9	363.9	363.8	363.8	363.7	363.6
135°	383.9	384.1	384.3	384.4	384.6	384.8	385.0	385.1
137.5°	403.3	403.5	403.7	403.7	403.7	403.6	403.6	403.6
140°	415.3	415.6	415.9	416.0	416.1	416.2	416.3	416.4
142.5°	426.4	426.6	426.8	426.9	426.9	427.0	427.0	427.0
145°	442.3	442.4	442.5	442.6	442.7	442.9	443.1	443.2
147.5°	456.2	456.2	456.3	456.4	456.5	456.6	456.7	456.8
150°	465.1	465.1	465.1	465.2	465.3	465.4	465.5	465.5
152.5°	472.9	473.0	473.2	473.2	473.2	473.1	473.0	473.0
155°	483.4	483.7	484.1	484.1	483.9	483.6	483.4	483.1
157.5°	492.4	492.8	493.3	493.3	492.8	492.4	492.0	491.5
160°	498.2	498.7	499.2	499.2	498.7	498.2	497.7	497.1
162.5°	502.8	503.3	503.9	503.9	503.3	502.7	502.0	501.5
165°	509.5	510.1	510.8	510.7	510.0	509.2	508.4	507.6
167.5°	514.3	515.1	515.8	515.7	514.9	514.0	513.2	512.3
170°	517.2	517.9	518.7	518.6	517.6	516.8	515.9	515.1
172.5°	519.1	519.8	520.5	520.4	519.4	518.5	517.5	516.6
175°	521.3	522.1	522.9	522.7	521.7	520.6	519.6	518.6
177.5°	522.2	522.7	523.3	523.1	522.4	521.5	520.6	519.9
180°	521.7	521.7	521.7	521.7	521.7	521.7	521.7	521.7

(END OF REPORT)