

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332799-830

Luminaire Tested: **S124DIW-S795D1560U830-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332799-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S795D1560U830-4F0-1E-UDD-A
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 795 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1560 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9222.7 lumens
Efficiency: N/A
Efficacy: 135.4 lumens/watt
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 68.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332799-830

CATALOG NUMBER: S124DIW-S795D1560U830-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332799-830

CATALOG NUMBER: S124DIW-S795D1560U830-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44	36
1	95	91	87	84	86	82	79	76	66	64	62	52	51	49	39	38	37	31
2	86	79	73	68	78	72	67	63	58	55	52	46	43	41	34	33	31	26
3	79	70	63	57	71	64	57	53	52	47	44	41	38	35	30	29	27	22
4	72	62	54	48	65	56	50	45	46	41	37	36	33	30	27	25	23	19
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	25	22	20	17
6	61	49	42	36	55	45	38	33	37	32	28	29	26	23	22	20	18	15
7	56	44	37	31	51	41	34	29	34	28	25	27	23	20	20	18	16	13
8	52	40	33	28	47	37	30	26	31	25	22	24	21	18	19	16	14	12
9	49	37	29	25	44	34	27	23	28	23	20	22	19	16	17	15	13	11
10	45	34	27	22	41	31	25	20	26	21	18	21	17	15	16	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9769	9769	9769	9769
5°	11505	9794	8645	9794
10°	13774	9752	7783	9752
15°	16298	9653	7148	9653
20°	18148	9552	6580	9552
25°	18441	9404	6188	9404
30°	15691	9261	6065	9261
35°	12064	9030	6067	9030
40°	9403	8759	6181	8759
45°	7840	8350	6284	8350
50°	6900	7851	6498	7851
55°	6321	7253	6759	7253
60°	5924	6717	7074	6717
65°	5515	6118	7335	6118
70°	5042	5526	7501	5526
75°	4504	4863	7411	4863
80°	3775	3984	7178	3984
85°	2788	2881	6873	2881



TEST NUMBER: P332799-830

CATALOG NUMBER: S124DIW-S795D1560U830-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	117.9	1.3
10°-20°	363.4	3.9
20°-30°	576.2	6.2
30°-40°	641.2	7.0
40°-50°	583.7	6.3
50°-60°	477.0	5.2
60°-70°	340.5	3.7
70°-80°	187.5	2.0
80°-90°	56.7	0.6
90°-100°	65.0	0.7
100°-110°	414.4	4.5
110°-120°	792.8	8.6
120°-130°	1006.4	10.9
130°-140°	1076.8	11.7
140°-150°	1006.9	10.9
150°-160°	812.0	8.8
160°-170°	523.7	5.7
170°-180°	180.5	2.0
0°-30°	1057.5	11.5
0°-40°	1698.7	18.4
0°-60°	2759.4	29.9
0°-90°	3344.2	36.3
90°-120°	1272.2	13.8
90°-150°	4362.3	47.3
90°-180°	5879.0	63.7
0°-180°	9222.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1210	1210	1210	1210	1210	
5°	1420	1209	1067	1209	1420	144
15°	1950	1155	855	1155	1950	551
25°	2070	1056	695	1056	2070	913
35°	1224	916	616	916	1224	777
45°	687	731	550	731	687	541
55°	449	515	480	515	449	406
65°	289	320	384	320	289	286
75°	144	156	238	156	144	154
85°	30	31	74	31	30	38
90°	43	4	43	4	43	19
95°	41	78	41	78	41	33
105°	405	428	405	428	405	353
115°	805	799	805	799	805	796
125°	1131	1123	1131	1123	1131	1008
135°	1403	1393	1403	1393	1403	1080
145°	1615	1606	1615	1606	1615	1009
155°	1760	1761	1760	1761	1760	811
165°	1849	1858	1849	1858	1849	522
175°	1889	1900	1889	1900	1889	180
180°	1900	1900	1900	1900	1900	



TEST NUMBER: P332799-830

CATALOG NUMBER: S124DIW-S795D1560U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1
2.5°	1287.9	1287.5	1283.5	1282.7	1279.9	1276.3	1275.4	1269.0	1256.2	1250.2	1248.6
5°	1419.7	1429.6	1416.6	1414.1	1412.6	1396.1	1387.5	1377.5	1354.4	1341.0	1330.4
7.5°	1576.9	1578.0	1572.3	1567.7	1555.0	1540.5	1518.9	1495.8	1468.4	1439.7	1418.2
10°	1680.3	1684.3	1677.8	1676.8	1651.2	1635.2	1603.1	1576.0	1544.9	1510.3	1478.8
12.5°	1789.4	1783.8	1780.5	1759.0	1754.3	1725.0	1687.7	1659.8	1611.9	1572.2	1530.1
15°	1950.0	1939.0	1931.9	1902.3	1887.8	1847.2	1807.6	1777.1	1714.4	1654.7	1609.6
17.5°	2044.2	2055.2	2039.0	2026.8	1989.2	1960.8	1920.3	1856.1	1807.1	1733.1	1676.1
20°	2112.4	2113.4	2104.4	2091.9	2062.3	2026.2	1982.1	1911.9	1853.2	1779.5	1701.4
22.5°	2130.8	2131.1	2127.2	2115.5	2093.1	2063.9	2019.4	1960.8	1889.7	1809.6	1731.5
25°	2070.3	2068.3	2072.8	2085.8	2077.3	2068.3	2042.7	1999.1	1933.0	1848.2	1764.0
27.5°	1845.3	1859.2	1884.6	1916.7	1947.6	1971.1	1977.7	1968.8	1927.8	1858.1	1769.9
30°	1683.3	1700.3	1719.4	1751.4	1813.6	1849.3	1888.3	1917.9	1901.4	1845.7	1763.5
32.5°	1505.2	1509.5	1537.8	1574.2	1631.2	1699.7	1761.6	1821.7	1841.6	1812.4	1743.9
35°	1224.1	1231.1	1261.7	1297.8	1367.5	1451.2	1544.5	1627.7	1696.3	1723.9	1688.8
37.5°	998.9	1019.1	1040.7	1079.5	1140.9	1216.2	1313.1	1420.7	1523.1	1591.7	1603.3
40°	892.3	904.8	920.4	949.9	1002.0	1076.3	1159.4	1282.8	1391.6	1489.8	1521.9
42.5°	808.0	815.4	824.9	851.7	891.4	965.2	1041.1	1149.6	1258.9	1376.3	1430.0
45°	686.7	694.3	710.3	725.9	755.9	807.1	877.7	967.0	1076.8	1190.1	1289.3
47.5°	599.2	604.0	613.5	630.1	655.6	689.4	746.9	821.4	923.1	1033.1	1138.9
50°	549.4	553.4	560.9	576.0	595.5	625.6	672.7	742.4	822.1	932.9	1036.6
52.5°	510.1	511.7	517.3	527.4	543.0	568.3	606.9	664.6	738.7	837.4	940.8
55°	449.1	451.2	456.2	463.7	477.2	493.2	522.8	565.9	630.7	716.3	806.1
57.5°	399.0	400.4	404.6	407.6	418.7	431.7	454.5	485.2	534.2	606.9	687.0
60°	366.9	365.9	371.0	373.4	381.0	392.0	409.5	439.1	481.7	540.4	614.1
62.5°	335.6	334.2	338.5	341.8	346.1	355.5	369.9	393.0	427.6	480.6	544.3
65°	288.7	286.7	289.3	293.2	297.3	302.3	312.8	333.4	360.9	399.0	447.6
67.5°	241.6	243.7	244.1	246.1	248.5	255.2	262.5	277.0	296.4	327.0	368.2
70°	213.6	214.1	216.0	216.0	217.5	223.6	229.6	238.1	257.1	285.2	318.8
72.5°	185.5	187.6	186.8	188.4	189.5	193.5	197.9	206.0	222.3	243.1	271.5
75°	144.4	145.9	145.9	146.4	147.9	149.4	152.9	158.9	170.4	186.0	205.6
77.5°	105.3	105.5	106.1	108.0	108.0	110.4	113.0	117.8	123.5	134.1	146.1
80°	81.2	82.2	81.7	82.8	82.8	84.7	85.7	91.7	94.3	101.2	110.7
82.5°	59.6	60.5	60.4	61.8	62.7	63.1	64.5	66.8	69.4	75.6	79.5
85°	30.1	31.1	30.1	31.1	32.6	33.1	34.6	35.1	37.1	38.6	42.1
87.5°	17.3	18.5	18.3	18.6	19.2	19.4	19.4	18.7	19.9	19.9	21.0
90°	42.6	42.0	41.4	40.7	40.2	38.8	36.9	35.1	33.2	31.3	28.7
92.5°	39.2	39.1	39.0	38.8	38.7	37.7	35.8	33.9	32.0	30.2	27.6
95°	41.2	40.9	40.6	40.2	40.0	38.8	36.9	35.1	33.2	31.3	30.9
97.5°	39.8	39.5	39.2	38.8	38.5	38.3	38.1	37.9	37.7	37.5	72.8
100°	39.8	39.5	39.2	38.8	38.5	41.1	46.5	51.8	57.2	62.6	106.1
102.5°	40.9	40.9	40.8	40.7	40.7	69.7	127.5	185.5	243.4	301.3	307.0
105°	405.1	416.5	427.8	439.2	450.5	454.9	452.0	449.1	446.3	443.5	441.9
107.5°	564.6	563.4	562.1	561.0	559.8	558.5	557.1	555.7	554.3	552.9	550.7
110°	634.0	633.0	632.1	631.1	630.2	629.3	628.8	628.1	627.5	626.8	624.9



TEST NUMBER: P332799-830

CATALOG NUMBER: S124DIW-S795D1560U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	703.3	702.1	700.9	699.7	698.5	698.0	698.0	698.2	698.3	698.5	697.6
115°	804.6	804.6	804.6	804.6	804.6	804.2	803.5	803.0	802.3	801.6	802.0
117.5°	907.4	907.6	907.7	907.8	908.0	908.0	908.1	908.3	908.4	908.5	907.9
120°	972.2	972.9	973.5	974.1	974.8	974.8	974.1	973.5	972.9	972.2	972.5
122.5°	1035.9	1036.5	1037.2	1037.8	1038.4	1038.6	1038.2	1037.8	1037.5	1037.1	1036.6
125°	1131.4	1131.1	1130.8	1130.5	1130.2	1129.5	1128.6	1127.7	1126.7	1125.8	1126.3
127.5°	1215.3	1215.5	1215.8	1216.1	1216.3	1216.5	1216.7	1216.9	1217.1	1217.3	1215.8
130°	1272.1	1272.1	1272.1	1272.1	1272.1	1272.0	1271.7	1271.4	1271.0	1270.7	1269.8
132.5°	1324.5	1324.7	1324.9	1325.2	1325.5	1325.4	1325.1	1324.8	1324.5	1324.2	1323.0
135°	1402.9	1402.3	1401.7	1401.0	1400.4	1399.8	1399.1	1398.5	1397.9	1397.2	1396.0
137.5°	1470.0	1470.2	1470.4	1470.6	1470.7	1470.6	1469.8	1469.1	1468.4	1467.7	1466.3
140°	1516.6	1516.3	1516.0	1515.7	1515.3	1514.8	1513.8	1512.9	1511.9	1510.9	1510.3
142.5°	1555.3	1555.2	1555.2	1555.1	1555.0	1554.6	1554.0	1553.3	1552.6	1551.9	1551.5
145°	1614.7	1614.1	1613.4	1612.8	1612.2	1611.7	1611.4	1611.1	1610.7	1610.4	1610.4
147.5°	1663.9	1663.6	1663.2	1662.9	1662.6	1662.4	1662.1	1661.8	1661.6	1661.3	1661.6
150°	1695.7	1695.4	1695.1	1694.8	1694.5	1694.3	1694.3	1694.3	1694.3	1694.3	1694.6
152.5°	1723.0	1723.2	1723.3	1723.5	1723.7	1723.6	1723.1	1722.6	1722.1	1721.6	1722.1
155°	1759.7	1760.7	1761.6	1762.6	1763.5	1763.3	1762.1	1760.8	1759.5	1758.2	1759.3
157.5°	1790.4	1792.1	1793.7	1795.4	1797.0	1797.0	1795.4	1793.7	1792.1	1790.4	1791.5
160°	1810.8	1812.8	1814.7	1816.6	1818.4	1818.4	1816.6	1814.7	1812.8	1810.8	1811.2
162.5°	1826.7	1828.9	1831.1	1833.2	1835.3	1835.5	1833.6	1831.7	1829.8	1827.9	1828.2
165°	1849.3	1852.1	1854.9	1857.8	1860.6	1860.8	1858.2	1855.7	1853.1	1850.7	1850.7
167.5°	1866.0	1869.2	1872.4	1875.5	1878.7	1878.9	1876.0	1873.3	1870.5	1867.7	1867.9
170°	1876.2	1879.4	1882.5	1885.7	1888.9	1889.2	1886.7	1884.1	1881.6	1879.1	1878.8
172.5°	1881.9	1885.4	1888.8	1892.2	1895.5	1896.0	1893.5	1890.9	1888.4	1885.9	1885.6
175°	1889.0	1892.8	1896.6	1900.4	1904.2	1904.7	1901.9	1898.9	1896.1	1893.3	1893.0
177.5°	1893.6	1896.6	1899.6	1902.7	1905.7	1906.2	1904.2	1902.1	1900.2	1898.1	1897.6
180°	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4



TEST NUMBER: P332799-830

CATALOG NUMBER: S124DIW-S795D1560U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1
2.5°	1249.0	1243.4	1239.3	1236.1	1227.4	1222.1	1218.1	1212.5	1206.1	1199.3	1190.8
5°	1319.8	1302.8	1290.3	1271.2	1253.2	1238.1	1222.7	1208.6	1191.6	1173.0	1159.4
7.5°	1394.4	1369.0	1336.5	1308.3	1276.7	1249.1	1224.5	1199.2	1172.9	1147.5	1124.1
10°	1441.7	1409.1	1373.0	1330.4	1290.3	1254.7	1221.6	1189.6	1158.5	1127.4	1100.8
12.5°	1492.6	1452.0	1398.6	1348.9	1303.9	1256.3	1216.4	1177.1	1139.6	1106.9	1075.9
15°	1560.9	1502.3	1440.7	1374.0	1314.8	1259.2	1204.6	1155.0	1112.9	1069.7	1039.6
17.5°	1603.0	1530.4	1459.9	1390.3	1318.7	1248.5	1189.6	1132.3	1079.6	1036.7	998.8
20°	1630.7	1558.5	1470.7	1401.1	1315.9	1243.7	1175.5	1111.8	1056.7	1011.1	971.9
22.5°	1654.7	1571.3	1483.6	1391.9	1307.0	1230.5	1155.8	1091.7	1035.5	987.4	949.9
25°	1667.7	1572.0	1476.8	1385.5	1289.3	1198.5	1130.9	1055.7	995.5	944.9	904.8
27.5°	1669.1	1566.8	1459.1	1357.6	1258.3	1173.8	1088.4	1021.2	958.8	905.2	866.7
30°	1664.7	1558.0	1442.2	1332.4	1232.7	1140.9	1066.8	993.5	929.9	876.8	836.6
32.5°	1650.7	1539.5	1420.5	1304.3	1201.0	1111.3	1034.6	965.1	903.1	850.6	808.6
35°	1610.1	1500.3	1373.5	1252.7	1146.9	1056.2	987.0	916.3	854.2	804.6	763.9
37.5°	1546.6	1447.4	1318.4	1193.4	1089.6	998.4	929.9	866.0	809.9	759.5	717.9
40°	1491.3	1404.1	1274.8	1152.9	1040.7	953.9	889.8	831.1	775.5	727.8	688.2
42.5°	1427.6	1351.5	1232.3	1103.2	994.9	907.9	845.3	792.6	740.2	696.2	656.6
45°	1313.8	1263.8	1151.4	1032.2	919.4	837.2	777.5	731.4	687.3	644.1	611.1
47.5°	1183.1	1158.3	1063.8	950.5	843.4	762.3	710.6	668.0	629.3	592.9	563.6
50°	1095.3	1083.3	1001.5	892.3	790.0	713.8	661.7	625.1	592.0	560.0	532.3
52.5°	1008.7	1008.2	934.6	834.5	739.9	666.5	614.7	580.6	552.0	525.8	501.1
55°	876.3	890.2	832.6	743.4	658.6	592.5	545.9	515.3	495.3	473.7	455.2
57.5°	754.6	777.9	730.4	651.8	581.1	520.1	479.6	456.6	435.2	422.2	408.7
60°	675.2	697.3	660.2	594.0	527.4	475.2	436.6	416.0	397.5	388.5	379.0
62.5°	604.6	624.3	596.8	535.5	477.6	427.5	394.9	375.1	362.6	352.8	346.5
65°	503.8	520.3	496.8	452.1	402.6	362.4	335.8	320.3	308.3	304.3	297.3
67.5°	407.3	422.3	409.5	371.6	331.9	301.4	280.7	265.8	258.6	255.1	250.2
70°	349.9	365.0	351.4	318.3	287.8	262.2	242.6	234.1	226.6	225.1	218.0
72.5°	301.3	311.6	298.0	272.2	246.0	224.5	209.3	200.4	196.5	193.8	190.0
75°	226.1	235.1	226.1	206.0	187.5	172.5	159.4	155.9	151.4	149.9	147.4
77.5°	160.0	167.9	160.9	148.4	134.5	122.9	115.9	111.4	110.4	107.7	109.0
80°	122.3	127.3	120.8	112.3	101.2	93.2	88.2	85.7	82.8	81.7	83.7
82.5°	87.8	90.0	86.7	81.0	72.8	67.6	64.2	61.3	60.7	60.9	60.9
85°	45.6	45.1	44.6	39.6	37.1	33.6	31.6	31.1	30.5	31.6	32.6
87.5°	20.5	20.4	19.5	17.2	15.4	13.5	12.3	11.3	12.3	13.5	14.6
90°	26.2	23.7	21.2	18.2	14.7	11.2	7.7	4.2	7.7	11.2	14.7
92.5°	25.1	22.5	20.0	18.7	18.5	18.3	18.1	17.9	18.1	18.3	18.5
95°	30.6	30.3	30.0	35.3	46.0	56.7	67.4	78.1	67.4	56.7	46.0
97.5°	108.0	143.3	178.5	192.8	186.2	179.4	172.7	166.0	172.7	179.4	186.2
100°	149.7	193.3	236.9	255.8	250.2	244.5	238.8	233.1	238.8	244.5	250.2
102.5°	312.7	318.4	324.0	324.8	320.7	316.5	312.4	308.1	312.4	316.5	320.7
105°	440.4	438.8	437.2	435.5	433.6	431.6	429.7	427.8	429.7	431.6	433.6
107.5°	548.7	546.5	544.3	542.8	541.9	540.9	540.0	538.9	540.0	540.9	541.9
110°	623.0	621.1	619.3	617.8	616.9	616.0	615.0	614.1	615.0	616.0	616.9



TEST NUMBER: P332799-830

CATALOG NUMBER: S124DIW-S795D1560U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	696.7	695.8	694.9	693.6	691.9	690.2	688.5	686.8	688.5	690.2	691.9
115°	802.3	802.6	803.0	802.6	801.6	800.7	799.7	798.8	799.7	800.7	801.6
117.5°	907.2	906.4	905.8	904.8	903.5	902.3	901.0	899.8	901.0	902.3	903.5
120°	972.9	973.2	973.5	973.0	971.8	970.5	969.2	968.0	969.2	970.5	971.8
122.5°	1036.1	1035.8	1035.3	1034.7	1033.9	1033.1	1032.4	1031.6	1032.4	1033.1	1033.9
125°	1127.0	1127.7	1128.2	1127.9	1126.7	1125.4	1124.2	1122.9	1124.2	1125.4	1126.7
127.5°	1214.4	1213.0	1211.4	1210.6	1210.2	1209.9	1209.7	1209.3	1209.7	1209.9	1210.2
130°	1268.9	1267.9	1267.0	1266.3	1266.0	1265.6	1265.4	1265.1	1265.4	1265.6	1266.0
132.5°	1321.7	1320.6	1319.4	1318.5	1318.0	1317.4	1316.7	1316.2	1316.7	1317.4	1318.0
135°	1394.7	1393.5	1392.1	1391.7	1392.0	1392.3	1392.6	1393.0	1392.6	1392.3	1392.0
137.5°	1465.0	1463.6	1462.2	1461.4	1461.3	1461.1	1461.0	1460.9	1461.0	1461.1	1461.3
140°	1509.7	1509.0	1508.4	1507.8	1507.1	1506.6	1505.9	1505.2	1505.9	1506.6	1507.1
142.5°	1551.1	1550.8	1550.4	1549.6	1548.5	1547.4	1546.1	1545.0	1546.1	1547.4	1548.5
145°	1610.4	1610.4	1610.4	1610.0	1609.0	1608.1	1607.1	1606.2	1607.1	1608.1	1609.0
147.5°	1662.0	1662.3	1662.6	1661.9	1660.1	1658.3	1656.5	1654.8	1656.5	1658.3	1660.1
150°	1695.0	1695.3	1695.5	1695.1	1693.8	1692.5	1691.3	1690.1	1691.3	1692.5	1693.8
152.5°	1722.7	1723.3	1723.9	1723.6	1722.6	1721.6	1720.6	1719.6	1720.6	1721.6	1722.6
155°	1760.2	1761.1	1762.1	1762.4	1762.1	1761.7	1761.4	1761.1	1761.4	1761.7	1762.1
157.5°	1792.5	1793.6	1794.7	1795.4	1795.5	1795.7	1795.9	1796.1	1795.9	1795.7	1795.5
160°	1811.5	1811.8	1812.1	1812.8	1813.7	1814.7	1815.6	1816.6	1815.6	1814.7	1813.7
162.5°	1828.5	1828.8	1829.2	1829.9	1831.2	1832.3	1833.5	1834.8	1833.5	1832.3	1831.2
165°	1850.7	1850.7	1850.7	1851.4	1853.0	1854.6	1856.1	1857.8	1856.1	1854.6	1853.0
167.5°	1868.1	1868.3	1868.5	1869.3	1871.0	1872.6	1874.3	1875.9	1874.3	1872.6	1871.0
170°	1878.5	1878.1	1877.8	1878.6	1880.5	1882.4	1884.3	1886.2	1884.3	1882.4	1880.5
172.5°	1885.3	1885.0	1884.6	1885.5	1887.3	1889.2	1891.1	1893.0	1891.1	1889.2	1887.3
175°	1892.6	1892.3	1892.1	1892.8	1894.7	1896.6	1898.5	1900.4	1898.5	1896.6	1894.7
177.5°	1897.1	1896.6	1896.1	1896.8	1898.5	1900.3	1902.1	1903.8	1902.1	1900.3	1898.5
180°	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4



TEST NUMBER: P332799-830

CATALOG NUMBER: S124DIW-S795D1560U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1
2.5°	1186.8	1183.3	1178.0	1170.8	1164.8	1158.4	1156.8	1154.3	1159.1	1155.2	1154.0
5°	1147.9	1137.4	1123.9	1108.3	1099.3	1086.3	1083.7	1078.7	1073.7	1073.3	1068.2
7.5°	1106.7	1091.3	1073.6	1057.7	1043.0	1028.8	1019.5	1017.5	1010.1	1005.8	1000.8
10°	1080.2	1061.2	1040.7	1025.6	1008.6	993.5	983.0	977.0	971.9	966.5	961.5
12.5°	1049.0	1028.7	1011.8	995.5	975.2	963.8	946.5	936.1	935.1	935.2	922.2
15°	1012.6	992.5	966.5	943.4	932.4	910.3	900.8	888.7	881.3	873.7	867.7
17.5°	971.0	946.0	925.7	899.2	878.2	860.6	848.1	840.8	829.5	818.9	811.2
20°	944.9	918.3	896.8	868.7	845.6	824.1	813.6	803.5	795.0	786.0	777.5
22.5°	918.4	890.7	864.3	837.1	815.6	792.9	782.7	769.0	760.9	755.9	747.4
25°	876.8	846.7	816.6	790.5	768.5	748.4	734.9	724.3	715.3	711.3	705.8
27.5°	831.4	801.5	772.5	742.9	717.8	703.3	692.5	684.6	679.3	674.0	671.6
30°	802.6	771.5	740.4	712.8	689.8	675.2	665.2	659.7	655.6	653.2	650.6
32.5°	773.3	742.6	709.9	684.8	664.1	651.2	643.6	638.0	636.0	635.1	634.2
35°	726.3	695.3	665.2	642.6	623.1	618.1	611.5	608.6	607.6	611.1	612.6
37.5°	680.9	652.1	624.4	602.6	589.7	582.4	580.1	580.3	583.9	587.0	590.6
40°	651.7	623.6	597.6	578.4	566.5	561.9	560.9	563.5	567.4	571.0	575.0
42.5°	623.2	595.5	571.8	554.0	545.6	541.5	542.1	544.6	550.2	554.5	560.5
45°	579.0	555.9	532.8	518.3	511.3	512.3	512.3	516.8	522.4	528.9	535.4
47.5°	537.3	514.2	495.1	483.0	479.3	478.4	481.3	487.1	495.0	503.1	512.2
50°	509.3	487.2	470.7	459.7	455.6	457.1	461.2	466.7	476.2	486.3	495.8
52.5°	480.8	460.8	445.4	435.2	432.4	435.1	439.1	447.8	456.2	467.0	478.5
55°	436.6	419.5	407.6	400.0	399.0	400.5	405.0	414.5	426.6	440.2	451.2
57.5°	392.6	378.3	367.3	362.1	362.6	364.0	371.5	382.8	395.6	410.0	424.2
60°	363.0	349.9	340.9	336.9	337.3	340.4	349.4	360.0	376.0	390.0	405.0
62.5°	334.9	323.4	314.8	311.2	310.5	317.1	325.7	336.7	352.7	368.3	384.6
65°	289.7	280.7	273.7	271.7	273.2	278.2	289.3	303.8	317.4	333.8	350.9
67.5°	245.6	238.2	233.4	234.3	236.1	243.6	252.8	265.2	280.6	297.7	314.6
70°	217.5	210.6	206.5	207.0	210.0	219.0	227.1	239.6	256.2	273.7	287.8
72.5°	188.7	184.1	180.5	182.6	185.6	191.8	201.8	214.3	228.8	245.2	260.0
75°	144.9	144.9	142.9	144.4	148.9	154.9	162.4	175.4	190.0	203.0	215.1
77.5°	107.4	106.4	107.6	109.5	112.1	119.2	127.8	137.1	148.1	161.1	171.1
80°	82.2	82.8	85.2	88.2	89.3	94.7	103.8	112.3	120.8	131.9	141.4
82.5°	61.7	62.3	63.5	67.4	68.3	74.3	80.1	88.6	96.3	103.8	111.7
85°	33.6	33.6	36.1	37.6	40.1	44.1	47.6	52.6	59.7	64.7	72.2
87.5°	16.5	17.1	19.1	20.5	22.1	24.7	25.9	30.6	32.6	35.1	38.9
90°	18.2	21.2	23.7	26.2	28.7	31.3	33.2	35.1	36.9	38.8	40.2
92.5°	18.7	20.0	22.5	25.1	27.6	30.2	32.0	33.9	35.8	37.7	38.7
95°	35.3	30.0	30.3	30.6	30.9	31.3	33.2	35.1	36.9	38.8	40.0
97.5°	192.8	178.5	143.3	108.0	72.8	37.5	37.7	37.9	38.1	38.3	38.5
100°	255.8	236.9	193.3	149.7	106.1	62.6	57.2	51.8	46.5	41.1	38.5
102.5°	324.8	324.0	318.4	312.7	307.0	301.3	243.4	185.5	127.5	69.7	40.7
105°	435.5	437.2	438.8	440.4	441.9	443.5	446.3	449.1	452.0	454.9	450.5
107.5°	542.8	544.3	546.5	548.7	550.7	552.9	554.3	555.7	557.1	558.5	559.8
110°	617.8	619.3	621.1	623.0	624.9	626.8	627.5	628.1	628.8	629.3	630.2



TEST NUMBER: P332799-830

CATALOG NUMBER: S124DIW-S795D1560U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	693.6	694.9	695.8	696.7	697.6	698.5	698.3	698.2	698.0	698.0	698.5
115°	802.6	803.0	802.6	802.3	802.0	801.6	802.3	803.0	803.5	804.2	804.6
117.5°	904.8	905.8	906.4	907.2	907.9	908.5	908.4	908.3	908.1	908.0	908.0
120°	973.0	973.5	973.2	972.9	972.5	972.2	972.9	973.5	974.1	974.8	974.8
122.5°	1034.7	1035.3	1035.8	1036.1	1036.6	1037.1	1037.5	1037.8	1038.2	1038.6	1038.4
125°	1127.9	1128.2	1127.7	1127.0	1126.3	1125.8	1126.7	1127.7	1128.6	1129.5	1130.2
127.5°	1210.6	1211.4	1213.0	1214.4	1215.8	1217.3	1217.1	1216.9	1216.7	1216.5	1216.3
130°	1266.3	1267.0	1267.9	1268.9	1269.8	1270.7	1271.0	1271.4	1271.7	1272.0	1272.1
132.5°	1318.5	1319.4	1320.6	1321.7	1323.0	1324.2	1324.5	1324.8	1325.1	1325.4	1325.5
135°	1391.7	1392.1	1393.5	1394.7	1396.0	1397.2	1397.9	1398.5	1399.1	1399.8	1400.4
137.5°	1461.4	1462.2	1463.6	1465.0	1466.3	1467.7	1468.4	1469.1	1469.8	1470.6	1470.7
140°	1507.8	1508.4	1509.0	1509.7	1510.3	1510.9	1511.9	1512.9	1513.8	1514.8	1515.3
142.5°	1549.6	1550.4	1550.8	1551.1	1551.5	1551.9	1552.6	1553.3	1554.0	1554.6	1555.0
145°	1610.0	1610.4	1610.4	1610.4	1610.4	1610.4	1610.7	1611.1	1611.4	1611.7	1612.2
147.5°	1661.9	1662.6	1662.3	1662.0	1661.6	1661.3	1661.6	1661.8	1662.1	1662.4	1662.6
150°	1695.1	1695.5	1695.3	1695.0	1694.6	1694.3	1694.3	1694.3	1694.3	1694.3	1694.5
152.5°	1723.6	1723.9	1723.3	1722.7	1722.1	1721.6	1722.1	1722.6	1723.1	1723.6	1723.7
155°	1762.4	1762.1	1761.1	1760.2	1759.3	1758.2	1759.5	1760.8	1762.1	1763.3	1763.5
157.5°	1795.4	1794.7	1793.6	1792.5	1791.5	1790.4	1792.1	1793.7	1795.4	1797.0	1797.0
160°	1812.8	1812.1	1811.8	1811.5	1811.2	1810.8	1812.8	1814.7	1816.6	1818.4	1818.4
162.5°	1829.9	1829.2	1828.8	1828.5	1828.2	1827.9	1829.8	1831.7	1833.6	1835.5	1835.3
165°	1851.4	1850.7	1850.7	1850.7	1850.7	1850.7	1853.1	1855.7	1858.2	1860.8	1860.6
167.5°	1869.3	1868.5	1868.3	1868.1	1867.9	1867.7	1870.5	1873.3	1876.0	1878.9	1878.7
170°	1878.6	1877.8	1878.1	1878.5	1878.8	1879.1	1881.6	1884.1	1886.7	1889.2	1888.9
172.5°	1885.5	1884.6	1885.0	1885.3	1885.6	1885.9	1888.4	1890.9	1893.5	1896.0	1895.5
175°	1892.8	1892.1	1892.3	1892.6	1893.0	1893.3	1896.1	1898.9	1901.9	1904.7	1904.2
177.5°	1896.8	1896.1	1896.6	1897.1	1897.6	1898.1	1900.2	1902.1	1904.2	1906.2	1905.7
180°	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4



TEST NUMBER: P332799-830

CATALOG NUMBER: S124DIW-S795D1560U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1
2.5°	1153.1	1152.4	1149.5	1149.1	1149.5	1152.4	1153.1	1154.0	1155.2	1159.1	1154.3
5°	1065.3	1062.7	1061.2	1066.8	1061.2	1062.7	1065.3	1068.2	1073.3	1073.7	1078.7
7.5°	998.9	996.9	992.5	991.2	992.5	996.9	998.9	1000.8	1005.8	1010.1	1017.5
10°	956.4	954.4	950.5	949.4	950.5	954.4	956.4	961.5	966.5	971.9	977.0
12.5°	915.5	911.5	910.7	911.7	910.7	911.5	915.5	922.2	935.2	935.1	936.1
15°	861.2	859.2	853.7	855.2	853.7	859.2	861.2	867.7	873.7	881.3	888.7
17.5°	807.7	805.2	798.5	804.5	798.5	805.2	807.7	811.2	818.9	829.5	840.8
20°	774.0	770.0	766.5	765.9	766.5	770.0	774.0	777.5	786.0	795.0	803.5
22.5°	741.9	738.3	738.0	734.7	738.0	738.3	741.9	747.4	755.9	760.9	769.0
25°	701.8	698.3	697.3	694.7	697.3	698.3	701.8	705.8	711.3	715.3	724.3
27.5°	671.0	669.3	667.5	668.3	667.5	669.3	671.0	671.6	674.0	679.3	684.6
30°	652.1	651.7	650.6	650.6	650.6	651.7	652.1	650.6	653.2	655.6	659.7
32.5°	636.5	636.4	637.1	637.1	637.1	636.4	636.5	634.2	635.1	636.0	638.0
35°	614.5	616.0	617.1	615.6	617.1	616.0	614.5	612.6	611.1	607.6	608.6
37.5°	594.7	596.3	597.7	599.4	597.7	596.3	594.7	590.6	587.0	583.9	580.3
40°	579.5	583.0	584.0	586.5	584.0	583.0	579.5	575.0	571.0	567.4	563.5
42.5°	565.1	568.9	571.6	572.0	571.6	568.9	565.1	560.5	554.5	550.2	544.6
45°	542.9	546.9	550.4	550.4	550.4	546.9	542.9	535.4	528.9	522.4	516.8
47.5°	519.9	525.8	529.2	530.2	529.2	525.8	519.9	512.2	503.1	495.0	487.1
50°	504.3	511.3	514.8	517.4	514.8	511.3	504.3	495.8	486.3	476.2	466.7
52.5°	489.1	496.1	500.8	502.1	500.8	496.1	489.1	478.5	467.0	456.2	447.8
55°	462.7	472.7	478.2	480.2	478.2	472.7	462.7	451.2	440.2	426.6	414.5
57.5°	437.8	447.0	453.5	455.0	453.5	447.0	437.8	424.2	410.0	395.6	382.8
60°	418.6	428.6	436.6	438.1	436.6	428.6	418.6	405.0	390.0	376.0	360.0
62.5°	398.9	409.3	416.6	420.5	416.6	409.3	398.9	384.6	368.3	352.7	336.7
65°	365.0	375.4	382.5	384.0	382.5	375.4	365.0	350.9	333.8	317.4	303.8
67.5°	327.8	338.4	343.0	345.9	343.0	338.4	327.8	314.6	297.7	280.6	265.2
70°	301.8	310.3	315.3	317.8	315.3	310.3	301.8	287.8	273.7	256.2	239.6
72.5°	272.1	281.0	286.8	287.3	286.8	281.0	272.1	260.0	245.2	228.8	214.3
75°	226.6	234.6	237.6	237.6	237.6	234.6	226.6	215.1	203.0	190.0	175.4
77.5°	179.4	183.5	187.3	188.0	187.3	183.5	179.4	171.1	161.1	148.1	137.1
80°	148.9	151.4	154.4	154.4	154.4	151.4	148.9	141.4	131.9	120.8	112.3
82.5°	117.6	119.7	122.7	122.3	122.7	119.7	117.6	111.7	103.8	96.3	88.6
85°	71.2	75.7	75.2	74.2	75.2	75.7	71.2	72.2	64.7	59.7	52.6
87.5°	40.2	40.7	42.1	43.0	42.1	40.7	40.2	38.9	35.1	32.6	30.6
90°	40.7	41.4	42.0	42.6	42.0	41.4	40.7	40.2	38.8	36.9	35.1
92.5°	38.8	39.0	39.1	39.2	39.1	39.0	38.8	38.7	37.7	35.8	33.9
95°	40.2	40.6	40.9	41.2	40.9	40.6	40.2	40.0	38.8	36.9	35.1
97.5°	38.8	39.2	39.5	39.8	39.5	39.2	38.8	38.5	38.3	38.1	37.9
100°	38.8	39.2	39.5	39.8	39.5	39.2	38.8	38.5	41.1	46.5	51.8
102.5°	40.7	40.8	40.9	40.9	40.9	40.8	40.7	40.7	69.7	127.5	185.5
105°	439.2	427.8	416.5	405.1	416.5	427.8	439.2	450.5	454.9	452.0	449.1
107.5°	561.0	562.1	563.4	564.6	563.4	562.1	561.0	559.8	558.5	557.1	555.7
110°	631.1	632.1	633.0	634.0	633.0	632.1	631.1	630.2	629.3	628.8	628.1



TEST NUMBER: P332799-830

CATALOG NUMBER: S124DIW-S795D1560U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	699.7	700.9	702.1	703.3	702.1	700.9	699.7	698.5	698.0	698.0	698.2
115°	804.6	804.6	804.6	804.6	804.6	804.6	804.6	804.6	804.2	803.5	803.0
117.5°	907.8	907.7	907.6	907.4	907.6	907.7	907.8	908.0	908.0	908.1	908.3
120°	974.1	973.5	972.9	972.2	972.9	973.5	974.1	974.8	974.8	974.1	973.5
122.5°	1037.8	1037.2	1036.5	1035.9	1036.5	1037.2	1037.8	1038.4	1038.6	1038.2	1037.8
125°	1130.5	1130.8	1131.1	1131.4	1131.1	1130.8	1130.5	1130.2	1129.5	1128.6	1127.7
127.5°	1216.1	1215.8	1215.5	1215.3	1215.5	1215.8	1216.1	1216.3	1216.5	1216.7	1216.9
130°	1272.1	1272.1	1272.1	1272.1	1272.1	1272.1	1272.1	1272.1	1272.0	1271.7	1271.4
132.5°	1325.2	1324.9	1324.7	1324.5	1324.7	1324.9	1325.2	1325.5	1325.4	1325.1	1324.8
135°	1401.0	1401.7	1402.3	1402.9	1402.3	1401.7	1401.0	1400.4	1399.8	1399.1	1398.5
137.5°	1470.6	1470.4	1470.2	1470.0	1470.2	1470.4	1470.6	1470.7	1470.6	1469.8	1469.1
140°	1515.7	1516.0	1516.3	1516.6	1516.3	1516.0	1515.7	1515.3	1514.8	1513.8	1512.9
142.5°	1555.1	1555.2	1555.2	1555.3	1555.2	1555.2	1555.1	1555.0	1554.6	1554.0	1553.3
145°	1612.8	1613.4	1614.1	1614.7	1614.1	1613.4	1612.8	1612.2	1611.7	1611.4	1611.1
147.5°	1662.9	1663.2	1663.6	1663.9	1663.6	1663.2	1662.9	1662.6	1662.4	1662.1	1661.8
150°	1694.8	1695.1	1695.4	1695.7	1695.4	1695.1	1694.8	1694.5	1694.3	1694.3	1694.3
152.5°	1723.5	1723.3	1723.2	1723.0	1723.2	1723.3	1723.5	1723.7	1723.6	1723.1	1722.6
155°	1762.6	1761.6	1760.7	1759.7	1760.7	1761.6	1762.6	1763.5	1763.3	1762.1	1760.8
157.5°	1795.4	1793.7	1792.1	1790.4	1792.1	1793.7	1795.4	1797.0	1797.0	1795.4	1793.7
160°	1816.6	1814.7	1812.8	1810.8	1812.8	1814.7	1816.6	1818.4	1818.4	1816.6	1814.7
162.5°	1833.2	1831.1	1828.9	1826.7	1828.9	1831.1	1833.2	1835.3	1835.5	1833.6	1831.7
165°	1857.8	1854.9	1852.1	1849.3	1852.1	1854.9	1857.8	1860.6	1860.8	1858.2	1855.7
167.5°	1875.5	1872.4	1869.2	1866.0	1869.2	1872.4	1875.5	1878.7	1878.9	1876.0	1873.3
170°	1885.7	1882.5	1879.4	1876.2	1879.4	1882.5	1885.7	1888.9	1889.2	1886.7	1884.1
172.5°	1892.2	1888.8	1885.4	1881.9	1885.4	1888.8	1892.2	1895.5	1896.0	1893.5	1890.9
175°	1900.4	1896.6	1892.8	1889.0	1892.8	1896.6	1900.4	1904.2	1904.7	1901.9	1898.9
177.5°	1902.7	1899.6	1896.6	1893.6	1896.6	1899.6	1902.7	1905.7	1906.2	1904.2	1902.1
180°	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4



TEST NUMBER: P332799-830

CATALOG NUMBER: S124DIW-S795D1560U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1
2.5°	1156.8	1158.4	1164.8	1170.8	1178.0	1183.3	1186.8	1190.8	1199.3	1206.1	1212.5
5°	1083.7	1086.3	1099.3	1108.3	1123.9	1137.4	1147.9	1159.4	1173.0	1191.6	1208.6
7.5°	1019.5	1028.8	1043.0	1057.7	1073.6	1091.3	1106.7	1124.1	1147.5	1172.9	1199.2
10°	983.0	993.5	1008.6	1025.6	1040.7	1061.2	1080.2	1100.8	1127.4	1158.5	1189.6
12.5°	946.5	963.8	975.2	995.5	1011.8	1028.7	1049.0	1075.9	1106.9	1139.6	1177.1
15°	900.8	910.3	932.4	943.4	966.5	992.5	1012.6	1039.6	1069.7	1112.9	1155.0
17.5°	848.1	860.6	878.2	899.2	925.7	946.0	971.0	998.8	1036.7	1079.6	1132.3
20°	813.6	824.1	845.6	868.7	896.8	918.3	944.9	971.9	1011.1	1056.7	1111.8
22.5°	782.7	792.9	815.6	837.1	864.3	890.7	918.4	949.9	987.4	1035.5	1091.7
25°	734.9	748.4	768.5	790.5	816.6	846.7	876.8	904.8	944.9	995.5	1055.7
27.5°	692.5	703.3	717.8	742.9	772.5	801.5	831.4	866.7	905.2	958.8	1021.2
30°	665.2	675.2	689.8	712.8	740.4	771.5	802.6	836.6	876.8	929.9	993.5
32.5°	643.6	651.2	664.1	684.8	709.9	742.6	773.3	808.6	850.6	903.1	965.1
35°	611.5	618.1	623.1	642.6	665.2	695.3	726.3	763.9	804.6	854.2	916.3
37.5°	580.1	582.4	589.7	602.6	624.4	652.1	680.9	717.9	759.5	809.9	866.0
40°	560.9	561.9	566.5	578.4	597.6	623.6	651.7	688.2	727.8	775.5	831.1
42.5°	542.1	541.5	545.6	554.0	571.8	595.5	623.2	656.6	696.2	740.2	792.6
45°	512.3	512.3	511.3	518.3	532.8	555.9	579.0	611.1	644.1	687.3	731.4
47.5°	481.3	478.4	479.3	483.0	495.1	514.2	537.3	563.6	592.9	629.3	668.0
50°	461.2	457.1	455.6	459.7	470.7	487.2	509.3	532.3	560.0	592.0	625.1
52.5°	439.1	435.1	432.4	435.2	445.4	460.8	480.8	501.1	525.8	552.0	580.6
55°	405.0	400.5	399.0	400.0	407.6	419.5	436.6	455.2	473.7	495.3	515.3
57.5°	371.5	364.0	362.6	362.1	367.3	378.3	392.6	408.7	422.2	435.2	456.6
60°	349.4	340.4	337.3	336.9	340.9	349.9	363.0	379.0	388.5	397.5	416.0
62.5°	325.7	317.1	310.5	311.2	314.8	323.4	334.9	346.5	352.8	362.6	375.1
65°	289.3	278.2	273.2	271.7	273.7	280.7	289.7	297.3	304.3	308.3	320.3
67.5°	252.8	243.6	236.1	234.3	233.4	238.2	245.6	250.2	255.1	258.6	265.8
70°	227.1	219.0	210.0	207.0	206.5	210.6	217.5	218.0	225.1	226.6	234.1
72.5°	201.8	191.8	185.6	182.6	180.5	184.1	188.7	190.0	193.8	196.5	200.4
75°	162.4	154.9	148.9	144.4	142.9	144.9	144.9	147.4	149.9	151.4	155.9
77.5°	127.8	119.2	112.1	109.5	107.6	106.4	107.4	109.0	107.7	110.4	111.4
80°	103.8	94.7	89.3	88.2	85.2	82.8	82.2	83.7	81.7	82.8	85.7
82.5°	80.1	74.3	68.3	67.4	63.5	62.3	61.7	60.9	60.9	60.7	61.3
85°	47.6	44.1	40.1	37.6	36.1	33.6	33.6	32.6	31.6	30.5	31.1
87.5°	25.9	24.7	22.1	20.5	19.1	17.1	16.5	14.6	13.5	12.3	11.3
90°	33.2	31.3	28.7	26.2	23.7	21.2	18.2	14.7	11.2	7.7	4.2
92.5°	32.0	30.2	27.6	25.1	22.5	20.0	18.7	18.5	18.3	18.1	17.9
95°	33.2	31.3	30.9	30.6	30.3	30.0	35.3	46.0	56.7	67.4	78.1
97.5°	37.7	37.5	72.8	108.0	143.3	178.5	192.8	186.2	179.4	172.7	166.0
100°	57.2	62.6	106.1	149.7	193.3	236.9	255.8	250.2	244.5	238.8	233.1
102.5°	243.4	301.3	307.0	312.7	318.4	324.0	324.8	320.7	316.5	312.4	308.1
105°	446.3	443.5	441.9	440.4	438.8	437.2	435.5	433.6	431.6	429.7	427.8
107.5°	554.3	552.9	550.7	548.7	546.5	544.3	542.8	541.9	540.9	540.0	538.9
110°	627.5	626.8	624.9	623.0	621.1	619.3	617.8	616.9	616.0	615.0	614.1



TEST NUMBER: P332799-830

CATALOG NUMBER: S124DIW-S795D1560U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	698.3	698.5	697.6	696.7	695.8	694.9	693.6	691.9	690.2	688.5	686.8
115°	802.3	801.6	802.0	802.3	802.6	803.0	802.6	801.6	800.7	799.7	798.8
117.5°	908.4	908.5	907.9	907.2	906.4	905.8	904.8	903.5	902.3	901.0	899.8
120°	972.9	972.2	972.5	972.9	973.2	973.5	973.0	971.8	970.5	969.2	968.0
122.5°	1037.5	1037.1	1036.6	1036.1	1035.8	1035.3	1034.7	1033.9	1033.1	1032.4	1031.6
125°	1126.7	1125.8	1126.3	1127.0	1127.7	1128.2	1127.9	1126.7	1125.4	1124.2	1122.9
127.5°	1217.1	1217.3	1215.8	1214.4	1213.0	1211.4	1210.6	1210.2	1209.9	1209.7	1209.3
130°	1271.0	1270.7	1269.8	1268.9	1267.9	1267.0	1266.3	1266.0	1265.6	1265.4	1265.1
132.5°	1324.5	1324.2	1323.0	1321.7	1320.6	1319.4	1318.5	1318.0	1317.4	1316.7	1316.2
135°	1397.9	1397.2	1396.0	1394.7	1393.5	1392.1	1391.7	1392.0	1392.3	1392.6	1393.0
137.5°	1468.4	1467.7	1466.3	1465.0	1463.6	1462.2	1461.4	1461.3	1461.1	1461.0	1460.9
140°	1511.9	1510.9	1510.3	1509.7	1509.0	1508.4	1507.8	1507.1	1506.6	1505.9	1505.2
142.5°	1552.6	1551.9	1551.5	1551.1	1550.8	1550.4	1549.6	1548.5	1547.4	1546.1	1545.0
145°	1610.7	1610.4	1610.4	1610.4	1610.4	1610.4	1610.0	1609.0	1608.1	1607.1	1606.2
147.5°	1661.6	1661.3	1661.6	1662.0	1662.3	1662.6	1661.9	1660.1	1658.3	1656.5	1654.8
150°	1694.3	1694.3	1694.6	1695.0	1695.3	1695.5	1695.1	1693.8	1692.5	1691.3	1690.1
152.5°	1722.1	1721.6	1722.1	1722.7	1723.3	1723.9	1723.6	1722.6	1721.6	1720.6	1719.6
155°	1759.5	1758.2	1759.3	1760.2	1761.1	1762.1	1762.4	1762.1	1761.7	1761.4	1761.1
157.5°	1792.1	1790.4	1791.5	1792.5	1793.6	1794.7	1795.4	1795.5	1795.7	1795.9	1796.1
160°	1812.8	1810.8	1811.2	1811.5	1811.8	1812.1	1812.8	1813.7	1814.7	1815.6	1816.6
162.5°	1829.8	1827.9	1828.2	1828.5	1828.8	1829.2	1829.9	1831.2	1832.3	1833.5	1834.8
165°	1853.1	1850.7	1850.7	1850.7	1850.7	1850.7	1851.4	1853.0	1854.6	1856.1	1857.8
167.5°	1870.5	1867.7	1867.9	1868.1	1868.3	1868.5	1869.3	1871.0	1872.6	1874.3	1875.9
170°	1881.6	1879.1	1878.8	1878.5	1878.1	1877.8	1878.6	1880.5	1882.4	1884.3	1886.2
172.5°	1888.4	1885.9	1885.6	1885.3	1885.0	1884.6	1885.5	1887.3	1889.2	1891.1	1893.0
175°	1896.1	1893.3	1893.0	1892.6	1892.3	1892.1	1892.8	1894.7	1896.6	1898.5	1900.4
177.5°	1900.2	1898.1	1897.6	1897.1	1896.6	1896.1	1896.8	1898.5	1900.3	1902.1	1903.8
180°	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4



TEST NUMBER: P332799-830

CATALOG NUMBER: S124DIW-S795D1560U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1
2.5°	1218.1	1222.1	1227.4	1236.1	1239.3	1243.4	1249.0	1248.6	1250.2	1256.2	1269.0
5°	1222.7	1238.1	1253.2	1271.2	1290.3	1302.8	1319.8	1330.4	1341.0	1354.4	1377.5
7.5°	1224.5	1249.1	1276.7	1308.3	1336.5	1369.0	1394.4	1418.2	1439.7	1468.4	1495.8
10°	1221.6	1254.7	1290.3	1330.4	1373.0	1409.1	1441.7	1478.8	1510.3	1544.9	1576.0
12.5°	1216.4	1256.3	1303.9	1348.9	1398.6	1452.0	1492.6	1530.1	1572.2	1611.9	1659.8
15°	1204.6	1259.2	1314.8	1374.0	1440.7	1502.3	1560.9	1609.6	1654.7	1714.4	1777.1
17.5°	1189.6	1248.5	1318.7	1390.3	1459.9	1530.4	1603.0	1676.1	1733.1	1807.1	1856.1
20°	1175.5	1243.7	1315.9	1401.1	1470.7	1558.5	1630.7	1701.4	1779.5	1853.2	1911.9
22.5°	1155.8	1230.5	1307.0	1391.9	1483.6	1571.3	1654.7	1731.5	1809.6	1889.7	1960.8
25°	1130.9	1198.5	1289.3	1385.5	1476.8	1572.0	1667.7	1764.0	1848.2	1933.0	1999.1
27.5°	1088.4	1173.8	1258.3	1357.6	1459.1	1566.8	1669.1	1769.9	1858.1	1927.8	1968.8
30°	1066.8	1140.9	1232.7	1332.4	1442.2	1558.0	1664.7	1763.5	1845.7	1901.4	1917.9
32.5°	1034.6	1111.3	1201.0	1304.3	1420.5	1539.5	1650.7	1743.9	1812.4	1841.6	1821.7
35°	987.0	1056.2	1146.9	1252.7	1373.5	1500.3	1610.1	1688.8	1723.9	1696.3	1627.7
37.5°	929.9	998.4	1089.6	1193.4	1318.4	1447.4	1546.6	1603.3	1591.7	1523.1	1420.7
40°	889.8	953.9	1040.7	1152.9	1274.8	1404.1	1491.3	1521.9	1489.8	1391.6	1282.8
42.5°	845.3	907.9	994.9	1103.2	1232.3	1351.5	1427.6	1430.0	1376.3	1258.9	1149.6
45°	777.5	837.2	919.4	1032.2	1151.4	1263.8	1313.8	1289.3	1190.1	1076.8	967.0
47.5°	710.6	762.3	843.4	950.5	1063.8	1158.3	1183.1	1138.9	1033.1	923.1	821.4
50°	661.7	713.8	790.0	892.3	1001.5	1083.3	1095.3	1036.6	932.9	822.1	742.4
52.5°	614.7	666.5	739.9	834.5	934.6	1008.2	1008.7	940.8	837.4	738.7	664.6
55°	545.9	592.5	658.6	743.4	832.6	890.2	876.3	806.1	716.3	630.7	565.9
57.5°	479.6	520.1	581.1	651.8	730.4	777.9	754.6	687.0	606.9	534.2	485.2
60°	436.6	475.2	527.4	594.0	660.2	697.3	675.2	614.1	540.4	481.7	439.1
62.5°	394.9	427.5	477.6	535.5	596.8	624.3	604.6	544.3	480.6	427.6	393.0
65°	335.8	362.4	402.6	452.1	496.8	520.3	503.8	447.6	399.0	360.9	333.4
67.5°	280.7	301.4	331.9	371.6	409.5	422.3	407.3	368.2	327.0	296.4	277.0
70°	242.6	262.2	287.8	318.3	351.4	365.0	349.9	318.8	285.2	257.1	238.1
72.5°	209.3	224.5	246.0	272.2	298.0	311.6	301.3	271.5	243.1	222.3	206.0
75°	159.4	172.5	187.5	206.0	226.1	235.1	226.1	205.6	186.0	170.4	158.9
77.5°	115.9	122.9	134.5	148.4	160.9	167.9	160.0	146.1	134.1	123.5	117.8
80°	88.2	93.2	101.2	112.3	120.8	127.3	122.3	110.7	101.2	94.3	91.7
82.5°	64.2	67.6	72.8	81.0	86.7	90.0	87.8	79.5	75.6	69.4	66.8
85°	31.6	33.6	37.1	39.6	44.6	45.1	45.6	42.1	38.6	37.1	35.1
87.5°	12.3	13.5	15.4	17.2	19.5	20.4	20.5	21.0	19.9	19.9	18.7
90°	7.7	11.2	14.7	18.2	21.2	23.7	26.2	28.7	31.3	33.2	35.1
92.5°	18.1	18.3	18.5	18.7	20.0	22.5	25.1	27.6	30.2	32.0	33.9
95°	67.4	56.7	46.0	35.3	30.0	30.3	30.6	30.9	31.3	33.2	35.1
97.5°	172.7	179.4	186.2	192.8	178.5	143.3	108.0	72.8	37.5	37.7	37.9
100°	238.8	244.5	250.2	255.8	236.9	193.3	149.7	106.1	62.6	57.2	51.8
102.5°	312.4	316.5	320.7	324.8	324.0	318.4	312.7	307.0	301.3	243.4	185.5
105°	429.7	431.6	433.6	435.5	437.2	438.8	440.4	441.9	443.5	446.3	449.1
107.5°	540.0	540.9	541.9	542.8	544.3	546.5	548.7	550.7	552.9	554.3	555.7
110°	615.0	616.0	616.9	617.8	619.3	621.1	623.0	624.9	626.8	627.5	628.1



TEST NUMBER: P332799-830

CATALOG NUMBER: S124DIW-S795D1560U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	688.5	690.2	691.9	693.6	694.9	695.8	696.7	697.6	698.5	698.3	698.2
115°	799.7	800.7	801.6	802.6	803.0	802.6	802.3	802.0	801.6	802.3	803.0
117.5°	901.0	902.3	903.5	904.8	905.8	906.4	907.2	907.9	908.5	908.4	908.3
120°	969.2	970.5	971.8	973.0	973.5	973.2	972.9	972.5	972.2	972.9	973.5
122.5°	1032.4	1033.1	1033.9	1034.7	1035.3	1035.8	1036.1	1036.6	1037.1	1037.5	1037.8
125°	1124.2	1125.4	1126.7	1127.9	1128.2	1127.7	1127.0	1126.3	1125.8	1126.7	1127.7
127.5°	1209.7	1209.9	1210.2	1210.6	1211.4	1213.0	1214.4	1215.8	1217.3	1217.1	1216.9
130°	1265.4	1265.6	1266.0	1266.3	1267.0	1267.9	1268.9	1269.8	1270.7	1271.0	1271.4
132.5°	1316.7	1317.4	1318.0	1318.5	1319.4	1320.6	1321.7	1323.0	1324.2	1324.5	1324.8
135°	1392.6	1392.3	1392.0	1391.7	1392.1	1393.5	1394.7	1396.0	1397.2	1397.9	1398.5
137.5°	1461.0	1461.1	1461.3	1461.4	1462.2	1463.6	1465.0	1466.3	1467.7	1468.4	1469.1
140°	1505.9	1506.6	1507.1	1507.8	1508.4	1509.0	1509.7	1510.3	1510.9	1511.9	1512.9
142.5°	1546.1	1547.4	1548.5	1549.6	1550.4	1550.8	1551.1	1551.5	1551.9	1552.6	1553.3
145°	1607.1	1608.1	1609.0	1610.0	1610.4	1610.4	1610.4	1610.4	1610.4	1610.7	1611.1
147.5°	1656.5	1658.3	1660.1	1661.9	1662.6	1662.3	1662.0	1661.6	1661.3	1661.6	1661.8
150°	1691.3	1692.5	1693.8	1695.1	1695.5	1695.3	1695.0	1694.6	1694.3	1694.3	1694.3
152.5°	1720.6	1721.6	1722.6	1723.6	1723.9	1723.3	1722.7	1722.1	1721.6	1722.1	1722.6
155°	1761.4	1761.7	1762.1	1762.4	1762.1	1761.1	1760.2	1759.3	1758.2	1759.5	1760.8
157.5°	1795.9	1795.7	1795.5	1795.4	1794.7	1793.6	1792.5	1791.5	1790.4	1792.1	1793.7
160°	1815.6	1814.7	1813.7	1812.8	1812.1	1811.8	1811.5	1811.2	1810.8	1812.8	1814.7
162.5°	1833.5	1832.3	1831.2	1829.9	1829.2	1828.8	1828.5	1828.2	1827.9	1829.8	1831.7
165°	1856.1	1854.6	1853.0	1851.4	1850.7	1850.7	1850.7	1850.7	1850.7	1853.1	1855.7
167.5°	1874.3	1872.6	1871.0	1869.3	1868.5	1868.3	1868.1	1867.9	1867.7	1870.5	1873.3
170°	1884.3	1882.4	1880.5	1878.6	1877.8	1878.1	1878.5	1878.8	1879.1	1881.6	1884.1
172.5°	1891.1	1889.2	1887.3	1885.5	1884.6	1885.0	1885.3	1885.6	1885.9	1888.4	1890.9
175°	1898.5	1896.6	1894.7	1892.8	1892.1	1892.3	1892.6	1893.0	1893.3	1896.1	1898.9
177.5°	1902.1	1900.3	1898.5	1896.8	1896.1	1896.6	1897.1	1897.6	1898.1	1900.2	1902.1
180°	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4



TEST NUMBER: P332799-830

CATALOG NUMBER: S124DIW-S795D1560U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1
2.5°	1275.4	1276.3	1279.9	1282.7	1283.5	1287.5	1287.9
5°	1387.5	1396.1	1412.6	1414.1	1416.6	1429.6	1419.7
7.5°	1518.9	1540.5	1555.0	1567.7	1572.3	1578.0	1576.9
10°	1603.1	1635.2	1651.2	1676.8	1677.8	1684.3	1680.3
12.5°	1687.7	1725.0	1754.3	1759.0	1780.5	1783.8	1789.4
15°	1807.6	1847.2	1887.8	1902.3	1931.9	1939.0	1950.0
17.5°	1920.3	1960.8	1989.2	2026.8	2039.0	2055.2	2044.2
20°	1982.1	2026.2	2062.3	2091.9	2104.4	2113.4	2112.4
22.5°	2019.4	2063.9	2093.1	2115.5	2127.2	2131.1	2130.8
25°	2042.7	2068.3	2077.3	2085.8	2072.8	2068.3	2070.3
27.5°	1977.7	1971.1	1947.6	1916.7	1884.6	1859.2	1845.3
30°	1888.3	1849.3	1813.6	1751.4	1719.4	1700.3	1683.3
32.5°	1761.6	1699.7	1631.2	1574.2	1537.8	1509.5	1505.2
35°	1544.5	1451.2	1367.5	1297.8	1261.7	1231.1	1224.1
37.5°	1313.1	1216.2	1140.9	1079.5	1040.7	1019.1	998.9
40°	1159.4	1076.3	1002.0	949.9	920.4	904.8	892.3
42.5°	1041.1	965.2	891.4	851.7	824.9	815.4	808.0
45°	877.7	807.1	755.9	725.9	710.3	694.3	686.7
47.5°	746.9	689.4	655.6	630.1	613.5	604.0	599.2
50°	672.7	625.6	595.5	576.0	560.9	553.4	549.4
52.5°	606.9	568.3	543.0	527.4	517.3	511.7	510.1
55°	522.8	493.2	477.2	463.7	456.2	451.2	449.1
57.5°	454.5	431.7	418.7	407.6	404.6	400.4	399.0
60°	409.5	392.0	381.0	373.4	371.0	365.9	366.9
62.5°	369.9	355.5	346.1	341.8	338.5	334.2	335.6
65°	312.8	302.3	297.3	293.2	289.3	286.7	288.7
67.5°	262.5	255.2	248.5	246.1	244.1	243.7	241.6
70°	229.6	223.6	217.5	216.0	216.0	214.1	213.6
72.5°	197.9	193.5	189.5	188.4	186.8	187.6	185.5
75°	152.9	149.4	147.9	146.4	145.9	145.9	144.4
77.5°	113.0	110.4	108.0	108.0	106.1	105.5	105.3
80°	85.7	84.7	82.8	82.8	81.7	82.2	81.2
82.5°	64.5	63.1	62.7	61.8	60.4	60.5	59.6
85°	34.6	33.1	32.6	31.1	30.1	31.1	30.1
87.5°	19.4	19.4	19.2	18.6	18.3	18.5	17.3
90°	36.9	38.8	40.2	40.7	41.4	42.0	42.6
92.5°	35.8	37.7	38.7	38.8	39.0	39.1	39.2
95°	36.9	38.8	40.0	40.2	40.6	40.9	41.2
97.5°	38.1	38.3	38.5	38.8	39.2	39.5	39.8
100°	46.5	41.1	38.5	38.8	39.2	39.5	39.8
102.5°	127.5	69.7	40.7	40.7	40.8	40.9	40.9
105°	452.0	454.9	450.5	439.2	427.8	416.5	405.1
107.5°	557.1	558.5	559.8	561.0	562.1	563.4	564.6
110°	628.8	629.3	630.2	631.1	632.1	633.0	634.0



TEST NUMBER: P332799-830

CATALOG NUMBER: S124DIW-S795D1560U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	698.0	698.0	698.5	699.7	700.9	702.1	703.3
115°	803.5	804.2	804.6	804.6	804.6	804.6	804.6
117.5°	908.1	908.0	908.0	907.8	907.7	907.6	907.4
120°	974.1	974.8	974.8	974.1	973.5	972.9	972.2
122.5°	1038.2	1038.6	1038.4	1037.8	1037.2	1036.5	1035.9
125°	1128.6	1129.5	1130.2	1130.5	1130.8	1131.1	1131.4
127.5°	1216.7	1216.5	1216.3	1216.1	1215.8	1215.5	1215.3
130°	1271.7	1272.0	1272.1	1272.1	1272.1	1272.1	1272.1
132.5°	1325.1	1325.4	1325.5	1325.2	1324.9	1324.7	1324.5
135°	1399.1	1399.8	1400.4	1401.0	1401.7	1402.3	1402.9
137.5°	1469.8	1470.6	1470.7	1470.6	1470.4	1470.2	1470.0
140°	1513.8	1514.8	1515.3	1515.7	1516.0	1516.3	1516.6
142.5°	1554.0	1554.6	1555.0	1555.1	1555.2	1555.2	1555.3
145°	1611.4	1611.7	1612.2	1612.8	1613.4	1614.1	1614.7
147.5°	1662.1	1662.4	1662.6	1662.9	1663.2	1663.6	1663.9
150°	1694.3	1694.3	1694.5	1694.8	1695.1	1695.4	1695.7
152.5°	1723.1	1723.6	1723.7	1723.5	1723.3	1723.2	1723.0
155°	1762.1	1763.3	1763.5	1762.6	1761.6	1760.7	1759.7
157.5°	1795.4	1797.0	1797.0	1795.4	1793.7	1792.1	1790.4
160°	1816.6	1818.4	1818.4	1816.6	1814.7	1812.8	1810.8
162.5°	1833.6	1835.5	1835.3	1833.2	1831.1	1828.9	1826.7
165°	1858.2	1860.8	1860.6	1857.8	1854.9	1852.1	1849.3
167.5°	1876.0	1878.9	1878.7	1875.5	1872.4	1869.2	1866.0
170°	1886.7	1889.2	1888.9	1885.7	1882.5	1879.4	1876.2
172.5°	1893.5	1896.0	1895.5	1892.2	1888.8	1885.4	1881.9
175°	1901.9	1904.7	1904.2	1900.4	1896.6	1892.8	1889.0
177.5°	1904.2	1906.2	1905.7	1902.7	1899.6	1896.6	1893.6
180°	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4

(END OF REPORT)