

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332803-830

Luminaire Tested: **S124DIW-S795D1560U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332803-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S795D1560U830-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1560 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9094.8 lumens
Efficiency: N/A
Efficacy: 133.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 68.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332803-830

CATALOG NUMBER: S124DIW-S795D1560U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332803-830

CATALOG NUMBER: S124DIW-S795D1560U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	43	43	43	35
1	94	90	86	83	85	82	78	76	66	64	62	51	50	48	38	37	36	30
2	86	79	73	68	77	71	66	62	58	54	51	45	42	40	33	32	30	25
3	78	69	62	56	71	63	57	52	51	46	43	40	37	34	29	27	26	21
4	72	61	53	48	65	56	49	44	45	40	36	35	32	29	26	24	22	18
5	66	54	46	41	59	49	43	37	40	35	31	32	28	25	24	21	19	16
6	60	49	41	35	54	44	37	32	36	31	27	29	25	22	21	19	17	14
7	56	44	36	31	50	40	33	28	33	28	24	26	22	19	19	17	15	12
8	52	40	32	27	47	36	30	25	30	25	21	24	20	17	18	15	13	11
9	48	36	29	24	43	33	27	22	27	22	19	22	18	15	16	14	12	10
10	45	33	26	21	41	30	24	20	25	20	17	20	16	14	15	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10101	10101	10101
5°	10131	10009	10083
10°	10067	9928	9977
15°	9947	9787	9812
20°	9784	9613	9620
25°	9600	9413	9386
30°	9374	9177	9093
35°	9140	8932	8814
40°	8896	8652	8495
45°	8643	8379	8218
50°	8361	8133	7882
55°	8058	7817	7562
60°	7753	7463	7237
65°	7412	7125	6837
70°	7027	6675	6413
75°	6441	6129	5973
80°	5732	5500	5360
85°	5011	4826	4733



TEST NUMBER: P332803-830

CATALOG NUMBER: S124DIW-S795D1560U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	117.8	1.3
10°-20°	332.0	3.7
20°-30°	488.6	5.4
30°-40°	568.1	6.2
40°-50°	568.1	6.2
50°-60°	496.9	5.5
60°-70°	369.0	4.1
70°-80°	209.7	2.3
80°-90°	66.0	0.7
90°-100°	65.0	0.7
100°-110°	414.4	4.6
110°-120°	792.8	8.7
120°-130°	1006.4	11.1
130°-140°	1076.8	11.8
140°-150°	1006.9	11.1
150°-160°	812.0	8.9
160°-170°	523.7	5.8
170°-180°	180.5	2.0
0°-30°	938.5	10.3
0°-40°	1506.5	16.6
0°-60°	2571.5	28.3
0°-90°	3216.2	35.4
90°-120°	1272.2	14.0
90°-150°	4362.3	48.0
90°-180°	5879.0	64.6
0°-180°	9094.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1251	1251	1251	1251	1251	
5°	1250	1246	1235	1245	1244	119
15°	1190	1185	1171	1176	1174	335
25°	1078	1070	1057	1057	1054	496
35°	927	920	906	899	894	580
45°	757	749	734	723	720	583
55°	572	569	555	544	537	513
65°	388	383	373	363	358	384
75°	206	202	196	193	192	219
85°	54	54	52	52	51	60
90°	4	20	31	40	43	7
95°	78	33	31	39	41	100
105°	428	436	444	453	405	448
115°	799	803	802	804	805	786
125°	1123	1128	1126	1130	1131	1002
135°	1393	1392	1397	1400	1403	1073
145°	1606	1610	1610	1612	1615	1003
155°	1761	1762	1758	1763	1760	812
165°	1858	1851	1851	1861	1849	525
175°	1900	1892	1893	1904	1889	181
180°	1900	1900	1900	1900	1900	



TEST NUMBER: P332803-830

CATALOG NUMBER: S124DIW-S795D1560U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1251.2	1251.2	1251.2	1251.2	1251.2	1251.2	1251.2	1251.2	1251.2	1251.2	1251.2
2.5°	1254.4	1253.9	1253.3	1252.8	1252.3	1251.0	1249.1	1247.1	1245.1	1243.2	1244.9
5°	1250.2	1249.3	1248.4	1247.5	1246.6	1244.9	1242.5	1240.0	1237.6	1235.1	1237.6
7.5°	1238.6	1237.7	1236.8	1235.9	1235.0	1233.2	1230.5	1227.8	1225.0	1222.3	1224.3
10°	1228.1	1227.3	1226.3	1225.5	1224.6	1222.7	1219.7	1216.9	1214.0	1211.1	1212.9
12.5°	1214.5	1213.6	1212.7	1211.8	1211.0	1208.9	1205.9	1202.8	1199.8	1196.7	1198.6
15°	1190.1	1189.1	1188.3	1187.3	1186.5	1184.4	1181.0	1177.7	1174.3	1171.0	1172.3
17.5°	1160.6	1159.4	1158.3	1157.3	1156.1	1154.0	1150.8	1147.6	1144.4	1141.3	1142.2
20°	1138.9	1137.7	1136.7	1135.6	1134.4	1132.2	1128.9	1125.5	1122.2	1118.9	1119.6
22.5°	1115.7	1114.2	1112.7	1111.3	1109.7	1107.4	1104.0	1100.7	1097.3	1094.0	1095.2
25°	1077.7	1076.2	1074.6	1073.1	1071.5	1069.1	1066.0	1062.9	1059.8	1056.7	1056.9
27.5°	1034.4	1032.8	1031.2	1029.6	1028.0	1025.8	1022.8	1020.0	1017.1	1014.2	1013.6
30°	1005.6	1003.8	1002.0	1000.2	998.4	996.1	993.2	990.3	987.4	984.5	983.6
32.5°	975.1	973.5	971.9	970.3	968.7	966.3	963.3	960.2	957.2	954.0	953.0
35°	927.4	925.8	924.3	922.7	921.1	918.8	915.7	912.6	909.5	906.3	904.7
37.5°	877.0	875.6	874.2	872.8	871.3	868.9	865.6	862.2	858.9	855.5	853.8
40°	844.1	842.4	840.6	838.8	837.0	834.4	831.1	827.7	824.4	821.0	818.9
42.5°	808.9	807.8	806.7	805.7	804.6	802.2	798.5	794.8	791.1	787.4	784.9
45°	757.0	755.4	753.8	752.2	750.7	748.1	744.6	741.0	737.4	733.9	731.4
47.5°	702.6	701.5	700.5	699.4	698.3	696.2	692.9	689.6	686.3	683.0	680.1
50°	665.7	664.8	663.9	663.0	662.1	660.2	657.0	653.9	650.7	647.6	644.5
52.5°	629.6	628.6	627.5	626.4	625.3	623.1	619.8	616.5	613.2	609.9	607.2
55°	572.5	571.7	571.1	570.4	569.8	567.9	564.8	561.7	558.6	555.4	552.7
57.5°	517.9	517.2	516.4	515.7	514.9	512.9	509.9	506.8	503.8	500.7	498.1
60°	480.2	479.1	478.0	476.9	475.8	473.7	470.9	468.0	465.1	462.2	460.1
62.5°	443.4	442.4	441.5	440.5	439.6	437.6	434.5	431.4	428.4	425.3	423.5
65°	388.0	386.9	385.8	384.7	383.5	381.8	379.7	377.4	375.1	373.0	370.7
67.5°	332.2	331.2	330.2	329.1	328.2	326.6	324.4	322.3	320.2	318.0	315.8
70°	297.7	296.2	294.6	293.0	291.5	289.8	288.0	286.3	284.5	282.8	281.0
72.5°	260.9	259.3	257.8	256.2	254.6	253.2	251.8	250.2	248.8	247.4	246.0
75°	206.5	205.4	204.3	203.2	202.1	201.0	199.8	198.7	197.7	196.5	195.6
77.5°	154.6	154.1	153.6	153.2	152.6	151.9	150.9	150.0	148.9	148.0	147.7
80°	123.3	122.6	122.0	121.3	120.6	120.1	119.6	119.2	118.8	118.3	117.8
82.5°	92.8	92.6	92.2	91.9	91.6	91.4	91.3	91.2	91.1	91.0	90.8
85°	54.1	54.1	54.1	54.1	54.1	53.9	53.4	53.1	52.6	52.1	52.1
87.5°	21.7	22.2	22.7	23.3	23.8	24.2	24.5	24.9	25.2	25.5	25.9
90°	4.2	7.7	11.2	14.7	18.2	21.2	23.7	26.2	28.7	31.3	33.2
92.5°	17.9	18.1	18.3	18.5	18.7	20.0	22.5	25.1	27.6	30.2	32.0
95°	78.1	67.4	56.7	46.0	35.3	30.0	30.3	30.6	30.9	31.3	33.2
97.5°	166.0	172.7	179.4	186.2	192.8	178.5	143.3	108.0	72.8	37.5	37.7
100°	233.1	238.8	244.5	250.2	255.8	236.9	193.3	149.7	106.1	62.6	57.2
102.5°	308.1	312.4	316.5	320.7	324.8	324.0	318.4	312.7	307.0	301.3	243.4
105°	427.8	429.7	431.6	433.6	435.5	437.2	438.8	440.4	441.9	443.5	446.3
107.5°	538.9	540.0	540.9	541.9	542.8	544.3	546.5	548.7	550.7	552.9	554.3
110°	614.1	615.0	616.0	616.9	617.8	619.3	621.1	623.0	624.9	626.8	627.5



TEST NUMBER: P332803-830

CATALOG NUMBER: S124DIW-S795D1560U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	686.8	688.5	690.2	691.9	693.6	694.9	695.8	696.7	697.6	698.5	698.3
115°	798.8	799.7	800.7	801.6	802.6	803.0	802.6	802.3	802.0	801.6	802.3
117.5°	899.8	901.0	902.3	903.5	904.8	905.8	906.4	907.2	907.9	908.5	908.4
120°	968.0	969.2	970.5	971.8	973.0	973.5	973.2	972.9	972.5	972.2	972.9
122.5°	1031.6	1032.4	1033.1	1033.9	1034.7	1035.3	1035.8	1036.1	1036.6	1037.1	1037.5
125°	1122.9	1124.2	1125.4	1126.7	1127.9	1128.2	1127.7	1127.0	1126.3	1125.8	1126.7
127.5°	1209.3	1209.7	1209.9	1210.2	1210.6	1211.4	1213.0	1214.4	1215.8	1217.3	1217.1
130°	1265.1	1265.4	1265.6	1266.0	1266.3	1267.0	1267.9	1268.9	1269.8	1270.7	1271.0
132.5°	1316.2	1316.7	1317.4	1318.0	1318.5	1319.4	1320.6	1321.7	1323.0	1324.2	1324.5
135°	1393.0	1392.6	1392.3	1392.0	1391.7	1392.1	1393.5	1394.7	1396.0	1397.2	1397.9
137.5°	1460.9	1461.0	1461.1	1461.3	1461.4	1462.2	1463.6	1465.0	1466.3	1467.7	1468.4
140°	1505.2	1505.9	1506.6	1507.1	1507.8	1508.4	1509.0	1509.7	1510.3	1510.9	1511.9
142.5°	1545.0	1546.1	1547.4	1548.5	1549.6	1550.4	1550.8	1551.1	1551.5	1551.9	1552.6
145°	1606.2	1607.1	1608.1	1609.0	1610.0	1610.4	1610.4	1610.4	1610.4	1610.4	1610.7
147.5°	1654.8	1656.5	1658.3	1660.1	1661.9	1662.6	1662.3	1662.0	1661.6	1661.3	1661.6
150°	1690.1	1691.3	1692.5	1693.8	1695.1	1695.5	1695.3	1695.0	1694.6	1694.3	1694.3
152.5°	1719.6	1720.6	1721.6	1722.6	1723.6	1723.9	1723.3	1722.7	1722.1	1721.6	1722.1
155°	1761.1	1761.4	1761.7	1762.1	1762.4	1762.1	1761.1	1760.2	1759.3	1758.2	1759.5
157.5°	1796.1	1795.9	1795.7	1795.5	1795.4	1794.7	1793.6	1792.5	1791.5	1790.4	1792.1
160°	1816.6	1815.6	1814.7	1813.7	1812.8	1812.1	1811.8	1811.5	1811.2	1810.8	1812.8
162.5°	1834.8	1833.5	1832.3	1831.2	1829.9	1829.2	1828.8	1828.5	1828.2	1827.9	1829.8
165°	1857.8	1856.1	1854.6	1853.0	1851.4	1850.7	1850.7	1850.7	1850.7	1850.7	1853.1
167.5°	1875.9	1874.3	1872.6	1871.0	1869.3	1868.5	1868.3	1868.1	1867.9	1867.7	1870.5
170°	1886.2	1884.3	1882.4	1880.5	1878.6	1877.8	1878.1	1878.5	1878.8	1879.1	1881.6
172.5°	1893.0	1891.1	1889.2	1887.3	1885.5	1884.6	1885.0	1885.3	1885.6	1885.9	1888.4
175°	1900.4	1898.5	1896.6	1894.7	1892.8	1892.1	1892.3	1892.6	1893.0	1893.3	1896.1
177.5°	1903.8	1902.1	1900.3	1898.5	1896.8	1896.1	1896.6	1897.1	1897.6	1898.1	1900.2
180°	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4



TEST NUMBER: P332803-830

CATALOG NUMBER: S124DIW-S795D1560U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1251.2	1251.2	1251.2	1251.2	1251.2	1251.2	1251.2	1251.2
2.5°	1246.7	1248.5	1250.3	1251.1	1250.9	1250.8	1250.6	1250.4
5°	1240.0	1242.5	1244.9	1245.9	1245.5	1245.1	1244.6	1244.2
7.5°	1226.2	1228.2	1230.1	1231.0	1230.8	1230.5	1230.2	1229.9
10°	1214.7	1216.4	1218.2	1218.9	1218.4	1218.0	1217.6	1217.1
12.5°	1200.6	1202.5	1204.5	1205.1	1204.6	1203.9	1203.2	1202.7
15°	1173.7	1175.0	1176.3	1176.7	1176.0	1175.4	1174.7	1174.0
17.5°	1143.0	1143.9	1144.7	1144.9	1144.4	1144.0	1143.6	1143.1
20°	1120.2	1120.9	1121.5	1121.6	1121.2	1120.8	1120.3	1119.8
22.5°	1096.4	1097.6	1098.8	1099.0	1098.2	1097.4	1096.6	1095.8
25°	1057.2	1057.3	1057.6	1057.2	1056.4	1055.5	1054.6	1053.7
27.5°	1013.1	1012.6	1012.0	1011.3	1010.1	1009.0	1007.9	1006.7
30°	982.7	981.8	980.9	980.0	978.8	977.7	976.6	975.5
32.5°	951.9	950.8	949.8	948.7	947.5	946.4	945.3	944.2
35°	903.2	901.6	900.0	898.7	897.6	896.5	895.4	894.3
37.5°	852.2	850.5	848.9	847.3	845.7	844.3	842.8	841.3
40°	816.6	814.5	812.2	810.5	809.4	808.3	807.2	806.1
42.5°	782.2	779.7	777.0	775.4	774.7	773.9	773.2	772.4
45°	729.0	726.5	724.1	722.6	721.8	721.1	720.5	719.8
47.5°	677.4	674.7	671.8	669.7	668.0	666.3	664.6	662.9
50°	641.4	638.3	635.2	632.9	631.6	630.3	629.0	627.6
52.5°	604.5	601.6	598.9	596.7	595.0	593.3	591.6	589.9
55°	550.1	547.4	544.7	542.7	541.4	540.1	538.7	537.3
57.5°	495.6	493.0	490.5	488.6	487.3	486.0	484.7	483.4
60°	458.2	456.2	454.1	452.6	451.5	450.3	449.2	448.2
62.5°	421.6	419.8	418.0	416.5	415.4	414.2	413.2	412.1
65°	368.5	366.3	364.0	362.4	361.3	360.1	359.0	357.9
67.5°	313.8	311.6	309.4	308.2	307.9	307.6	307.3	307.0
70°	279.2	277.4	275.6	274.4	273.7	273.1	272.4	271.7
72.5°	244.6	243.2	241.8	240.7	240.0	239.3	238.7	238.0
75°	194.7	193.8	192.9	192.4	192.2	191.9	191.7	191.5
77.5°	147.4	147.1	146.9	146.5	145.9	145.3	144.8	144.2
80°	117.4	117.0	116.5	116.2	115.9	115.7	115.6	115.3
82.5°	90.5	90.2	89.9	89.7	89.5	89.3	89.1	88.8
85°	52.1	52.1	52.1	52.0	51.8	51.6	51.4	51.1
87.5°	26.3	26.7	27.1	27.2	27.4	27.5	27.6	27.8
90°	35.1	36.9	38.8	40.2	40.7	41.4	42.0	42.6
92.5°	33.9	35.8	37.7	38.7	38.8	39.0	39.1	39.2
95°	35.1	36.9	38.8	40.0	40.2	40.6	40.9	41.2
97.5°	37.9	38.1	38.3	38.5	38.8	39.2	39.5	39.8
100°	51.8	46.5	41.1	38.5	38.8	39.2	39.5	39.8
102.5°	185.5	127.5	69.7	40.7	40.7	40.8	40.9	40.9
105°	449.1	452.0	454.9	450.5	439.2	427.8	416.5	405.1
107.5°	555.7	557.1	558.5	559.8	561.0	562.1	563.4	564.6
110°	628.1	628.8	629.3	630.2	631.1	632.1	633.0	634.0



TEST NUMBER: P332803-830

CATALOG NUMBER: S124DIW-S795D1560U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	698.2	698.0	698.0	698.5	699.7	700.9	702.1	703.3
115°	803.0	803.5	804.2	804.6	804.6	804.6	804.6	804.6
117.5°	908.3	908.1	908.0	908.0	907.8	907.7	907.6	907.4
120°	973.5	974.1	974.8	974.8	974.1	973.5	972.9	972.2
122.5°	1037.8	1038.2	1038.6	1038.4	1037.8	1037.2	1036.5	1035.9
125°	1127.7	1128.6	1129.5	1130.2	1130.5	1130.8	1131.1	1131.4
127.5°	1216.9	1216.7	1216.5	1216.3	1216.1	1215.8	1215.5	1215.3
130°	1271.4	1271.7	1272.0	1272.1	1272.1	1272.1	1272.1	1272.1
132.5°	1324.8	1325.1	1325.4	1325.5	1325.2	1324.9	1324.7	1324.5
135°	1398.5	1399.1	1399.8	1400.4	1401.0	1401.7	1402.3	1402.9
137.5°	1469.1	1469.8	1470.6	1470.7	1470.6	1470.4	1470.2	1470.0
140°	1512.9	1513.8	1514.8	1515.3	1515.7	1516.0	1516.3	1516.6
142.5°	1553.3	1554.0	1554.6	1555.0	1555.1	1555.2	1555.2	1555.3
145°	1611.1	1611.4	1611.7	1612.2	1612.8	1613.4	1614.1	1614.7
147.5°	1661.8	1662.1	1662.4	1662.6	1662.9	1663.2	1663.6	1663.9
150°	1694.3	1694.3	1694.3	1694.5	1694.8	1695.1	1695.4	1695.7
152.5°	1722.6	1723.1	1723.6	1723.7	1723.5	1723.3	1723.2	1723.0
155°	1760.8	1762.1	1763.3	1763.5	1762.6	1761.6	1760.7	1759.7
157.5°	1793.7	1795.4	1797.0	1797.0	1795.4	1793.7	1792.1	1790.4
160°	1814.7	1816.6	1818.4	1818.4	1816.6	1814.7	1812.8	1810.8
162.5°	1831.7	1833.6	1835.5	1835.3	1833.2	1831.1	1828.9	1826.7
165°	1855.7	1858.2	1860.8	1860.6	1857.8	1854.9	1852.1	1849.3
167.5°	1873.3	1876.0	1878.9	1878.7	1875.5	1872.4	1869.2	1866.0
170°	1884.1	1886.7	1889.2	1888.9	1885.7	1882.5	1879.4	1876.2
172.5°	1890.9	1893.5	1896.0	1895.5	1892.2	1888.8	1885.4	1881.9
175°	1898.9	1901.9	1904.7	1904.2	1900.4	1896.6	1892.8	1889.0
177.5°	1902.1	1904.2	1906.2	1905.7	1902.7	1899.6	1896.6	1893.6
180°	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4

(END OF REPORT)